

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P175506

Luminaire Tested: **LDA6A20840D010TE LAR35FL 6LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P175506
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26295)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A20840D010TE LAR35FL 6LFC1
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 35° Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1762.0 lumens
Efficiency: N/A
Efficacy: 60.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.56
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 29.12
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P175506

CATALOG NUMBER: LDA6A20840D010TE LAR35FL 6LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P175506

CATALOG NUMBER: LDA6A20840D010TE LAR35FL 6LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	99	96	105	101	98	95	98	96	93	96	94	92	94	92	91	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	85	90	87	85	89	86	84	83		
6	97	90	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	82	79	85	82	79	84	81	79	83	81	78	77		
8	91	84	80	77	90	84	79	77	83	79	76	82	78	76	81	78	76	75		
9	88	81	77	74	87	81	77	74	80	76	74	79	76	73	79	76	73	72		
10	86	79	74	72	85	78	74	71	78	74	71	77	74	71	76	73	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	283859
5°	270883
10°	231425
15°	189473
20°	121268
25°	46720
30°	9577
35°	2543
40°	794
45°	256
50°	111
55°	67
60°	77
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P175506

CATALOG NUMBER: LDA6A20840D010TE LAR35FL 6LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	443.4	25.2
10°-20°	891.2	50.6
20°-30°	390.6	22.2
30°-40°	32.6	1.9
40°-50°	3.3	0.2
50°-60°	0.7	0.0
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1725.2	97.9
0°-40°	1757.8	99.8
0°-60°	1761.8	100.0
0°-90°	1762.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1762.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5178	
5°	4922	443
15°	3338	891
25°	772	391
35°	38	33
45°	3	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P175506

CATALOG NUMBER: LDA6A20840D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5178.0
1°	5153.1
2°	5112.5
3°	5066.0
4°	5007.1
5°	4922.5
6°	4802.0
7°	4646.1
8°	4475.1
9°	4312.6
10°	4157.4
11°	4001.5
12°	3849.5
13°	3691.6
14°	3523.9
15°	3338.5
17.5°	2768.5
20°	2078.7
22.5°	1357.4
25°	772.4
27.5°	359.7
30°	151.3
32.5°	78.6
35°	38.0
37.5°	20.3
40°	11.1
42.5°	5.9
45°	3.3
47.5°	2.0
50°	1.3
52.5°	0.7
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P175506

CATALOG NUMBER: LDA6A20840D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)