

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179813

Luminaire Tested: **LDA6A55830D010TE LARH40FL 6LFC1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P179813
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26683)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A55830D010TE LARH40FL 6LFC1H
Description: PORTFOLIO 6" Flat Cone, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5441.3 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.61
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 61
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P179813

CATALOG NUMBER: LDA6A55830D010TE LARH40FL 6LFC1H

Luminous Intensity Polar Plot





TEST NUMBER: P179813

CATALOG NUMBER: LDA6A55830D010TE LARH40FL 6LFC1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	104		103	101	100		99	98	98
2	110	107	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	97	94		98	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	88	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	92	85	81	77		91	85	80	77		83	80	77		82	79	76		81	78	76
8	89	82	77	74		88	81	77	74		80	77	74		80	76	73		79	76	73
9	86	79	74	71		85	78	74	71		78	74	71		77	73	71		76	73	70
10	84	76	72	69		83	76	71	68		75	71	68		74	71	68		74	70	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	742578
5°	670475
10°	610148
15°	557750
20°	407068
25°	200479
30°	43437
35°	8258
40°	2204
45°	969
50°	571
55°	459
60°	428
65°	376
70°	305
75°	212
80°	0
85°	0



TEST NUMBER: P179813

CATALOG NUMBER: LDA6A55830D010TE LARH40FL 6LFC1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1126.9	20.7
10°-20°	2639.9	48.5
20°-30°	1522.9	28.0
30°-40°	132.4	2.4
40°-50°	11.0	0.2
50°-60°	4.4	0.1
60°-70°	2.6	0.0
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5289.7	97.2
0°-40°	5422.2	99.6
0°-60°	5437.6	99.9
0°-90°	5441.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5441.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13546	
5°	12184	###
15°	9828	2640
25°	3314	1523
35°	123	132
45°	12	11
55°	5	4
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P179813

CATALOG NUMBER: LDA6A55830D010TE LARH40FL 6LFC1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	13545.7
2.5°	12866.3
5°	12183.9
7.5°	11545.9
10°	10960.9
12.5°	10456.9
15°	9827.5
17.5°	8760.6
20°	6977.7
22.5°	5051.1
25°	3314.4
27.5°	1717.4
30°	686.2
32.5°	360.4
35°	123.4
37.5°	51.1
40°	30.8
42.5°	19.3
45°	12.5
47.5°	7.7
50°	6.7
52.5°	5.8
55°	4.8
57.5°	3.9
60°	3.9
62.5°	2.9
65°	2.9
67.5°	1.9
70°	1.9
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)