

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192076

Luminaire Tested: **LDA6A25930D010TE LARL20NF 6LAL1 30° Tilt**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26268)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A25930D010TE LARL20NF 6LAL1 30° Tilt
Description: PORTFOLIO 6" Lensed Adjustable, Self-flange Trim Ring, 20° Narrow Flood Optic, at 30° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2345.2 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 2.7 / 0.43 / 1.35
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192076

CATALOG NUMBER: LDA6A25930D010TE LARL20NF 6LAL1 30° Tilt

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192076

CATALOG NUMBER: LDA6A25930D010TE LARL20NF 6LAL1 30° Tilt

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82		
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74		
4	92	83	76	71	90	82	75	70	79	74	70	77	72	69	75	71	68	66		
5	86	75	68	63	84	74	68	63	72	67	62	71	66	62	69	65	61	59		
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53		
7	74	63	56	50	73	62	55	50	61	55	50	59	54	50	58	53	49	48		
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	44	43		
9	65	53	46	41	63	52	45	41	51	45	40	50	44	40	49	44	40	39		
10	60	49	41	37	59	48	41	37	47	41	37	46	40	36	45	40	36	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	2905	2905	2905
5°	28208	2564	1057
10°	83426	1831	668
15°	165603	1249	568
20°	427189	1015	799
25°	744509	1216	5746
30°	967092	1272	3241
35°	866540	555	308
40°	640629	200	0
45°	288487	217	0
50°	130154	239	0
55°	11622	268	0
60°	1403	307	0
65°	597	480	0
70°	449	593	0
75°	0	784	0
80°	0	1168	284
85°	0	2327	566



TEST NUMBER: P1192076

CATALOG NUMBER: LDA6A25930D010TE LARL20NF 6LAL1 30° Tilt

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.1	0.9
10°-20°	197.5	8.4
20°-30°	779.7	33.2
30°-40°	940.9	40.1
40°-50°	365.2	15.6
50°-60°	32.1	1.4
60°-70°	3.1	0.1
70°-80°	2.9	0.1
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	998.3	42.6
0°-40°	1939.2	82.7
0°-60°	2336.5	99.6
0°-90°	2345.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2345.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	53	53	53	53	53	
5°	513	250	47	23	19	81
15°	2918	1104	22	14	10	1069
25°	12308	1306	20	64	95	5629
35°	12948	664	8	8	5	7959
45°	3721	47	3	2	0	3269
55°	122	6	3	2	0	293
65°	5	4	4	3	0	5
75°	0	4	4	4	0	1
85°	0	4	4	4	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192076

CATALOG NUMBER: LDA6A25930D010TE LARL20NF 6LAL1 30° Tilt

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0
2.5°	166.2	158.2	149.0	152.5	154.5	159.0	155.3	141.6	149.9	143.6	137.9
5°	512.6	503.5	486.3	488.9	483.4	489.8	475.2	446.0	451.4	442.3	418.5
7.5°	999.8	961.4	933.1	934.9	918.5	925.7	898.3	848.1	842.5	795.9	788.7
10°	1498.7	1479.5	1445.7	1441.2	1412.0	1415.5	1372.6	1305.9	1287.6	1233.8	1202.6
12.5°	1988.5	1956.6	1908.9	1898.9	1851.4	1852.3	1793.9	1718.9	1691.5	1635.7	1592.8
15°	2917.9	2872.1	2763.4	2722.4	2590.8	2570.6	2426.3	2256.2	2174.1	2078.0	1952.0
17.5°	4633.1	4603.9	4391.0	4273.2	4006.3	3741.2	3585.0	3217.6	3002.8	2734.2	2501.1
20°	7322.6	7376.5	7004.6	6741.4	6246.2	5686.9	5292.1	4623.1	4176.2	3712.9	3274.3
22.5°	10183.0	10205.8	9824.8	9496.7	8920.0	8151.4	7242.2	6430.7	5612.0	4815.9	4092.2
25°	12308.5	12242.7	11823.3	11429.4	10822.6	10037.7	9154.0	8070.1	6950.7	5857.7	4797.6
26°	12957.5	12921.7	12501.3	12029.8	11361.8	10564.9	9645.5	8551.8	7369.3	6192.1	5013.3
27°	13558.8	13535.9	13079.9	12555.3	11806.9	10972.5	10010.2	8917.2	7685.4	6450.8	5169.7
28°	14168.2	14142.6	13590.6	12982.1	12168.8	11262.3	10262.5	9161.2	7889.3	6602.6	5234.4
29°	14812.4	14763.1	14057.7	13295.6	12410.0	11431.3	10394.1	9272.7	7958.6	6640.0	5218.1
30°	15277.7	15200.8	14394.9	13493.8	12508.7	11484.3	10408.7	9270.1	7915.7	6562.3	5113.0
31°	15394.5	15316.9	14489.0	13491.0	12436.5	11403.9	10303.7	9140.3	7736.6	6374.1	4935.7
32°	15111.3	15040.0	14250.5	13183.2	12208.0	11210.2	10094.3	8900.0	7458.8	6092.6	4695.4
33°	14478.8	14425.0	13744.2	12778.2	11880.8	10935.0	9794.5	8558.1	7064.0	5734.4	4412.9
34°	13681.2	13641.8	13118.2	12302.1	11466.0	10557.7	9406.3	8107.6	6544.0	5328.5	4105.0
35°	12948.3	12918.9	12495.0	11771.2	10991.7	10090.6	8914.6	7552.9	6008.5	4891.7	3776.0
36°	12242.7	12218.0	11849.8	11177.3	10425.0	9543.3	8295.8	6889.5	5433.7	4438.5	3435.1
37°	11506.3	11484.3	11168.1	10528.3	9788.2	8888.9	7561.2	6183.0	4849.7	3986.2	3085.2
38°	10742.2	10723.9	10434.2	9796.5	9045.3	8089.3	6723.1	5452.9	4280.4	3544.9	2770.8
39°	9889.5	9874.0	9607.2	8938.3	8135.9	7147.2	5860.5	4741.0	3740.3	3116.1	2466.4
40°	8952.0	8930.9	8664.2	7916.5	7106.1	6177.5	5031.6	4087.6	3230.5	2715.9	2198.7
42.5°	6086.2	6063.4	5865.1	5430.0	4649.7	4052.9	3334.6	2736.0	2289.1	1979.3	1712.6
45°	3721.1	3723.9	3619.8	3351.0	2881.3	2549.7	2159.5	1873.4	1672.3	1553.6	1368.0
47.5°	2250.8	2250.8	2204.1	2067.1	1856.0	1723.5	1561.7	1428.3	1274.7	1157.8	956.8
50°	1526.1	1527.0	1455.8	1463.0	1322.4	1240.1	1085.6	922.9	772.1	602.2	429.4
51°	1129.4	1135.1	1069.3	1099.3	944.9	875.4	729.2	591.3	457.8	326.2	188.2
52°	690.9	700.9	656.2	683.6	593.9	492.6	373.8	276.0	185.4	129.8	90.4
53°	320.7	329.0	306.1	318.9	266.0	207.4	157.1	127.9	102.4	83.2	61.2
54°	169.9	171.9	164.5	160.8	146.2	128.8	107.0	88.7	69.5	55.8	41.2
55°	121.6	121.6	117.9	114.2	102.4	87.8	71.2	60.3	45.7	36.6	26.6
57.5°	37.5	37.5	37.5	35.7	31.1	26.6	20.9	18.3	14.6	13.7	10.9
60°	12.8	12.8	12.8	12.0	10.9	10.0	9.1	8.3	7.4	7.4	6.3
61°	9.1	9.1	9.1	9.1	8.3	8.3	7.4	6.3	5.5	6.3	5.5
62°	7.4	8.3	7.4	7.4	7.4	6.3	5.5	5.5	4.6	5.5	4.6
63°	6.3	6.3	6.3	6.3	5.5	5.5	4.6	4.6	3.7	4.6	4.6
64°	5.5	5.5	5.5	5.5	4.6	4.6	3.7	3.7	2.8	3.7	3.7
65°	4.6	4.6	4.6	4.6	3.7	3.7	3.7	2.8	2.8	3.7	3.7
66°	3.7	3.7	3.7	3.7	3.7	2.8	2.8	2.8	1.8	2.8	2.8

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192076

CATALOG NUMBER: LDA6A25930D010TE LARL20NF 6LAL1 30° Tilt

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
72.5°	1.8	1.8	1.8	1.8	0.9	0.9	0.9	0.9	0.9	1.8	1.8
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.9	0.9
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.9	0.9
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.9	0.9
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.9	0.9
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.9	0.9
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192076

CATALOG NUMBER: LDA6A25930D010TE LARL20NF 6LAL1 30° Tilt

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	67.5°	90°	112.5°
0°	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0
2.5°	132.5	123.3	121.6	121.6	102.4	106.1	99.6	95.0	66.7	51.2	38.4
5°	404.8	371.9	358.2	346.4	294.3	289.7	257.7	250.3	89.5	46.6	29.2
7.5°	754.9	704.6	672.6	641.6	557.5	534.6	479.7	466.0	121.6	39.2	22.9
10°	1153.4	1081.0	1025.3	951.4	842.5	795.0	714.6	685.4	148.1	32.9	22.0
12.5°	1527.9	1445.7	1369.9	1272.1	1124.9	1049.0	943.1	905.7	158.2	27.4	20.1
15°	1851.4	1741.8	1647.7	1542.5	1378.0	1282.1	1152.3	1103.9	149.9	22.0	17.4
17.5°	2261.8	2076.2	1912.6	1765.6	1586.5	1469.5	1318.7	1240.1	121.6	19.2	15.5
20°	2868.6	2494.8	2207.0	1969.3	1720.7	1575.4	1408.3	1313.3	87.8	17.4	15.5
22.5°	3439.7	2906.1	2464.7	2124.6	1790.2	1616.6	1442.9	1337.9	62.1	17.4	18.3
25°	3905.8	3215.9	2642.9	2227.0	1828.5	1624.8	1430.1	1305.9	48.4	20.1	35.7
26°	4036.4	3292.6	2677.6	2235.3	1823.1	1612.9	1408.3	1276.7	42.9	27.4	66.7
27°	4117.8	3327.2	2678.4	2222.4	1803.0	1589.1	1375.4	1237.3	37.5	42.0	112.4
28°	4134.2	3310.9	2647.5	2186.9	1768.2	1557.3	1338.8	1189.8	34.7	53.0	127.9
29°	4089.5	3252.3	2590.8	2134.7	1726.3	1518.7	1295.0	1137.7	30.1	40.3	83.2
30°	3988.9	3155.5	2507.6	2068.0	1681.5	1475.8	1241.0	1075.6	24.6	20.1	37.5
31°	3838.1	3022.0	2405.2	1989.5	1631.2	1421.1	1176.0	1006.1	20.9	13.7	22.0
32°	3647.1	2862.1	2291.0	1908.9	1574.5	1354.3	1100.2	928.5	19.2	10.9	18.3
33°	3427.9	2694.1	2173.2	1827.7	1507.0	1274.7	1018.9	845.3	17.4	12.0	18.3
34°	3188.4	2522.2	2039.7	1742.7	1428.3	1188.0	932.0	747.5	15.5	10.9	13.7
35°	2928.9	2344.0	1920.0	1667.8	1339.7	1093.9	843.6	664.3	13.7	8.3	9.1
36°	2705.0	2170.4	1803.9	1572.8	1242.9	997.0	752.1	574.7	12.0	5.5	6.3
37°	2461.0	2007.6	1696.1	1474.1	1138.6	897.4	660.8	486.3	10.9	3.7	5.5
38°	2233.3	1857.9	1588.2	1360.8	1031.8	796.9	567.5	399.3	10.0	3.7	4.6
39°	2027.0	1721.8	1487.8	1240.1	919.4	691.7	473.4	313.5	9.1	2.8	4.6
40°	1849.7	1600.2	1367.1	1113.1	803.3	587.6	379.3	232.0	8.3	2.8	4.6
42.5°	1504.1	1283.9	1031.8	786.9	520.0	332.7	169.9	85.0	6.3	2.8	3.7
45°	1149.7	913.9	680.8	473.4	267.8	128.8	63.0	46.6	5.5	2.8	3.7
47.5°	746.6	548.4	365.6	206.5	89.5	52.1	32.9	23.7	4.6	2.8	3.7
50°	276.0	152.5	80.4	50.3	34.7	22.0	14.6	13.7	4.6	2.8	3.7
51°	113.3	74.1	50.3	33.8	22.0	15.5	12.0	12.0	4.6	2.8	3.7
52°	67.6	46.6	33.8	24.6	16.5	12.0	9.1	10.0	4.6	2.8	3.7
53°	44.9	32.0	24.6	19.2	12.8	9.1	6.3	7.4	4.6	2.8	3.7
54°	30.1	22.9	18.3	14.6	9.1	7.4	3.7	6.3	3.7	2.8	3.7
55°	20.9	16.5	13.7	10.9	6.3	4.6	2.8	5.5	3.7	2.8	3.7
57.5°	9.1	8.3	7.4	6.3	2.8	1.8	0.9	4.6	3.7	2.8	3.7
60°	6.3	5.5	4.6	4.6	0.9	0.9	0.0	3.7	3.7	2.8	3.7
61°	5.5	4.6	4.6	3.7	0.9	0.9	0.0	3.7	4.6	2.8	3.7
62°	4.6	4.6	3.7	3.7	0.9	0.0	0.0	3.7	4.6	2.8	4.6
63°	3.7	3.7	3.7	3.7	0.9	0.0	0.0	3.7	4.6	2.8	4.6
64°	3.7	3.7	3.7	3.7	0.0	0.0	0.0	3.7	4.6	2.8	4.6
65°	3.7	2.8	2.8	2.8	0.0	0.0	0.0	3.7	4.6	3.7	4.6
66°	2.8	2.8	2.8	2.8	0.0	0.0	0.0	3.7	4.6	3.7	4.6

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192076

CATALOG NUMBER: LDA6A25930D010TE LARL20NF 6LAL1 30° Tilt

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	67.5°	90°	112.5°
72.5°	1.8	1.8	1.8	1.8	0.0	0.0	0.0	2.8	4.6	3.7	5.5
75°	0.9	1.8	1.8	1.8	0.0	0.0	0.0	3.7	4.6	3.7	5.5
77.5°	0.9	1.8	1.8	1.8	0.0	0.0	0.0	3.7	4.6	3.7	5.5
80°	0.9	1.8	1.8	1.8	0.0	0.0	0.0	3.7	4.6	3.7	5.5
82.5°	0.9	1.8	1.8	1.8	0.0	0.0	0.0	3.7	4.6	3.7	5.5
85°	0.9	1.8	1.8	1.8	0.0	0.0	0.0	3.7	4.6	3.7	5.5
87.5°	0.9	1.8	1.8	1.8	0.0	0.0	0.0	3.7	4.6	3.7	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192076

CATALOG NUMBER: LDA6A25930D010TE LARL20NF 6LAL1 30° Tilt

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
0°	53.0	53.0	53.0
2.5°	32.0	29.2	27.4
5°	22.9	20.9	19.2
7.5°	19.2	16.5	15.5
10°	17.4	12.8	12.0
12.5°	14.6	10.9	10.0
15°	13.7	10.9	10.0
17.5°	13.7	10.9	10.0
20°	14.6	13.7	13.7
22.5°	20.9	22.9	23.7
25°	64.0	82.3	95.0
26°	149.9	224.8	301.5
27°	227.5	331.8	353.6
28°	204.8	237.7	231.2
29°	98.7	111.5	101.5
30°	43.8	52.1	51.2
31°	28.3	32.0	31.1
32°	23.7	22.0	20.9
33°	19.2	15.5	12.8
34°	12.8	10.0	8.3
35°	8.3	5.5	4.6
36°	5.5	2.8	1.8
37°	3.7	1.8	0.9
38°	3.7	0.9	0.0
39°	2.8	0.9	0.0
40°	2.8	0.9	0.0
42.5°	2.8	0.0	0.0
45°	1.8	0.0	0.0
47.5°	1.8	0.0	0.0
50°	2.8	0.9	0.0
51°	2.8	0.0	0.0
52°	2.8	0.0	0.0
53°	1.8	0.0	0.0
54°	1.8	0.0	0.0
55°	1.8	0.0	0.0
57.5°	1.8	0.0	0.0
60°	1.8	0.0	0.0
61°	2.8	0.0	0.0
62°	2.8	0.0	0.0
63°	2.8	0.0	0.0
64°	2.8	0.9	0.0
65°	2.8	0.9	0.0
66°	2.8	0.9	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P1192076

CATALOG NUMBER: LDA6A25930D010TE LARL20NF 6LAL1 30° Tilt

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
72.5°	3.7	0.9	0.0
75°	3.7	0.9	0.0
77.5°	3.7	0.9	0.0
80°	3.7	1.8	0.9
82.5°	3.7	1.8	0.9
85°	3.7	1.8	0.9
87.5°	3.7	1.8	0.9
90°	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°	2.8	2.8	2.8	2.8	2.8	2.8	1.8	1.8	1.8	2.8	2.8
70°	2.8	2.8	1.8	1.8	1.8	1.8	1.8	0.9	0.9	2.8	2.8

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°	2.8	2.8	2.8	2.8	0.0	0.0	0.0	3.7	4.6	3.7	4.6
70°	2.8	2.8	2.8	2.8	0.0	0.0	0.0	3.7	4.6	3.7	5.5

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°	3.7	0.9	0.0
70°	3.7	0.9	0.0

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)