

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192499

Luminaire Tested: **LDA6A55950D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192499
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26690)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A55950D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5165.9 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 2.55 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192499

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192499

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	75	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65		
5	85	74	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	52046	52046	52046
5°	134377	48244	15078
10°	254916	36806	5066
15°	455820	23927	5045
20°	679199	16276	9206
25°	774982	20306	57802
30°	838104	16958	17281
35°	880386	8252	5407
40°	894297	2963	2748
45°	796780	1969	1651
50°	511727	1382	1126
55°	134724	965	573
60°	30041	1009	450
65°	2880	1193	532
70°	962	1475	657
75°	212	1949	1080
80°	0	3189	1610
85°	0	5787	2579



TEST NUMBER: P1192499

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	2.2
10°-20°	601.8	11.6
20°-30°	1412.0	27.3
30°-40°	1624.1	31.4
40°-50°	1153.7	22.3
50°-60°	234.6	4.5
60°-70°	11.8	0.2
70°-80°	7.0	0.1
80°-90°	5.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2129.0	41.2
0°-40°	3753.1	72.7
0°-60°	5141.3	99.5
0°-90°	5165.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5165.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	949	949	949	949	949	
5°	2442	1766	877	351	274	298
15°	8032	3611	422	95	89	2409
25°	12812	4349	336	733	956	5905
35°	13155	3054	123	91	81	8172
45°	10277	1086	25	27	21	7574
55°	1410	28	10	10	6	1901
65°	22	8	9	8	4	54
75°	1	5	9	8	5	2
85°	0	5	9	7	4	0
90°	0	0	0	0	0	

TEST NUMBER: P1192499

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	949.4	949.4	949.4	949.4	949.4	949.4	949.4	949.4	949.4	949.4	949.4
2.5°	1636.0	1586.5	1562.2	1561.1	1490.4	1513.6	1490.4	1472.2	1406.5	1379.1	1333.7
5°	2441.9	2381.2	2332.7	2311.5	2190.1	2163.9	2151.8	2090.0	1952.5	1872.6	1766.4
7.5°	3392.4	3328.7	3248.8	3185.2	3009.1	2959.6	2927.3	2821.1	2617.8	2457.1	2258.9
10°	4579.4	4542.1	4412.6	4295.3	4028.4	3925.3	3828.2	3580.4	3314.6	2992.1	2736.1
12.5°	6178.1	6090.1	5859.7	5625.0	5206.3	5052.7	4892.0	4495.5	4089.2	3583.5	3160.9
15°	8031.5	7956.7	7601.8	7219.6	6624.1	6371.2	6119.5	5495.6	4870.6	4219.5	3610.9
17.5°	10165.1	10023.5	9670.6	9024.5	8191.4	7793.9	7324.7	6530.1	5628.1	4743.3	3986.9
20°	11642.4	11558.5	11260.2	10640.3	9691.9	9167.1	8584.7	7493.7	6260.0	5162.9	4233.7
22.5°	12450.3	12366.3	12142.9	11595.9	10818.3	10291.4	9615.0	8273.2	6737.2	5445.0	4349.9
25°	12812.3	12757.7	12635.3	12189.4	11469.5	10995.3	10355.2	8812.1	7035.6	5573.5	4349.0
27.5°	13147.1	13161.1	12858.9	12491.8	11828.4	11352.1	10745.5	9054.9	7094.3	5508.8	4209.4
30°	13240.0	13204.7	13072.2	12555.4	11937.6	11419.0	10768.7	8926.4	6865.8	5222.6	3932.3
32.5°	13182.4	13183.4	13059.1	12510.0	11783.9	11203.5	10472.4	8466.3	6420.8	4773.6	3501.6
35°	13155.2	13146.0	12823.5	12341.2	11419.0	10736.4	9815.2	7728.2	5804.0	4200.2	3053.6
37.5°	12884.0	12829.4	12596.9	11942.7	10736.4	9863.8	8871.8	6825.3	5044.6	3603.8	2594.6
40°	12496.7	12428.1	12050.0	11111.5	9569.5	8595.8	7609.9	5803.0	4249.9	3010.2	2083.0
42.5°	11703.1	11589.8	11016.5	9771.7	8067.0	7161.0	6344.0	4779.6	3474.2	2444.0	1599.7
45°	10277.4	10092.3	9298.5	7998.2	6511.8	5801.0	5110.4	3831.3	2781.7	1820.1	1086.0
47.5°	8252.0	8049.8	7329.8	6285.3	5098.3	4521.9	3935.4	2821.1	1881.8	1060.7	545.1
50°	6000.2	5860.6	5224.6	4343.9	3371.2	2887.9	2437.9	1573.3	902.9	512.6	223.4
52.5°	3457.2	3357.0	2914.1	2286.1	1658.3	1388.3	1116.3	686.6	460.0	203.2	71.9
55°	1409.6	1351.9	1157.8	980.7	736.1	636.1	530.8	342.8	154.8	48.6	28.3
57.5°	689.6	682.6	569.3	455.9	335.7	270.9	204.3	68.8	37.4	24.3	18.2
60°	274.0	263.8	181.0	105.1	58.7	47.5	40.5	28.3	21.3	16.2	13.2
62.5°	47.5	46.5	39.4	33.4	27.2	24.3	22.2	17.3	14.1	11.1	10.1
65°	22.2	22.2	20.3	18.2	15.2	14.1	13.2	11.1	9.2	8.1	8.1
67.5°	11.1	11.1	10.1	9.2	8.1	8.1	7.1	7.1	6.0	6.0	6.0
70°	6.0	6.0	6.0	5.1	5.1	5.1	5.1	5.1	4.1	5.1	5.1
72.5°	4.1	4.1	4.1	3.0	2.0	3.0	3.0	3.0	4.1	5.1	5.1
75°	1.0	1.0	1.0	2.0	2.0	2.0	3.0	3.0	4.1	5.1	5.1
77.5°	1.0	1.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	5.1	5.1
80°	0.0	1.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	5.1	5.1
82.5°	0.0	0.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	5.1	5.1
85°	0.0	0.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	5.1	5.1
87.5°	0.0	0.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	5.1	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192499

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	949.4	949.4	949.4	949.4	949.4	949.4	949.4	949.4	949.4	949.4	949.4
2.5°	1313.5	1260.9	1226.5	1165.8	1140.6	1129.4	1073.9	1020.2	968.7	931.3	873.7
5°	1685.6	1601.7	1473.3	1352.9	1300.3	1267.0	1157.8	1056.6	960.6	876.7	776.6
7.5°	2085.9	1913.1	1711.8	1518.7	1427.7	1367.0	1198.2	1050.6	913.1	785.7	649.1
10°	2470.2	2198.2	1905.0	1629.0	1505.6	1414.5	1194.1	1005.1	826.2	661.2	514.7
12.5°	2797.9	2446.0	2056.7	1698.7	1538.0	1421.7	1156.8	926.2	708.8	531.9	404.5
15°	3073.9	2636.1	2156.8	1722.0	1528.8	1391.3	1083.9	818.1	580.4	421.6	326.6
17.5°	3268.1	2728.0	2179.9	1682.6	1465.2	1306.4	973.8	679.5	455.9	340.8	257.9
20°	3381.2	2740.2	2123.5	1586.5	1354.0	1186.0	835.2	533.9	370.0	279.0	200.2
22.5°	3398.5	2680.6	2012.2	1457.1	1225.4	1063.7	695.8	447.0	336.8	260.9	196.1
25°	3315.6	2562.4	1867.6	1330.7	1109.3	943.4	601.5	452.0	378.1	335.7	348.9
27.5°	3154.7	2367.1	1701.9	1201.3	987.9	820.0	568.3	473.2	412.5	419.6	443.9
30°	2908.0	2092.1	1463.1	981.9	756.3	624.9	452.0	340.8	283.1	267.9	268.9
32.5°	2545.1	1747.3	1148.7	681.5	508.6	421.6	286.1	190.1	191.2	176.9	175.9
35°	2130.5	1406.5	859.5	457.0	351.9	293.3	168.8	133.4	128.3	123.3	116.4
37.5°	1720.0	1086.9	572.3	312.5	224.4	162.9	84.9	69.8	64.8	60.7	60.7
40°	1309.5	760.3	353.9	163.8	91.0	66.8	50.5	42.4	41.4	41.4	40.5
42.5°	950.5	449.0	192.1	64.8	50.5	44.5	35.4	31.3	31.3	31.3	31.3
45°	505.5	228.5	73.7	40.5	33.4	31.3	26.2	24.3	24.3	25.4	25.4
47.5°	233.6	85.9	37.4	27.2	23.3	23.3	20.3	19.2	19.2	20.3	20.3
50°	83.9	35.4	24.3	19.2	17.3	18.2	16.2	15.2	16.2	16.2	16.2
52.5°	32.3	22.2	17.3	15.2	13.2	14.1	12.2	12.2	13.2	13.2	13.2
55°	20.3	16.2	13.2	11.1	10.1	11.1	10.1	10.1	10.1	10.1	10.1
57.5°	14.1	12.2	10.1	9.2	8.1	9.2	9.2	9.2	9.2	9.2	9.2
60°	11.1	9.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	9.2	9.2
62.5°	9.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2
65°	8.1	7.1	8.1	8.1	7.1	8.1	8.1	8.1	9.2	9.2	10.1
67.5°	6.0	6.0	6.0	7.1	7.1	7.1	8.1	8.1	9.2	9.2	9.2
70°	6.0	6.0	7.1	7.1	7.1	7.1	8.1	8.1	9.2	9.2	9.2
72.5°	6.0	6.0	7.1	7.1	7.1	8.1	8.1	8.1	9.2	9.2	9.2
75°	6.0	6.0	7.1	7.1	7.1	8.1	8.1	8.1	9.2	9.2	9.2
77.5°	6.0	6.0	7.1	7.1	7.1	8.1	8.1	9.2	9.2	9.2	9.2
80°	6.0	7.1	7.1	8.1	8.1	8.1	8.1	9.2	9.2	10.1	10.1
82.5°	6.0	7.1	7.1	8.1	8.1	8.1	8.1	9.2	9.2	10.1	10.1
85°	6.0	7.1	7.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2
87.5°	6.0	7.1	7.1	8.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192499

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	949.4	949.4	949.4	949.4	949.4	949.4	949.4	949.4	949.4	949.4	949.4
2.5°	835.2	785.7	736.1	711.9	690.7	660.3	621.8	590.5	557.1	540.0	500.6
5°	697.6	612.8	541.0	506.6	480.3	443.9	404.5	376.2	350.9	336.8	311.4
7.5°	540.0	459.1	396.4	370.0	350.9	314.4	285.2	255.8	229.5	210.4	185.0
10°	417.6	355.0	303.4	278.1	256.9	218.4	183.0	155.8	127.4	108.3	100.2
12.5°	331.7	273.0	220.4	195.2	172.8	133.4	107.2	102.1	97.0	95.1	92.0
15°	254.8	201.2	145.6	120.2	111.3	106.2	100.2	99.1	95.1	95.1	92.0
17.5°	191.2	131.5	111.3	109.2	108.3	106.2	103.2	102.1	101.1	101.1	100.2
20°	137.5	127.4	124.3	126.4	127.4	129.4	128.3	128.3	132.4	141.5	139.6
22.5°	193.1	209.4	226.5	232.5	254.8	277.1	297.3	322.5	382.2	451.0	467.2
25°	382.2	430.8	475.3	499.5	535.9	585.5	633.0	691.7	733.1	767.4	806.8
27.5°	475.3	493.5	486.4	489.4	485.4	478.3	480.3	492.4	486.4	468.1	475.3
30°	281.1	295.3	287.1	291.2	280.1	280.1	277.1	283.1	279.0	272.0	270.0
32.5°	183.0	191.2	190.1	190.1	186.1	184.0	176.9	174.9	167.8	154.8	151.7
35°	110.2	105.1	100.2	97.0	95.1	95.1	94.0	94.0	91.0	88.0	86.9
37.5°	59.7	60.7	60.7	60.7	60.7	62.7	61.7	61.7	61.7	59.7	59.7
40°	41.4	43.5	43.5	43.5	44.5	44.5	44.5	45.4	44.5	44.5	44.5
42.5°	32.3	33.4	32.3	32.3	33.4	33.4	33.4	34.3	34.3	34.3	33.4
45°	26.2	26.2	25.4	26.2	26.2	27.2	27.2	27.2	27.2	26.2	26.2
47.5°	21.3	21.3	21.3	21.3	22.2	22.2	22.2	22.2	22.2	22.2	22.2
50°	17.3	17.3	17.3	18.2	18.2	18.2	17.3	18.2	18.2	18.2	17.3
52.5°	13.2	13.2	13.2	13.2	13.2	12.2	12.2	12.2	12.2	12.2	11.1
55°	10.1	10.1	10.1	10.1	10.1	11.1	10.1	11.1	10.1	10.1	9.2
57.5°	9.2	9.2	9.2	9.2	10.1	10.1	9.2	9.2	9.2	8.1	8.1
60°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	8.1	7.1	7.1
62.5°	10.1	10.1	9.2	9.2	9.2	9.2	8.1	8.1	8.1	7.1	7.1
65°	10.1	10.1	9.2	10.1	10.1	9.2	9.2	8.1	8.1	7.1	7.1
67.5°	10.1	10.1	10.1	10.1	10.1	10.1	9.2	9.2	8.1	8.1	7.1
70°	10.1	10.1	10.1	10.1	10.1	10.1	9.2	9.2	8.1	8.1	7.1
72.5°	10.1	10.1	10.1	10.1	10.1	10.1	9.2	9.2	9.2	8.1	7.1
75°	10.1	10.1	10.1	10.1	10.1	9.2	9.2	9.2	8.1	8.1	7.1
77.5°	10.1	10.1	10.1	10.1	10.1	9.2	9.2	9.2	8.1	8.1	7.1
80°	10.1	10.1	10.1	10.1	10.1	10.1	9.2	9.2	8.1	8.1	7.1
82.5°	10.1	10.1	10.1	10.1	10.1	9.2	9.2	9.2	8.1	8.1	7.1
85°	10.1	9.2	9.2	9.2	9.2	9.2	8.1	8.1	7.1	7.1	6.0
87.5°	9.2	9.2	9.2	9.2	9.2	8.1	8.1	7.1	6.0	5.1	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192499

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	949.4	949.4	949.4	949.4	949.4	949.4	949.4	949.4
2.5°	500.6	491.4	487.3	480.3	474.2	471.2	460.0	473.2
5°	306.4	295.3	292.2	286.1	279.0	275.0	266.9	274.0
7.5°	174.9	161.8	155.8	150.7	143.6	137.5	130.4	134.5
10°	98.1	94.0	95.1	92.0	91.0	90.0	88.9	91.0
12.5°	91.0	88.0	88.9	86.9	85.9	85.9	84.9	85.9
15°	92.0	88.9	91.0	88.9	88.0	88.0	86.9	88.9
17.5°	100.2	98.1	100.2	98.1	99.1	98.1	99.1	100.2
20°	140.5	143.6	149.7	145.6	148.6	152.7	157.8	157.8
22.5°	494.5	559.1	567.2	599.6	682.6	679.5	735.2	737.2
25°	863.5	867.6	904.0	891.8	892.8	935.3	931.3	955.6
27.5°	496.5	495.5	502.6	489.4	493.5	496.5	485.4	498.6
30°	277.1	272.0	275.0	267.9	267.9	270.0	266.9	273.0
32.5°	153.7	149.7	149.7	144.6	143.6	142.6	139.6	142.6
35°	88.0	84.9	85.9	83.9	81.8	80.8	79.9	80.8
37.5°	60.7	58.7	59.7	57.6	55.6	54.6	53.6	54.6
40°	44.5	43.5	43.5	41.4	40.5	39.4	38.4	38.4
42.5°	33.4	32.3	32.3	30.3	29.3	28.3	27.2	28.3
45°	25.4	24.3	24.3	23.3	22.2	21.3	21.3	21.3
47.5°	22.2	21.3	22.2	21.3	20.3	20.3	20.3	20.3
50°	17.3	17.3	17.3	16.2	15.2	15.2	14.1	13.2
52.5°	11.1	10.1	10.1	9.2	9.2	8.1	8.1	8.1
55°	9.2	8.1	8.1	7.1	7.1	6.0	6.0	6.0
57.5°	7.1	7.1	6.0	6.0	5.1	5.1	5.1	5.1
60°	6.0	6.0	6.0	5.1	5.1	4.1	4.1	4.1
62.5°	6.0	5.1	5.1	5.1	4.1	4.1	4.1	4.1
65°	6.0	5.1	5.1	5.1	4.1	4.1	4.1	4.1
67.5°	6.0	5.1	5.1	5.1	4.1	4.1	4.1	4.1
70°	7.1	6.0	6.0	5.1	5.1	5.1	4.1	4.1
72.5°	7.1	6.0	6.0	6.0	5.1	5.1	5.1	5.1
75°	7.1	6.0	6.0	6.0	5.1	5.1	5.1	5.1
77.5°	7.1	6.0	6.0	6.0	5.1	5.1	5.1	5.1
80°	7.1	6.0	6.0	6.0	5.1	5.1	5.1	5.1
82.5°	6.0	6.0	6.0	5.1	5.1	5.1	5.1	5.1
85°	6.0	5.1	5.1	5.1	4.1	4.1	4.1	4.1
87.5°	4.1	4.1	3.0	3.0	3.0	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)