

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192505

Luminaire Tested: **LDA6A55950D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192505
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A55950D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5434.8 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192505

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192505

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	50	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	40	38		
10	60	48	41	37	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	58038	58038	58038
5°	154028	53808	20587
10°	336211	43514	6134
15°	507489	31788	5335
20°	590320	21824	8377
25°	651032	23548	55787
30°	720288	17731	17344
35°	730994	9068	6492
40°	747801	3693	3113
45°	754078	2272	1884
50°	635237	1552	1203
55°	209809	1061	679
60°	41247	1009	450
65°	4851	1310	532
70°	1298	1475	657
75°	212	1949	1080
80°	0	3189	1610
85°	0	6353	2579

TEST NUMBER: P1192505

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.9	2.6
10°-20°	711.5	13.1
20°-30°	1404.3	25.8
30°-40°	1584.0	29.1
40°-50°	1257.5	23.1
50°-60°	307.5	5.7
60°-70°	16.4	0.3
70°-80°	7.0	0.1
80°-90°	5.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2256.6	41.5
0°-40°	3840.6	70.7
0°-60°	5405.6	99.5
0°-90°	5434.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5434.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1059	1059	1059	1059	1059	
5°	2799	2097	978	492	374	370
15°	8942	4753	560	110	94	2508
25°	10763	5761	389	705	922	4985
35°	10923	3667	136	107	97	6869
45°	9727	1143	29	30	24	7290
55°	2195	50	11	11	7	2575
65°	37	9	10	8	4	91
75°	1	5	9	8	5	3
85°	0	5	10	7	4	0
90°	0	0	0	0	0	

TEST NUMBER: P1192505

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7
2.5°	1837.4	1801.9	1818.1	1792.9	1721.0	1698.8	1716.9	1689.7	1607.8	1576.4	1544.1
5°	2799.0	2767.5	2777.7	2720.0	2585.5	2539.1	2536.0	2453.2	2287.3	2194.3	2097.2
7.5°	4244.0	4200.6	4188.4	4049.9	3790.9	3693.9	3646.3	3442.1	3129.7	2908.2	2690.8
10°	6039.8	6082.2	6038.8	5814.3	5407.8	5225.8	5110.6	4724.3	4161.0	3739.3	3332.9
12.5°	7840.8	7867.0	7785.1	7506.1	6989.3	6770.9	6601.1	6106.6	5364.3	4648.4	4041.8
15°	8941.9	9066.3	8989.4	8794.3	8393.8	8129.0	7976.3	7365.5	6431.2	5644.4	4752.6
17.5°	9726.6	9841.8	9778.2	9618.4	9166.4	8952.9	8854.0	8351.4	7334.1	6334.0	5284.4
20°	10118.9	10259.5	10201.9	10020.8	9689.2	9511.2	9390.9	8900.5	7983.4	6846.7	5639.4
22.5°	10384.9	10540.7	10477.9	10313.1	9975.4	9768.1	9711.5	9247.3	8323.1	7154.2	5790.0
25°	10763.1	10893.5	10716.6	10513.4	10179.6	9961.2	9926.8	9452.6	8485.9	7270.4	5760.8
27.5°	11034.1	11188.8	10888.5	10682.3	10300.9	10071.4	10027.0	9581.1	8501.1	7178.5	5523.1
30°	11378.8	11278.8	11015.0	10715.5	10309.0	10064.3	10007.7	9506.1	8349.3	6839.8	5058.0
32.5°	11242.4	11218.1	10954.2	10602.3	10223.1	9976.3	9900.6	9275.7	7932.8	6255.2	4399.6
35°	10922.9	10999.7	10779.2	10560.8	10089.7	9832.8	9727.5	8935.9	7304.9	5502.8	3666.6
37.5°	10735.7	10784.3	10644.7	10377.8	9910.7	9573.0	9373.7	8364.5	6482.7	4554.4	2959.7
40°	10449.6	10573.0	10438.5	10132.1	9593.1	9130.1	8783.1	7332.1	5399.8	3590.7	2314.6
42.5°	10136.2	10246.4	10118.0	9750.9	8989.4	8368.6	7792.2	6118.7	4227.8	2743.4	1736.2
45°	9726.6	9825.7	9595.1	9023.9	7945.8	7089.4	6514.0	4805.2	3188.3	2015.3	1142.6
47.5°	8988.5	8962.1	8635.5	7747.8	6420.0	5652.5	4983.1	3442.1	2119.4	1141.6	568.3
50°	7448.4	7202.7	6722.4	5691.9	4308.6	3479.5	3022.4	1776.6	961.7	553.1	357.0
52.5°	4824.5	4550.3	4110.4	3158.9	2068.9	1660.4	1331.7	802.9	501.6	312.5	140.5
55°	2195.2	2001.1	1720.1	1276.1	887.7	738.2	624.9	406.5	268.9	116.4	49.5
57.5°	836.3	771.6	685.6	547.1	410.5	355.0	294.3	195.2	83.9	43.5	29.3
60°	376.2	348.9	320.5	250.8	175.9	126.4	96.1	52.6	35.4	25.4	19.2
62.5°	128.3	107.2	88.9	63.8	47.5	41.5	36.4	29.3	21.3	17.3	13.2
65°	37.4	36.4	34.3	30.3	24.3	22.2	21.3	17.3	13.2	11.1	9.2
67.5°	18.2	17.3	16.2	15.2	12.2	11.1	11.1	10.1	8.1	7.1	6.0
70°	8.1	8.1	7.1	7.1	6.0	6.0	6.0	5.1	5.1	5.1	5.1
72.5°	4.1	4.1	4.1	3.0	3.0	3.0	3.0	4.1	4.1	5.1	5.1
75°	1.0	2.0	2.0	2.0	2.0	3.0	3.0	4.1	4.1	5.1	5.1
77.5°	1.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	4.1	5.1	5.1
80°	0.0	1.0	1.0	2.0	2.0	2.0	3.0	3.0	4.1	5.1	5.1
82.5°	0.0	1.0	1.0	2.0	2.0	2.0	3.0	3.0	4.1	5.1	5.1
85°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.1	5.1
87.5°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.1	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192505

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7
2.5°	1465.2	1443.9	1360.1	1295.3	1265.1	1263.0	1195.2	1153.8	1080.9	1024.4	970.7
5°	1926.3	1832.3	1662.3	1527.9	1463.3	1429.8	1296.4	1200.3	1074.9	977.8	881.8
7.5°	2395.5	2216.6	1977.9	1722.0	1616.9	1552.2	1345.9	1192.2	1025.3	889.8	770.5
10°	2875.8	2560.4	2204.4	1866.6	1715.0	1605.8	1340.9	1132.5	940.4	781.7	651.1
12.5°	3376.4	2878.8	2383.4	1960.7	1760.4	1616.9	1295.3	1045.5	836.3	667.4	543.1
15°	3798.1	3125.6	2496.6	1983.0	1746.4	1572.4	1198.3	935.3	725.0	560.1	447.0
17.5°	4123.6	3264.1	2517.9	1928.4	1667.4	1473.3	1072.9	814.0	607.7	462.1	349.9
20°	4287.5	3285.4	2451.1	1799.0	1524.8	1324.6	930.3	690.7	509.6	374.1	278.1
22.5°	4299.7	3186.2	2305.5	1632.1	1368.2	1164.9	813.0	595.6	447.0	335.7	263.8
25°	4141.8	2995.2	2110.4	1461.2	1207.3	1024.4	729.0	571.3	450.0	389.3	358.0
27.5°	3842.5	2730.2	1896.0	1290.2	1068.8	927.3	694.7	571.3	487.4	439.9	451.0
30°	3427.9	2392.4	1597.8	1057.7	869.6	746.2	546.1	427.8	335.7	280.1	270.0
32.5°	2890.0	1957.6	1238.6	781.7	634.0	538.0	369.1	267.9	216.3	211.3	205.3
35°	2378.3	1546.2	940.4	577.4	467.2	380.2	235.6	157.8	143.6	135.5	129.4
37.5°	1878.8	1156.8	675.5	419.6	320.5	241.7	121.3	102.1	88.9	80.9	73.7
40°	1412.6	831.3	476.2	253.9	168.0	104.2	72.9	62.7	55.6	51.6	49.5
42.5°	999.0	553.1	295.3	107.2	79.9	65.7	50.5	44.5	40.5	38.4	36.4
45°	580.4	343.8	119.4	62.7	50.5	45.4	37.4	33.4	31.3	29.3	28.3
47.5°	363.0	138.5	61.7	40.5	35.4	32.3	27.2	26.2	24.3	23.3	23.3
50°	146.6	61.7	38.4	28.3	25.4	24.3	21.3	20.3	18.2	18.2	18.2
52.5°	55.6	36.4	26.2	20.3	18.2	17.3	15.2	15.2	14.1	14.1	14.1
55°	32.3	24.3	18.2	14.1	13.2	13.2	12.2	12.2	11.1	11.1	11.1
57.5°	21.3	16.2	13.2	10.1	10.1	10.1	9.2	9.2	9.2	9.2	9.2
60°	14.1	11.1	9.2	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2
62.5°	10.1	9.2	8.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2	10.1
65°	8.1	7.1	7.1	7.1	7.1	8.1	8.1	9.2	9.2	10.1	10.1
67.5°	6.0	6.0	6.0	6.0	7.1	7.1	8.1	9.2	9.2	9.2	10.1
70°	5.1	6.0	6.0	7.1	7.1	7.1	8.1	8.1	9.2	9.2	10.1
72.5°	5.1	6.0	6.0	7.1	7.1	7.1	8.1	9.2	9.2	9.2	10.1
75°	5.1	6.0	6.0	7.1	7.1	7.1	8.1	9.2	9.2	9.2	10.1
77.5°	6.0	6.0	7.1	7.1	7.1	8.1	8.1	9.2	9.2	10.1	10.1
80°	6.0	6.0	7.1	7.1	7.1	8.1	8.1	9.2	9.2	10.1	10.1
82.5°	6.0	6.0	7.1	7.1	7.1	8.1	8.1	9.2	9.2	10.1	10.1
85°	6.0	6.0	7.1	7.1	7.1	8.1	8.1	9.2	9.2	10.1	10.1
87.5°	6.0	6.0	7.1	7.1	7.1	8.1	8.1	9.2	9.2	9.2	10.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192505

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7
2.5°	944.4	897.9	847.3	831.3	815.0	783.7	764.4	730.1	704.8	679.5	659.3
5°	818.1	744.3	682.6	656.2	631.0	587.5	557.1	520.7	491.5	466.1	442.9
7.5°	686.6	601.7	540.0	513.7	488.4	440.9	402.5	357.0	322.5	294.3	270.9
10°	565.2	484.3	417.6	386.3	357.0	307.4	270.9	234.6	205.3	181.0	159.8
12.5°	460.1	373.2	305.4	282.2	253.9	213.4	179.0	139.6	122.3	115.3	110.2
15°	357.0	279.0	222.5	201.2	175.9	137.5	122.3	115.3	110.2	107.2	103.2
17.5°	272.0	207.4	151.7	137.5	129.4	121.3	117.3	112.3	109.2	108.3	105.1
20°	213.4	156.7	142.6	138.5	138.5	136.4	133.4	133.4	132.4	135.5	135.5
22.5°	219.3	219.3	231.5	230.6	246.8	262.8	275.0	314.4	336.8	384.3	416.6
25°	383.2	419.6	462.1	475.3	506.6	553.1	601.7	662.3	704.8	750.3	768.5
27.5°	478.3	484.3	478.3	493.5	473.2	461.0	465.1	472.2	472.2	475.3	487.4
30°	283.1	297.3	310.3	320.5	315.4	310.3	308.5	293.3	293.3	287.1	282.2
32.5°	192.1	190.1	188.0	192.1	188.0	188.0	185.0	186.1	179.9	175.9	173.9
35°	131.5	125.3	118.4	119.4	115.3	114.3	111.3	111.3	107.2	105.1	104.2
37.5°	72.9	72.9	69.8	70.8	69.8	69.8	69.8	70.8	69.8	69.8	70.8
40°	49.5	49.5	48.6	49.5	48.6	49.5	50.5	50.5	50.5	50.5	49.5
42.5°	37.4	37.4	36.4	37.4	36.4	37.4	38.4	38.4	38.4	38.4	38.4
45°	29.3	29.3	29.3	29.3	29.3	29.3	29.3	30.3	30.3	29.3	29.3
47.5°	23.3	24.3	23.3	23.3	23.3	23.3	24.3	24.3	23.3	23.3	23.3
50°	19.2	19.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2
52.5°	15.2	14.1	14.1	13.2	13.2	13.2	13.2	13.2	13.2	13.2	12.2
55°	11.1	11.1	10.1	10.1	10.1	11.1	11.1	11.1	11.1	10.1	10.1
57.5°	10.1	10.1	10.1	9.2	9.2	10.1	10.1	9.2	9.2	9.2	8.1
60°	9.2	10.1	9.2	9.2	9.2	9.2	9.2	8.1	8.1	8.1	7.1
62.5°	10.1	10.1	9.2	9.2	9.2	9.2	8.1	8.1	8.1	7.1	7.1
65°	10.1	10.1	10.1	9.2	9.2	9.2	9.2	8.1	8.1	7.1	7.1
67.5°	10.1	10.1	10.1	10.1	9.2	9.2	9.2	8.1	8.1	8.1	7.1
70°	10.1	10.1	10.1	10.1	10.1	9.2	9.2	9.2	8.1	8.1	7.1
72.5°	10.1	10.1	10.1	9.2	9.2	9.2	9.2	9.2	8.1	8.1	7.1
75°	10.1	10.1	10.1	9.2	9.2	9.2	9.2	8.1	8.1	8.1	7.1
77.5°	10.1	10.1	10.1	9.2	9.2	9.2	9.2	8.1	8.1	8.1	7.1
80°	10.1	10.1	10.1	9.2	9.2	9.2	9.2	8.1	8.1	8.1	7.1
82.5°	10.1	10.1	10.1	9.2	9.2	9.2	9.2	8.1	8.1	7.1	7.1
85°	10.1	10.1	9.2	9.2	9.2	9.2	8.1	8.1	7.1	7.1	6.0
87.5°	9.2	9.2	9.2	9.2	8.1	8.1	8.1	7.1	6.0	6.0	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192505

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7	1058.7
2.5°	635.0	631.0	628.0	634.0	632.0	606.6	609.8	608.7
5°	416.6	407.6	400.5	403.5	395.4	384.3	376.2	374.1
7.5°	247.7	237.6	231.5	225.5	223.4	209.4	203.3	207.4
10°	136.4	122.3	121.3	118.4	114.3	111.3	109.2	110.2
12.5°	105.1	104.2	102.1	101.1	99.1	98.1	97.0	96.1
15°	100.2	99.1	98.1	97.0	96.1	95.1	94.0	94.0
17.5°	103.2	103.2	102.1	101.1	101.1	102.1	101.1	100.2
20°	134.5	134.5	136.4	139.6	139.6	142.6	146.6	143.6
22.5°	436.8	459.1	486.4	494.5	542.0	580.4	651.1	619.8
25°	798.8	849.4	861.5	878.8	905.0	918.2	905.0	922.3
27.5°	485.4	502.6	504.5	505.5	511.6	510.6	497.5	505.5
30°	282.2	288.2	286.2	285.2	283.1	272.0	270.0	274.0
32.5°	176.9	174.9	173.9	172.8	172.8	166.9	169.8	168.0
35°	101.1	104.2	103.2	102.1	99.1	98.1	98.1	97.0
37.5°	67.8	68.8	67.8	66.8	64.8	63.8	62.7	61.7
40°	48.6	49.5	48.6	47.5	46.5	45.4	44.5	43.5
42.5°	36.4	37.4	36.4	36.4	34.3	33.4	32.3	31.3
45°	28.3	27.2	27.2	27.2	26.2	25.4	24.3	24.3
47.5°	23.3	23.3	23.3	22.2	21.3	21.3	21.3	20.3
50°	17.3	18.2	17.3	17.3	16.2	15.2	15.2	14.1
52.5°	12.2	12.2	11.1	11.1	10.1	9.2	9.2	9.2
55°	9.2	9.2	9.2	8.1	8.1	7.1	7.1	7.1
57.5°	8.1	7.1	7.1	7.1	6.0	6.0	5.1	5.1
60°	7.1	6.0	6.0	5.1	5.1	4.1	4.1	4.1
62.5°	6.0	5.1	5.1	5.1	4.1	4.1	4.1	4.1
65°	6.0	5.1	5.1	5.1	4.1	4.1	4.1	4.1
67.5°	6.0	6.0	5.1	5.1	5.1	4.1	4.1	4.1
70°	6.0	6.0	6.0	5.1	5.1	5.1	4.1	4.1
72.5°	7.1	6.0	6.0	6.0	5.1	5.1	5.1	5.1
75°	7.1	6.0	6.0	6.0	5.1	5.1	5.1	5.1
77.5°	7.1	6.0	6.0	6.0	5.1	5.1	5.1	5.1
80°	6.0	6.0	6.0	5.1	5.1	5.1	5.1	5.1
82.5°	6.0	6.0	6.0	6.0	5.1	5.1	5.1	5.1
85°	6.0	5.1	5.1	5.1	4.1	4.1	4.1	4.1
87.5°	5.1	4.1	4.1	3.0	3.0	3.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)