

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192508

Luminaire Tested: **LDA6A55950D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26685)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A55950D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4410.5 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 2.12 / 1.05 / 1.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192508

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192508

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	76	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55		
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44		
8	67	55	47	42	65	54	47	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	43	38	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	78053	78053	78053
5°	125434	76513	48806
10°	185479	73290	32759
15°	252748	69331	24336
20°	312606	65421	23067
25°	362168	64413	37865
30°	395137	61706	37898
35°	406109	53318	29640
40°	395470	41979	23079
45°	358588	31050	18188
50°	282524	22933	12332
55°	168453	16334	7044
60°	86144	10865	2664
65°	41185	5772	1193
70°	19442	2597	1138
75°	7922	1716	1271
80°	3852	1894	1294
85°	1887	3208	1887

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192508

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.2	3.3
10°-20°	516.4	11.7
20°-30°	972.0	22.0
30°-40°	1183.6	26.8
40°-50°	985.2	22.3
50°-60°	471.9	10.7
60°-70°	113.3	2.6
70°-80°	17.9	0.4
80°-90°	4.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1634.5	37.1
0°-40°	2818.1	63.9
0°-60°	4275.1	96.9
0°-90°	4410.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4410.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1424	1424	1424	1424	1424	
5°	2279	1934	1390	1011	887	250
15°	4453	3026	1222	554	429	1277
25°	5988	3536	1065	604	626	2750
35°	6068	3105	797	464	443	3760
45°	4625	2076	400	247	235	3502
55°	1762	856	171	96	74	1660
65°	318	185	44	14	9	363
75°	37	19	8	7	6	51
85°	3	3	5	4	3	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192508

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8
2.5°	1841.4	1776.7	1797.0	1793.0	1788.9	1767.6	1752.5	1739.3	1706.0	1706.0	1663.4
5°	2279.4	2203.4	2222.7	2208.4	2190.2	2157.9	2128.7	2095.2	2033.6	2007.2	1933.5
7.5°	2779.8	2693.9	2711.1	2682.8	2644.3	2600.8	2553.3	2490.6	2392.5	2332.8	2218.6
10°	3332.0	3209.5	3219.7	3177.3	3113.6	3054.8	3009.3	2890.1	2750.5	2651.4	2491.6
12.5°	3854.8	3747.5	3750.7	3691.0	3598.9	3527.2	3458.3	3300.5	3114.5	2972.9	2762.7
15°	4453.4	4321.9	4290.6	4209.6	4089.4	4001.4	3907.4	3708.1	3474.5	3287.5	3025.6
17.5°	4935.7	4800.2	4780.0	4704.1	4532.3	4426.1	4307.8	4083.2	3787.0	3554.4	3232.8
20°	5358.5	5223.9	5189.6	5091.4	4894.2	4773.0	4630.4	4365.4	4041.9	3755.6	3392.6
22.5°	5704.2	5556.6	5508.0	5386.8	5167.3	5030.8	4856.9	4567.7	4206.6	3887.1	3487.6
25°	5987.5	5819.5	5757.9	5620.4	5373.6	5222.9	5031.7	4708.2	4314.9	3962.0	3536.2
27.5°	6168.4	6000.6	5932.9	5775.1	5498.1	5336.2	5127.8	4778.1	4353.2	3972.1	3526.1
30°	6242.2	6068.3	5991.4	5812.5	5514.2	5343.3	5125.8	4747.6	4303.8	3899.3	3441.2
32.5°	6196.7	6025.9	5939.9	5745.8	5435.2	5251.3	5033.8	4630.4	4173.3	3754.6	3293.5
35°	6068.3	5899.4	5810.5	5603.1	5279.6	5087.4	4871.0	4453.4	3991.3	3563.6	3105.4
37.5°	5846.8	5687.1	5585.0	5379.7	5054.1	4857.8	4643.5	4221.8	3749.6	3347.1	2888.1
40°	5526.2	5374.6	5273.4	5054.1	4746.7	4548.4	4346.3	3918.5	3473.6	3081.2	2638.3
42.5°	5117.8	4978.2	4881.2	4667.8	4374.6	4179.3	3994.3	3583.8	3160.0	2786.9	2368.3
45°	4625.3	4503.9	4408.9	4232.0	3942.7	3757.7	3590.8	3218.7	2807.2	2464.4	2076.0
47.5°	4045.9	3945.8	3853.7	3692.9	3432.1	3257.1	3119.6	2778.8	2429.9	2107.4	1776.7
50°	3312.7	3241.0	3169.2	3002.4	2818.2	2665.6	2565.5	2262.1	1980.0	1727.1	1453.2
52.5°	2497.7	2454.2	2403.6	2284.3	2161.0	2072.0	1983.1	1752.5	1541.1	1353.0	1139.6
55°	1762.5	1740.3	1700.9	1652.4	1558.3	1497.6	1420.7	1303.4	1139.6	1013.3	856.4
57.5°	1191.2	1185.1	1157.8	1128.6	1077.0	1056.7	992.0	916.1	824.2	730.1	618.8
60°	785.7	772.6	766.5	750.3	710.8	694.7	671.4	622.9	566.3	500.6	431.8
62.5°	505.5	498.6	493.5	486.4	462.1	462.1	438.9	416.6	374.1	333.7	289.2
65°	317.5	311.4	310.3	305.4	296.3	292.2	275.0	259.0	238.7	216.3	185.0
67.5°	204.3	195.2	190.1	187.1	181.0	173.9	168.0	160.8	144.6	131.5	111.3
70°	121.3	113.3	112.3	113.3	106.2	105.1	99.1	94.0	82.9	74.8	62.7
72.5°	68.8	64.8	63.8	63.8	59.7	58.7	54.6	51.6	45.4	39.4	34.3
75°	37.4	34.3	34.3	34.3	32.3	31.3	29.3	28.3	24.3	22.2	19.2
77.5°	21.3	20.3	20.3	19.2	18.2	17.3	16.2	16.2	14.1	13.2	12.2
80°	12.2	12.2	12.2	12.2	11.1	11.1	10.1	10.1	9.2	9.2	8.1
82.5°	7.1	7.1	7.1	7.1	7.1	7.1	6.0	6.0	6.0	6.0	5.1
85°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
87.5°	0.0	0.0	1.0	1.0	1.0	1.0	1.0	2.0	2.0	2.0	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192508

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8
2.5°	1644.2	1613.9	1611.8	1567.4	1539.1	1515.9	1498.6	1477.3	1429.8	1403.6	1384.3
5°	1881.9	1819.2	1786.8	1706.0	1661.4	1622.0	1573.4	1522.9	1445.1	1390.4	1346.0
7.5°	2128.7	2024.5	1955.6	1835.4	1774.7	1713.0	1631.1	1549.2	1443.0	1361.2	1293.3
10°	2358.2	2210.5	2101.3	1939.6	1860.6	1779.8	1664.4	1554.3	1421.7	1316.6	1227.7
12.5°	2583.7	2389.5	2238.8	2033.6	1937.5	1837.4	1689.8	1551.3	1395.5	1269.1	1164.9
15°	2799.1	2555.4	2363.2	2115.5	2003.1	1882.9	1706.0	1542.1	1365.2	1221.6	1103.2
17.5°	2971.0	2681.7	2451.2	2166.0	2039.6	1903.1	1699.9	1515.9	1323.6	1171.0	1041.6
20°	3089.3	2762.7	2499.7	2186.3	2047.7	1901.0	1676.6	1479.4	1280.1	1121.4	990.0
22.5°	3153.0	2799.1	2513.0	2180.3	2035.6	1881.9	1648.3	1446.0	1245.8	1087.0	961.7
25°	3176.3	2802.1	2498.7	2153.8	2008.2	1851.6	1614.9	1414.7	1218.6	1064.9	947.4
27.5°	3149.0	2759.6	2447.1	2099.2	1951.6	1797.0	1561.4	1370.1	1178.0	1032.5	922.3
30°	3055.8	2660.5	2346.0	2002.2	1857.5	1708.9	1476.4	1288.2	1112.4	974.8	869.6
32.5°	2908.4	2514.9	2203.4	1868.7	1729.2	1586.6	1364.2	1185.1	1021.4	891.8	797.8
35°	2725.2	2340.9	2037.7	1713.0	1581.5	1447.1	1235.7	1066.8	913.1	796.7	704.8
37.5°	2517.9	2147.8	1854.5	1556.3	1422.7	1296.4	1091.1	946.5	798.8	692.7	608.7
40°	2285.3	1926.4	1659.3	1369.3	1251.8	1136.6	946.5	815.0	680.6	586.6	513.7
42.5°	2036.6	1702.0	1455.2	1194.2	1077.0	971.8	800.8	682.6	563.3	485.4	427.8
45°	1772.7	1477.3	1240.7	1007.1	901.0	810.0	654.3	547.1	460.1	400.5	357.0
47.5°	1496.7	1235.7	1025.4	822.1	728.1	649.3	523.8	441.9	373.2	329.7	296.3
50°	1218.6	986.0	819.1	646.3	565.2	502.6	409.4	353.0	302.4	268.9	243.7
52.5°	952.5	762.4	626.9	487.4	425.7	382.2	319.5	280.1	241.7	216.3	197.2
55°	703.8	574.4	458.0	353.9	317.5	290.3	245.8	217.4	190.1	170.9	156.7
57.5°	508.6	411.5	326.6	259.9	235.6	217.4	185.0	165.9	146.6	132.4	121.3
60°	357.0	284.1	230.6	190.1	172.8	160.8	137.5	125.3	111.3	99.1	88.0
62.5°	234.6	191.2	160.8	134.5	124.4	115.3	99.1	90.0	77.8	69.8	59.7
65°	152.7	125.3	107.2	90.0	81.8	77.8	66.8	59.7	51.6	44.5	38.4
67.5°	93.0	77.8	67.8	56.7	52.6	48.6	41.5	36.4	31.3	26.2	23.3
70°	51.6	45.4	39.4	33.4	30.3	28.3	24.3	22.2	18.2	16.2	13.2
72.5°	30.3	26.2	23.3	19.2	18.2	17.3	14.1	13.2	11.1	10.1	9.2
75°	18.2	15.2	14.1	12.2	11.1	11.1	10.1	9.2	8.1	8.1	7.1
77.5°	11.1	10.1	9.2	8.1	8.1	8.1	7.1	7.1	7.1	6.0	6.0
80°	7.1	7.1	7.1	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
82.5°	5.1	5.1	5.1	4.1	5.1	4.1	5.1	5.1	5.1	5.1	5.1
85°	3.0	3.0	4.1	4.1	4.1	4.1	4.1	5.1	5.1	5.1	5.1
87.5°	3.0	3.0	4.1	4.1	4.1	4.1	4.1	5.1	5.1	5.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192508

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8
2.5°	1362.2	1324.6	1297.4	1277.1	1284.2	1248.8	1237.7	1199.3	1185.1	1185.1	1164.9
5°	1300.4	1240.7	1194.2	1164.9	1162.9	1112.4	1086.0	1037.5	1011.2	992.0	972.8
7.5°	1226.7	1149.7	1088.0	1052.7	1042.5	982.9	947.4	899.0	859.6	834.3	811.0
10°	1147.7	1055.7	986.0	945.5	930.4	865.6	819.1	774.6	732.2	705.8	681.6
12.5°	1071.9	971.8	894.9	853.4	834.3	767.5	720.0	673.5	633.0	605.7	581.5
15°	1002.1	895.9	815.0	773.6	752.3	686.6	639.1	593.6	554.1	528.8	506.6
17.5°	936.4	828.3	747.2	706.8	683.6	622.9	577.4	532.9	497.5	474.2	454.1
20°	886.9	779.7	704.8	669.4	646.3	589.6	550.2	511.7	482.4	465.1	446.0
22.5°	865.6	766.5	702.7	670.4	654.3	608.7	581.5	554.1	535.0	531.9	519.8
25°	862.6	775.6	723.0	695.8	685.7	651.1	635.0	617.9	603.6	607.7	609.8
27.5°	849.4	768.6	725.1	701.8	693.8	665.4	653.2	637.1	626.9	632.0	634.1
30°	803.9	729.1	688.7	669.4	661.3	633.0	622.9	604.7	596.6	597.7	596.6
32.5°	733.2	662.3	624.9	607.7	598.7	573.4	562.2	546.1	533.9	532.9	530.9
35°	647.2	583.4	549.1	533.9	524.8	503.7	493.5	478.3	464.2	463.1	461.0
37.5°	559.2	502.6	473.2	460.1	452.1	434.8	422.7	412.6	403.5	399.5	398.4
40°	474.2	423.7	402.5	392.4	386.3	368.1	361.9	351.9	344.9	340.8	339.8
42.5°	394.4	359.0	341.8	332.7	327.6	314.4	307.4	299.3	292.2	288.2	287.1
45°	334.7	305.4	289.2	282.2	278.1	265.9	260.9	252.8	246.8	243.7	242.7
47.5°	279.0	255.8	244.7	236.6	235.6	225.5	218.4	212.4	206.3	203.3	202.3
50°	228.5	209.4	200.2	195.2	194.2	184.0	179.0	173.9	168.8	165.9	163.9
52.5°	188.0	169.8	163.9	156.7	155.8	146.6	142.6	137.5	132.4	128.4	125.3
55°	148.6	134.5	128.4	122.3	121.3	111.3	107.2	101.1	96.1	92.0	88.0
57.5°	113.3	102.1	96.1	90.0	88.9	81.8	74.8	69.8	64.8	59.7	56.7
60°	82.9	71.9	64.8	61.7	58.7	51.6	46.5	42.4	38.4	35.4	32.3
62.5°	54.6	46.5	41.5	37.4	35.4	30.3	27.2	24.3	22.2	21.3	20.3
65°	33.4	28.3	24.3	22.2	22.2	19.2	17.3	15.2	14.1	14.1	13.2
67.5°	20.3	17.3	15.2	14.1	13.2	12.2	11.1	11.1	10.1	10.1	9.2
70°	12.2	11.1	10.1	9.2	9.2	9.2	9.2	9.2	8.1	8.1	8.1
72.5°	9.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	7.1	7.1	7.1
75°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	6.0
77.5°	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
80°	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	5.1	5.1	5.1
82.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
85°	5.1	5.1	5.1	5.1	5.1	5.1	4.1	4.1	4.1	4.1	4.1
87.5°	5.1	4.1	4.1	4.1	4.1	4.1	3.0	3.0	3.0	3.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192508

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8	1423.8
2.5°	1154.8	1162.9	1150.8	1142.6	1134.5	1140.7	1112.4	1100.2
5°	954.6	945.5	939.3	932.4	920.2	922.3	897.9	886.9
7.5°	789.8	783.7	768.6	760.4	748.3	748.3	726.0	717.0
10°	659.3	650.3	636.1	629.0	617.9	608.7	597.7	588.5
12.5°	560.1	550.2	538.0	531.9	520.7	513.7	502.6	504.5
15°	486.4	476.3	465.1	459.1	450.0	442.9	433.8	428.8
17.5°	434.8	425.7	416.6	410.5	403.5	397.4	389.4	388.3
20°	430.8	423.7	418.6	414.5	408.6	404.6	400.5	395.4
22.5°	515.7	516.7	517.7	517.7	518.8	518.8	519.8	509.6
25°	608.7	619.8	619.8	622.9	632.0	632.0	630.0	626.0
27.5°	633.0	644.2	641.2	643.1	652.2	654.3	647.2	648.2
30°	592.6	602.8	596.6	597.7	603.6	603.6	594.7	598.7
32.5°	524.8	530.9	522.8	522.8	527.9	526.9	520.7	520.7
35°	453.0	456.1	449.0	452.1	452.1	449.0	442.9	442.9
37.5°	391.4	392.4	385.3	386.3	386.3	383.2	377.2	377.2
40°	332.7	335.7	329.7	331.7	329.7	326.6	323.5	322.5
42.5°	281.1	283.1	278.1	281.1	280.1	280.1	279.0	280.1
45°	236.6	238.7	234.6	236.6	237.6	236.6	233.6	234.6
47.5°	196.1	198.2	198.2	196.1	195.2	190.1	187.1	187.1
50°	158.8	157.8	156.7	153.7	150.7	147.7	144.6	144.6
52.5°	119.4	117.3	116.4	113.3	112.3	109.2	109.2	106.2
55°	81.8	80.9	80.9	77.8	77.8	74.8	73.7	73.7
57.5°	51.6	49.5	50.5	48.6	47.5	44.5	44.5	43.5
60°	29.3	28.3	28.3	27.2	26.2	24.3	24.3	24.3
62.5°	19.2	18.2	18.2	17.3	17.3	16.2	16.2	15.2
65°	12.2	11.1	11.1	10.1	10.1	9.2	9.2	9.2
67.5°	9.2	8.1	8.1	8.1	8.1	8.1	7.1	7.1
70°	8.1	8.1	7.1	7.1	7.1	7.1	7.1	7.1
72.5°	7.1	7.1	7.1	7.1	6.0	6.0	6.0	6.0
75°	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
77.5°	6.0	5.1	5.1	5.1	5.1	5.1	5.1	5.1
80°	5.1	5.1	5.1	5.1	5.1	5.1	4.1	4.1
82.5°	5.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
85°	4.1	3.0	3.0	3.0	3.0	3.0	3.0	3.0
87.5°	2.0	2.0	2.0	2.0	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)