

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192511

Luminaire Tested: **LDA6A60927D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192511
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26689)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60927D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4228.3 lumens
Efficiency: N/A
Efficacy: 58.9 lumens/watt
Spacing Criteria (0/90/45): 2.34 / 0.96 / 1.3
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192511

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192511

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104	110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91	103	98	94	90		95	91	88		92	89	86		89	86	84
3	99	91	85	80	97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	76	71	90	82	76	71		80	74	70		77	73	69		76	72	68
5	86	76	69	64	84	75	68	63		73	67	63		71	66	62		70	65	62
6	80	70	62	57	79	69	62	57		67	61	57		66	60	56		64	59	56
7	75	64	57	51	74	63	56	51		62	56	51		60	55	51		59	54	50
8	70	59	52	47	69	58	51	46		57	51	46		56	50	46		55	50	46
9	66	54	47	42	64	54	47	42		53	46	42		52	46	42		51	45	42
10	62	50	43	38	61	50	43	38		49	43	38		48	42	38		47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	65987	65987	65987
5°	129011	62728	22881
10°	217153	53857	5071
15°	330694	40783	8331
20°	477873	33037	92933
25°	711186	53447	26856
30°	821443	18294	5305
35°	821702	4089	2871
40°	671608	2283	1760
45°	508572	1481	1132
50°	337746	1006	776
55°	54297	870	602
60°	3399	899	493
65°	1064	1180	584
70°	593	1314	721
75°	381	1546	953
80°	284	2305	1421
85°	566	4592	1698

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192511

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.7	3.0
10°-20°	537.2	12.7
20°-30°	1264.7	29.9
30°-40°	1332.5	31.5
40°-50°	830.9	19.6
50°-60°	119.4	2.8
60°-70°	7.6	0.2
70°-80°	6.0	0.1
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1927.6	45.6
0°-40°	3260.1	77.1
0°-60°	4210.3	99.6
0°-90°	4228.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4228.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1204	1204	1204	1204	1204	
5°	2344	1898	1140	592	416	272
15°	5827	3298	719	125	147	1735
25°	11758	3954	884	639	444	5291
35°	12278	2896	61	56	43	7406
45°	6560	802	19	21	15	5134
55°	568	15	9	10	6	1021
65°	8	6	9	7	4	12
75°	2	4	7	7	4	2
85°	1	4	7	6	3	1
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192511

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7
2.5°	1757.2	1745.4	1749.0	1721.6	1685.2	1701.5	1660.5	1661.4	1635.9	1571.1	1542.8
5°	2344.4	2342.6	2339.9	2289.7	2225.0	2232.3	2172.1	2149.3	2083.6	1969.6	1897.6
7.5°	3074.0	3074.8	3061.2	2938.9	2866.9	2862.3	2767.5	2699.1	2576.9	2397.3	2265.9
10°	3901.0	3926.5	3901.9	3714.1	3580.0	3581.9	3411.3	3280.0	3084.0	2822.2	2635.3
12.5°	4872.1	4875.7	4837.5	4590.4	4386.1	4370.5	4141.7	3890.9	3592.7	3250.8	2979.0
15°	5826.8	5852.3	5803.1	5498.6	5214.0	5171.2	4879.4	4548.4	4178.2	3672.0	3298.2
17.5°	6885.5	6845.4	6714.9	6279.2	5937.1	5874.2	5560.6	5127.4	4655.1	4043.2	3552.6
20°	8191.4	8205.0	7928.6	7277.7	6699.5	6454.2	6090.4	5616.1	5027.1	4315.8	3722.2
22.5°	10057.0	9983.1	9390.4	8337.2	7468.3	7140.8	6622.0	5968.2	5305.3	4522.8	3849.0
25°	11757.6	11563.4	11017.2	9568.2	8207.7	7802.9	7265.7	6268.2	5536.0	4676.0	3953.9
27.5°	12734.2	12647.5	12028.4	10566.7	8805.0	8235.1	7479.1	6488.9	5672.7	4751.7	3984.0
30°	12976.8	12992.3	12441.5	10897.7	8946.4	8295.3	7513.8	6482.4	5580.7	4616.8	3810.7
32.5°	12914.8	12830.9	12142.4	10532.1	8569.7	7977.0	7174.6	6192.5	5214.0	4214.7	3379.3
35°	12278.3	12155.2	11308.1	9581.0	7930.5	7354.2	6626.6	5717.4	4702.5	3702.1	2896.1
37.5°	11067.3	10925.1	9947.6	8439.3	7163.6	6675.8	6046.5	5188.6	4185.4	3224.3	2471.1
40°	9384.9	9208.0	8391.0	7345.1	6339.2	5998.3	5466.6	4584.9	3649.3	2772.1	2079.0
42.5°	7812.0	7727.2	7236.6	6339.2	5661.8	5332.6	4796.4	3975.7	3114.9	2309.8	1539.2
45°	6559.9	6503.4	6177.9	5608.0	4920.5	4612.2	4107.1	3306.5	2370.0	1555.6	801.6
47.5°	5742.0	5598.0	5279.7	4681.5	3917.3	3533.5	3052.0	2178.4	1336.8	689.3	246.2
50°	3960.2	3973.9	3614.6	2955.4	2305.2	1980.5	1635.9	1002.2	442.2	150.5	42.9
52.5°	2085.5	1931.3	1678.7	1253.8	872.6	665.7	486.0	200.6	80.3	30.1	22.8
55°	568.1	498.8	398.5	281.7	152.3	106.7	70.2	37.4	26.4	21.0	14.6
57.5°	55.6	52.9	48.4	39.2	33.8	31.0	28.3	22.8	18.3	12.8	9.1
60°	31.0	30.1	28.3	24.6	21.9	20.1	18.3	15.5	11.0	8.2	7.3
62.5°	17.3	16.5	15.5	13.6	11.8	11.0	11.0	9.1	7.3	6.3	6.3
65°	8.2	8.2	8.2	8.2	8.2	7.3	6.3	6.3	6.3	6.3	6.3
67.5°	6.3	6.3	6.3	5.5	5.5	5.5	5.5	5.5	5.5	4.5	5.5
70°	3.7	3.7	4.5	3.7	3.7	3.7	3.7	3.7	3.7	3.7	4.5
72.5°	1.8	2.7	2.7	2.7	2.7	2.7	2.7	2.7	3.7	3.7	4.5
75°	1.8	1.8	1.8	1.8	2.7	2.7	2.7	2.7	3.7	3.7	4.5
77.5°	1.8	1.8	1.8	1.8	1.8	1.8	2.7	2.7	3.7	3.7	4.5
80°	0.9	0.9	0.9	1.8	1.8	1.8	1.8	2.7	3.7	3.7	4.5
82.5°	0.9	0.9	0.9	0.9	1.8	1.8	1.8	2.7	3.7	3.7	4.5
85°	0.9	0.9	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.7	4.5
87.5°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.7	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192511

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7
2.5°	1513.7	1469.0	1424.4	1379.7	1377.8	1351.4	1312.2	1260.2	1217.4	1180.9	1145.3
5°	1825.5	1733.4	1641.4	1549.3	1521.9	1474.5	1389.7	1294.0	1211.9	1139.9	1070.5
7.5°	2138.3	1983.3	1837.4	1693.3	1635.9	1563.9	1431.6	1293.0	1174.5	1068.7	965.7
10°	2417.4	2192.1	1987.0	1784.5	1701.5	1607.7	1429.7	1253.8	1103.4	967.5	836.2
12.5°	2674.5	2360.9	2100.9	1845.6	1732.6	1618.5	1401.6	1191.8	1012.1	849.8	698.5
15°	2900.7	2515.9	2181.2	1872.9	1734.4	1597.5	1342.3	1106.1	904.5	718.6	554.4
17.5°	3062.0	2593.4	2207.7	1848.3	1687.0	1533.8	1254.8	1002.2	785.1	590.9	432.2
20°	3160.5	2625.3	2193.9	1802.8	1631.3	1472.6	1189.9	944.6	734.1	566.3	458.7
22.5°	3225.3	2656.2	2199.4	1801.9	1630.4	1480.9	1217.4	987.5	816.1	725.9	713.1
25°	3294.5	2700.0	2239.5	1842.8	1683.3	1544.7	1289.4	1065.0	921.8	883.6	889.1
27.5°	3290.9	2680.9	2201.2	1807.3	1639.6	1499.1	1200.0	916.5	782.3	674.7	635.6
30°	3094.9	2459.3	1940.5	1499.1	1301.2	1128.9	734.9	477.8	330.1	289.0	248.0
32.5°	2636.3	1992.5	1450.8	1036.8	814.2	608.2	289.0	153.2	130.4	109.4	99.4
35°	2192.1	1588.5	1085.1	626.5	395.8	245.3	103.9	68.4	64.7	61.1	61.1
37.5°	1811.9	1247.5	701.2	264.4	145.0	88.5	50.2	45.6	43.7	42.9	42.9
40°	1417.1	813.4	303.7	87.5	46.5	40.1	35.6	33.8	32.8	31.9	32.8
42.5°	836.2	327.3	88.5	32.8	31.0	29.1	26.4	25.6	25.6	24.6	25.6
45°	284.5	84.8	29.1	23.8	21.9	21.9	20.1	20.1	20.1	19.1	21.0
47.5°	73.8	26.4	19.1	17.3	16.5	16.5	15.5	15.5	15.5	15.5	16.5
50°	25.6	17.3	13.6	12.8	11.8	12.8	11.8	11.8	11.8	11.8	12.8
52.5°	15.5	11.8	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0
55°	10.0	9.1	8.2	8.2	8.2	8.2	8.2	9.1	9.1	9.1	9.1
57.5°	8.2	7.3	7.3	7.3	7.3	7.3	8.2	7.3	7.3	8.2	9.1
60°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	8.2	8.2	9.1
62.5°	6.3	7.3	7.3	7.3	7.3	7.3	7.3	8.2	8.2	8.2	9.1
65°	6.3	6.3	6.3	7.3	7.3	7.3	8.2	8.2	8.2	9.1	9.1
67.5°	5.5	5.5	6.3	6.3	7.3	7.3	7.3	8.2	8.2	8.2	9.1
70°	5.5	5.5	5.5	6.3	6.3	6.3	6.3	7.3	7.3	8.2	8.2
72.5°	4.5	5.5	5.5	6.3	6.3	6.3	6.3	7.3	7.3	7.3	8.2
75°	4.5	5.5	5.5	6.3	6.3	6.3	6.3	6.3	7.3	7.3	8.2
77.5°	4.5	5.5	5.5	6.3	6.3	6.3	6.3	7.3	7.3	7.3	8.2
80°	4.5	5.5	5.5	6.3	6.3	6.3	6.3	7.3	7.3	7.3	7.3
82.5°	4.5	5.5	5.5	6.3	6.3	6.3	6.3	7.3	7.3	7.3	7.3
85°	4.5	5.5	5.5	6.3	6.3	6.3	6.3	6.3	7.3	7.3	7.3
87.5°	4.5	5.5	5.5	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192511

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7
2.5°	1096.1	1080.5	1025.8	1018.6	1009.5	964.7	946.5	915.5	871.8	859.0	843.5
5°	989.4	938.3	858.1	836.2	812.4	742.2	699.5	648.3	591.9	560.8	531.7
7.5°	853.5	782.3	675.7	632.8	606.4	529.8	461.4	393.0	310.0	262.6	232.5
10°	702.1	604.5	493.3	444.0	408.5	297.2	232.5	202.4	174.1	151.3	131.4
12.5°	549.8	439.5	313.7	257.1	228.8	189.6	154.1	116.7	103.9	103.1	99.4
15°	403.1	279.9	211.5	190.6	170.5	122.2	121.2	121.2	124.9	127.7	128.6
17.5°	297.2	246.2	193.3	180.6	189.6	196.9	209.7	228.8	244.3	288.2	279.1
20°	435.9	432.2	471.5	521.5	557.1	632.8	728.6	837.0	950.1	1076.0	1171.8
22.5°	747.7	838.9	910.0	970.2	1002.2	1087.8	1163.5	1200.9	1222.8	1211.9	1196.4
25°	913.7	946.5	924.7	903.7	906.4	828.9	772.3	700.3	639.3	583.6	550.8
27.5°	546.2	499.7	434.1	388.5	379.3	327.3	289.0	249.0	237.1	200.6	185.1
30°	196.9	183.3	162.3	145.9	144.0	130.4	122.2	113.1	112.1	103.9	99.4
32.5°	89.3	89.3	82.0	83.8	82.0	79.3	78.5	75.7	75.7	73.0	71.2
35°	58.4	59.2	58.4	58.4	57.4	57.4	57.4	55.6	56.5	54.7	52.0
37.5°	42.9	43.7	41.9	42.9	42.9	42.9	42.9	41.9	41.1	39.2	38.3
40°	32.8	32.8	32.8	32.8	32.8	32.8	32.8	31.9	31.9	31.0	29.1
42.5°	25.6	26.4	26.4	26.4	26.4	26.4	26.4	26.4	26.4	25.6	25.6
45°	21.0	21.9	21.0	21.9	21.9	21.9	21.0	21.0	21.0	20.1	19.1
47.5°	16.5	16.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5	14.6
50°	12.8	12.8	12.8	12.8	12.8	12.8	13.6	12.8	12.8	12.8	12.8
52.5°	10.0	11.0	11.0	11.8	11.8	11.8	11.8	11.8	11.0	11.0	10.0
55°	9.1	10.0	10.0	11.0	11.0	11.0	11.0	10.0	10.0	10.0	9.1
57.5°	9.1	10.0	10.0	10.0	10.0	10.0	10.0	9.1	9.1	8.2	8.2
60°	9.1	9.1	9.1	10.0	10.0	9.1	9.1	8.2	8.2	7.3	7.3
62.5°	9.1	9.1	9.1	10.0	10.0	9.1	9.1	8.2	7.3	7.3	6.3
65°	9.1	10.0	9.1	10.0	10.0	9.1	9.1	8.2	7.3	7.3	6.3
67.5°	9.1	10.0	10.0	10.0	9.1	9.1	9.1	8.2	7.3	7.3	6.3
70°	8.2	9.1	9.1	9.1	9.1	9.1	8.2	8.2	7.3	7.3	6.3
72.5°	8.2	9.1	8.2	9.1	9.1	8.2	8.2	8.2	7.3	7.3	6.3
75°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.3	6.3
77.5°	8.2	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.3	6.3
80°	8.2	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.3	6.3	5.5
82.5°	7.3	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.3	6.3	5.5
85°	7.3	7.3	7.3	7.3	7.3	7.3	6.3	6.3	5.5	4.5	4.5
87.5°	6.3	7.3	6.3	6.3	6.3	6.3	5.5	4.5	3.7	3.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192511

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7	1203.7
2.5°	818.9	796.1	796.9	800.6	777.8	766.0	763.2	751.4
5°	492.4	466.0	461.4	457.8	425.9	413.1	403.1	415.8
7.5°	211.5	201.6	199.7	196.9	182.4	175.1	171.5	175.1
10°	104.9	98.5	99.4	100.3	95.8	93.0	92.1	91.1
12.5°	103.9	103.1	103.9	103.9	104.9	103.1	103.9	103.9
15°	134.9	134.9	137.7	139.5	144.0	143.2	145.0	146.8
17.5°	336.4	319.1	328.3	328.3	369.3	332.8	363.9	335.6
20°	1322.1	1384.2	1447.2	1500.1	1553.8	1570.2	1602.2	1593.0
22.5°	1172.6	1179.9	1170.8	1160.8	1158.1	1160.8	1111.6	1118.9
25°	503.4	499.7	485.1	469.6	474.1	477.8	460.5	444.0
27.5°	172.3	167.8	163.2	159.6	157.8	155.0	149.5	145.9
30°	97.6	94.8	93.0	92.1	90.3	88.5	85.7	83.8
32.5°	70.2	68.4	67.5	66.5	64.7	62.9	60.2	59.2
35°	52.0	50.2	49.2	48.4	46.5	44.7	43.7	42.9
37.5°	38.3	36.4	36.4	36.4	33.8	31.9	31.0	30.1
40°	29.1	28.3	28.3	28.3	26.4	25.6	24.6	24.6
42.5°	25.6	24.6	24.6	24.6	22.8	21.9	21.9	21.0
45°	19.1	18.3	18.3	17.3	16.5	16.5	15.5	14.6
47.5°	14.6	13.6	13.6	13.6	12.8	11.8	11.8	11.0
50°	11.8	11.8	11.0	11.8	10.0	10.0	10.0	9.1
52.5°	10.0	10.0	9.1	9.1	8.2	8.2	8.2	7.3
55°	9.1	8.2	8.2	8.2	7.3	7.3	7.3	6.3
57.5°	7.3	7.3	6.3	6.3	5.5	5.5	5.5	5.5
60°	6.3	6.3	5.5	5.5	4.5	4.5	4.5	4.5
62.5°	6.3	5.5	5.5	5.5	4.5	4.5	4.5	4.5
65°	6.3	5.5	5.5	5.5	4.5	4.5	4.5	4.5
67.5°	6.3	5.5	5.5	5.5	4.5	4.5	4.5	4.5
70°	6.3	6.3	5.5	5.5	5.5	4.5	4.5	4.5
72.5°	6.3	6.3	5.5	5.5	5.5	5.5	4.5	4.5
75°	5.5	5.5	5.5	5.5	4.5	4.5	4.5	4.5
77.5°	5.5	5.5	5.5	5.5	4.5	4.5	4.5	4.5
80°	5.5	5.5	4.5	4.5	4.5	4.5	4.5	4.5
82.5°	5.5	4.5	4.5	4.5	4.5	3.7	3.7	3.7
85°	3.7	3.7	3.7	3.7	2.7	2.7	2.7	2.7
87.5°	2.7	1.8	1.8	1.8	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)