

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192525

Luminaire Tested: **LDA6A60927D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192525
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26685)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60927D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3977.6 lumens
Efficiency: N/A
Efficacy: 55.4 lumens/watt
Spacing Criteria (0/90/45): 2.12 / 1.05 / 1.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192525

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192525

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	76	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55		
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44		
8	67	55	47	42	65	54	47	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	43	38	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	70389	70389	70389
5°	113119	69002	44007
10°	167276	66098	29547
15°	227941	62526	21947
20°	281920	59003	20803
25°	326614	58092	34151
30°	356359	55654	34170
35°	366250	48091	26729
40°	356668	37857	20818
45°	323398	28003	16397
50°	254798	20690	11121
55°	151928	14728	6356
60°	77691	9791	2401
65°	37151	5202	1064
70°	17535	2340	1010
75°	7159	1546	1165
80°	3473	1736	1168
85°	1698	2830	1698



TEST NUMBER: P1192525

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.8	3.3
10°-20°	465.7	11.7
20°-30°	876.6	22.0
30°-40°	1067.4	26.8
40°-50°	888.5	22.3
50°-60°	425.6	10.7
60°-70°	102.2	2.6
70°-80°	16.1	0.4
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1474.1	37.1
0°-40°	2541.5	63.9
0°-60°	3855.6	96.9
0°-90°	3977.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3977.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1284	1284	1284	1284	1284	
5°	2056	1744	1254	912	800	225
15°	4016	2729	1102	500	387	1151
25°	5400	3189	960	544	565	2480
35°	5473	2801	719	419	399	3391
45°	4171	1872	361	222	212	3159
55°	1590	772	154	87	66	1497
65°	286	167	40	13	8	328
75°	34	17	7	6	6	46
85°	3	3	4	4	3	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192525

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
2.5°	1660.7	1602.3	1620.6	1616.9	1613.3	1594.1	1580.5	1568.5	1538.4	1538.4	1500.2
5°	2055.6	1987.2	2004.5	1991.8	1975.3	1946.2	1919.7	1889.6	1833.9	1810.3	1743.7
7.5°	2507.0	2429.5	2444.9	2419.5	2384.9	2345.6	2302.7	2246.2	2157.7	2103.9	2000.9
10°	3005.0	2894.6	2903.7	2865.5	2808.0	2755.1	2714.0	2606.4	2480.5	2391.2	2247.0
12.5°	3476.5	3379.8	3382.5	3328.6	3245.7	3181.0	3118.9	2976.7	2808.9	2681.2	2491.5
15°	4016.3	3897.7	3869.4	3796.6	3688.0	3608.7	3523.9	3344.2	3133.6	2964.8	2728.6
17.5°	4451.3	4329.1	4310.9	4242.5	4087.5	3991.7	3885.0	3682.5	3415.3	3205.6	2915.6
20°	4832.5	4711.2	4680.3	4591.8	4413.9	4304.5	4175.9	3937.0	3645.1	3387.0	3059.7
22.5°	5144.4	5011.2	4967.5	4858.1	4660.2	4537.1	4380.2	4119.4	3793.8	3505.6	3145.4
25°	5399.7	5248.4	5192.8	5068.8	4846.3	4710.4	4538.0	4246.1	3891.4	3573.1	3189.1
27.5°	5563.0	5411.7	5350.5	5208.3	4958.4	4812.5	4624.6	4309.1	3926.0	3582.2	3180.1
30°	5629.6	5472.7	5403.4	5242.0	4973.0	4818.8	4622.8	4281.7	3881.4	3516.6	3103.5
32.5°	5588.6	5434.5	5357.0	5181.8	4901.8	4735.9	4539.8	4175.9	3763.7	3386.2	2970.3
35°	5472.7	5320.4	5240.2	5053.3	4761.4	4588.2	4392.9	4016.3	3599.5	3213.7	2800.6
37.5°	5273.0	5129.0	5036.8	4851.7	4558.1	4381.1	4187.7	3807.4	3381.5	3018.6	2604.6
40°	4984.0	4847.1	4756.0	4558.1	4280.8	4102.1	3919.7	3533.9	3132.6	2778.8	2379.4
42.5°	4615.5	4489.6	4402.1	4209.7	3945.2	3769.2	3602.3	3232.0	2849.9	2513.4	2135.8
45°	4171.4	4062.0	3976.2	3816.6	3555.8	3388.8	3238.5	2902.8	2531.6	2222.4	1872.3
47.5°	3648.8	3558.5	3475.5	3330.5	3095.3	2937.5	2813.4	2506.1	2191.5	1900.6	1602.3
50°	2987.6	2922.9	2858.2	2707.7	2541.7	2404.0	2313.7	2040.1	1785.7	1557.7	1310.5
52.5°	2252.5	2213.4	2167.7	2060.1	1948.9	1868.7	1788.4	1580.5	1389.9	1220.3	1027.7
55°	1589.6	1569.5	1533.9	1490.2	1405.4	1350.7	1281.3	1175.6	1027.7	913.8	772.5
57.5°	1074.3	1068.8	1044.2	1017.7	971.2	953.0	894.7	826.2	743.2	658.4	558.1
60°	708.6	696.8	691.3	676.7	641.1	626.5	605.5	561.8	510.7	451.5	389.5
62.5°	456.0	449.7	445.0	438.7	416.8	416.8	395.8	375.7	337.4	301.0	260.8
65°	286.4	280.9	280.0	275.4	267.2	263.6	248.1	233.5	215.2	195.2	166.9
67.5°	184.2	176.0	171.5	168.8	163.3	156.8	151.3	145.0	130.4	118.6	100.3
70°	109.4	102.1	101.3	102.1	95.8	94.8	89.3	84.8	74.8	67.5	56.5
72.5°	62.0	58.4	57.4	57.4	53.9	52.9	49.2	46.5	41.1	35.6	31.0
75°	33.8	31.0	31.0	31.0	29.1	28.3	26.4	25.6	21.9	20.1	17.3
77.5°	19.1	18.3	18.3	17.3	16.5	15.5	14.6	14.6	12.8	11.8	11.0
80°	11.0	11.0	11.0	11.0	10.0	10.0	9.1	9.1	8.2	8.2	7.3
82.5°	6.3	6.3	6.3	6.3	6.3	6.3	5.5	5.5	5.5	5.5	4.5
85°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
87.5°	0.0	0.0	0.9	0.9	0.9	0.9	0.9	1.8	1.8	1.8	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192525

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
2.5°	1482.9	1455.5	1453.6	1413.5	1388.1	1367.0	1351.5	1332.4	1289.5	1265.9	1248.5
5°	1697.2	1640.7	1611.4	1538.4	1498.4	1462.8	1419.0	1373.5	1303.3	1253.9	1213.8
7.5°	1919.7	1825.8	1763.8	1655.2	1600.5	1544.9	1471.1	1397.1	1301.4	1227.5	1166.4
10°	2126.8	1993.6	1895.1	1749.1	1678.0	1605.1	1501.2	1401.7	1282.2	1187.4	1107.2
12.5°	2330.0	2155.0	2019.0	1833.9	1747.3	1657.0	1523.9	1398.9	1258.5	1144.5	1050.7
15°	2524.4	2304.6	2131.3	1907.8	1806.7	1698.1	1538.4	1390.8	1231.1	1101.7	995.0
17.5°	2679.4	2418.5	2210.6	1953.5	1839.4	1716.4	1533.1	1367.0	1193.7	1056.0	939.3
20°	2786.0	2491.5	2254.4	1971.6	1846.7	1714.5	1512.0	1334.2	1154.6	1011.4	892.8
22.5°	2843.5	2524.4	2266.3	1966.2	1835.8	1697.2	1486.5	1304.1	1123.5	980.3	867.3
25°	2864.5	2527.1	2253.5	1942.5	1811.2	1669.8	1456.4	1275.8	1098.9	960.4	854.5
27.5°	2839.9	2488.8	2207.0	1893.3	1760.1	1620.6	1408.1	1235.8	1062.5	931.1	831.7
30°	2755.9	2399.4	2115.8	1805.7	1675.3	1541.2	1331.5	1161.9	1003.1	879.2	784.3
32.5°	2622.9	2268.1	1987.2	1685.3	1559.5	1430.8	1230.3	1068.8	921.1	804.4	719.6
35°	2457.7	2111.2	1837.6	1544.9	1426.3	1305.1	1114.4	962.2	823.5	718.6	635.6
37.5°	2270.8	1937.0	1672.6	1403.5	1283.2	1169.1	984.0	853.6	720.4	624.8	549.0
40°	2061.1	1737.3	1496.5	1234.8	1129.0	1025.1	853.6	735.0	613.8	529.0	463.3
42.5°	1836.8	1534.8	1312.3	1077.1	971.2	876.4	722.2	615.6	508.0	437.7	385.8
45°	1598.6	1332.4	1119.0	908.3	812.5	730.5	590.0	493.4	414.9	361.2	321.9
47.5°	1349.7	1114.4	924.8	741.4	656.6	585.5	472.4	398.5	336.6	297.3	267.2
50°	1098.9	889.2	738.7	582.7	509.8	453.3	369.3	318.3	272.7	242.6	219.8
52.5°	859.1	687.6	565.4	439.5	384.0	344.7	288.2	252.6	218.0	195.2	177.8
55°	634.8	518.0	413.1	319.1	286.4	261.7	221.7	196.1	171.5	154.1	141.4
57.5°	458.7	371.2	294.5	234.3	212.5	196.1	166.9	149.5	132.2	119.4	109.4
60°	321.9	256.3	207.9	171.5	156.0	145.0	124.1	113.1	100.3	89.3	79.3
62.5°	211.5	172.3	145.0	121.2	112.2	103.9	89.3	81.2	70.2	62.9	53.9
65°	137.7	113.1	96.6	81.2	73.8	70.2	60.2	53.9	46.5	40.1	34.6
67.5°	84.0	70.2	61.1	51.1	47.4	43.7	37.4	32.8	28.3	23.8	21.0
70°	46.5	41.1	35.6	30.1	27.4	25.6	21.9	20.1	16.5	14.6	11.8
72.5°	27.4	23.8	21.0	17.3	16.5	15.5	12.8	11.8	10.0	9.1	8.2
75°	16.5	13.6	12.8	11.0	10.0	10.0	9.1	8.2	7.3	7.3	6.3
77.5°	10.0	9.1	8.2	7.3	7.3	7.3	6.3	6.3	6.3	5.5	5.5
80°	6.3	6.3	6.3	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
82.5°	4.5	4.5	4.5	3.7	4.5	3.7	4.5	4.5	4.5	4.5	4.5
85°	2.7	2.7	3.7	3.7	3.7	3.7	3.7	4.5	4.5	4.5	4.5
87.5°	2.7	2.7	3.7	3.7	3.7	3.7	3.7	4.5	4.5	4.5	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192525

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
2.5°	1228.4	1194.7	1170.1	1151.8	1158.3	1126.3	1116.2	1081.6	1068.8	1068.8	1050.7
5°	1172.8	1119.0	1077.1	1050.7	1048.8	1003.1	979.5	935.7	912.0	894.7	877.4
7.5°	1106.2	1036.9	981.3	949.4	940.2	886.4	854.5	810.7	775.1	752.3	731.4
10°	1035.1	952.1	889.2	852.6	839.0	780.6	738.7	698.6	660.2	636.6	614.6
12.5°	966.7	876.4	807.1	769.6	752.3	692.1	649.4	607.3	570.9	546.3	524.4
15°	903.8	808.0	735.0	697.6	678.5	619.3	576.4	535.3	499.7	476.9	456.8
17.5°	844.5	746.9	674.0	637.4	616.5	561.8	520.7	480.6	448.7	427.7	409.4
20°	799.7	703.1	635.6	603.7	582.7	531.7	496.1	461.5	435.0	419.6	402.1
22.5°	780.6	691.3	633.8	604.7	590.0	549.0	524.4	499.7	482.4	479.8	468.8
25°	777.9	699.5	652.1	627.4	618.3	587.4	572.7	557.3	544.5	548.1	549.9
27.5°	766.1	693.1	653.9	632.9	625.6	600.0	589.2	574.6	565.4	569.9	571.8
30°	725.0	657.5	621.1	603.7	596.5	570.9	561.8	545.3	538.1	539.0	538.1
32.5°	661.2	597.3	563.6	548.1	539.8	517.0	507.0	492.4	481.6	480.6	478.8
35°	583.7	526.2	495.2	481.6	473.3	454.2	445.0	431.4	418.6	417.7	415.9
37.5°	504.4	453.3	426.7	414.9	407.6	392.1	381.2	372.0	363.9	360.2	359.4
40°	427.7	382.1	363.0	353.9	348.4	331.9	326.5	317.3	311.0	307.3	306.5
42.5°	355.7	323.8	308.3	300.0	295.5	283.7	277.2	269.9	263.6	259.9	258.9
45°	301.8	275.4	260.8	254.4	250.8	239.8	235.3	228.0	222.5	219.8	218.9
47.5°	251.8	230.7	220.7	213.4	212.5	203.4	197.0	191.6	186.1	183.3	182.4
50°	206.1	188.8	180.6	176.0	175.1	166.0	161.5	156.8	152.3	149.5	147.7
52.5°	169.6	153.2	147.7	141.4	140.5	132.2	128.6	124.1	119.4	115.8	113.1
55°	134.0	121.2	115.8	110.4	109.4	100.3	96.6	91.1	86.6	83.0	79.3
57.5°	102.1	92.1	86.6	81.2	80.3	73.8	67.5	62.9	58.4	53.9	51.1
60°	74.8	64.7	58.4	55.7	52.9	46.5	41.9	38.3	34.6	31.9	29.1
62.5°	49.2	41.9	37.4	33.8	31.9	27.4	24.6	21.9	20.1	19.1	18.3
65°	30.1	25.6	21.9	20.1	20.1	17.3	15.5	13.6	12.8	12.8	11.8
67.5°	18.3	15.5	13.6	12.8	11.8	11.0	10.0	10.0	9.1	9.1	8.2
70°	11.0	10.0	9.1	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3
72.5°	8.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	6.3	6.3	6.3
75°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	5.5
77.5°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
80°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.5	4.5	4.5
82.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
85°	4.5	4.5	4.5	4.5	4.5	4.5	3.7	3.7	3.7	3.7	3.7
87.5°	4.5	3.7	3.7	3.7	3.7	3.7	2.7	2.7	2.7	2.7	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192525

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
2.5°	1041.5	1048.8	1037.9	1030.5	1023.2	1028.7	1003.1	992.3
5°	860.9	852.6	847.3	840.8	829.8	831.7	809.9	799.7
7.5°	712.3	706.8	693.1	685.8	674.8	674.8	654.7	646.6
10°	594.7	586.4	573.6	567.2	557.3	549.0	539.0	530.8
12.5°	505.2	496.1	485.1	479.8	469.6	463.3	453.3	455.0
15°	438.7	429.5	419.6	414.1	405.8	399.4	391.3	386.7
17.5°	392.1	384.0	375.7	370.2	363.9	358.4	351.1	350.2
20°	388.5	382.1	377.5	373.9	368.5	364.8	361.2	356.6
22.5°	465.1	466.0	467.0	467.0	467.8	467.8	468.8	459.6
25°	549.0	559.1	559.1	561.8	569.9	569.9	568.2	564.6
27.5°	570.9	580.9	578.2	580.0	588.2	590.0	583.7	584.5
30°	534.5	543.5	538.1	539.0	544.5	544.5	536.3	539.8
32.5°	473.3	478.8	471.5	471.5	476.1	475.1	469.6	469.6
35°	408.6	411.3	404.9	407.6	407.6	404.9	399.4	399.4
37.5°	352.9	353.9	347.4	348.4	348.4	345.6	340.2	340.2
40°	300.0	302.8	297.3	299.2	297.3	294.5	291.8	290.9
42.5°	253.6	255.4	250.8	253.6	252.6	252.6	251.8	252.6
45°	213.4	215.2	211.5	213.4	214.3	213.4	210.7	211.5
47.5°	176.9	178.8	178.8	176.9	176.0	171.5	168.8	168.8
50°	143.2	142.2	141.4	138.7	135.9	133.2	130.4	130.4
52.5°	107.6	105.8	104.9	102.1	101.3	98.5	98.5	95.8
55°	73.8	73.0	73.0	70.2	70.2	67.5	66.5	66.5
57.5°	46.5	44.7	45.6	43.7	42.9	40.1	40.1	39.2
60°	26.4	25.6	25.6	24.6	23.8	21.9	21.9	21.9
62.5°	17.3	16.5	16.5	15.5	15.5	14.6	14.6	13.6
65°	11.0	10.0	10.0	9.1	9.1	8.2	8.2	8.2
67.5°	8.2	7.3	7.3	7.3	7.3	7.3	6.3	6.3
70°	7.3	7.3	6.3	6.3	6.3	6.3	6.3	6.3
72.5°	6.3	6.3	6.3	6.3	5.5	5.5	5.5	5.5
75°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
77.5°	5.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
80°	4.5	4.5	4.5	4.5	4.5	4.5	3.7	3.7
82.5°	4.5	3.7	3.7	3.7	3.7	3.7	3.7	3.7
85°	3.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
87.5°	1.8	1.8	1.8	1.8	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)