

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192533

Luminaire Tested: **LDA6A60930D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192533
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26690)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60930D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4986.1 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 2.55 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192533

CATALOG NUMBER: LDA6A60930D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192533

CATALOG NUMBER: LDA6A60930D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	75	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65		
5	85	74	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	50243	50243	50243
5°	129705	46566	14561
10°	246054	35532	4893
15°	439974	23099	4875
20°	655578	15716	8879
25°	748035	19598	55787
30°	808960	16370	16686
35°	849762	7971	5227
40°	863210	2863	2648
45°	769072	1892	1589
50°	493928	1330	1083
55°	130031	927	554
60°	29011	965	428
65°	2776	1141	506
70°	930	1410	625
75°	212	1864	1038
80°	0	3062	1547
85°	0	5535	2453



TEST NUMBER: P1192533

CATALOG NUMBER: LDA6A60930D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.3	2.2
10°-20°	580.8	11.6
20°-30°	1362.9	27.3
30°-40°	1567.6	31.4
40°-50°	1113.5	22.3
50°-60°	226.4	4.5
60°-70°	11.3	0.2
70°-80°	6.7	0.1
80°-90°	5.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2055.0	41.2
0°-40°	3622.6	72.7
0°-60°	4962.5	99.5
0°-90°	4986.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4986.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	916	916	916	916	916	
5°	2357	1705	846	339	265	287
15°	7752	3485	407	92	86	2326
25°	12367	4198	324	708	922	5699
35°	12698	2948	119	88	78	7888
45°	9920	1048	24	26	20	7310
55°	1360	27	10	10	6	1835
65°	21	8	9	8	4	52
75°	1	5	9	8	5	2
85°	0	5	9	7	4	0
90°	0	0	0	0	0	

TEST NUMBER: P1192533

CATALOG NUMBER: LDA6A60930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	916.5	916.5	916.5	916.5	916.5	916.5	916.5	916.5	916.5	916.5	916.5
2.5°	1579.1	1531.4	1507.9	1506.9	1438.6	1461.1	1438.6	1421.1	1357.6	1331.3	1287.3
5°	2357.0	2298.5	2251.6	2231.1	2114.0	2088.6	2076.9	2017.3	1884.6	1807.5	1705.0
7.5°	3274.4	3213.0	3135.9	3074.3	2904.6	2856.7	2825.5	2723.0	2526.8	2371.7	2180.4
10°	4420.2	4384.2	4259.3	4146.1	3888.3	3788.8	3695.1	3456.0	3199.4	2888.0	2641.0
12.5°	5963.3	5878.4	5655.9	5429.5	5025.4	4877.1	4721.8	4339.2	3946.9	3458.9	3050.9
15°	7752.3	7680.0	7337.5	6968.6	6393.7	6149.8	5906.7	5304.6	4701.4	4072.8	3485.2
17.5°	9811.7	9675.0	9334.4	8710.7	7906.4	7523.0	7070.0	6302.9	5432.4	4578.4	3848.4
20°	11237.5	11156.5	10868.7	10270.4	9354.8	8848.3	8286.2	7233.1	6042.4	4983.5	4086.5
22.5°	12017.4	11936.4	11720.7	11192.7	10442.2	9933.7	9280.8	7985.5	6503.0	5255.7	4198.7
25°	12366.8	12314.1	12195.9	11765.5	11070.7	10612.9	9995.1	8505.7	6791.0	5379.6	4197.7
27.5°	12689.8	12703.5	12411.6	12057.4	11417.2	10957.5	10371.9	8740.0	6847.5	5317.2	4063.1
30°	12779.6	12745.5	12617.6	12118.9	11522.6	11021.8	10394.3	8616.0	6627.0	5041.0	3795.6
32.5°	12723.9	12724.9	12604.9	12074.9	11374.3	10814.0	10108.3	8172.0	6197.5	4607.7	3379.8
35°	12697.6	12688.9	12377.5	11912.0	11021.8	10363.1	9473.9	7459.5	5602.1	4054.3	2947.5
37.5°	12436.1	12383.4	12158.9	11527.4	10363.1	9520.8	8563.4	6588.0	4869.2	3478.4	2504.4
40°	12062.3	11995.8	11630.9	10725.1	9236.8	8296.9	7345.3	5601.2	4102.1	2905.6	2010.5
42.5°	11296.1	11186.8	10633.4	9432.0	7786.4	6912.0	6123.3	4613.5	3353.5	2359.0	1544.1
45°	9920.0	9741.4	8975.3	7720.1	6285.4	5599.2	4932.7	3698.0	2685.0	1756.8	1048.2
47.5°	7965.1	7769.8	7075.0	6066.8	4921.0	4364.7	3798.5	2723.0	1816.3	1023.8	526.1
50°	5791.5	5656.8	5042.9	4192.9	3253.9	2787.5	2353.1	1518.6	871.5	494.9	215.7
52.5°	3336.9	3240.3	2812.8	2206.7	1600.6	1340.1	1077.5	662.7	444.0	196.2	69.3
55°	1360.5	1304.8	1117.6	946.7	710.5	613.9	512.4	330.8	149.3	46.8	27.3
57.5°	665.6	658.8	549.5	440.1	324.0	261.5	197.2	66.4	36.1	23.4	17.5
60°	264.6	254.7	174.7	101.5	56.7	45.8	39.0	27.3	20.5	15.6	12.7
62.5°	45.8	44.8	38.0	32.2	26.3	23.4	21.4	16.6	13.6	10.7	9.7
65°	21.4	21.4	19.5	17.5	14.6	13.6	12.7	10.7	8.8	7.8	7.8
67.5°	10.7	10.7	9.7	8.8	7.8	7.8	6.8	6.8	5.8	5.8	5.8
70°	5.8	5.8	5.8	4.9	4.9	4.9	4.9	4.9	3.9	4.9	4.9
72.5°	3.9	3.9	3.9	2.9	1.9	2.9	2.9	2.9	3.9	4.9	4.9
75°	1.0	1.0	1.0	1.9	1.9	1.9	2.9	2.9	3.9	4.9	4.9
77.5°	1.0	1.0	1.0	1.0	1.9	1.9	1.9	2.9	3.9	4.9	4.9
80°	0.0	1.0	1.0	1.0	1.9	1.9	1.9	2.9	3.9	4.9	4.9
82.5°	0.0	0.0	1.0	1.0	1.9	1.9	1.9	2.9	3.9	4.9	4.9
85°	0.0	0.0	1.0	1.0	1.9	1.9	1.9	2.9	3.9	4.9	4.9
87.5°	0.0	0.0	1.0	1.0	1.9	1.9	1.9	2.9	3.9	4.9	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192533

CATALOG NUMBER: LDA6A60930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	916.5	916.5	916.5	916.5	916.5	916.5	916.5	916.5	916.5	916.5	916.5
2.5°	1267.8	1217.1	1183.8	1125.3	1101.0	1090.1	1036.5	984.7	935.0	898.9	843.3
5°	1627.0	1546.0	1422.1	1305.8	1255.1	1223.0	1117.6	1019.9	927.2	846.2	749.5
7.5°	2013.4	1846.6	1652.4	1465.9	1378.1	1319.6	1156.5	1014.1	881.3	758.3	626.6
10°	2384.4	2121.8	1838.8	1572.3	1453.3	1365.4	1152.6	970.1	797.4	638.3	496.8
12.5°	2700.6	2361.0	1985.2	1639.7	1484.5	1372.2	1116.6	894.1	684.2	513.4	390.4
15°	2967.0	2544.4	2081.8	1662.1	1475.7	1343.0	1046.3	789.6	560.2	407.0	315.2
17.5°	3154.4	2633.2	2104.2	1624.0	1414.2	1261.0	939.9	655.8	440.1	328.9	248.8
20°	3263.7	2644.9	2049.6	1531.4	1306.8	1144.8	806.2	515.3	357.2	269.4	193.3
22.5°	3280.3	2587.4	1942.3	1406.4	1182.9	1026.8	671.4	431.4	325.0	251.8	189.4
25°	3200.3	2473.2	1802.6	1284.4	1070.6	910.6	580.8	436.2	365.0	324.0	336.7
27.5°	3045.1	2284.8	1642.6	1159.5	953.5	791.6	548.5	456.7	398.2	405.1	428.4
30°	2807.0	2019.3	1412.2	947.7	730.0	603.2	436.2	328.9	273.3	258.6	259.6
32.5°	2456.5	1686.5	1108.8	657.8	491.0	407.0	276.2	183.5	184.5	170.8	169.9
35°	2056.5	1357.6	829.6	441.1	339.6	283.1	163.0	128.8	123.9	119.1	112.2
37.5°	1660.2	1049.2	552.4	301.6	216.7	157.1	82.0	67.4	62.5	58.6	58.6
40°	1263.9	733.9	341.6	158.2	87.9	64.5	48.7	40.9	40.0	40.0	39.0
42.5°	917.5	433.3	185.5	62.5	48.7	42.9	34.1	30.2	30.2	30.2	30.2
45°	488.0	220.6	71.3	39.0	32.2	30.2	25.3	23.4	23.4	24.4	24.4
47.5°	225.4	83.0	36.1	26.3	22.4	22.4	19.5	18.5	18.5	19.5	19.5
50°	81.0	34.1	23.4	18.5	16.6	17.5	15.6	14.6	15.6	15.6	15.6
52.5°	31.2	21.4	16.6	14.6	12.7	13.6	11.7	11.7	12.7	12.7	12.7
55°	19.5	15.6	12.7	10.7	9.7	10.7	9.7	9.7	9.7	9.7	9.7
57.5°	13.6	11.7	9.7	8.8	7.8	8.8	8.8	8.8	8.8	8.8	8.8
60°	10.7	8.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	8.8	8.8
62.5°	8.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	8.8	8.8	8.8
65°	7.8	6.8	7.8	7.8	6.8	7.8	7.8	7.8	8.8	8.8	9.7
67.5°	5.8	5.8	5.8	6.8	6.8	6.8	7.8	7.8	8.8	8.8	8.8
70°	5.8	5.8	6.8	6.8	6.8	6.8	7.8	7.8	8.8	8.8	8.8
72.5°	5.8	5.8	6.8	6.8	6.8	7.8	7.8	7.8	8.8	8.8	8.8
75°	5.8	5.8	6.8	6.8	6.8	7.8	7.8	7.8	8.8	8.8	8.8
77.5°	5.8	5.8	6.8	6.8	6.8	7.8	7.8	8.8	8.8	8.8	8.8
80°	5.8	6.8	6.8	7.8	7.8	7.8	7.8	8.8	8.8	9.7	9.7
82.5°	5.8	6.8	6.8	7.8	7.8	7.8	7.8	8.8	8.8	9.7	9.7
85°	5.8	6.8	6.8	7.8	7.8	7.8	7.8	8.8	8.8	8.8	8.8
87.5°	5.8	6.8	6.8	7.8	7.8	7.8	7.8	7.8	8.8	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192533

CATALOG NUMBER: LDA6A60930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	916.5	916.5	916.5	916.5	916.5	916.5	916.5	916.5	916.5	916.5	916.5
2.5°	806.2	758.3	710.5	687.2	666.6	637.3	600.3	569.9	537.8	521.2	483.2
5°	673.4	591.5	522.2	489.0	463.5	428.4	390.4	363.0	338.6	325.0	300.6
7.5°	521.2	443.1	382.6	357.2	338.6	303.5	275.3	246.9	221.5	203.0	178.6
10°	403.1	342.5	292.8	268.5	247.9	210.8	176.7	150.2	123.0	104.4	96.6
12.5°	320.1	263.6	212.8	188.4	166.9	128.8	103.5	98.6	93.7	91.8	88.8
15°	245.9	194.2	140.5	116.1	107.4	102.5	96.6	95.7	91.8	91.8	88.8
17.5°	184.5	126.9	107.4	105.4	104.4	102.5	99.6	98.6	97.6	97.6	96.6
20°	132.7	123.0	120.0	122.0	123.0	124.9	123.9	123.9	127.8	136.6	134.7
22.5°	186.4	202.0	218.6	224.5	245.9	267.5	287.0	311.3	369.0	435.3	450.9
25°	369.0	415.8	458.7	482.2	517.3	565.1	611.0	667.5	707.6	740.8	778.8
27.5°	458.7	476.3	469.4	472.4	468.4	461.6	463.5	475.4	469.4	451.8	458.7
30°	271.4	285.0	277.2	281.1	270.4	270.4	267.5	273.3	269.4	262.6	260.5
32.5°	176.7	184.5	183.5	183.5	179.6	177.7	170.8	168.9	162.1	149.3	146.4
35°	106.4	101.5	96.6	93.7	91.8	91.8	90.8	90.8	87.9	84.9	84.0
37.5°	57.6	58.6	58.6	58.6	58.6	60.6	59.6	59.6	59.6	57.6	57.6
40°	40.0	41.9	41.9	41.9	42.9	42.9	42.9	43.9	42.9	42.9	42.9
42.5°	31.2	32.2	31.2	31.2	32.2	32.2	32.2	33.1	33.1	33.1	32.2
45°	25.3	25.3	24.4	25.3	25.3	26.3	26.3	26.3	26.3	25.3	25.3
47.5°	20.5	20.5	20.5	20.5	21.4	21.4	21.4	21.4	21.4	21.4	21.4
50°	16.6	16.6	16.6	17.5	17.5	17.5	16.6	17.5	17.5	17.5	16.6
52.5°	12.7	12.7	12.7	12.7	12.7	11.7	11.7	11.7	11.7	11.7	10.7
55°	9.7	9.7	9.7	9.7	9.7	10.7	9.7	10.7	9.7	9.7	8.8
57.5°	8.8	8.8	8.8	8.8	9.7	9.7	8.8	8.8	8.8	7.8	7.8
60°	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	7.8	6.8	6.8
62.5°	9.7	9.7	8.8	8.8	8.8	8.8	7.8	7.8	7.8	6.8	6.8
65°	9.7	9.7	8.8	9.7	9.7	8.8	8.8	7.8	7.8	6.8	6.8
67.5°	9.7	9.7	9.7	9.7	9.7	9.7	8.8	8.8	7.8	7.8	6.8
70°	9.7	9.7	9.7	9.7	9.7	9.7	8.8	8.8	7.8	7.8	6.8
72.5°	9.7	9.7	9.7	9.7	9.7	9.7	8.8	8.8	8.8	7.8	6.8
75°	9.7	9.7	9.7	9.7	9.7	8.8	8.8	8.8	7.8	7.8	6.8
77.5°	9.7	9.7	9.7	9.7	9.7	8.8	8.8	8.8	7.8	7.8	6.8
80°	9.7	9.7	9.7	9.7	9.7	9.7	8.8	8.8	7.8	7.8	6.8
82.5°	9.7	9.7	9.7	9.7	9.7	8.8	8.8	8.8	7.8	7.8	6.8
85°	9.7	8.8	8.8	8.8	8.8	8.8	7.8	7.8	6.8	6.8	5.8
87.5°	8.8	8.8	8.8	8.8	8.8	7.8	7.8	6.8	5.8	4.9	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192533

CATALOG NUMBER: LDA6A60930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	916.5	916.5	916.5	916.5	916.5	916.5	916.5	916.5
2.5°	483.2	474.4	470.4	463.5	457.7	454.8	444.0	456.7
5°	295.7	285.0	282.1	276.2	269.4	265.5	257.6	264.6
7.5°	168.9	156.1	150.2	145.4	138.6	132.7	125.9	129.8
10°	94.7	90.8	91.8	88.8	87.9	86.9	85.9	87.9
12.5°	87.9	84.9	85.9	84.0	83.0	83.0	82.0	83.0
15°	88.8	85.9	87.9	85.9	84.9	84.9	84.0	85.9
17.5°	96.6	94.7	96.6	94.7	95.7	94.7	95.7	96.6
20°	135.6	138.6	144.4	140.5	143.4	147.3	152.2	152.2
22.5°	477.3	539.7	547.5	578.8	658.8	655.8	709.6	711.5
25°	833.5	837.4	872.5	860.8	861.8	902.8	898.9	922.3
27.5°	479.3	478.3	485.1	472.4	476.3	479.3	468.4	481.2
30°	267.5	262.6	265.5	258.6	258.6	260.5	257.6	263.6
32.5°	148.3	144.4	144.4	139.5	138.6	137.6	134.7	137.6
35°	84.9	82.0	83.0	81.0	79.1	78.1	77.1	78.1
37.5°	58.6	56.7	57.6	55.7	53.7	52.8	51.7	52.8
40°	42.9	41.9	41.9	40.0	39.0	38.0	37.0	37.0
42.5°	32.2	31.2	31.2	29.2	28.3	27.3	26.3	27.3
45°	24.4	23.4	23.4	22.4	21.4	20.5	20.5	20.5
47.5°	21.4	20.5	21.4	20.5	19.5	19.5	19.5	19.5
50°	16.6	16.6	16.6	15.6	14.6	14.6	13.6	12.7
52.5°	10.7	9.7	9.7	8.8	8.8	7.8	7.8	7.8
55°	8.8	7.8	7.8	6.8	6.8	5.8	5.8	5.8
57.5°	6.8	6.8	5.8	5.8	4.9	4.9	4.9	4.9
60°	5.8	5.8	5.8	4.9	4.9	3.9	3.9	3.9
62.5°	5.8	4.9	4.9	4.9	3.9	3.9	3.9	3.9
65°	5.8	4.9	4.9	4.9	3.9	3.9	3.9	3.9
67.5°	5.8	4.9	4.9	4.9	3.9	3.9	3.9	3.9
70°	6.8	5.8	5.8	4.9	4.9	4.9	3.9	3.9
72.5°	6.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
75°	6.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
77.5°	6.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
80°	6.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
82.5°	5.8	5.8	5.8	4.9	4.9	4.9	4.9	4.9
85°	5.8	4.9	4.9	4.9	3.9	3.9	3.9	3.9
87.5°	3.9	3.9	2.9	2.9	2.9	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)