

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192542

Luminaire Tested: **LDA6A60930D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192542
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26685)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60930D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4257.1 lumens
Efficiency: N/A
Efficacy: 59.3 lumens/watt
Spacing Criteria (0/90/45): 2.12 / 1.05 / 1.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192542

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192542

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	76	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55		
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44		
8	67	55	47	42	65	54	47	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	43	38	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	75339	75339	75339
5°	121065	73855	47105
10°	179027	70740	31624
15°	243957	66919	23485
20°	301732	63151	22268
25°	349569	62163	36546
30°	381400	59560	36575
35°	391988	51477	28610
40°	381729	40512	22277
45°	346121	29964	17552
50°	272699	22149	11897
55°	162594	15770	6815
60°	83151	10493	2566
65°	39758	5565	1141
70°	18769	2500	1090
75°	7646	1652	1228
80°	3694	1831	1231
85°	1824	3082	1824

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192542

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.1	3.3
10°-20°	498.4	11.7
20°-30°	938.2	22.0
30°-40°	1142.4	26.8
40°-50°	951.0	22.3
50°-60°	455.5	10.7
60°-70°	109.4	2.6
70°-80°	17.2	0.4
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1577.6	37.1
0°-40°	2720.1	63.9
0°-60°	4126.5	96.9
0°-90°	4257.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4257.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1374	1374	1374	1374	1374	
5°	2200	1866	1342	976	856	241
15°	4298	2920	1179	535	414	1232
25°	5779	3413	1028	583	604	2655
35°	5857	2997	769	448	428	3629
45°	4464	2004	386	238	226	3381
55°	1701	827	165	93	71	1603
65°	306	179	43	14	9	351
75°	36	18	8	7	6	49
85°	3	3	5	4	3	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192542

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3
2.5°	1777.4	1714.9	1734.4	1730.5	1726.6	1706.1	1691.5	1678.8	1646.7	1646.7	1605.6
5°	2200.0	2126.8	2145.4	2131.6	2114.1	2082.9	2054.6	2022.3	1962.9	1937.5	1866.2
7.5°	2683.2	2600.2	2616.8	2589.5	2552.4	2510.4	2464.6	2404.0	2309.3	2251.8	2141.5
10°	3216.1	3098.0	3107.7	3066.8	3005.2	2948.7	2904.7	2789.6	2654.9	2559.2	2405.0
12.5°	3720.8	3617.2	3620.1	3562.6	3473.8	3404.4	3338.2	3185.8	3006.2	2869.6	2666.6
15°	4298.5	4171.7	4141.4	4063.3	3947.2	3862.3	3771.5	3579.2	3353.7	3173.2	2920.3
17.5°	4764.1	4633.4	4613.9	4540.6	4374.7	4272.2	4158.0	3941.3	3655.3	3430.9	3120.4
20°	5172.1	5042.3	5009.2	4914.5	4724.2	4606.9	4469.4	4213.6	3901.3	3625.1	3274.7
22.5°	5506.0	5363.4	5316.6	5199.4	4987.6	4855.9	4688.0	4408.8	4060.4	3752.0	3366.4
25°	5779.2	5617.2	5557.7	5425.0	5186.7	5041.3	4856.9	4544.5	4164.8	3824.2	3413.2
27.5°	5953.9	5791.9	5726.5	5574.2	5306.9	5150.7	4949.6	4611.8	4201.9	3834.0	3403.5
30°	6025.2	5857.3	5783.1	5610.4	5322.5	5157.5	4947.6	4582.6	4154.1	3763.7	3321.5
32.5°	5981.2	5816.4	5733.4	5546.0	5246.3	5068.6	4858.8	4469.4	4028.2	3624.1	3179.0
35°	5857.3	5694.3	5608.5	5408.4	5095.9	4910.6	4701.6	4298.5	3852.5	3439.7	2997.4
37.5°	5643.6	5489.3	5390.7	5192.6	4878.3	4688.9	4482.0	4075.0	3619.2	3230.8	2787.6
40°	5334.2	5187.7	5090.1	4878.3	4581.6	4390.3	4195.0	3782.2	3352.8	2974.0	2546.6
42.5°	4939.8	4805.1	4711.4	4505.4	4222.5	4034.1	3855.4	3459.2	3050.2	2690.0	2285.9
45°	4464.5	4347.4	4255.6	4084.8	3805.6	3627.1	3466.0	3106.7	2709.5	2378.6	2003.8
47.5°	3905.2	3808.5	3719.8	3564.6	3312.7	3143.9	3011.1	2682.2	2345.5	2034.2	1714.9
50°	3197.5	3128.3	3059.0	2897.9	2720.2	2572.9	2476.3	2183.4	1911.1	1667.1	1402.6
52.5°	2410.8	2368.9	2320.0	2204.9	2085.8	1999.9	1914.0	1691.5	1487.5	1305.9	1100.0
55°	1701.2	1679.8	1641.8	1594.9	1504.1	1445.6	1371.4	1258.2	1100.0	978.0	826.7
57.5°	1149.8	1144.0	1117.6	1089.3	1039.4	1019.9	957.6	884.3	795.5	704.7	597.3
60°	758.4	745.8	739.8	724.2	686.2	670.6	648.2	601.2	546.7	483.2	416.8
62.5°	488.0	481.2	476.3	469.5	446.0	446.0	423.6	402.1	361.2	322.1	279.2
65°	306.5	300.6	299.6	294.8	286.0	282.1	265.5	249.9	230.3	208.9	178.6
67.5°	197.2	188.4	183.5	180.6	174.7	167.9	162.1	155.2	139.5	126.9	107.4
70°	117.1	109.3	108.3	109.3	102.5	101.5	95.7	90.8	80.1	72.3	60.6
72.5°	66.4	62.5	61.5	61.5	57.6	56.7	52.8	49.8	43.9	38.0	33.1
75°	36.1	33.1	33.1	33.1	31.2	30.2	28.3	27.3	23.4	21.4	18.5
77.5°	20.5	19.5	19.5	18.5	17.5	16.6	15.6	15.6	13.6	12.7	11.7
80°	11.7	11.7	11.7	11.7	10.7	10.7	9.7	9.7	8.8	8.8	7.8
82.5°	6.8	6.8	6.8	6.8	6.8	6.8	5.8	5.8	5.8	5.8	4.9
85°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
87.5°	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192542

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3
2.5°	1587.1	1557.8	1555.9	1512.9	1485.6	1463.1	1446.6	1426.0	1380.2	1354.8	1336.2
5°	1816.4	1756.0	1724.6	1646.7	1603.6	1565.6	1518.7	1470.0	1394.8	1342.1	1299.1
7.5°	2054.6	1954.1	1887.7	1771.6	1712.9	1653.5	1574.4	1495.3	1392.8	1313.7	1248.4
10°	2276.2	2133.7	2028.2	1872.1	1795.9	1717.8	1606.6	1500.2	1372.4	1270.8	1184.9
12.5°	2493.8	2306.4	2161.0	1962.9	1870.1	1773.5	1630.9	1497.3	1347.0	1224.9	1124.4
15°	2701.7	2466.5	2281.0	2042.0	1933.5	1817.4	1646.7	1488.5	1317.6	1179.1	1064.9
17.5°	2867.7	2588.5	2366.0	2090.7	1968.7	1837.0	1640.8	1463.1	1277.7	1130.2	1005.3
20°	2981.8	2666.6	2412.8	2110.2	1976.5	1834.9	1618.3	1427.9	1235.6	1082.5	955.6
22.5°	3043.4	2701.7	2425.4	2104.3	1964.8	1816.4	1591.0	1395.8	1202.5	1049.3	928.2
25°	3065.8	2704.6	2411.8	2079.0	1938.5	1787.2	1558.8	1365.5	1176.2	1027.7	914.5
27.5°	3039.5	2663.7	2362.1	2026.2	1883.8	1734.4	1507.0	1322.5	1137.0	996.5	890.2
30°	2949.7	2568.0	2264.5	1932.5	1793.0	1649.6	1425.0	1243.6	1073.7	940.9	839.4
32.5°	2807.1	2427.4	2126.8	1803.7	1669.1	1531.4	1316.7	1144.0	985.8	860.9	770.1
35°	2630.5	2259.6	1966.8	1653.5	1526.5	1396.7	1192.7	1029.7	881.4	769.2	680.3
37.5°	2430.4	2073.2	1790.1	1502.1	1373.3	1251.3	1053.2	913.6	771.1	668.6	587.6
40°	2205.9	1859.4	1601.7	1321.5	1208.3	1097.1	913.6	786.7	656.9	566.1	495.8
42.5°	1965.8	1642.8	1404.5	1152.8	1039.4	937.9	773.1	658.9	543.6	468.5	412.9
45°	1711.0	1426.0	1197.6	972.2	869.7	781.8	631.5	528.0	444.0	386.5	344.5
47.5°	1444.6	1192.7	989.7	793.5	702.7	626.6	505.6	426.5	360.2	318.2	286.0
50°	1176.2	951.7	790.6	623.7	545.7	485.1	395.3	340.6	291.8	259.7	235.2
52.5°	919.4	735.9	605.1	470.5	410.9	369.0	308.4	270.4	233.2	208.9	190.3
55°	679.4	554.4	442.1	341.6	306.5	280.1	237.1	209.8	183.5	165.0	151.3
57.5°	491.0	397.3	315.2	250.9	227.4	209.8	178.6	160.1	141.5	127.8	117.1
60°	344.5	274.3	222.5	183.5	166.9	155.2	132.7	121.0	107.4	95.7	84.9
62.5°	226.4	184.5	155.2	129.8	120.0	111.3	95.7	86.9	75.2	67.4	57.6
65°	147.3	121.0	103.5	86.9	79.1	75.2	64.5	57.6	49.8	42.9	37.0
67.5°	89.8	75.2	65.4	54.7	50.8	46.8	40.0	35.1	30.2	25.3	22.4
70°	49.8	43.9	38.0	32.2	29.2	27.3	23.4	21.4	17.5	15.6	12.7
72.5°	29.2	25.3	22.4	18.5	17.5	16.6	13.6	12.7	10.7	9.7	8.8
75°	17.5	14.6	13.6	11.7	10.7	10.7	9.7	8.8	7.8	7.8	6.8
77.5°	10.7	9.7	8.8	7.8	7.8	7.8	6.8	6.8	6.8	5.8	5.8
80°	6.8	6.8	6.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
82.5°	4.9	4.9	4.9	3.9	4.9	3.9	4.9	4.9	4.9	4.9	4.9
85°	2.9	2.9	3.9	3.9	3.9	3.9	3.9	4.9	4.9	4.9	4.9
87.5°	2.9	2.9	3.9	3.9	3.9	3.9	3.9	4.9	4.9	4.9	3.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192542

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3
2.5°	1314.7	1278.6	1252.3	1232.7	1239.5	1205.4	1194.7	1157.6	1144.0	1144.0	1124.4
5°	1255.2	1197.6	1152.8	1124.4	1122.4	1073.7	1048.3	1001.4	976.1	957.6	938.9
7.5°	1184.0	1109.8	1050.3	1016.0	1006.3	948.8	914.5	867.7	829.6	805.2	782.8
10°	1107.8	1019.0	951.7	912.6	898.0	835.5	790.6	747.7	706.6	681.3	657.9
12.5°	1034.6	937.9	863.8	823.8	805.2	740.8	695.0	650.1	611.0	584.7	561.3
15°	967.3	864.8	786.7	746.7	726.1	662.8	616.8	573.0	534.8	510.5	489.0
17.5°	903.8	799.4	721.3	682.3	659.9	601.2	557.4	514.4	480.2	457.8	438.2
20°	856.0	752.6	680.3	646.2	623.7	569.1	530.9	493.9	465.6	449.0	430.4
22.5°	835.5	739.8	678.4	647.2	631.5	587.6	561.3	534.8	516.3	513.4	501.7
25°	832.5	748.7	697.9	671.6	661.8	628.5	612.9	596.4	582.7	586.6	588.6
27.5°	819.9	741.7	699.8	677.4	669.6	642.2	630.5	614.9	605.1	610.0	612.0
30°	776.0	703.7	664.7	646.2	638.3	611.0	601.2	583.7	575.9	576.9	575.9
32.5°	707.6	639.3	603.2	586.6	577.8	553.5	542.6	527.0	515.3	514.4	512.4
35°	624.6	563.2	530.0	515.3	506.6	486.1	476.3	461.7	448.1	447.1	445.0
37.5°	539.7	485.1	456.8	444.0	436.2	419.7	408.0	398.2	389.5	385.6	384.6
40°	457.8	409.0	388.5	378.7	372.9	355.3	349.5	339.6	332.8	328.9	327.9
42.5°	380.7	346.4	329.9	321.1	316.2	303.5	296.7	288.9	282.1	278.2	277.2
45°	323.0	294.8	279.2	272.4	268.5	256.8	251.9	244.0	238.1	235.2	234.2
47.5°	269.4	246.9	236.2	228.4	227.4	217.6	210.8	205.0	199.1	196.2	195.2
50°	220.6	202.0	193.3	188.4	187.4	177.7	172.8	167.9	163.0	160.1	158.2
52.5°	181.6	164.0	158.2	151.3	150.4	141.5	137.6	132.7	127.8	123.9	121.0
55°	143.4	129.8	123.9	118.1	117.1	107.4	103.5	97.6	92.7	88.8	84.9
57.5°	109.3	98.6	92.7	86.9	85.9	79.1	72.3	67.4	62.5	57.6	54.7
60°	80.1	69.3	62.5	59.6	56.7	49.8	44.8	40.9	37.0	34.1	31.2
62.5°	52.8	44.8	40.0	36.1	34.1	29.2	26.3	23.4	21.4	20.5	19.5
65°	32.2	27.3	23.4	21.4	21.4	18.5	16.6	14.6	13.6	13.6	12.7
67.5°	19.5	16.6	14.6	13.6	12.7	11.7	10.7	10.7	9.7	9.7	8.8
70°	11.7	10.7	9.7	8.8	8.8	8.8	8.8	8.8	7.8	7.8	7.8
72.5°	8.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	6.8	6.8	6.8
75°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	5.8
77.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
80°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	4.9	4.9	4.9
82.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
85°	4.9	4.9	4.9	4.9	4.9	4.9	3.9	3.9	3.9	3.9	3.9
87.5°	4.9	3.9	3.9	3.9	3.9	3.9	2.9	2.9	2.9	2.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192542

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3	1374.3
2.5°	1114.6	1122.4	1110.7	1102.9	1095.1	1101.0	1073.7	1062.0
5°	921.4	912.6	906.7	899.9	888.2	890.2	866.8	856.0
7.5°	762.3	756.5	741.7	733.9	722.2	722.2	700.8	692.0
10°	636.3	627.6	613.9	607.1	596.4	587.6	576.9	568.1
12.5°	540.7	530.9	519.2	513.4	502.7	495.8	485.1	487.1
15°	469.5	459.8	449.0	443.1	434.3	427.5	418.7	413.8
17.5°	419.7	410.9	402.1	396.3	389.5	383.6	375.8	374.8
20°	415.8	409.0	404.1	400.2	394.3	390.4	386.5	381.7
22.5°	497.8	498.8	499.7	499.7	500.7	500.7	501.7	491.9
25°	587.6	598.3	598.3	601.2	610.0	610.0	608.1	604.2
27.5°	611.0	621.7	618.8	620.7	629.5	631.5	624.6	625.6
30°	572.0	581.7	575.9	576.9	582.7	582.7	573.9	577.8
32.5°	506.6	512.4	504.6	504.6	509.5	508.5	502.7	502.7
35°	437.2	440.1	433.3	436.2	436.2	433.3	427.5	427.5
37.5°	377.8	378.7	371.9	372.9	372.9	370.0	364.1	364.1
40°	321.1	324.0	318.2	320.1	318.2	315.2	312.3	311.3
42.5°	271.4	273.3	268.5	271.4	270.4	270.4	269.4	270.4
45°	228.4	230.3	226.4	228.4	229.3	228.4	225.4	226.4
47.5°	189.4	191.3	191.3	189.4	188.4	183.5	180.6	180.6
50°	153.3	152.3	151.3	148.3	145.4	142.5	139.5	139.5
52.5°	115.2	113.2	112.2	109.3	108.3	105.4	105.4	102.5
55°	79.1	78.1	78.1	75.2	75.2	72.3	71.3	71.3
57.5°	49.8	47.8	48.7	46.8	45.8	42.9	42.9	41.9
60°	28.3	27.3	27.3	26.3	25.3	23.4	23.4	23.4
62.5°	18.5	17.5	17.5	16.6	16.6	15.6	15.6	14.6
65°	11.7	10.7	10.7	9.7	9.7	8.8	8.8	8.8
67.5°	8.8	7.8	7.8	7.8	7.8	7.8	6.8	6.8
70°	7.8	7.8	6.8	6.8	6.8	6.8	6.8	6.8
72.5°	6.8	6.8	6.8	6.8	5.8	5.8	5.8	5.8
75°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
77.5°	5.8	4.9	4.9	4.9	4.9	4.9	4.9	4.9
80°	4.9	4.9	4.9	4.9	4.9	4.9	3.9	3.9
82.5°	4.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
85°	3.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
87.5°	1.9	1.9	1.9	1.9	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)