

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192543

Luminaire Tested: **LDA6A60935D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192543
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60935D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5244.5 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192543

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192543

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104	110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91	103	98	94	90		95	91	88		92	89	86		89	86	84
3	99	91	85	80	96	89	84	80		87	82	78		84	80	77		82	79	76
4	92	83	76	71	90	82	76	71		79	74	70		77	73	69		75	71	68
5	86	76	69	64	84	75	68	63		73	67	63		71	66	62		69	65	61
6	80	69	62	57	79	69	62	57		67	61	56		65	60	56		64	59	55
7	75	64	56	51	73	63	56	51		62	55	51		60	55	50		59	54	50
8	70	59	51	46	69	58	51	46		57	50	46		56	50	46		54	49	46
9	66	54	47	42	64	53	47	42		52	46	42		51	46	42		50	45	41
10	61	50	43	38	60	49	43	38		48	42	38		48	42	38		47	41	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	81167	81167	81167
5°	157269	77344	26084
10°	267202	67684	11712
15°	411739	53984	18627
20°	596038	35131	32395
25°	874496	33903	41658
30°	1016808	32119	31916
35°	1029176	17012	16871
40°	852089	6412	7078
45°	643547	2179	2589
50°	440293	802	802
55°	61236	698	105
60°	1601	680	0
65°	415	947	0
70°	176	1170	0
75°	0	1546	0
80°	0	2620	347
85°	0	5221	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P1192543

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.3	3.0
10°-20°	656.6	12.5
20°-30°	1497.8	28.6
30°-40°	1733.3	33.0
40°-50°	1045.3	19.9
50°-60°	142.0	2.7
60°-70°	4.6	0.1
70°-80°	5.0	0.1
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2309.7	44.0
0°-40°	4042.9	77.1
0°-60°	5230.3	99.7
0°-90°	5244.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5244.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1481	1481	1481	1481	1481	
5°	2858	2340	1406	769	474	333
15°	7255	4078	951	293	328	2148
25°	14458	4832	560	674	689	6543
35°	15378	3684	254	259	252	9268
45°	8301	1003	28	34	33	6491
55°	641	7	7	5	1	1256
65°	3	4	7	4	0	5
75°	0	5	7	5	0	0
85°	0	5	8	5	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P1192543

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6
2.5°	2141.1	2121.3	2129.7	2107.8	2052.6	2041.1	2040.0	2025.5	1978.6	1942.2	1898.3
5°	2857.9	2856.9	2862.1	2815.3	2718.4	2688.2	2673.5	2638.1	2524.5	2437.0	2340.1
7.5°	3753.0	3746.7	3740.4	3655.0	3502.9	3444.5	3407.0	3278.9	3122.6	2967.3	2794.4
10°	4800.1	4796.9	4773.0	4622.9	4379.2	4271.8	4198.8	3995.7	3744.5	3523.7	3229.9
12.5°	6016.0	5987.8	5945.2	5725.2	5390.8	5274.1	5113.6	4791.7	4406.2	4067.6	3657.1
15°	7254.8	7214.2	7138.1	6855.7	6441.0	6242.0	6043.0	5618.9	5095.9	4604.1	4078.1
17.5°	8466.5	8421.7	8243.5	7764.2	7358.9	7116.2	6895.3	6312.9	5698.2	5065.7	4398.9
20°	10216.9	10054.4	9743.9	8988.5	8235.2	7797.6	7539.2	6923.4	6162.9	5426.3	4627.0
22.5°	12554.9	12194.5	11532.8	10305.4	9229.2	8597.7	8174.8	7355.8	6497.3	5661.7	4767.8
25°	14457.5	14293.8	13541.6	11795.4	10115.8	9371.9	8783.2	7699.7	6741.1	5819.0	4832.4
27.5°	15683.7	15643.2	14783.6	13029.0	10839.9	9863.7	9206.3	7926.8	6858.8	5852.4	4801.0
30°	16063.1	16126.6	15301.3	13447.9	11049.4	9962.7	9243.7	7930.0	6768.2	5701.3	4601.1
32.5°	16034.9	16038.0	15026.3	13086.3	10708.7	9675.1	8931.1	7666.3	6433.8	5323.1	4220.8
35°	15378.5	15217.0	14073.0	11975.6	9915.7	9004.1	8312.4	7155.8	5882.5	4754.3	3684.2
37.5°	13937.5	13726.0	12392.4	10553.4	8977.1	8134.2	7575.7	6485.8	5226.2	4146.8	3129.9
40°	11906.9	11606.8	10506.5	9231.3	7949.7	7316.3	6847.4	5736.7	4523.9	3550.8	2609.9
42.5°	9874.1	9727.2	9000.0	7963.2	7086.0	6490.0	6000.4	4952.1	3848.7	2963.2	1952.5
45°	8300.9	8174.8	7686.1	7002.6	6142.1	5598.1	5126.2	4134.2	2990.2	1988.0	1003.4
47.5°	7154.7	7052.6	6584.8	5866.9	4923.0	4328.1	3841.5	2711.1	1694.2	858.5	251.1
50°	5162.6	5058.4	4600.0	3768.6	2916.3	2418.3	2068.2	1210.6	480.4	174.0	26.1
52.5°	2530.7	2445.3	2133.8	1597.2	1072.1	771.0	563.7	227.1	55.2	18.8	12.6
55°	640.7	588.7	490.7	308.4	151.1	90.7	58.4	20.8	13.5	10.5	7.3
57.5°	36.4	35.5	32.3	24.0	17.7	15.6	13.5	10.5	7.3	6.2	5.2
60°	14.6	13.5	12.6	10.5	8.3	7.3	7.3	5.2	4.1	4.1	4.1
62.5°	6.2	6.2	6.2	5.2	4.1	4.1	4.1	3.2	4.1	4.1	4.1
65°	3.2	3.2	3.2	2.1	2.1	2.1	3.2	3.2	3.2	4.1	4.1
67.5°	2.1	1.1	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.1	4.1
70°	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.1	5.2
72.5°	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.1	5.2
75°	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.2	4.1	4.1	5.2
77.5°	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.2	4.1	4.1	5.2
80°	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.2	4.1	4.1	5.2
82.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.1	4.1	5.2
85°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.1	4.1	5.2
87.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.1	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192543

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6
2.5°	1842.1	1804.6	1749.4	1712.9	1677.5	1644.1	1588.9	1557.7	1501.4	1449.2	1404.5
5°	2223.4	2129.7	2016.1	1919.1	1856.6	1795.2	1683.7	1601.4	1498.2	1405.5	1320.1
7.5°	2609.0	2443.2	2256.8	2097.4	2000.4	1905.6	1738.9	1605.6	1459.7	1327.4	1201.3
10°	2959.1	2710.0	2446.4	2218.2	2086.9	1964.0	1744.1	1567.1	1379.4	1215.9	1057.5
12.5°	3284.0	2943.3	2599.6	2301.5	2139.1	1991.0	1722.3	1505.5	1282.5	1088.8	904.4
15°	3573.7	3136.1	2711.1	2349.5	2158.8	1983.8	1671.3	1419.0	1168.0	951.2	717.9
17.5°	3793.5	3255.9	2760.1	2342.2	2123.4	1928.5	1583.7	1310.7	1046.0	783.5	520.0
20°	3927.0	3307.0	2749.6	2285.9	2047.3	1841.0	1479.5	1193.0	899.2	602.2	458.4
22.5°	3983.1	3302.8	2700.6	2201.6	1953.6	1745.2	1379.4	1078.3	744.9	544.9	478.3
25°	3992.5	3260.2	2631.9	2108.9	1860.9	1653.5	1278.4	948.2	647.1	560.5	535.6
27.5°	3920.6	3160.1	2502.7	1975.4	1730.6	1516.0	1127.3	753.3	607.5	558.5	575.2
30°	3708.1	2931.9	2274.5	1741.0	1504.6	1289.9	805.4	590.8	504.2	507.4	511.6
32.5°	3334.1	2552.7	1907.7	1398.2	1139.9	850.2	501.2	394.9	383.4	383.4	381.3
35°	2835.0	2089.0	1497.3	884.6	566.8	408.5	259.4	260.5	255.3	254.2	253.2
37.5°	2319.3	1648.2	948.2	365.7	245.9	170.8	153.2	155.2	153.2	156.3	154.1
40°	1828.6	1018.0	346.0	116.7	86.5	83.4	85.4	87.5	87.5	89.6	89.6
42.5°	1062.7	337.5	90.7	46.9	46.9	44.8	45.8	47.9	49.0	50.0	49.0
45°	315.7	69.8	29.1	26.1	26.1	25.0	25.0	26.1	27.1	28.1	28.1
47.5°	50.0	19.7	16.7	14.6	14.6	14.6	14.6	14.6	15.6	15.6	16.7
50°	15.6	12.6	10.5	9.4	9.4	8.3	8.3	9.4	9.4	9.4	10.5
52.5°	9.4	7.3	7.3	6.2	7.3	7.3	6.2	7.3	7.3	7.3	8.3
55°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3
57.5°	5.2	5.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
60°	5.2	5.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	7.3
62.5°	5.2	5.2	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3
65°	5.2	5.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3
67.5°	5.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3
70°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
72.5°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
75°	6.2	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	8.3
77.5°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3	8.3	8.3	8.3
80°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3
82.5°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3
85°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3
87.5°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192543

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6
2.5°	1365.9	1318.0	1295.1	1262.8	1239.9	1188.8	1168.0	1132.5	1103.4	1055.4	1058.6
5°	1247.2	1156.5	1095.0	1047.1	1013.7	932.4	878.3	821.1	768.9	704.3	680.3
7.5°	1082.6	971.1	877.2	820.0	777.2	668.9	549.1	455.3	384.5	333.4	313.7
10°	917.9	773.1	624.2	535.6	474.0	369.8	316.7	291.7	268.8	240.7	221.9
12.5°	726.1	520.0	384.5	349.0	324.0	289.7	255.3	228.1	233.4	234.5	241.8
15°	496.0	374.1	331.3	307.3	280.3	260.5	272.0	279.2	292.8	293.8	303.2
17.5°	403.2	351.1	316.7	315.7	317.8	329.3	346.9	356.3	374.1	378.2	391.8
20°	403.2	373.0	402.1	402.1	407.4	423.0	445.9	459.5	479.3	486.6	503.3
22.5°	459.5	480.4	516.8	520.9	523.0	539.7	568.8	582.5	605.4	609.5	627.2
25°	560.5	579.3	612.7	615.7	616.8	629.3	651.2	658.5	674.1	665.8	676.2
27.5°	592.8	601.1	622.0	624.2	618.9	624.2	632.4	632.4	637.7	621.0	624.2
30°	520.9	523.0	533.5	534.5	523.0	525.1	526.2	525.1	524.1	506.3	506.3
32.5°	386.5	386.5	400.1	397.0	384.5	387.6	387.6	387.6	386.5	371.9	369.8
35°	256.3	257.4	268.8	266.7	257.4	259.4	259.4	262.6	259.4	251.1	249.1
37.5°	156.3	157.3	162.6	163.5	160.5	161.5	162.6	161.5	163.5	159.4	157.3
40°	90.7	92.7	96.9	98.0	96.9	96.9	98.0	98.9	103.1	98.0	95.9
42.5°	53.1	54.2	56.3	56.3	56.3	56.3	57.3	58.4	59.3	58.4	57.3
45°	30.2	31.3	32.3	32.3	33.4	32.3	33.4	33.4	34.4	33.4	33.4
47.5°	17.7	17.7	18.8	18.8	19.7	18.8	19.7	19.7	19.7	18.8	18.8
50°	10.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	10.5	10.5
52.5°	8.3	8.3	8.3	8.3	8.3	7.3	7.3	7.3	7.3	6.2	6.2
55°	7.3	7.3	7.3	7.3	7.3	7.3	6.2	5.2	5.2	4.1	4.1
57.5°	6.2	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	3.2	3.2
60°	7.3	7.3	7.3	7.3	6.2	6.2	6.2	5.2	4.1	3.2	3.2
62.5°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	3.2	3.2
65°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	3.2	3.2
67.5°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	4.1	3.2
70°	7.3	8.3	8.3	7.3	7.3	7.3	6.2	5.2	5.2	4.1	3.2
72.5°	7.3	8.3	8.3	7.3	7.3	7.3	6.2	5.2	5.2	4.1	3.2
75°	8.3	8.3	8.3	8.3	7.3	7.3	6.2	6.2	5.2	4.1	3.2
77.5°	8.3	8.3	8.3	8.3	7.3	7.3	6.2	6.2	5.2	4.1	3.2
80°	8.3	8.3	8.3	8.3	8.3	7.3	7.3	6.2	5.2	4.1	4.1
82.5°	8.3	8.3	8.3	8.3	8.3	7.3	7.3	6.2	5.2	4.1	4.1
85°	8.3	8.3	8.3	8.3	8.3	7.3	7.3	6.2	5.2	4.1	3.2
87.5°	8.3	8.3	8.3	8.3	7.3	7.3	6.2	6.2	5.2	4.1	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192543

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6	1480.6
2.5°	1020.1	996.1	985.7	1002.3	994.0	969.0	974.1	958.5
5°	608.4	572.0	549.1	559.4	526.2	496.0	496.0	474.0
7.5°	293.8	282.3	276.1	278.2	270.9	261.5	256.3	256.3
10°	206.3	202.2	203.1	203.1	209.5	208.4	211.5	210.4
12.5°	244.8	246.9	248.0	252.1	257.4	257.4	260.5	258.3
15°	313.7	311.6	317.8	318.8	327.2	328.2	332.4	328.2
17.5°	399.1	403.2	409.4	408.5	425.0	426.1	426.1	425.0
20°	513.6	516.8	523.0	525.1	544.9	547.0	554.3	555.3
22.5°	638.7	638.7	641.8	646.0	664.7	665.8	668.9	668.9
25°	681.4	675.2	676.2	681.4	691.8	687.6	690.8	688.7
27.5°	626.2	616.8	614.8	622.0	629.3	617.8	622.0	622.0
30°	508.5	500.1	498.0	505.3	510.6	498.0	502.2	504.2
32.5°	371.9	366.8	365.7	370.9	375.1	364.7	368.9	371.9
35°	251.1	249.1	246.9	248.0	254.2	245.9	250.1	252.1
37.5°	159.4	155.2	156.3	158.4	162.6	157.3	161.5	161.5
40°	98.0	95.9	95.9	98.0	100.0	95.9	98.0	98.9
42.5°	57.3	57.3	57.3	58.4	59.3	57.3	57.3	58.4
45°	33.4	32.3	32.3	33.4	34.4	32.3	33.4	33.4
47.5°	18.8	17.7	17.7	18.8	18.8	17.7	18.8	18.8
50°	10.5	9.4	9.4	10.5	10.5	9.4	9.4	9.4
52.5°	5.2	5.2	5.2	5.2	5.2	5.2	4.1	4.1
55°	3.2	3.2	2.1	2.1	2.1	2.1	2.1	1.1
57.5°	2.1	2.1	1.1	1.1	1.1	1.1	0.0	0.0
60°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
62.5°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
65°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
67.5°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.2	2.1	2.1	1.1	1.1	1.1	0.0	0.0
72.5°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
75°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
77.5°	3.2	2.1	2.1	2.1	1.1	1.1	1.1	0.0
80°	3.2	2.1	2.1	2.1	1.1	1.1	1.1	1.1
82.5°	3.2	2.1	2.1	2.1	1.1	1.1	1.1	1.1
85°	3.2	2.1	2.1	2.1	1.1	1.1	1.1	0.0
87.5°	3.2	2.1	2.1	2.1	1.1	1.1	1.1	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)