

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192545

Luminaire Tested: **LDA6A60935D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192545
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26689)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60935D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4830.8 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 2.34 / 0.96 / 1.3
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192545

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192545

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	51	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	61	50	43	38	49	43	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	75389	75389	75389
5°	147391	71665	26139
10°	248092	61533	5800
15°	377811	46595	9518
20°	545954	37739	106182
25°	812515	61062	30685
30°	938474	20902	6071
35°	938777	4671	3279
40°	767302	2605	2011
45°	581037	1698	1295
50°	385864	1151	887
55°	62029	994	698
60°	3892	1031	570
65°	1219	1349	675
70°	657	1507	833
75°	445	1758	1101
80°	347	2620	1642
85°	692	5221	2013

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192545

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.6	3.0
10°-20°	613.8	12.7
20°-30°	1444.9	29.9
30°-40°	1522.4	31.5
40°-50°	949.2	19.6
50°-60°	136.4	2.8
60°-70°	8.7	0.2
70°-80°	6.8	0.1
80°-90°	5.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2202.2	45.6
0°-40°	3724.6	77.1
0°-60°	4810.2	99.6
0°-90°	4830.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4830.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1375	1375	1375	1375	1375	
5°	2678	2168	1302	676	475	311
15°	6657	3768	821	143	168	1982
25°	13433	4517	1010	730	507	6044
35°	14028	3309	70	65	49	8462
45°	7495	916	22	24	17	5866
55°	649	17	10	12	7	1166
65°	9	7	10	8	5	14
75°	2	5	8	8	5	2
85°	1	5	8	6	3	1
90°	0	0	0	0	0	

TEST NUMBER: P1192545

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2
2.5°	2007.5	1993.9	1998.1	1966.9	1925.2	1944.0	1897.1	1898.2	1868.9	1795.0	1762.7
5°	2678.4	2676.3	2673.2	2615.9	2541.9	2550.3	2481.5	2455.5	2380.5	2250.2	2168.0
7.5°	3511.9	3512.9	3497.3	3357.6	3275.4	3270.2	3161.8	3083.7	2944.1	2738.9	2588.9
10°	4456.8	4485.9	4457.8	4243.2	4090.0	4092.1	3897.4	3747.3	3523.4	3224.3	3010.7
12.5°	5566.3	5570.5	5526.7	5244.4	5011.0	4993.3	4731.8	4445.3	4104.6	3714.0	3403.5
15°	6657.0	6686.2	6629.9	6282.0	5957.0	5908.0	5574.6	5196.5	4773.5	4195.3	3768.2
17.5°	7866.5	7820.7	7671.8	7173.7	6783.0	6711.2	6352.8	5857.9	5318.3	4619.2	4058.8
20°	9358.4	9374.0	9058.4	8314.5	7654.0	7373.8	6958.0	6416.4	5743.4	4930.8	4252.6
22.5°	11489.9	11405.5	10728.3	9525.1	8532.2	8158.2	7565.5	6818.5	6061.2	5167.2	4397.3
25°	13432.8	13210.9	12586.9	10931.4	9377.1	8914.6	8300.9	7161.3	6324.7	5342.3	4517.2
27.5°	14548.5	14449.6	13742.2	12072.3	10059.5	9408.3	8544.7	7413.4	6481.0	5428.7	4551.6
30°	14825.6	14843.4	14214.1	12450.4	10221.0	9477.2	8584.3	7406.1	6375.7	5274.6	4353.6
32.5°	14754.8	14659.0	13872.4	12032.7	9790.7	9113.6	8196.8	7074.8	5957.0	4815.2	3860.9
35°	14027.7	13887.1	12919.2	10946.1	9060.4	8402.0	7570.6	6532.0	5372.6	4229.7	3308.7
37.5°	12644.1	12481.7	11364.9	9641.7	8184.3	7626.9	6908.1	5927.7	4781.8	3683.7	2823.2
40°	10722.1	10519.9	9586.5	8391.6	7242.5	6852.9	6245.5	5238.1	4169.2	3167.1	2375.2
42.5°	8924.9	8828.1	8267.6	7242.5	6468.4	6092.4	5479.8	4542.2	3558.7	2638.8	1758.5
45°	7494.6	7430.0	7058.1	6407.0	5621.5	5269.3	4692.2	3777.6	2707.7	1777.3	915.8
47.5°	6560.2	6395.5	6031.9	5348.5	4475.6	4036.9	3486.8	2488.8	1527.2	787.6	281.2
50°	4524.4	4540.1	4129.6	3376.4	2633.7	2262.8	1868.9	1145.0	505.2	171.9	49.0
52.5°	2382.5	2206.5	1917.9	1432.4	997.0	760.5	555.3	229.2	91.6	34.4	26.1
55°	649.0	569.8	455.3	321.9	174.0	121.9	80.2	42.8	30.2	24.0	16.7
57.5°	63.6	60.4	55.2	44.8	38.5	35.5	32.3	26.1	20.8	14.6	10.4
60°	35.5	34.4	32.3	28.1	25.0	22.9	20.8	17.7	12.6	9.4	8.3
62.5°	19.7	18.8	17.7	15.6	13.5	12.6	12.6	10.4	8.3	7.3	7.3
65°	9.4	9.4	9.4	9.4	9.4	8.3	7.3	7.3	7.3	7.3	7.3
67.5°	7.3	7.3	7.3	6.2	6.2	6.2	6.2	6.2	6.2	5.2	6.2
70°	4.1	4.1	5.2	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.2
72.5°	2.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.1	4.1	5.2
75°	2.1	2.1	2.1	2.1	3.2	3.2	3.2	3.2	4.1	4.1	5.2
77.5°	2.1	2.1	2.1	2.1	2.1	2.1	3.2	3.2	4.1	4.1	5.2
80°	1.1	1.1	1.1	2.1	2.1	2.1	2.1	3.2	4.1	4.1	5.2
82.5°	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.2	4.1	4.1	5.2
85°	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.1	5.2
87.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.1	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192545

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2
2.5°	1729.4	1678.3	1627.3	1576.2	1574.1	1543.9	1499.1	1439.7	1390.8	1349.1	1308.5
5°	2085.7	1980.4	1875.3	1770.0	1738.8	1684.6	1587.7	1478.2	1384.5	1302.3	1223.1
7.5°	2443.0	2265.9	2099.2	1934.6	1868.9	1786.7	1635.6	1477.3	1341.8	1221.0	1103.3
10°	2761.8	2504.4	2270.1	2038.8	1944.0	1836.6	1633.5	1432.4	1260.6	1105.4	955.4
12.5°	3055.6	2697.2	2400.2	2108.6	1979.4	1849.2	1601.2	1361.6	1156.4	971.0	798.0
15°	3313.9	2874.2	2492.0	2139.8	1981.5	1825.2	1533.6	1263.7	1033.5	821.0	633.4
17.5°	3498.3	2962.8	2522.2	2111.7	1927.3	1752.3	1433.5	1145.0	897.0	675.1	493.8
20°	3610.9	2999.3	2506.6	2059.6	1863.8	1682.5	1359.6	1079.3	838.6	646.9	524.0
22.5°	3684.8	3034.7	2512.8	2058.5	1862.7	1691.9	1390.8	1128.3	932.4	829.2	814.7
25°	3763.9	3084.7	2558.6	2105.4	1923.1	1764.7	1473.1	1216.9	1053.2	1009.5	1015.8
27.5°	3759.8	3062.9	2514.9	2064.9	1873.2	1712.7	1371.0	1047.0	893.8	770.9	726.1
30°	3535.8	2809.7	2216.9	1712.7	1486.7	1289.7	839.7	545.9	377.1	330.2	283.3
32.5°	3011.8	2276.3	1657.5	1184.6	930.3	694.8	330.2	175.0	149.0	125.0	113.6
35°	2504.4	1814.8	1239.8	715.7	452.1	280.3	118.8	78.1	74.0	69.8	69.8
37.5°	2070.0	1425.1	801.1	302.1	165.6	101.0	57.3	52.0	50.0	49.0	49.0
40°	1619.0	929.3	346.9	100.0	53.1	45.8	40.6	38.5	37.5	36.4	37.5
42.5°	955.4	374.0	101.0	37.5	35.5	33.4	30.2	29.1	29.1	28.1	29.1
45°	325.0	96.9	33.4	27.1	25.0	25.0	22.9	22.9	22.9	21.9	24.0
47.5°	84.3	30.2	21.9	19.7	18.8	18.8	17.7	17.7	17.7	17.7	18.8
50°	29.1	19.7	15.6	14.6	13.5	14.6	13.5	13.5	13.5	13.5	14.6
52.5°	17.7	13.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5
55°	11.5	10.4	9.4	9.4	9.4	9.4	9.4	10.4	10.4	10.4	10.4
57.5°	9.4	8.3	8.3	8.3	8.3	8.3	9.4	8.3	8.3	9.4	10.4
60°	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	9.4	9.4	10.4
62.5°	7.3	8.3	8.3	8.3	8.3	8.3	8.3	9.4	9.4	9.4	10.4
65°	7.3	7.3	7.3	8.3	8.3	8.3	9.4	9.4	9.4	10.4	10.4
67.5°	6.2	6.2	7.3	7.3	8.3	8.3	8.3	9.4	9.4	9.4	10.4
70°	6.2	6.2	6.2	7.3	7.3	7.3	7.3	8.3	8.3	9.4	9.4
72.5°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	8.3	8.3	8.3	9.4
75°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	7.3	8.3	8.3	9.4
77.5°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	8.3	8.3	8.3	9.4
80°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3
82.5°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3
85°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	7.3	8.3	8.3	8.3
87.5°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192545

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2
2.5°	1252.2	1234.5	1172.0	1163.7	1153.3	1102.2	1081.4	1045.9	995.9	981.3	963.6
5°	1130.3	1072.0	980.3	955.4	928.2	848.0	799.0	740.8	676.1	640.7	607.3
7.5°	975.1	893.8	772.0	723.0	692.8	605.3	527.2	449.0	354.2	300.0	265.6
10°	802.2	690.7	563.6	507.3	466.7	339.6	265.6	231.3	199.0	172.9	150.0
12.5°	628.2	502.2	358.4	293.8	261.5	216.7	176.1	133.3	118.8	117.7	113.6
15°	460.5	319.9	241.6	217.8	194.8	139.6	138.6	138.6	142.7	145.9	146.8
17.5°	339.6	281.2	220.8	206.3	216.7	225.1	239.6	261.5	279.2	329.3	318.8
20°	498.0	493.8	538.6	595.9	636.6	723.0	832.4	956.3	1085.5	1229.3	1338.7
22.5°	854.2	958.4	1039.7	1108.4	1145.0	1242.8	1329.3	1372.0	1397.1	1384.5	1366.9
25°	1043.8	1081.4	1056.4	1032.4	1035.5	947.0	882.4	800.1	730.3	666.8	629.3
27.5°	624.0	570.9	495.8	443.8	433.3	374.0	330.2	284.4	270.9	229.2	211.4
30°	225.1	209.4	185.5	166.7	164.6	149.0	139.6	129.2	128.2	118.8	113.6
32.5°	102.1	102.1	93.7	95.9	93.7	90.7	89.6	86.5	86.5	83.4	81.3
35°	66.7	67.8	66.7	66.7	65.7	65.7	65.7	63.6	64.6	62.5	59.3
37.5°	49.0	50.0	47.9	49.0	49.0	49.0	49.0	47.9	46.9	44.8	43.7
40°	37.5	37.5	37.5	37.5	37.5	37.5	37.5	36.4	36.4	35.5	33.4
42.5°	29.1	30.2	30.2	30.2	30.2	30.2	30.2	30.2	30.2	29.1	29.1
45°	24.0	25.0	24.0	25.0	25.0	25.0	24.0	24.0	24.0	22.9	21.9
47.5°	18.8	18.8	17.7	17.7	17.7	17.7	17.7	17.7	17.7	17.7	16.7
50°	14.6	14.6	14.6	14.6	14.6	14.6	15.6	14.6	14.6	14.6	14.6
52.5°	11.5	12.6	12.6	13.5	13.5	13.5	13.5	13.5	12.6	12.6	11.5
55°	10.4	11.5	11.5	12.6	12.6	12.6	12.6	11.5	11.5	11.5	10.4
57.5°	10.4	11.5	11.5	11.5	11.5	11.5	11.5	10.4	10.4	9.4	9.4
60°	10.4	10.4	10.4	11.5	11.5	10.4	10.4	9.4	9.4	8.3	8.3
62.5°	10.4	10.4	10.4	11.5	11.5	10.4	10.4	9.4	8.3	8.3	7.3
65°	10.4	11.5	10.4	11.5	11.5	10.4	10.4	9.4	8.3	8.3	7.3
67.5°	10.4	11.5	11.5	11.5	10.4	10.4	10.4	9.4	8.3	8.3	7.3
70°	9.4	10.4	10.4	10.4	10.4	10.4	9.4	9.4	8.3	8.3	7.3
72.5°	9.4	10.4	9.4	10.4	10.4	9.4	9.4	9.4	8.3	8.3	7.3
75°	9.4	9.4	9.4	9.4	9.4	9.4	9.4	8.3	8.3	7.3	7.3
77.5°	9.4	9.4	9.4	9.4	9.4	9.4	8.3	8.3	8.3	7.3	7.3
80°	9.4	9.4	9.4	9.4	9.4	9.4	8.3	8.3	7.3	7.3	6.2
82.5°	8.3	9.4	9.4	9.4	9.4	9.4	8.3	8.3	7.3	7.3	6.2
85°	8.3	8.3	8.3	8.3	8.3	8.3	7.3	7.3	6.2	5.2	5.2
87.5°	7.3	8.3	7.3	7.3	7.3	7.3	6.2	5.2	4.1	4.1	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192545

CATALOG NUMBER: LDA6A60935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2	1375.2
2.5°	935.5	909.5	910.5	914.7	888.7	875.1	872.0	858.5
5°	562.6	532.4	527.2	523.0	486.6	472.0	460.5	475.0
7.5°	241.6	230.2	228.1	225.1	208.4	200.0	195.8	200.0
10°	119.8	112.5	113.6	114.5	109.4	106.3	105.2	104.2
12.5°	118.8	117.7	118.8	118.8	119.8	117.7	118.8	118.8
15°	154.1	154.1	157.3	159.4	164.6	163.5	165.6	167.7
17.5°	384.5	364.6	375.1	375.1	421.9	380.2	415.7	383.4
20°	1510.5	1581.5	1653.4	1713.8	1775.2	1794.0	1830.4	1820.1
22.5°	1339.7	1348.1	1337.6	1326.2	1323.1	1326.2	1270.0	1278.3
25°	575.0	570.9	554.2	536.5	541.8	545.9	526.1	507.3
27.5°	196.9	191.7	186.4	182.3	180.2	177.1	170.8	166.7
30°	111.5	108.3	106.3	105.2	103.1	101.0	98.0	95.9
32.5°	80.2	78.1	77.1	76.0	74.0	71.9	68.7	67.8
35°	59.3	57.3	56.3	55.2	53.1	51.1	50.0	49.0
37.5°	43.7	41.7	41.7	41.7	38.5	36.4	35.5	34.4
40°	33.4	32.3	32.3	32.3	30.2	29.1	28.1	28.1
42.5°	29.1	28.1	28.1	28.1	26.1	25.0	25.0	24.0
45°	21.9	20.8	20.8	19.7	18.8	18.8	17.7	16.7
47.5°	16.7	15.6	15.6	15.6	14.6	13.5	13.5	12.6
50°	13.5	13.5	12.6	13.5	11.5	11.5	11.5	10.4
52.5°	11.5	11.5	10.4	10.4	9.4	9.4	9.4	8.3
55°	10.4	9.4	9.4	9.4	8.3	8.3	8.3	7.3
57.5°	8.3	8.3	7.3	7.3	6.2	6.2	6.2	6.2
60°	7.3	7.3	6.2	6.2	5.2	5.2	5.2	5.2
62.5°	7.3	6.2	6.2	6.2	5.2	5.2	5.2	5.2
65°	7.3	6.2	6.2	6.2	5.2	5.2	5.2	5.2
67.5°	7.3	6.2	6.2	6.2	5.2	5.2	5.2	5.2
70°	7.3	7.3	6.2	6.2	6.2	5.2	5.2	5.2
72.5°	7.3	7.3	6.2	6.2	6.2	6.2	5.2	5.2
75°	6.2	6.2	6.2	6.2	5.2	5.2	5.2	5.2
77.5°	6.2	6.2	6.2	6.2	5.2	5.2	5.2	5.2
80°	6.2	6.2	5.2	5.2	5.2	5.2	5.2	5.2
82.5°	6.2	5.2	5.2	5.2	5.2	4.1	4.1	4.1
85°	4.1	4.1	4.1	4.1	3.2	3.2	3.2	3.2
87.5°	3.2	2.1	2.1	2.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)