

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192550

Luminaire Tested: **LDA6A60935D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192550
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26690)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60935D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5322.5 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 2.55 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192550

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192550

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	75	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65		
5	85	74	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	53631	53631	53631
5°	138454	49708	15535
10°	262654	37925	5216
15°	469657	24654	5199
20°	699810	16778	9486
25°	798500	20917	59550
30°	863538	17477	17800
35°	907095	8506	5581
40°	921441	3063	2834
45°	820961	2023	1698
50°	527258	1424	1151
55°	138805	994	593
60°	30951	1031	450
65°	2970	1219	532
70°	994	1507	657
75°	233	1991	1101
80°	0	3283	1642
85°	0	5913	2579



TEST NUMBER: P1192550

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.8	2.2
10°-20°	620.0	11.6
20°-30°	1454.8	27.3
30°-40°	1673.3	31.4
40°-50°	1188.7	22.3
50°-60°	241.7	4.5
60°-70°	12.1	0.2
70°-80°	7.2	0.1
80°-90°	6.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2193.6	41.2
0°-40°	3867.0	72.7
0°-60°	5297.3	99.5
0°-90°	5322.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5322.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	978	978	978	978	978	
5°	2516	1820	903	362	282	307
15°	8275	3720	434	98	92	2482
25°	13201	4481	346	755	984	6084
35°	13554	3146	127	94	83	8420
45°	10589	1119	26	28	22	7804
55°	1452	29	10	10	6	1959
65°	23	8	9	8	4	55
75°	1	5	9	8	5	2
85°	0	5	9	7	4	0
90°	0	0	0	0	0	

TEST NUMBER: P1192550

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	978.3	978.3	978.3	978.3	978.3	978.3	978.3	978.3	978.3	978.3	978.3
2.5°	1685.6	1634.6	1609.6	1608.6	1535.6	1559.6	1535.6	1516.9	1449.2	1421.1	1374.2
5°	2516.0	2453.5	2403.5	2381.7	2256.7	2229.5	2217.1	2153.5	2011.7	1929.5	1820.1
7.5°	3495.3	3429.8	3347.4	3281.7	3100.5	3049.5	3016.1	2906.8	2697.3	2531.7	2327.5
10°	4718.4	4679.9	4546.6	4425.7	4150.7	4044.4	3944.4	3689.1	3415.2	3082.7	2819.2
12.5°	6365.7	6275.0	6037.4	5795.8	5364.4	5206.1	5040.4	4632.0	4213.2	3692.3	3256.8
15°	8275.3	8198.2	7832.5	7438.8	6825.1	6564.7	6305.2	5662.3	5018.6	4347.6	3720.4
17.5°	10473.6	10327.7	9964.1	9298.4	8439.9	8030.5	7547.1	6728.2	5798.8	4887.3	4107.9
20°	11995.7	11909.2	11601.9	10963.2	9986.1	9445.3	8845.2	7721.1	6450.0	5319.7	4362.1
22.5°	12828.1	12741.7	12511.4	11947.8	11146.6	10603.9	9906.9	8524.3	6941.7	5610.3	4482.0
25°	13201.1	13144.8	13018.8	12559.3	11817.6	11328.9	10669.4	9079.6	7249.2	5742.6	4480.9
27.5°	13546.0	13560.6	13249.0	12870.9	12187.4	11696.7	11071.6	9329.6	7309.6	5676.0	4337.1
30°	13641.8	13605.3	13468.9	12936.5	12299.9	11765.4	11095.6	9197.4	7074.0	5381.1	4051.7
32.5°	13582.4	13583.5	13455.3	12889.7	12141.6	11543.5	10790.3	8723.3	6615.6	4918.5	3607.9
35°	13554.3	13544.9	13212.6	12715.7	11765.4	11062.2	10113.2	7962.7	5980.1	4327.8	3146.3
37.5°	13275.1	13218.8	12979.2	12305.1	11062.2	10163.1	9141.1	7032.4	5197.7	3713.1	2673.3
40°	12876.0	12805.2	12415.5	11448.7	9859.9	8856.7	7840.9	5979.2	4378.8	3101.5	2146.1
42.5°	12058.2	11941.5	11350.9	10068.3	8311.7	7378.3	6536.5	4924.7	3579.8	2518.2	1648.2
45°	10589.3	10398.5	9580.8	8240.9	6709.4	5977.0	5265.4	3947.6	2866.1	1875.3	1118.9
47.5°	8502.5	8294.1	7552.3	6476.1	5252.9	4659.1	4054.8	2906.8	1938.9	1092.9	561.5
50°	6182.3	6038.5	5383.2	4475.7	3473.5	2975.5	2511.8	1621.1	930.4	528.3	230.2
52.5°	3562.0	3458.9	3002.6	2355.6	1708.6	1430.5	1150.2	707.4	474.0	209.4	74.0
55°	1452.3	1392.9	1192.9	1010.6	758.4	655.3	547.0	353.1	159.4	50.0	29.1
57.5°	710.5	703.2	586.5	469.9	345.8	279.2	210.4	70.8	38.5	25.0	18.8
60°	282.3	271.9	186.4	108.3	60.4	49.0	41.7	29.1	21.9	16.7	13.5
62.5°	49.0	47.9	40.6	34.4	28.1	25.0	22.9	17.7	14.6	11.5	10.4
65°	22.9	22.9	20.8	18.8	15.6	14.6	13.5	11.5	9.4	8.3	8.3
67.5°	11.5	11.5	10.4	9.4	8.3	8.3	7.3	7.3	6.2	6.2	6.2
70°	6.2	6.2	6.2	5.2	5.2	5.2	5.2	5.2	4.1	5.2	5.2
72.5°	4.1	4.1	4.1	3.2	2.1	3.2	3.2	3.2	4.1	5.2	5.2
75°	1.1	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.1	5.2	5.2
77.5°	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.2	4.1	5.2	5.2
80°	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.2	4.1	5.2	5.2
82.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.1	5.2	5.2
85°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.1	5.2	5.2
87.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.1	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192550

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	978.3	978.3	978.3	978.3	978.3	978.3	978.3	978.3	978.3	978.3	978.3
2.5°	1353.3	1299.1	1263.8	1201.3	1175.2	1163.7	1106.5	1051.3	998.1	959.5	900.2
5°	1736.7	1650.3	1518.0	1393.9	1339.8	1305.5	1192.9	1088.7	989.7	903.3	800.1
7.5°	2149.3	1971.2	1763.9	1564.9	1471.1	1408.5	1234.5	1082.5	940.7	809.5	668.9
10°	2545.2	2265.0	1962.9	1678.5	1551.2	1457.5	1230.4	1035.5	851.2	681.3	530.3
12.5°	2882.8	2520.2	2119.1	1750.2	1584.6	1464.8	1191.9	954.4	730.3	548.0	416.8
15°	3167.2	2716.1	2222.2	1774.2	1575.2	1433.5	1116.8	842.9	598.1	434.4	336.6
17.5°	3367.3	2810.9	2246.2	1733.7	1509.6	1346.0	1003.2	700.1	469.9	351.1	265.6
20°	3483.9	2823.4	2187.8	1634.6	1395.0	1222.1	860.6	550.1	381.3	287.6	206.3
22.5°	3501.6	2761.9	2073.3	1501.3	1262.7	1096.0	716.8	460.5	346.9	268.8	202.2
25°	3416.1	2640.0	1924.2	1371.0	1142.9	972.1	619.9	465.7	389.7	345.8	359.5
27.5°	3250.5	2439.0	1753.4	1237.7	1017.9	845.0	585.5	487.5	425.0	432.3	457.3
30°	2996.3	2155.5	1507.5	1011.7	779.3	643.9	465.7	351.1	291.7	276.1	277.1
32.5°	2622.4	1800.3	1183.5	702.1	524.0	434.4	294.9	195.8	196.9	182.3	181.3
35°	2195.1	1449.2	885.5	470.9	362.5	302.1	174.0	137.6	132.3	127.1	119.8
37.5°	1772.2	1120.0	589.7	321.9	231.3	167.7	87.5	71.9	66.7	62.5	62.5
40°	1349.2	783.4	364.6	168.8	93.7	68.7	52.0	43.7	42.8	42.8	41.7
42.5°	979.4	462.6	197.9	66.7	52.0	45.8	36.4	32.3	32.3	32.3	32.3
45°	520.9	235.4	76.0	41.7	34.4	32.3	27.1	25.0	25.0	26.1	26.1
47.5°	240.7	88.6	38.5	28.1	24.0	24.0	20.8	19.7	19.7	20.8	20.8
50°	86.5	36.4	25.0	19.7	17.7	18.8	16.7	15.6	16.7	16.7	16.7
52.5°	33.4	22.9	17.7	15.6	13.5	14.6	12.6	12.6	13.5	13.5	13.5
55°	20.8	16.7	13.5	11.5	10.4	11.5	10.4	10.4	10.4	10.4	10.4
57.5°	14.6	12.6	10.4	9.4	8.3	9.4	9.4	9.4	9.4	9.4	9.4
60°	11.5	9.4	8.3	8.3	8.3	8.3	8.3	8.3	8.3	9.4	9.4
62.5°	9.4	8.3	8.3	8.3	8.3	8.3	8.3	8.3	9.4	9.4	9.4
65°	8.3	7.3	8.3	8.3	7.3	8.3	8.3	8.3	9.4	9.4	10.4
67.5°	6.2	6.2	6.2	7.3	7.3	7.3	8.3	8.3	9.4	9.4	9.4
70°	6.2	6.2	7.3	7.3	7.3	7.3	8.3	8.3	9.4	9.4	9.4
72.5°	6.2	6.2	7.3	7.3	7.3	8.3	8.3	8.3	9.4	9.4	9.4
75°	6.2	6.2	7.3	7.3	7.3	8.3	8.3	8.3	9.4	9.4	9.4
77.5°	6.2	6.2	7.3	7.3	7.3	8.3	8.3	9.4	9.4	9.4	9.4
80°	6.2	7.3	7.3	8.3	8.3	8.3	8.3	9.4	9.4	10.4	10.4
82.5°	6.2	7.3	7.3	8.3	8.3	8.3	8.3	9.4	9.4	10.4	10.4
85°	6.2	7.3	7.3	8.3	8.3	8.3	8.3	9.4	9.4	9.4	9.4
87.5°	6.2	7.3	7.3	8.3	8.3	8.3	8.3	8.3	9.4	9.4	9.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192550

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	978.3	978.3	978.3	978.3	978.3	978.3	978.3	978.3	978.3	978.3	978.3
2.5°	860.6	809.5	758.4	733.5	711.5	680.3	640.7	608.4	574.1	556.4	515.7
5°	718.8	631.3	557.4	521.9	494.9	457.3	416.8	387.5	361.5	346.9	320.8
7.5°	556.4	473.0	408.3	381.3	361.5	324.0	293.8	263.6	236.5	216.7	190.7
10°	430.3	365.7	312.6	286.5	264.7	225.1	188.5	160.5	131.2	111.5	103.1
12.5°	341.7	281.2	227.1	201.1	178.2	137.6	110.4	105.3	100.0	98.0	94.8
15°	262.6	207.3	150.0	123.9	114.5	109.4	103.1	102.1	98.0	98.0	94.8
17.5°	196.9	135.4	114.5	112.5	111.5	109.4	106.3	105.3	104.2	104.2	103.1
20°	141.7	131.2	128.2	130.3	131.2	133.3	132.3	132.3	136.5	145.9	143.8
22.5°	199.0	215.7	233.4	239.6	262.6	285.5	306.3	332.3	393.8	464.6	481.3
25°	393.8	443.8	489.6	514.7	552.1	603.2	652.2	712.6	755.4	790.7	831.4
27.5°	489.6	508.4	501.1	504.2	500.1	492.8	494.9	507.4	501.1	482.3	489.6
30°	289.7	304.3	295.9	300.0	288.6	288.6	285.5	291.7	287.6	280.3	278.2
32.5°	188.5	196.9	195.8	195.8	191.7	189.6	182.3	180.2	172.9	159.4	156.2
35°	113.6	108.3	103.1	100.0	98.0	98.0	96.9	96.9	93.7	90.7	89.6
37.5°	61.4	62.5	62.5	62.5	62.5	64.6	63.6	63.6	63.6	61.4	61.4
40°	42.8	44.8	44.8	44.8	45.8	45.8	45.8	46.9	45.8	45.8	45.8
42.5°	33.4	34.4	33.4	33.4	34.4	34.4	34.4	35.5	35.5	35.5	34.4
45°	27.1	27.1	26.1	27.1	27.1	28.1	28.1	28.1	28.1	27.1	27.1
47.5°	21.9	21.9	21.9	21.9	22.9	22.9	22.9	22.9	22.9	22.9	22.9
50°	17.7	17.7	17.7	18.8	18.8	18.8	17.7	18.8	18.8	18.8	17.7
52.5°	13.5	13.5	13.5	13.5	13.5	12.6	12.6	12.6	12.6	12.6	11.5
55°	10.4	10.4	10.4	10.4	10.4	11.5	10.4	11.5	10.4	10.4	9.4
57.5°	9.4	9.4	9.4	9.4	10.4	10.4	9.4	9.4	9.4	8.3	8.3
60°	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	8.3	7.3	7.3
62.5°	10.4	10.4	9.4	9.4	9.4	9.4	8.3	8.3	8.3	7.3	7.3
65°	10.4	10.4	9.4	10.4	10.4	9.4	9.4	8.3	8.3	7.3	7.3
67.5°	10.4	10.4	10.4	10.4	10.4	10.4	9.4	9.4	8.3	8.3	7.3
70°	10.4	10.4	10.4	10.4	10.4	10.4	9.4	9.4	8.3	8.3	7.3
72.5°	10.4	10.4	10.4	10.4	10.4	10.4	9.4	9.4	9.4	8.3	7.3
75°	10.4	10.4	10.4	10.4	10.4	9.4	9.4	9.4	8.3	8.3	7.3
77.5°	10.4	10.4	10.4	10.4	10.4	9.4	9.4	9.4	8.3	8.3	7.3
80°	10.4	10.4	10.4	10.4	10.4	10.4	9.4	9.4	8.3	8.3	7.3
82.5°	10.4	10.4	10.4	10.4	10.4	9.4	9.4	9.4	8.3	8.3	7.3
85°	10.4	9.4	9.4	9.4	9.4	9.4	8.3	8.3	7.3	7.3	6.2
87.5°	9.4	9.4	9.4	9.4	9.4	8.3	8.3	7.3	6.2	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192550

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	978.3	978.3	978.3	978.3	978.3	978.3	978.3	978.3
2.5°	515.7	506.3	502.2	494.9	488.6	485.5	474.0	487.5
5°	315.7	304.3	301.1	294.9	287.6	283.4	275.0	282.3
7.5°	180.2	166.7	160.5	155.2	147.9	141.7	134.4	138.6
10°	101.0	96.9	98.0	94.8	93.7	92.7	91.6	93.7
12.5°	93.7	90.7	91.6	89.6	88.6	88.6	87.5	88.6
15°	94.8	91.6	93.7	91.6	90.7	90.7	89.6	91.6
17.5°	103.1	101.0	103.1	101.0	102.1	101.0	102.1	103.1
20°	144.8	147.9	154.1	150.0	153.2	157.3	162.6	162.6
22.5°	509.5	576.1	584.4	617.8	703.2	700.1	757.5	759.5
25°	889.7	893.9	931.4	918.9	919.9	963.6	959.5	984.5
27.5°	511.6	510.5	517.8	504.2	508.4	511.6	500.1	513.6
30°	285.5	280.3	283.4	276.1	276.1	278.2	275.0	281.2
32.5°	158.4	154.1	154.1	149.0	147.9	147.0	143.8	147.0
35°	90.7	87.5	88.6	86.5	84.4	83.4	82.3	83.4
37.5°	62.5	60.4	61.4	59.3	57.3	56.3	55.2	56.3
40°	45.8	44.8	44.8	42.8	41.7	40.6	39.6	39.6
42.5°	34.4	33.4	33.4	31.2	30.2	29.1	28.1	29.1
45°	26.1	25.0	25.0	24.0	22.9	21.9	21.9	21.9
47.5°	22.9	21.9	22.9	21.9	20.8	20.8	20.8	20.8
50°	17.7	17.7	17.7	16.7	15.6	15.6	14.6	13.5
52.5°	11.5	10.4	10.4	9.4	9.4	8.3	8.3	8.3
55°	9.4	8.3	8.3	7.3	7.3	6.2	6.2	6.2
57.5°	7.3	7.3	6.2	6.2	5.2	5.2	5.2	5.2
60°	6.2	6.2	6.2	5.2	5.2	4.1	4.1	4.1
62.5°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
65°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
67.5°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
70°	7.3	6.2	6.2	5.2	5.2	5.2	4.1	4.1
72.5°	7.3	6.2	6.2	6.2	5.2	5.2	5.2	5.2
75°	7.3	6.2	6.2	6.2	5.2	5.2	5.2	5.2
77.5°	7.3	6.2	6.2	6.2	5.2	5.2	5.2	5.2
80°	7.3	6.2	6.2	6.2	5.2	5.2	5.2	5.2
82.5°	6.2	6.2	6.2	5.2	5.2	5.2	5.2	5.2
85°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
87.5°	4.1	4.1	3.2	3.2	3.2	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)