

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192565

Luminaire Tested: **LDA6A60940D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192565
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60940D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5859.9 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192565

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192565

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	57945	57945	57945
5°	148640	52713	16415
10°	289746	40508	7888
15°	520128	27520	10579
20°	772231	20885	17467
25°	877762	17209	27389
30°	951501	18819	25763
35°	1002247	12193	15975
40°	1023918	5417	7779
45°	924801	2070	2892
50°	608765	819	819
55°	166713	707	0
60°	33298	811	0
65°	2361	1103	0
70°	337	1362	0
75°	0	2033	0
80°	0	3031	347
85°	0	6038	692



TEST NUMBER: P1192565

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.5	2.2
10°-20°	687.9	11.7
20°-30°	1559.1	26.6
30°-40°	1871.4	31.9
40°-50°	1318.9	22.5
50°-60°	272.1	4.6
60°-70°	9.6	0.2
70°-80°	5.7	0.1
80°-90°	5.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2376.4	40.6
0°-40°	4247.9	72.5
0°-60°	5839.0	99.6
0°-90°	5859.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5859.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1057	1057	1057	1057	1057	
5°	2701	1968	958	398	298	332
15°	9165	4032	485	173	186	2720
25°	14512	4877	284	398	453	6697
35°	14976	3415	182	239	239	9310
45°	11929	1171	27	36	37	8773
55°	1744	23	7	5	0	2299
65°	18	5	8	5	0	54
75°	0	5	10	6	0	0
85°	0	6	10	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192565

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0
2.5°	1801.8	1747.4	1768.8	1705.9	1692.1	1680.3	1692.1	1623.9	1585.5	1536.5	1497.1
5°	2701.1	2636.1	2651.0	2541.3	2491.2	2457.1	2450.7	2310.0	2204.6	2088.4	1968.0
7.5°	3760.3	3698.5	3690.0	3519.5	3416.1	3357.5	3333.0	3131.6	2949.4	2742.6	2516.8
10°	5205.1	5064.5	5020.8	4773.6	4576.5	4451.8	4298.4	3976.6	3656.9	3344.7	3057.0
12.5°	6886.5	6809.9	6701.2	6265.3	5920.1	5743.2	5514.2	5011.2	4527.5	4011.8	3530.1
15°	9164.6	8891.9	8706.4	8076.7	7520.5	7247.8	6913.2	6143.9	5412.9	4759.7	4032.0
17.5°	11390.6	11247.8	10958.0	10140.7	9284.0	8853.5	8354.9	7309.6	6277.1	5347.9	4459.2
20°	13237.1	13102.9	12772.6	12002.2	11051.7	10416.7	9789.0	8354.9	7005.9	5816.7	4744.9
22.5°	14121.5	14036.2	13766.7	13107.2	12297.3	11693.2	11018.7	9244.6	7545.0	6123.7	4874.8
25°	14511.5	14472.1	14298.3	13778.4	13015.5	12503.0	11865.8	9874.3	7880.7	6266.4	4877.0
27.5°	14906.8	14914.3	14530.7	14119.3	13395.9	12903.6	12289.9	10153.5	7941.4	6186.4	4717.1
30°	15031.4	14952.6	14783.2	14192.9	13505.7	12982.4	12324.0	10024.6	7692.1	5858.3	4398.6
32.5°	14980.4	14949.4	14763.0	14138.6	13319.2	12742.7	11994.8	9513.1	7199.8	5389.5	3946.7
35°	14976.1	14918.6	14491.2	13955.3	12946.2	12234.4	11248.9	8686.2	6502.9	4771.4	3415.0
37.5°	14705.5	14562.6	14241.9	13519.5	12189.7	11287.3	10182.3	7676.1	5650.5	4077.8	2887.6
40°	14308.0	14116.2	13694.3	12601.0	10879.2	9839.1	8760.8	6528.5	4748.0	3393.7	2327.1
42.5°	13477.9	13188.1	12591.4	11087.9	9132.7	8195.0	7297.9	5366.0	3872.1	2765.1	1776.2
45°	11928.7	11532.3	10725.6	9075.2	7377.7	6612.7	5891.3	4317.5	3099.7	2051.1	1171.0
47.5°	9587.7	9220.1	8485.9	7224.3	5785.9	5139.1	4563.7	3211.5	2101.2	1188.1	559.4
50°	7138.0	6822.7	6249.3	5020.8	3883.8	3375.6	2883.4	1824.2	984.6	564.7	232.3
52.5°	4258.9	4102.3	3594.1	2784.2	1917.9	1652.6	1326.5	772.5	496.6	204.6	62.9
55°	1744.3	1610.0	1419.3	1139.0	834.4	707.5	605.3	381.4	154.5	42.6	23.4
57.5°	788.5	758.7	672.4	528.5	383.6	321.8	217.4	72.5	34.1	21.3	13.9
60°	303.7	273.8	234.5	126.9	54.3	45.8	37.3	24.5	17.1	11.7	8.5
62.5°	43.7	41.6	37.3	29.9	23.4	21.3	18.2	12.8	9.6	7.4	6.3
65°	18.2	18.2	16.0	12.8	10.6	9.6	8.5	6.3	5.4	5.4	5.4
67.5°	7.4	7.4	6.3	5.4	4.3	4.3	4.3	3.2	4.3	4.3	5.4
70°	2.1	2.1	2.1	2.1	2.1	2.1	3.2	3.2	4.3	4.3	5.4
72.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.3	5.4	5.4
75°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.3	5.4	5.4
77.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.3	5.4	5.4
80°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.3	5.4	6.3
82.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.3	5.4	6.3
85°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.3	5.4	6.3
87.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.3	5.4	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192565

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0
2.5°	1463.0	1394.8	1375.6	1315.9	1265.9	1241.4	1210.4	1141.2	1088.9	1019.7	978.1
5°	1883.9	1755.0	1652.6	1528.0	1446.0	1392.7	1309.6	1182.7	1080.5	957.9	870.5
7.5°	2338.8	2103.4	1919.0	1713.4	1595.1	1502.4	1360.7	1178.5	1028.2	865.2	729.9
10°	2777.9	2426.2	2136.4	1841.3	1685.6	1556.7	1361.8	1132.7	933.4	727.7	585.0
12.5°	3164.6	2710.7	2302.6	1923.3	1730.4	1569.5	1325.6	1050.7	809.9	598.8	473.0
15°	3487.5	2931.3	2419.8	1954.2	1733.7	1541.9	1249.9	933.4	672.4	484.9	396.4
17.5°	3732.6	3047.4	2456.0	1916.9	1671.9	1463.0	1133.8	785.2	545.6	411.3	333.5
20°	3859.3	3069.8	2403.9	1815.7	1557.8	1343.6	981.3	637.2	462.4	358.0	279.2
22.5°	3875.3	3006.9	2279.2	1670.8	1413.9	1198.7	813.0	531.7	412.4	316.5	246.2
25°	3780.5	2870.6	2101.2	1506.6	1256.2	1032.5	661.7	476.3	375.1	284.5	283.4
27.5°	3578.1	2636.1	1888.2	1315.9	1065.5	839.6	561.5	430.5	334.6	301.6	320.7
30°	3292.5	2335.6	1626.1	1075.1	832.2	645.7	473.0	354.8	294.0	297.3	313.3
32.5°	2905.7	1962.8	1318.0	787.4	595.6	485.8	354.8	241.9	244.0	245.1	258.9
35°	2419.8	1573.8	984.6	529.6	418.7	342.1	200.3	177.9	181.2	182.2	191.8
37.5°	1939.2	1209.4	654.3	352.7	263.2	180.1	124.7	119.3	121.5	120.4	131.1
40°	1485.3	842.9	392.1	174.7	101.3	84.2	76.8	73.5	74.6	75.7	82.0
42.5°	1051.6	457.1	193.9	66.0	53.3	49.0	45.8	43.7	44.7	44.7	49.0
45°	533.9	216.3	66.0	36.2	33.0	29.9	27.7	26.7	26.7	26.7	28.8
47.5°	231.2	71.4	31.0	22.4	20.2	19.1	17.1	16.0	16.0	16.0	17.1
50°	72.5	28.8	19.1	14.9	12.8	11.7	10.6	10.6	10.6	9.6	10.6
52.5°	26.7	18.2	12.8	9.6	8.5	8.5	8.5	7.4	8.5	7.4	8.5
55°	16.0	11.7	8.5	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
57.5°	10.6	8.5	7.4	7.4	6.3	6.3	7.4	7.4	7.4	7.4	7.4
60°	7.4	7.4	6.3	6.3	6.3	6.3	7.4	7.4	7.4	7.4	7.4
62.5°	6.3	6.3	6.3	6.3	6.3	6.3	7.4	7.4	7.4	7.4	8.5
65°	5.4	6.3	6.3	6.3	6.3	6.3	7.4	7.4	8.5	8.5	8.5
67.5°	5.4	6.3	6.3	7.4	7.4	7.4	7.4	8.5	8.5	8.5	8.5
70°	6.3	6.3	7.4	7.4	7.4	7.4	8.5	8.5	8.5	8.5	9.6
72.5°	6.3	6.3	7.4	7.4	7.4	7.4	8.5	8.5	9.6	9.6	9.6
75°	6.3	7.4	7.4	7.4	7.4	8.5	8.5	8.5	9.6	9.6	9.6
77.5°	6.3	7.4	7.4	8.5	8.5	8.5	8.5	9.6	9.6	9.6	9.6
80°	6.3	7.4	7.4	8.5	8.5	8.5	9.6	9.6	9.6	9.6	10.6
82.5°	6.3	7.4	7.4	8.5	8.5	8.5	9.6	9.6	9.6	9.6	10.6
85°	7.4	7.4	8.5	8.5	8.5	8.5	9.6	9.6	9.6	9.6	10.6
87.5°	7.4	7.4	8.5	8.5	8.5	8.5	9.6	9.6	10.6	9.6	10.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192565

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0
2.5°	922.7	860.9	818.3	802.3	771.5	722.5	693.6	667.0	617.0	606.2	578.6
5°	770.4	671.3	601.0	574.3	539.2	497.7	457.1	430.5	398.5	385.7	366.5
7.5°	607.3	508.3	447.6	426.3	401.8	367.6	331.3	304.8	271.7	254.7	238.7
10°	477.3	403.8	352.7	331.3	305.9	269.5	232.3	197.2	168.4	150.2	147.1
12.5°	387.9	327.1	272.7	250.4	220.6	184.4	157.7	156.6	154.5	153.4	155.6
15°	317.6	258.9	201.4	176.9	168.4	167.3	170.5	173.6	172.7	175.8	177.9
17.5°	261.0	198.1	185.3	186.4	187.5	190.7	196.1	204.6	205.7	210.9	215.2
20°	213.1	210.0	215.2	219.5	222.8	229.1	240.8	251.5	254.7	262.1	270.6
22.5°	241.9	251.5	263.2	268.6	272.7	284.5	297.3	314.4	320.7	330.4	342.1
25°	292.0	307.9	326.1	332.4	338.9	358.0	372.9	393.2	398.5	410.2	422.0
27.5°	333.5	350.6	369.7	378.2	383.6	402.7	415.5	428.3	428.3	434.8	443.3
30°	327.1	341.0	356.9	363.4	365.4	379.3	392.1	396.4	394.2	397.5	403.8
32.5°	271.7	282.3	295.1	300.5	302.6	312.2	322.8	322.8	321.8	321.8	326.1
35°	201.4	208.9	215.2	220.6	223.7	230.2	239.7	238.7	238.7	236.5	239.7
37.5°	135.4	139.5	147.1	149.2	150.2	154.5	161.9	161.9	159.9	160.9	163.0
40°	82.0	87.4	91.6	92.7	94.8	98.0	103.3	103.3	103.3	103.3	104.4
42.5°	49.0	52.2	55.4	55.4	56.4	60.7	62.9	62.9	62.9	62.9	64.0
45°	28.8	29.9	31.9	33.0	33.0	35.2	36.2	36.2	36.2	36.2	37.3
47.5°	17.1	18.2	18.2	19.1	19.1	20.2	21.3	21.3	20.2	20.2	20.2
50°	10.6	10.6	10.6	10.6	11.7	11.7	11.7	11.7	11.7	11.7	10.6
52.5°	8.5	8.5	8.5	8.5	7.4	7.4	7.4	7.4	6.3	6.3	5.4
55°	7.4	7.4	7.4	7.4	7.4	6.3	6.3	6.3	5.4	4.3	3.2
57.5°	7.4	7.4	7.4	7.4	7.4	6.3	6.3	5.4	4.3	4.3	3.2
60°	7.4	7.4	7.4	7.4	7.4	6.3	6.3	5.4	4.3	4.3	3.2
62.5°	8.5	8.5	7.4	7.4	7.4	6.3	6.3	5.4	5.4	4.3	3.2
65°	8.5	8.5	7.4	7.4	7.4	7.4	6.3	6.3	5.4	4.3	3.2
67.5°	8.5	8.5	8.5	8.5	7.4	7.4	7.4	6.3	5.4	4.3	3.2
70°	9.6	9.6	8.5	8.5	8.5	7.4	7.4	6.3	5.4	5.4	4.3
72.5°	9.6	9.6	8.5	8.5	8.5	8.5	7.4	6.3	6.3	5.4	4.3
75°	9.6	9.6	9.6	9.6	8.5	8.5	7.4	7.4	6.3	5.4	4.3
77.5°	9.6	9.6	9.6	9.6	8.5	8.5	8.5	7.4	6.3	5.4	4.3
80°	9.6	9.6	9.6	9.6	9.6	8.5	8.5	7.4	6.3	5.4	4.3
82.5°	10.6	10.6	9.6	9.6	9.6	8.5	8.5	7.4	6.3	5.4	5.4
85°	10.6	10.6	9.6	9.6	9.6	8.5	8.5	7.4	6.3	6.3	5.4
87.5°	10.6	10.6	9.6	9.6	9.6	8.5	8.5	7.4	6.3	6.3	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192565

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0	1057.0
2.5°	561.5	529.6	518.9	526.4	517.9	511.4	502.9	498.6
5°	351.7	328.2	320.7	322.8	315.4	309.0	300.5	298.3
7.5°	216.3	193.9	185.3	185.3	176.9	169.4	164.1	160.9
10°	144.9	140.6	141.7	142.8	141.7	142.8	139.5	141.7
12.5°	155.6	153.4	155.6	156.6	156.6	158.8	154.5	157.7
15°	181.2	179.0	182.2	184.4	184.4	187.5	183.3	186.4
17.5°	221.7	220.6	225.9	228.0	229.1	234.5	229.1	233.4
20°	280.3	279.2	286.6	289.8	288.8	299.4	292.0	299.4
22.5°	355.9	353.8	364.4	367.6	368.6	382.5	376.2	381.4
25°	431.5	433.7	439.1	444.3	445.4	457.1	447.6	452.8
27.5°	447.6	444.3	447.6	453.9	455.0	460.3	451.8	456.0
30°	404.9	399.6	400.7	408.1	410.2	412.4	404.9	407.0
32.5°	329.3	320.7	320.7	328.2	330.4	333.5	320.7	326.1
35°	243.0	235.4	235.4	240.8	241.9	244.0	234.5	238.7
37.5°	166.2	159.9	161.9	164.1	165.1	167.3	166.2	165.1
40°	106.5	102.2	105.5	105.5	106.5	107.6	107.6	108.7
42.5°	64.9	61.8	64.0	64.0	64.9	64.9	64.9	66.0
45°	37.3	36.2	36.2	37.3	37.3	37.3	36.2	37.3
47.5°	20.2	19.1	20.2	20.2	20.2	20.2	20.2	20.2
50°	10.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6
52.5°	5.4	4.3	4.3	4.3	3.2	4.3	3.2	3.2
55°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
57.5°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
60°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.2	2.1	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.2	2.1	2.1	1.1	1.1	0.0	0.0	0.0
72.5°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
75°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
77.5°	3.2	3.2	2.1	2.1	1.1	1.1	1.1	0.0
80°	4.3	3.2	2.1	2.1	2.1	1.1	1.1	1.1
82.5°	4.3	3.2	2.1	2.1	2.1	1.1	1.1	1.1
85°	4.3	3.2	3.2	2.1	2.1	1.1	1.1	1.1
87.5°	4.3	3.2	3.2	2.1	2.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)