

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192567

Luminaire Tested: **LDA6A60940D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192567
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26690)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60940D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5443.3 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 2.55 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192567

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192567

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	75	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65		
5	85	74	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	54842	54842	54842
5°	141597	50836	15893
10°	268616	38788	5338
15°	480315	25216	5318
20°	715696	17151	9696
25°	816622	21400	60905
30°	883136	17870	18212
35°	927688	8700	5702
40°	942351	3120	2898
45°	839591	2070	1737
50°	539223	1458	1185
55°	141959	1013	602
60°	31664	1053	471
65°	3035	1245	558
70°	1010	1539	689
75°	233	2033	1144
80°	0	3346	1705
85°	0	6038	2705



TEST NUMBER: P1192567

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.5	2.2
10°-20°	634.1	11.6
20°-30°	1487.8	27.3
30°-40°	1711.3	31.4
40°-50°	1215.6	22.3
50°-60°	247.2	4.5
60°-70°	12.4	0.2
70°-80°	7.3	0.1
80°-90°	6.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2243.4	41.2
0°-40°	3954.7	72.7
0°-60°	5417.5	99.5
0°-90°	5443.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5443.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1000	1000	1000	1000	1000	
5°	2573	1861	924	370	289	314
15°	8463	3805	444	100	94	2539
25°	13501	4583	354	772	1007	6222
35°	13862	3218	130	96	85	8611
45°	10830	1144	27	29	22	7981
55°	1485	30	11	11	6	2003
65°	23	8	10	8	4	56
75°	1	5	10	8	5	3
85°	0	5	10	7	4	0
90°	0	0	0	0	0	

TEST NUMBER: P1192567

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4
2.5°	1723.9	1671.8	1646.2	1645.1	1570.5	1595.0	1570.5	1551.4	1482.0	1453.3	1405.4
5°	2573.1	2509.2	2458.1	2435.7	2307.9	2280.2	2267.4	2202.3	2057.4	1973.2	1861.4
7.5°	3574.7	3507.5	3423.3	3356.3	3170.8	3118.7	3084.6	2972.7	2758.5	2589.1	2380.2
10°	4825.5	4786.2	4649.7	4526.1	4244.9	4136.2	4034.0	3772.8	3492.7	3152.8	2883.1
12.5°	6510.1	6417.4	6174.5	5927.2	5486.1	5324.2	5154.8	4737.1	4308.9	3776.1	3330.7
15°	8463.1	8384.3	8010.3	7607.5	6980.0	6713.6	6448.3	5790.9	5132.4	4446.2	3804.9
17.5°	10711.2	10562.1	10190.3	9509.4	8631.5	8212.7	7718.3	6880.9	5930.4	4998.2	4201.1
20°	12268.0	12179.5	11865.2	11212.1	10212.6	9659.6	9045.9	7896.3	6596.4	5440.3	4461.2
22.5°	13119.2	13030.8	12795.4	12219.0	11399.6	10844.4	10131.7	8717.8	7099.3	5737.6	4583.7
25°	13500.7	13443.1	13314.2	12844.3	12085.8	11586.0	10911.6	9285.6	7413.7	5872.9	4582.7
27.5°	13853.4	13868.3	13549.8	13163.0	12464.0	11962.1	11322.8	9541.4	7475.4	5804.8	4435.6
30°	13951.4	13914.1	13774.6	13230.0	12579.1	12032.5	11347.3	9406.0	7234.7	5503.2	4143.6
32.5°	13890.7	13891.7	13760.7	13182.1	12417.1	11805.5	11035.1	8921.3	6765.7	5030.1	3689.7
35°	13862.0	13852.3	13512.5	13004.2	12032.5	11313.3	10342.6	8143.5	6115.9	4426.0	3217.8
37.5°	13576.3	13518.8	13273.8	12584.4	11313.3	10393.8	9348.5	7192.0	5315.6	3797.4	2734.0
40°	13168.2	13095.9	12697.4	11708.5	10083.7	9057.6	8018.8	6114.8	4478.2	3171.9	2194.9
42.5°	12331.9	12212.5	11608.5	10296.8	8500.4	7545.8	6684.8	5036.5	3661.0	2575.3	1685.6
45°	10829.6	10634.6	9798.2	8428.0	6861.6	6112.7	5385.0	4037.1	2931.1	1917.9	1144.4
47.5°	8695.4	8482.3	7723.7	6623.1	5372.2	4764.9	4146.8	2972.7	1982.9	1117.7	574.3
50°	6322.6	6175.5	5505.4	4577.3	3552.3	3043.0	2568.9	1657.9	951.5	540.2	235.4
52.5°	3642.9	3537.4	3070.7	2409.0	1747.4	1462.9	1176.3	723.5	484.7	214.1	75.7
55°	1485.3	1424.5	1220.0	1033.5	775.6	670.2	559.3	361.2	163.0	51.2	29.9
57.5°	726.6	719.2	599.9	480.5	353.8	285.5	215.2	72.5	39.5	25.6	19.1
60°	288.8	278.1	190.7	110.8	61.8	50.1	42.6	29.9	22.4	17.1	13.9
62.5°	50.1	49.0	41.6	35.2	28.8	25.6	23.4	18.2	14.9	11.7	10.6
65°	23.4	23.4	21.3	19.1	16.0	14.9	13.9	11.7	9.6	8.5	8.5
67.5°	11.7	11.7	10.6	9.6	8.5	8.5	7.4	7.4	6.3	6.3	6.3
70°	6.3	6.3	6.3	5.4	5.4	5.4	5.4	5.4	4.3	5.4	5.4
72.5°	4.3	4.3	4.3	3.2	2.1	3.2	3.2	3.2	4.3	5.4	5.4
75°	1.1	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.3	5.4	5.4
77.5°	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.2	4.3	5.4	5.4
80°	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.2	4.3	5.4	5.4
82.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.3	5.4	5.4
85°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.3	5.4	5.4
87.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.3	5.4	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192567

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4
2.5°	1384.1	1328.6	1292.4	1228.4	1201.9	1190.2	1131.6	1075.0	1020.7	981.3	920.6
5°	1776.2	1687.7	1552.5	1425.6	1370.2	1335.1	1220.0	1113.4	1012.3	923.8	818.3
7.5°	2198.1	2015.9	1803.8	1600.3	1504.4	1440.5	1262.6	1107.1	962.2	827.9	684.0
10°	2603.0	2316.4	2007.4	1716.5	1586.5	1490.6	1258.3	1059.1	870.5	696.8	542.4
12.5°	2948.2	2577.4	2167.2	1790.0	1620.6	1498.1	1218.9	976.0	746.9	560.4	426.1
15°	3239.1	2777.7	2272.6	1814.6	1610.9	1466.1	1142.2	862.0	611.6	444.3	344.1
17.5°	3443.7	2874.6	2297.1	1773.0	1543.9	1376.6	1026.0	716.0	480.5	359.1	271.7
20°	3563.0	2887.4	2237.5	1671.8	1426.7	1249.8	880.1	562.6	389.9	294.0	210.9
22.5°	3581.1	2824.6	2120.3	1535.4	1291.3	1120.8	733.1	471.0	354.8	274.9	206.7
25°	3493.8	2700.0	1968.0	1402.2	1168.9	994.1	633.9	476.2	398.5	353.8	367.6
27.5°	3324.3	2494.3	1793.2	1265.9	1041.0	864.1	598.8	498.6	434.7	442.2	467.7
30°	3064.3	2204.5	1541.7	1034.6	796.9	658.5	476.2	359.1	298.3	282.3	283.4
32.5°	2681.8	1841.1	1210.4	718.1	535.9	444.3	301.5	200.3	201.4	186.4	185.3
35°	2245.0	1482.0	905.6	481.6	370.8	309.0	177.9	140.6	135.3	130.0	122.6
37.5°	1812.4	1145.3	603.1	329.3	236.5	171.6	89.4	73.5	68.2	64.0	64.0
40°	1379.8	801.2	372.9	172.5	95.9	70.3	53.3	44.7	43.6	43.6	42.6
42.5°	1001.5	473.0	202.4	68.2	53.3	46.9	37.3	33.0	33.0	33.0	33.0
45°	532.8	240.8	77.7	42.6	35.2	33.0	27.7	25.6	25.6	26.7	26.7
47.5°	246.2	90.5	39.5	28.8	24.5	24.5	21.3	20.2	20.2	21.3	21.3
50°	88.5	37.3	25.6	20.2	18.2	19.1	17.1	16.0	17.1	17.1	17.1
52.5°	34.1	23.4	18.2	16.0	13.9	14.9	12.8	12.8	13.9	13.9	13.9
55°	21.3	17.1	13.9	11.7	10.6	11.7	10.6	10.6	10.6	10.6	10.6
57.5°	14.9	12.8	10.6	9.6	8.5	9.6	9.6	9.6	9.6	9.6	9.6
60°	11.7	9.6	8.5	8.5	8.5	8.5	8.5	8.5	8.5	9.6	9.6
62.5°	9.6	8.5	8.5	8.5	8.5	8.5	8.5	8.5	9.6	9.6	9.6
65°	8.5	7.4	8.5	8.5	7.4	8.5	8.5	8.5	9.6	9.6	10.6
67.5°	6.3	6.3	6.3	7.4	7.4	7.4	8.5	8.5	9.6	9.6	9.6
70°	6.3	6.3	7.4	7.4	7.4	7.4	8.5	8.5	9.6	9.6	9.6
72.5°	6.3	6.3	7.4	7.4	7.4	8.5	8.5	8.5	9.6	9.6	9.6
75°	6.3	6.3	7.4	7.4	7.4	8.5	8.5	8.5	9.6	9.6	9.6
77.5°	6.3	6.3	7.4	7.4	7.4	8.5	8.5	9.6	9.6	9.6	9.6
80°	6.3	7.4	7.4	8.5	8.5	8.5	8.5	9.6	9.6	10.6	10.6
82.5°	6.3	7.4	7.4	8.5	8.5	8.5	8.5	9.6	9.6	10.6	10.6
85°	6.3	7.4	7.4	8.5	8.5	8.5	8.5	9.6	9.6	9.6	9.6
87.5°	6.3	7.4	7.4	8.5	8.5	8.5	8.5	8.5	9.6	9.6	9.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192567

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4
2.5°	880.1	827.9	775.6	750.2	727.7	695.8	655.2	622.2	587.1	569.0	527.4
5°	735.2	645.7	570.0	533.9	506.1	467.7	426.1	396.4	369.7	354.8	328.2
7.5°	569.0	483.8	417.7	389.9	369.7	331.3	300.5	269.5	241.9	221.7	195.0
10°	440.0	374.0	319.6	293.1	270.6	230.2	192.9	164.1	134.3	114.1	105.5
12.5°	349.5	287.7	232.3	205.7	182.2	140.6	113.0	107.6	102.2	100.2	97.0
15°	268.5	212.0	153.4	126.7	117.2	111.9	105.5	104.4	100.2	100.2	97.0
17.5°	201.4	138.6	117.2	115.0	114.1	111.9	108.7	107.6	106.5	106.5	105.5
20°	144.9	134.3	131.0	133.2	134.3	136.4	135.3	135.3	139.5	149.2	147.1
22.5°	203.5	220.6	238.7	245.1	268.5	292.0	313.3	339.9	402.7	475.2	492.3
25°	402.7	453.9	500.8	526.3	564.7	617.0	667.0	728.8	772.5	808.6	850.2
27.5°	500.8	520.0	512.5	515.7	511.4	504.0	506.1	518.9	512.5	493.3	500.8
30°	296.2	311.1	302.6	306.8	295.1	295.1	292.0	298.3	294.0	286.6	284.5
32.5°	192.9	201.4	200.3	200.3	196.1	193.9	186.4	184.4	176.8	163.0	159.9
35°	116.1	110.8	105.5	102.2	100.2	100.2	99.1	99.1	95.9	92.7	91.6
37.5°	62.9	64.0	64.0	64.0	64.0	66.0	64.9	64.9	64.9	62.9	62.9
40°	43.6	45.8	45.8	45.8	46.9	46.9	46.9	47.9	46.9	46.9	46.9
42.5°	34.1	35.2	34.1	34.1	35.2	35.2	35.2	36.2	36.2	36.2	35.2
45°	27.7	27.7	26.7	27.7	27.7	28.8	28.8	28.8	28.8	27.7	27.7
47.5°	22.4	22.4	22.4	22.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4
50°	18.2	18.2	18.2	19.1	19.1	19.1	18.2	19.1	19.1	19.1	18.2
52.5°	13.9	13.9	13.9	13.9	13.9	12.8	12.8	12.8	12.8	12.8	11.7
55°	10.6	10.6	10.6	10.6	10.6	11.7	10.6	11.7	10.6	10.6	9.6
57.5°	9.6	9.6	9.6	9.6	10.6	10.6	9.6	9.6	9.6	8.5	8.5
60°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	8.5	7.4	7.4
62.5°	10.6	10.6	9.6	9.6	9.6	9.6	8.5	8.5	8.5	7.4	7.4
65°	10.6	10.6	9.6	10.6	10.6	9.6	9.6	8.5	8.5	7.4	7.4
67.5°	10.6	10.6	10.6	10.6	10.6	10.6	9.6	9.6	8.5	8.5	7.4
70°	10.6	10.6	10.6	10.6	10.6	10.6	9.6	9.6	8.5	8.5	7.4
72.5°	10.6	10.6	10.6	10.6	10.6	10.6	9.6	9.6	9.6	8.5	7.4
75°	10.6	10.6	10.6	10.6	10.6	9.6	9.6	9.6	8.5	8.5	7.4
77.5°	10.6	10.6	10.6	10.6	10.6	9.6	9.6	9.6	8.5	8.5	7.4
80°	10.6	10.6	10.6	10.6	10.6	10.6	9.6	9.6	8.5	8.5	7.4
82.5°	10.6	10.6	10.6	10.6	10.6	9.6	9.6	9.6	8.5	8.5	7.4
85°	10.6	9.6	9.6	9.6	9.6	9.6	8.5	8.5	7.4	7.4	6.3
87.5°	9.6	9.6	9.6	9.6	9.6	8.5	8.5	7.4	6.3	5.4	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192567

CATALOG NUMBER: LDA6A60940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4	1000.4
2.5°	527.4	517.8	513.5	506.1	499.7	496.6	484.7	498.6
5°	322.8	311.1	307.9	301.5	294.0	289.8	281.2	288.8
7.5°	184.4	170.5	164.1	158.8	151.3	144.9	137.5	141.7
10°	103.3	99.1	100.2	97.0	95.9	94.8	93.7	95.9
12.5°	95.9	92.7	93.7	91.6	90.5	90.5	89.4	90.5
15°	97.0	93.7	95.9	93.7	92.7	92.7	91.6	93.7
17.5°	105.5	103.3	105.5	103.3	104.4	103.3	104.4	105.5
20°	148.1	151.3	157.7	153.4	156.6	160.9	166.2	166.2
22.5°	521.1	589.2	597.7	631.8	719.2	716.0	774.6	776.7
25°	909.9	914.2	952.6	939.8	940.9	985.6	981.3	1006.9
27.5°	523.1	522.0	529.6	515.7	520.0	523.1	511.4	525.3
30°	292.0	286.6	289.8	282.3	282.3	284.5	281.2	287.7
32.5°	161.9	157.7	157.7	152.3	151.3	150.2	147.1	150.2
35°	92.7	89.4	90.5	88.5	86.3	85.2	84.2	85.2
37.5°	64.0	61.8	62.9	60.7	58.6	57.5	56.4	57.5
40°	46.9	45.8	45.8	43.6	42.6	41.6	40.5	40.5
42.5°	35.2	34.1	34.1	31.9	31.0	29.9	28.8	29.9
45°	26.7	25.6	25.6	24.5	23.4	22.4	22.4	22.4
47.5°	23.4	22.4	23.4	22.4	21.3	21.3	21.3	21.3
50°	18.2	18.2	18.2	17.1	16.0	16.0	14.9	13.9
52.5°	11.7	10.6	10.6	9.6	9.6	8.5	8.5	8.5
55°	9.6	8.5	8.5	7.4	7.4	6.3	6.3	6.3
57.5°	7.4	7.4	6.3	6.3	5.4	5.4	5.4	5.4
60°	6.3	6.3	6.3	5.4	5.4	4.3	4.3	4.3
62.5°	6.3	5.4	5.4	5.4	4.3	4.3	4.3	4.3
65°	6.3	5.4	5.4	5.4	4.3	4.3	4.3	4.3
67.5°	6.3	5.4	5.4	5.4	4.3	4.3	4.3	4.3
70°	7.4	6.3	6.3	5.4	5.4	5.4	4.3	4.3
72.5°	7.4	6.3	6.3	6.3	5.4	5.4	5.4	5.4
75°	7.4	6.3	6.3	6.3	5.4	5.4	5.4	5.4
77.5°	7.4	6.3	6.3	6.3	5.4	5.4	5.4	5.4
80°	7.4	6.3	6.3	6.3	5.4	5.4	5.4	5.4
82.5°	6.3	6.3	6.3	5.4	5.4	5.4	5.4	5.4
85°	6.3	5.4	5.4	5.4	4.3	4.3	4.3	4.3
87.5°	4.3	4.3	3.2	3.2	3.2	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)