

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192571

Luminaire Tested: **LDA6A60940D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60940D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6162.5 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192571

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192571

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74
5	85	74	67	62	83	73	66	61	71	65	61		70	64	60		68
6	79	68	60	55	77	67	60	55	65	59	54		64	58	54		62
7	74	62	55	49	72	61	54	49	60	53	49		59	53	49		57
8	69	57	49	44	67	56	49	44	55	49	44		54	48	44		53
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49
10	60	48	41	36	59	48	41	36	47	41	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	63317	63317	63317
5°	173783	58342	23806
10°	380827	47750	9074
15°	581717	36345	10641
20°	673972	27034	16533
25°	735212	22235	26681
30°	821006	20161	27245
35°	835327	13833	18685
40°	850007	6555	9453
45°	851391	2729	4132
50°	719772	1185	1271
55°	231772	812	201
60°	46027	932	0
65°	4696	1103	0
70°	513	1539	0
75°	0	2033	0
80°	0	3346	347
85°	0	6667	692



TEST NUMBER: P1192571

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.8	2.5
10°-20°	810.9	13.2
20°-30°	1552.6	25.2
30°-40°	1829.2	29.7
40°-50°	1436.8	23.3
50°-60°	350.1	5.7
60°-70°	15.0	0.2
70°-80°	5.7	0.1
80°-90°	5.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2520.2	40.9
0°-40°	4349.4	70.6
0°-60°	6136.2	99.6
0°-90°	6162.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6162.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1155	1155	1155	1155	1155	
5°	3158	2285	1060	555	433	417
15°	10250	5264	640	183	188	2861
25°	12155	6401	368	385	441	5665
35°	12482	4047	207	266	279	7827
45°	10982	1251	35	49	53	8251
55°	2425	46	8	5	2	2886
65°	36	5	8	5	0	96
75°	0	5	10	6	0	0
85°	0	6	11	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192571

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0
2.5°	1979.7	1975.4	1946.5	1973.2	1892.3	1889.0	1852.8	1836.9	1790.0	1745.2	1681.3
5°	3158.0	3088.8	3032.3	3034.5	2878.9	2850.1	2769.1	2687.1	2561.3	2444.2	2285.4
7.5°	4813.7	4731.7	4612.4	4562.3	4265.0	4177.6	4010.4	3791.9	3518.1	3245.4	2951.4
10°	6841.3	6854.1	6699.6	6556.9	6107.2	5930.4	5659.8	5229.3	4710.4	4198.0	3676.9
12.5°	8881.7	8873.1	8688.9	8472.6	7918.5	7669.2	7309.1	6772.1	6084.8	5290.1	4475.0
15°	10249.8	10310.4	10232.7	10060.2	9587.0	9301.5	8895.6	8166.7	7329.3	6364.0	5264.5
17.5°	11108.5	11166.0	11138.3	11003.1	10585.4	10280.6	9941.8	9345.2	8376.7	7163.1	5886.7
20°	11552.8	11643.3	11630.6	11483.6	11168.2	10915.7	10541.7	9988.7	9150.2	7718.2	6289.4
22.5°	11849.0	11918.2	11937.5	11771.3	11445.2	11205.5	10931.7	10371.3	9582.7	8057.1	6449.3
25°	12154.8	12277.3	12156.9	11952.3	11652.9	11422.9	11130.9	10593.9	9789.5	8195.5	6401.3
27.5°	12529.8	12588.4	12315.7	12129.3	11796.9	11547.5	11237.4	10722.8	9825.7	8084.7	6127.5
30°	12969.9	12727.0	12536.3	12166.6	11789.3	11546.4	11231.1	10641.9	9635.0	7717.2	5596.9
32.5°	12897.5	12674.7	12458.4	12067.4	11694.5	11453.7	11102.1	10372.2	9184.2	7102.3	4864.9
35°	12481.9	12529.8	12296.5	11972.6	11550.7	11302.5	10918.9	9988.7	8419.3	6254.3	4046.6
37.5°	12131.4	12236.9	12084.4	11785.0	11356.7	11021.1	10503.3	9372.9	7421.0	5178.2	3271.0
40°	11877.8	11911.9	11829.9	11494.2	10979.6	10494.8	9896.0	8266.9	6208.5	4064.8	2581.7
42.5°	11484.7	11575.2	11430.3	11063.8	10283.9	9735.2	8867.9	6989.5	4822.2	3104.8	1943.4
45°	10981.8	11068.0	10889.0	10279.6	9195.0	8390.5	7332.5	5449.8	3567.1	2288.6	1250.9
47.5°	10161.3	10214.5	9868.3	9025.6	7448.6	6691.0	5606.5	3799.4	2298.2	1279.6	608.4
50°	8439.6	8414.0	7700.1	6663.4	4982.1	4187.3	3337.1	2059.5	1032.4	606.2	380.3
52.5°	5439.2	5380.6	4674.2	3731.3	2523.0	1925.3	1446.9	888.6	538.0	338.8	150.2
55°	2425.0	2402.7	1966.9	1527.8	1032.4	888.6	678.7	435.8	286.6	118.3	45.8
57.5°	899.3	879.0	774.6	650.0	498.6	414.4	329.3	208.9	73.5	39.5	24.5
60°	419.8	418.7	368.6	303.7	210.9	159.9	92.7	49.0	31.0	21.3	13.9
62.5°	134.3	131.0	91.6	67.1	47.9	41.6	33.0	24.5	16.0	11.7	8.5
65°	36.2	36.2	33.0	27.7	22.4	19.1	16.0	11.7	7.4	6.3	5.4
67.5°	13.9	13.9	12.8	11.7	8.5	7.4	6.3	5.4	4.3	5.4	5.4
70°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	5.4
72.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.3	5.4	5.4
75°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.3	5.4	5.4
77.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.3	5.4	5.4
80°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.3	5.4	5.4
82.5°	0.0	0.0	1.1	2.1	2.1	2.1	3.2	4.3	4.3	5.4	6.3
85°	0.0	0.0	1.1	2.1	2.1	3.2	3.2	4.3	4.3	5.4	6.3
87.5°	0.0	0.0	1.1	2.1	2.1	3.2	3.2	4.3	4.3	5.4	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192571

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0
2.5°	1634.5	1564.2	1467.2	1410.6	1396.8	1367.0	1314.8	1237.0	1173.1	1111.3	1075.0
5°	2151.1	1984.9	1798.5	1667.5	1614.1	1542.8	1416.0	1285.0	1164.6	1060.2	978.1
7.5°	2698.8	2425.0	2123.5	1880.5	1793.1	1680.3	1473.5	1278.5	1113.4	968.5	858.7
10°	3243.2	2802.2	2393.0	2041.5	1898.7	1745.2	1472.5	1219.9	1026.0	857.8	736.3
12.5°	3787.7	3153.8	2591.2	2138.3	1953.0	1759.1	1428.8	1130.5	915.3	743.7	627.6
15°	4290.6	3433.9	2725.5	2171.4	1947.6	1718.5	1340.3	1021.8	799.1	640.4	532.8
17.5°	4665.7	3581.0	2756.4	2121.3	1863.4	1609.9	1205.0	893.9	688.2	548.7	438.9
20°	4850.0	3604.4	2682.8	1978.6	1718.5	1455.5	1057.0	771.4	593.4	463.4	370.8
22.5°	4850.0	3493.6	2523.0	1799.6	1537.5	1277.5	914.2	670.2	518.9	403.8	326.1
25°	4665.7	3273.1	2308.8	1592.9	1338.2	1101.7	790.6	594.5	461.4	367.6	302.6
27.5°	4307.6	2968.4	2033.9	1362.7	1142.2	945.1	692.5	525.3	417.6	331.3	332.4
30°	3815.5	2594.5	1718.5	1119.7	940.9	776.7	582.8	440.0	334.5	318.5	328.2
32.5°	3246.5	2146.9	1361.6	868.4	728.8	611.6	443.2	311.1	266.4	268.5	279.2
35°	2662.6	1689.8	1024.9	643.5	542.3	443.2	290.9	204.6	202.4	206.7	214.1
37.5°	2102.2	1264.8	741.6	471.0	364.4	272.7	156.6	140.6	140.6	144.9	149.2
40°	1574.8	897.1	510.3	279.2	176.8	124.7	99.1	91.6	90.5	91.6	97.0
42.5°	1081.5	567.9	303.7	111.9	85.2	72.5	62.9	57.5	56.4	57.5	60.7
45°	607.3	349.5	118.3	59.7	51.2	45.8	39.5	36.2	35.2	35.2	37.3
47.5°	380.3	138.6	53.3	37.3	31.9	29.9	25.6	23.4	22.4	22.4	23.4
50°	146.0	54.3	33.0	24.5	21.3	19.1	17.1	14.9	13.9	13.9	14.9
52.5°	50.1	31.9	21.3	16.0	13.9	12.8	10.6	9.6	9.6	9.6	9.6
55°	27.7	19.1	12.8	9.6	8.5	8.5	8.5	8.5	8.5	8.5	8.5
57.5°	17.1	11.7	8.5	7.4	7.4	7.4	7.4	7.4	7.4	8.5	8.5
60°	9.6	7.4	6.3	6.3	6.3	6.3	7.4	7.4	7.4	8.5	8.5
62.5°	6.3	6.3	6.3	6.3	6.3	6.3	7.4	7.4	8.5	8.5	8.5
65°	5.4	5.4	5.4	6.3	6.3	6.3	7.4	7.4	8.5	8.5	8.5
67.5°	5.4	5.4	6.3	6.3	6.3	7.4	7.4	8.5	8.5	8.5	8.5
70°	5.4	6.3	6.3	7.4	7.4	7.4	8.5	8.5	8.5	9.6	9.6
72.5°	5.4	6.3	6.3	7.4	7.4	7.4	8.5	8.5	9.6	9.6	9.6
75°	6.3	6.3	6.3	7.4	7.4	7.4	8.5	9.6	9.6	9.6	9.6
77.5°	6.3	6.3	7.4	7.4	7.4	8.5	8.5	9.6	9.6	9.6	9.6
80°	6.3	6.3	7.4	7.4	8.5	8.5	9.6	9.6	9.6	10.6	10.6
82.5°	6.3	6.3	7.4	8.5	8.5	8.5	9.6	9.6	10.6	10.6	10.6
85°	6.3	7.4	7.4	8.5	8.5	8.5	9.6	9.6	10.6	10.6	10.6
87.5°	6.3	7.4	7.4	8.5	8.5	8.5	9.6	9.6	10.6	10.6	10.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192571

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0
2.5°	1027.1	982.4	937.6	904.5	888.6	872.6	837.4	791.6	772.5	744.8	728.8
5°	895.0	819.4	759.7	720.3	696.8	665.9	625.4	580.6	555.1	526.3	507.2
7.5°	758.6	670.2	612.7	576.4	553.0	514.6	463.4	410.2	379.3	347.3	325.0
10°	639.3	555.1	490.1	448.6	418.7	374.0	322.8	285.5	258.9	231.2	208.9
12.5°	533.9	443.2	374.0	338.8	318.5	276.0	233.4	191.8	175.8	170.5	170.5
15°	432.6	350.6	292.0	262.1	240.8	195.0	186.4	184.4	183.3	182.2	184.4
17.5°	352.7	283.4	221.7	206.7	204.6	203.5	204.6	204.6	205.7	208.9	214.1
20°	296.2	232.3	228.0	229.1	229.1	233.4	238.7	243.0	247.2	252.5	262.1
22.5°	263.2	262.1	269.5	270.6	276.0	282.3	292.0	298.3	309.0	314.3	328.2
25°	303.7	311.1	325.0	329.3	337.8	348.4	363.4	371.8	384.6	391.0	407.0
27.5°	344.1	355.8	372.9	378.2	385.7	402.7	413.3	420.9	427.2	431.5	441.1
30°	341.0	351.6	368.6	369.7	380.3	392.1	398.5	404.9	409.2	408.1	413.3
32.5°	288.8	298.3	314.3	314.3	326.1	335.6	338.8	344.1	344.1	344.1	346.3
35°	221.7	228.0	238.7	241.9	251.4	257.8	259.9	266.4	266.4	264.2	264.2
37.5°	153.4	161.9	169.4	171.6	177.9	182.2	187.5	188.6	186.4	187.5	187.5
40°	100.2	105.5	110.8	111.9	117.2	120.4	125.8	125.8	126.7	125.8	127.8
42.5°	61.8	66.0	69.2	71.4	73.5	75.7	78.8	79.9	81.0	79.9	82.0
45°	38.4	40.5	42.6	43.6	44.7	45.8	49.0	49.0	49.0	49.0	50.1
47.5°	23.4	24.5	25.6	25.6	26.7	27.7	28.8	28.8	28.8	28.8	29.9
50°	13.9	14.9	14.9	14.9	16.0	16.0	17.1	17.1	17.1	16.0	17.1
52.5°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	8.5	9.6
55°	8.5	8.5	7.4	7.4	7.4	7.4	7.4	6.3	5.4	5.4	4.3
57.5°	7.4	7.4	7.4	7.4	7.4	6.3	6.3	5.4	5.4	4.3	3.2
60°	7.4	7.4	7.4	7.4	7.4	6.3	6.3	5.4	4.3	4.3	3.2
62.5°	8.5	7.4	7.4	7.4	7.4	6.3	6.3	5.4	4.3	4.3	3.2
65°	8.5	8.5	7.4	7.4	7.4	6.3	6.3	5.4	5.4	4.3	3.2
67.5°	8.5	8.5	8.5	7.4	8.5	7.4	6.3	6.3	5.4	4.3	4.3
70°	9.6	8.5	8.5	8.5	8.5	7.4	7.4	6.3	5.4	4.3	4.3
72.5°	9.6	9.6	8.5	8.5	8.5	7.4	7.4	6.3	5.4	5.4	4.3
75°	9.6	9.6	8.5	8.5	8.5	7.4	7.4	6.3	6.3	5.4	4.3
77.5°	9.6	9.6	9.6	8.5	8.5	8.5	7.4	7.4	6.3	5.4	4.3
80°	9.6	9.6	9.6	9.6	9.6	8.5	8.5	7.4	6.3	5.4	4.3
82.5°	10.6	9.6	9.6	9.6	9.6	8.5	8.5	7.4	6.3	5.4	5.4
85°	10.6	10.6	9.6	9.6	9.6	8.5	8.5	7.4	6.3	6.3	5.4
87.5°	10.6	9.6	9.6	9.6	9.6	8.5	8.5	7.4	6.3	5.4	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192571

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0	1155.0
2.5°	712.7	704.2	704.2	689.3	687.3	675.5	685.1	678.7
5°	485.8	472.0	467.7	452.8	447.5	433.7	438.0	432.6
7.5°	305.7	292.0	287.7	277.0	270.6	259.9	261.0	257.8
10°	186.4	173.6	170.5	167.3	164.1	163.0	164.1	163.0
12.5°	169.4	168.3	166.2	167.3	165.1	166.2	167.3	166.2
15°	184.4	186.4	184.4	185.3	184.4	186.4	187.5	187.5
17.5°	216.3	220.6	218.4	221.7	220.6	225.9	225.9	225.9
20°	265.3	272.7	270.6	274.9	274.9	281.2	281.2	283.4
22.5°	333.5	343.0	342.1	351.6	349.5	356.9	356.9	359.1
25°	415.5	425.2	426.1	432.6	431.5	438.9	438.9	441.1
27.5°	449.7	454.9	453.9	457.1	458.2	462.4	465.6	463.4
30°	421.9	426.1	425.2	427.2	427.2	430.4	433.7	430.4
32.5°	354.8	358.0	358.0	362.3	359.1	360.1	365.4	362.3
35°	271.7	273.8	271.7	273.8	274.9	274.9	280.3	279.2
37.5°	193.9	195.0	195.0	198.1	195.0	195.0	200.3	201.4
40°	130.0	131.0	130.0	134.3	132.1	132.1	135.3	132.1
42.5°	83.1	84.2	83.1	86.3	84.2	86.3	87.4	88.5
45°	51.2	51.2	50.1	52.2	51.2	52.2	53.3	53.3
47.5°	29.9	29.9	28.8	31.0	29.9	29.9	29.9	31.0
50°	16.0	16.0	16.0	17.1	16.0	16.0	16.0	14.9
52.5°	8.5	8.5	7.4	8.5	7.4	7.4	7.4	7.4
55°	4.3	3.2	3.2	3.2	2.1	2.1	2.1	2.1
57.5°	3.2	2.1	2.1	1.1	1.1	1.1	0.0	0.0
60°	2.1	2.1	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.1	2.1	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.1	2.1	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.2	2.1	2.1	1.1	1.1	0.0	0.0	0.0
70°	3.2	2.1	2.1	1.1	1.1	0.0	0.0	0.0
72.5°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
75°	3.2	3.2	2.1	2.1	1.1	1.1	0.0	0.0
77.5°	4.3	3.2	2.1	2.1	1.1	1.1	0.0	0.0
80°	4.3	3.2	2.1	2.1	2.1	1.1	1.1	1.1
82.5°	4.3	3.2	3.2	2.1	2.1	1.1	1.1	1.1
85°	4.3	3.2	3.2	2.1	2.1	1.1	1.1	1.1
87.5°	4.3	3.2	3.2	2.1	2.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)