

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192573

Luminaire Tested: **LDA6A60940D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60940D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5726.7 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192573

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192573

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	50	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	44	40	38		
10	60	48	41	37	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	61157	61157	61157
5°	162299	56697	21693
10°	354274	45846	6463
15°	534759	33502	5624
20°	622039	22997	8827
25°	686011	24812	58782
30°	758990	18680	18281
35°	770271	9557	6840
40°	787983	3886	3278
45°	794602	2403	1985
50°	669368	1629	1271
55°	221087	1118	707
60°	43461	1053	471
65°	5124	1375	558
70°	1362	1539	689
75°	233	2033	1144
80°	0	3346	1705
85°	0	6667	2705

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192573

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.4	2.6
10°-20°	749.7	13.1
20°-30°	1479.7	25.8
30°-40°	1669.1	29.1
40°-50°	1325.1	23.1
50°-60°	324.0	5.7
60°-70°	17.3	0.3
70°-80°	7.4	0.1
80°-90°	6.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2377.9	41.5
0°-40°	4047.0	70.7
0°-60°	5696.0	99.5
0°-90°	5726.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5726.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1116	1116	1116	1116	1116	
5°	2949	2210	1030	518	394	390
15°	9422	5008	590	116	99	2643
25°	11341	6070	410	743	972	5253
35°	11510	3864	143	113	102	7238
45°	10249	1204	31	32	26	7682
55°	2313	52	12	12	7	2714
65°	40	10	11	8	4	96
75°	1	5	10	8	5	3
85°	0	5	11	7	4	0
90°	0	0	0	0	0	

TEST NUMBER: P1192573

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6
2.5°	1936.1	1898.8	1915.8	1889.1	1813.5	1790.1	1809.2	1780.5	1694.2	1661.2	1627.0
5°	2949.3	2916.3	2927.0	2866.2	2724.5	2675.5	2672.3	2585.0	2410.2	2312.2	2209.9
7.5°	4472.0	4426.2	4413.4	4267.4	3994.6	3892.4	3842.3	3627.1	3297.8	3064.5	2835.4
10°	6364.3	6409.1	6363.3	6126.7	5698.4	5506.6	5385.1	4978.1	4384.7	3940.2	3511.9
12.5°	8262.0	8289.7	8203.4	7909.4	7364.9	7134.7	6955.7	6434.7	5652.6	4898.2	4258.9
15°	9422.4	9553.5	9472.4	9266.9	8844.9	8565.7	8404.8	7761.2	6776.7	5947.7	5008.0
17.5°	10249.3	10370.6	10303.6	10135.2	9658.9	9434.0	9329.7	8800.1	7728.2	6674.4	5568.4
20°	10662.6	10810.8	10750.0	10559.3	10209.8	10022.3	9895.5	9378.7	8412.3	7214.7	5942.4
22.5°	10942.9	11107.0	11040.9	10867.2	10511.4	10292.9	10233.3	9744.2	8770.3	7538.6	6101.1
25°	11341.4	11478.8	11292.4	11078.3	10726.6	10496.4	10460.2	9960.5	8941.9	7661.0	6070.3
27.5°	11627.0	11790.0	11473.6	11256.2	10854.4	10612.5	10565.7	10095.9	8957.8	7564.2	5819.9
30°	11990.2	11884.8	11606.8	11291.3	10862.9	10605.1	10545.4	10016.9	8798.0	7207.2	5329.8
32.5°	11846.5	11820.9	11542.8	11172.0	10772.4	10512.4	10432.5	9774.0	8359.0	6591.2	4636.1
35°	11509.8	11590.7	11358.4	11128.2	10631.8	10361.1	10250.2	9416.0	7697.3	5798.6	3863.6
37.5°	11312.6	11363.8	11216.7	10935.4	10443.1	10087.3	9877.4	8813.9	6831.1	4799.1	3118.8
40°	11011.1	11141.0	10999.3	10676.5	10108.5	9620.6	9255.0	7726.1	5689.9	3783.7	2439.0
42.5°	10680.8	10796.9	10661.6	10274.9	9472.4	8818.2	8210.8	6447.5	4455.0	2890.8	1829.4
45°	10249.3	10353.7	10110.7	9508.7	8372.8	7470.3	6864.1	5063.4	3359.6	2123.6	1204.1
47.5°	9471.5	9443.7	9099.6	8164.1	6765.0	5956.2	5250.8	3627.1	2233.3	1203.0	598.8
50°	7848.6	7589.7	7083.5	5997.8	4540.1	3666.4	3184.9	1872.1	1013.4	582.8	376.2
52.5°	5083.6	4794.8	4331.3	3328.6	2180.0	1749.6	1403.3	846.1	528.5	329.3	148.1
55°	2313.2	2108.6	1812.5	1344.7	935.5	777.8	658.5	428.3	283.4	122.6	52.2
57.5°	881.1	813.0	722.4	576.5	432.6	374.0	310.1	205.7	88.5	45.8	31.0
60°	396.4	367.6	337.8	264.3	185.3	133.2	101.3	55.4	37.3	26.7	20.2
62.5°	135.3	113.0	93.7	67.1	50.1	43.7	38.4	31.0	22.4	18.2	13.9
65°	39.5	38.4	36.2	31.9	25.6	23.4	22.4	18.2	13.9	11.7	9.6
67.5°	19.1	18.2	17.1	16.0	12.8	11.7	11.7	10.6	8.5	7.4	6.3
70°	8.5	8.5	7.4	7.4	6.3	6.3	6.3	5.4	5.4	5.4	5.4
72.5°	4.3	4.3	4.3	3.2	3.2	3.2	3.2	4.3	4.3	5.4	5.4
75°	1.1	2.1	2.1	2.1	2.1	3.2	3.2	4.3	4.3	5.4	5.4
77.5°	1.1	1.1	1.1	2.1	2.1	2.1	3.2	4.3	4.3	5.4	5.4
80°	0.0	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.3	5.4	5.4
82.5°	0.0	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.3	5.4	5.4
85°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.3	5.4	5.4
87.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.3	5.4	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192573

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6
2.5°	1543.9	1521.5	1433.2	1364.9	1333.0	1330.8	1259.4	1215.8	1139.0	1079.4	1022.9
5°	2029.8	1930.7	1751.7	1610.0	1541.9	1506.6	1366.0	1264.8	1132.7	1030.3	929.2
7.5°	2524.3	2335.6	2084.1	1814.6	1703.8	1635.6	1418.2	1256.2	1080.4	937.7	811.9
10°	3030.3	2697.9	2322.8	1966.9	1807.1	1692.0	1412.9	1193.3	990.9	823.6	686.2
12.5°	3557.7	3033.5	2511.5	2066.1	1855.0	1703.8	1364.9	1101.7	881.1	703.2	572.2
15°	4002.2	3293.6	2630.8	2089.5	1840.2	1656.9	1262.7	985.6	763.9	590.3	471.0
17.5°	4345.2	3439.5	2653.2	2032.0	1757.1	1552.5	1130.5	857.8	640.4	486.9	368.6
20°	4517.8	3461.8	2582.8	1895.6	1606.8	1395.9	980.2	727.7	537.0	394.2	293.1
22.5°	4530.6	3357.4	2429.3	1719.8	1441.7	1227.5	856.7	627.6	471.0	353.8	278.1
25°	4364.3	3156.1	2223.8	1539.7	1272.2	1079.4	768.2	602.0	474.1	410.2	377.1
27.5°	4048.9	2876.9	1997.8	1359.6	1126.2	977.0	732.0	602.0	513.6	463.5	475.2
30°	3612.1	2521.0	1683.6	1114.5	916.4	786.3	575.4	450.7	353.8	295.1	284.5
32.5°	3045.2	2062.8	1305.2	823.6	668.0	566.9	389.0	282.3	228.0	222.6	216.3
35°	2506.1	1629.2	990.9	608.4	492.3	400.7	248.2	166.2	151.3	142.8	136.4
37.5°	1979.7	1218.9	711.8	442.2	337.8	254.7	127.8	107.6	93.7	85.3	77.7
40°	1488.5	875.9	501.8	267.5	176.9	109.8	76.8	66.0	58.6	54.3	52.2
42.5°	1052.7	582.8	311.1	113.0	84.2	69.2	53.3	46.9	42.6	40.5	38.4
45°	611.6	362.3	125.8	66.0	53.3	47.9	39.5	35.2	33.0	31.0	29.9
47.5°	382.5	146.0	64.9	42.6	37.3	34.1	28.8	27.7	25.6	24.5	24.5
50°	154.5	64.9	40.5	29.9	26.7	25.6	22.4	21.3	19.1	19.1	19.1
52.5°	58.6	38.4	27.7	21.3	19.1	18.2	16.0	16.0	14.9	14.9	14.9
55°	34.1	25.6	19.1	14.9	13.9	13.9	12.8	12.8	11.7	11.7	11.7
57.5°	22.4	17.1	13.9	10.6	10.6	10.6	9.6	9.6	9.6	9.6	9.6
60°	14.9	11.7	9.6	8.5	8.5	8.5	8.5	9.6	9.6	9.6	9.6
62.5°	10.6	9.6	8.5	8.5	8.5	8.5	8.5	9.6	9.6	9.6	10.6
65°	8.5	7.4	7.4	7.4	7.4	8.5	8.5	9.6	9.6	10.6	10.6
67.5°	6.3	6.3	6.3	6.3	7.4	7.4	8.5	9.6	9.6	9.6	10.6
70°	5.4	6.3	6.3	7.4	7.4	7.4	8.5	8.5	9.6	9.6	10.6
72.5°	5.4	6.3	6.3	7.4	7.4	7.4	8.5	9.6	9.6	9.6	10.6
75°	5.4	6.3	6.3	7.4	7.4	7.4	8.5	9.6	9.6	9.6	10.6
77.5°	6.3	6.3	7.4	7.4	7.4	8.5	8.5	9.6	9.6	10.6	10.6
80°	6.3	6.3	7.4	7.4	7.4	8.5	8.5	9.6	9.6	10.6	10.6
82.5°	6.3	6.3	7.4	7.4	7.4	8.5	8.5	9.6	9.6	10.6	10.6
85°	6.3	6.3	7.4	7.4	7.4	8.5	8.5	9.6	9.6	10.6	10.6
87.5°	6.3	6.3	7.4	7.4	7.4	8.5	8.5	9.6	9.6	9.6	10.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192573

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6
2.5°	995.2	946.2	892.8	875.9	858.8	825.8	805.5	769.3	742.7	716.0	694.7
5°	862.0	784.3	719.2	691.5	664.9	619.0	587.1	548.7	517.9	491.2	466.7
7.5°	723.5	634.0	569.0	541.3	514.6	464.5	424.1	376.2	339.9	310.1	285.5
10°	595.6	510.3	440.0	407.0	376.2	323.9	285.5	247.2	216.3	190.7	168.4
12.5°	484.9	393.2	321.8	297.3	267.5	224.8	188.6	147.1	128.9	121.5	116.1
15°	376.2	294.0	234.5	212.0	185.3	144.9	128.9	121.5	116.1	113.0	108.7
17.5°	286.6	218.5	159.9	144.9	136.4	127.8	123.6	118.3	115.0	114.1	110.8
20°	224.8	165.1	150.2	146.0	146.0	143.8	140.6	140.6	139.5	142.8	142.8
22.5°	231.2	231.2	244.0	243.0	260.0	277.0	289.8	331.3	354.8	404.9	439.1
25°	403.8	442.2	486.9	500.8	533.9	582.8	634.0	697.9	742.7	790.6	809.7
27.5°	504.0	510.3	504.0	520.0	498.6	485.8	490.1	497.5	497.5	500.8	513.6
30°	298.3	313.3	327.1	337.8	332.4	327.1	325.0	309.0	309.0	302.6	297.3
32.5°	202.4	200.3	198.1	202.4	198.1	198.1	195.0	196.1	189.6	185.3	183.3
35°	138.6	132.1	124.7	125.8	121.5	120.4	117.2	117.2	113.0	110.8	109.8
37.5°	76.8	76.8	73.5	74.6	73.5	73.5	73.5	74.6	73.5	73.5	74.6
40°	52.2	52.2	51.2	52.2	51.2	52.2	53.3	53.3	53.3	53.3	52.2
42.5°	39.5	39.5	38.4	39.5	38.4	39.5	40.5	40.5	40.5	40.5	40.5
45°	31.0	31.0	31.0	31.0	31.0	31.0	31.0	31.9	31.9	31.0	31.0
47.5°	24.5	25.6	24.5	24.5	24.5	24.5	25.6	25.6	24.5	24.5	24.5
50°	20.2	20.2	19.1	19.1	19.1	19.1	19.1	19.1	19.1	19.1	19.1
52.5°	16.0	14.9	14.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	12.8
55°	11.7	11.7	10.6	10.6	10.6	11.7	11.7	11.7	11.7	10.6	10.6
57.5°	10.6	10.6	10.6	9.6	9.6	10.6	10.6	9.6	9.6	9.6	8.5
60°	9.6	10.6	9.6	9.6	9.6	9.6	9.6	8.5	8.5	8.5	7.4
62.5°	10.6	10.6	9.6	9.6	9.6	9.6	8.5	8.5	8.5	7.4	7.4
65°	10.6	10.6	10.6	9.6	9.6	9.6	9.6	8.5	8.5	7.4	7.4
67.5°	10.6	10.6	10.6	10.6	9.6	9.6	9.6	8.5	8.5	8.5	7.4
70°	10.6	10.6	10.6	10.6	10.6	9.6	9.6	9.6	8.5	8.5	7.4
72.5°	10.6	10.6	10.6	9.6	9.6	9.6	9.6	9.6	8.5	8.5	7.4
75°	10.6	10.6	10.6	9.6	9.6	9.6	9.6	8.5	8.5	8.5	7.4
77.5°	10.6	10.6	10.6	9.6	9.6	9.6	9.6	8.5	8.5	8.5	7.4
80°	10.6	10.6	10.6	9.6	9.6	9.6	9.6	8.5	8.5	8.5	7.4
82.5°	10.6	10.6	10.6	9.6	9.6	9.6	9.6	8.5	8.5	7.4	7.4
85°	10.6	10.6	9.6	9.6	9.6	9.6	8.5	8.5	7.4	7.4	6.3
87.5°	9.6	9.6	9.6	9.6	8.5	8.5	8.5	7.4	6.3	6.3	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192573

CATALOG NUMBER: LDA6A60940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6	1115.6
2.5°	669.1	664.9	661.7	668.0	665.9	639.3	642.6	641.5
5°	439.1	429.4	422.0	425.2	416.6	404.9	396.4	394.2
7.5°	261.0	250.4	244.0	237.6	235.4	220.6	214.2	218.5
10°	143.8	128.9	127.8	124.7	120.4	117.2	115.0	116.1
12.5°	110.8	109.8	107.6	106.5	104.4	103.3	102.2	101.3
15°	105.5	104.4	103.3	102.2	101.3	100.2	99.1	99.1
17.5°	108.7	108.7	107.6	106.5	106.5	107.6	106.5	105.5
20°	141.7	141.7	143.8	147.1	147.1	150.2	154.5	151.3
22.5°	460.3	483.8	512.5	521.1	571.1	611.6	686.2	653.2
25°	841.8	895.0	907.8	926.0	953.7	967.5	953.7	971.8
27.5°	511.4	529.6	531.7	532.8	539.1	538.1	524.2	532.8
30°	297.3	303.7	301.6	300.5	298.3	286.6	284.5	288.8
32.5°	186.4	184.4	183.3	182.2	182.2	175.8	179.0	176.9
35°	106.5	109.8	108.7	107.6	104.4	103.3	103.3	102.2
37.5°	71.4	72.5	71.4	70.3	68.2	67.1	66.0	64.9
40°	51.2	52.2	51.2	50.1	49.0	47.9	46.9	45.8
42.5°	38.4	39.5	38.4	38.4	36.2	35.2	34.1	33.0
45°	29.9	28.8	28.8	28.8	27.7	26.7	25.6	25.6
47.5°	24.5	24.5	24.5	23.4	22.4	22.4	22.4	21.3
50°	18.2	19.1	18.2	18.2	17.1	16.0	16.0	14.9
52.5°	12.8	12.8	11.7	11.7	10.6	9.6	9.6	9.6
55°	9.6	9.6	9.6	8.5	8.5	7.4	7.4	7.4
57.5°	8.5	7.4	7.4	7.4	6.3	6.3	5.4	5.4
60°	7.4	6.3	6.3	5.4	5.4	4.3	4.3	4.3
62.5°	6.3	5.4	5.4	5.4	4.3	4.3	4.3	4.3
65°	6.3	5.4	5.4	5.4	4.3	4.3	4.3	4.3
67.5°	6.3	6.3	5.4	5.4	5.4	4.3	4.3	4.3
70°	6.3	6.3	6.3	5.4	5.4	5.4	4.3	4.3
72.5°	7.4	6.3	6.3	6.3	5.4	5.4	5.4	5.4
75°	7.4	6.3	6.3	6.3	5.4	5.4	5.4	5.4
77.5°	7.4	6.3	6.3	6.3	5.4	5.4	5.4	5.4
80°	6.3	6.3	6.3	5.4	5.4	5.4	5.4	5.4
82.5°	6.3	6.3	6.3	6.3	5.4	5.4	5.4	5.4
85°	6.3	5.4	5.4	5.4	4.3	4.3	4.3	4.3
87.5°	5.4	4.3	4.3	3.2	3.2	3.2	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)