

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192582

Luminaire Tested: **LDA6A60950D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192582
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60950D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6094.3 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192582

CATALOG NUMBER: LDA6A60950D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot





TEST NUMBER: P1192582

CATALOG NUMBER: LDA6A60950D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	60264	60264	60264
5°	154584	54820	17070
10°	301336	42128	8205
15°	540934	28621	11005
20°	803121	21719	18167
25°	912875	17898	28483
30°	989564	19573	26795
35°	1042333	12682	16610
40°	1064874	5632	8087
45°	961790	2155	3008
50°	633114	853	853
55°	173385	736	0
60°	34624	844	0
65°	2452	1141	0
70°	353	1410	0
75°	0	2118	0
80°	0	3157	347
85°	0	6290	692

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192582

CATALOG NUMBER: LDA6A60950D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.7	2.2
10°-20°	715.4	11.7
20°-30°	1621.4	26.6
30°-40°	1946.3	31.9
40°-50°	1371.7	22.5
50°-60°	283.0	4.6
60°-70°	10.0	0.2
70°-80°	6.0	0.1
80°-90°	5.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2471.5	40.6
0°-40°	4417.8	72.5
0°-60°	6072.5	99.6
0°-90°	6094.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6094.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1099	1099	1099	1099	1099	
5°	2809	2047	996	414	310	346
15°	9531	4193	504	180	194	2829
25°	15092	5072	296	414	471	6965
35°	15575	3552	190	248	248	9682
45°	12406	1218	28	38	39	9124
55°	1814	24	8	6	0	2390
65°	19	6	9	6	0	56
75°	0	6	10	7	0	0
85°	0	7	10	7	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192582

CATALOG NUMBER: LDA6A60950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3
2.5°	1873.9	1817.3	1839.6	1774.1	1759.8	1747.5	1759.8	1688.9	1648.9	1598.0	1557.0
5°	2809.1	2741.5	2757.0	2643.0	2590.8	2555.4	2548.7	2402.4	2292.8	2171.9	2046.7
7.5°	3910.7	3846.4	3837.6	3660.3	3552.7	3491.8	3466.3	3256.9	3067.4	2852.3	2617.5
10°	5413.3	5267.1	5221.6	4964.5	4759.6	4629.9	4470.3	4135.7	3803.2	3478.5	3179.3
12.5°	7162.0	7082.3	6969.2	6515.9	6156.9	5972.9	5734.8	5211.6	4708.6	4172.3	3671.3
15°	9531.2	9247.6	9054.7	8399.8	7821.3	7537.7	7189.7	6389.7	5629.4	4950.1	4193.3
17.5°	11846.2	11697.7	11396.3	10546.3	9655.4	9207.6	8689.1	7602.0	6528.2	5561.8	4637.6
20°	13766.6	13627.0	13283.5	12482.3	11493.8	10833.4	10180.6	8689.1	7286.1	6049.4	4934.7
22.5°	14686.4	14597.6	14317.4	13631.5	12789.2	12160.9	11459.4	9614.4	7846.8	6368.6	5069.8
25°	15092.0	15051.0	14870.2	14329.5	13536.1	13003.1	12340.4	10269.3	8195.9	6517.1	5072.1
27.5°	15503.1	15510.9	15111.9	14684.1	13931.7	13419.7	12781.5	10559.6	8259.1	6433.9	4905.8
30°	15632.7	15550.7	15374.5	14760.6	14045.9	13501.7	12817.0	10425.6	7999.8	6092.6	4574.5
32.5°	15579.6	15547.4	15353.5	14704.1	13852.0	13252.4	12474.6	9893.6	7487.8	5605.1	4104.6
35°	15575.1	15515.3	15070.8	14513.5	13464.0	12723.8	11698.9	9033.6	6763.0	4962.3	3551.6
37.5°	15293.7	15145.1	14811.6	14060.3	12677.3	11738.8	10589.6	7983.1	5876.5	4240.9	3003.1
40°	14880.3	14680.8	14242.1	13105.0	11314.4	10232.7	9111.2	6789.6	4937.9	3529.4	2420.2
42.5°	14017.0	13715.6	13095.1	11531.4	9498.0	8522.8	7589.8	5580.6	4027.0	2875.7	1847.2
45°	12405.8	11993.6	11154.6	9438.2	7672.8	6877.2	6127.0	4490.2	3223.7	2133.1	1217.8
47.5°	9971.2	9588.9	8825.3	7513.3	6017.3	5344.7	4746.2	3340.0	2185.2	1235.6	581.8
50°	7423.5	7095.6	6499.3	5221.6	4039.2	3510.6	2998.7	1897.2	1024.0	587.3	241.6
52.5°	4429.3	4266.4	3737.9	2895.6	1994.6	1718.7	1379.6	803.4	516.5	212.8	65.4
55°	1814.1	1674.4	1476.1	1184.6	867.8	735.8	629.5	396.7	160.7	44.3	24.3
57.5°	820.0	789.0	699.3	549.6	398.9	334.7	226.1	75.4	35.5	22.2	14.5
60°	315.8	284.8	243.9	132.0	56.5	47.6	38.8	25.5	17.8	12.2	8.8
62.5°	45.4	43.3	38.8	31.1	24.3	22.2	18.9	13.3	10.0	7.7	6.6
65°	18.9	18.9	16.6	13.3	11.0	10.0	8.8	6.6	5.6	5.6	5.6
67.5°	7.7	7.7	6.6	5.6	4.5	4.5	4.5	3.3	4.5	4.5	5.6
70°	2.2	2.2	2.2	2.2	2.2	2.2	3.3	3.3	4.5	4.5	5.6
72.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.3	4.5	5.6	5.6
75°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.3	4.5	5.6	5.6
77.5°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.5	5.6	5.6
80°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.5	5.6	6.6
82.5°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.5	5.6	6.6
85°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.5	5.6	6.6
87.5°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.5	5.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192582

CATALOG NUMBER: LDA6A60950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3
2.5°	1521.5	1450.6	1430.6	1368.5	1316.5	1291.1	1258.8	1186.8	1132.5	1060.5	1017.2
5°	1959.3	1825.2	1718.7	1589.1	1503.8	1448.4	1362.0	1230.0	1123.7	996.2	905.3
7.5°	2432.4	2187.5	1995.8	1781.9	1658.9	1562.5	1415.1	1225.6	1069.3	899.8	759.1
10°	2889.0	2523.2	2221.9	1915.0	1753.0	1619.0	1416.3	1178.0	970.7	756.8	608.4
12.5°	3291.2	2819.1	2394.7	2000.2	1799.6	1632.3	1378.6	1092.7	842.3	622.8	491.9
15°	3627.0	3048.6	2516.6	2032.4	1803.0	1603.6	1299.9	970.7	699.3	504.3	412.3
17.5°	3881.9	3169.3	2554.2	1993.6	1738.8	1521.5	1179.2	816.6	567.4	427.8	346.8
20°	4013.7	3192.6	2500.1	1888.3	1620.1	1397.3	1020.6	662.7	480.9	372.3	290.4
22.5°	4030.3	3127.2	2370.4	1737.6	1470.5	1246.6	845.5	553.0	428.9	329.2	256.0
25°	3931.7	2985.4	2185.2	1566.9	1306.4	1073.8	688.2	495.4	390.1	295.9	294.7
27.5°	3721.2	2741.5	1963.7	1368.5	1108.1	873.2	584.0	447.7	348.0	313.7	333.5
30°	3424.2	2429.0	1691.1	1118.1	865.5	671.5	491.9	369.0	305.8	309.2	325.8
32.5°	3021.9	2041.3	1370.7	818.9	619.4	505.2	369.0	251.6	253.8	254.9	269.3
35°	2516.6	1636.8	1024.0	550.8	435.4	355.8	208.3	185.0	188.4	189.5	199.5
37.5°	2016.8	1257.8	680.5	366.8	273.7	187.3	129.7	124.1	126.4	125.2	136.3
40°	1544.7	876.6	407.8	181.7	105.4	87.6	79.9	76.4	77.6	78.7	85.3
42.5°	1093.7	475.4	201.7	68.6	55.4	51.0	47.6	45.4	46.5	46.5	51.0
45°	555.3	225.0	68.6	37.6	34.3	31.1	28.8	27.8	27.8	27.8	30.0
47.5°	240.4	74.3	32.2	23.3	21.0	19.9	17.8	16.6	16.6	16.6	17.8
50°	75.4	30.0	19.9	15.5	13.3	12.2	11.0	11.0	11.0	10.0	11.0
52.5°	27.8	18.9	13.3	10.0	8.8	8.8	8.8	7.7	8.8	7.7	8.8
55°	16.6	12.2	8.8	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
57.5°	11.0	8.8	7.7	7.7	6.6	6.6	7.7	7.7	7.7	7.7	7.7
60°	7.7	7.7	6.6	6.6	6.6	6.6	7.7	7.7	7.7	7.7	7.7
62.5°	6.6	6.6	6.6	6.6	6.6	6.6	7.7	7.7	7.7	7.7	8.8
65°	5.6	6.6	6.6	6.6	6.6	6.6	7.7	7.7	8.8	8.8	8.8
67.5°	5.6	6.6	6.6	7.7	7.7	7.7	7.7	8.8	8.8	8.8	8.8
70°	6.6	6.6	7.7	7.7	7.7	7.7	8.8	8.8	8.8	8.8	10.0
72.5°	6.6	6.6	7.7	7.7	7.7	7.7	8.8	8.8	10.0	10.0	10.0
75°	6.6	7.7	7.7	7.7	7.7	8.8	8.8	8.8	10.0	10.0	10.0
77.5°	6.6	7.7	7.7	8.8	8.8	8.8	8.8	10.0	10.0	10.0	10.0
80°	6.6	7.7	7.7	8.8	8.8	8.8	10.0	10.0	10.0	10.0	11.0
82.5°	6.6	7.7	7.7	8.8	8.8	8.8	10.0	10.0	10.0	10.0	11.0
85°	7.7	7.7	8.8	8.8	8.8	8.8	10.0	10.0	10.0	10.0	11.0
87.5°	7.7	7.7	8.8	8.8	8.8	8.8	10.0	10.0	11.0	10.0	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192582

CATALOG NUMBER: LDA6A60950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3
2.5°	959.6	895.3	851.0	834.4	802.4	751.4	721.3	693.7	641.7	630.4	601.7
5°	801.2	698.2	625.0	597.3	560.8	517.6	475.4	447.7	414.4	401.1	381.2
7.5°	631.6	528.6	465.5	443.4	417.9	382.3	344.6	317.0	282.6	264.9	248.2
10°	496.4	420.0	366.8	344.6	318.1	280.3	241.6	205.1	175.1	156.2	153.0
12.5°	403.4	340.2	283.6	260.4	229.4	191.8	164.0	162.9	160.7	159.5	161.8
15°	330.3	269.3	209.5	184.0	175.1	174.0	177.3	180.5	179.6	182.8	185.0
17.5°	271.4	206.0	192.7	193.9	195.0	198.3	203.9	212.8	213.9	219.3	223.8
20°	221.6	218.4	223.8	228.3	231.7	238.3	250.4	261.6	264.9	272.6	281.4
22.5°	251.6	261.6	273.7	279.3	283.6	295.9	309.2	327.0	333.5	343.6	355.8
25°	303.7	320.2	339.1	345.7	352.5	372.3	387.8	408.9	414.4	426.6	438.9
27.5°	346.8	364.6	384.5	393.3	398.9	418.8	432.1	445.4	445.4	452.2	461.0
30°	340.2	354.6	371.2	377.9	380.0	394.5	407.8	412.3	410.0	413.4	420.0
32.5°	282.6	293.6	306.9	312.5	314.7	324.7	335.7	335.7	334.7	334.7	339.1
35°	209.5	217.3	223.8	229.4	232.6	239.4	249.3	248.2	248.2	246.0	249.3
37.5°	140.8	145.1	153.0	155.2	156.2	160.7	168.4	168.4	166.3	167.3	169.5
40°	85.3	90.9	95.3	96.4	98.6	101.9	107.4	107.4	107.4	107.4	108.6
42.5°	51.0	54.3	57.6	57.6	58.7	63.1	65.4	65.4	65.4	65.4	66.6
45°	30.0	31.1	33.2	34.3	34.3	36.6	37.6	37.6	37.6	37.6	38.8
47.5°	17.8	18.9	18.9	19.9	19.9	21.0	22.2	22.2	21.0	21.0	21.0
50°	11.0	11.0	11.0	11.0	12.2	12.2	12.2	12.2	12.2	12.2	11.0
52.5°	8.8	8.8	8.8	8.8	7.7	7.7	7.7	7.7	6.6	6.6	5.6
55°	7.7	7.7	7.7	7.7	7.7	6.6	6.6	6.6	5.6	4.5	3.3
57.5°	7.7	7.7	7.7	7.7	7.7	6.6	6.6	5.6	4.5	4.5	3.3
60°	7.7	7.7	7.7	7.7	7.7	6.6	6.6	5.6	4.5	4.5	3.3
62.5°	8.8	8.8	7.7	7.7	7.7	6.6	6.6	5.6	5.6	4.5	3.3
65°	8.8	8.8	7.7	7.7	7.7	7.7	6.6	6.6	5.6	4.5	3.3
67.5°	8.8	8.8	8.8	8.8	7.7	7.7	7.7	6.6	5.6	4.5	3.3
70°	10.0	10.0	8.8	8.8	8.8	7.7	7.7	6.6	5.6	5.6	4.5
72.5°	10.0	10.0	8.8	8.8	8.8	8.8	7.7	6.6	6.6	5.6	4.5
75°	10.0	10.0	10.0	10.0	8.8	8.8	7.7	7.7	6.6	5.6	4.5
77.5°	10.0	10.0	10.0	10.0	8.8	8.8	8.8	7.7	6.6	5.6	4.5
80°	10.0	10.0	10.0	10.0	10.0	8.8	8.8	7.7	6.6	5.6	4.5
82.5°	11.0	11.0	10.0	10.0	10.0	8.8	8.8	7.7	6.6	5.6	5.6
85°	11.0	11.0	10.0	10.0	10.0	8.8	8.8	7.7	6.6	6.6	5.6
87.5°	11.0	11.0	10.0	10.0	10.0	8.8	8.8	7.7	6.6	6.6	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192582

CATALOG NUMBER: LDA6A60950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3	1099.3
2.5°	584.0	550.8	539.7	547.5	538.6	531.9	523.0	518.5
5°	365.8	341.3	333.5	335.7	328.0	321.4	312.5	310.2
7.5°	225.0	201.7	192.7	192.7	184.0	176.2	170.7	167.3
10°	150.7	146.2	147.4	148.5	147.4	148.5	145.1	147.4
12.5°	161.8	159.5	161.8	162.9	162.9	165.2	160.7	164.0
15°	188.4	186.2	189.5	191.8	191.8	195.0	190.6	193.9
17.5°	230.6	229.4	234.9	237.1	238.3	243.9	238.3	242.7
20°	291.5	290.4	298.1	301.4	300.4	311.4	303.7	311.4
22.5°	370.1	368.0	379.0	382.3	383.3	397.8	391.2	396.7
25°	448.8	451.0	456.7	462.1	463.2	475.4	465.5	470.9
27.5°	465.5	462.1	465.5	472.1	473.2	478.7	469.9	474.2
30°	421.1	415.6	416.7	424.4	426.6	428.9	421.1	423.3
32.5°	342.5	333.5	333.5	341.3	343.6	346.8	333.5	339.1
35°	252.7	244.8	244.8	250.4	251.6	253.8	243.9	248.2
37.5°	172.8	166.3	168.4	170.7	171.7	174.0	172.8	171.7
40°	110.8	106.3	109.7	109.7	110.8	111.9	111.9	113.0
42.5°	67.5	64.3	66.6	66.6	67.5	67.5	67.5	68.6
45°	38.8	37.6	37.6	38.8	38.8	38.8	37.6	38.8
47.5°	21.0	19.9	21.0	21.0	21.0	21.0	21.0	21.0
50°	11.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0
52.5°	5.6	4.5	4.5	4.5	3.3	4.5	3.3	3.3
55°	3.3	2.2	2.2	2.2	1.1	1.1	0.0	0.0
57.5°	2.2	1.1	1.1	1.1	0.0	0.0	0.0	0.0
60°	2.2	1.1	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.2	1.1	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.2	1.1	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.3	2.2	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.3	2.2	2.2	1.1	1.1	0.0	0.0	0.0
72.5°	3.3	2.2	2.2	2.2	1.1	1.1	0.0	0.0
75°	3.3	2.2	2.2	2.2	1.1	1.1	0.0	0.0
77.5°	3.3	3.3	2.2	2.2	1.1	1.1	1.1	0.0
80°	4.5	3.3	2.2	2.2	2.2	1.1	1.1	1.1
82.5°	4.5	3.3	2.2	2.2	2.2	1.1	1.1	1.1
85°	4.5	3.3	3.3	2.2	2.2	1.1	1.1	1.1
87.5°	4.5	3.3	3.3	2.2	2.2	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)