

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192664

Luminaire Tested: **LDA6A65950D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192664
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26689)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A65950D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5363.3 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 2.34 / 0.96 / 1.3
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 66.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192664

CATALOG NUMBER: LDA6A65950D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192664

CATALOG NUMBER: LDA6A65950D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	51	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	61	50	43	38	49	43	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	83694	83694	83694
5°	163641	79562	29028
10°	275440	68313	6435
15°	419458	51726	10573
20°	606136	41899	117879
25°	902078	67788	34073
30°	1041926	23212	6735
35°	1042260	5187	3634
40°	851875	2898	2240
45°	645082	1876	1434
50°	428404	1288	981
55°	68872	1099	774
60°	4309	1140	625
65°	1349	1492	739
70°	753	1667	914
75°	487	1949	1207
80°	347	2904	1799
85°	692	5787	2139



TEST NUMBER: P1192664

CATALOG NUMBER: LDA6A65950D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.4	3.0
10°-20°	681.4	12.7
20°-30°	1604.2	29.9
30°-40°	1690.2	31.5
40°-50°	1053.9	19.6
50°-60°	151.4	2.8
60°-70°	9.7	0.2
70°-80°	7.6	0.1
80°-90°	5.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2445.0	45.6
0°-40°	4135.1	77.1
0°-60°	5340.4	99.6
0°-90°	5363.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5363.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1527	1527	1527	1527	1527	
5°	2974	2407	1446	751	528	345
15°	7391	4184	911	158	186	2201
25°	14914	5015	1121	811	563	6711
35°	15574	3673	78	72	54	9394
45°	8321	1017	24	27	18	6512
55°	721	18	12	13	8	1295
65°	10	8	12	9	6	15
75°	2	6	9	9	6	3
85°	1	6	9	7	3	1
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192664

CATALOG NUMBER: LDA6A65950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7
2.5°	2228.8	2213.7	2218.4	2183.7	2137.5	2158.3	2106.2	2107.5	2074.9	1992.8	1957.0
5°	2973.7	2971.4	2968.0	2904.3	2822.1	2831.4	2755.1	2726.2	2642.8	2498.3	2406.9
7.5°	3899.0	3900.2	3882.7	3727.8	3636.4	3630.6	3510.3	3423.7	3268.6	3040.8	2874.2
10°	4948.1	4980.5	4949.2	4710.9	4541.0	4543.2	4326.9	4160.4	3911.8	3579.8	3342.7
12.5°	6179.8	6184.5	6135.9	5822.4	5563.3	5543.7	5253.5	4935.3	4557.1	4123.4	3778.6
15°	7390.8	7423.3	7360.7	6974.4	6613.6	6559.2	6189.1	5769.2	5299.6	4657.6	4183.5
17.5°	8733.7	8682.9	8517.4	7964.5	7530.8	7451.0	7053.1	6503.6	5904.6	5128.4	4506.2
20°	10390.0	10407.3	10056.8	9230.9	8497.7	8186.6	7725.0	7123.7	6376.4	5474.2	4721.3
22.5°	12756.4	12662.7	11910.8	10575.0	9472.7	9057.5	8399.5	7570.1	6729.3	5736.8	4882.1
25°	14913.5	14667.1	13974.4	12136.5	10410.8	9897.3	9216.1	7950.6	7021.9	5931.2	5015.2
27.5°	16152.2	16042.3	15257.0	13402.9	11168.4	10445.4	9486.7	8230.6	7195.3	6027.1	5053.3
30°	16459.9	16479.6	15781.0	13822.8	11347.6	10521.8	9530.6	8222.4	7078.6	5856.0	4833.5
32.5°	16381.2	16274.9	15401.6	13359.0	10870.0	10118.1	9100.3	7854.7	6613.6	5345.9	4286.5
35°	15574.0	15417.8	14343.3	12152.7	10059.1	9328.1	8405.2	7252.0	5964.7	4695.9	3673.4
37.5°	14037.9	13857.5	12617.6	10704.5	9086.4	8467.6	7669.5	6581.1	5308.9	4089.8	3134.5
40°	11903.9	11679.6	10643.3	9316.6	8040.9	7608.3	6934.0	5815.5	4628.8	3516.1	2637.0
42.5°	9908.8	9801.2	9178.9	8040.9	7181.4	6763.8	6083.9	5042.9	3951.1	2929.7	1952.4
45°	8320.7	8249.1	7836.2	7113.3	6241.1	5850.1	5209.4	4193.9	3006.1	1973.2	1016.6
47.5°	7283.2	7100.5	6696.8	5938.1	4968.8	4482.0	3871.2	2763.2	1695.6	874.3	312.3
50°	5023.2	5040.6	4584.8	3748.6	2924.0	2512.2	2074.9	1271.1	560.9	190.8	54.3
52.5°	2645.1	2449.7	2129.4	1590.4	1106.9	844.3	616.5	254.5	101.8	38.2	28.9
55°	720.6	632.6	505.4	357.3	193.1	135.4	89.0	47.4	33.6	26.6	18.5
57.5°	70.5	67.1	61.4	49.8	42.8	39.3	35.8	28.9	23.2	16.2	11.5
60°	39.3	38.2	35.8	31.3	27.8	25.4	23.2	19.7	13.8	10.4	9.2
62.5°	21.9	20.8	19.7	17.3	15.1	13.8	13.8	11.5	9.2	8.1	8.1
65°	10.4	10.4	10.4	10.4	10.4	9.2	8.1	8.1	8.1	8.1	8.1
67.5°	8.1	8.1	8.1	7.0	7.0	7.0	7.0	7.0	7.0	5.7	7.0
70°	4.7	4.7	5.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	5.7
72.5°	2.3	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.7	4.7	5.7
75°	2.3	2.3	2.3	2.3	3.4	3.4	3.4	3.4	4.7	4.7	5.7
77.5°	2.3	2.3	2.3	2.3	2.3	2.3	3.4	3.4	4.7	4.7	5.7
80°	1.1	1.1	1.1	2.3	2.3	2.3	2.3	3.4	4.7	4.7	5.7
82.5°	1.1	1.1	1.1	1.1	2.3	2.3	2.3	3.4	4.7	4.7	5.7
85°	1.1	1.1	1.1	1.1	2.3	2.3	2.3	3.4	3.4	4.7	5.7
87.5°	0.0	0.0	1.1	1.1	2.3	2.3	2.3	3.4	3.4	4.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192664

CATALOG NUMBER: LDA6A65950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7
2.5°	1920.0	1863.3	1806.6	1750.0	1747.6	1714.1	1664.3	1598.5	1544.1	1497.8	1452.7
5°	2315.6	2198.8	2081.9	1965.1	1930.3	1870.2	1762.7	1641.3	1537.2	1445.8	1357.9
7.5°	2712.2	2515.7	2330.6	2147.9	2074.9	1983.6	1815.9	1640.1	1489.7	1355.5	1224.8
10°	3066.1	2780.5	2520.3	2263.6	2158.3	2039.1	1813.6	1590.4	1399.5	1227.2	1060.6
12.5°	3392.4	2994.6	2664.9	2341.0	2197.5	2053.0	1777.7	1511.6	1283.9	1078.0	886.0
15°	3679.2	3191.1	2766.7	2375.8	2199.9	2026.3	1702.5	1403.1	1147.3	911.4	703.1
17.5°	3884.0	3289.5	2800.2	2344.5	2139.8	1945.4	1591.5	1271.1	995.9	749.5	548.3
20°	4008.8	3330.0	2782.8	2286.6	2069.2	1867.9	1509.4	1198.3	931.1	718.2	581.8
22.5°	4090.9	3369.2	2789.8	2285.5	2068.0	1878.3	1544.1	1252.7	1035.1	920.7	904.5
25°	4178.9	3424.7	2840.7	2337.5	2135.1	1959.3	1635.4	1351.0	1169.3	1120.7	1127.7
27.5°	4174.2	3400.5	2792.1	2292.5	2079.6	1901.5	1522.1	1162.4	992.4	855.8	806.2
30°	3925.6	3119.4	2461.4	1901.5	1650.5	1431.9	932.3	606.0	418.7	366.7	314.6
32.5°	3343.8	2527.2	1840.2	1315.1	1032.8	771.5	366.7	194.4	165.5	138.8	126.0
35°	2780.5	2014.8	1376.4	794.7	501.9	311.2	131.9	86.7	82.2	77.5	77.5
37.5°	2298.2	1582.4	889.4	335.4	184.0	112.2	63.6	57.9	55.5	54.3	54.3
40°	1797.4	1031.7	385.2	111.0	59.0	50.9	45.1	42.8	41.7	40.5	41.7
42.5°	1060.6	415.3	112.2	41.7	39.3	37.0	33.6	32.3	32.3	31.3	32.3
45°	360.9	107.5	37.0	30.1	27.8	27.8	25.4	25.4	25.4	24.2	26.6
47.5°	93.7	33.6	24.2	21.9	20.8	20.8	19.7	19.7	19.7	19.7	20.8
50°	32.3	21.9	17.3	16.2	15.1	16.2	15.1	15.1	15.1	15.1	16.2
52.5°	19.7	15.1	12.8	12.8	12.8	12.8	12.8	12.8	12.8	12.8	12.8
55°	12.8	11.5	10.4	10.4	10.4	10.4	10.4	11.5	11.5	11.5	11.5
57.5°	10.4	9.2	9.2	9.2	9.2	9.2	10.4	9.2	9.2	10.4	11.5
60°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.4	10.4	11.5
62.5°	8.1	9.2	9.2	9.2	9.2	9.2	9.2	10.4	10.4	10.4	11.5
65°	8.1	8.1	8.1	9.2	9.2	9.2	10.4	10.4	10.4	11.5	11.5
67.5°	7.0	7.0	8.1	8.1	9.2	9.2	9.2	10.4	10.4	10.4	11.5
70°	7.0	7.0	7.0	8.1	8.1	8.1	8.1	9.2	9.2	10.4	10.4
72.5°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	9.2	9.2	9.2	10.4
75°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	8.1	9.2	9.2	10.4
77.5°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	9.2	9.2	9.2	10.4
80°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2
82.5°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2
85°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2
87.5°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192664

CATALOG NUMBER: LDA6A65950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7
2.5°	1390.3	1370.6	1301.2	1291.9	1280.4	1223.8	1200.6	1161.2	1105.7	1089.6	1069.8
5°	1254.9	1190.2	1088.4	1060.6	1030.6	941.4	887.1	822.3	750.7	711.3	674.3
7.5°	1082.6	992.4	857.1	802.8	769.2	672.0	585.2	498.5	393.3	333.1	294.9
10°	890.6	766.8	625.8	563.3	518.1	377.1	294.9	256.8	220.9	192.1	166.5
12.5°	697.4	557.4	397.8	326.2	290.3	240.6	195.5	148.0	131.9	130.7	126.0
15°	511.3	355.2	268.3	241.7	216.3	155.0	153.8	153.8	158.4	161.9	163.1
17.5°	377.1	312.3	245.2	229.0	240.6	249.8	266.0	290.3	310.0	365.5	353.9
20°	552.9	548.3	598.0	661.6	706.7	802.8	924.1	1061.7	1205.3	1364.8	1486.3
22.5°	948.5	1064.1	1154.3	1230.6	1271.1	1379.9	1475.9	1523.3	1551.1	1537.2	1517.5
25°	1159.0	1200.6	1172.8	1146.3	1149.7	1051.3	979.7	888.4	810.9	740.2	698.7
27.5°	692.8	633.9	550.5	492.8	481.2	415.3	366.7	315.7	300.7	254.5	234.8
30°	249.8	232.5	205.9	185.0	182.7	165.5	155.0	143.5	142.3	131.9	126.0
32.5°	113.4	113.4	104.1	106.4	104.1	100.7	99.4	96.0	96.0	92.6	90.3
35°	74.0	75.2	74.0	74.0	72.8	72.8	72.8	70.5	71.8	69.4	65.9
37.5°	54.3	55.5	53.2	54.3	54.3	54.3	54.3	53.2	52.0	49.8	48.6
40°	41.7	41.7	41.7	41.7	41.7	41.7	41.7	40.5	40.5	39.3	37.0
42.5°	32.3	33.6	33.6	33.6	33.6	33.6	33.6	33.6	33.6	32.3	32.3
45°	26.6	27.8	26.6	27.8	27.8	27.8	26.6	26.6	26.6	25.4	24.2
47.5°	20.8	20.8	19.7	19.7	19.7	19.7	19.7	19.7	19.7	19.7	18.5
50°	16.2	16.2	16.2	16.2	16.2	16.2	17.3	16.2	16.2	16.2	16.2
52.5°	12.8	13.8	13.8	15.1	15.1	15.1	15.1	15.1	13.8	13.8	12.8
55°	11.5	12.8	12.8	13.8	13.8	13.8	13.8	12.8	12.8	12.8	11.5
57.5°	11.5	12.8	12.8	12.8	12.8	12.8	12.8	11.5	11.5	10.4	10.4
60°	11.5	11.5	11.5	12.8	12.8	11.5	11.5	10.4	10.4	9.2	9.2
62.5°	11.5	11.5	11.5	12.8	12.8	11.5	11.5	10.4	9.2	9.2	8.1
65°	11.5	12.8	11.5	12.8	12.8	11.5	11.5	10.4	9.2	9.2	8.1
67.5°	11.5	12.8	12.8	12.8	11.5	11.5	11.5	10.4	9.2	9.2	8.1
70°	10.4	11.5	11.5	11.5	11.5	11.5	10.4	10.4	9.2	9.2	8.1
72.5°	10.4	11.5	10.4	11.5	11.5	10.4	10.4	10.4	9.2	9.2	8.1
75°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1
77.5°	10.4	10.4	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1	8.1
80°	10.4	10.4	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1	7.0
82.5°	9.2	10.4	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1	7.0
85°	9.2	9.2	9.2	9.2	9.2	9.2	8.1	8.1	7.0	5.7	5.7
87.5°	8.1	9.2	8.1	8.1	8.1	8.1	7.0	5.7	4.7	4.7	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192664

CATALOG NUMBER: LDA6A65950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7	1526.7
2.5°	1038.6	1009.7	1010.9	1015.6	986.5	971.6	968.0	953.1
5°	624.5	591.0	585.2	580.6	540.2	524.0	511.3	527.5
7.5°	268.3	255.5	253.3	249.8	231.3	222.0	217.5	222.0
10°	133.0	125.0	126.0	127.2	121.4	117.9	116.9	115.6
12.5°	131.9	130.7	131.9	131.9	133.0	130.7	131.9	131.9
15°	171.2	171.2	174.6	177.0	182.7	181.6	184.0	186.3
17.5°	426.7	404.8	416.3	416.3	468.4	422.2	461.4	425.7
20°	1677.1	1755.7	1835.6	1902.7	1970.9	1991.7	2032.2	2020.6
22.5°	1487.4	1496.7	1485.1	1472.4	1468.9	1472.4	1409.9	1419.2
25°	638.5	633.9	615.4	595.6	601.4	606.0	584.1	563.3
27.5°	218.6	212.8	207.0	202.5	200.1	196.6	189.7	185.0
30°	123.8	120.3	117.9	116.9	114.5	112.2	108.8	106.4
32.5°	89.0	86.7	85.6	84.4	82.2	79.9	76.2	75.2
35°	65.9	63.6	62.4	61.4	59.0	56.7	55.5	54.3
37.5°	48.6	46.3	46.3	46.3	42.8	40.5	39.3	38.2
40°	37.0	35.8	35.8	35.8	33.6	32.3	31.3	31.3
42.5°	32.3	31.3	31.3	31.3	28.9	27.8	27.8	26.6
45°	24.2	23.2	23.2	21.9	20.8	20.8	19.7	18.5
47.5°	18.5	17.3	17.3	17.3	16.2	15.1	15.1	13.8
50°	15.1	15.1	13.8	15.1	12.8	12.8	12.8	11.5
52.5°	12.8	12.8	11.5	11.5	10.4	10.4	10.4	9.2
55°	11.5	10.4	10.4	10.4	9.2	9.2	9.2	8.1
57.5°	9.2	9.2	8.1	8.1	7.0	7.0	7.0	7.0
60°	8.1	8.1	7.0	7.0	5.7	5.7	5.7	5.7
62.5°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
65°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
67.5°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
70°	8.1	8.1	7.0	7.0	7.0	5.7	5.7	5.7
72.5°	8.1	8.1	7.0	7.0	7.0	7.0	5.7	5.7
75°	7.0	7.0	7.0	7.0	5.7	5.7	5.7	5.7
77.5°	7.0	7.0	7.0	7.0	5.7	5.7	5.7	5.7
80°	7.0	7.0	5.7	5.7	5.7	5.7	5.7	5.7
82.5°	7.0	5.7	5.7	5.7	5.7	4.7	4.7	4.7
85°	4.7	4.7	4.7	4.7	3.4	3.4	3.4	3.4
87.5°	3.4	2.3	2.3	2.3	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)