

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192667

Luminaire Tested: **LDA6A65950D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192667
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A65950D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6361.5 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 66.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192667

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192667

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	62901	62901	62901
5°	161369	57225	17824
10°	314551	43982	8567
15°	564657	29870	11493
20°	838329	22670	18966
25°	952894	18685	29736
30°	1032950	20427	27966
35°	1088035	13237	17346
40°	1111554	5882	8437
45°	1003957	2241	3140
50°	660874	887	887
55°	180973	774	0
60°	36148	888	0
65°	2555	1193	0
70°	369	1475	0
75°	0	2203	0
80°	0	3283	347
85°	0	6542	692

TEST NUMBER: P1192667

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.6	2.2
10°-20°	746.8	11.7
20°-30°	1692.5	26.6
30°-40°	2031.6	31.9
40°-50°	1431.8	22.5
50°-60°	295.4	4.6
60°-70°	10.4	0.2
70°-80°	6.2	0.1
80°-90°	6.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2579.9	40.6
0°-40°	4611.5	72.5
0°-60°	6338.8	99.6
0°-90°	6361.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6361.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1147	1147	1147	1147	1147	
5°	2932	2136	1040	433	324	361
15°	9949	4377	526	187	202	2953
25°	15754	5294	309	433	492	7270
35°	16258	3707	198	259	259	10107
45°	12950	1271	29	39	40	9524
55°	1894	26	8	6	0	2495
65°	20	6	9	6	0	58
75°	0	6	10	7	0	0
85°	0	7	10	7	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192667

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4
2.5°	1956.0	1897.1	1920.2	1851.9	1836.8	1824.2	1836.8	1762.8	1721.2	1668.1	1625.2
5°	2932.4	2861.9	2878.0	2758.8	2704.5	2667.5	2660.4	2507.8	2393.2	2267.2	2136.5
7.5°	4082.1	4015.0	4005.8	3820.6	3708.4	3644.8	3618.3	3399.7	3201.8	2977.4	2732.2
10°	5650.7	5498.0	5450.5	5182.2	4968.2	4832.9	4666.4	4316.9	3969.9	3631.0	3318.6
12.5°	7476.0	7392.6	7274.7	6801.6	6426.8	6234.8	5986.1	5440.1	4915.0	4355.1	3832.3
15°	9949.2	9653.0	9451.7	8768.0	8164.2	7868.1	7504.8	6669.7	5876.2	5167.1	4377.0
17.5°	12365.6	12210.5	11895.9	11008.6	10078.6	9611.3	9069.9	7935.2	6814.3	5805.7	4841.0
20°	14370.1	14224.4	13865.8	13029.5	11997.6	11308.2	10626.9	9069.9	7605.5	6314.6	5151.0
22.5°	15330.2	15237.7	14945.1	14229.1	13350.0	12693.9	11961.9	10035.8	8190.8	6647.8	5292.1
25°	15753.6	15710.8	15522.2	14957.7	14129.4	13573.1	12881.4	10719.5	8555.1	6802.8	5294.3
27.5°	16182.8	16190.9	15774.4	15327.9	14542.5	14008.1	13341.8	11022.5	8621.2	6716.0	5121.0
30°	16318.1	16232.4	16048.6	15407.8	14661.7	14093.7	13378.9	10882.6	8350.5	6359.7	4775.0
32.5°	16262.5	16229.0	16026.6	15348.8	14459.2	13833.5	13021.4	10327.3	7816.1	5850.8	4284.6
35°	16258.0	16195.4	15731.7	15149.8	14054.4	13281.6	12211.7	9429.7	7059.6	5179.9	3707.4
37.5°	15964.1	15809.1	15461.0	14676.7	13233.1	12253.4	11053.7	8333.1	6134.2	4426.9	3134.8
40°	15532.6	15324.4	14866.4	13679.5	11810.3	10681.3	9510.7	7087.3	5154.4	3684.2	2526.3
42.5°	14631.6	14317.0	13669.1	12037.1	9914.4	8896.5	7922.5	5825.4	4203.6	3001.8	1928.3
45°	12949.7	12519.3	11643.7	9851.9	8009.2	7178.7	6395.6	4687.1	3365.0	2226.7	1271.3
47.5°	10408.2	10009.3	9212.2	7842.7	6281.1	5579.0	4954.2	3486.4	2281.0	1289.7	607.3
50°	7749.0	7406.7	6784.2	5450.5	4216.3	3664.5	3130.2	1980.4	1068.8	613.1	252.1
52.5°	4623.5	4453.5	3901.8	3022.6	2082.2	1794.1	1440.2	838.7	539.0	222.0	68.3
55°	1893.5	1747.8	1540.8	1236.6	905.7	768.0	657.1	414.1	167.8	46.3	25.5
57.5°	855.9	823.6	729.9	573.8	416.4	349.3	236.0	78.6	37.0	23.2	15.1
60°	329.7	297.2	254.5	137.6	59.0	49.8	40.5	26.6	18.5	12.8	9.2
62.5°	47.4	45.1	40.5	32.3	25.5	23.2	19.7	13.8	10.4	8.1	7.0
65°	19.7	19.7	17.3	13.8	11.5	10.4	9.2	7.0	5.7	5.7	5.7
67.5°	8.1	8.1	7.0	5.7	4.7	4.7	4.7	3.4	4.7	4.7	5.7
70°	2.3	2.3	2.3	2.3	2.3	2.3	3.4	3.4	4.7	4.7	5.7
72.5°	0.0	0.0	1.1	1.1	2.3	2.3	2.3	3.4	4.7	5.7	5.7
75°	0.0	0.0	1.1	1.1	2.3	2.3	2.3	3.4	4.7	5.7	5.7
77.5°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
80°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	7.0
82.5°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	7.0
85°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	7.0
87.5°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192667

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4
2.5°	1588.2	1514.1	1493.4	1428.5	1374.2	1347.6	1314.1	1238.8	1182.2	1107.0	1061.8
5°	2045.2	1905.2	1794.1	1658.7	1569.7	1512.0	1421.7	1284.0	1172.9	1039.9	945.2
7.5°	2539.1	2283.4	2083.2	1860.0	1731.7	1631.0	1477.2	1279.4	1116.3	939.2	792.3
10°	3015.6	2633.9	2319.3	1998.9	1830.0	1690.0	1478.4	1229.6	1013.3	790.1	635.1
12.5°	3435.5	2942.8	2499.7	2087.9	1878.6	1703.8	1438.9	1140.6	879.1	650.1	513.6
15°	3786.0	3182.2	2626.9	2121.5	1882.0	1673.8	1356.9	1013.3	729.9	526.3	430.4
17.5°	4052.0	3308.3	2666.2	2080.9	1814.9	1588.2	1230.7	852.5	592.3	446.5	362.0
20°	4189.6	3332.6	2609.6	1971.0	1691.1	1458.7	1065.4	691.7	502.0	388.6	303.1
22.5°	4207.1	3264.4	2474.3	1813.8	1534.9	1301.4	882.5	577.2	447.6	343.6	267.2
25°	4104.0	3116.3	2281.0	1635.6	1363.8	1120.8	718.3	517.0	407.2	308.9	307.6
27.5°	3884.3	2861.9	2049.7	1428.5	1156.8	911.6	609.6	467.4	363.3	327.3	348.2
30°	3574.3	2535.5	1765.2	1167.2	903.4	701.0	513.6	385.2	319.2	322.7	340.1
32.5°	3154.4	2130.8	1430.8	854.9	646.7	527.5	385.2	262.6	264.9	266.1	281.1
35°	2626.9	1708.5	1068.8	574.9	454.6	371.3	217.5	193.1	196.7	197.8	208.2
37.5°	2105.3	1312.9	710.3	382.8	285.7	195.5	135.4	129.5	131.9	130.7	142.3
40°	1612.5	915.0	425.7	189.7	109.9	91.3	83.3	79.9	80.9	82.2	89.0
42.5°	1141.7	496.3	210.6	71.8	57.9	53.2	49.8	47.4	48.6	48.6	53.2
45°	579.6	234.8	71.8	39.3	35.8	32.3	30.1	28.9	28.9	28.9	31.3
47.5°	251.1	77.5	33.6	24.2	21.9	20.8	18.5	17.3	17.3	17.3	18.5
50°	78.6	31.3	20.8	16.2	13.8	12.8	11.5	11.5	11.5	10.4	11.5
52.5°	28.9	19.7	13.8	10.4	9.2	9.2	9.2	8.1	9.2	8.1	9.2
55°	17.3	12.8	9.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
57.5°	11.5	9.2	8.1	8.1	7.0	7.0	8.1	8.1	8.1	8.1	8.1
60°	8.1	8.1	7.0	7.0	7.0	7.0	8.1	8.1	8.1	8.1	8.1
62.5°	7.0	7.0	7.0	7.0	7.0	7.0	8.1	8.1	8.1	8.1	9.2
65°	5.7	7.0	7.0	7.0	7.0	7.0	8.1	8.1	9.2	9.2	9.2
67.5°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2
70°	7.0	7.0	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2	10.4
72.5°	7.0	7.0	8.1	8.1	8.1	8.1	9.2	9.2	10.4	10.4	10.4
75°	7.0	8.1	8.1	8.1	8.1	9.2	9.2	9.2	10.4	10.4	10.4
77.5°	7.0	8.1	8.1	9.2	9.2	9.2	9.2	10.4	10.4	10.4	10.4
80°	7.0	8.1	8.1	9.2	9.2	9.2	10.4	10.4	10.4	10.4	11.5
82.5°	7.0	8.1	8.1	9.2	9.2	9.2	10.4	10.4	10.4	10.4	11.5
85°	8.1	8.1	9.2	9.2	9.2	9.2	10.4	10.4	10.4	10.4	11.5
87.5°	8.1	8.1	9.2	9.2	9.2	9.2	10.4	10.4	11.5	10.4	11.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192667

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4
2.5°	1001.7	934.6	888.4	871.0	837.4	784.3	753.1	724.2	669.8	658.1	628.2
5°	836.4	728.8	652.4	623.5	585.3	540.2	496.3	467.4	432.6	418.8	397.9
7.5°	659.4	551.7	485.9	462.7	436.1	399.0	359.8	330.8	294.9	276.4	259.2
10°	518.2	438.4	382.8	359.8	332.0	292.6	252.1	214.0	182.7	163.1	159.6
12.5°	421.1	355.2	296.2	271.9	239.5	200.1	171.2	170.0	167.8	166.5	168.9
15°	344.8	281.1	218.6	192.1	182.7	181.6	185.0	188.6	187.4	190.8	193.1
17.5°	283.4	215.1	201.2	202.5	203.5	207.0	212.9	222.0	223.3	229.1	233.6
20°	231.4	227.9	233.6	238.3	241.7	248.7	261.5	273.0	276.4	284.5	293.8
22.5°	262.6	273.0	285.7	291.5	296.2	308.9	322.7	341.3	348.2	358.6	371.3
25°	317.0	334.3	353.9	360.9	367.8	388.6	404.8	426.9	432.6	445.4	458.0
27.5°	362.0	380.5	401.3	410.7	416.4	437.3	451.2	465.0	465.0	472.0	481.2
30°	355.2	370.1	387.5	394.5	396.8	411.8	425.7	430.4	428.0	431.4	438.4
32.5°	294.9	306.6	320.4	326.2	328.5	338.9	350.5	350.5	349.3	349.3	353.9
35°	218.6	226.7	233.6	239.5	242.9	249.8	260.2	259.2	259.2	256.8	260.2
37.5°	147.0	151.5	159.6	162.0	163.1	167.8	175.9	175.9	173.5	174.6	177.0
40°	89.0	94.8	99.4	100.7	103.0	106.4	112.2	112.2	112.2	112.2	113.4
42.5°	53.2	56.7	60.2	60.2	61.4	65.9	68.3	68.3	68.3	68.3	69.4
45°	31.3	32.3	34.7	35.8	35.8	38.2	39.3	39.3	39.3	39.3	40.5
47.5°	18.5	19.7	19.7	20.8	20.8	21.9	23.2	23.2	21.9	21.9	21.9
50°	11.5	11.5	11.5	11.5	12.8	12.8	12.8	12.8	12.8	12.8	11.5
52.5°	9.2	9.2	9.2	9.2	8.1	8.1	8.1	8.1	7.0	7.0	5.7
55°	8.1	8.1	8.1	8.1	8.1	7.0	7.0	7.0	5.7	4.7	3.4
57.5°	8.1	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	4.7	3.4
60°	8.1	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	4.7	3.4
62.5°	9.2	9.2	8.1	8.1	8.1	7.0	7.0	5.7	5.7	4.7	3.4
65°	9.2	9.2	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	3.4
67.5°	9.2	9.2	9.2	9.2	8.1	8.1	8.1	7.0	5.7	4.7	3.4
70°	10.4	10.4	9.2	9.2	9.2	8.1	8.1	7.0	5.7	5.7	4.7
72.5°	10.4	10.4	9.2	9.2	9.2	9.2	8.1	7.0	7.0	5.7	4.7
75°	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1	7.0	5.7	4.7
77.5°	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1	7.0	5.7	4.7
80°	10.4	10.4	10.4	10.4	10.4	9.2	9.2	8.1	7.0	5.7	4.7
82.5°	11.5	11.5	10.4	10.4	10.4	9.2	9.2	8.1	7.0	5.7	5.7
85°	11.5	11.5	10.4	10.4	10.4	9.2	9.2	8.1	7.0	7.0	5.7
87.5°	11.5	11.5	10.4	10.4	10.4	9.2	9.2	8.1	7.0	7.0	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192667

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4	1147.4
2.5°	609.6	574.9	563.4	571.5	562.1	555.3	546.0	541.4
5°	381.8	356.2	348.2	350.5	342.4	335.4	326.2	323.9
7.5°	234.8	210.6	201.2	201.2	192.1	184.0	178.2	174.6
10°	157.4	152.7	153.9	155.0	153.9	155.0	151.5	153.9
12.5°	168.9	166.5	168.9	170.0	170.0	172.3	167.8	171.2
15°	196.7	194.4	197.8	200.1	200.1	203.5	199.0	202.5
17.5°	240.6	239.5	245.2	247.6	248.7	254.5	248.7	253.3
20°	304.2	303.1	311.2	314.7	313.5	325.1	317.0	325.1
22.5°	386.4	384.1	395.6	399.0	400.3	415.3	408.4	414.1
25°	468.4	470.8	476.5	482.4	483.5	496.3	485.9	491.6
27.5°	485.9	482.4	485.9	492.8	494.0	499.7	490.4	495.0
30°	439.5	433.8	434.9	443.0	445.4	447.6	439.5	441.8
32.5°	357.4	348.2	348.2	356.2	358.6	362.0	348.2	353.9
35°	263.7	255.6	255.6	261.5	262.6	264.9	254.5	259.2
37.5°	180.5	173.5	175.9	178.2	179.3	181.6	180.5	179.3
40°	115.6	111.1	114.5	114.5	115.6	116.9	116.9	117.9
42.5°	70.5	67.1	69.4	69.4	70.5	70.5	70.5	71.8
45°	40.5	39.3	39.3	40.5	40.5	40.5	39.3	40.5
47.5°	21.9	20.8	21.9	21.9	21.9	21.9	21.9	21.9
50°	11.5	10.4	10.4	10.4	10.4	10.4	10.4	10.4
52.5°	5.7	4.7	4.7	4.7	3.4	4.7	3.4	3.4
55°	3.4	2.3	2.3	2.3	1.1	1.1	0.0	0.0
57.5°	2.3	1.1	1.1	1.1	0.0	0.0	0.0	0.0
60°	2.3	1.1	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.3	1.1	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.3	1.1	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.4	2.3	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.4	2.3	2.3	1.1	1.1	0.0	0.0	0.0
72.5°	3.4	2.3	2.3	2.3	1.1	1.1	0.0	0.0
75°	3.4	2.3	2.3	2.3	1.1	1.1	0.0	0.0
77.5°	3.4	3.4	2.3	2.3	1.1	1.1	1.1	0.0
80°	4.7	3.4	2.3	2.3	2.3	1.1	1.1	1.1
82.5°	4.7	3.4	2.3	2.3	2.3	1.1	1.1	1.1
85°	4.7	3.4	3.4	2.3	2.3	1.1	1.1	1.1
87.5°	4.7	3.4	3.4	2.3	2.3	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)