

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192672

Luminaire Tested: **LDA6A65950D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192672
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26684)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A65950D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4767.7 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 2.21 / 1.07 / 1.54
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 66.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192672

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192672

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	61		
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54		
6	77	65	57	51	75	64	57	51	62	56	51	61	55	50	59	54	50	48		
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35		
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	75213	75213	75213
5°	119486	74284	48250
10°	179272	71286	32392
15°	256897	67560	23962
20°	339115	63163	19975
25°	407026	61576	29185
30°	454798	61725	44083
35°	467585	55272	37624
40°	450594	43954	27974
45°	397111	32647	21529
50°	309687	24170	14891
55°	179110	17682	9625
60°	83710	12302	4309
65°	39161	6745	1790
70°	18176	2965	1298
75°	7583	1949	1483
80°	3283	2210	1799
85°	692	3585	2956

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192672

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.9	3.0
10°-20°	520.8	10.9
20°-30°	1031.0	21.6
30°-40°	1333.0	28.0
40°-50°	1095.4	23.0
50°-60°	506.4	10.6
60°-70°	115.6	2.4
70°-80°	18.9	0.4
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1693.6	35.5
0°-40°	3026.6	63.5
0°-60°	4628.4	97.1
0°-90°	4767.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4767.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1372	1372	1372	1372	1372	
5°	2171	1867	1350	976	877	240
15°	4526	3027	1190	533	422	1322
25°	6729	3766	1018	500	482	3098
35°	6987	3447	826	548	562	4326
45°	5122	2327	421	280	278	3898
55°	1874	906	185	119	101	1761
65°	302	185	52	20	14	346
75°	36	21	9	8	7	48
85°	1	3	6	6	5	3
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192672

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0
2.5°	1742.1	1715.5	1731.7	1739.7	1698.2	1707.4	1712.0	1679.7	1670.3	1653.1	1602.1
5°	2171.3	2140.0	2152.8	2152.8	2091.4	2094.9	2092.7	2031.3	1997.7	1953.8	1867.0
7.5°	2676.8	2645.7	2647.8	2636.3	2549.6	2543.7	2506.8	2431.5	2365.7	2284.6	2155.1
10°	3220.5	3202.0	3190.4	3161.5	3047.0	3027.3	2972.9	2853.9	2745.1	2621.2	2438.5
12.5°	3859.0	3822.0	3788.5	3742.1	3592.9	3555.9	3479.6	3307.2	3147.7	2974.1	2732.3
15°	4526.5	4497.6	4443.3	4370.3	4179.4	4120.5	4021.1	3789.7	3590.6	3337.4	3027.3
17.5°	5217.1	5163.9	5084.1	4981.1	4750.9	4667.6	4543.8	4247.7	3984.0	3668.1	3293.4
20°	5812.9	5771.2	5661.3	5528.3	5264.5	5153.5	5007.7	4644.5	4321.7	3947.0	3506.3
22.5°	6330.0	6274.3	6139.1	5978.2	5683.3	5545.6	5381.4	4975.4	4582.0	4147.1	3662.4
25°	6729.1	6687.4	6526.6	6339.2	6015.3	5855.7	5674.0	5213.6	4777.6	4299.8	3766.5
27.5°	7054.0	6983.5	6804.2	6592.5	6243.2	6057.0	5864.9	5360.5	4888.5	4377.3	3805.8
30°	7184.7	7111.9	6922.2	6687.4	6317.2	6112.5	5914.7	5376.7	4880.4	4350.6	3758.4
32.5°	7160.5	7078.3	6876.0	6627.2	6248.9	6030.3	5830.2	5271.4	4764.8	4230.4	3630.0
35°	6986.9	6918.8	6709.4	6449.1	6072.0	5841.7	5632.4	5079.5	4571.6	4044.1	3447.3
37.5°	6725.5	6628.4	6432.9	6171.5	5772.3	5558.3	5351.3	4805.2	4308.9	3786.2	3219.3
40°	6296.5	6179.6	5984.1	5756.1	5376.7	5163.9	4975.4	4465.2	3977.1	3488.8	2947.6
42.5°	5756.1	5664.8	5483.2	5248.4	4900.2	4696.6	4527.6	4037.2	3604.5	3152.2	2647.8
45°	5122.2	5034.3	4879.4	4667.6	4353.0	4176.0	4021.1	3584.9	3195.0	2782.1	2327.4
47.5°	4436.2	4349.6	4214.2	4027.9	3746.8	3594.1	3458.7	3101.3	2733.5	2372.6	1973.5
50°	3631.2	3512.0	3437.9	3281.8	3047.0	2917.4	2813.3	2492.8	2221.0	1930.7	1598.7
52.5°	2710.3	2672.2	2565.8	2455.9	2290.5	2194.5	2126.2	1920.3	1694.8	1484.2	1230.8
55°	1874.0	1839.3	1774.4	1707.4	1596.4	1547.8	1496.9	1372.0	1221.5	1078.2	905.7
57.5°	1184.6	1210.0	1168.3	1130.2	1063.1	1045.8	1006.4	933.6	840.9	750.8	643.2
60°	763.5	777.4	750.8	728.8	691.7	677.9	659.4	615.4	559.9	507.8	434.9
62.5°	483.5	490.5	475.5	462.7	441.8	436.1	423.4	397.9	364.3	333.2	286.8
65°	301.9	307.6	297.2	289.1	276.5	277.7	266.1	251.1	231.4	211.6	185.0
67.5°	186.3	189.7	182.7	178.2	170.0	170.0	163.1	153.9	141.1	129.6	112.2
70°	113.4	114.5	109.9	107.5	101.8	100.7	97.1	90.3	82.2	74.0	63.6
72.5°	65.9	67.1	63.6	61.4	57.9	57.9	55.5	52.0	48.6	41.7	35.8
75°	35.8	37.0	34.7	33.6	31.3	32.3	30.1	28.9	25.5	23.2	20.8
77.5°	18.5	19.7	18.5	17.3	17.3	17.3	16.2	15.1	15.1	12.8	12.8
80°	10.4	10.4	10.4	10.4	10.4	9.2	9.2	9.2	9.2	9.2	8.1
82.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	4.7
85°	1.1	1.1	2.3	2.3	2.3	2.3	2.3	2.3	2.3	3.4	3.4
87.5°	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.3	2.3	2.3	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192672

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0
2.5°	1587.0	1586.0	1532.8	1509.6	1491.0	1462.1	1441.4	1419.3	1399.7	1363.9	1333.7
5°	1823.1	1790.8	1702.8	1647.3	1612.6	1566.2	1515.4	1464.4	1414.8	1349.9	1296.8
7.5°	2070.6	2001.2	1869.4	1776.8	1723.6	1658.8	1573.2	1493.4	1412.4	1323.4	1247.1
10°	2306.6	2193.3	2025.5	1884.5	1811.5	1728.3	1610.2	1499.2	1392.9	1280.6	1185.7
12.5°	2547.3	2385.2	2166.6	1983.9	1891.3	1788.4	1636.9	1499.2	1367.3	1237.7	1125.5
15°	2785.5	2571.5	2299.6	2072.9	1960.7	1838.1	1655.4	1491.0	1336.1	1190.4	1065.4
17.5°	2989.1	2724.2	2396.8	2134.3	2002.4	1863.6	1654.1	1466.8	1294.5	1137.1	1004.1
20°	3147.7	2834.1	2465.1	2165.5	2017.4	1866.0	1635.6	1430.9	1247.1	1082.7	946.2
22.5°	3255.2	2905.9	2499.8	2171.3	2012.8	1853.2	1606.8	1395.1	1204.2	1039.9	903.4
25°	3322.3	2941.6	2510.2	2163.2	1996.7	1831.2	1580.2	1363.9	1176.6	1018.0	890.8
27.5°	3335.1	2931.3	2489.3	2129.6	1958.4	1791.8	1541.9	1333.7	1152.1	1005.2	890.8
30°	3272.5	2864.2	2418.8	2054.4	1886.7	1723.6	1478.5	1279.4	1109.3	975.1	871.0
32.5°	3153.4	2740.4	2302.0	1943.4	1780.4	1627.6	1391.6	1201.9	1037.7	913.8	820.1
35°	2981.1	2574.9	2150.4	1803.4	1645.0	1502.7	1270.2	1096.7	940.5	825.9	739.2
37.5°	2771.7	2376.1	1973.5	1643.7	1493.4	1360.3	1138.3	975.1	830.5	723.0	645.5
40°	2517.2	2160.9	1774.4	1468.0	1324.5	1204.2	999.4	842.1	705.6	614.2	543.7
42.5°	2251.1	1920.3	1562.8	1271.3	1144.0	1029.5	847.9	706.8	585.3	510.1	454.6
45°	1976.9	1653.1	1340.7	1081.6	985.6	857.2	689.4	574.9	476.5	421.1	377.1
47.5°	1668.2	1393.9	1105.8	878.1	777.4	690.7	550.6	458.1	394.5	345.9	312.3
50°	1336.1	1117.4	875.7	681.3	598.1	532.1	429.2	365.6	317.0	283.4	258.0
52.5°	1027.3	854.9	659.4	499.7	447.7	397.9	334.3	290.4	255.6	230.2	211.6
55°	763.5	623.5	474.3	370.2	333.2	300.8	262.6	227.9	202.5	185.0	170.0
57.5°	537.9	434.9	333.2	268.3	248.7	227.9	199.1	175.9	158.4	144.6	133.0
60°	359.8	296.2	234.8	196.7	182.7	168.9	150.4	134.2	121.4	112.2	100.7
62.5°	241.8	199.1	164.3	141.1	131.9	122.6	109.9	98.4	89.0	79.9	70.5
65°	155.0	131.9	111.1	96.0	89.0	84.4	75.2	67.1	60.2	52.0	45.1
67.5°	95.0	82.2	69.4	60.2	56.7	53.2	47.4	41.7	37.0	31.3	26.6
70°	55.5	48.6	41.7	35.8	34.7	32.3	27.8	24.2	21.9	18.5	16.2
72.5°	32.3	28.9	24.2	21.9	20.8	18.5	17.3	15.1	12.8	11.5	10.4
75°	18.5	16.2	13.8	12.8	12.8	11.5	10.4	10.4	9.2	9.2	8.1
77.5°	11.5	10.4	9.2	9.2	9.2	8.1	8.1	8.1	8.1	7.0	7.0
80°	8.1	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
82.5°	4.7	4.7	4.7	4.7	4.7	5.7	5.7	5.7	5.7	5.7	7.0
85°	3.4	4.7	4.7	4.7	4.7	4.7	5.7	5.7	5.7	5.7	5.7
87.5°	3.4	4.7	4.7	4.7	4.7	4.7	5.7	5.7	5.7	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192672

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0
2.5°	1316.4	1297.9	1241.2	1260.9	1225.1	1196.1	1193.8	1176.6	1146.4	1130.2	1122.1
5°	1256.2	1214.6	1145.2	1149.9	1108.2	1063.1	1038.8	1015.7	976.4	952.0	935.8
7.5°	1182.3	1125.5	1043.4	1037.7	993.7	939.3	904.6	872.2	829.5	798.2	778.5
10°	1104.8	1035.3	939.3	932.4	886.1	827.1	787.8	750.8	706.8	675.6	654.7
12.5°	1033.0	953.2	857.2	839.8	794.8	734.6	691.7	652.4	609.6	583.0	558.7
15°	964.7	878.1	776.3	760.0	716.0	655.9	608.5	573.8	533.3	507.8	485.9
17.5°	896.6	807.4	706.8	688.3	646.7	588.7	547.1	510.1	473.1	448.9	429.2
20°	837.5	748.4	650.1	631.6	593.4	537.9	499.7	465.0	431.5	408.4	392.2
22.5°	799.3	712.6	623.5	607.3	571.5	521.7	485.9	455.8	426.9	404.9	392.2
25°	797.0	721.8	642.0	632.7	602.7	561.1	535.6	517.1	499.7	482.5	477.8
27.5°	811.0	749.6	682.6	680.3	655.9	628.2	616.6	610.8	601.5	595.7	603.8
30°	802.9	750.8	694.1	694.1	675.6	655.9	650.1	647.8	642.0	643.2	652.4
32.5°	760.0	712.6	658.1	659.4	647.8	625.8	622.3	621.2	614.2	613.2	620.0
35°	682.6	638.6	593.4	594.7	585.3	564.5	559.9	557.5	548.3	543.7	548.3
37.5°	593.4	557.5	514.8	514.8	505.4	489.3	484.6	480.1	474.3	469.7	469.7
40°	502.0	473.1	438.4	437.3	430.4	414.1	409.4	406.0	400.3	392.2	394.5
42.5°	424.5	397.9	370.2	367.8	363.3	349.3	344.8	340.1	334.3	327.4	327.4
45°	352.8	335.5	311.3	310.0	305.3	293.8	290.4	284.6	280.0	273.0	273.0
47.5°	293.8	280.0	260.2	259.2	255.6	245.2	241.8	237.1	232.5	227.9	227.9
50°	246.4	232.5	216.3	215.2	212.9	204.8	200.1	196.7	193.1	189.7	187.4
52.5°	202.5	190.8	178.2	177.0	174.6	166.5	163.1	160.8	157.4	151.5	151.5
55°	163.1	153.9	142.3	141.1	138.8	131.9	128.4	123.8	119.2	113.4	112.2
57.5°	127.3	119.2	109.9	108.8	105.2	99.4	93.7	89.0	84.4	79.9	77.5
60°	96.0	86.7	78.6	76.4	74.0	65.9	61.4	56.7	52.0	48.6	46.3
62.5°	64.8	59.0	49.8	48.6	46.3	41.7	35.8	33.6	31.3	28.9	27.8
65°	40.5	35.8	31.3	30.1	27.8	24.2	21.9	20.8	19.7	18.5	17.3
67.5°	24.2	21.9	18.5	18.5	17.3	16.2	13.8	13.8	12.8	12.8	11.5
70°	15.1	13.8	12.8	11.5	11.5	11.5	10.4	10.4	10.4	10.4	10.4
72.5°	10.4	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2
75°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
77.5°	8.1	8.1	7.0	8.1	8.1	8.1	8.1	7.0	8.1	7.0	7.0
80°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
82.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	5.7	5.7	5.7	5.7
85°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	4.7
87.5°	5.7	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192672

CATALOG NUMBER: LDA6A65950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0	1372.0
2.5°	1124.3	1092.0	1104.8	1086.3	1080.5	1075.9	1068.8	1090.8
5°	928.9	894.2	902.3	883.8	875.7	867.6	859.6	876.8
7.5°	766.9	733.4	736.8	720.7	712.6	703.2	695.2	709.2
10°	640.8	609.6	610.8	595.7	587.6	578.4	571.5	581.9
12.5°	544.9	515.9	515.9	504.4	497.4	486.9	481.2	489.3
15°	472.0	446.5	446.5	434.9	429.2	419.8	414.1	422.2
17.5°	416.4	393.3	393.3	385.2	379.4	371.3	366.7	373.7
20°	379.4	359.8	360.9	352.8	348.2	338.9	336.6	342.4
22.5°	382.8	364.3	366.7	360.9	356.2	349.3	347.0	355.2
25°	478.9	465.0	473.1	473.1	475.5	465.0	469.7	482.5
27.5°	615.4	608.5	621.2	616.6	625.8	625.8	630.4	646.7
30°	665.2	659.4	673.2	672.2	681.3	679.0	681.3	696.4
32.5°	629.3	623.5	635.1	633.9	640.8	635.1	636.2	649.0
35°	553.0	547.1	555.3	554.0	558.7	551.8	555.3	562.2
37.5°	472.0	466.2	470.8	469.7	470.8	462.7	467.4	470.8
40°	396.9	389.8	396.9	392.2	393.3	385.2	386.4	390.9
42.5°	332.0	323.9	329.7	329.7	329.7	323.9	325.1	329.7
45°	276.5	270.6	274.2	273.0	274.2	269.6	273.0	277.7
47.5°	229.1	224.4	226.7	225.5	225.5	221.0	222.0	222.0
50°	188.6	184.0	185.0	184.0	180.5	174.6	173.5	174.6
52.5°	149.2	143.5	143.5	141.1	138.8	134.2	134.2	135.4
55°	109.9	105.2	105.2	104.1	101.8	98.4	98.4	100.7
57.5°	74.0	70.5	71.8	70.5	70.5	65.9	68.3	68.3
60°	45.1	42.8	42.8	41.7	39.3	38.2	37.0	39.3
62.5°	26.6	25.5	25.5	24.2	24.2	23.2	23.2	23.2
65°	17.3	16.2	16.2	15.1	15.1	13.8	12.8	13.8
67.5°	11.5	10.4	10.4	10.4	10.4	9.2	9.2	9.2
70°	10.4	9.2	9.2	9.2	9.2	8.1	8.1	8.1
72.5°	9.2	8.1	9.2	8.1	8.1	8.1	8.1	8.1
75°	8.1	8.1	8.1	7.0	7.0	7.0	7.0	7.0
77.5°	7.0	7.0	7.0	7.0	7.0	5.7	5.7	5.7
80°	7.0	5.7	5.7	5.7	5.7	5.7	5.7	5.7
82.5°	5.7	5.7	5.7	5.7	5.7	4.7	4.7	4.7
85°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
87.5°	3.4	3.4	3.4	3.4	3.4	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)