

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192673

Luminaire Tested: **LDA6A65950D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192673
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A65950D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6690.0 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 66.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192673

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



TEST NUMBER: P1192673

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	68734	68734	68734
5°	188658	63334	25842
10°	413430	51830	9853
15°	631508	39455	11549
20°	731663	29356	17945
25°	798137	24134	28967
30°	891276	21889	29587
35°	906828	15018	20284
40°	922757	7113	10269
45°	924259	2962	4489
50°	781373	1288	1382
55°	251614	879	220
60°	49963	1009	0
65°	5098	1193	0
70°	545	1667	0
75°	0	2203	0
80°	0	3631	347
85°	0	7233	692



TEST NUMBER: P1192673

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.2	2.5
10°-20°	880.3	13.2
20°-30°	1685.4	25.2
30°-40°	1985.7	29.7
40°-50°	1559.7	23.3
50°-60°	380.1	5.7
60°-70°	16.3	0.2
70°-80°	6.1	0.1
80°-90°	6.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2735.9	40.9
0°-40°	4721.6	70.6
0°-60°	6661.4	99.6
0°-90°	6690.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6690.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1254	1254	1254	1254	1254	
5°	3428	2481	1151	603	470	453
15°	11127	5715	695	199	204	3106
25°	13195	6949	399	418	479	6150
35°	13550	4393	224	289	303	8497
45°	11922	1358	38	53	58	8957
55°	2633	50	9	6	2	3133
65°	39	6	9	6	0	104
75°	0	6	10	7	0	0
85°	0	7	12	7	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192673

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8
2.5°	2149.2	2144.5	2113.2	2142.1	2054.2	2050.8	2011.4	1994.1	1943.2	1894.7	1825.2
5°	3428.3	3353.1	3291.9	3294.1	3125.3	3094.1	3006.2	2917.2	2780.6	2653.4	2481.0
7.5°	5225.8	5136.8	5007.2	4952.8	4630.1	4535.2	4353.6	4116.6	3819.2	3523.2	3204.0
10°	7427.0	7440.8	7273.0	7118.2	6629.9	6438.0	6144.2	5676.8	5113.6	4557.2	3991.6
12.5°	9641.8	9632.7	9432.6	9197.8	8596.3	8325.7	7934.8	7351.8	6605.7	5742.8	4857.9
15°	11127.1	11193.0	11108.6	10921.1	10407.6	10097.6	9656.9	8865.8	7956.7	6908.7	5715.1
17.5°	12059.3	12121.7	12091.7	11944.8	11491.4	11160.6	10792.8	10145.1	9093.7	7776.2	6390.6
20°	12541.7	12640.0	12626.1	12466.5	12124.1	11850.0	11444.0	10843.7	9933.4	8378.8	6827.7
22.5°	12863.1	12938.3	12959.2	12778.8	12424.9	12164.6	11867.2	11258.9	10402.9	8746.7	7001.3
25°	13195.1	13328.2	13197.5	12975.4	12650.4	12400.6	12083.6	11500.6	10627.3	8897.0	6949.3
27.5°	13602.3	13665.9	13369.8	13167.4	12806.6	12535.8	12199.2	11640.6	10666.8	8776.8	6651.9
30°	14080.0	13816.3	13609.2	13207.9	12798.4	12534.8	12192.3	11552.7	10459.7	8377.7	6075.9
32.5°	14001.3	13759.6	13524.8	13100.4	12695.5	12434.0	12052.5	11260.1	9970.4	7710.4	5281.3
35°	13550.3	13602.3	13349.0	12997.3	12539.3	12269.9	11853.4	10843.7	9139.9	6789.6	4393.1
37.5°	13169.7	13284.2	13118.9	12793.8	12328.9	11964.5	11402.4	10175.0	8056.2	5621.4	3550.9
40°	12894.4	12931.5	12842.4	12478.1	11919.4	11393.1	10743.1	8974.6	6739.8	4412.6	2802.6
42.5°	12467.7	12565.9	12408.7	12010.8	11164.1	10568.4	9627.0	7587.7	5235.0	3370.5	2109.7
45°	11921.7	12015.4	11821.1	11159.4	9981.9	9108.7	7960.2	5916.4	3872.4	2484.6	1357.9
47.5°	11031.1	11088.9	10712.9	9798.2	8086.2	7263.8	6086.3	4124.7	2495.0	1389.1	660.5
50°	9161.9	9134.2	8359.2	7233.8	5408.5	4545.7	3622.6	2235.8	1120.8	658.1	412.9
52.5°	5904.7	5841.2	5074.3	4050.6	2738.9	2090.1	1570.8	964.6	584.1	367.7	163.1
55°	2632.6	2608.2	2135.1	1658.7	1120.8	964.6	736.7	473.1	311.2	128.4	49.8
57.5°	976.2	954.2	840.8	705.6	541.3	449.9	357.3	226.7	79.9	42.8	26.6
60°	455.7	454.6	400.2	329.7	229.1	173.5	100.7	53.2	33.6	23.2	15.1
62.5°	145.7	142.3	99.4	72.8	52.0	45.1	35.8	26.6	17.3	12.8	9.2
65°	39.3	39.3	35.8	30.1	24.2	20.8	17.3	12.8	8.1	7.0	5.7
67.5°	15.1	15.1	13.8	12.8	9.2	8.1	7.0	5.7	4.7	5.7	5.7
70°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.7	4.7	5.7
72.5°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
75°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
77.5°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
80°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
82.5°	0.0	0.0	1.1	2.3	2.3	2.3	3.4	4.7	4.7	5.7	7.0
85°	0.0	0.0	1.1	2.3	2.3	3.4	3.4	4.7	4.7	5.7	7.0
87.5°	0.0	0.0	1.1	2.3	2.3	3.4	3.4	4.7	4.7	5.7	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192673

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8
2.5°	1774.3	1697.9	1592.8	1531.4	1516.3	1484.0	1427.3	1343.0	1273.5	1206.4	1167.1
5°	2335.3	2154.9	1952.4	1810.1	1752.3	1674.9	1537.2	1395.0	1264.2	1150.9	1061.8
7.5°	2929.8	2632.6	2305.3	2041.4	1946.7	1824.1	1599.6	1388.0	1208.7	1051.4	932.3
10°	3520.9	3042.0	2597.8	2216.2	2061.2	1894.7	1598.5	1324.4	1113.8	931.1	799.3
12.5°	4112.0	3423.8	2813.0	2321.4	2120.1	1909.6	1551.1	1227.2	993.5	807.4	681.2
15°	4658.0	3727.9	2958.7	2357.3	2114.4	1865.8	1455.1	1109.2	867.5	695.2	578.3
17.5°	5065.0	3887.5	2992.3	2302.9	2023.0	1747.7	1308.2	970.4	747.2	595.6	476.5
20°	5265.2	3912.9	2912.5	2147.9	1865.8	1580.0	1147.4	837.4	644.3	503.2	402.5
22.5°	5265.2	3792.8	2738.9	1953.6	1669.0	1386.8	992.5	727.6	563.3	438.4	353.9
25°	5065.0	3553.3	2506.5	1729.2	1452.8	1196.0	858.3	645.4	500.9	399.0	328.5
27.5°	4676.5	3222.5	2208.1	1479.4	1239.9	1026.0	751.8	570.2	453.3	359.6	360.9
30°	4142.0	2816.4	1865.8	1215.7	1021.3	843.2	632.6	477.7	363.3	345.8	356.2
32.5°	3524.4	2330.7	1478.2	942.7	791.1	663.9	481.2	337.7	289.1	291.5	303.1
35°	2890.6	1834.5	1112.8	698.7	588.7	481.2	315.7	222.0	219.8	224.4	232.5
37.5°	2282.1	1373.0	805.1	511.3	395.6	296.2	170.0	152.7	152.7	157.4	161.9
40°	1709.6	974.0	554.0	303.1	192.1	135.4	107.5	99.4	98.4	99.4	105.2
42.5°	1174.0	616.5	329.7	121.4	92.6	78.6	68.2	62.4	61.4	62.4	65.9
45°	659.3	379.4	128.4	64.8	55.5	49.8	42.8	39.3	38.2	38.2	40.5
47.5°	412.9	150.4	57.9	40.5	34.7	32.3	27.8	25.5	24.2	24.2	25.5
50°	158.4	59.0	35.8	26.6	23.2	20.8	18.5	16.2	15.1	15.1	16.2
52.5°	54.3	34.7	23.2	17.3	15.1	13.8	11.5	10.4	10.4	10.4	10.4
55°	30.1	20.8	13.8	10.4	9.2	9.2	9.2	9.2	9.2	9.2	9.2
57.5°	18.5	12.8	9.2	8.1	8.1	8.1	8.1	8.1	8.1	9.2	9.2
60°	10.4	8.1	7.0	7.0	7.0	7.0	8.1	8.1	8.1	9.2	9.2
62.5°	7.0	7.0	7.0	7.0	7.0	7.0	8.1	8.1	9.2	9.2	9.2
65°	5.7	5.7	5.7	7.0	7.0	7.0	8.1	8.1	9.2	9.2	9.2
67.5°	5.7	5.7	7.0	7.0	7.0	8.1	8.1	9.2	9.2	9.2	9.2
70°	5.7	7.0	7.0	8.1	8.1	8.1	9.2	9.2	9.2	10.4	10.4
72.5°	5.7	7.0	7.0	8.1	8.1	8.1	9.2	9.2	10.4	10.4	10.4
75°	7.0	7.0	7.0	8.1	8.1	8.1	9.2	10.4	10.4	10.4	10.4
77.5°	7.0	7.0	8.1	8.1	8.1	9.2	9.2	10.4	10.4	10.4	10.4
80°	7.0	7.0	8.1	8.1	9.2	9.2	10.4	10.4	10.4	11.5	11.5
82.5°	7.0	7.0	8.1	9.2	9.2	9.2	10.4	10.4	11.5	11.5	11.5
85°	7.0	8.1	8.1	9.2	9.2	9.2	10.4	10.4	11.5	11.5	11.5
87.5°	7.0	8.1	8.1	9.2	9.2	9.2	10.4	10.4	11.5	11.5	11.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192673

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8
2.5°	1115.0	1066.4	1017.8	982.1	964.6	947.3	909.2	859.4	838.6	808.5	791.1
5°	971.6	889.4	824.7	781.9	756.5	722.9	679.0	630.3	602.6	571.4	550.6
7.5°	823.6	727.6	665.1	625.8	600.3	558.7	503.2	445.3	411.8	377.1	352.8
10°	694.0	602.6	532.1	486.9	454.6	406.0	350.5	310.0	281.1	251.1	226.7
12.5°	579.5	481.2	406.0	367.7	345.8	299.6	253.3	208.2	190.8	185.0	185.0
15°	469.6	380.5	316.9	284.5	261.5	211.6	202.5	200.1	199.0	197.8	200.1
17.5°	382.8	307.6	240.6	224.4	222.0	221.0	222.0	222.0	223.2	226.7	232.5
20°	321.6	252.1	247.5	248.7	248.7	253.3	259.2	263.6	268.3	274.0	284.5
22.5°	285.7	284.5	292.6	293.8	299.6	306.5	316.9	323.9	335.4	341.1	356.2
25°	329.7	337.7	352.8	357.3	366.7	378.2	394.4	403.7	417.6	424.5	441.8
27.5°	373.7	386.3	404.8	410.6	418.7	437.2	448.9	456.9	463.8	468.4	478.9
30°	370.1	381.8	400.2	401.3	412.9	425.7	432.6	439.5	444.2	442.9	448.9
32.5°	313.5	323.9	341.1	341.1	353.9	364.3	367.7	373.7	373.7	373.7	375.9
35°	240.6	247.5	259.2	262.6	273.0	280.0	282.2	289.1	289.1	286.8	286.8
37.5°	166.5	175.9	184.0	186.3	193.1	197.8	203.5	204.7	202.5	203.5	203.5
40°	108.8	114.5	120.3	121.4	127.3	130.7	136.4	136.4	137.6	136.4	138.8
42.5°	67.1	71.8	75.2	77.5	79.9	82.2	85.6	86.7	87.9	86.7	89.0
45°	41.7	43.9	46.3	47.4	48.6	49.8	53.2	53.2	53.2	53.2	54.3
47.5°	25.5	26.6	27.8	27.8	28.9	30.1	31.3	31.3	31.3	31.3	32.3
50°	15.1	16.2	16.2	16.2	17.3	17.3	18.5	18.5	18.5	17.3	18.5
52.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	9.2	10.4
55°	9.2	9.2	8.1	8.1	8.1	8.1	8.1	7.0	5.7	5.7	4.7
57.5°	8.1	8.1	8.1	8.1	8.1	7.0	7.0	5.7	5.7	4.7	3.4
60°	8.1	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	4.7	3.4
62.5°	9.2	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	4.7	3.4
65°	9.2	9.2	8.1	8.1	8.1	7.0	7.0	5.7	5.7	4.7	3.4
67.5°	9.2	9.2	9.2	8.1	9.2	8.1	7.0	7.0	5.7	4.7	4.7
70°	10.4	9.2	9.2	9.2	9.2	8.1	8.1	7.0	5.7	4.7	4.7
72.5°	10.4	10.4	9.2	9.2	9.2	8.1	8.1	7.0	5.7	5.7	4.7
75°	10.4	10.4	9.2	9.2	9.2	8.1	8.1	7.0	7.0	5.7	4.7
77.5°	10.4	10.4	10.4	9.2	9.2	9.2	8.1	8.1	7.0	5.7	4.7
80°	10.4	10.4	10.4	10.4	10.4	9.2	9.2	8.1	7.0	5.7	4.7
82.5°	11.5	10.4	10.4	10.4	10.4	9.2	9.2	8.1	7.0	5.7	5.7
85°	11.5	11.5	10.4	10.4	10.4	9.2	9.2	8.1	7.0	7.0	5.7
87.5°	11.5	10.4	10.4	10.4	10.4	9.2	9.2	8.1	7.0	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192673

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8	1253.8
2.5°	773.8	764.6	764.6	748.4	746.1	733.3	743.8	736.7
5°	527.5	512.4	507.8	491.6	485.8	470.8	475.5	469.6
7.5°	332.0	316.9	312.3	300.7	293.8	282.2	283.4	280.0
10°	202.5	188.4	185.0	181.6	178.2	177.0	178.2	177.0
12.5°	184.0	182.7	180.4	181.6	179.3	180.4	181.6	180.4
15°	200.1	202.5	200.1	201.2	200.1	202.5	203.5	203.5
17.5°	234.8	239.4	237.1	240.6	239.4	245.2	245.2	245.2
20°	288.1	296.2	293.8	298.4	298.4	305.3	305.3	307.6
22.5°	362.0	372.4	371.3	381.8	379.4	387.5	387.5	389.8
25°	451.0	461.4	462.7	469.6	468.4	476.5	476.5	478.9
27.5°	488.1	493.8	492.8	496.2	497.4	501.9	505.4	503.2
30°	458.0	462.7	461.4	463.8	463.8	467.4	470.8	467.4
32.5°	385.2	388.6	388.6	393.3	389.8	390.9	396.8	393.3
35°	294.9	297.2	294.9	297.2	298.4	298.4	304.2	303.1
37.5°	210.6	211.6	211.6	215.1	211.6	211.6	217.5	218.6
40°	141.1	142.3	141.1	145.7	143.5	143.5	147.0	143.5
42.5°	90.3	91.3	90.3	93.7	91.3	93.7	94.8	96.0
45°	55.5	55.5	54.3	56.7	55.5	56.7	57.9	57.9
47.5°	32.3	32.3	31.3	33.6	32.3	32.3	32.3	33.6
50°	17.3	17.3	17.3	18.5	17.3	17.3	17.3	16.2
52.5°	9.2	9.2	8.1	9.2	8.1	8.1	8.1	8.1
55°	4.7	3.4	3.4	3.4	2.3	2.3	2.3	2.3
57.5°	3.4	2.3	2.3	1.1	1.1	1.1	0.0	0.0
60°	2.3	2.3	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.3	2.3	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.3	2.3	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.4	2.3	2.3	1.1	1.1	0.0	0.0	0.0
70°	3.4	2.3	2.3	1.1	1.1	0.0	0.0	0.0
72.5°	3.4	2.3	2.3	2.3	1.1	1.1	0.0	0.0
75°	3.4	3.4	2.3	2.3	1.1	1.1	0.0	0.0
77.5°	4.7	3.4	2.3	2.3	1.1	1.1	0.0	0.0
80°	4.7	3.4	2.3	2.3	2.3	1.1	1.1	1.1
82.5°	4.7	3.4	3.4	2.3	2.3	1.1	1.1	1.1
85°	4.7	3.4	3.4	2.3	2.3	1.1	1.1	1.1
87.5°	4.7	3.4	3.4	2.3	2.3	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)