

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192675

Luminaire Tested: **LDA6A65950D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192675
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A65950D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6216.9 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 66.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192675

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192675

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	103	110	107	104	102		103	100	98			99	97	95			95
2	105	99	94	90	103	97	93	89		94	90	87			91	88	85			88
3	98	90	84	79	96	88	83	78		86	81	77			83	79	76			81
4	91	82	75	70	89	80	74	69		78	73	68			76	71	67			74
5	85	74	67	62	83	73	67	61		71	65	61			70	64	60			68
6	79	68	60	55	77	67	60	55		65	59	54			64	58	54			62
7	74	62	55	49	72	61	54	49		60	54	49			59	53	49			57
8	69	57	50	44	67	56	49	44		55	49	44			54	48	44			53
9	64	52	45	40	63	52	45	40		51	44	40			50	44	40			49
10	60	48	41	37	59	48	41	36		47	41	36			46	40	36			45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	66393	66393	66393
5°	176188	61551	23553
10°	384601	49771	7014
15°	580531	36368	6101
20°	675285	24969	9579
25°	744726	26941	63814
30°	823962	20282	19845
35°	836204	10373	7435
40°	855431	4222	3564
45°	862609	2605	2155
50°	726663	1774	1382
55°	240011	1223	774
60°	47189	1140	515
65°	5552	1492	610
70°	1475	1667	753
75°	233	2203	1207
80°	0	3631	1799
85°	0	7233	2956



TEST NUMBER: P1192675

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.2	2.6
10°-20°	813.9	13.1
20°-30°	1606.4	25.8
30°-40°	1812.0	29.1
40°-50°	1438.5	23.1
50°-60°	351.7	5.7
60°-70°	18.8	0.3
70°-80°	8.0	0.1
80°-90°	6.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2581.4	41.5
0°-40°	4393.4	70.7
0°-60°	6183.5	99.5
0°-90°	6216.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6216.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1211	1211	1211	1211	1211	
5°	3202	2399	1118	562	428	423
15°	10229	5437	641	126	108	2869
25°	12312	6590	445	806	1055	5703
35°	12495	4194	155	123	111	7858
45°	11126	1307	34	35	28	8339
55°	2511	57	13	13	8	2946
65°	43	10	12	9	5	105
75°	1	6	10	9	6	3
85°	0	6	12	8	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192675

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1
2.5°	2101.7	2061.3	2079.8	2050.9	1968.7	1943.3	1964.0	1932.9	1839.2	1803.3	1766.3
5°	3201.7	3166.0	3177.5	3111.6	2957.8	2904.5	2901.1	2806.1	2616.4	2510.1	2399.1
7.5°	4854.7	4805.0	4791.2	4632.6	4336.6	4225.5	4171.1	3937.4	3580.1	3326.8	3078.0
10°	6909.1	6957.7	6907.9	6651.1	6186.1	5978.0	5846.0	5404.3	4759.9	4277.6	3812.5
12.5°	8969.2	8999.2	8905.5	8586.3	7995.3	7745.4	7551.1	6985.4	6136.4	5317.5	4623.4
15°	10228.9	10371.1	10283.3	10060.0	9602.0	9298.8	9124.2	8425.6	7356.8	6456.8	5436.6
17.5°	11126.5	11258.3	11185.5	11002.8	10485.7	10241.6	10128.4	9553.4	8389.7	7245.8	6045.1
20°	11575.3	11736.1	11670.2	11463.2	11083.7	10880.2	10742.5	10181.4	9132.3	7832.1	6451.0
22.5°	11879.5	12057.7	11985.9	11797.4	11411.0	11174.0	11109.1	10578.3	9520.9	8183.8	6623.4
25°	12312.1	12461.4	12258.9	12026.4	11644.8	11394.9	11355.6	10813.1	9707.2	8316.8	6589.9
27.5°	12622.2	12799.1	12455.6	12219.7	11783.6	11520.9	11470.1	10959.9	9724.6	8211.6	6318.0
30°	13016.6	12902.1	12600.2	12257.8	11792.8	11512.8	11448.1	10874.3	9551.0	7824.1	5785.9
32.5°	12860.4	12832.7	12530.8	12128.2	11694.4	11412.2	11325.4	10610.6	9074.4	7155.5	5032.9
35°	12495.0	12582.8	12330.7	12080.8	11541.7	11247.9	11127.6	10222.0	8356.2	6294.9	4194.2
37.5°	12280.9	12336.4	12176.8	11871.4	11337.0	10950.7	10722.8	9568.4	7415.7	5209.9	3385.7
40°	11953.6	12094.7	11940.8	11590.3	10973.9	10444.1	10047.2	8387.4	6176.9	4107.5	2647.7
42.5°	11595.0	11721.0	11574.2	11154.2	10283.3	9573.0	8913.6	6999.3	4836.3	3138.2	1986.1
45°	11126.5	11239.8	10976.2	10322.5	9089.5	8109.8	7451.6	5496.8	3647.2	2305.4	1307.1
47.5°	10282.1	10252.0	9878.4	8862.8	7344.0	6466.1	5700.3	3937.4	2424.6	1305.9	650.1
50°	8520.4	8239.3	7690.0	6511.2	4928.8	3980.2	3457.5	2032.4	1100.0	632.7	408.4
52.5°	5518.8	5205.3	4702.0	3613.6	2366.6	1899.4	1523.4	918.4	573.8	357.4	160.8
55°	2511.2	2289.1	1967.6	1459.7	1015.7	844.5	714.8	465.0	307.6	133.0	56.7
57.5°	956.6	882.5	784.3	625.8	469.7	406.0	336.6	223.2	96.0	49.8	33.6
60°	430.4	399.0	366.7	286.8	201.2	144.6	109.9	60.1	40.5	28.9	21.9
62.5°	147.0	122.6	101.8	72.8	54.3	47.4	41.7	33.6	24.2	19.7	15.1
65°	42.8	41.7	39.3	34.7	27.8	25.5	24.2	19.7	15.1	12.8	10.4
67.5°	20.8	19.7	18.5	17.3	13.8	12.8	12.8	11.5	9.2	8.1	7.0
70°	9.2	9.2	8.1	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
72.5°	4.7	4.7	4.7	3.4	3.4	3.4	3.4	4.7	4.7	5.7	5.7
75°	1.1	2.3	2.3	2.3	2.3	3.4	3.4	4.7	4.7	5.7	5.7
77.5°	1.1	1.1	1.1	2.3	2.3	2.3	3.4	4.7	4.7	5.7	5.7
80°	0.0	1.1	1.1	2.3	2.3	2.3	3.4	3.4	4.7	5.7	5.7
82.5°	0.0	1.1	1.1	2.3	2.3	2.3	3.4	3.4	4.7	5.7	5.7
85°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
87.5°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192675

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1
2.5°	1676.1	1651.8	1555.8	1481.8	1447.1	1444.7	1367.2	1319.9	1236.5	1171.8	1110.4
5°	2203.6	2096.0	1901.6	1747.8	1673.8	1635.6	1482.9	1373.0	1229.6	1118.5	1008.6
7.5°	2740.3	2535.5	2262.5	1970.0	1849.6	1775.6	1539.6	1363.8	1172.9	1018.0	881.5
10°	3289.7	2928.7	2521.7	2135.3	1961.9	1836.8	1533.9	1295.4	1075.7	894.1	745.0
12.5°	3862.2	3293.3	2726.5	2242.9	2013.9	1849.6	1481.8	1196.0	956.6	763.4	621.1
15°	4344.7	3575.4	2855.9	2268.3	1997.6	1798.8	1370.7	1070.0	829.4	640.8	511.3
17.5°	4717.1	3733.9	2880.2	2205.8	1907.4	1685.3	1227.3	931.1	695.2	528.6	400.3
20°	4904.5	3758.1	2803.9	2057.8	1744.3	1515.4	1064.2	790.0	583.0	428.0	318.1
22.5°	4918.4	3644.8	2637.3	1866.9	1565.0	1332.6	930.1	681.3	511.3	384.1	301.9
25°	4737.9	3426.2	2414.2	1671.5	1381.1	1171.8	834.0	653.5	514.7	445.4	409.4
27.5°	4395.6	3123.1	2168.8	1476.0	1222.6	1060.8	794.7	653.5	557.4	503.2	515.9
30°	3921.2	2736.8	1827.6	1209.8	994.8	853.6	624.6	489.3	384.1	320.4	308.8
32.5°	3305.8	2239.3	1417.0	894.1	725.2	615.4	422.2	306.6	247.6	241.7	234.8
35°	2720.5	1768.6	1075.7	660.5	534.5	434.9	269.6	180.4	164.2	155.0	148.0
37.5°	2149.3	1323.3	772.7	480.1	366.7	276.4	138.8	116.9	101.8	92.6	84.4
40°	1616.0	950.9	544.9	290.4	192.1	119.2	83.3	71.8	63.6	59.0	56.7
42.5°	1142.8	632.7	337.7	122.6	91.3	75.2	57.9	50.9	46.3	43.9	41.7
45°	663.9	393.3	136.4	71.8	57.9	52.0	42.8	38.2	35.8	33.6	32.3
47.5°	415.3	158.4	70.5	46.3	40.5	37.0	31.3	30.1	27.8	26.6	26.6
50°	167.8	70.5	43.9	32.3	28.9	27.8	24.2	23.2	20.8	20.8	20.8
52.5°	63.6	41.7	30.1	23.2	20.8	19.7	17.3	17.3	16.2	16.2	16.2
55°	37.0	27.8	20.8	16.2	15.1	15.1	13.8	13.8	12.8	12.8	12.8
57.5°	24.2	18.5	15.1	11.5	11.5	11.5	10.4	10.4	10.4	10.4	10.4
60°	16.2	12.8	10.4	9.2	9.2	9.2	9.2	10.4	10.4	10.4	10.4
62.5°	11.5	10.4	9.2	9.2	9.2	9.2	9.2	10.4	10.4	10.4	11.5
65°	9.2	8.1	8.1	8.1	8.1	9.2	9.2	10.4	10.4	11.5	11.5
67.5°	7.0	7.0	7.0	7.0	8.1	8.1	9.2	10.4	10.4	10.4	11.5
70°	5.7	7.0	7.0	8.1	8.1	8.1	9.2	9.2	10.4	10.4	11.5
72.5°	5.7	7.0	7.0	8.1	8.1	8.1	9.2	10.4	10.4	10.4	11.5
75°	5.7	7.0	7.0	8.1	8.1	8.1	9.2	10.4	10.4	10.4	11.5
77.5°	7.0	7.0	8.1	8.1	8.1	9.2	9.2	10.4	10.4	11.5	11.5
80°	7.0	7.0	8.1	8.1	8.1	9.2	9.2	10.4	10.4	11.5	11.5
82.5°	7.0	7.0	8.1	8.1	8.1	9.2	9.2	10.4	10.4	11.5	11.5
85°	7.0	7.0	8.1	8.1	8.1	9.2	9.2	10.4	10.4	11.5	11.5
87.5°	7.0	7.0	8.1	8.1	8.1	9.2	9.2	10.4	10.4	10.4	11.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192675

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1
2.5°	1080.4	1027.1	969.3	950.9	932.4	896.5	874.4	835.1	806.2	777.4	754.2
5°	935.8	851.3	780.8	750.8	721.8	672.0	637.3	595.7	562.1	533.2	506.6
7.5°	785.4	688.2	617.7	587.6	558.7	504.4	460.4	408.4	369.0	336.6	310.0
10°	646.7	554.0	477.8	441.8	408.4	351.7	310.0	268.3	234.8	207.0	182.7
12.5°	526.3	426.9	349.3	322.7	290.4	244.1	204.8	159.6	139.9	131.9	126.0
15°	408.4	319.2	254.5	230.2	201.2	157.4	139.9	131.9	126.0	122.6	117.9
17.5°	311.2	237.1	173.5	157.4	148.0	138.8	134.2	128.4	125.0	123.8	120.3
20°	244.1	179.3	163.1	158.4	158.4	156.1	152.7	152.7	151.5	155.0	155.0
22.5°	251.1	251.1	264.9	263.7	282.3	300.7	314.7	359.8	385.2	439.5	476.5
25°	438.4	480.1	528.6	543.6	579.6	632.7	688.2	757.6	806.2	858.3	879.1
27.5°	547.1	554.0	547.1	564.5	541.3	527.5	532.1	540.2	540.2	543.6	557.4
30°	323.9	340.1	355.2	366.7	360.9	355.2	352.8	335.4	335.4	328.5	322.7
32.5°	219.8	217.5	215.1	219.8	215.1	215.1	211.6	212.9	205.9	201.2	199.0
35°	150.4	143.5	135.4	136.4	131.9	130.7	127.3	127.3	122.6	120.3	119.2
37.5°	83.3	83.3	79.9	80.9	79.9	79.9	79.9	80.9	79.9	79.9	80.9
40°	56.7	56.7	55.5	56.7	55.5	56.7	57.9	57.9	57.9	57.9	56.7
42.5°	42.8	42.8	41.7	42.8	41.7	42.8	43.9	43.9	43.9	43.9	43.9
45°	33.6	33.6	33.6	33.6	33.6	33.6	33.6	34.7	34.7	33.6	33.6
47.5°	26.6	27.8	26.6	26.6	26.6	26.6	27.8	27.8	26.6	26.6	26.6
50°	21.9	21.9	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8
52.5°	17.3	16.2	16.2	15.1	15.1	15.1	15.1	15.1	15.1	15.1	13.8
55°	12.8	12.8	11.5	11.5	11.5	12.8	12.8	12.8	12.8	11.5	11.5
57.5°	11.5	11.5	11.5	10.4	10.4	11.5	11.5	10.4	10.4	10.4	9.2
60°	10.4	11.5	10.4	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1
62.5°	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1	8.1
65°	11.5	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1
67.5°	11.5	11.5	11.5	11.5	10.4	10.4	10.4	9.2	9.2	9.2	8.1
70°	11.5	11.5	11.5	11.5	11.5	10.4	10.4	10.4	9.2	9.2	8.1
72.5°	11.5	11.5	11.5	10.4	10.4	10.4	10.4	10.4	9.2	9.2	8.1
75°	11.5	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1
77.5°	11.5	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1
80°	11.5	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1
82.5°	11.5	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1
85°	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1	7.0
87.5°	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1	7.0	7.0	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192675

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1	1211.1
2.5°	726.4	721.8	718.3	725.2	722.9	694.1	697.5	696.3
5°	476.5	466.1	458.0	461.6	452.3	439.5	430.4	428.0
7.5°	283.4	271.9	264.9	257.9	255.6	239.5	232.5	237.1
10°	156.1	139.9	138.8	135.4	130.7	127.3	125.0	126.0
12.5°	120.3	119.2	116.9	115.6	113.4	112.2	111.1	109.9
15°	114.5	113.4	112.2	111.1	109.9	108.8	107.5	107.5
17.5°	117.9	117.9	116.9	115.6	115.6	116.9	115.6	114.5
20°	153.9	153.9	156.1	159.6	159.6	163.1	167.8	164.2
22.5°	499.7	525.1	556.4	565.7	620.0	663.9	745.0	709.1
25°	913.8	971.6	985.6	1005.2	1035.2	1050.3	1035.2	1055.0
27.5°	555.3	574.9	577.2	578.3	585.3	584.1	569.1	578.3
30°	322.7	329.7	327.3	326.2	323.9	311.2	308.8	313.5
32.5°	202.5	200.1	199.0	197.8	197.8	190.8	194.4	192.1
35°	115.6	119.2	117.9	116.9	113.4	112.2	112.2	111.1
37.5°	77.5	78.6	77.5	76.4	74.0	72.8	71.8	70.5
40°	55.5	56.7	55.5	54.3	53.2	52.0	50.9	49.8
42.5°	41.7	42.8	41.7	41.7	39.3	38.2	37.0	35.8
45°	32.3	31.3	31.3	31.3	30.1	28.9	27.8	27.8
47.5°	26.6	26.6	26.6	25.5	24.2	24.2	24.2	23.2
50°	19.7	20.8	19.7	19.7	18.5	17.3	17.3	16.2
52.5°	13.8	13.8	12.8	12.8	11.5	10.4	10.4	10.4
55°	10.4	10.4	10.4	9.2	9.2	8.1	8.1	8.1
57.5°	9.2	8.1	8.1	8.1	7.0	7.0	5.7	5.7
60°	8.1	7.0	7.0	5.7	5.7	4.7	4.7	4.7
62.5°	7.0	5.7	5.7	5.7	4.7	4.7	4.7	4.7
65°	7.0	5.7	5.7	5.7	4.7	4.7	4.7	4.7
67.5°	7.0	7.0	5.7	5.7	5.7	4.7	4.7	4.7
70°	7.0	7.0	7.0	5.7	5.7	5.7	4.7	4.7
72.5°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
75°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
77.5°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
80°	7.0	7.0	7.0	5.7	5.7	5.7	5.7	5.7
82.5°	7.0	7.0	7.0	7.0	5.7	5.7	5.7	5.7
85°	7.0	5.7	5.7	5.7	4.7	4.7	4.7	4.7
87.5°	5.7	4.7	4.7	3.4	3.4	3.4	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)