

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192679

Luminaire Tested: **LDA6A70927D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70927D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5416.8 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192679

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot





TEST NUMBER: P1192679

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	83836	83836	83836
5°	162436	79892	26942
10°	275980	69911	12102
15°	425281	55766	19234
20°	615634	36292	33463
25°	903246	35016	43031
30°	1050238	33176	32967
35°	1063019	17574	17427
40°	880099	6627	7314
45°	664697	2248	2667
50°	454774	819	819
55°	63262	717	96
60°	1656	713	0
65°	415	973	0
70°	160	1202	0
75°	0	1589	0
80°	0	2715	316
85°	0	5409	0



TEST NUMBER: P1192679

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.4	3.0
10°-20°	678.2	12.5
20°-30°	1547.0	28.6
30°-40°	1790.3	33.1
40°-50°	1079.7	19.9
50°-60°	146.7	2.7
60°-70°	4.7	0.1
70°-80°	5.1	0.1
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2385.6	44.0
0°-40°	4175.9	77.1
0°-60°	5402.2	99.7
0°-90°	5416.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5416.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1529	1529	1529	1529	1529	
5°	2952	2417	1452	794	490	344
15°	7493	4212	983	302	339	2218
25°	14933	4991	579	696	711	6758
35°	15884	3805	263	268	260	9573
45°	8574	1036	29	36	34	6704
55°	662	8	8	5	1	1297
65°	3	4	8	4	0	5
75°	0	5	8	5	0	0
85°	0	5	9	5	0	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192679

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3
2.5°	2211.4	2191.0	2199.7	2177.1	2120.0	2108.2	2107.2	2092.1	2043.6	2006.0	1960.8
5°	2951.8	2950.8	2956.2	2907.8	2807.8	2776.6	2761.5	2724.8	2607.6	2517.2	2417.1
7.5°	3876.3	3869.8	3863.4	3775.2	3618.1	3557.8	3519.0	3386.7	3225.2	3064.9	2886.3
10°	4957.8	4954.6	4929.9	4774.9	4523.1	4412.2	4336.9	4127.1	3867.7	3639.6	3336.1
12.5°	6213.7	6184.7	6140.5	5913.5	5568.1	5447.6	5281.8	4949.3	4551.2	4201.3	3777.4
15°	7493.4	7451.4	7372.7	7081.1	6652.9	6447.2	6241.8	5803.8	5263.5	4755.5	4212.1
17.5°	8744.8	8698.7	8514.6	8019.5	7600.9	7350.1	7122.1	6520.4	5885.6	5232.3	4543.5
20°	10552.8	10385.0	10064.3	9284.1	8506.0	8054.0	7787.1	7151.1	6365.4	5604.6	4779.2
22.5°	12967.7	12595.4	11912.1	10644.4	9532.7	8880.4	8443.6	7597.8	6711.0	5847.9	4924.4
25°	14932.8	14763.8	13986.9	12183.3	10448.4	9680.1	9072.1	7952.8	6962.8	6010.4	4991.2
27.5°	16199.5	16157.5	15269.6	13457.5	11196.4	10188.0	9509.0	8187.5	7084.4	6044.8	4959.0
30°	16591.2	16656.8	15804.5	13890.0	11412.7	10290.2	9547.6	8190.6	6990.8	5888.7	4752.3
32.5°	16562.2	16565.3	15520.4	13516.6	11060.8	9993.3	9224.8	7918.4	6645.3	5498.0	4359.5
35°	15884.2	15717.4	14535.6	12369.4	10241.9	9300.2	8585.6	7391.1	6076.0	4910.5	3805.3
37.5°	14395.9	14177.3	12799.9	10900.5	9272.3	8401.6	7824.8	6699.0	5398.0	4283.1	3232.8
40°	12298.3	11988.4	10852.0	9534.8	8211.1	7556.8	7072.5	5925.4	4672.7	3667.5	2695.7
42.5°	10198.7	10047.0	9295.9	8225.1	7318.9	6703.3	6197.6	5115.0	3975.4	3060.6	2016.7
45°	8573.7	8443.6	7938.8	7232.8	6344.0	5782.2	5294.7	4270.2	3088.6	2053.3	1036.3
47.5°	7390.0	7284.6	6801.3	6059.9	5084.9	4470.3	3967.8	2800.1	1749.9	886.8	259.4
50°	5332.4	5224.7	4751.3	3892.4	3012.2	2497.7	2136.2	1250.5	496.1	179.7	26.9
52.5°	2613.9	2525.8	2204.0	1649.8	1107.4	796.3	582.2	234.5	57.1	19.4	12.9
55°	661.9	608.0	506.9	318.5	156.0	93.6	60.3	21.6	13.9	10.8	7.5
57.5°	37.7	36.5	33.4	24.7	18.3	16.1	13.9	10.8	7.5	6.5	5.3
60°	15.1	13.9	12.9	10.8	8.6	7.5	7.5	5.3	4.3	4.3	4.3
62.5°	6.5	6.5	6.5	5.3	4.3	4.3	4.3	3.2	4.3	4.3	4.3
65°	3.2	3.2	3.2	2.2	2.2	2.2	3.2	3.2	3.2	4.3	4.3
67.5°	2.2	1.0	1.0	1.0	2.2	2.2	2.2	3.2	3.2	4.3	4.3
70°	1.0	1.0	1.0	1.0	2.2	2.2	2.2	3.2	3.2	4.3	5.3
72.5°	0.0	1.0	1.0	1.0	2.2	2.2	2.2	3.2	3.2	4.3	5.3
75°	0.0	1.0	1.0	1.0	2.2	2.2	2.2	3.2	4.3	4.3	5.3
77.5°	0.0	1.0	1.0	1.0	2.2	2.2	2.2	3.2	4.3	4.3	5.3
80°	0.0	1.0	1.0	1.0	2.2	2.2	2.2	3.2	4.3	4.3	5.3
82.5°	0.0	0.0	1.0	1.0	2.2	2.2	2.2	3.2	4.3	4.3	5.3
85°	0.0	0.0	1.0	1.0	2.2	2.2	2.2	3.2	4.3	4.3	5.3
87.5°	0.0	0.0	1.0	1.0	2.2	2.2	2.2	3.2	3.2	4.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192679

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3
2.5°	1902.7	1863.9	1806.9	1769.3	1732.6	1698.2	1641.1	1608.8	1550.7	1496.9	1450.6
5°	2296.6	2199.7	2082.3	1982.2	1917.7	1854.3	1739.1	1654.1	1547.5	1451.8	1363.5
7.5°	2694.7	2523.6	2330.9	2166.3	2066.2	1968.3	1796.2	1658.4	1507.7	1371.1	1240.8
10°	3056.2	2799.1	2526.8	2291.1	2155.5	2028.5	1801.5	1618.6	1424.9	1255.9	1092.3
12.5°	3392.0	3040.1	2685.0	2377.2	2209.4	2056.6	1778.9	1555.0	1324.8	1124.6	934.1
15°	3691.2	3239.3	2800.1	2426.7	2229.8	2049.0	1726.1	1465.7	1206.3	982.6	741.4
17.5°	3918.3	3363.0	2850.8	2419.2	2193.2	1992.0	1635.8	1353.8	1080.5	809.3	536.9
20°	4056.1	3415.7	2840.0	2361.1	2114.7	1901.6	1528.1	1232.2	928.8	622.1	473.5
22.5°	4114.2	3411.4	2789.4	2274.0	2017.7	1802.6	1424.9	1113.8	769.5	562.8	493.9
25°	4123.8	3367.3	2718.3	2178.1	1922.0	1707.9	1320.5	979.3	668.4	578.9	553.2
27.5°	4049.6	3264.0	2584.9	2040.5	1787.5	1565.8	1164.5	778.1	627.4	576.8	594.0
30°	3830.0	3028.3	2349.2	1798.3	1554.0	1332.3	831.9	610.1	520.8	524.1	528.5
32.5°	3443.8	2636.6	1970.4	1444.1	1177.3	878.2	517.7	407.8	396.0	396.0	393.9
35°	2928.3	2157.7	1546.4	913.7	585.4	421.9	267.9	269.0	263.7	262.6	261.6
37.5°	2395.5	1702.5	979.3	377.8	253.9	176.4	158.2	160.3	158.2	161.5	159.3
40°	1888.6	1051.4	357.3	120.5	89.3	86.1	88.3	90.4	90.4	92.6	92.6
42.5°	1097.7	348.7	93.6	48.5	48.5	46.3	47.3	49.5	50.6	51.6	50.6
45°	326.1	72.0	30.2	26.9	26.9	25.9	25.9	26.9	28.0	29.0	29.0
47.5°	51.6	20.4	17.3	15.1	15.1	15.1	15.1	15.1	16.1	16.1	17.3
50°	16.1	12.9	10.8	9.6	9.6	8.6	8.6	9.6	9.6	9.6	10.8
52.5°	9.6	7.5	7.5	6.5	7.5	7.5	6.5	7.5	7.5	7.5	8.6
55°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	7.5	7.5	7.5
57.5°	5.3	5.3	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
60°	5.3	5.3	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	7.5
62.5°	5.3	5.3	6.5	6.5	6.5	6.5	6.5	6.5	7.5	7.5	7.5
65°	5.3	5.3	6.5	6.5	6.5	6.5	6.5	7.5	7.5	7.5	7.5
67.5°	5.3	6.5	6.5	6.5	6.5	7.5	7.5	7.5	7.5	7.5	7.5
70°	5.3	6.5	6.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
72.5°	5.3	6.5	6.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
75°	6.5	6.5	6.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	8.6
77.5°	6.5	6.5	7.5	7.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6
80°	6.5	6.5	7.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	8.6
82.5°	6.5	6.5	7.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	8.6
85°	6.5	6.5	7.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	8.6
87.5°	6.5	6.5	7.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192679

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3
2.5°	1410.8	1361.3	1337.7	1304.4	1280.6	1227.9	1206.3	1169.8	1139.6	1090.1	1093.4
5°	1288.1	1194.5	1131.1	1081.5	1047.1	963.1	907.2	848.0	794.2	727.5	702.7
7.5°	1118.2	1003.0	906.1	847.0	802.8	690.9	567.1	470.2	397.2	344.4	324.0
10°	948.0	798.5	644.6	553.2	489.6	382.1	327.1	301.4	277.7	248.6	229.2
12.5°	750.0	536.9	397.2	360.5	334.8	299.2	263.7	235.7	241.0	242.2	249.6
15°	512.2	386.4	342.2	317.5	289.5	269.0	280.8	288.5	302.4	303.4	313.2
17.5°	416.4	362.7	327.1	326.1	328.3	340.1	358.3	368.1	386.4	390.7	404.6
20°	416.4	385.2	415.4	415.4	420.7	436.9	460.6	474.5	495.1	502.6	519.8
22.5°	474.5	496.1	533.8	538.1	540.2	557.5	587.6	601.6	625.2	629.5	647.8
25°	578.9	598.3	632.8	636.0	637.0	650.0	672.5	680.2	696.3	687.6	698.4
27.5°	612.3	620.9	642.5	644.6	639.2	644.6	653.3	653.3	658.6	641.3	644.6
30°	538.1	540.2	551.0	552.0	540.2	542.4	543.4	542.4	541.2	523.0	523.0
32.5°	399.3	399.3	413.3	410.0	397.2	400.3	400.3	400.3	399.3	384.2	382.1
35°	264.7	265.9	277.7	275.5	265.9	267.9	267.9	271.2	267.9	259.4	257.3
37.5°	161.5	162.5	167.8	169.0	165.8	166.8	167.8	166.8	169.0	164.6	162.5
40°	93.6	95.8	100.1	101.1	100.1	100.1	101.1	102.2	106.6	101.1	99.1
42.5°	54.9	55.9	58.1	58.1	58.1	58.1	59.2	60.3	61.4	60.3	59.2
45°	31.2	32.4	33.4	33.4	34.4	33.4	34.4	34.4	35.5	34.4	34.4
47.5°	18.3	18.3	19.4	19.4	20.4	19.4	20.4	20.4	20.4	19.4	19.4
50°	10.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	10.8	10.8
52.5°	8.6	8.6	8.6	8.6	8.6	7.5	7.5	7.5	7.5	6.5	6.5
55°	7.5	7.5	7.5	7.5	7.5	7.5	6.5	5.3	5.3	4.3	4.3
57.5°	6.5	7.5	7.5	7.5	7.5	6.5	6.5	5.3	4.3	3.2	3.2
60°	7.5	7.5	7.5	7.5	6.5	6.5	6.5	5.3	4.3	3.2	3.2
62.5°	7.5	7.5	7.5	7.5	7.5	6.5	6.5	5.3	4.3	3.2	3.2
65°	7.5	7.5	7.5	7.5	7.5	6.5	6.5	5.3	4.3	3.2	3.2
67.5°	7.5	7.5	7.5	7.5	7.5	6.5	6.5	5.3	4.3	4.3	3.2
70°	7.5	8.6	8.6	7.5	7.5	7.5	6.5	5.3	5.3	4.3	3.2
72.5°	7.5	8.6	8.6	7.5	7.5	7.5	6.5	5.3	5.3	4.3	3.2
75°	8.6	8.6	8.6	8.6	7.5	7.5	6.5	6.5	5.3	4.3	3.2
77.5°	8.6	8.6	8.6	8.6	7.5	7.5	6.5	6.5	5.3	4.3	3.2
80°	8.6	8.6	8.6	8.6	8.6	7.5	7.5	6.5	5.3	4.3	4.3
82.5°	8.6	8.6	8.6	8.6	8.6	7.5	7.5	6.5	5.3	4.3	4.3
85°	8.6	8.6	8.6	8.6	8.6	7.5	7.5	6.5	5.3	4.3	3.2
87.5°	8.6	8.6	8.6	8.6	7.5	7.5	6.5	6.5	5.3	4.3	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192679

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3	1529.3
2.5°	1053.6	1028.9	1018.1	1035.3	1026.7	1000.8	1006.1	990.0
5°	628.5	590.9	567.1	577.9	543.4	512.2	512.2	489.6
7.5°	303.4	291.6	285.1	287.3	279.8	270.0	264.7	264.7
10°	213.1	208.8	209.8	209.8	216.3	215.3	218.4	217.4
12.5°	252.9	255.1	256.1	260.4	265.9	265.9	269.0	266.9
15°	324.0	321.8	328.3	329.3	337.9	338.9	343.2	338.9
17.5°	412.1	416.4	422.9	421.9	439.0	440.2	440.2	439.0
20°	530.6	533.8	540.2	542.4	562.8	565.0	572.5	573.6
22.5°	659.7	659.7	662.9	667.2	686.6	687.6	690.9	690.9
25°	703.7	697.4	698.4	703.7	714.5	710.2	713.5	711.4
27.5°	646.8	637.0	635.0	642.5	650.0	638.2	642.5	642.5
30°	525.1	516.5	514.4	522.0	527.3	514.4	518.7	520.8
32.5°	384.2	378.8	377.8	383.1	387.4	376.6	380.9	384.2
35°	259.4	257.3	255.1	256.1	262.6	253.9	258.3	260.4
37.5°	164.6	160.3	161.5	163.6	167.8	162.5	166.8	166.8
40°	101.1	99.1	99.1	101.1	103.2	99.1	101.1	102.2
42.5°	59.2	59.2	59.2	60.3	61.4	59.2	59.2	60.3
45°	34.4	33.4	33.4	34.4	35.5	33.4	34.4	34.4
47.5°	19.4	18.3	18.3	19.4	19.4	18.3	19.4	19.4
50°	10.8	9.6	9.6	10.8	10.8	9.6	9.6	9.6
52.5°	5.3	5.3	5.3	5.3	5.3	5.3	4.3	4.3
55°	3.2	3.2	2.2	2.2	2.2	2.2	2.2	1.0
57.5°	2.2	2.2	1.0	1.0	1.0	1.0	0.0	0.0
60°	2.2	2.2	1.0	1.0	1.0	0.0	0.0	0.0
62.5°	2.2	2.2	1.0	1.0	1.0	0.0	0.0	0.0
65°	2.2	2.2	1.0	1.0	1.0	0.0	0.0	0.0
67.5°	2.2	2.2	1.0	1.0	1.0	0.0	0.0	0.0
70°	3.2	2.2	2.2	1.0	1.0	1.0	0.0	0.0
72.5°	3.2	2.2	2.2	2.2	1.0	1.0	0.0	0.0
75°	3.2	2.2	2.2	2.2	1.0	1.0	0.0	0.0
77.5°	3.2	2.2	2.2	2.2	1.0	1.0	1.0	0.0
80°	3.2	2.2	2.2	2.2	1.0	1.0	1.0	1.0
82.5°	3.2	2.2	2.2	2.2	1.0	1.0	1.0	1.0
85°	3.2	2.2	2.2	2.2	1.0	1.0	1.0	0.0
87.5°	3.2	2.2	2.2	2.2	1.0	1.0	1.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)