

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192690

Luminaire Tested: **LDA6A70927D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192690
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70927D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6223.9 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192690

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192690

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	103	110	107	104	102		103	100	98			99	97	95			95
2	105	99	94	90	103	97	93	89		94	90	87			91	88	85			88
3	98	90	84	79	96	88	83	78		86	81	77			83	79	76			81
4	91	82	75	70	89	80	74	69		78	73	68			76	71	67			74
5	85	74	67	62	83	73	66	61		71	65	61			70	64	60			68
6	79	68	60	55	77	67	60	55		65	59	54			64	58	54			62
7	74	62	55	49	72	61	54	49		60	53	49			59	53	49			57
8	69	57	49	44	67	56	49	44		55	49	44			54	48	44			53
9	64	52	45	40	63	52	45	40		51	44	40			50	44	40			49
10	60	48	41	36	59	48	41	36		47	41	36			46	40	36			45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	63948	63948	63948
5°	175517	58920	24042
10°	384618	48218	9163
15°	587512	36703	10749
20°	680687	27308	16702
25°	742537	22459	26947
30°	829185	20370	27517
35°	843646	13974	18872
40°	858473	6627	9546
45°	859864	2752	4171
50°	726927	1185	1288
55°	234075	822	210
60°	46477	943	0
65°	4735	1116	0
70°	513	1539	0
75°	0	2033	0
80°	0	3410	316
85°	0	6793	629



TEST NUMBER: P1192690

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.3	2.5
10°-20°	818.9	13.2
20°-30°	1568.0	25.2
30°-40°	1847.4	29.7
40°-50°	1451.1	23.3
50°-60°	353.6	5.7
60°-70°	15.2	0.2
70°-80°	5.7	0.1
80°-90°	5.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2545.3	40.9
0°-40°	4392.7	70.6
0°-60°	6197.3	99.6
0°-90°	6223.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6223.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1166	1166	1166	1166	1166	
5°	3190	2308	1071	561	437	422
15°	10352	5317	647	185	189	2890
25°	12276	6465	371	388	446	5722
35°	12606	4087	209	269	282	7905
45°	11091	1263	36	50	54	8333
55°	2449	46	9	5	2	2915
65°	36	5	9	5	0	97
75°	0	5	10	6	0	0
85°	0	6	11	6	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192690

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5
2.5°	1999.3	1995.0	1966.0	1992.9	1911.1	1907.9	1871.4	1855.1	1807.8	1762.7	1698.1
5°	3189.5	3119.5	3062.6	3064.7	2907.6	2878.5	2796.7	2713.9	2586.9	2468.5	2308.2
7.5°	4861.8	4778.8	4658.3	4607.8	4307.6	4219.3	4050.3	3829.7	3553.2	3277.7	2980.8
10°	6909.4	6922.4	6766.3	6622.1	6168.0	5989.4	5716.0	5281.3	4757.4	4239.7	3713.5
12.5°	8970.2	8961.5	8775.5	8556.9	7997.4	7745.6	7381.9	6839.5	6145.4	5342.7	4519.5
15°	10351.9	10413.1	10334.6	10160.4	9682.5	9394.1	8984.1	8248.2	7402.3	6427.4	5316.9
17.5°	11219.1	11277.2	11249.3	11112.6	10690.8	10383.1	10040.9	9438.2	8460.1	7234.4	5945.3
20°	11667.9	11759.4	11746.4	11597.9	11279.4	11024.4	10646.7	10088.2	9241.4	7795.0	6352.1
22.5°	11967.0	12037.0	12056.3	11888.5	11559.2	11317.1	11040.5	10474.5	9678.2	8137.3	6513.5
25°	12275.9	12399.5	12278.0	12071.4	11769.0	11536.6	11241.7	10699.4	9887.0	8277.2	6465.1
27.5°	12654.6	12713.9	12438.4	12250.0	11914.2	11662.4	11349.4	10829.6	9923.5	8165.3	6188.6
30°	13099.1	12853.7	12661.1	12287.7	11906.8	11661.4	11342.9	10747.8	9731.0	7794.0	5652.6
32.5°	13025.9	12801.0	12582.6	12187.6	11811.0	11567.8	11212.7	10475.6	9275.7	7173.1	4913.4
35°	12606.2	12654.6	12419.0	12091.8	11665.8	11415.0	11027.6	10088.2	8503.1	6316.5	4087.0
37.5°	12252.2	12358.7	12204.8	11902.4	11469.9	11131.0	10608.0	9466.2	7494.8	5229.7	3303.6
40°	11996.1	12030.6	11947.6	11608.7	11089.0	10599.4	9994.6	8349.2	6270.2	4105.2	2607.3
42.5°	11599.0	11690.5	11544.1	11174.0	10386.3	9832.1	8956.2	7059.1	4870.4	3135.6	1962.8
45°	11091.1	11178.3	10997.5	10381.9	9286.5	8474.1	7405.5	5504.1	3602.7	2311.4	1263.2
47.5°	10262.6	10316.4	9966.7	9115.4	7522.8	6757.7	5662.3	3837.3	2321.2	1292.3	614.4
50°	8523.5	8497.8	7776.8	6729.8	5031.7	4228.9	3370.3	2080.0	1042.7	612.3	384.2
52.5°	5493.3	5434.2	4720.7	3768.5	2548.2	1944.4	1461.3	897.4	543.4	342.2	151.7
55°	2449.1	2426.6	1986.4	1543.1	1042.7	897.4	685.5	440.2	289.5	119.5	46.3
57.5°	908.2	887.8	782.3	656.4	503.6	418.6	332.5	210.9	74.2	39.8	24.7
60°	423.9	422.9	372.3	306.7	213.1	161.3	93.6	49.5	31.2	21.6	13.9
62.5°	135.6	132.3	92.6	67.7	48.5	42.0	33.4	24.7	16.1	11.8	8.6
65°	36.5	36.5	33.4	28.0	22.6	19.4	16.1	11.8	7.5	6.5	5.3
67.5°	13.9	13.9	12.9	11.8	8.6	7.5	6.5	5.3	4.3	5.3	5.3
70°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	5.3
72.5°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.3	5.3	5.3
75°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.3	5.3	5.3
77.5°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.3	5.3	5.3
80°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.3	5.3	5.3
82.5°	0.0	0.0	1.0	2.2	2.2	2.2	3.2	4.3	4.3	5.3	6.5
85°	0.0	0.0	1.0	2.2	2.2	3.2	3.2	4.3	4.3	5.3	6.5
87.5°	0.0	0.0	1.0	2.2	2.2	3.2	3.2	4.3	4.3	5.3	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192690

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5
2.5°	1650.6	1579.7	1481.8	1424.7	1410.8	1380.6	1327.8	1249.3	1184.7	1122.3	1085.8
5°	2172.6	2004.7	1816.4	1684.0	1630.2	1558.2	1430.1	1297.8	1176.1	1070.7	987.9
7.5°	2725.7	2449.1	2144.6	1899.3	1811.0	1696.9	1488.1	1291.3	1124.5	978.1	867.4
10°	3275.5	2830.1	2416.9	2061.8	1917.5	1762.7	1487.1	1232.0	1036.2	866.2	743.6
12.5°	3825.4	3185.2	2616.9	2159.7	1972.5	1776.6	1443.0	1141.7	924.3	751.0	633.9
15°	4333.3	3468.2	2752.5	2193.0	1967.1	1735.8	1353.7	1032.0	807.0	646.7	538.1
17.5°	4712.2	3616.6	2783.8	2142.4	1882.0	1625.9	1217.1	902.9	695.1	554.2	443.3
20°	4898.3	3640.3	2709.6	1998.3	1735.8	1469.9	1067.4	779.1	599.3	468.1	374.4
22.5°	4898.3	3528.5	2548.2	1817.4	1552.7	1290.3	923.3	676.8	524.0	407.8	329.3
25°	4712.2	3305.7	2331.8	1608.8	1351.5	1112.7	798.5	600.5	465.9	371.3	305.6
27.5°	4350.6	2998.0	2054.3	1376.3	1153.5	954.5	699.4	530.5	421.8	334.6	335.8
30°	3853.5	2620.3	1735.8	1131.0	950.2	784.4	588.6	444.5	337.9	321.8	331.5
32.5°	3278.8	2168.3	1375.3	877.0	736.1	617.6	447.6	314.2	269.0	271.2	282.0
35°	2689.1	1706.7	1035.2	650.0	547.7	447.6	293.8	206.6	204.5	208.8	216.3
37.5°	2123.2	1277.3	748.9	475.7	368.0	275.5	158.2	142.1	142.1	146.4	150.7
40°	1590.4	906.1	515.5	282.0	178.6	126.0	100.1	92.6	91.5	92.6	97.9
42.5°	1092.3	573.6	306.7	113.0	86.1	73.2	63.6	58.1	57.1	58.1	61.4
45°	613.3	353.0	119.5	60.3	51.6	46.3	39.8	36.5	35.5	35.5	37.7
47.5°	384.2	139.9	53.8	37.7	32.2	30.2	25.9	23.7	22.6	22.6	23.7
50°	147.4	54.9	33.4	24.7	21.6	19.4	17.3	15.1	13.9	13.9	15.1
52.5°	50.6	32.2	21.6	16.1	13.9	12.9	10.8	9.6	9.6	9.6	9.6
55°	28.0	19.4	12.9	9.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
57.5°	17.3	11.8	8.6	7.5	7.5	7.5	7.5	7.5	7.5	8.6	8.6
60°	9.6	7.5	6.5	6.5	6.5	6.5	7.5	7.5	7.5	8.6	8.6
62.5°	6.5	6.5	6.5	6.5	6.5	6.5	7.5	7.5	8.6	8.6	8.6
65°	5.3	5.3	5.3	6.5	6.5	6.5	7.5	7.5	8.6	8.6	8.6
67.5°	5.3	5.3	6.5	6.5	6.5	7.5	7.5	8.6	8.6	8.6	8.6
70°	5.3	6.5	6.5	7.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6
72.5°	5.3	6.5	6.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6	9.6
75°	6.5	6.5	6.5	7.5	7.5	7.5	8.6	9.6	9.6	9.6	9.6
77.5°	6.5	6.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6	9.6	9.6
80°	6.5	6.5	7.5	7.5	8.6	8.6	9.6	9.6	9.6	10.8	10.8
82.5°	6.5	6.5	7.5	8.6	8.6	8.6	9.6	9.6	10.8	10.8	10.8
85°	6.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6	10.8	10.8	10.8
87.5°	6.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6	10.8	10.8	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192690

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5
2.5°	1037.3	992.2	946.9	913.5	897.4	881.3	845.8	799.5	780.1	752.2	736.1
5°	903.9	827.5	767.3	727.5	703.7	672.5	631.7	586.4	560.7	531.6	512.2
7.5°	766.1	676.8	618.8	582.1	558.5	519.7	468.1	414.3	383.1	350.9	328.1
10°	645.6	560.7	494.9	453.0	422.9	377.8	326.0	288.5	261.4	233.5	210.9
12.5°	539.1	447.6	377.8	342.2	321.8	278.7	235.7	193.7	177.6	172.1	172.1
15°	436.9	354.0	294.8	264.7	243.2	196.9	188.4	186.2	185.1	184.1	186.2
17.5°	356.2	286.3	223.9	208.8	206.6	205.5	206.6	206.6	207.6	210.9	216.3
20°	299.1	234.5	230.2	231.4	231.4	235.7	241.0	245.3	249.6	255.1	264.7
22.5°	265.7	264.7	272.2	273.4	278.7	285.1	294.8	301.3	312.0	317.5	331.5
25°	306.7	314.2	328.1	332.5	341.1	351.9	367.0	375.6	388.4	394.9	411.1
27.5°	347.6	359.3	376.6	382.1	389.5	406.8	417.6	425.1	431.5	435.8	445.5
30°	344.4	355.0	372.3	373.4	384.2	396.0	402.5	409.0	413.3	412.1	417.6
32.5°	291.6	301.3	317.5	317.5	329.3	338.9	342.2	347.6	347.6	347.6	349.7
35°	223.9	230.2	241.0	244.3	253.9	260.4	262.6	269.0	269.0	266.9	266.9
37.5°	155.0	163.5	171.1	173.3	179.7	184.1	189.4	190.5	188.4	189.4	189.4
40°	101.1	106.6	111.9	113.0	118.3	121.7	127.0	127.0	128.1	127.0	129.1
42.5°	62.4	66.7	69.9	72.0	74.2	76.4	79.7	80.7	81.8	80.7	82.8
45°	38.7	40.8	43.0	44.1	45.2	46.3	49.5	49.5	49.5	49.5	50.6
47.5°	23.7	24.7	25.9	25.9	26.9	28.0	29.0	29.0	29.0	29.0	30.2
50°	13.9	15.1	15.1	15.1	16.1	16.1	17.3	17.3	17.3	16.1	17.3
52.5°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	8.6	9.6
55°	8.6	8.6	7.5	7.5	7.5	7.5	7.5	6.5	5.3	5.3	4.3
57.5°	7.5	7.5	7.5	7.5	7.5	6.5	6.5	5.3	5.3	4.3	3.2
60°	7.5	7.5	7.5	7.5	7.5	6.5	6.5	5.3	4.3	4.3	3.2
62.5°	8.6	7.5	7.5	7.5	7.5	6.5	6.5	5.3	4.3	4.3	3.2
65°	8.6	8.6	7.5	7.5	7.5	6.5	6.5	5.3	5.3	4.3	3.2
67.5°	8.6	8.6	8.6	7.5	8.6	7.5	6.5	6.5	5.3	4.3	4.3
70°	9.6	8.6	8.6	8.6	8.6	7.5	7.5	6.5	5.3	4.3	4.3
72.5°	9.6	9.6	8.6	8.6	8.6	7.5	7.5	6.5	5.3	5.3	4.3
75°	9.6	9.6	8.6	8.6	8.6	7.5	7.5	6.5	6.5	5.3	4.3
77.5°	9.6	9.6	9.6	8.6	8.6	8.6	7.5	7.5	6.5	5.3	4.3
80°	9.6	9.6	9.6	9.6	9.6	8.6	8.6	7.5	6.5	5.3	4.3
82.5°	10.8	9.6	9.6	9.6	9.6	8.6	8.6	7.5	6.5	5.3	5.3
85°	10.8	10.8	9.6	9.6	9.6	8.6	8.6	7.5	6.5	6.5	5.3
87.5°	10.8	9.6	9.6	9.6	9.6	8.6	8.6	7.5	6.5	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192690

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5
2.5°	719.8	711.2	711.2	696.3	694.1	682.2	691.9	685.5
5°	490.6	476.7	472.4	457.3	452.0	438.0	442.3	436.9
7.5°	308.9	294.8	290.5	279.8	273.4	262.6	263.6	260.4
10°	188.4	175.4	172.1	169.0	165.7	164.6	165.7	164.6
12.5°	171.1	170.0	167.8	169.0	166.8	167.8	169.0	167.8
15°	186.2	188.4	186.2	187.2	186.2	188.4	189.4	189.4
17.5°	218.4	222.7	220.6	223.9	222.7	228.1	228.1	228.1
20°	267.9	275.5	273.4	277.7	277.7	284.1	284.1	286.3
22.5°	336.8	346.5	345.4	355.0	353.0	360.5	360.5	362.7
25°	419.6	429.4	430.4	436.9	435.8	443.3	443.3	445.5
27.5°	454.1	459.4	458.4	461.6	462.7	467.1	470.2	468.1
30°	426.1	430.4	429.4	431.5	431.5	434.7	438.0	434.7
32.5°	358.3	361.5	361.5	365.8	362.7	363.7	369.1	365.8
35°	274.4	276.5	274.4	276.5	277.7	277.7	283.0	282.0
37.5°	195.9	196.9	196.9	200.2	196.9	196.9	202.3	203.3
40°	131.3	132.3	131.3	135.6	133.4	133.4	136.6	133.4
42.5°	84.0	85.0	84.0	87.1	85.0	87.1	88.3	89.3
45°	51.6	51.6	50.6	52.8	51.6	52.8	53.8	53.8
47.5°	30.2	30.2	29.0	31.2	30.2	30.2	30.2	31.2
50°	16.1	16.1	16.1	17.3	16.1	16.1	16.1	15.1
52.5°	8.6	8.6	7.5	8.6	7.5	7.5	7.5	7.5
55°	4.3	3.2	3.2	3.2	2.2	2.2	2.2	2.2
57.5°	3.2	2.2	2.2	1.0	1.0	1.0	0.0	0.0
60°	2.2	2.2	1.0	1.0	0.0	0.0	0.0	0.0
62.5°	2.2	2.2	1.0	1.0	0.0	0.0	0.0	0.0
65°	2.2	2.2	1.0	1.0	0.0	0.0	0.0	0.0
67.5°	3.2	2.2	2.2	1.0	1.0	0.0	0.0	0.0
70°	3.2	2.2	2.2	1.0	1.0	0.0	0.0	0.0
72.5°	3.2	2.2	2.2	2.2	1.0	1.0	0.0	0.0
75°	3.2	3.2	2.2	2.2	1.0	1.0	0.0	0.0
77.5°	4.3	3.2	2.2	2.2	1.0	1.0	0.0	0.0
80°	4.3	3.2	2.2	2.2	2.2	1.0	1.0	1.0
82.5°	4.3	3.2	3.2	2.2	2.2	1.0	1.0	1.0
85°	4.3	3.2	3.2	2.2	2.2	1.0	1.0	1.0
87.5°	4.3	3.2	3.2	2.2	2.2	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)