

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192692

Luminaire Tested: **LDA6A70927D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192692
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70927D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5783.7 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192692

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192692

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74
5	85	74	67	62	83	73	67	61	71	65	61		70	64	60		68
6	79	68	60	55	77	67	60	55	65	59	54		64	58	54		62
7	74	62	55	49	72	61	54	49	60	54	49		59	53	49		57
8	69	57	50	44	67	56	49	44	55	49	44		54	48	44		53
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49
10	60	48	41	37	59	48	41	36	47	41	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	61760	61760	61760
5°	163917	57269	21913
10°	357803	46308	6530
15°	540088	33837	5681
20°	628240	23230	8920
25°	692846	25060	59362
30°	766555	18870	18459
35°	777934	9650	6906
40°	795834	3929	3313
45°	802510	2419	2008
50°	676037	1655	1288
55°	223294	1128	717
60°	43889	1053	471
65°	5163	1401	558
70°	1378	1539	689
75°	212	2033	1123
80°	0	3410	1673
85°	0	6793	2705

TEST NUMBER: P1192692

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	2.6
10°-20°	757.1	13.1
20°-30°	1494.5	25.8
30°-40°	1685.7	29.1
40°-50°	1338.2	23.1
50°-60°	327.2	5.7
60°-70°	17.5	0.3
70°-80°	7.4	0.1
80°-90°	6.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2401.6	41.5
0°-40°	4087.3	70.7
0°-60°	5752.7	99.5
0°-90°	5783.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5783.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1127	1127	1127	1127	1127	
5°	2979	2232	1041	523	398	393
15°	9516	5058	596	117	100	2669
25°	11454	6131	414	750	981	5305
35°	11624	3902	144	114	103	7311
45°	10351	1216	31	32	26	7758
55°	2336	53	12	12	8	2741
65°	40	10	11	9	4	97
75°	1	5	10	9	5	3
85°	0	5	11	8	4	0
90°	0	0	0	0	0	

TEST NUMBER: P1192692

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6
2.5°	1955.3	1917.7	1934.9	1908.0	1831.5	1807.9	1827.2	1798.2	1711.0	1677.7	1643.3
5°	2978.7	2945.4	2956.2	2894.8	2751.7	2702.2	2698.9	2610.8	2434.2	2335.3	2231.9
7.5°	4516.5	4470.2	4457.4	4309.9	4034.5	3931.1	3880.5	3663.2	3330.6	3094.9	2863.6
10°	6427.7	6473.0	6426.7	6187.7	5755.2	5561.5	5438.8	5027.7	4428.3	3979.6	3546.9
12.5°	8344.4	8372.2	8285.1	7988.2	7438.3	7205.8	7025.0	6498.7	5708.9	4947.0	4301.2
15°	9516.3	9648.6	9566.8	9359.1	8932.9	8651.1	8488.6	7838.5	6844.3	6006.9	5057.9
17.5°	10351.3	10474.0	10406.2	10236.1	9755.1	9528.1	9422.7	8887.8	7805.1	6740.9	5623.9
20°	10768.9	10918.4	10857.0	10664.5	10311.5	10122.1	9994.0	9472.1	8496.1	7286.4	6001.6
22.5°	11051.9	11217.5	11150.8	10975.5	10616.0	10395.5	10335.2	9841.3	8857.7	7613.6	6162.0
25°	11454.4	11593.1	11404.9	11188.5	10833.5	10600.9	10564.4	10059.7	9030.8	7737.4	6130.8
27.5°	11742.7	11907.3	11587.8	11368.2	10962.6	10718.3	10671.0	10196.3	9047.1	7639.5	5877.8
30°	12109.7	12003.2	11722.3	11403.8	10971.2	10710.8	10650.4	10116.8	8885.6	7279.0	5382.9
32.5°	11964.4	11938.5	11657.7	11283.3	10879.8	10617.1	10536.4	9871.3	8442.3	6656.9	4682.3
35°	11624.3	11706.2	11471.6	11239.1	10737.7	10464.3	10352.3	9509.8	7773.9	5856.2	3902.1
37.5°	11425.3	11477.0	11328.4	11044.4	10547.2	10187.7	9975.7	8901.7	6899.1	4846.9	3149.9
40°	11120.8	11252.1	11109.0	10782.8	10209.2	9716.5	9347.3	7803.1	5746.5	3821.4	2463.2
42.5°	10787.2	10904.5	10767.7	10377.2	9566.8	8906.0	8292.7	6511.7	4499.2	2919.5	1847.8
45°	10351.3	10456.7	10211.4	9603.4	8456.2	7544.7	6932.4	5113.8	3393.0	2144.7	1216.1
47.5°	9565.8	9537.7	9190.2	8245.3	6832.3	6015.6	5303.2	3663.2	2255.6	1214.9	604.8
50°	7926.8	7665.3	7154.1	6057.6	4585.4	3703.0	3216.6	1890.8	1023.4	588.7	379.9
52.5°	5134.2	4842.6	4374.4	3361.8	2201.8	1767.0	1417.3	854.4	533.8	332.5	149.5
55°	2336.3	2129.6	1830.5	1358.0	944.9	785.6	665.1	432.5	286.3	123.8	52.8
57.5°	890.0	821.1	729.6	582.2	436.9	377.8	313.2	207.6	89.3	46.3	31.2
60°	400.3	371.3	341.1	266.9	187.2	134.4	102.2	55.9	37.7	26.9	20.4
62.5°	136.6	114.0	94.8	67.7	50.6	44.1	38.7	31.2	22.6	18.3	13.9
65°	39.8	38.7	36.5	32.4	25.9	23.7	22.6	18.3	13.9	11.8	9.6
67.5°	19.4	18.3	17.3	16.1	12.9	11.8	11.8	10.8	8.6	7.5	6.5
70°	8.6	8.6	7.5	7.5	6.5	6.5	6.5	5.3	5.3	5.3	5.3
72.5°	4.3	4.3	4.3	3.2	3.2	3.2	3.2	4.3	4.3	5.3	5.3
75°	1.0	2.2	2.2	2.2	2.2	3.2	3.2	4.3	4.3	5.3	5.3
77.5°	1.0	1.0	1.0	2.2	2.2	2.2	3.2	4.3	4.3	5.3	5.3
80°	0.0	1.0	1.0	2.2	2.2	2.2	3.2	3.2	4.3	5.3	5.3
82.5°	0.0	1.0	1.0	2.2	2.2	2.2	3.2	3.2	4.3	5.3	5.3
85°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.3	5.3	5.3
87.5°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192692

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6
2.5°	1559.3	1536.8	1447.5	1378.6	1346.2	1344.1	1272.0	1227.9	1150.4	1090.1	1033.0
5°	2050.1	1950.0	1769.1	1626.0	1557.2	1521.7	1379.6	1277.3	1143.9	1040.7	938.4
7.5°	2549.4	2358.8	2104.9	1832.7	1720.7	1651.9	1432.4	1268.7	1091.3	947.0	820.1
10°	3060.6	2724.8	2346.0	1986.5	1825.1	1708.9	1426.9	1205.3	1000.8	831.9	693.1
12.5°	3593.2	3063.7	2536.4	2086.6	1873.5	1720.7	1378.6	1112.7	890.0	710.2	577.9
15°	4042.0	3326.3	2656.9	2110.4	1858.4	1673.4	1275.2	995.4	771.6	596.2	475.7
17.5°	4388.5	3473.7	2679.5	2052.1	1774.6	1568.0	1141.7	866.2	646.8	491.8	372.3
20°	4562.8	3496.4	2608.6	1914.5	1622.7	1409.8	990.0	734.9	542.4	398.2	295.9
22.5°	4575.7	3390.9	2453.6	1736.9	1455.9	1239.7	865.2	633.9	475.7	357.3	280.8
25°	4407.8	3187.5	2246.0	1555.0	1285.0	1090.1	775.9	608.0	478.8	414.3	380.9
27.5°	4089.3	2905.5	2017.7	1373.1	1137.4	986.9	739.3	608.0	518.7	468.1	480.0
30°	3648.1	2546.2	1700.2	1125.6	925.5	794.2	581.1	455.3	357.3	298.1	287.3
32.5°	3075.5	2083.3	1318.3	831.9	674.7	572.5	392.9	285.1	230.4	224.9	218.4
35°	2531.1	1645.5	1000.8	614.4	497.1	404.6	250.8	167.8	152.9	144.2	137.8
37.5°	1999.5	1231.0	718.8	446.6	341.1	257.3	129.1	108.7	94.8	86.1	78.5
40°	1503.4	884.6	506.9	270.0	178.6	110.9	77.5	66.7	59.2	54.9	52.8
42.5°	1063.2	588.7	314.2	114.0	85.0	69.9	53.8	47.3	43.0	40.8	38.7
45°	617.7	365.8	127.0	66.7	53.8	48.5	39.8	35.5	33.4	31.2	30.2
47.5°	386.4	147.4	65.7	43.0	37.7	34.4	29.0	28.0	25.9	24.7	24.7
50°	156.0	65.7	40.8	30.2	26.9	25.9	22.6	21.6	19.4	19.4	19.4
52.5°	59.2	38.7	28.0	21.6	19.4	18.3	16.1	16.1	15.1	15.1	15.1
55°	34.4	25.9	19.4	15.1	13.9	13.9	12.9	12.9	11.8	11.8	11.8
57.5°	22.6	17.3	13.9	10.8	10.8	10.8	9.6	9.6	9.6	9.6	9.6
60°	15.1	11.8	9.6	8.6	8.6	8.6	8.6	9.6	9.6	9.6	9.6
62.5°	10.8	9.6	8.6	8.6	8.6	8.6	8.6	9.6	9.6	9.6	10.8
65°	8.6	7.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6	10.8	10.8
67.5°	6.5	6.5	6.5	6.5	7.5	7.5	8.6	9.6	9.6	9.6	10.8
70°	5.3	6.5	6.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6	10.8
72.5°	5.3	6.5	6.5	7.5	7.5	7.5	8.6	9.6	9.6	9.6	10.8
75°	5.3	6.5	6.5	7.5	7.5	7.5	8.6	9.6	9.6	9.6	10.8
77.5°	6.5	6.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6	10.8	10.8
80°	6.5	6.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6	10.8	10.8
82.5°	6.5	6.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6	10.8	10.8
85°	6.5	6.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6	10.8	10.8
87.5°	6.5	6.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6	9.6	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192692

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6
2.5°	1005.1	955.7	901.7	884.6	867.4	834.0	813.6	776.9	750.0	723.2	701.6
5°	870.5	792.0	726.5	698.4	671.5	625.2	593.0	554.2	523.0	496.1	471.4
7.5°	730.6	640.3	574.6	546.7	519.8	469.2	428.4	379.9	343.2	313.2	288.5
10°	601.5	515.5	444.5	411.1	379.9	327.1	288.5	249.6	218.4	192.7	170.0
12.5°	489.6	397.0	325.0	300.2	270.0	227.1	190.5	148.5	130.3	122.7	117.3
15°	379.9	297.1	236.7	214.1	187.2	146.4	130.3	122.7	117.3	114.0	109.7
17.5°	289.5	220.6	161.5	146.4	137.8	129.1	124.8	119.5	116.2	115.2	111.9
20°	227.1	166.8	151.7	147.4	147.4	145.2	142.1	142.1	140.9	144.2	144.2
22.5°	233.5	233.5	246.5	245.3	262.6	279.8	292.8	334.6	358.3	409.0	443.3
25°	407.8	446.6	491.8	505.7	539.1	588.7	640.3	704.9	750.0	798.5	817.9
27.5°	509.0	515.5	509.0	525.1	503.6	490.8	495.1	502.6	502.6	505.7	518.7
30°	301.3	316.4	330.4	341.1	335.8	330.4	328.3	312.0	312.0	305.6	300.2
32.5°	204.5	202.3	200.2	204.5	200.2	200.2	197.0	198.0	191.5	187.2	185.1
35°	139.9	133.4	126.0	127.0	122.7	121.7	118.3	118.3	114.0	111.9	110.9
37.5°	77.5	77.5	74.2	75.3	74.2	74.2	74.2	75.3	74.2	74.2	75.3
40°	52.8	52.8	51.6	52.8	51.6	52.8	53.8	53.8	53.8	53.8	52.8
42.5°	39.8	39.8	38.7	39.8	38.7	39.8	40.8	40.8	40.8	40.8	40.8
45°	31.2	31.2	31.2	31.2	31.2	31.2	31.2	32.4	32.4	31.2	31.2
47.5°	24.7	25.9	24.7	24.7	24.7	24.7	25.9	25.9	24.7	24.7	24.7
50°	20.4	20.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
52.5°	16.1	15.1	15.1	13.9	13.9	13.9	13.9	13.9	13.9	13.9	12.9
55°	11.8	11.8	10.8	10.8	10.8	11.8	11.8	11.8	11.8	10.8	10.8
57.5°	10.8	10.8	10.8	9.6	9.6	10.8	10.8	9.6	9.6	9.6	8.6
60°	9.6	10.8	9.6	9.6	9.6	9.6	9.6	8.6	8.6	8.6	7.5
62.5°	10.8	10.8	9.6	9.6	9.6	9.6	8.6	8.6	8.6	7.5	7.5
65°	10.8	10.8	10.8	9.6	9.6	9.6	9.6	8.6	8.6	7.5	7.5
67.5°	10.8	10.8	10.8	10.8	9.6	9.6	9.6	8.6	8.6	8.6	7.5
70°	10.8	10.8	10.8	10.8	10.8	9.6	9.6	9.6	8.6	8.6	7.5
72.5°	10.8	10.8	10.8	9.6	9.6	9.6	9.6	9.6	8.6	8.6	7.5
75°	10.8	10.8	10.8	9.6	9.6	9.6	9.6	8.6	8.6	8.6	7.5
77.5°	10.8	10.8	10.8	9.6	9.6	9.6	9.6	8.6	8.6	8.6	7.5
80°	10.8	10.8	10.8	9.6	9.6	9.6	9.6	8.6	8.6	8.6	7.5
82.5°	10.8	10.8	10.8	9.6	9.6	9.6	9.6	8.6	8.6	7.5	7.5
85°	10.8	10.8	9.6	9.6	9.6	9.6	8.6	8.6	7.5	7.5	6.5
87.5°	9.6	9.6	9.6	9.6	8.6	8.6	8.6	7.5	6.5	6.5	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192692

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6	1126.6
2.5°	675.8	671.5	668.2	674.7	672.5	645.6	649.0	647.8
5°	443.3	433.7	426.2	429.4	420.7	409.0	400.3	398.2
7.5°	263.7	252.9	246.5	240.0	237.8	222.7	216.3	220.6
10°	145.2	130.3	129.1	126.0	121.7	118.3	116.2	117.3
12.5°	111.9	110.9	108.7	107.6	105.4	104.4	103.2	102.2
15°	106.6	105.4	104.4	103.2	102.2	101.1	100.1	100.1
17.5°	109.7	109.7	108.7	107.6	107.6	108.7	107.6	106.6
20°	143.1	143.1	145.2	148.5	148.5	151.7	156.0	152.9
22.5°	464.9	488.6	517.7	526.3	576.8	617.7	693.1	659.7
25°	850.1	903.9	916.8	935.1	963.1	977.1	963.1	981.4
27.5°	516.5	534.8	536.9	538.1	544.6	543.4	529.5	538.1
30°	300.2	306.7	304.6	303.4	301.3	289.5	287.3	291.6
32.5°	188.4	186.2	185.1	184.1	184.1	177.6	180.8	178.6
35°	107.6	110.9	109.7	108.7	105.4	104.4	104.4	103.2
37.5°	72.0	73.2	72.0	71.0	68.9	67.7	66.7	65.7
40°	51.6	52.8	51.6	50.6	49.5	48.5	47.3	46.3
42.5°	38.7	39.8	38.7	38.7	36.5	35.5	34.4	33.4
45°	30.2	29.0	29.0	29.0	28.0	26.9	25.9	25.9
47.5°	24.7	24.7	24.7	23.7	22.6	22.6	22.6	21.6
50°	18.3	19.4	18.3	18.3	17.3	16.1	16.1	15.1
52.5°	12.9	12.9	11.8	11.8	10.8	9.6	9.6	9.6
55°	9.6	9.6	9.6	8.6	8.6	7.5	7.5	7.5
57.5°	8.6	7.5	7.5	7.5	6.5	6.5	5.3	5.3
60°	7.5	6.5	6.5	5.3	5.3	4.3	4.3	4.3
62.5°	6.5	5.3	5.3	5.3	4.3	4.3	4.3	4.3
65°	6.5	5.3	5.3	5.3	4.3	4.3	4.3	4.3
67.5°	6.5	6.5	5.3	5.3	5.3	4.3	4.3	4.3
70°	6.5	6.5	6.5	5.3	5.3	5.3	4.3	4.3
72.5°	7.5	6.5	6.5	6.5	5.3	5.3	5.3	5.3
75°	7.5	6.5	6.5	6.5	5.3	5.3	5.3	5.3
77.5°	7.5	6.5	6.5	6.5	5.3	5.3	5.3	5.3
80°	6.5	6.5	6.5	5.3	5.3	5.3	5.3	5.3
82.5°	6.5	6.5	6.5	6.5	5.3	5.3	5.3	5.3
85°	6.5	5.3	5.3	5.3	4.3	4.3	4.3	4.3
87.5°	5.3	4.3	4.3	3.2	3.2	3.2	2.2	2.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)