

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192696

Luminaire Tested: **LDA6A70930D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192696
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70930D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5797.6 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192696

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192696

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104	110	107	104	102		103	101	99			99	97	96			96
2	105	100	95	91	103	98	94	90		95	91	88			92	89	86			89
3	99	91	85	80	96	89	84	80		87	82	78			84	80	77			82
4	92	83	76	71	90	82	76	71		79	74	70			77	73	69			75
5	86	76	69	64	84	75	68	63		73	67	63			71	66	62			69
6	80	69	62	57	79	69	62	57		67	61	56			65	60	56			64
7	75	64	56	51	73	63	56	51		62	55	51			60	55	50			59
8	70	59	51	46	69	58	51	46		57	50	46			56	50	46			54
9	66	54	47	42	64	53	47	42		52	46	42			51	46	42			50
10	61	50	43	38	60	49	43	38		48	42	38			48	42	38			47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	89724	89724	89724
5°	173855	85499	28835
10°	295374	74820	12953
15°	455156	59683	20590
20°	658891	38842	35814
25°	966715	37478	46049
30°	1124034	35505	35290
35°	1137712	18805	18651
40°	941943	7092	7829
45°	711407	2411	2853
50°	486730	887	887
55°	67697	774	115
60°	1765	757	0
65°	454	1051	0
70°	192	1298	0
75°	0	1716	0
80°	0	2904	379
85°	0	5787	0

TEST NUMBER: P1192696

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.7	3.0
10°-20°	725.8	12.5
20°-30°	1655.7	28.6
30°-40°	1916.1	33.0
40°-50°	1155.5	19.9
50°-60°	157.0	2.7
60°-70°	5.1	0.1
70°-80°	5.5	0.1
80°-90°	5.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2553.2	44.0
0°-40°	4469.3	77.1
0°-60°	5781.8	99.7
0°-90°	5797.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5797.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1637	1637	1637	1637	1637	
5°	3159	2587	1554	850	524	368
15°	8020	4508	1052	324	363	2374
25°	15982	5342	620	745	761	7233
35°	17000	4073	281	287	279	10245
45°	9176	1109	31	38	37	7175
55°	708	8	8	6	1	1389
65°	4	5	8	5	0	5
75°	0	6	8	6	0	0
85°	0	6	9	6	0	0
90°	0	0	0	0	0	0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192696

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7
2.5°	2366.9	2345.0	2354.2	2330.1	2269.0	2256.3	2255.2	2239.1	2187.3	2146.9	2098.6
5°	3159.3	3158.2	3163.9	3112.2	3005.1	2971.5	2955.4	2916.3	2790.8	2694.0	2586.9
7.5°	4148.7	4141.8	4134.9	4040.4	3872.3	3807.7	3766.3	3624.7	3451.8	3280.3	3089.0
10°	5306.2	5302.8	5276.3	5110.5	4840.9	4722.3	4641.7	4417.1	4139.5	3895.3	3570.5
12.5°	6650.4	6619.2	6572.1	6329.0	5959.3	5830.4	5652.9	5297.0	4871.0	4496.5	4042.7
15°	8019.8	7974.9	7890.8	7578.8	7120.4	6900.3	6680.3	6211.6	5633.4	5089.7	4508.0
17.5°	9359.4	9309.8	9112.9	8583.1	8135.0	7866.7	7622.5	6978.6	6299.1	5600.0	4862.8
20°	11294.3	11114.7	10771.5	9936.5	9103.7	8619.9	8334.3	7653.6	6812.8	5998.5	5115.1
22.5°	13878.9	13480.5	12749.1	11392.3	10202.5	9504.5	9036.9	8131.5	7182.5	6258.7	5270.6
25°	15982.1	15801.3	14969.8	13039.3	11182.6	10360.2	9709.6	8511.7	7452.1	6432.7	5342.0
27.5°	17337.8	17292.8	16342.6	14403.1	11983.1	10903.9	10177.2	8762.8	7582.2	6469.5	5307.4
30°	17757.0	17827.3	16915.0	14866.1	12214.6	11013.4	10218.6	8766.2	7482.0	6302.6	5086.2
32.5°	17725.9	17729.4	16611.1	14466.3	11838.0	10695.4	9873.0	8474.8	7112.3	5884.4	4665.9
35°	17000.3	16821.7	15557.2	13238.6	10961.4	9953.7	9188.9	7910.4	6502.9	5255.6	4072.7
37.5°	15407.3	15173.5	13699.3	11666.3	9923.8	8992.0	8374.5	7169.8	5777.3	4584.1	3459.9
40°	13162.5	12830.8	11614.6	10204.8	8788.1	8087.8	7569.6	6341.7	5001.1	3925.2	2885.3
42.5°	10915.4	10753.1	9949.1	8803.1	7833.3	7174.4	6633.2	5474.5	4254.6	3275.7	2158.4
45°	9176.2	9036.9	8496.6	7741.1	6789.8	6188.6	5666.7	4570.3	3305.6	2197.6	1109.1
47.5°	7909.2	7796.3	7279.3	6485.6	5442.1	4784.5	4246.6	2997.0	1872.8	949.1	277.5
50°	5707.1	5591.9	5085.1	4166.1	3223.8	2673.3	2286.2	1338.3	531.0	192.4	28.8
52.5°	2797.7	2703.2	2358.8	1765.7	1185.2	852.3	623.1	251.1	61.1	20.7	13.8
55°	708.3	650.8	542.5	340.9	166.9	100.2	64.6	23.0	15.0	11.5	8.1
57.5°	40.3	39.1	35.7	26.5	19.6	17.3	15.0	11.5	8.1	6.9	5.8
60°	16.1	15.0	13.8	11.5	9.2	8.1	8.1	5.8	4.6	4.6	4.6
62.5°	6.9	6.9	6.9	5.8	4.6	4.6	4.6	3.5	4.6	4.6	4.6
65°	3.5	3.5	3.5	2.3	2.3	2.3	3.5	3.5	3.5	4.6	4.6
67.5°	2.3	1.2	1.2	1.2	2.3	2.3	2.3	3.5	3.5	4.6	4.6
70°	1.2	1.2	1.2	1.2	2.3	2.3	2.3	3.5	3.5	4.6	5.8
72.5°	0.0	1.2	1.2	1.2	2.3	2.3	2.3	3.5	3.5	4.6	5.8
75°	0.0	1.2	1.2	1.2	2.3	2.3	2.3	3.5	4.6	4.6	5.8
77.5°	0.0	1.2	1.2	1.2	2.3	2.3	2.3	3.5	4.6	4.6	5.8
80°	0.0	1.2	1.2	1.2	2.3	2.3	2.3	3.5	4.6	4.6	5.8
82.5°	0.0	0.0	1.2	1.2	2.3	2.3	2.3	3.5	4.6	4.6	5.8
85°	0.0	0.0	1.2	1.2	2.3	2.3	2.3	3.5	4.6	4.6	5.8
87.5°	0.0	0.0	1.2	1.2	2.3	2.3	2.3	3.5	3.5	4.6	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192696

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7
2.5°	2036.3	1994.9	1933.8	1893.5	1854.4	1817.4	1756.5	1722.0	1659.7	1602.2	1552.6
5°	2457.9	2354.2	2228.7	2121.6	2052.4	1984.5	1861.3	1770.3	1656.2	1553.7	1459.2
7.5°	2884.1	2700.9	2494.7	2318.6	2211.4	2106.6	1922.3	1774.9	1613.7	1467.4	1328.0
10°	3271.1	2995.9	2704.4	2452.2	2307.1	2171.2	1928.0	1732.3	1525.0	1344.1	1169.1
12.5°	3630.4	3253.8	2873.6	2544.3	2364.6	2201.1	1903.9	1664.3	1417.8	1203.6	999.8
15°	3950.7	3466.9	2997.0	2597.2	2386.4	2193.0	1847.5	1568.7	1291.1	1051.6	793.6
17.5°	4193.7	3599.4	3051.1	2589.2	2347.3	2131.9	1750.7	1448.9	1156.4	866.1	574.8
20°	4341.1	3655.7	3039.6	2527.1	2263.2	2035.1	1635.5	1318.8	993.9	665.8	506.7
22.5°	4403.3	3651.1	2985.4	2433.8	2159.5	1929.2	1525.0	1192.1	823.5	602.4	528.7
25°	4413.7	3604.0	2909.4	2331.2	2057.1	1827.9	1413.2	1048.1	715.2	619.6	592.0
27.5°	4334.2	3493.4	2766.6	2183.8	1913.1	1675.8	1246.3	832.7	671.5	617.3	635.7
30°	4099.2	3241.2	2514.3	1924.6	1663.1	1425.9	890.4	653.1	557.5	560.9	565.6
32.5°	3685.6	2821.9	2108.9	1545.7	1260.1	939.9	554.0	436.6	423.9	423.9	421.6
35°	3134.0	2309.4	1655.1	977.8	626.5	451.5	286.7	287.9	282.1	281.0	279.8
37.5°	2563.9	1822.2	1048.1	404.2	271.8	188.9	169.2	171.5	169.2	172.7	170.4
40°	2021.3	1125.3	382.4	129.0	95.6	92.2	94.5	96.8	96.8	99.1	99.1
42.5°	1174.8	373.2	100.2	51.8	51.8	49.5	50.6	52.9	54.1	55.2	54.1
45°	349.0	77.2	32.2	28.8	28.8	27.6	27.6	28.8	29.9	31.1	31.1
47.5°	55.2	21.9	18.4	16.1	16.1	16.1	16.1	16.1	17.3	17.3	18.4
50°	17.3	13.8	11.5	10.4	10.4	9.2	9.2	10.4	10.4	10.4	11.5
52.5°	10.4	8.1	8.1	6.9	8.1	8.1	6.9	8.1	8.1	8.1	9.2
55°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	8.1	8.1	8.1
57.5°	5.8	5.8	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
60°	5.8	5.8	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	8.1
62.5°	5.8	5.8	6.9	6.9	6.9	6.9	6.9	6.9	8.1	8.1	8.1
65°	5.8	5.8	6.9	6.9	6.9	6.9	6.9	8.1	8.1	8.1	8.1
67.5°	5.8	6.9	6.9	6.9	6.9	8.1	8.1	8.1	8.1	8.1	8.1
70°	5.8	6.9	6.9	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
72.5°	5.8	6.9	6.9	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
75°	6.9	6.9	6.9	8.1	8.1	8.1	8.1	8.1	8.1	8.1	9.2
77.5°	6.9	6.9	8.1	8.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2
80°	6.9	6.9	8.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2
82.5°	6.9	6.9	8.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2
85°	6.9	6.9	8.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2
87.5°	6.9	6.9	8.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192696

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7
2.5°	1510.0	1456.9	1431.6	1396.0	1370.7	1314.2	1291.1	1252.0	1219.7	1166.8	1170.2
5°	1378.7	1278.5	1210.5	1157.6	1120.7	1030.9	970.9	907.6	850.0	778.7	752.1
7.5°	1196.7	1073.4	969.8	906.5	859.2	739.4	607.0	503.3	425.1	368.5	346.7
10°	1014.8	854.6	689.9	592.0	524.0	408.8	350.1	322.5	297.2	266.0	245.3
12.5°	802.8	574.8	425.1	385.8	358.2	320.2	282.1	252.2	258.0	259.1	267.2
15°	548.3	413.6	366.2	339.8	309.9	287.9	300.7	308.7	323.7	324.8	335.2
17.5°	445.8	388.1	350.1	349.0	351.3	363.9	383.5	393.9	413.6	418.2	433.1
20°	445.8	412.4	444.6	444.6	450.4	467.6	492.9	507.9	529.9	537.9	556.3
22.5°	507.9	531.0	571.3	575.9	578.2	596.6	628.8	643.8	669.2	673.8	693.4
25°	619.6	640.3	677.3	680.7	681.9	695.7	719.8	727.9	745.2	735.9	747.5
27.5°	655.4	664.6	687.6	689.9	684.2	689.9	699.1	699.1	704.9	686.5	689.9
30°	575.9	578.2	589.7	590.9	578.2	580.5	581.7	580.5	579.4	559.8	559.8
32.5°	427.4	427.4	442.3	438.9	425.1	428.5	428.5	428.5	427.4	411.3	408.8
35°	283.3	284.4	297.2	294.9	284.4	286.7	286.7	290.2	286.7	277.5	275.2
37.5°	172.7	173.8	179.7	180.9	177.4	178.6	179.7	178.6	180.9	176.3	173.8
40°	100.2	102.5	107.1	108.3	107.1	107.1	108.3	109.4	114.0	108.3	106.0
42.5°	58.8	60.0	62.3	62.3	62.3	62.3	63.4	64.6	65.7	64.6	63.4
45°	33.4	34.5	35.7	35.7	36.8	35.7	36.8	36.8	38.0	36.8	36.8
47.5°	19.6	19.6	20.7	20.7	21.9	20.7	21.9	21.9	21.9	20.7	20.7
50°	11.5	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7	11.5	11.5
52.5°	9.2	9.2	9.2	9.2	9.2	8.1	8.1	8.1	8.1	6.9	6.9
55°	8.1	8.1	8.1	8.1	8.1	8.1	6.9	5.8	5.8	4.6	4.6
57.5°	6.9	8.1	8.1	8.1	8.1	6.9	6.9	5.8	4.6	3.5	3.5
60°	8.1	8.1	8.1	8.1	6.9	6.9	6.9	5.8	4.6	3.5	3.5
62.5°	8.1	8.1	8.1	8.1	8.1	6.9	6.9	5.8	4.6	3.5	3.5
65°	8.1	8.1	8.1	8.1	8.1	6.9	6.9	5.8	4.6	3.5	3.5
67.5°	8.1	8.1	8.1	8.1	8.1	6.9	6.9	5.8	4.6	4.6	3.5
70°	8.1	9.2	9.2	8.1	8.1	8.1	6.9	5.8	5.8	4.6	3.5
72.5°	8.1	9.2	9.2	8.1	8.1	8.1	6.9	5.8	5.8	4.6	3.5
75°	9.2	9.2	9.2	9.2	8.1	8.1	6.9	6.9	5.8	4.6	3.5
77.5°	9.2	9.2	9.2	9.2	8.1	8.1	6.9	6.9	5.8	4.6	3.5
80°	9.2	9.2	9.2	9.2	9.2	8.1	8.1	6.9	5.8	4.6	4.6
82.5°	9.2	9.2	9.2	9.2	9.2	8.1	8.1	6.9	5.8	4.6	4.6
85°	9.2	9.2	9.2	9.2	9.2	8.1	8.1	6.9	5.8	4.6	3.5
87.5°	9.2	9.2	9.2	9.2	8.1	8.1	6.9	6.9	5.8	4.6	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192696

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7	1636.7
2.5°	1127.6	1101.0	1089.5	1107.9	1098.7	1071.1	1076.9	1059.6
5°	672.7	632.3	607.0	618.5	581.7	548.3	548.3	524.0
7.5°	324.8	312.2	305.3	307.6	299.5	289.0	283.3	283.3
10°	228.1	223.5	224.6	224.6	231.5	230.4	233.8	232.7
12.5°	270.6	272.9	274.1	278.7	284.4	284.4	287.9	285.6
15°	346.7	344.4	351.3	352.4	361.6	362.8	367.4	362.8
17.5°	441.2	445.8	452.7	451.5	469.9	471.1	471.1	469.9
20°	567.9	571.3	578.2	580.5	602.4	604.7	612.7	613.9
22.5°	706.0	706.0	709.5	714.1	734.8	735.9	739.4	739.4
25°	753.2	746.3	747.5	753.2	764.9	760.1	763.7	761.3
27.5°	692.2	681.9	679.6	687.6	695.7	683.0	687.6	687.6
30°	562.1	552.9	550.6	558.6	564.4	550.6	555.2	557.5
32.5°	411.3	405.4	404.2	410.0	414.7	403.1	407.7	411.3
35°	277.5	275.2	272.9	274.1	281.0	271.8	276.4	278.7
37.5°	176.3	171.5	172.7	175.0	179.7	173.8	178.6	178.6
40°	108.3	106.0	106.0	108.3	110.6	106.0	108.3	109.4
42.5°	63.4	63.4	63.4	64.6	65.7	63.4	63.4	64.6
45°	36.8	35.7	35.7	36.8	38.0	35.7	36.8	36.8
47.5°	20.7	19.6	19.6	20.7	20.7	19.6	20.7	20.7
50°	11.5	10.4	10.4	11.5	11.5	10.4	10.4	10.4
52.5°	5.8	5.8	5.8	5.8	5.8	5.8	4.6	4.6
55°	3.5	3.5	2.3	2.3	2.3	2.3	2.3	1.2
57.5°	2.3	2.3	1.2	1.2	1.2	1.2	0.0	0.0
60°	2.3	2.3	1.2	1.2	1.2	0.0	0.0	0.0
62.5°	2.3	2.3	1.2	1.2	1.2	0.0	0.0	0.0
65°	2.3	2.3	1.2	1.2	1.2	0.0	0.0	0.0
67.5°	2.3	2.3	1.2	1.2	1.2	0.0	0.0	0.0
70°	3.5	2.3	2.3	1.2	1.2	1.2	0.0	0.0
72.5°	3.5	2.3	2.3	2.3	1.2	1.2	0.0	0.0
75°	3.5	2.3	2.3	2.3	1.2	1.2	0.0	0.0
77.5°	3.5	2.3	2.3	2.3	1.2	1.2	1.2	0.0
80°	3.5	2.3	2.3	2.3	1.2	1.2	1.2	1.2
82.5°	3.5	2.3	2.3	2.3	1.2	1.2	1.2	1.2
85°	3.5	2.3	2.3	2.3	1.2	1.2	1.2	0.0
87.5°	3.5	2.3	2.3	2.3	1.2	1.2	1.2	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)