

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192171

Luminaire Tested: **LDA6A40927D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192171
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26673)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40927D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3253.3 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.56 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192171

CATALOG NUMBER: LDA6A40927D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192171

CATALOG NUMBER: LDA6A40927D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82		
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	55	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	50489	50489	50489
5°	101100	48024	12877
10°	169553	41059	3524
15°	258923	30778	5114
20°	370980	22507	60234
25°	551530	37345	30891
30°	644637	16515	4805
35°	648197	3440	2543
40°	536713	1918	1474
45°	401747	1225	1163
50°	281552	878	674
55°	45255	679	535
60°	2774	691	428
65°	817	921	415
70°	513	1010	625
75°	318	1186	826
80°	253	1768	1231
85°	503	3522	1510



TEST NUMBER: P1192171

CATALOG NUMBER: LDA6A40927D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.4	2.9
10°-20°	402.9	12.4
20°-30°	969.5	29.8
30°-40°	1033.0	31.8
40°-50°	644.1	19.8
50°-60°	94.1	2.9
60°-70°	6.0	0.2
70°-80°	4.7	0.1
80°-90°	3.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1467.8	45.1
0°-40°	2500.8	76.9
0°-60°	3239.1	99.6
0°-90°	3253.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3253.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	921	921	921	921	921	
5°	1837	1474	873	435	234	213
15°	4562	2535	542	84	90	1354
25°	9118	3015	617	640	511	4109
35°	9686	2237	51	47	38	5844
45°	5182	654	16	18	15	4079
55°	474	11	7	8	6	837
65°	6	5	7	6	3	9
75°	2	3	6	6	4	2
85°	1	3	6	5	2	1
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192171

CATALOG NUMBER: LDA6A40927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	921.0	921.0	921.0	921.0	921.0	921.0	921.0	921.0	921.0	921.0	921.0
2.5°	1370.0	1323.4	1339.1	1304.4	1291.7	1294.9	1269.6	1249.0	1238.0	1211.1	1183.4
5°	1837.2	1783.4	1799.3	1747.1	1714.7	1707.6	1668.0	1623.8	1584.3	1524.2	1473.6
7.5°	2404.0	2337.7	2348.7	2270.4	2204.8	2182.7	2122.6	2036.5	1956.5	1854.6	1757.4
10°	3045.9	2983.5	2980.3	2861.0	2748.7	2705.2	2617.5	2475.2	2339.2	2185.8	2026.2
12.5°	3802.5	3708.4	3692.6	3539.3	3371.7	3300.5	3178.0	2960.5	2745.5	2521.8	2291.8
15°	4562.2	4461.0	4435.8	4242.8	4008.9	3913.2	3749.5	3460.2	3163.7	2847.5	2535.3
17.5°	5371.8	5209.6	5072.9	4849.9	4579.6	4481.5	4269.7	3898.9	3525.8	3135.3	2717.9
20°	6359.1	6178.0	5986.0	5605.0	5109.2	4916.4	4684.0	4265.7	3800.1	3348.8	2853.0
22.5°	7712.5	7415.2	7007.4	6394.7	5713.2	5438.1	5079.2	4537.7	4011.2	3504.5	2943.2
25°	9118.1	8707.8	8259.6	7318.0	6265.8	5929.8	5457.9	4745.6	4178.8	3619.1	3015.2
27.5°	9927.6	9598.0	9089.6	8103.0	6714.1	6272.9	5729.0	4902.2	4285.5	3674.4	3035.6
30°	10183.7	9916.6	9454.9	8443.0	6864.3	6338.5	5754.3	4903.7	4234.1	3578.0	2917.1
32.5°	10077.0	9823.3	9312.5	8230.4	6589.1	6105.3	5538.5	4704.5	3981.2	3281.5	2612.7
35°	9685.7	9350.5	8729.9	7524.4	6121.2	5640.5	5110.9	4348.0	3592.2	2879.2	2237.3
37.5°	8807.4	8459.5	7753.6	6619.2	5517.9	5099.8	4673.7	3948.8	3200.9	2513.2	1909.9
40°	7499.9	7132.2	6552.0	5755.9	4867.4	4581.9	4222.3	3506.9	2786.7	2154.3	1607.2
42.5°	6180.4	5944.8	5601.0	4970.2	4351.1	4069.7	3720.3	3025.3	2388.2	1784.2	1220.6
45°	5182.0	4995.5	4767.0	4368.5	3784.3	3519.5	3194.6	2540.8	1861.7	1192.1	654.5
47.5°	4515.6	4287.8	4088.7	3644.4	3017.5	2695.8	2351.0	1674.4	1073.5	517.0	181.0
50°	3301.3	3027.0	2841.2	2343.1	1774.0	1506.0	1253.8	777.1	347.8	115.4	30.0
52.5°	1673.6	1466.5	1357.3	1025.3	677.5	506.7	372.4	160.5	68.8	22.9	17.4
55°	473.5	381.0	341.5	225.3	122.5	86.2	56.2	28.5	20.6	15.8	11.1
57.5°	49.0	41.9	39.5	32.4	26.1	24.5	22.1	17.4	13.5	11.1	7.1
60°	25.3	22.9	22.1	19.8	16.6	15.0	14.2	11.8	8.7	6.3	5.6
62.5°	13.5	12.7	11.1	10.3	8.7	8.7	7.9	6.3	5.6	5.6	4.7
65°	6.3	6.3	6.3	6.3	5.6	5.6	4.7	4.7	4.7	4.7	4.7
67.5°	4.7	4.7	4.7	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
70°	3.2	3.2	3.2	3.2	2.4	2.4	2.4	2.4	2.4	3.2	3.2
72.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	2.4	2.4	3.2	3.2
75°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	2.4	2.4	3.2	3.2
77.5°	0.8	0.8	1.5	1.5	1.5	1.5	1.5	2.4	2.4	3.2	3.2
80°	0.8	0.8	0.8	0.8	1.5	1.5	1.5	2.4	2.4	3.2	3.2
82.5°	0.8	0.8	0.8	0.8	1.5	1.5	1.5	2.4	2.4	3.2	3.2
85°	0.8	0.8	0.8	0.8	1.5	1.5	1.5	1.5	2.4	3.2	3.2
87.5°	0.0	0.0	0.8	0.8	0.8	1.5	1.5	1.5	2.4	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192171

CATALOG NUMBER: LDA6A40927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	921.0	921.0	921.0	921.0	921.0	921.0	921.0	921.0	921.0	921.0	921.0
2.5°	1150.3	1130.5	1098.8	1067.3	1057.8	1031.7	1000.8	964.5	930.4	903.6	877.5
5°	1392.1	1339.1	1279.9	1200.1	1171.6	1127.3	1060.9	989.8	928.1	872.7	821.4
7.5°	1633.2	1533.7	1425.3	1309.9	1261.0	1195.3	1090.9	990.5	898.9	817.4	740.8
10°	1846.7	1693.3	1540.8	1381.8	1313.1	1228.4	1089.4	961.3	844.3	737.6	641.2
12.5°	2043.6	1831.7	1629.3	1425.3	1339.1	1237.2	1065.6	910.7	771.6	646.6	533.6
15°	2215.9	1943.2	1692.6	1445.9	1336.8	1219.8	1019.0	841.2	686.2	542.3	419.8
17.5°	2336.0	2006.4	1710.7	1424.5	1304.4	1170.0	947.8	758.1	588.2	437.2	297.3
20°	2408.0	2023.0	1693.3	1377.9	1245.1	1105.9	881.5	689.3	524.1	385.8	268.8
22.5°	2447.5	2030.9	1680.7	1361.4	1226.1	1093.3	884.7	701.3	559.7	466.4	456.9
25°	2487.0	2056.2	1702.8	1380.3	1253.8	1130.5	931.3	743.9	647.5	617.4	627.7
27.5°	2484.7	2040.4	1682.3	1362.9	1241.1	1113.0	890.9	694.0	627.7	581.0	542.3
30°	2343.9	1890.2	1524.2	1185.0	1045.9	875.1	593.7	407.9	312.3	260.9	234.7
32.5°	2018.3	1541.6	1164.5	823.8	687.8	497.3	255.3	134.3	115.4	102.8	91.7
35°	1677.6	1227.7	876.7	519.4	345.4	189.0	87.7	56.9	53.0	51.4	50.6
37.5°	1383.5	970.8	576.3	207.9	124.2	70.4	40.3	36.4	35.6	36.4	35.6
40°	1091.7	640.4	228.5	69.5	38.0	30.9	28.5	26.1	26.1	26.8	26.1
42.5°	653.7	238.8	69.5	26.1	24.5	22.1	21.3	20.6	19.8	20.6	20.6
45°	215.8	60.9	22.9	18.2	17.4	16.6	15.8	15.8	15.8	15.8	16.6
47.5°	49.0	21.3	15.8	13.5	13.5	12.7	12.7	11.8	12.7	12.7	13.5
50°	18.9	13.5	11.1	10.3	10.3	9.5	9.5	9.5	9.5	10.3	10.3
52.5°	11.8	9.5	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	8.7
55°	7.9	7.1	6.3	6.3	6.3	6.3	6.3	7.1	7.1	7.1	7.1
57.5°	5.6	5.6	5.6	5.6	6.3	5.6	6.3	5.6	5.6	6.3	7.1
60°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	6.3	6.3	7.1
62.5°	4.7	5.6	5.6	5.6	5.6	5.6	5.6	6.3	6.3	6.3	7.1
65°	4.7	4.7	5.6	5.6	5.6	5.6	6.3	6.3	6.3	7.1	7.1
67.5°	3.9	4.7	4.7	5.6	5.6	5.6	5.6	6.3	6.3	6.3	7.1
70°	3.9	3.9	4.7	4.7	4.7	4.7	5.6	5.6	5.6	6.3	6.3
72.5°	3.9	3.9	4.7	4.7	4.7	4.7	4.7	5.6	5.6	5.6	6.3
75°	3.9	3.9	4.7	4.7	4.7	4.7	4.7	5.6	5.6	5.6	6.3
77.5°	3.9	3.9	4.7	4.7	4.7	4.7	4.7	5.6	5.6	5.6	6.3
80°	3.9	3.9	4.7	4.7	4.7	4.7	5.6	5.6	5.6	5.6	6.3
82.5°	3.9	3.9	4.7	4.7	4.7	4.7	4.7	5.6	5.6	5.6	5.6
85°	3.9	3.9	4.7	4.7	4.7	4.7	4.7	4.7	5.6	5.6	5.6
87.5°	3.9	3.9	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192171

CATALOG NUMBER: LDA6A40927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	921.0	921.0	921.0	921.0	921.0	921.0	921.0	921.0	921.0	921.0	921.0
2.5°	842.7	810.3	794.4	770.8	772.3	732.8	717.8	689.3	673.6	656.9	638.0
5°	759.0	702.0	661.6	630.1	612.7	561.2	526.5	481.4	434.8	389.8	352.6
7.5°	653.7	578.6	517.0	476.7	452.2	348.6	282.3	229.3	208.7	192.9	177.0
10°	536.8	443.5	334.4	279.1	245.0	196.1	176.3	146.3	124.9	105.1	93.3
12.5°	419.0	276.7	200.0	183.4	171.6	127.2	100.4	93.3	75.9	71.9	70.4
15°	263.2	181.9	141.5	121.7	106.0	88.6	81.5	80.6	83.8	84.6	83.8
17.5°	186.6	145.5	106.7	104.3	104.3	113.9	115.4	122.5	128.9	134.3	135.2
20°	239.6	215.0	250.6	266.4	294.1	328.0	377.8	447.5	508.3	570.0	617.4
22.5°	458.5	512.3	591.3	619.0	665.7	738.4	807.1	871.2	936.0	984.2	994.5
25°	674.3	711.5	758.1	747.8	762.0	758.1	719.4	667.2	639.5	588.9	571.5
27.5°	516.2	477.5	445.1	407.9	389.8	355.0	305.1	273.5	245.0	216.6	204.7
30°	210.3	184.2	165.2	151.8	143.9	124.9	115.4	105.1	100.4	93.3	89.3
32.5°	82.2	77.5	75.1	72.7	71.9	69.5	67.2	64.0	63.3	63.3	60.1
35°	49.0	49.0	49.0	48.2	49.0	48.2	47.4	46.6	47.4	47.4	45.1
37.5°	34.8	35.6	35.6	35.6	35.6	35.6	35.6	35.6	34.8	34.8	32.4
40°	26.1	26.8	27.7	26.8	27.7	27.7	26.8	26.1	26.1	26.1	24.5
42.5°	21.3	21.3	21.3	21.3	22.1	21.3	21.3	21.3	21.3	21.3	20.6
45°	17.4	17.4	17.4	17.4	18.2	18.2	17.4	17.4	18.2	18.2	17.4
47.5°	13.5	13.5	13.5	13.5	13.5	13.5	13.5	12.7	12.7	12.7	11.8
50°	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	11.1	10.3	10.3
52.5°	8.7	8.7	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	8.7
55°	7.9	7.9	8.7	8.7	8.7	8.7	8.7	7.9	7.9	7.9	7.1
57.5°	7.1	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.1	7.1	6.3
60°	7.1	7.1	7.9	7.9	7.9	7.9	7.1	7.1	6.3	6.3	5.6
62.5°	7.1	7.1	7.9	7.9	7.9	7.1	7.1	6.3	6.3	5.6	5.6
65°	7.1	7.9	7.9	7.9	7.9	7.1	7.1	6.3	6.3	5.6	5.6
67.5°	7.1	7.9	7.9	7.9	7.9	7.1	7.1	6.3	6.3	5.6	5.6
70°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	6.3	6.3	5.6	5.6
72.5°	6.3	7.1	7.1	7.1	7.1	7.1	6.3	6.3	6.3	5.6	5.6
75°	6.3	6.3	6.3	6.3	7.1	6.3	6.3	6.3	5.6	5.6	4.7
77.5°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	5.6	5.6	5.6	4.7
80°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	5.6	5.6	4.7	4.7
82.5°	6.3	6.3	6.3	6.3	6.3	6.3	5.6	5.6	4.7	4.7	4.7
85°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	4.7	4.7	3.9	3.9
87.5°	5.6	5.6	5.6	5.6	5.6	4.7	4.7	3.9	3.2	3.2	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192171

CATALOG NUMBER: LDA6A40927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	921.0	921.0	921.0	921.0	921.0	921.0	921.0	921.0
2.5°	617.4	603.9	600.9	600.9	593.7	579.5	577.1	572.4
5°	312.3	279.1	272.7	265.6	253.8	239.6	235.6	234.0
7.5°	161.3	147.0	144.6	139.9	132.8	125.7	124.2	123.3
10°	94.8	86.2	82.2	75.1	68.0	64.0	64.0	63.3
12.5°	70.4	70.4	70.4	70.4	70.4	70.4	70.4	70.4
15°	85.4	87.7	87.7	88.6	89.3	90.1	91.7	90.1
17.5°	143.9	155.7	154.9	156.6	162.0	169.2	166.0	169.9
20°	698.9	789.7	815.8	842.0	921.0	995.2	980.2	1032.5
22.5°	1004.0	1031.7	1020.6	1013.5	1030.1	1021.4	1058.5	1034.0
25°	538.3	532.9	532.9	509.1	513.8	502.0	517.8	510.7
27.5°	198.4	181.0	179.4	168.4	175.5	158.9	163.7	160.5
30°	85.4	86.2	83.0	80.6	78.3	76.6	76.6	75.9
32.5°	58.5	58.5	56.9	55.3	53.8	52.2	51.4	50.6
35°	43.5	43.5	41.9	41.1	40.3	38.8	38.0	38.0
37.5°	31.6	31.6	30.9	30.0	28.5	27.7	26.8	26.8
40°	24.5	23.8	22.9	22.9	21.3	21.3	20.6	20.6
42.5°	19.8	19.8	19.8	18.9	18.2	17.4	17.4	17.4
45°	17.4	17.4	16.6	15.8	15.8	15.8	15.0	15.0
47.5°	11.8	11.8	11.1	11.1	10.3	10.3	9.5	9.5
50°	9.5	9.5	9.5	9.5	8.7	7.9	7.9	7.9
52.5°	8.7	7.9	7.9	7.9	7.1	7.1	6.3	6.3
55°	7.1	7.1	6.3	6.3	5.6	5.6	5.6	5.6
57.5°	6.3	5.6	5.6	5.6	4.7	4.7	4.7	4.7
60°	5.6	4.7	4.7	4.7	3.9	3.9	3.9	3.9
62.5°	4.7	4.7	4.7	4.7	3.9	3.9	3.9	3.9
65°	4.7	4.7	4.7	3.9	3.9	3.9	3.9	3.2
67.5°	4.7	4.7	4.7	4.7	3.9	3.9	3.9	3.9
70°	4.7	4.7	4.7	4.7	3.9	3.9	3.9	3.9
72.5°	4.7	4.7	4.7	4.7	3.9	3.9	3.9	3.9
75°	4.7	4.7	4.7	4.7	3.9	3.9	3.9	3.9
77.5°	4.7	3.9	3.9	3.9	3.9	3.9	3.9	3.9
80°	4.7	3.9	3.9	3.9	3.9	3.2	3.2	3.9
82.5°	3.9	3.9	3.9	3.9	3.2	3.2	3.2	3.2
85°	3.2	3.2	3.2	3.2	2.4	2.4	2.4	2.4
87.5°	2.4	1.5	1.5	1.5	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)