

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192698

Luminaire Tested: **LDA6A70930D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192698
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26689)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70930D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5340.4 lumens
Efficiency: N/A
Efficacy: 68.4 lumens/watt
Spacing Criteria (0/90/45): 2.34 / 0.96 / 1.3
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192698

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192698

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104	110	107	104	102		103	101	99			99	97	96			96
2	105	100	95	91	103	98	94	90		95	91	88			92	89	86			89
3	99	91	85	80	97	90	84	80		87	82	78			84	80	77			82
4	92	83	76	71	90	82	76	71		80	74	70			77	73	69			76
5	86	76	69	64	84	75	68	63		73	67	63			71	66	62			70
6	80	70	62	57	79	69	62	57		67	61	57			66	60	56			64
7	75	64	57	51	74	63	56	51		62	56	51			60	55	51			59
8	70	59	52	47	69	58	51	46		57	51	46			56	50	46			55
9	66	54	47	42	64	54	47	42		53	46	42			52	46	42			51
10	62	50	43	38	61	50	43	38		49	43	38			48	42	38			47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	83338	83338	83338
5°	162937	79215	28896
10°	274249	68013	6413
15°	417658	51504	10522
20°	603528	41724	117377
25°	898201	67504	33921
30°	1037451	23111	6710
35°	1037776	5166	3621
40°	848218	2884	2226
45°	642315	1876	1427
50°	426570	1279	981
55°	68576	1099	774
60°	4287	1140	636
65°	1349	1492	752
70°	737	1667	930
75°	487	1949	1228
80°	379	2904	1831
85°	755	5787	2201

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192698

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.7	3.0
10°-20°	678.5	12.7
20°-30°	1597.3	29.9
30°-40°	1682.9	31.5
40°-50°	1049.3	19.6
50°-60°	150.8	2.8
60°-70°	9.6	0.2
70°-80°	7.6	0.1
80°-90°	5.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2434.5	45.6
0°-40°	4117.4	77.1
0°-60°	5317.5	99.6
0°-90°	5340.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5340.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1520	1520	1520	1520	1520	
5°	2961	2397	1440	748	525	343
15°	7359	4166	908	158	185	2191
25°	14849	4994	1116	807	561	6682
35°	15507	3658	77	72	54	9354
45°	8285	1012	24	26	18	6484
55°	718	18	12	13	8	1289
65°	10	8	12	9	6	15
75°	2	6	9	9	6	3
85°	1	6	9	7	4	1
90°	0	0	0	0	0	

TEST NUMBER: P1192698

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2
2.5°	2219.2	2204.3	2208.9	2174.3	2128.2	2149.0	2097.1	2098.3	2066.1	1984.2	1948.6
5°	2960.9	2958.6	2955.2	2891.7	2810.1	2819.3	2743.2	2714.4	2631.5	2487.5	2396.7
7.5°	3882.2	3883.4	3866.1	3711.8	3620.8	3615.0	3495.3	3408.8	3254.5	3027.6	2861.8
10°	4926.7	4959.0	4927.9	4690.6	4521.4	4523.7	4308.3	4142.5	3894.9	3564.4	3328.3
12.5°	6153.3	6157.9	6109.5	5797.4	5539.5	5519.9	5230.9	4914.1	4537.5	4105.7	3762.4
15°	7359.1	7391.3	7329.1	6944.5	6585.1	6531.1	6162.5	5744.4	5276.9	4637.7	4165.5
17.5°	8696.1	8645.5	8480.8	7930.2	7498.4	7418.9	7022.7	6475.7	5879.3	5106.5	4486.9
20°	10345.3	10362.5	10013.7	9191.3	8461.3	8151.4	7691.9	7093.0	6349.0	5450.7	4701.0
22.5°	12701.5	12608.3	11859.7	10529.6	9432.0	9018.6	8363.3	7537.5	6700.3	5712.2	4861.2
25°	14849.4	14604.1	13914.3	12084.3	10366.0	9854.6	9176.4	7916.4	6991.7	5905.7	4993.6
27.5°	16082.9	15973.5	15191.5	13345.3	11120.3	10400.6	9445.8	8195.1	7164.4	6001.2	5031.6
30°	16389.2	16408.7	15713.2	13763.5	11298.9	10476.6	9489.7	8187.0	7048.2	5830.8	4812.7
32.5°	16310.8	16205.0	15335.4	13301.6	10823.3	10074.7	9061.2	7820.9	6585.1	5322.9	4268.0
35°	15507.0	15351.5	14281.7	12100.5	10016.0	9288.1	8369.1	7220.9	5939.1	4675.7	3657.6
37.5°	13977.6	13798.0	12563.3	10658.6	9047.4	8431.2	7636.6	6552.9	5286.1	4072.3	3121.0
40°	11852.8	11629.4	10597.5	9276.6	8006.3	7575.6	6904.1	5790.5	4609.0	3501.0	2625.7
42.5°	9866.1	9759.2	9139.5	8006.3	7150.6	6734.8	6057.7	5021.2	3934.0	2917.2	1944.0
45°	8285.0	8213.6	7802.4	7082.7	6214.3	5825.0	5187.0	4175.8	2993.1	1964.7	1012.3
47.5°	7251.9	7070.0	6668.1	5912.6	4947.5	4462.7	3854.6	2751.3	1688.3	870.7	310.9
50°	5001.7	5018.9	4565.1	3732.5	2911.4	2501.3	2066.1	1265.7	558.5	190.0	54.1
52.5°	2633.8	2439.2	2120.1	1583.5	1102.2	840.8	613.9	253.4	101.4	38.0	28.8
55°	717.5	630.0	503.3	355.9	192.3	134.7	88.7	47.2	33.4	26.5	18.4
57.5°	70.3	66.9	61.0	49.5	42.6	39.1	35.7	28.8	23.0	16.1	11.5
60°	39.1	38.0	35.7	31.1	27.6	25.3	23.0	19.6	13.8	10.4	9.2
62.5°	21.9	20.7	19.6	17.3	15.0	13.8	13.8	11.5	9.2	8.1	8.1
65°	10.4	10.4	10.4	10.4	10.4	9.2	8.1	8.1	8.1	8.1	8.1
67.5°	8.1	8.1	8.1	6.9	6.9	6.9	6.9	6.9	6.9	5.8	6.9
70°	4.6	4.6	5.8	4.6	4.6	4.6	4.6	4.6	4.6	4.6	5.8
72.5°	2.3	3.5	3.5	3.5	3.5	3.5	3.5	3.5	4.6	4.6	5.8
75°	2.3	2.3	2.3	2.3	3.5	3.5	3.5	3.5	4.6	4.6	5.8
77.5°	2.3	2.3	2.3	2.3	2.3	2.3	3.5	3.5	4.6	4.6	5.8
80°	1.2	1.2	1.2	2.3	2.3	2.3	2.3	3.5	4.6	4.6	5.8
82.5°	1.2	1.2	1.2	1.2	2.3	2.3	2.3	3.5	4.6	4.6	5.8
85°	1.2	1.2	1.2	1.2	2.3	2.3	2.3	3.5	3.5	4.6	5.8
87.5°	0.0	0.0	1.2	1.2	2.3	2.3	2.3	3.5	3.5	4.6	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192698

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2
2.5°	1911.8	1855.3	1798.9	1742.4	1740.1	1706.7	1657.3	1591.5	1537.5	1491.5	1446.4
5°	2305.6	2189.3	2073.0	1956.6	1922.1	1862.2	1755.2	1634.2	1530.6	1439.5	1352.0
7.5°	2700.6	2504.8	2320.6	2138.7	2066.1	1975.0	1808.1	1633.1	1483.3	1349.7	1219.5
10°	3053.1	2768.5	2509.4	2253.7	2149.0	2030.4	1805.8	1583.5	1393.5	1221.8	1056.0
12.5°	3377.8	2981.6	2653.5	2330.9	2188.1	2044.2	1770.1	1505.3	1278.3	1073.3	882.2
15°	3663.4	3177.5	2754.7	2365.4	2190.4	2017.7	1695.2	1397.0	1142.5	907.5	700.1
17.5°	3867.3	3275.2	2788.2	2334.4	2130.6	1937.1	1584.6	1265.7	991.6	746.3	545.9
20°	3991.6	3315.7	2770.8	2276.9	2060.3	1859.9	1503.0	1193.1	927.1	715.2	579.2
22.5°	4073.5	3354.8	2777.9	2275.7	2059.2	1870.2	1537.5	1247.3	1030.7	916.7	900.6
25°	4160.9	3410.0	2828.5	2327.5	2125.9	1950.9	1628.5	1345.1	1164.3	1116.0	1122.9
27.5°	4156.3	3385.8	2780.2	2282.6	2070.7	1893.4	1515.6	1157.4	988.2	852.3	802.7
30°	3908.7	3106.0	2450.7	1893.4	1643.4	1425.7	928.2	603.5	416.9	365.1	313.2
32.5°	3329.5	2516.3	1832.3	1309.4	1028.4	768.2	365.1	193.4	164.6	138.2	125.5
35°	2768.5	2006.2	1370.5	791.2	499.8	309.7	131.3	86.4	81.8	77.2	77.2
37.5°	2288.4	1575.4	885.6	334.0	183.1	111.7	63.3	57.5	55.2	54.1	54.1
40°	1789.7	1027.3	383.5	110.6	58.7	50.6	44.9	42.6	41.4	40.3	41.4
42.5°	1056.0	413.4	111.7	41.4	39.1	36.8	33.4	32.2	32.2	31.1	32.2
45°	359.3	107.1	36.8	29.9	27.6	27.6	25.3	25.3	25.3	24.2	26.5
47.5°	93.3	33.4	24.2	21.9	20.7	20.7	19.6	19.6	19.6	19.6	20.7
50°	32.2	21.9	17.3	16.1	15.0	16.1	15.0	15.0	15.0	15.0	16.1
52.5°	19.6	15.0	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7
55°	12.7	11.5	10.4	10.4	10.4	10.4	10.4	11.5	11.5	11.5	11.5
57.5°	10.4	9.2	9.2	9.2	9.2	9.2	10.4	9.2	9.2	10.4	11.5
60°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.4	10.4	11.5
62.5°	8.1	9.2	9.2	9.2	9.2	9.2	9.2	10.4	10.4	10.4	11.5
65°	8.1	8.1	8.1	9.2	9.2	9.2	10.4	10.4	10.4	11.5	11.5
67.5°	6.9	6.9	8.1	8.1	9.2	9.2	9.2	10.4	10.4	10.4	11.5
70°	6.9	6.9	6.9	8.1	8.1	8.1	8.1	9.2	9.2	10.4	10.4
72.5°	5.8	6.9	6.9	8.1	8.1	8.1	8.1	9.2	9.2	9.2	10.4
75°	5.8	6.9	6.9	8.1	8.1	8.1	8.1	8.1	9.2	9.2	10.4
77.5°	5.8	6.9	6.9	8.1	8.1	8.1	8.1	9.2	9.2	9.2	10.4
80°	5.8	6.9	6.9	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2
82.5°	5.8	6.9	6.9	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2
85°	5.8	6.9	6.9	8.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2
87.5°	5.8	6.9	6.9	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192698

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2
2.5°	1384.3	1364.8	1295.6	1286.4	1274.9	1218.4	1195.4	1156.3	1101.0	1084.8	1065.2
5°	1249.6	1185.0	1083.6	1056.0	1026.1	937.4	883.3	818.8	747.5	708.2	671.4
7.5°	1077.9	988.2	853.4	799.2	765.9	669.1	582.8	496.4	391.6	331.7	293.6
10°	886.8	763.6	623.1	560.8	515.9	375.5	293.6	255.7	220.0	191.1	165.8
12.5°	694.4	555.1	396.2	324.8	289.0	239.6	194.7	147.4	131.3	130.1	125.5
15°	509.0	353.6	267.2	240.7	215.4	154.3	153.1	153.1	157.7	161.2	162.3
17.5°	375.5	310.9	244.2	228.1	239.6	248.8	264.9	289.0	308.6	363.9	352.4
20°	550.5	545.9	595.5	658.7	703.6	799.2	920.2	1057.2	1200.0	1359.0	1479.8
22.5°	944.3	1059.5	1149.4	1225.3	1265.7	1374.0	1469.5	1516.8	1544.4	1530.6	1511.0
25°	1154.0	1195.4	1167.8	1141.3	1144.8	1046.8	975.5	884.5	807.3	737.1	695.5
27.5°	689.8	631.1	548.2	490.6	479.1	413.4	365.1	314.3	299.4	253.4	233.8
30°	248.8	231.5	205.1	184.2	181.9	164.6	154.3	142.8	141.6	131.3	125.5
32.5°	112.9	112.9	103.7	106.0	103.7	100.2	99.1	95.6	95.6	92.2	89.9
35°	73.8	74.9	73.8	73.8	72.6	72.6	72.6	70.3	71.5	69.2	65.7
37.5°	54.1	55.2	52.9	54.1	54.1	54.1	54.1	52.9	51.8	49.5	48.3
40°	41.4	41.4	41.4	41.4	41.4	41.4	41.4	40.3	40.3	39.1	36.8
42.5°	32.2	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	32.2	32.2
45°	26.5	27.6	26.5	27.6	27.6	27.6	26.5	26.5	26.5	25.3	24.2
47.5°	20.7	20.7	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6	18.4
50°	16.1	16.1	16.1	16.1	16.1	16.1	17.3	16.1	16.1	16.1	16.1
52.5°	12.7	13.8	13.8	15.0	15.0	15.0	15.0	15.0	13.8	13.8	12.7
55°	11.5	12.7	12.7	13.8	13.8	13.8	13.8	12.7	12.7	12.7	11.5
57.5°	11.5	12.7	12.7	12.7	12.7	12.7	12.7	11.5	11.5	10.4	10.4
60°	11.5	11.5	11.5	12.7	12.7	11.5	11.5	10.4	10.4	9.2	9.2
62.5°	11.5	11.5	11.5	12.7	12.7	11.5	11.5	10.4	9.2	9.2	8.1
65°	11.5	12.7	11.5	12.7	12.7	11.5	11.5	10.4	9.2	9.2	8.1
67.5°	11.5	12.7	12.7	12.7	11.5	11.5	11.5	10.4	9.2	9.2	8.1
70°	10.4	11.5	11.5	11.5	11.5	11.5	10.4	10.4	9.2	9.2	8.1
72.5°	10.4	11.5	10.4	11.5	11.5	10.4	10.4	10.4	9.2	9.2	8.1
75°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1
77.5°	10.4	10.4	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1	8.1
80°	10.4	10.4	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1	6.9
82.5°	9.2	10.4	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1	6.9
85°	9.2	9.2	9.2	9.2	9.2	9.2	8.1	8.1	6.9	5.8	5.8
87.5°	8.1	9.2	8.1	8.1	8.1	8.1	6.9	5.8	4.6	4.6	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192698

CATALOG NUMBER: LDA6A70930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2	1520.2
2.5°	1034.2	1005.4	1006.6	1011.2	982.4	967.3	963.9	948.9
5°	621.9	588.6	582.8	578.1	537.8	521.7	509.0	525.1
7.5°	267.2	254.5	252.2	248.8	230.4	221.2	216.6	221.2
10°	132.4	124.4	125.5	126.7	120.9	117.5	116.3	115.2
12.5°	131.3	130.1	131.3	131.3	132.4	130.1	131.3	131.3
15°	170.4	170.4	173.8	176.2	181.9	180.8	183.1	185.4
17.5°	424.9	403.1	414.6	414.6	466.5	420.3	459.6	423.8
20°	1669.9	1748.3	1827.6	1894.5	1962.4	1983.1	2023.5	2012.0
22.5°	1481.0	1490.3	1478.7	1466.0	1462.6	1466.0	1403.9	1413.1
25°	635.7	631.1	612.7	593.2	598.9	603.5	581.7	560.8
27.5°	217.7	212.0	206.2	201.6	199.3	195.9	188.8	184.2
30°	123.2	119.8	117.5	116.3	114.0	111.7	108.3	106.0
32.5°	88.7	86.4	85.3	84.1	81.8	79.5	76.1	74.9
35°	65.7	63.3	62.1	61.0	58.7	56.4	55.2	54.1
37.5°	48.3	46.0	46.0	46.0	42.6	40.3	39.1	38.0
40°	36.8	35.7	35.7	35.7	33.4	32.2	31.1	31.1
42.5°	32.2	31.1	31.1	31.1	28.8	27.6	27.6	26.5
45°	24.2	23.0	23.0	21.9	20.7	20.7	19.6	18.4
47.5°	18.4	17.3	17.3	17.3	16.1	15.0	15.0	13.8
50°	15.0	15.0	13.8	15.0	12.7	12.7	12.7	11.5
52.5°	12.7	12.7	11.5	11.5	10.4	10.4	10.4	9.2
55°	11.5	10.4	10.4	10.4	9.2	9.2	9.2	8.1
57.5°	9.2	9.2	8.1	8.1	6.9	6.9	6.9	6.9
60°	8.1	8.1	6.9	6.9	5.8	5.8	5.8	5.8
62.5°	8.1	6.9	6.9	6.9	5.8	5.8	5.8	5.8
65°	8.1	6.9	6.9	6.9	5.8	5.8	5.8	5.8
67.5°	8.1	6.9	6.9	6.9	5.8	5.8	5.8	5.8
70°	8.1	8.1	6.9	6.9	6.9	5.8	5.8	5.8
72.5°	8.1	8.1	6.9	6.9	6.9	6.9	5.8	5.8
75°	6.9	6.9	6.9	6.9	5.8	5.8	5.8	5.8
77.5°	6.9	6.9	6.9	6.9	5.8	5.8	5.8	5.8
80°	6.9	6.9	5.8	5.8	5.8	5.8	5.8	5.8
82.5°	6.9	5.8	5.8	5.8	5.8	4.6	4.6	4.6
85°	4.6	4.6	4.6	4.6	3.5	3.5	3.5	3.5
87.5°	3.5	2.3	2.3	2.3	1.2	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)