

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192180

Luminaire Tested: **LDA6A40927D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192180
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26672)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40927D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4014.6 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 2.54 / 0.51 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192180

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192180

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	85	75	68	62	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	40	39		
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	49404	49404	49404
5°	126331	45548	16619
10°	271516	36745	6118
15°	396081	26873	6998
20°	448500	19322	10793
25°	486203	15545	16737
30°	542495	12761	16116
35°	550636	8252	10741
40°	554696	3957	5432
45°	551220	1651	2264
50°	441342	742	742
55°	131618	535	76
60°	26862	614	0
65°	2568	726	0
70°	240	1010	0
75°	0	1334	0
80°	0	2241	253
85°	0	4466	503

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192180

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.4	2.9
10°-20°	563.1	14.0
20°-30°	1034.8	25.8
30°-40°	1187.3	29.6
40°-50°	898.3	22.4
50°-60°	199.0	5.0
60°-70°	8.4	0.2
70°-80°	3.7	0.1
80°-90°	3.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1714.3	42.7
0°-40°	2901.5	72.3
0°-60°	3998.9	99.6
0°-90°	4014.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4014.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	901	901	901	901	901	
5°	2296	1715	828	405	302	303
15°	6979	3785	474	122	123	1945
25°	8038	4451	257	249	277	3750
35°	8228	2747	123	154	160	5154
45°	7110	777	21	28	29	5306
55°	1377	29	6	4	1	1705
65°	20	4	6	3	0	53
75°	0	3	6	4	0	0
85°	0	4	7	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192180

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	901.2	901.2	901.2	901.2	901.2	901.2	901.2	901.2	901.2	901.2	901.2
2.5°	1526.6	1511.5	1515.4	1534.4	1456.2	1453.8	1417.4	1412.7	1376.3	1309.9	1276.7
5°	2295.7	2286.2	2269.6	2276.0	2186.7	2126.5	2063.3	2017.4	1924.1	1798.4	1714.7
7.5°	3522.6	3419.8	3370.1	3274.4	3160.5	3044.4	2927.3	2791.4	2595.4	2376.4	2199.3
10°	4877.6	4832.5	4730.6	4669.7	4417.5	4246.7	4064.9	3786.7	3427.8	3030.9	2700.5
12.5°	6205.7	6152.7	5998.5	5868.9	5533.0	5380.4	5144.0	4793.0	4337.6	3772.5	3249.9
15°	6978.9	6990.7	6816.0	6809.6	6520.3	6321.8	6117.1	5702.1	5124.3	4475.2	3785.0
17.5°	7431.8	7461.0	7287.9	7336.9	7048.4	6842.9	6690.3	6386.8	5772.4	4993.8	4198.6
20°	7687.9	7734.5	7550.4	7588.4	7341.7	7202.5	7047.6	6747.2	6204.9	5345.6	4433.3
22.5°	7883.2	7901.4	7696.7	7747.2	7477.7	7338.5	7228.6	6947.2	6412.1	5531.4	4506.8
25°	8038.1	8084.0	7850.0	7854.0	7586.0	7446.8	7325.1	7069.0	6500.5	5580.4	4450.7
27.5°	8261.1	8298.2	7954.4	7924.3	7665.0	7511.6	7379.6	7127.4	6496.6	5471.2	4238.9
30°	8570.1	8363.1	8011.2	7933.8	7642.1	7486.3	7344.9	7017.5	6351.2	5177.2	3853.8
32.5°	8481.7	8314.1	7967.0	7843.7	7554.3	7387.6	7225.4	6827.0	6013.6	4721.8	3328.9
35°	8227.9	8174.1	7809.7	7770.9	7420.8	7246.0	7083.2	6538.5	5495.8	4126.5	2747.1
37.5°	8013.6	7922.0	7687.1	7626.3	7258.7	7065.8	6806.5	6107.7	4811.2	3367.7	2193.8
40°	7751.2	7689.5	7462.7	7397.8	6972.5	6678.4	6361.5	5326.6	3984.3	2621.4	1694.1
42.5°	7472.1	7416.8	7202.5	7066.6	6499.8	6110.9	5618.3	4381.1	3067.3	1975.6	1269.6
45°	7110.0	7031.8	6763.8	6510.8	5698.2	5141.6	4587.5	3343.2	2245.1	1406.4	777.1
47.5°	6487.9	6363.8	6038.9	5530.6	4532.2	3997.8	3420.7	2267.2	1386.6	724.1	391.3
50°	5174.9	4958.2	4525.8	3921.0	2902.8	2390.5	1938.3	1152.6	595.3	373.1	230.0
52.5°	3189.0	2990.6	2622.2	2038.7	1338.4	1030.8	811.8	536.8	328.0	211.1	85.4
55°	1377.1	1253.0	1076.7	821.4	583.4	479.9	385.8	268.0	169.2	64.8	29.2
57.5°	520.2	483.0	437.9	359.7	268.8	224.6	189.0	118.6	41.1	24.5	16.6
60°	245.0	222.1	196.1	155.7	102.8	74.3	46.6	30.0	19.8	13.5	9.5
62.5°	67.2	50.6	41.9	33.9	26.1	22.9	19.8	15.0	11.1	7.1	5.6
65°	19.8	17.4	16.6	14.2	11.8	10.3	8.7	7.1	5.6	3.9	3.9
67.5°	7.1	7.1	6.3	5.6	4.7	3.9	3.9	3.2	3.2	3.2	3.2
70°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	2.4	2.4	3.2	3.2
72.5°	0.0	0.0	0.8	0.8	1.5	1.5	1.5	2.4	2.4	3.2	3.2
75°	0.0	0.0	0.8	0.8	1.5	1.5	1.5	2.4	2.4	3.2	3.2
77.5°	0.0	0.0	0.8	0.8	1.5	1.5	1.5	2.4	3.2	3.2	3.9
80°	0.0	0.0	0.8	0.8	1.5	1.5	1.5	2.4	3.2	3.2	3.9
82.5°	0.0	0.0	0.8	0.8	1.5	1.5	1.5	2.4	3.2	3.2	3.9
85°	0.0	0.0	0.8	0.8	1.5	1.5	1.5	2.4	3.2	3.2	3.9
87.5°	0.0	0.0	0.8	0.8	1.5	1.5	1.5	2.4	3.2	3.2	3.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192180

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	901.2	901.2	901.2	901.2	901.2	901.2	901.2	901.2	901.2	901.2	901.2
2.5°	1249.0	1203.1	1138.3	1105.2	1075.9	1068.0	1007.9	969.2	923.3	875.9	826.1
5°	1636.4	1519.4	1395.3	1291.0	1238.0	1207.2	1090.2	1002.4	917.8	827.7	751.0
7.5°	2020.6	1811.1	1630.0	1461.6	1369.2	1299.6	1132.1	1000.0	871.9	754.9	651.4
10°	2392.2	2090.2	1801.6	1574.0	1446.6	1343.1	1126.5	954.9	794.4	660.1	551.8
12.5°	2768.5	2328.1	1944.7	1634.1	1482.2	1349.4	1088.5	879.8	709.9	567.6	455.4
15°	3104.5	2513.1	2034.0	1648.3	1464.8	1308.4	1014.3	784.2	615.0	473.5	375.5
17.5°	3337.7	2612.7	2039.6	1596.1	1392.1	1223.7	910.7	683.8	519.4	394.5	308.3
20°	3443.6	2609.6	1964.5	1487.8	1274.3	1098.8	788.2	581.0	433.2	331.2	257.7
22.5°	3411.9	2510.0	1831.7	1334.4	1130.4	954.9	674.3	490.2	372.4	284.6	226.1
25°	3253.8	2336.0	1675.9	1181.0	975.5	811.8	571.5	419.0	323.3	257.0	205.5
27.5°	2995.3	2098.9	1466.5	1001.6	813.5	686.2	481.4	362.1	284.6	226.9	214.3
30°	2617.5	1811.1	1220.6	807.9	656.9	543.1	390.5	291.7	227.6	201.6	202.3
32.5°	2200.9	1494.2	959.8	617.4	494.9	419.0	288.5	204.0	166.9	165.2	166.0
35°	1785.8	1163.6	713.9	451.4	362.8	302.0	185.8	128.1	124.2	123.3	124.9
37.5°	1417.4	865.6	514.6	315.4	240.3	184.2	100.4	86.9	83.8	85.4	86.2
40°	1058.5	607.1	347.8	186.6	117.0	84.6	60.9	56.2	54.5	55.3	55.3
42.5°	728.1	379.5	207.1	77.5	56.2	46.6	38.8	36.4	34.8	33.9	34.8
45°	392.1	236.4	80.6	39.5	33.2	30.0	24.5	22.9	22.1	21.3	21.3
47.5°	250.6	87.7	36.4	24.5	21.3	19.8	16.6	15.0	14.2	13.5	13.5
50°	94.1	33.9	22.1	15.8	13.5	12.7	10.3	9.5	8.7	8.7	8.7
52.5°	32.4	20.6	14.2	10.3	8.7	7.9	7.1	6.3	6.3	6.3	6.3
55°	18.2	12.7	8.7	6.3	6.3	5.6	5.6	5.6	5.6	5.6	5.6
57.5°	11.1	7.1	5.6	4.7	4.7	4.7	4.7	5.6	5.6	5.6	5.6
60°	6.3	4.7	4.7	4.7	4.7	4.7	4.7	4.7	5.6	5.6	5.6
62.5°	3.9	3.9	3.9	3.9	3.9	4.7	4.7	5.6	5.6	5.6	5.6
65°	3.9	3.9	3.9	3.9	3.9	4.7	4.7	5.6	5.6	5.6	5.6
67.5°	3.2	3.9	3.9	4.7	4.7	4.7	4.7	5.6	5.6	6.3	5.6
70°	3.9	3.9	3.9	4.7	4.7	4.7	5.6	5.6	6.3	6.3	6.3
72.5°	3.9	3.9	3.9	4.7	4.7	4.7	5.6	5.6	6.3	6.3	6.3
75°	3.9	3.9	4.7	4.7	4.7	5.6	5.6	6.3	6.3	6.3	6.3
77.5°	3.9	3.9	4.7	4.7	4.7	5.6	5.6	6.3	6.3	7.1	6.3
80°	3.9	3.9	4.7	5.6	5.6	5.6	5.6	6.3	6.3	7.1	7.1
82.5°	3.9	4.7	4.7	5.6	5.6	5.6	6.3	6.3	7.1	7.1	7.1
85°	3.9	4.7	4.7	5.6	5.6	5.6	6.3	6.3	7.1	7.1	7.1
87.5°	3.9	4.7	4.7	5.6	5.6	5.6	6.3	6.3	7.1	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192180

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	901.2	901.2	901.2	901.2	901.2	901.2	901.2	901.2	901.2	901.2	901.2
2.5°	799.2	753.4	716.3	717.0	686.2	662.5	632.4	615.9	602.4	580.3	559.7
5°	694.9	624.5	571.5	561.2	525.7	489.3	452.2	424.5	404.8	383.4	363.6
7.5°	581.8	501.2	440.4	426.1	396.0	362.1	328.0	300.4	276.7	253.8	230.0
10°	472.0	398.4	343.1	328.9	298.8	263.2	230.8	206.4	188.1	169.9	151.8
12.5°	381.8	317.0	264.8	246.7	222.1	194.4	168.4	144.6	124.9	117.0	114.6
15°	309.1	247.4	206.4	191.3	170.8	142.3	127.2	123.3	122.5	122.5	122.5
17.5°	249.8	201.6	164.4	148.6	138.4	136.7	136.7	136.7	137.5	139.2	142.3
20°	209.5	166.9	152.6	154.2	154.2	155.7	158.9	161.3	164.4	168.4	173.1
22.5°	185.8	177.0	175.5	180.2	181.0	185.8	192.1	196.9	202.3	208.7	212.6
25°	203.2	206.4	208.7	215.8	218.2	226.1	235.6	242.7	249.0	256.1	260.9
27.5°	221.4	226.9	231.7	238.8	240.3	250.6	258.5	263.2	268.0	271.2	274.3
30°	208.7	214.3	219.0	225.3	225.3	236.4	240.3	244.3	248.2	249.8	253.0
32.5°	171.6	177.0	181.9	186.6	187.3	195.2	200.0	201.6	204.7	205.5	207.9
35°	128.9	131.3	136.0	139.9	140.7	146.3	150.2	151.8	154.2	154.2	155.7
37.5°	88.6	90.1	94.1	96.5	98.0	101.9	104.3	106.0	107.5	108.3	109.1
40°	57.7	58.5	60.9	63.3	64.8	67.2	68.8	70.4	71.2	72.7	72.7
42.5°	35.6	36.4	38.0	39.5	39.5	41.9	42.7	44.2	45.1	45.9	45.9
45°	22.1	22.9	22.9	23.8	24.5	25.3	26.8	26.8	27.7	27.7	27.7
47.5°	13.5	14.2	13.5	14.2	14.2	15.0	15.8	15.8	15.8	15.8	15.8
50°	8.7	8.7	8.7	8.7	8.7	8.7	9.5	9.5	9.5	9.5	8.7
52.5°	6.3	6.3	5.6	6.3	5.6	5.6	5.6	5.6	5.6	5.6	4.7
55°	5.6	5.6	5.6	5.6	4.7	4.7	4.7	3.9	3.9	3.2	3.2
57.5°	5.6	5.6	4.7	4.7	4.7	3.9	3.9	3.9	3.2	3.2	2.4
60°	5.6	5.6	4.7	4.7	4.7	3.9	3.9	3.2	3.2	2.4	2.4
62.5°	5.6	5.6	4.7	4.7	4.7	4.7	3.9	3.9	3.2	3.2	2.4
65°	5.6	5.6	5.6	4.7	4.7	4.7	3.9	3.9	3.2	3.2	2.4
67.5°	5.6	5.6	5.6	5.6	4.7	4.7	4.7	3.9	3.2	3.2	2.4
70°	5.6	5.6	5.6	5.6	5.6	4.7	4.7	3.9	3.9	3.2	2.4
72.5°	6.3	6.3	5.6	5.6	5.6	4.7	4.7	3.9	3.9	3.2	3.2
75°	6.3	6.3	5.6	5.6	5.6	4.7	4.7	3.9	3.9	3.2	3.2
77.5°	6.3	6.3	6.3	6.3	5.6	5.6	4.7	4.7	3.9	3.9	3.2
80°	6.3	6.3	6.3	6.3	5.6	5.6	5.6	4.7	3.9	3.9	3.2
82.5°	6.3	6.3	6.3	6.3	6.3	5.6	5.6	4.7	3.9	3.9	3.2
85°	6.3	6.3	6.3	6.3	6.3	5.6	5.6	4.7	3.9	3.9	3.2
87.5°	6.3	6.3	6.3	6.3	6.3	5.6	5.6	4.7	3.9	3.9	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192180

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	901.2	901.2	901.2	901.2	901.2	901.2	901.2	901.2
2.5°	540.7	530.5	529.7	520.9	503.5	512.3	501.2	493.3
5°	346.3	335.1	324.1	325.7	313.0	315.4	306.8	302.0
7.5°	219.7	207.9	204.7	204.7	190.5	190.5	185.0	181.9
10°	138.4	128.9	125.7	120.1	113.9	113.1	110.7	109.9
12.5°	112.2	112.2	109.9	110.7	110.7	110.7	109.9	109.9
15°	122.5	123.3	121.0	121.7	123.3	122.5	123.3	123.3
17.5°	141.5	145.5	142.3	143.9	147.0	146.3	147.0	147.8
20°	173.1	179.4	175.5	178.7	182.6	181.9	184.2	185.0
22.5°	215.8	223.7	219.7	222.9	229.3	227.6	230.8	232.4
25°	263.2	271.2	266.4	270.3	274.3	275.9	275.9	276.7
27.5°	274.3	279.1	275.9	279.8	281.4	283.0	281.4	282.3
30°	251.4	255.3	252.1	256.1	256.1	257.7	256.1	254.6
32.5°	207.1	210.3	206.4	211.1	210.3	211.1	211.9	212.6
35°	156.6	158.1	155.7	156.6	157.3	158.1	160.5	160.5
37.5°	109.1	111.5	109.1	109.9	109.9	111.5	113.1	113.1
40°	72.7	75.1	72.7	74.3	73.6	74.3	75.9	75.9
42.5°	45.9	47.4	45.9	46.6	46.6	46.6	47.4	48.2
45°	27.7	28.5	27.7	28.5	28.5	28.5	29.2	29.2
47.5°	15.8	16.6	15.8	15.8	16.6	15.8	16.6	16.6
50°	8.7	8.7	8.7	8.7	8.7	7.9	7.9	8.7
52.5°	4.7	4.7	3.9	3.9	3.9	3.9	3.9	3.9
55°	2.4	2.4	1.5	1.5	1.5	0.8	1.5	0.8
57.5°	1.5	1.5	0.8	0.8	0.8	0.8	0.0	0.0
60°	1.5	1.5	0.8	0.8	0.8	0.0	0.0	0.0
62.5°	1.5	1.5	0.8	0.8	0.8	0.0	0.0	0.0
65°	1.5	1.5	0.8	0.8	0.8	0.0	0.0	0.0
67.5°	2.4	1.5	0.8	0.8	0.8	0.0	0.0	0.0
70°	2.4	1.5	1.5	0.8	0.8	0.0	0.0	0.0
72.5°	2.4	1.5	1.5	1.5	0.8	0.8	0.0	0.0
75°	2.4	1.5	1.5	1.5	0.8	0.8	0.0	0.0
77.5°	2.4	2.4	1.5	1.5	0.8	0.8	0.8	0.0
80°	2.4	2.4	1.5	1.5	1.5	0.8	0.8	0.8
82.5°	2.4	2.4	1.5	1.5	1.5	0.8	0.8	0.8
85°	2.4	2.4	1.5	1.5	1.5	0.8	0.8	0.8
87.5°	2.4	2.4	1.5	1.5	1.5	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)