

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192715

Luminaire Tested: **LDA6A70935D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192715
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26689)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70935D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5700.6 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 2.34 / 0.96 / 1.3
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192715

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192715

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	51	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	61	50	43	38	49	43	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	88957	88957	88957
5°	173926	84569	30844
10°	292758	72611	6841
15°	445837	54983	11232
20°	644249	44536	125293
25°	958797	72053	36208
30°	1107436	24668	7166
35°	1107791	5514	3868
40°	905446	3077	2376
45°	685645	2008	1527
50°	455337	1365	1040
55°	73202	1166	822
60°	4583	1217	680
65°	1440	1583	804
70°	785	1779	994
75°	508	2076	1313
80°	410	3094	1957
85°	818	6164	2327



TEST NUMBER: P1192715

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.4	3.0
10°-20°	724.3	12.7
20°-30°	1705.0	29.9
30°-40°	1796.5	31.5
40°-50°	1120.1	19.6
50°-60°	160.9	2.8
60°-70°	10.3	0.2
70°-80°	8.0	0.1
80°-90°	6.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2598.7	45.6
0°-40°	4395.1	77.1
0°-60°	5676.2	99.6
0°-90°	5700.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5700.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1623	1623	1623	1623	1623	
5°	3161	2558	1537	798	560	367
15°	7856	4447	969	168	198	2339
25°	15851	5330	1191	862	599	7133
35°	16553	3904	82	76	58	9985
45°	8844	1081	26	28	20	6922
55°	766	20	12	14	9	1376
65°	11	9	12	10	6	16
75°	2	6	10	10	6	3
85°	1	6	10	7	4	1
90°	0	0	0	0	0	

TEST NUMBER: P1192715

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7
2.5°	2368.9	2352.9	2357.8	2321.0	2271.8	2294.0	2238.6	2239.9	2205.4	2118.1	2080.0
5°	3160.6	3158.2	3154.5	3086.9	2999.6	3009.5	2928.3	2897.6	2809.1	2655.3	2558.3
7.5°	4144.2	4145.4	4127.0	3962.2	3865.1	3858.9	3731.1	3638.9	3474.1	3232.0	3055.0
10°	5259.2	5293.6	5260.4	5007.1	4826.4	4828.8	4599.0	4422.0	4157.7	3804.8	3552.8
12.5°	6568.5	6573.4	6521.7	6188.6	5913.2	5892.3	5583.8	5245.7	4843.6	4382.6	4016.2
15°	7855.6	7890.0	7823.5	7413.0	7029.5	6971.7	6578.2	6132.0	5632.9	4950.6	4446.6
17.5°	9282.8	9228.7	9053.0	8465.3	8004.3	7919.4	7496.5	6912.6	6275.8	5450.9	4789.6
20°	11043.3	11061.7	10689.2	9811.5	9032.0	8701.4	8210.8	7571.6	6777.4	5818.6	5018.2
22.5°	13558.5	13458.9	12659.8	11240.0	10068.3	9627.0	8927.6	8046.1	7152.4	6097.5	5189.0
25°	15851.2	15589.4	14853.0	12899.5	11065.4	10519.6	9795.4	8450.6	7463.5	6304.2	5330.5
27.5°	17167.8	17051.1	16216.3	14245.7	11870.7	11102.2	10083.1	8748.1	7647.8	6406.1	5371.1
30°	17494.8	17515.8	16773.3	14691.9	12061.2	11183.5	10129.9	8739.5	7523.6	6224.2	5137.4
32.5°	17411.3	17298.3	16370.0	14199.0	11553.5	10754.4	9672.6	8348.5	7029.5	5682.1	4556.0
35°	16553.2	16387.3	15245.1	12916.8	10691.7	9914.7	8933.6	7708.1	6339.8	4991.2	3904.4
37.5°	14920.6	14728.9	13411.0	11377.6	9657.8	9000.1	8151.8	6995.0	5642.7	4347.0	3331.5
40°	12652.5	12413.9	11312.4	9902.4	8546.4	8086.7	7370.0	6181.2	4919.8	3737.3	2802.9
42.5°	10531.8	10417.5	9756.1	8546.4	7633.0	7189.2	6466.4	5360.0	4199.4	3113.9	2075.1
45°	8843.9	8767.7	8328.8	7560.5	6633.6	6218.0	5537.0	4457.7	3195.2	2097.3	1080.6
47.5°	7741.3	7547.0	7117.9	6311.5	5281.3	4763.7	4114.6	2936.9	1802.2	929.4	331.9
50°	5339.0	5357.6	4873.1	3984.3	3107.9	2670.2	2205.4	1351.1	596.2	202.9	57.8
52.5°	2811.5	2603.7	2263.2	1690.3	1176.5	897.4	655.3	270.5	108.1	40.6	30.8
55°	765.9	672.4	537.2	379.9	205.3	143.8	94.6	50.5	35.7	28.3	19.7
57.5°	75.1	71.3	65.1	52.9	45.4	41.8	38.1	30.8	24.6	17.3	12.2
60°	41.8	40.6	38.1	33.2	29.5	27.0	24.6	20.9	14.8	11.1	9.8
62.5°	23.3	22.1	20.9	18.4	16.0	14.8	14.8	12.2	9.8	8.6	8.6
65°	11.1	11.1	11.1	11.1	11.1	9.8	8.6	8.6	8.6	8.6	8.6
67.5°	8.6	8.6	8.6	7.3	7.3	7.3	7.3	7.3	7.3	6.2	7.3
70°	4.9	4.9	6.2	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.2
72.5°	2.4	3.7	3.7	3.7	3.7	3.7	3.7	3.7	4.9	4.9	6.2
75°	2.4	2.4	2.4	2.4	3.7	3.7	3.7	3.7	4.9	4.9	6.2
77.5°	2.4	2.4	2.4	2.4	2.4	2.4	3.7	3.7	4.9	4.9	6.2
80°	1.3	1.3	1.3	2.4	2.4	2.4	2.4	3.7	4.9	4.9	6.2
82.5°	1.3	1.3	1.3	1.3	2.4	2.4	2.4	3.7	4.9	4.9	6.2
85°	1.3	1.3	1.3	1.3	2.4	2.4	2.4	3.7	3.7	4.9	6.2
87.5°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	3.7	4.9	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192715

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7
2.5°	2040.8	1980.5	1920.3	1860.0	1857.6	1821.9	1769.0	1699.0	1641.1	1592.0	1544.1
5°	2461.2	2337.0	2212.9	2088.6	2051.8	1987.8	1873.5	1744.4	1633.8	1536.8	1443.3
7.5°	2882.8	2673.9	2477.2	2282.9	2205.4	2108.3	1930.0	1743.2	1583.3	1440.8	1301.9
10°	3259.0	2955.3	2678.8	2405.9	2294.0	2167.3	1927.6	1690.3	1487.6	1304.4	1127.4
12.5°	3605.7	3182.8	2832.4	2488.2	2335.8	2182.1	1889.5	1606.8	1364.6	1145.8	941.7
15°	3910.5	3391.7	2940.6	2525.1	2338.3	2153.8	1809.7	1491.2	1219.5	968.8	747.5
17.5°	4128.1	3496.3	2976.3	2491.8	2274.3	2067.8	1691.6	1351.1	1058.5	796.6	582.7
20°	4261.0	3539.3	2957.9	2430.4	2199.4	1985.4	1604.3	1273.6	989.6	763.4	618.3
22.5°	4348.3	3581.1	2965.2	2429.1	2198.1	1996.5	1641.1	1331.4	1100.3	978.5	961.4
25°	4441.6	3640.1	3019.3	2484.5	2269.4	2082.5	1738.4	1435.9	1242.8	1191.2	1198.7
27.5°	4436.7	3614.3	2967.7	2436.6	2210.4	2021.1	1617.9	1235.5	1054.7	909.7	856.9
30°	4172.4	3315.5	2616.1	2021.1	1754.3	1521.9	990.9	644.2	445.0	389.7	334.3
32.5°	3554.1	2686.1	1955.9	1397.8	1097.7	819.9	389.7	206.5	175.9	147.5	134.0
35°	2955.3	2141.6	1463.0	844.5	533.5	330.7	140.2	92.2	87.3	82.4	82.4
37.5°	2442.7	1681.7	945.3	356.5	195.4	119.2	67.6	61.4	59.0	57.8	57.8
40°	1910.5	1096.6	409.4	118.1	62.7	54.1	47.9	45.4	44.3	43.0	44.3
42.5°	1127.4	441.3	119.2	44.3	41.8	39.4	35.7	34.4	34.4	33.2	34.4
45°	383.5	114.3	39.4	31.9	29.5	29.5	27.0	27.0	27.0	25.9	28.3
47.5°	99.5	35.7	25.9	23.3	22.1	22.1	20.9	20.9	20.9	20.9	22.1
50°	34.4	23.3	18.4	17.3	16.0	17.3	16.0	16.0	16.0	16.0	17.3
52.5°	20.9	16.0	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5
55°	13.5	12.2	11.1	11.1	11.1	11.1	11.1	12.2	12.2	12.2	12.2
57.5°	11.1	9.8	9.8	9.8	9.8	9.8	11.1	9.8	9.8	11.1	12.2
60°	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.8	11.1	11.1	12.2
62.5°	8.6	9.8	9.8	9.8	9.8	9.8	9.8	11.1	11.1	11.1	12.2
65°	8.6	8.6	8.6	9.8	9.8	9.8	11.1	11.1	11.1	12.2	12.2
67.5°	7.3	7.3	8.6	8.6	9.8	9.8	9.8	11.1	11.1	11.1	12.2
70°	7.3	7.3	7.3	8.6	8.6	8.6	8.6	9.8	9.8	11.1	11.1
72.5°	6.2	7.3	7.3	8.6	8.6	8.6	8.6	9.8	9.8	9.8	11.1
75°	6.2	7.3	7.3	8.6	8.6	8.6	8.6	8.6	9.8	9.8	11.1
77.5°	6.2	7.3	7.3	8.6	8.6	8.6	8.6	9.8	9.8	9.8	11.1
80°	6.2	7.3	7.3	8.6	8.6	8.6	8.6	9.8	9.8	9.8	9.8
82.5°	6.2	7.3	7.3	8.6	8.6	8.6	8.6	9.8	9.8	9.8	9.8
85°	6.2	7.3	7.3	8.6	8.6	8.6	8.6	8.6	9.8	9.8	9.8
87.5°	6.2	7.3	7.3	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192715

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7
2.5°	1477.6	1456.8	1383.0	1373.3	1360.9	1300.6	1276.0	1234.2	1175.2	1158.0	1137.1
5°	1333.9	1265.0	1156.8	1127.4	1095.3	1000.7	942.9	874.1	797.8	756.1	716.7
7.5°	1150.7	1054.7	910.9	853.1	817.5	714.2	622.1	529.9	418.0	354.0	313.5
10°	946.6	815.0	665.1	598.6	550.7	400.8	313.5	272.9	234.8	204.0	177.0
12.5°	741.3	592.6	422.9	346.7	308.6	255.7	207.8	157.3	140.2	138.9	134.0
15°	543.4	377.5	285.1	257.0	229.9	164.8	163.5	163.5	168.4	172.1	173.3
17.5°	400.8	331.9	260.6	243.4	255.7	265.6	282.7	308.6	329.4	388.5	376.2
20°	587.7	582.7	635.6	703.2	751.2	853.1	982.3	1128.5	1280.9	1450.6	1579.7
22.5°	1008.0	1131.0	1226.9	1308.0	1351.1	1466.6	1568.7	1619.0	1648.6	1633.8	1613.0
25°	1231.8	1276.0	1246.6	1218.2	1222.0	1117.4	1041.2	944.2	861.8	786.9	742.6
27.5°	736.4	673.7	585.1	523.7	511.3	441.3	389.7	335.6	319.7	270.5	249.5
30°	265.6	247.0	218.9	196.7	194.3	175.9	164.8	152.4	151.3	140.2	134.0
32.5°	120.5	120.5	110.6	113.2	110.6	107.0	105.7	102.1	102.1	98.4	95.9
35°	78.7	80.0	78.7	78.7	77.5	77.5	77.5	75.1	76.2	73.8	70.0
37.5°	57.8	59.0	56.5	57.8	57.8	57.8	57.8	56.5	55.4	52.9	51.6
40°	44.3	44.3	44.3	44.3	44.3	44.3	44.3	43.0	43.0	41.8	39.4
42.5°	34.4	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	34.4	34.4
45°	28.3	29.5	28.3	29.5	29.5	29.5	28.3	28.3	28.3	27.0	25.9
47.5°	22.1	22.1	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9	19.7
50°	17.3	17.3	17.3	17.3	17.3	17.3	18.4	17.3	17.3	17.3	17.3
52.5°	13.5	14.8	14.8	16.0	16.0	16.0	16.0	16.0	14.8	14.8	13.5
55°	12.2	13.5	13.5	14.8	14.8	14.8	14.8	13.5	13.5	13.5	12.2
57.5°	12.2	13.5	13.5	13.5	13.5	13.5	13.5	12.2	12.2	11.1	11.1
60°	12.2	12.2	12.2	13.5	13.5	12.2	12.2	11.1	11.1	9.8	9.8
62.5°	12.2	12.2	12.2	13.5	13.5	12.2	12.2	11.1	9.8	9.8	8.6
65°	12.2	13.5	12.2	13.5	13.5	12.2	12.2	11.1	9.8	9.8	8.6
67.5°	12.2	13.5	13.5	13.5	12.2	12.2	12.2	11.1	9.8	9.8	8.6
70°	11.1	12.2	12.2	12.2	12.2	12.2	11.1	11.1	9.8	9.8	8.6
72.5°	11.1	12.2	11.1	12.2	12.2	11.1	11.1	11.1	9.8	9.8	8.6
75°	11.1	11.1	11.1	11.1	11.1	11.1	11.1	9.8	9.8	8.6	8.6
77.5°	11.1	11.1	11.1	11.1	11.1	11.1	9.8	9.8	9.8	8.6	8.6
80°	11.1	11.1	11.1	11.1	11.1	11.1	9.8	9.8	8.6	8.6	7.3
82.5°	9.8	11.1	11.1	11.1	11.1	11.1	9.8	9.8	8.6	8.6	7.3
85°	9.8	9.8	9.8	9.8	9.8	9.8	8.6	8.6	7.3	6.2	6.2
87.5°	8.6	9.8	8.6	8.6	8.6	8.6	7.3	6.2	4.9	4.9	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192715

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7	1622.7
2.5°	1103.9	1073.3	1074.4	1079.3	1048.7	1032.6	1029.0	1013.0
5°	663.9	628.2	622.1	617.2	574.2	556.9	543.4	560.5
7.5°	285.1	271.6	269.2	265.6	245.9	236.0	231.1	236.0
10°	141.4	132.7	134.0	135.2	129.1	125.4	124.1	122.9
12.5°	140.2	138.9	140.2	140.2	141.4	138.9	140.2	140.2
15°	181.9	181.9	185.6	188.1	194.3	193.0	195.4	197.9
17.5°	453.7	430.2	442.6	442.6	497.8	448.6	490.5	452.4
20°	1782.5	1866.2	1951.0	2022.4	2094.8	2117.0	2160.0	2147.7
22.5°	1580.9	1590.8	1578.5	1564.9	1561.3	1564.9	1498.6	1508.4
25°	678.6	673.7	654.0	633.1	639.3	644.2	620.8	598.6
27.5°	232.4	226.2	220.0	215.1	212.7	208.9	201.6	196.7
30°	131.6	127.8	125.4	124.1	121.7	119.2	115.6	113.2
32.5°	94.6	92.2	91.0	89.7	87.3	84.8	81.1	80.0
35°	70.0	67.6	66.4	65.1	62.7	60.3	59.0	57.8
37.5°	51.6	49.2	49.2	49.2	45.4	43.0	41.8	40.6
40°	39.4	38.1	38.1	38.1	35.7	34.4	33.2	33.2
42.5°	34.4	33.2	33.2	33.2	30.8	29.5	29.5	28.3
45°	25.9	24.6	24.6	23.3	22.1	22.1	20.9	19.7
47.5°	19.7	18.4	18.4	18.4	17.3	16.0	16.0	14.8
50°	16.0	16.0	14.8	16.0	13.5	13.5	13.5	12.2
52.5°	13.5	13.5	12.2	12.2	11.1	11.1	11.1	9.8
55°	12.2	11.1	11.1	11.1	9.8	9.8	9.8	8.6
57.5°	9.8	9.8	8.6	8.6	7.3	7.3	7.3	7.3
60°	8.6	8.6	7.3	7.3	6.2	6.2	6.2	6.2
62.5°	8.6	7.3	7.3	7.3	6.2	6.2	6.2	6.2
65°	8.6	7.3	7.3	7.3	6.2	6.2	6.2	6.2
67.5°	8.6	7.3	7.3	7.3	6.2	6.2	6.2	6.2
70°	8.6	8.6	7.3	7.3	7.3	6.2	6.2	6.2
72.5°	8.6	8.6	7.3	7.3	7.3	7.3	6.2	6.2
75°	7.3	7.3	7.3	7.3	6.2	6.2	6.2	6.2
77.5°	7.3	7.3	7.3	7.3	6.2	6.2	6.2	6.2
80°	7.3	7.3	6.2	6.2	6.2	6.2	6.2	6.2
82.5°	7.3	6.2	6.2	6.2	6.2	4.9	4.9	4.9
85°	4.9	4.9	4.9	4.9	3.7	3.7	3.7	3.7
87.5°	3.7	2.4	2.4	2.4	1.3	1.3	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)