

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192185

Luminaire Tested: **LDA6A40927D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26669)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40927D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3026.4 lumens
Efficiency: N/A
Efficacy: 60.8 lumens/watt
Spacing Criteria (0/90/45): 2.14 / 1.07 / 1.49
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192185

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192185

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62		
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55		
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49		
7	72	59	52	46	70	59	51	46	57	51	46	56	50	45	55	49	45	43		
8	67	54	47	41	65	54	46	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	37	33	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	53137	53137	53137
5°	85059	52471	34019
10°	124280	50389	22929
15°	169927	47787	17321
20°	212579	45247	17484
25°	245567	45099	27116
30°	269003	42690	25225
35°	277778	36192	19468
40°	271859	28231	15336
45°	247809	20839	11769
50°	199183	15368	7889
55°	121286	10886	4454
60°	62934	7192	1732
65°	30665	3788	817
70°	14057	1651	753
75°	5867	1186	826
80°	2999	1231	1010
85°	2013	2453	1510

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192185

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.4	3.3
10°-20°	352.2	11.6
20°-30°	666.9	22.0
30°-40°	807.7	26.7
40°-50°	676.0	22.3
50°-60°	327.6	10.8
60°-70°	80.3	2.7
70°-80°	13.0	0.4
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1118.6	37.0
0°-40°	1926.3	63.6
0°-60°	2929.8	96.8
0°-90°	3026.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3026.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	969	969	969	969	969	
5°	1546	1331	954	697	618	169
15°	2994	2082	842	385	305	864
25°	4060	2452	746	439	448	1870
35°	4151	2167	541	312	291	2572
45°	3196	1462	269	164	152	2425
55°	1269	599	114	62	47	1189
65°	236	131	29	10	6	266
75°	28	14	6	5	4	37
85°	3	2	4	3	2	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192185

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	969.3	969.3	969.3	969.3	969.3	969.3	969.3	969.3	969.3	969.3	969.3
2.5°	1230.2	1201.7	1208.1	1212.8	1191.4	1204.9	1182.0	1174.0	1155.1	1159.8	1145.6
5°	1545.7	1506.1	1494.3	1494.3	1458.7	1470.5	1450.0	1413.6	1376.5	1365.4	1331.4
7.5°	1884.8	1841.3	1822.4	1814.5	1762.2	1755.1	1737.7	1681.6	1620.8	1588.4	1528.2
10°	2232.6	2193.1	2166.3	2148.1	2076.2	2063.5	2032.7	1953.6	1876.9	1807.4	1708.5
12.5°	2616.1	2563.2	2527.6	2497.5	2405.1	2385.3	2339.4	2233.5	2112.5	2028.8	1898.2
15°	2994.1	2940.3	2893.7	2850.2	2737.9	2709.4	2647.7	2513.4	2371.8	2246.9	2081.6
17.5°	3353.8	3285.8	3228.8	3170.4	3038.3	3002.7	2922.1	2772.7	2575.0	2433.5	2234.3
20°	3643.9	3577.5	3511.9	3437.5	3286.5	3243.8	3145.8	2968.8	2744.2	2574.3	2341.8
22.5°	3881.1	3806.0	3741.2	3643.9	3474.0	3424.2	3311.1	3110.3	2867.5	2669.1	2413.7
25°	4059.8	3980.0	3913.5	3804.5	3616.2	3558.5	3426.5	3209.1	2944.3	2726.0	2452.5
27.5°	4200.5	4108.9	4033.7	3912.8	3705.6	3640.8	3496.1	3261.3	2975.0	2737.1	2450.9
30°	4249.6	4160.2	4075.6	3945.2	3722.2	3650.3	3500.1	3245.5	2947.4	2691.2	2396.3
32.5°	4228.2	4135.7	4043.9	3905.6	3670.0	3592.6	3440.7	3168.7	2862.8	2593.2	2295.9
35°	4150.7	4056.6	3958.6	3815.5	3568.8	3485.1	3333.2	3051.8	2733.9	2464.3	2167.0
37.5°	4010.0	3915.9	3823.4	3669.2	3417.1	3330.0	3180.7	2888.9	2579.0	2307.0	2017.7
40°	3798.9	3705.6	3620.2	3464.5	3210.7	3123.0	2981.4	2692.1	2393.2	2124.3	1846.1
42.5°	3526.9	3437.5	3360.9	3208.3	2960.0	2876.3	2743.4	2463.6	2184.5	1924.3	1662.7
45°	3196.4	3115.0	3044.7	2900.8	2671.5	2590.8	2473.0	2208.2	1948.1	1704.5	1461.9
47.5°	2815.4	2741.0	2679.4	2546.6	2333.9	2260.3	2159.2	1913.2	1680.9	1458.7	1242.8
50°	2335.5	2270.6	2227.9	2113.3	1923.5	1861.9	1783.6	1576.5	1385.9	1194.6	1015.9
52.5°	1782.1	1731.5	1711.7	1625.5	1478.4	1435.7	1385.1	1226.3	1087.1	936.1	796.9
55°	1269.0	1235.8	1223.1	1166.9	1070.4	1042.8	999.4	901.3	808.7	702.1	599.3
57.5°	864.1	846.7	837.2	802.5	743.2	724.2	699.7	636.4	577.2	507.6	434.0
60°	574.0	566.9	559.0	537.6	502.8	488.6	476.7	434.8	398.5	355.0	303.6
62.5°	372.4	369.2	363.6	350.3	336.8	327.3	314.7	287.0	265.6	243.5	204.8
65°	236.4	233.2	230.8	222.2	213.5	204.0	199.3	183.4	169.9	155.7	131.3
67.5°	146.3	143.9	143.1	137.5	131.3	125.7	122.5	112.2	104.4	95.7	79.8
70°	87.7	86.9	85.4	82.2	78.3	74.3	72.7	65.6	60.9	55.3	45.1
72.5°	50.6	49.8	49.1	46.6	44.2	42.7	41.1	38.8	33.2	30.0	25.3
75°	27.7	27.7	26.8	25.3	24.5	22.9	22.1	20.6	18.2	16.6	14.2
77.5°	15.8	15.0	15.0	14.2	13.5	13.5	12.7	11.8	10.3	10.3	8.7
80°	9.5	9.5	9.5	8.7	8.7	8.7	7.9	7.9	7.1	6.3	6.3
82.5°	6.3	5.6	5.6	5.6	5.6	5.6	4.7	4.7	4.7	4.7	3.9
85°	3.2	3.2	3.2	3.2	2.4	3.2	2.4	2.4	2.4	2.4	2.4
87.5°	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.5	1.5	1.5	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192185

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	969.3	969.3	969.3	969.3	969.3	969.3	969.3	969.3	969.3	969.3	969.3
2.5°	1108.4	1100.5	1084.7	1062.6	1054.7	1050.0	1023.8	1000.1	983.5	962.1	941.7
5°	1269.7	1240.5	1202.5	1156.6	1138.4	1122.7	1074.5	1030.1	993.8	953.5	915.5
7.5°	1436.6	1382.0	1317.9	1245.2	1215.2	1187.5	1114.8	1049.1	993.0	935.3	880.8
10°	1593.1	1510.1	1417.5	1320.3	1275.3	1234.9	1138.4	1053.9	979.6	905.2	838.1
12.5°	1746.5	1633.4	1510.8	1385.9	1327.4	1275.3	1155.8	1052.3	960.6	873.7	796.1
15°	1894.3	1748.0	1597.0	1443.6	1373.3	1309.3	1167.8	1046.8	940.8	842.0	755.9
17.5°	2013.6	1841.3	1658.7	1478.4	1399.4	1325.0	1166.1	1030.9	914.0	806.4	714.7
20°	2097.5	1899.0	1695.9	1494.3	1408.1	1325.9	1154.3	1009.6	886.3	775.6	683.0
22.5°	2144.9	1925.9	1708.5	1494.3	1401.8	1315.6	1137.7	989.8	865.7	757.4	668.8
25°	2164.6	1930.6	1703.0	1481.6	1385.9	1297.4	1118.7	970.9	849.1	745.6	663.3
27.5°	2148.9	1903.0	1672.1	1446.8	1348.8	1260.2	1082.4	937.6	819.9	721.0	642.7
30°	2085.6	1833.4	1603.4	1379.7	1280.8	1194.6	1022.3	882.3	769.2	674.4	600.0
32.5°	1982.9	1732.2	1506.1	1287.9	1189.9	1106.9	942.4	809.6	701.3	611.1	542.3
35°	1857.9	1612.0	1393.9	1181.1	1087.1	1008.0	853.1	723.4	623.8	540.8	477.5
37.5°	1717.2	1479.2	1263.4	1068.1	978.0	902.9	758.2	636.4	544.7	468.0	411.9
40°	1559.1	1334.5	1131.3	946.4	861.0	791.4	654.7	547.2	463.3	394.5	347.1
42.5°	1392.3	1182.8	993.8	820.7	740.0	676.8	552.6	456.9	383.5	327.3	289.4
45°	1213.6	1019.9	846.7	691.8	624.6	561.4	456.2	369.2	311.5	268.8	240.3
47.5°	1023.0	851.4	698.9	563.7	505.2	449.8	361.3	294.9	253.0	220.5	199.3
50°	831.7	687.1	557.3	441.9	392.1	347.9	279.9	234.8	204.0	180.2	162.8
52.5°	649.9	532.9	426.9	332.9	295.6	264.1	217.5	185.8	162.8	144.6	132.1
55°	487.8	395.3	312.3	241.9	219.8	200.0	169.2	143.9	128.1	113.9	104.4
57.5°	353.5	282.3	222.2	177.9	163.7	150.2	128.1	110.7	98.9	87.7	80.6
60°	248.2	196.1	157.3	130.4	119.4	111.5	94.1	83.0	73.6	65.6	58.5
62.5°	166.9	132.8	109.9	92.5	85.4	79.8	68.8	59.3	52.2	45.9	39.5
65°	106.8	89.3	74.3	62.4	57.7	53.8	46.6	38.8	33.9	29.2	24.5
67.5°	65.6	56.2	46.6	38.8	35.6	33.2	28.5	23.8	20.6	17.4	15.0
70°	38.0	32.4	26.8	22.9	21.4	19.8	16.6	14.2	12.7	10.3	8.7
72.5°	21.4	18.9	15.8	13.5	12.7	11.8	10.3	8.7	7.9	7.1	6.3
75°	12.7	11.1	9.5	8.7	7.9	7.9	7.1	6.3	5.6	5.6	4.7
77.5°	7.9	7.1	6.3	6.3	5.6	5.6	5.6	4.7	4.7	4.7	4.7
80°	5.6	5.6	4.7	4.7	4.7	4.7	3.9	3.9	3.9	3.9	3.9
82.5°	3.9	3.9	3.9	3.2	3.2	3.2	3.2	3.2	3.9	3.9	3.9
85°	2.4	2.4	3.2	3.2	3.2	3.2	3.2	3.2	3.9	3.9	3.9
87.5°	2.4	2.4	2.4	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192185

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	969.3	969.3	969.3	969.3	969.3	969.3	969.3	969.3	969.3	969.3	969.3
2.5°	919.4	910.0	892.6	876.7	874.4	852.3	829.3	824.6	816.7	804.0	789.0
5°	877.6	852.3	822.2	800.1	790.6	759.0	727.4	713.1	697.3	672.9	658.6
7.5°	828.6	791.4	749.5	724.2	710.7	671.2	634.9	614.3	592.9	566.9	549.5
10°	774.8	728.2	679.1	650.6	634.9	592.2	553.4	529.7	506.8	480.7	462.5
12.5°	724.2	671.2	617.5	587.4	570.0	525.8	486.3	461.0	438.0	416.6	395.3
15°	679.1	619.9	563.7	533.7	515.5	470.4	432.5	407.2	385.0	364.5	345.5
17.5°	635.6	574.0	518.7	489.3	471.2	429.3	393.0	370.0	348.6	329.7	313.1
20°	605.6	547.2	494.9	467.2	451.5	414.2	383.5	365.3	350.3	333.6	319.4
22.5°	597.7	545.5	500.5	477.5	465.7	436.5	414.2	403.2	398.5	388.2	380.3
25°	597.7	551.9	513.9	494.9	485.4	463.3	445.9	441.9	438.8	432.5	428.5
27.5°	582.6	540.0	506.0	489.3	481.5	461.7	446.7	441.9	438.0	433.3	428.5
30°	543.1	503.6	472.0	456.9	449.0	430.1	414.2	408.8	404.8	397.7	393.7
32.5°	490.2	452.2	426.2	408.8	401.6	383.5	368.5	362.1	358.9	352.6	345.5
35°	430.9	397.7	372.4	358.2	351.0	335.2	321.8	315.5	312.3	305.2	296.5
37.5°	370.8	340.8	320.2	306.8	301.2	288.5	276.7	272.0	268.8	263.2	256.1
40°	311.5	290.2	272.0	261.7	257.0	246.7	236.4	231.7	229.3	224.6	219.0
42.5°	262.5	245.1	230.8	222.2	218.2	210.3	201.6	196.9	194.5	189.8	185.8
45°	219.8	206.4	195.2	187.4	184.2	177.1	169.9	166.0	163.7	159.8	155.7
47.5°	184.2	172.3	162.8	157.3	154.2	148.6	142.3	138.4	136.8	133.6	129.6
50°	151.0	142.3	134.4	129.6	127.2	121.8	116.2	113.1	111.5	108.3	104.4
52.5°	121.8	115.4	108.3	103.6	101.2	97.2	91.8	88.6	86.2	83.0	78.3
55°	95.7	90.1	84.6	79.8	78.3	73.6	68.8	64.1	61.6	58.5	54.5
57.5°	74.3	68.0	62.4	58.5	56.9	52.2	47.4	42.7	40.3	36.4	33.9
60°	53.0	47.4	41.9	39.5	38.0	33.2	29.2	25.3	23.8	21.4	19.8
62.5°	34.8	30.9	26.1	23.8	22.9	19.8	16.6	15.8	14.2	13.5	12.7
65°	21.4	18.9	15.8	14.2	13.5	12.7	11.1	10.3	9.5	8.7	8.7
67.5°	12.7	11.8	10.3	9.5	8.7	7.9	7.9	7.1	7.1	6.3	6.3
70°	8.7	7.9	7.1	6.3	6.3	6.3	6.3	6.3	6.3	5.6	5.6
72.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6
75°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
77.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	3.9	3.9
80°	3.9	4.7	4.7	4.7	4.7	3.9	3.9	3.9	3.9	3.9	3.9
82.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
85°	3.9	3.9	3.9	3.9	3.9	3.2	3.2	3.2	3.2	3.2	2.4
87.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	2.4	2.4	2.4	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192185

CATALOG NUMBER: LDA6A40927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	969.3	969.3	969.3	969.3	969.3	969.3	969.3	969.3
2.5°	787.5	780.4	773.3	784.3	783.5	772.4	780.4	767.7
5°	650.6	640.4	632.5	639.6	635.6	624.6	629.3	618.2
7.5°	539.2	527.3	517.8	523.4	517.0	506.8	505.2	500.5
10°	450.7	438.0	429.3	433.3	426.9	417.4	415.1	411.9
12.5°	383.5	371.6	363.6	366.8	360.6	351.8	350.3	352.6
15°	331.2	322.6	316.2	318.6	309.9	305.2	303.6	305.2
17.5°	301.2	291.7	287.0	289.4	283.0	278.3	277.5	276.7
20°	313.8	306.8	305.2	309.1	304.4	300.5	302.8	299.7
22.5°	382.7	381.8	382.7	392.1	389.8	388.2	389.8	389.8
25°	430.9	434.0	434.8	445.1	445.9	444.3	448.3	448.3
27.5°	429.3	430.1	429.3	439.6	441.2	438.0	441.9	442.7
30°	391.3	391.3	388.9	397.7	397.7	396.1	397.7	398.5
32.5°	341.5	340.8	340.0	343.9	343.9	341.5	343.2	343.2
35°	294.9	291.7	291.7	294.1	293.3	290.9	291.7	290.9
37.5°	254.6	250.6	250.6	252.2	249.9	247.5	248.2	248.2
40°	217.5	214.3	214.3	216.6	215.1	212.6	214.3	214.3
42.5°	182.6	181.9	181.9	183.4	183.4	181.9	184.2	185.0
45°	154.2	151.8	151.8	153.4	153.4	151.8	152.6	151.8
47.5°	128.1	125.7	125.7	125.7	124.2	121.8	121.8	121.0
50°	101.9	98.0	97.2	97.2	95.7	93.3	93.3	92.5
52.5°	75.9	71.9	71.9	71.2	69.5	68.8	68.0	68.0
55°	52.2	49.1	49.8	48.2	48.2	46.6	47.4	46.6
57.5°	32.4	30.9	30.9	30.0	28.5	27.7	27.7	26.8
60°	18.9	17.4	17.4	17.4	16.6	15.8	15.8	15.8
62.5°	12.7	11.8	11.8	11.8	10.3	10.3	9.5	9.5
65°	7.9	7.1	7.1	7.1	6.3	6.3	6.3	6.3
67.5°	6.3	6.3	5.6	5.6	5.6	5.6	5.6	5.6
70°	5.6	5.6	5.6	5.6	5.6	4.7	4.7	4.7
72.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
75°	4.7	4.7	3.9	4.7	3.9	3.9	3.9	3.9
77.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
80°	3.9	3.9	3.9	3.9	3.9	3.2	3.2	3.2
82.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
85°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
87.5°	2.4	1.5	1.5	1.5	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)