

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192718

Luminaire Tested: **LDA6A70935D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70935D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6761.5 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192718

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192718

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	66864	66864	66864
5°	171505	60830	18941
10°	334324	46748	9101
15°	600151	31748	12208
20°	891043	24100	20156
25°	1012813	19858	31611
30°	1097897	21712	29726
35°	1156451	14067	18431
40°	1181456	6247	8974
45°	1067080	2388	3334
50°	702425	947	947
55°	192366	822	0
60°	38418	943	0
65°	2711	1271	0
70°	385	1571	0
75°	0	2351	0
80°	0	3504	410
85°	0	6982	818



TEST NUMBER: P1192718

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.4	2.2
10°-20°	793.7	11.7
20°-30°	1798.9	26.6
30°-40°	2159.4	31.9
40°-50°	1521.9	22.5
50°-60°	314.0	4.6
60°-70°	11.1	0.2
70°-80°	6.6	0.1
80°-90°	6.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2742.1	40.6
0°-40°	4901.4	72.5
0°-60°	6737.3	99.6
0°-90°	6761.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6761.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1220	1220	1220	1220	1220	
5°	3117	2271	1105	460	344	383
15°	10575	4652	559	199	215	3138
25°	16744	5627	328	460	523	7727
35°	17280	3940	210	275	275	10742
45°	13764	1351	31	42	43	10123
55°	2013	27	9	6	0	2652
65°	21	6	10	6	0	62
75°	0	6	11	7	0	0
85°	0	7	11	7	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192718

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7
2.5°	2079.0	2016.3	2040.9	1968.4	1952.5	1938.9	1952.5	1873.7	1829.5	1772.9	1727.4
5°	3116.6	3041.7	3059.0	2932.3	2874.5	2835.2	2827.8	2665.6	2543.8	2409.7	2270.8
7.5°	4338.8	4267.4	4257.7	4060.9	3941.7	3874.0	3845.8	3613.5	3403.2	3164.7	2904.0
10°	6005.9	5843.7	5793.3	5508.0	5280.6	5136.7	4959.7	4588.4	4219.6	3859.3	3527.3
12.5°	7946.0	7857.6	7732.2	7229.4	6830.9	6626.8	6362.6	5782.2	5224.0	4628.9	4073.2
15°	10574.6	10260.0	10046.0	9319.4	8677.7	8362.9	7976.8	7089.2	6245.6	5492.0	4652.4
17.5°	13143.1	12978.3	12643.9	11700.8	10712.4	10215.7	9640.2	8434.2	7242.9	6170.7	5145.3
20°	15273.7	15118.9	14737.7	13848.7	12752.1	12019.4	11295.2	9640.2	8083.8	6711.7	5474.9
22.5°	16294.1	16195.8	15884.7	15123.8	14189.4	13492.3	12714.0	10666.9	8705.9	7065.7	5624.9
25°	16744.2	16698.6	16498.3	15898.3	15017.9	14426.6	13691.4	11393.5	9093.2	7230.5	5627.3
27.5°	17200.3	17209.0	16766.4	16291.7	15456.9	14888.9	14180.8	11715.7	9163.3	7138.3	5442.8
30°	17344.1	17253.2	17057.7	16376.5	15583.5	14979.8	14220.0	11566.8	8875.5	6759.6	5075.3
32.5°	17285.2	17249.5	17034.4	16313.8	15368.4	14703.3	13840.1	10976.7	8307.5	6218.6	4554.0
35°	17280.3	17213.8	16720.8	16102.4	14938.1	14116.8	12979.5	10022.6	7503.4	5505.5	3940.4
37.5°	16968.0	16803.2	16433.2	15599.6	14065.1	13023.8	11748.9	8857.1	6519.9	4705.2	3331.9
40°	16509.4	16288.1	15801.2	14539.7	12552.8	11353.0	10108.7	7532.9	5478.5	3915.9	2685.1
42.5°	15551.6	15217.2	14528.6	12793.8	10537.8	9455.9	8420.7	6191.6	4467.9	3190.6	2049.5
45°	13763.9	13306.6	12375.8	10471.4	8512.9	7630.1	6797.7	4981.8	3576.5	2366.7	1351.3
47.5°	11062.8	10638.6	9791.5	8335.9	6676.0	5929.7	5265.8	3705.6	2424.5	1370.8	645.5
50°	8236.2	7872.3	7210.8	5793.3	4481.4	3895.0	3327.0	2104.9	1136.0	651.7	268.0
52.5°	4914.2	4733.5	4146.9	3212.6	2213.0	1906.9	1530.7	891.4	572.9	236.1	72.5
55°	2012.7	1857.7	1637.7	1314.3	962.7	816.3	698.3	440.2	178.3	49.2	27.0
57.5°	909.8	875.4	775.8	609.8	442.6	371.3	250.8	83.5	39.4	24.6	16.0
60°	350.4	315.9	270.5	146.2	62.7	52.9	43.0	28.3	19.7	13.5	9.8
62.5°	50.5	47.9	43.0	34.4	27.0	24.6	20.9	14.8	11.1	8.6	7.3
65°	20.9	20.9	18.4	14.8	12.4	11.1	9.8	7.3	6.2	6.2	6.2
67.5°	8.6	8.6	7.3	6.2	4.9	4.9	4.9	3.7	4.9	4.9	6.2
70°	2.4	2.4	2.4	2.4	2.4	2.4	3.7	3.7	4.9	4.9	6.2
72.5°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	4.9	6.2	6.2
75°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	4.9	6.2	6.2
77.5°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	4.9	6.2	6.2
80°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	4.9	6.2	7.3
82.5°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	4.9	6.2	7.3
85°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	4.9	6.2	7.3
87.5°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	4.9	6.2	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192718

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7
2.5°	1688.0	1609.4	1587.2	1518.3	1460.7	1432.4	1396.7	1316.7	1256.5	1176.5	1128.7
5°	2173.8	2024.9	1906.9	1763.1	1668.3	1606.9	1511.0	1364.8	1246.7	1105.4	1004.4
7.5°	2698.6	2427.0	2214.3	1977.1	1840.4	1733.6	1570.0	1359.7	1186.5	998.4	842.2
10°	3205.2	2799.6	2465.1	2124.6	1945.0	1796.3	1571.3	1307.0	1077.0	839.8	675.0
12.5°	3651.6	3127.7	2656.9	2219.2	1996.6	1811.0	1529.4	1212.2	934.4	690.9	545.9
15°	4024.0	3382.2	2792.1	2254.9	2000.3	1779.0	1442.1	1077.0	775.8	559.4	457.4
17.5°	4306.8	3516.2	2833.9	2211.9	1929.0	1688.0	1308.1	906.1	629.5	474.5	384.8
20°	4453.1	3542.1	2773.7	2095.0	1797.5	1550.4	1132.4	735.2	533.6	413.1	322.1
22.5°	4471.6	3469.5	2629.9	1927.9	1631.5	1383.2	938.1	613.4	475.8	365.1	284.0
25°	4362.2	3312.2	2424.5	1738.5	1449.6	1191.4	763.6	549.6	432.8	328.3	327.0
27.5°	4128.5	3041.7	2178.7	1518.3	1229.5	968.8	647.9	496.7	386.1	348.0	370.1
30°	3799.1	2695.0	1876.1	1240.5	960.3	745.0	545.9	409.4	339.4	343.0	361.5
32.5°	3352.8	2264.6	1520.8	908.6	687.3	560.7	409.4	279.1	281.6	282.8	298.8
35°	2792.1	1815.9	1136.0	611.0	483.2	394.7	231.1	205.3	209.1	210.2	221.3
37.5°	2237.6	1395.4	754.9	406.9	303.7	207.8	143.8	137.8	140.2	138.9	151.3
40°	1713.9	972.5	452.4	201.6	116.8	97.1	88.6	84.8	86.1	87.3	94.6
42.5°	1213.5	527.4	223.7	76.2	61.5	56.5	52.9	50.5	51.6	51.6	56.5
45°	616.0	249.6	76.2	41.8	38.1	34.4	31.9	30.8	30.8	30.8	33.2
47.5°	266.7	82.4	35.7	25.9	23.3	22.1	19.7	18.4	18.4	18.4	19.7
50°	83.5	33.2	22.1	17.3	14.8	13.5	12.4	12.4	12.4	11.1	12.4
52.5°	30.8	20.9	14.8	11.1	9.8	9.8	9.8	8.6	9.8	8.6	9.8
55°	18.4	13.5	9.8	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
57.5°	12.4	9.8	8.6	8.6	7.3	7.3	8.6	8.6	8.6	8.6	8.6
60°	8.6	8.6	7.3	7.3	7.3	7.3	8.6	8.6	8.6	8.6	8.6
62.5°	7.3	7.3	7.3	7.3	7.3	7.3	8.6	8.6	8.6	8.6	9.8
65°	6.2	7.3	7.3	7.3	7.3	7.3	8.6	8.6	9.8	9.8	9.8
67.5°	6.2	7.3	7.3	8.6	8.6	8.6	8.6	9.8	9.8	9.8	9.8
70°	7.3	7.3	8.6	8.6	8.6	8.6	9.8	9.8	9.8	9.8	11.1
72.5°	7.3	7.3	8.6	8.6	8.6	8.6	9.8	9.8	11.1	11.1	11.1
75°	7.3	8.6	8.6	8.6	8.6	9.8	9.8	9.8	11.1	11.1	11.1
77.5°	7.3	8.6	8.6	9.8	9.8	9.8	9.8	11.1	11.1	11.1	11.1
80°	7.3	8.6	8.6	9.8	9.8	9.8	11.1	11.1	11.1	11.1	12.4
82.5°	7.3	8.6	8.6	9.8	9.8	9.8	11.1	11.1	11.1	11.1	12.4
85°	8.6	8.6	9.8	9.8	9.8	9.8	11.1	11.1	11.1	11.1	12.4
87.5°	8.6	8.6	9.8	9.8	9.8	9.8	11.1	11.1	12.4	11.1	12.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192718

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7
2.5°	1064.7	993.3	944.2	925.8	890.1	833.6	800.4	769.6	711.9	699.6	667.6
5°	888.9	774.6	693.4	662.8	622.1	574.2	527.4	496.7	459.9	445.0	422.9
7.5°	700.9	586.4	516.4	491.8	463.5	424.2	382.4	351.6	313.5	293.8	275.4
10°	550.7	465.9	406.9	382.4	352.9	311.0	268.0	227.5	194.3	173.4	169.7
12.5°	447.5	377.5	314.8	288.9	254.5	212.7	181.9	180.8	178.3	177.0	179.5
15°	366.4	298.8	232.4	204.0	194.3	193.0	196.7	200.5	199.2	202.9	205.3
17.5°	301.3	228.6	214.0	215.1	216.4	220.0	226.2	236.1	237.3	243.4	248.3
20°	245.9	242.2	248.3	253.2	257.0	264.3	277.8	290.2	293.8	302.4	312.3
22.5°	279.1	290.2	303.7	309.9	314.8	328.3	343.0	362.7	370.1	381.2	394.7
25°	336.9	355.3	376.2	383.6	391.0	413.1	430.4	453.7	459.9	473.4	486.9
27.5°	384.8	404.5	426.6	436.4	442.6	464.7	479.6	494.2	494.2	501.6	511.5
30°	377.5	393.4	411.8	419.3	421.8	437.7	452.4	457.4	455.0	458.6	465.9
32.5°	313.5	325.8	340.5	346.7	349.1	360.2	372.6	372.6	371.3	371.3	376.2
35°	232.4	241.0	248.3	254.5	258.3	265.6	276.7	275.4	275.4	272.9	276.7
37.5°	156.2	161.1	169.7	172.1	173.4	178.3	186.9	186.9	184.5	185.6	188.1
40°	94.6	100.8	105.7	107.0	109.4	113.2	119.2	119.2	119.2	119.2	120.5
42.5°	56.5	60.3	64.0	64.0	65.1	70.0	72.5	72.5	72.5	72.5	73.8
45°	33.2	34.4	37.0	38.1	38.1	40.6	41.8	41.8	41.8	41.8	43.0
47.5°	19.7	20.9	20.9	22.1	22.1	23.3	24.6	24.6	23.3	23.3	23.3
50°	12.4	12.4	12.4	12.4	13.5	13.5	13.5	13.5	13.5	13.5	12.4
52.5°	9.8	9.8	9.8	9.8	8.6	8.6	8.6	8.6	7.3	7.3	6.2
55°	8.6	8.6	8.6	8.6	8.6	7.3	7.3	7.3	6.2	4.9	3.7
57.5°	8.6	8.6	8.6	8.6	8.6	7.3	7.3	6.2	4.9	4.9	3.7
60°	8.6	8.6	8.6	8.6	8.6	7.3	7.3	6.2	4.9	4.9	3.7
62.5°	9.8	9.8	8.6	8.6	8.6	7.3	7.3	6.2	6.2	4.9	3.7
65°	9.8	9.8	8.6	8.6	8.6	8.6	7.3	7.3	6.2	4.9	3.7
67.5°	9.8	9.8	9.8	9.8	8.6	8.6	8.6	7.3	6.2	4.9	3.7
70°	11.1	11.1	9.8	9.8	9.8	8.6	8.6	7.3	6.2	6.2	4.9
72.5°	11.1	11.1	9.8	9.8	9.8	9.8	8.6	7.3	7.3	6.2	4.9
75°	11.1	11.1	11.1	11.1	9.8	9.8	8.6	8.6	7.3	6.2	4.9
77.5°	11.1	11.1	11.1	11.1	9.8	9.8	9.8	8.6	7.3	6.2	4.9
80°	11.1	11.1	11.1	11.1	11.1	9.8	9.8	8.6	7.3	6.2	4.9
82.5°	12.4	12.4	11.1	11.1	11.1	9.8	9.8	8.6	7.3	6.2	6.2
85°	12.4	12.4	11.1	11.1	11.1	9.8	9.8	8.6	7.3	7.3	6.2
87.5°	12.4	12.4	11.1	11.1	11.1	9.8	9.8	8.6	7.3	7.3	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192718

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7	1219.7
2.5°	647.9	611.0	598.8	607.4	597.5	590.1	580.4	575.3
5°	405.8	378.6	370.1	372.6	363.9	356.6	346.7	344.2
7.5°	249.6	223.7	214.0	214.0	204.0	195.4	189.4	185.6
10°	167.2	162.3	163.5	164.8	163.5	164.8	161.1	163.5
12.5°	179.5	177.0	179.5	180.8	180.8	183.2	178.3	181.9
15°	209.1	206.5	210.2	212.7	212.7	216.4	211.5	215.1
17.5°	255.7	254.5	260.7	263.1	264.3	270.5	264.3	269.2
20°	323.4	322.1	330.7	334.5	333.2	345.5	336.9	345.5
22.5°	410.7	408.2	420.5	424.2	425.3	441.3	434.0	440.2
25°	498.0	500.4	506.6	512.6	513.9	527.4	516.4	522.6
27.5°	516.4	512.6	516.4	523.7	525.0	531.2	521.3	526.2
30°	467.2	461.0	462.3	470.9	473.4	475.8	467.2	469.6
32.5°	379.9	370.1	370.1	378.6	381.2	384.8	370.1	376.2
35°	280.3	271.8	271.8	277.8	279.1	281.6	270.5	275.4
37.5°	191.8	184.5	186.9	189.4	190.5	193.0	191.8	190.5
40°	122.9	118.1	121.7	121.7	122.9	124.2	124.2	125.4
42.5°	75.1	71.3	73.8	73.8	75.1	75.1	75.1	76.2
45°	43.0	41.8	41.8	43.0	43.0	43.0	41.8	43.0
47.5°	23.3	22.1	23.3	23.3	23.3	23.3	23.3	23.3
50°	12.4	11.1	11.1	11.1	11.1	11.1	11.1	11.1
52.5°	6.2	4.9	4.9	4.9	3.7	4.9	3.7	3.7
55°	3.7	2.4	2.4	2.4	1.3	1.3	0.0	0.0
57.5°	2.4	1.3	1.3	1.3	0.0	0.0	0.0	0.0
60°	2.4	1.3	1.3	1.3	0.0	0.0	0.0	0.0
62.5°	2.4	1.3	1.3	1.3	0.0	0.0	0.0	0.0
65°	2.4	1.3	1.3	1.3	0.0	0.0	0.0	0.0
67.5°	3.7	2.4	1.3	1.3	1.3	0.0	0.0	0.0
70°	3.7	2.4	2.4	1.3	1.3	0.0	0.0	0.0
72.5°	3.7	2.4	2.4	2.4	1.3	1.3	0.0	0.0
75°	3.7	2.4	2.4	2.4	1.3	1.3	0.0	0.0
77.5°	3.7	3.7	2.4	2.4	1.3	1.3	1.3	0.0
80°	4.9	3.7	2.4	2.4	2.4	1.3	1.3	1.3
82.5°	4.9	3.7	2.4	2.4	2.4	1.3	1.3	1.3
85°	4.9	3.7	3.7	2.4	2.4	1.3	1.3	1.3
87.5°	4.9	3.7	3.7	2.4	2.4	1.3	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)