

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192193

Luminaire Tested: **LDA6A40930D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192193
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26674)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40930D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3788.2 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 2.68 / 0.47 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192193

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192193

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91		
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81		
3	98	89	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72		
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	78	67	59	54	77	66	59	54	65	58	53	63	57	53	61	57	53	51		
7	73	61	54	48	71	60	53	48	59	53	48	58	52	47	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	32717	32717	32717
5°	86237	29848	9630
10°	172186	22884	3819
15°	313481	16061	4183
20°	482027	11528	26375
25°	565309	17215	21824
30°	615500	10812	6362
35°	647809	4484	2630
40°	664259	1982	1496
45°	616622	1302	1101
50°	432515	998	503
55°	158178	717	325
60°	33407	735	175
65°	2828	869	208
70°	946	1074	401
75°	169	1419	720
80°	253	2115	1073
85°	0	4214	1006



TEST NUMBER: P1192193

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.1	2.0
10°-20°	412.9	10.9
20°-30°	998.1	26.3
30°-40°	1173.3	31.0
40°-50°	886.3	23.4
50°-60°	222.4	5.9
60°-70°	10.8	0.3
70°-80°	5.1	0.1
80°-90°	4.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1486.1	39.2
0°-40°	2659.4	70.2
0°-60°	3768.1	99.5
0°-90°	3788.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3788.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	597	597	597	597	597	
5°	1567	1138	542	230	175	195
15°	5524	2396	283	76	74	1672
25°	9346	2981	285	395	361	4299
35°	9680	2197	67	48	39	6028
45°	7954	863	17	18	14	5860
55°	1655	24	8	7	3	1831
65°	22	6	7	6	2	59
75°	1	4	7	6	3	2
85°	0	4	7	5	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1192193

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	596.8	596.8	596.8	596.8	596.8	596.8	596.8	596.8	596.8	596.8	596.8
2.5°	1041.4	1024.7	1012.9	992.9	982.8	987.0	966.0	937.6	929.2	904.1	860.6
5°	1567.1	1549.5	1521.9	1479.2	1447.5	1442.4	1401.4	1332.8	1289.2	1224.7	1137.7
7.5°	2212.6	2197.5	2151.5	2087.8	2034.2	2014.2	1953.9	1833.3	1737.0	1608.1	1458.3
10°	3093.2	3034.6	2948.4	2819.5	2696.5	2639.5	2533.2	2334.0	2177.4	2000.8	1797.3
12.5°	4197.4	4093.6	3953.8	3760.4	3548.6	3442.4	3273.3	2968.5	2694.7	2391.7	2095.3
15°	5523.5	5418.8	5216.2	4916.6	4575.8	4405.0	4155.6	3675.1	3267.4	2822.8	2395.9
17.5°	7088.1	6917.4	6647.7	6213.2	5685.8	5417.9	5064.7	4399.1	3791.4	3211.2	2658.7
20°	8262.6	8137.9	7882.6	7428.0	6799.3	6454.3	5979.7	5063.1	4278.6	3521.9	2858.0
22.5°	8983.3	8871.2	8636.8	8256.7	7679.1	7296.5	6761.6	5645.7	4657.0	3737.0	2957.7
25°	9345.9	9265.5	9102.3	8770.7	8265.9	7881.7	7340.9	6076.8	4913.2	3853.3	2981.1
27.5°	9664.8	9530.0	9264.7	9038.6	8591.6	8200.6	7688.3	6291.1	5002.8	3840.0	2921.7
30°	9723.4	9646.3	9437.1	9114.0	8697.9	8302.8	7762.8	6260.1	4901.4	3684.2	2760.0
32.5°	9673.2	9606.2	9448.0	9095.6	8630.1	8193.9	7601.2	6005.6	4604.3	3395.5	2487.1
35°	9679.9	9573.5	9296.5	8995.1	8414.1	7901.8	7206.1	5540.2	4188.3	3020.4	2196.6
37.5°	9551.8	9376.8	9148.2	8759.8	7975.5	7340.0	6544.8	4940.0	3687.6	2637.8	1857.6
40°	9282.2	9149.2	8845.2	8248.4	7227.9	6429.2	5694.3	4251.0	3141.0	2220.1	1514.4
42.5°	8841.9	8682.9	8258.4	7358.4	6145.4	5448.9	4787.6	3546.2	2603.5	1815.7	1188.7
45°	7953.6	7710.9	7155.9	6082.7	5047.9	4457.0	3917.8	2891.5	2110.4	1420.6	863.1
47.5°	6534.7	6327.9	5741.2	4845.4	4030.9	3573.7	3114.1	2280.4	1570.5	913.4	443.7
50°	5071.4	4908.1	4460.2	3674.2	2994.5	2550.8	2189.1	1455.8	837.1	420.2	199.3
52.5°	3336.8	3233.9	2849.6	2293.7	1719.5	1403.0	1139.4	632.0	390.1	186.7	68.6
55°	1655.0	1522.8	1339.4	992.9	718.2	581.0	493.0	311.4	161.6	53.6	24.3
57.5°	674.7	645.4	581.0	448.7	344.9	291.3	232.7	97.1	36.0	21.8	15.0
60°	304.7	291.3	252.8	177.4	96.3	59.5	41.9	26.7	18.4	13.4	10.1
62.5°	53.6	49.4	43.5	33.5	26.7	23.5	20.1	15.0	11.7	9.3	7.5
65°	21.8	21.8	20.1	17.6	14.2	13.4	11.7	9.3	7.5	6.7	5.9
67.5°	11.7	10.9	10.9	9.3	8.3	7.5	6.7	5.9	5.9	5.0	5.0
70°	5.9	5.9	5.9	5.0	4.2	4.2	4.2	4.2	4.2	4.2	4.2
72.5°	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5	2.5	3.4	3.4
75°	0.8	0.8	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	4.2
77.5°	0.8	0.8	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	4.2
80°	0.8	0.8	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	4.2
82.5°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	2.5	3.4	4.2
85°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	2.5	3.4	4.2
87.5°	0.0	0.0	0.8	0.8	0.8	1.6	1.6	2.5	2.5	3.4	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192193

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	596.8	596.8	596.8	596.8	596.8	596.8	596.8	596.8	596.8	596.8	596.8
2.5°	858.9	815.3	781.9	750.1	742.5	716.6	692.3	650.4	612.8	577.6	537.5
5°	1104.2	1018.8	947.6	878.2	855.6	812.0	753.4	678.1	607.7	542.4	473.8
7.5°	1371.2	1226.4	1100.0	982.8	941.8	879.8	785.2	678.1	576.8	483.1	399.3
10°	1633.2	1417.3	1226.4	1057.3	995.3	915.0	785.2	648.8	519.9	411.1	328.1
12.5°	1886.1	1589.7	1331.9	1108.4	1027.1	926.7	764.3	597.8	447.9	340.7	271.3
15°	2083.7	1735.4	1406.4	1128.5	1027.1	910.8	715.8	526.6	375.1	283.0	221.0
17.5°	2231.8	1821.6	1431.5	1109.2	992.1	861.4	642.1	442.8	308.9	234.4	175.0
20°	2318.0	1843.4	1405.6	1053.2	925.1	786.9	550.9	365.0	262.0	197.6	141.4
22.5°	2338.2	1813.3	1345.3	981.2	848.9	709.1	470.5	326.5	252.8	201.7	176.6
25°	2315.6	1752.1	1265.8	908.3	776.9	638.7	441.2	351.6	303.0	284.6	304.7
27.5°	2226.0	1638.3	1167.9	827.1	694.9	565.9	418.6	354.1	304.7	296.4	287.1
30°	2066.1	1466.7	1017.2	676.5	536.6	429.5	297.2	211.0	168.3	170.8	169.1
32.5°	1815.7	1217.2	796.1	473.0	369.2	290.5	196.7	124.8	117.2	117.2	115.5
35°	1540.3	988.7	598.6	332.4	257.0	204.3	117.2	91.2	77.0	67.0	60.3
37.5°	1259.9	769.3	412.7	224.4	163.3	104.6	56.1	46.1	41.0	38.5	37.6
40°	975.3	541.6	263.7	123.0	72.0	46.1	36.0	31.0	28.5	27.7	27.7
42.5°	721.6	349.1	142.3	48.6	38.5	31.8	25.9	22.6	21.8	21.8	20.9
45°	434.5	175.0	53.6	30.1	25.1	22.6	19.2	17.6	16.8	16.8	17.6
47.5°	200.9	65.3	29.3	20.1	18.4	16.8	15.0	14.2	14.2	14.2	15.0
50°	72.8	28.5	18.4	14.2	13.4	12.5	11.7	10.9	10.9	11.7	11.7
52.5°	27.7	17.6	13.4	10.9	10.1	10.1	9.3	9.3	9.3	9.3	9.3
55°	16.8	12.5	10.1	8.3	8.3	7.5	7.5	7.5	7.5	7.5	7.5
57.5°	10.9	9.3	7.5	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
60°	8.3	6.7	5.9	5.9	5.9	5.9	5.9	6.7	6.7	6.7	6.7
62.5°	6.7	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.7	6.7	6.7
65°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.7	6.7	6.7	7.5
67.5°	5.0	5.0	5.0	5.0	5.0	5.9	5.9	5.9	6.7	6.7	6.7
70°	4.2	4.2	5.0	5.0	5.0	5.9	5.9	5.9	6.7	6.7	6.7
72.5°	4.2	5.0	5.0	5.0	5.0	5.9	5.9	5.9	6.7	6.7	6.7
75°	4.2	5.0	5.0	5.0	5.9	5.9	5.9	5.9	6.7	6.7	6.7
77.5°	4.2	5.0	5.0	5.0	5.9	5.9	5.9	6.7	6.7	6.7	7.5
80°	4.2	5.0	5.0	5.9	5.9	5.9	5.9	6.7	6.7	6.7	7.5
82.5°	4.2	5.0	5.0	5.9	5.9	5.9	6.7	6.7	6.7	7.5	7.5
85°	4.2	5.0	5.0	5.9	5.9	5.9	6.7	6.7	6.7	6.7	7.5
87.5°	4.2	5.0	5.0	5.9	5.9	5.9	5.9	6.7	6.7	6.7	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192193

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	596.8	596.8	596.8	596.8	596.8	596.8	596.8	596.8	596.8	596.8	596.8
2.5°	515.7	481.3	457.0	435.3	426.9	407.7	386.8	362.5	342.3	340.7	323.9
5°	427.8	380.1	345.7	323.9	313.1	293.0	268.7	252.8	230.2	223.5	206.8
7.5°	345.7	301.4	269.5	249.5	236.9	212.6	185.1	167.5	149.1	134.8	116.3
10°	281.2	238.6	204.3	184.1	171.6	145.7	117.2	97.1	80.3	77.0	75.3
12.5°	226.0	182.5	148.1	126.4	113.1	88.8	81.2	77.9	75.3	72.8	72.8
15°	175.8	131.5	94.6	86.2	83.7	81.2	79.5	77.9	76.2	75.3	76.2
17.5°	128.1	92.9	88.8	87.8	86.2	86.2	87.8	88.8	90.4	92.1	94.6
20°	113.1	113.9	123.0	129.7	127.2	139.8	157.4	171.6	205.9	226.8	255.3
22.5°	202.5	232.7	275.4	301.4	315.6	357.5	403.6	473.0	508.2	558.4	603.6
25°	346.6	381.7	418.6	428.7	436.2	440.4	434.5	402.6	395.1	380.9	376.7
27.5°	259.5	242.8	248.6	251.1	248.6	245.2	235.3	217.7	213.5	206.8	208.4
30°	153.2	148.1	154.9	154.0	154.0	154.0	150.7	136.4	129.7	122.2	117.2
32.5°	113.1	103.8	96.3	89.6	87.0	82.9	80.3	74.5	72.0	68.6	68.6
35°	56.1	53.6	53.6	51.9	51.0	51.9	51.9	49.4	47.7	46.9	46.9
37.5°	36.8	36.8	37.6	36.8	36.8	36.8	36.8	36.0	35.2	34.4	34.4
40°	27.7	27.7	28.5	28.5	27.7	27.7	27.7	26.7	26.7	26.7	26.7
42.5°	21.8	21.8	21.8	21.8	20.9	21.8	21.8	21.8	20.9	20.9	20.1
45°	18.4	17.6	17.6	17.6	17.6	17.6	18.4	17.6	17.6	16.8	16.8
47.5°	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0	14.2	14.2
50°	11.7	11.7	11.7	11.7	11.7	10.9	10.9	10.1	10.1	9.3	9.3
52.5°	9.3	9.3	8.3	8.3	8.3	8.3	8.3	8.3	7.5	7.5	7.5
55°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.7	5.9	5.9
57.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.0
60°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.9	5.0	5.0	5.0
62.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.9	5.0	5.0	4.2
65°	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.9	5.9	5.0	5.0
67.5°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.9	5.9	5.0
70°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.9	5.9	5.0
72.5°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.9	5.9	5.0
75°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.9	5.9	5.0
77.5°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.9	5.9	5.0
80°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.9	5.9	5.0
82.5°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.9	5.9	5.0
85°	7.5	7.5	6.7	6.7	6.7	6.7	6.7	5.9	5.0	5.0	4.2
87.5°	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.0	4.2	4.2	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192193

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	596.8	596.8	596.8	596.8	596.8	596.8	596.8	596.8
2.5°	320.6	308.9	306.4	309.7	296.4	296.4	296.4	302.2
5°	200.1	188.4	185.1	185.9	175.0	167.5	171.6	175.0
7.5°	108.8	96.3	92.1	92.1	81.2	77.0	77.9	79.5
10°	72.8	71.2	71.2	70.4	68.6	67.8	68.6	68.6
12.5°	70.4	69.4	69.4	68.6	68.6	67.8	67.8	68.6
15°	73.7	73.7	73.7	72.8	72.8	72.0	73.7	73.7
17.5°	93.7	95.5	98.8	100.5	103.8	100.5	106.4	105.4
20°	275.4	303.0	354.1	373.4	428.7	401.8	459.6	452.1
22.5°	623.7	643.7	652.2	656.3	657.1	684.0	688.1	697.3
25°	368.4	363.3	359.1	359.1	344.1	361.7	358.3	360.8
27.5°	196.7	195.0	190.8	192.6	185.1	190.8	192.6	192.6
30°	111.3	108.0	104.6	104.6	97.9	101.3	100.5	100.5
32.5°	64.5	62.7	61.1	60.3	58.6	58.6	57.8	57.8
35°	44.3	43.5	42.7	41.9	40.2	39.3	39.3	39.3
37.5°	32.6	31.8	31.0	31.0	30.1	28.5	28.5	28.5
40°	25.1	24.3	23.5	23.5	22.6	20.9	20.9	20.9
42.5°	19.2	18.4	17.6	16.8	16.8	15.9	15.0	15.0
45°	15.9	15.9	15.0	15.0	14.2	14.2	14.2	14.2
47.5°	13.4	13.4	12.5	12.5	12.5	11.7	11.7	10.9
50°	8.3	7.5	7.5	6.7	6.7	5.9	5.9	5.9
52.5°	6.7	5.9	5.9	5.0	5.0	4.2	4.2	4.2
55°	5.0	5.0	4.2	4.2	4.2	3.4	3.4	3.4
57.5°	4.2	4.2	3.4	3.4	3.4	2.5	2.5	2.5
60°	4.2	3.4	3.4	2.5	2.5	2.5	1.6	1.6
62.5°	4.2	3.4	3.4	2.5	2.5	1.6	1.6	1.6
65°	4.2	3.4	3.4	2.5	2.5	2.5	2.5	1.6
67.5°	4.2	4.2	3.4	3.4	3.4	2.5	2.5	2.5
70°	5.0	4.2	4.2	3.4	3.4	3.4	3.4	2.5
72.5°	5.0	4.2	4.2	4.2	3.4	3.4	3.4	3.4
75°	5.0	4.2	4.2	4.2	3.4	3.4	3.4	3.4
77.5°	5.0	4.2	4.2	4.2	3.4	3.4	3.4	3.4
80°	5.0	4.2	4.2	4.2	3.4	3.4	3.4	3.4
82.5°	4.2	4.2	4.2	3.4	3.4	3.4	3.4	3.4
85°	3.4	3.4	3.4	2.5	2.5	2.5	2.5	1.6
87.5°	2.5	2.5	1.6	1.6	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)