

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192720

Luminaire Tested: **LDA6A70935D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192720
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26690)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70935D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6280.8 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 2.55 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192720

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192720

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	75	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65		
5	85	74	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	63284	63284	63284
5°	163383	58662	18336
10°	309942	44755	6157
15°	554214	29092	6135
20°	825803	19800	11189
25°	942266	24685	70268
30°	1019005	20623	21010
35°	1070408	10038	6585
40°	1087337	3614	3342
45°	968759	2388	2008
50°	622189	1680	1365
55°	163798	1166	698
60°	36532	1217	537
65°	3502	1440	636
70°	1170	1779	785
75°	275	2351	1313
80°	0	3852	1957
85°	0	6982	3082



TEST NUMBER: P1192720

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.2	2.2
10°-20°	731.7	11.6
20°-30°	1716.7	27.3
30°-40°	1974.6	31.4
40°-50°	1402.7	22.3
50°-60°	285.2	4.5
60°-70°	14.3	0.2
70°-80°	8.5	0.1
80°-90°	7.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2588.6	41.2
0°-40°	4563.2	72.7
0°-60°	6251.0	99.5
0°-90°	6280.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6280.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1154	1154	1154	1154	1154	
5°	2969	2148	1066	427	333	362
15°	9765	4390	513	116	108	2929
25°	15578	5288	408	891	1162	7179
35°	15995	3713	150	111	98	9936
45°	12496	1320	31	33	26	9209
55°	1714	34	12	12	7	2311
65°	27	10	11	10	5	65
75°	1	6	11	10	6	3
85°	0	6	11	9	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192720

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4
2.5°	1989.1	1928.9	1899.4	1898.3	1812.1	1840.4	1812.1	1790.0	1710.2	1677.0	1621.6
5°	2969.0	2895.2	2836.2	2810.5	2663.0	2630.9	2616.2	2541.2	2373.9	2276.9	2147.7
7.5°	4124.7	4047.3	3950.1	3872.6	3658.8	3598.5	3559.1	3430.1	3182.9	2987.5	2746.5
10°	5567.9	5522.5	5365.2	5222.5	4898.0	4772.6	4654.5	4353.3	4030.0	3637.8	3326.7
12.5°	7511.8	7404.8	7124.4	6839.2	6330.2	6143.4	5947.8	5466.0	4971.8	4357.0	3843.1
15°	9765.2	9674.2	9242.6	8778.0	8053.9	7746.6	7440.4	6681.8	5922.1	5130.4	4390.2
17.5°	12359.3	12187.2	11758.1	10972.5	9959.5	9476.3	8905.9	7939.6	6842.8	5767.2	4847.5
20°	14155.4	14053.3	13690.7	12937.1	11784.0	11145.8	10437.7	9111.2	7611.3	6277.4	5147.5
22.5°	15137.7	15035.8	14764.0	14098.9	13153.5	12513.0	11690.5	10059.0	8191.5	6620.4	5289.0
25°	15577.9	15511.4	15362.8	14820.5	13945.2	13368.6	12590.4	10714.3	8554.3	6776.5	5287.7
27.5°	15984.8	16002.1	15634.4	15188.2	14381.6	13802.6	13064.9	11009.3	8625.6	6697.9	5118.0
30°	16097.8	16054.8	15893.8	15265.6	14514.4	13883.7	13093.2	10853.3	8347.7	6349.9	4781.2
32.5°	16027.8	16029.1	15877.8	15210.3	14327.6	13621.8	12733.0	10293.8	7806.7	5804.0	4257.5
35°	15994.6	15983.5	15591.4	15005.0	13883.7	13053.8	11933.9	9396.4	7056.8	5106.9	3712.8
37.5°	15665.2	15598.7	15316.0	14520.5	13053.8	11992.9	10786.9	8298.5	6133.5	4381.6	3154.6
40°	15194.2	15110.7	14650.8	13509.9	11635.1	10451.3	9252.6	7055.6	5167.2	3659.9	2532.5
42.5°	14229.2	14091.5	13394.5	11881.0	9808.2	8706.7	7713.4	5811.4	4224.3	2971.5	1945.0
45°	12495.7	12270.7	11305.7	9724.7	7917.4	7053.1	6213.4	4658.3	3382.1	2212.9	1320.3
47.5°	10033.2	9787.3	8912.1	7642.1	6198.6	5497.9	4784.8	3430.1	2287.9	1289.7	662.6
50°	7295.4	7125.7	6352.3	5281.5	4098.9	3511.2	2964.1	1912.9	1097.9	623.4	271.6
52.5°	4203.3	4081.7	3543.1	2779.7	2016.2	1688.0	1357.3	834.7	559.4	247.0	87.3
55°	1713.8	1643.7	1407.6	1192.5	895.0	773.3	645.5	416.7	188.1	59.0	34.4
57.5°	838.5	829.8	692.1	554.5	408.1	329.4	248.3	83.5	45.4	29.5	22.1
60°	333.2	320.8	220.0	127.8	71.3	57.8	49.2	34.4	25.9	19.7	16.0
62.5°	57.8	56.5	47.9	40.6	33.2	29.5	27.0	20.9	17.3	13.5	12.2
65°	27.0	27.0	24.6	22.1	18.4	17.3	16.0	13.5	11.1	9.8	9.8
67.5°	13.5	13.5	12.2	11.1	9.8	9.8	8.6	8.6	7.3	7.3	7.3
70°	7.3	7.3	7.3	6.2	6.2	6.2	6.2	6.2	4.9	6.2	6.2
72.5°	4.9	4.9	4.9	3.7	2.4	3.7	3.7	3.7	4.9	6.2	6.2
75°	1.3	1.3	1.3	2.4	2.4	2.4	3.7	3.7	4.9	6.2	6.2
77.5°	1.3	1.3	1.3	1.3	2.4	2.4	2.4	3.7	4.9	6.2	6.2
80°	0.0	1.3	1.3	1.3	2.4	2.4	2.4	3.7	4.9	6.2	6.2
82.5°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	4.9	6.2	6.2
85°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	4.9	6.2	6.2
87.5°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	4.9	6.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192720

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4
2.5°	1597.0	1533.0	1491.3	1417.5	1386.8	1373.3	1305.7	1240.5	1177.8	1132.3	1062.2
5°	2049.4	1947.4	1791.3	1644.9	1581.0	1540.5	1407.6	1284.7	1167.9	1066.0	944.2
7.5°	2536.3	2326.0	2081.5	1846.6	1735.9	1662.1	1456.8	1277.3	1110.1	955.2	789.3
10°	3003.5	2672.7	2316.3	1980.6	1830.5	1719.9	1451.9	1222.0	1004.4	804.0	625.8
12.5°	3401.8	2974.0	2500.6	2065.3	1869.9	1728.6	1406.5	1126.2	861.8	646.7	491.8
15°	3737.4	3205.1	2622.3	2093.7	1858.9	1691.6	1317.9	994.6	705.8	512.6	397.2
17.5°	3973.5	3316.9	2650.6	2045.8	1781.3	1588.4	1183.9	826.1	554.5	414.3	313.5
20°	4111.1	3331.8	2581.7	1928.9	1646.2	1442.1	1015.5	649.1	449.9	339.4	243.4
22.5°	4132.0	3259.1	2446.5	1771.6	1490.0	1293.3	845.8	543.4	409.4	317.2	238.6
25°	4031.2	3115.3	2270.7	1617.9	1348.7	1147.1	731.5	549.6	459.9	408.1	424.2
27.5°	3835.8	2878.1	2069.1	1460.5	1201.1	997.1	690.9	575.3	501.6	510.2	539.7
30°	3535.8	2543.6	1778.9	1193.8	919.6	759.8	549.6	414.3	344.2	325.8	327.0
32.5°	3094.5	2124.4	1396.5	828.6	618.3	512.6	348.0	231.1	232.4	215.1	214.0
35°	2590.3	1710.2	1045.0	555.6	427.8	356.5	205.3	162.3	156.2	150.0	141.4
37.5°	2091.2	1321.6	695.8	379.9	272.9	197.9	103.2	84.8	78.7	73.8	73.8
40°	1592.1	924.5	430.2	199.2	110.6	81.1	61.4	51.6	50.5	50.5	49.2
42.5°	1155.7	545.9	233.5	78.7	61.4	54.1	43.0	38.1	38.1	38.1	38.1
45°	614.7	277.8	89.7	49.2	40.6	38.1	31.9	29.5	29.5	30.8	30.8
47.5°	284.0	104.5	45.4	33.2	28.3	28.3	24.6	23.3	23.3	24.6	24.6
50°	102.1	43.0	29.5	23.3	20.9	22.1	19.7	18.4	19.7	19.7	19.7
52.5°	39.4	27.0	20.9	18.4	16.0	17.3	14.8	14.8	16.0	16.0	16.0
55°	24.6	19.7	16.0	13.5	12.2	13.5	12.2	12.2	12.2	12.2	12.2
57.5°	17.3	14.8	12.2	11.1	9.8	11.1	11.1	11.1	11.1	11.1	11.1
60°	13.5	11.1	9.8	9.8	9.8	9.8	9.8	9.8	9.8	11.1	11.1
62.5°	11.1	9.8	9.8	9.8	9.8	9.8	9.8	9.8	11.1	11.1	11.1
65°	9.8	8.6	9.8	9.8	8.6	9.8	9.8	9.8	11.1	11.1	12.2
67.5°	7.3	7.3	7.3	8.6	8.6	8.6	9.8	9.8	11.1	11.1	11.1
70°	7.3	7.3	8.6	8.6	8.6	8.6	9.8	9.8	11.1	11.1	11.1
72.5°	7.3	7.3	8.6	8.6	8.6	9.8	9.8	9.8	11.1	11.1	11.1
75°	7.3	7.3	8.6	8.6	8.6	9.8	9.8	9.8	11.1	11.1	11.1
77.5°	7.3	7.3	8.6	8.6	8.6	9.8	9.8	11.1	11.1	11.1	11.1
80°	7.3	8.6	8.6	9.8	9.8	9.8	9.8	11.1	11.1	12.2	12.2
82.5°	7.3	8.6	8.6	9.8	9.8	9.8	9.8	11.1	11.1	12.2	12.2
85°	7.3	8.6	8.6	9.8	9.8	9.8	9.8	11.1	11.1	11.1	11.1
87.5°	7.3	8.6	8.6	9.8	9.8	9.8	9.8	9.8	11.1	11.1	11.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192720

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4
2.5°	1015.5	955.2	895.0	865.5	839.6	802.8	756.1	718.0	677.4	656.6	608.5
5°	848.3	745.0	657.7	615.9	584.0	539.7	491.8	457.3	426.6	409.4	378.6
7.5°	656.6	558.2	481.9	449.9	426.6	382.4	346.7	311.0	279.1	255.7	225.0
10°	507.7	431.5	368.8	338.1	312.3	265.6	222.5	189.4	154.9	131.6	121.7
12.5°	403.2	331.9	268.0	237.3	210.2	162.3	130.3	124.2	118.1	115.6	111.9
15°	309.9	244.6	177.0	146.2	135.2	129.1	121.7	120.5	115.6	115.6	111.9
17.5°	232.4	159.8	135.2	132.7	131.6	129.1	125.4	124.2	122.9	122.9	121.7
20°	167.2	154.9	151.3	153.7	154.9	157.3	156.2	156.2	161.1	172.1	169.7
22.5°	234.8	254.5	275.4	282.7	309.9	336.9	361.5	392.1	464.7	548.3	568.0
25°	464.7	523.7	577.8	607.4	651.5	711.8	769.6	840.9	891.4	933.1	981.1
27.5°	577.8	599.9	591.3	595.0	590.1	581.5	584.0	598.8	591.3	569.1	577.8
30°	341.8	359.1	349.1	354.0	340.5	340.5	336.9	344.2	339.4	330.7	328.3
32.5°	222.5	232.4	231.1	231.1	226.2	223.7	215.1	212.7	204.0	188.1	184.3
35°	134.0	127.8	121.7	118.1	115.6	115.6	114.3	114.3	110.6	107.0	105.7
37.5°	72.5	73.8	73.8	73.8	73.8	76.2	75.1	75.1	75.1	72.5	72.5
40°	50.5	52.9	52.9	52.9	54.1	54.1	54.1	55.4	54.1	54.1	54.1
42.5°	39.4	40.6	39.4	39.4	40.6	40.6	40.6	41.8	41.8	41.8	40.6
45°	31.9	31.9	30.8	31.9	31.9	33.2	33.2	33.2	33.2	31.9	31.9
47.5°	25.9	25.9	25.9	25.9	27.0	27.0	27.0	27.0	27.0	27.0	27.0
50°	20.9	20.9	20.9	22.1	22.1	22.1	20.9	22.1	22.1	22.1	20.9
52.5°	16.0	16.0	16.0	16.0	16.0	14.8	14.8	14.8	14.8	14.8	13.5
55°	12.2	12.2	12.2	12.2	12.2	13.5	12.2	13.5	12.2	12.2	11.1
57.5°	11.1	11.1	11.1	11.1	12.2	12.2	11.1	11.1	11.1	9.8	9.8
60°	11.1	11.1	11.1	11.1	11.1	11.1	11.1	11.1	9.8	8.6	8.6
62.5°	12.2	12.2	11.1	11.1	11.1	11.1	9.8	9.8	9.8	8.6	8.6
65°	12.2	12.2	11.1	12.2	12.2	11.1	11.1	9.8	9.8	8.6	8.6
67.5°	12.2	12.2	12.2	12.2	12.2	12.2	11.1	11.1	9.8	9.8	8.6
70°	12.2	12.2	12.2	12.2	12.2	12.2	11.1	11.1	9.8	9.8	8.6
72.5°	12.2	12.2	12.2	12.2	12.2	12.2	11.1	11.1	11.1	9.8	8.6
75°	12.2	12.2	12.2	12.2	12.2	11.1	11.1	11.1	9.8	9.8	8.6
77.5°	12.2	12.2	12.2	12.2	12.2	11.1	11.1	11.1	9.8	9.8	8.6
80°	12.2	12.2	12.2	12.2	12.2	12.2	11.1	11.1	9.8	9.8	8.6
82.5°	12.2	12.2	12.2	12.2	12.2	11.1	11.1	11.1	9.8	9.8	8.6
85°	12.2	11.1	11.1	11.1	11.1	11.1	9.8	9.8	8.6	8.6	7.3
87.5°	11.1	11.1	11.1	11.1	11.1	9.8	9.8	8.6	7.3	6.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192720

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4
2.5°	608.5	597.5	592.6	584.0	576.6	572.9	559.4	575.3
5°	372.6	359.1	355.3	348.0	339.4	334.5	324.5	333.2
7.5°	212.7	196.7	189.4	183.2	174.6	167.2	158.6	163.5
10°	119.2	114.3	115.6	111.9	110.6	109.4	108.1	110.6
12.5°	110.6	107.0	108.1	105.7	104.5	104.5	103.2	104.5
15°	111.9	108.1	110.6	108.1	107.0	107.0	105.7	108.1
17.5°	121.7	119.2	121.7	119.2	120.5	119.2	120.5	121.7
20°	170.8	174.6	181.9	177.0	180.8	185.6	191.8	191.8
22.5°	601.2	679.9	689.6	729.0	829.8	826.1	893.8	896.3
25°	1049.9	1054.9	1099.0	1084.4	1085.5	1137.1	1132.3	1161.7
27.5°	603.7	602.4	611.0	595.0	599.9	603.7	590.1	606.1
30°	336.9	330.7	334.5	325.8	325.8	328.3	324.5	331.9
32.5°	186.9	181.9	181.9	175.9	174.6	173.4	169.7	173.4
35°	107.0	103.2	104.5	102.1	99.7	98.4	97.1	98.4
37.5°	73.8	71.3	72.5	70.0	67.6	66.4	65.1	66.4
40°	54.1	52.9	52.9	50.5	49.2	47.9	46.7	46.7
42.5°	40.6	39.4	39.4	36.8	35.7	34.4	33.2	34.4
45°	30.8	29.5	29.5	28.3	27.0	25.9	25.9	25.9
47.5°	27.0	25.9	27.0	25.9	24.6	24.6	24.6	24.6
50°	20.9	20.9	20.9	19.7	18.4	18.4	17.3	16.0
52.5°	13.5	12.2	12.2	11.1	11.1	9.8	9.8	9.8
55°	11.1	9.8	9.8	8.6	8.6	7.3	7.3	7.3
57.5°	8.6	8.6	7.3	7.3	6.2	6.2	6.2	6.2
60°	7.3	7.3	7.3	6.2	6.2	4.9	4.9	4.9
62.5°	7.3	6.2	6.2	6.2	4.9	4.9	4.9	4.9
65°	7.3	6.2	6.2	6.2	4.9	4.9	4.9	4.9
67.5°	7.3	6.2	6.2	6.2	4.9	4.9	4.9	4.9
70°	8.6	7.3	7.3	6.2	6.2	6.2	4.9	4.9
72.5°	8.6	7.3	7.3	7.3	6.2	6.2	6.2	6.2
75°	8.6	7.3	7.3	7.3	6.2	6.2	6.2	6.2
77.5°	8.6	7.3	7.3	7.3	6.2	6.2	6.2	6.2
80°	8.6	7.3	7.3	7.3	6.2	6.2	6.2	6.2
82.5°	7.3	7.3	7.3	6.2	6.2	6.2	6.2	6.2
85°	7.3	6.2	6.2	6.2	4.9	4.9	4.9	4.9
87.5°	4.9	4.9	3.7	3.7	3.7	2.4	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)