

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192730

Luminaire Tested: **LDA6A70940D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192730
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70940D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6329.0 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192730

CATALOG NUMBER: LDA6A70940D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192730

CATALOG NUMBER: LDA6A70940D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104	110	107	104	102		103	101	99			99	97	96			96
2	105	100	95	91	103	98	94	90		95	91	88			92	89	86			89
3	99	91	85	80	96	89	84	80		87	82	78			84	80	77			82
4	92	83	76	71	90	82	76	71		79	74	70			77	73	69			75
5	86	76	69	64	84	75	68	63		73	67	63			71	66	62			69
6	80	69	62	57	79	69	62	57		67	61	56			65	60	56			64
7	75	64	56	51	73	63	56	51		62	55	51			60	55	50			59
8	70	59	51	46	69	58	51	46		57	50	46			56	50	46			54
9	66	54	47	42	64	53	47	42		52	46	42			51	46	42			50
10	61	50	43	38	60	49	43	38		48	42	38			48	42	38			47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	97953	97953	97953
5°	189797	93341	31488
10°	322461	81684	14134
15°	496893	65148	22475
20°	719313	42395	39098
25°	1055353	40914	50271
30°	1227100	38759	38519
35°	1242032	20539	20365
40°	1028312	7736	8552
45°	776639	2628	3124
50°	531360	972	972
55°	73909	841	124
60°	1919	822	0
65°	480	1141	0
70°	208	1410	0
75°	0	1864	0
80°	0	3189	410
85°	0	6353	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192730

CATALOG NUMBER: LDA6A70940D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.5	3.0
10°-20°	792.4	12.5
20°-30°	1807.5	28.6
30°-40°	2091.7	33.1
40°-50°	1261.5	19.9
50°-60°	171.4	2.7
60°-70°	5.5	0.1
70°-80°	6.0	0.1
80°-90°	5.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2787.3	44.0
0°-40°	4879.1	77.1
0°-60°	6312.0	99.7
0°-90°	6329.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6329.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1787	1787	1787	1787	1787	
5°	3449	2824	1696	928	572	401
15°	8755	4921	1148	353	396	2592
25°	17448	5832	676	814	831	7896
35°	18559	4446	307	313	304	11185
45°	10018	1211	34	42	40	7833
55°	773	9	9	6	1	1516
65°	4	5	9	5	0	6
75°	0	6	9	6	0	0
85°	0	6	10	6	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1192730

CATALOG NUMBER: LDA6A70940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8
2.5°	2583.9	2560.0	2570.1	2543.8	2477.0	2463.2	2461.9	2444.4	2387.7	2343.7	2291.0
5°	3449.0	3447.8	3454.0	3397.5	3280.6	3244.0	3226.5	3183.6	3046.6	2941.1	2824.2
7.5°	4529.1	4521.5	4514.1	4410.9	4227.3	4156.9	4111.7	3957.0	3768.5	3581.1	3372.3
10°	5792.8	5789.1	5760.0	5579.0	5284.8	5155.2	5067.2	4822.1	4519.1	4252.5	3897.9
12.5°	7260.1	7226.2	7174.7	6909.4	6505.8	6364.9	6171.3	5782.8	5317.4	4908.9	4413.4
15°	8755.2	8706.1	8614.4	8273.6	7773.2	7533.1	7292.9	6781.1	6149.9	5556.4	4921.4
17.5°	10217.6	10163.5	9948.4	9370.0	8881.0	8587.9	8321.3	7618.5	6876.6	6113.5	5308.7
20°	12330.0	12133.8	11759.1	10847.6	9938.5	9410.3	9098.4	8355.4	7437.4	6548.5	5584.0
22.5°	15151.5	14716.5	13918.0	12436.8	11138.0	10376.0	9865.4	8877.1	7841.1	6832.6	5753.9
25°	17447.5	17250.1	16342.3	14235.0	12208.0	11310.1	10599.8	9292.1	8135.3	7022.6	5831.8
27.5°	18927.5	18878.4	17841.1	15723.7	13081.9	11903.7	11110.3	9566.2	8277.3	7062.7	5794.0
30°	19385.2	19461.8	18466.0	16229.1	13334.7	12023.1	11155.6	9569.9	8168.1	6880.5	5552.7
32.5°	19351.2	19355.0	18134.1	15792.9	12923.4	11676.1	10778.4	9251.8	7764.4	6424.0	5093.7
35°	18559.1	18364.2	16983.6	14452.4	11966.6	10866.4	10031.5	8635.7	7099.2	5737.5	4446.2
37.5°	16820.1	16564.9	14955.4	12736.0	10833.6	9816.4	9142.4	7827.3	6307.0	5004.4	3777.2
40°	14369.4	14007.3	12679.5	11140.5	9593.9	8829.4	8263.5	6923.2	5459.7	4285.1	3149.7
42.5°	11916.2	11738.9	10861.4	9610.2	8551.6	7832.3	7241.3	5976.3	4644.8	3576.1	2356.4
45°	10017.6	9865.4	9275.7	8450.9	7412.3	6756.0	6186.4	4989.3	3608.7	2399.1	1210.9
47.5°	8634.5	8511.3	7946.8	7080.4	5941.2	5223.3	4636.0	3271.8	2044.5	1036.1	303.0
50°	6230.4	6104.6	5551.4	4548.0	3519.4	2918.3	2495.9	1461.1	579.6	209.9	31.5
52.5°	3054.2	2951.1	2575.1	1927.6	1293.9	930.5	680.3	274.1	66.6	22.6	15.1
55°	773.3	710.4	592.3	372.1	182.3	109.4	70.5	25.2	16.4	12.5	8.8
57.5°	44.0	42.7	39.0	28.9	21.4	18.8	16.4	12.5	8.8	7.5	6.3
60°	17.5	16.4	15.1	12.5	10.1	8.8	8.8	6.3	5.0	5.0	5.0
62.5°	7.5	7.5	7.5	6.3	5.0	5.0	5.0	3.7	5.0	5.0	5.0
65°	3.7	3.7	3.7	2.4	2.4	2.4	3.7	3.7	3.7	5.0	5.0
67.5°	2.4	1.3	1.3	1.3	2.4	2.4	2.4	3.7	3.7	5.0	5.0
70°	1.3	1.3	1.3	1.3	2.4	2.4	2.4	3.7	3.7	5.0	6.3
72.5°	0.0	1.3	1.3	1.3	2.4	2.4	2.4	3.7	3.7	5.0	6.3
75°	0.0	1.3	1.3	1.3	2.4	2.4	2.4	3.7	5.0	5.0	6.3
77.5°	0.0	1.3	1.3	1.3	2.4	2.4	2.4	3.7	5.0	5.0	6.3
80°	0.0	1.3	1.3	1.3	2.4	2.4	2.4	3.7	5.0	5.0	6.3
82.5°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	5.0	5.0	6.3
85°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	5.0	5.0	6.3
87.5°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	3.7	5.0	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192730

CATALOG NUMBER: LDA6A70940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8
2.5°	2223.1	2177.8	2111.2	2067.2	2024.4	1984.1	1917.5	1879.8	1811.8	1749.0	1694.9
5°	2683.2	2570.1	2433.0	2316.1	2240.6	2166.4	2032.0	1932.6	1808.1	1696.2	1593.1
7.5°	3148.6	2948.5	2723.5	2531.1	2414.2	2299.7	2098.6	1937.7	1761.6	1601.9	1449.8
10°	3571.0	3270.5	2952.3	2677.1	2518.6	2370.2	2104.9	1891.1	1664.7	1467.4	1276.2
12.5°	3963.3	3552.1	3137.2	2777.6	2581.4	2402.8	2078.4	1816.9	1547.8	1314.0	1091.4
15°	4312.9	3784.7	3271.8	2835.4	2605.3	2394.1	2016.9	1712.6	1409.5	1147.9	866.4
17.5°	4578.2	3929.4	3330.9	2826.6	2562.6	2327.5	1911.2	1581.8	1262.4	945.6	627.4
20°	4739.1	3990.9	3318.2	2758.7	2470.7	2221.8	1785.5	1439.7	1085.1	726.7	553.2
22.5°	4807.0	3985.9	3259.1	2656.9	2357.5	2106.2	1664.7	1301.4	899.0	657.6	577.2
25°	4818.3	3934.4	3176.2	2544.9	2245.7	1995.5	1542.8	1144.2	780.8	676.4	646.4
27.5°	4731.6	3813.6	3020.3	2384.0	2088.5	1829.5	1360.5	909.1	733.1	674.0	694.1
30°	4475.1	3538.2	2744.9	2101.2	1815.7	1556.6	971.9	712.9	608.5	612.3	617.3
32.5°	4023.7	3080.5	2302.3	1687.4	1375.6	1026.0	604.8	476.5	462.7	462.7	460.1
35°	3421.3	2521.0	1806.8	1067.5	684.0	492.9	313.0	314.3	308.0	306.9	305.6
37.5°	2799.0	1989.1	1144.2	441.3	296.8	206.2	184.8	187.4	184.8	188.7	186.1
40°	2206.7	1228.5	417.4	140.8	104.4	100.7	103.1	105.7	105.7	108.1	108.1
42.5°	1282.5	407.4	109.4	56.5	56.5	54.1	55.4	57.8	59.1	60.4	59.1
45°	381.1	84.3	35.2	31.5	31.5	30.2	30.2	31.5	32.6	33.9	33.9
47.5°	60.4	23.9	20.1	17.5	17.5	17.5	17.5	17.5	18.8	18.8	20.1
50°	18.8	15.1	12.5	11.4	11.4	10.1	10.1	11.4	11.4	11.4	12.5
52.5°	11.4	8.8	8.8	7.5	8.8	8.8	7.5	8.8	8.8	8.8	10.1
55°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	8.8	8.8	8.8
57.5°	6.3	6.3	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
60°	6.3	6.3	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	8.8
62.5°	6.3	6.3	7.5	7.5	7.5	7.5	7.5	7.5	8.8	8.8	8.8
65°	6.3	6.3	7.5	7.5	7.5	7.5	7.5	8.8	8.8	8.8	8.8
67.5°	6.3	7.5	7.5	7.5	7.5	8.8	8.8	8.8	8.8	8.8	8.8
70°	6.3	7.5	7.5	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8
72.5°	6.3	7.5	7.5	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8
75°	7.5	7.5	7.5	8.8	8.8	8.8	8.8	8.8	8.8	8.8	10.1
77.5°	7.5	7.5	8.8	8.8	8.8	8.8	8.8	8.8	10.1	10.1	10.1
80°	7.5	7.5	8.8	8.8	8.8	8.8	8.8	10.1	10.1	10.1	10.1
82.5°	7.5	7.5	8.8	8.8	8.8	8.8	8.8	10.1	10.1	10.1	10.1
85°	7.5	7.5	8.8	8.8	8.8	8.8	8.8	10.1	10.1	10.1	10.1
87.5°	7.5	7.5	8.8	8.8	8.8	8.8	8.8	10.1	10.1	10.1	10.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192730

CATALOG NUMBER: LDA6A70940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8
2.5°	1648.5	1590.5	1562.9	1524.0	1496.3	1434.7	1409.5	1366.8	1331.6	1273.7	1277.5
5°	1505.1	1395.7	1321.5	1263.7	1223.4	1125.3	1059.9	990.8	927.9	850.0	821.1
7.5°	1306.4	1171.9	1058.8	989.6	938.0	807.3	662.6	549.4	464.0	402.3	378.5
10°	1107.8	932.9	753.2	646.4	572.2	446.3	382.2	352.0	324.4	290.5	267.9
12.5°	876.4	627.4	464.0	421.2	391.0	349.6	308.0	275.4	281.7	282.8	291.8
15°	598.5	451.4	399.9	371.0	338.2	314.3	328.1	336.9	353.3	354.6	366.0
17.5°	486.6	423.8	382.2	381.1	383.5	397.3	418.7	430.1	451.4	456.4	472.8
20°	486.6	450.1	485.3	485.3	491.6	510.5	538.2	554.5	578.3	587.3	607.3
22.5°	554.5	579.6	623.6	628.7	631.3	651.4	686.5	702.9	730.5	735.5	756.9
25°	676.4	699.1	739.4	743.1	744.4	759.5	785.8	794.6	813.6	803.5	816.0
27.5°	715.4	725.5	750.6	753.2	746.9	753.2	763.3	763.3	769.5	749.5	753.2
30°	628.7	631.3	643.8	645.1	631.3	633.7	635.0	633.7	632.4	611.1	611.1
32.5°	466.5	466.5	482.9	479.1	464.0	467.8	467.8	467.8	466.5	448.9	446.3
35°	309.3	310.6	324.4	322.0	310.6	313.0	313.0	316.9	313.0	303.0	300.5
37.5°	188.7	189.8	196.1	197.4	193.7	194.8	196.1	194.8	197.4	192.4	189.8
40°	109.4	111.9	116.9	118.2	116.9	116.9	118.2	119.5	124.5	118.2	115.6
42.5°	64.1	65.4	67.9	67.9	67.9	67.9	69.2	70.5	71.6	70.5	69.2
45°	36.5	37.7	39.0	39.0	40.3	39.0	40.3	40.3	41.6	40.3	40.3
47.5°	21.4	21.4	22.6	22.6	23.9	22.6	23.9	23.9	23.9	22.6	22.6
50°	12.5	13.8	13.8	13.8	13.8	13.8	13.8	13.8	13.8	12.5	12.5
52.5°	10.1	10.1	10.1	10.1	10.1	8.8	8.8	8.8	8.8	7.5	7.5
55°	8.8	8.8	8.8	8.8	8.8	8.8	7.5	6.3	6.3	5.0	5.0
57.5°	7.5	8.8	8.8	8.8	8.8	7.5	7.5	6.3	5.0	3.7	3.7
60°	8.8	8.8	8.8	8.8	7.5	7.5	7.5	6.3	5.0	3.7	3.7
62.5°	8.8	8.8	8.8	8.8	8.8	7.5	7.5	6.3	5.0	3.7	3.7
65°	8.8	8.8	8.8	8.8	8.8	7.5	7.5	6.3	5.0	3.7	3.7
67.5°	8.8	8.8	8.8	8.8	8.8	7.5	7.5	6.3	5.0	5.0	3.7
70°	8.8	10.1	10.1	8.8	8.8	8.8	7.5	6.3	6.3	5.0	3.7
72.5°	8.8	10.1	10.1	8.8	8.8	8.8	7.5	6.3	6.3	5.0	3.7
75°	10.1	10.1	10.1	10.1	8.8	8.8	7.5	7.5	6.3	5.0	3.7
77.5°	10.1	10.1	10.1	10.1	8.8	8.8	7.5	7.5	6.3	5.0	3.7
80°	10.1	10.1	10.1	10.1	10.1	8.8	8.8	7.5	6.3	5.0	5.0
82.5°	10.1	10.1	10.1	10.1	10.1	8.8	8.8	7.5	6.3	5.0	5.0
85°	10.1	10.1	10.1	10.1	10.1	8.8	8.8	7.5	6.3	5.0	3.7
87.5°	10.1	10.1	10.1	10.1	8.8	8.8	7.5	7.5	6.3	5.0	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192730

CATALOG NUMBER: LDA6A70940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8	1786.8
2.5°	1231.0	1202.0	1189.5	1209.6	1199.5	1169.4	1175.7	1156.8
5°	734.4	690.4	662.6	675.3	635.0	598.5	598.5	572.2
7.5°	354.6	340.8	333.2	335.8	327.0	315.6	309.3	309.3
10°	248.9	243.9	245.2	245.2	252.8	251.5	255.2	253.9
12.5°	295.5	297.9	299.2	304.3	310.6	310.6	314.3	311.9
15°	378.5	376.0	383.5	384.8	394.9	396.0	401.0	396.0
17.5°	481.6	486.6	494.1	492.9	513.1	514.2	514.2	513.1
20°	619.9	623.6	631.3	633.7	657.6	660.2	668.9	670.2
22.5°	770.7	770.7	774.5	779.5	802.2	803.5	807.3	807.3
25°	822.4	814.7	816.0	822.4	834.9	829.8	833.6	831.1
27.5°	755.6	744.4	741.8	750.6	759.5	745.6	750.6	750.6
30°	613.6	603.5	601.1	609.8	616.2	601.1	606.1	608.5
32.5°	448.9	442.6	441.3	447.6	452.7	440.0	445.0	448.9
35°	303.0	300.5	297.9	299.2	306.9	296.8	301.8	304.3
37.5°	192.4	187.4	188.7	191.1	196.1	189.8	194.8	194.8
40°	118.2	115.6	115.6	118.2	120.6	115.6	118.2	119.5
42.5°	69.2	69.2	69.2	70.5	71.6	69.2	69.2	70.5
45°	40.3	39.0	39.0	40.3	41.6	39.0	40.3	40.3
47.5°	22.6	21.4	21.4	22.6	22.6	21.4	22.6	22.6
50°	12.5	11.4	11.4	12.5	12.5	11.4	11.4	11.4
52.5°	6.3	6.3	6.3	6.3	6.3	6.3	5.0	5.0
55°	3.7	3.7	2.4	2.4	2.4	2.4	2.4	1.3
57.5°	2.4	2.4	1.3	1.3	1.3	1.3	0.0	0.0
60°	2.4	2.4	1.3	1.3	1.3	0.0	0.0	0.0
62.5°	2.4	2.4	1.3	1.3	1.3	0.0	0.0	0.0
65°	2.4	2.4	1.3	1.3	1.3	0.0	0.0	0.0
67.5°	2.4	2.4	1.3	1.3	1.3	0.0	0.0	0.0
70°	3.7	2.4	2.4	1.3	1.3	1.3	0.0	0.0
72.5°	3.7	2.4	2.4	2.4	1.3	1.3	0.0	0.0
75°	3.7	2.4	2.4	2.4	1.3	1.3	0.0	0.0
77.5°	3.7	2.4	2.4	2.4	1.3	1.3	1.3	0.0
80°	3.7	2.4	2.4	2.4	1.3	1.3	1.3	1.3
82.5°	3.7	2.4	2.4	2.4	1.3	1.3	1.3	1.3
85°	3.7	2.4	2.4	2.4	1.3	1.3	1.3	0.0
87.5°	3.7	2.4	2.4	2.4	1.3	1.3	1.3	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)