

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192197

Luminaire Tested: **LDA6A40930D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192197
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26672)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40930D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4251.2 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 2.54 / 0.51 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192197

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192197

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	85	75	68	62	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	40	39		
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	52315	52315	52315
5°	133777	48228	17598
10°	287514	38910	6474
15°	419412	28462	7406
20°	474927	20465	11428
25°	514850	16459	17723
30°	574462	13515	17060
35°	583081	8733	11370
40°	587372	4194	5746
45°	583704	1752	2403
50°	467345	793	793
55°	139379	564	76
60°	28452	647	0
65°	2711	765	0
70°	256	1074	0
75°	0	1419	0
80°	0	2368	253
85°	0	4717	503

TEST NUMBER: P1192197

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.2	2.9
10°-20°	596.2	14.0
20°-30°	1095.8	25.8
30°-40°	1257.2	29.6
40°-50°	951.2	22.4
50°-60°	210.8	5.0
60°-70°	8.9	0.2
70°-80°	3.9	0.1
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1815.3	42.7
0°-40°	3072.5	72.3
0°-60°	4234.5	99.6
0°-90°	4251.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4251.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	954	954	954	954	954	
5°	2431	1816	876	429	320	321
15°	7390	4008	502	130	130	2059
25°	8512	4713	272	264	293	3971
35°	8713	2909	130	163	170	5457
45°	7529	823	23	29	31	5619
55°	1458	31	6	4	1	1805
65°	21	4	6	3	0	56
75°	0	3	7	4	0	0
85°	0	4	8	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192197

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3
2.5°	1616.5	1600.5	1604.7	1624.8	1542.0	1539.4	1500.9	1495.9	1457.4	1387.1	1351.9
5°	2431.0	2420.9	2403.3	2410.1	2315.5	2251.9	2184.8	2136.3	2037.5	1904.4	1815.7
7.5°	3730.2	3621.4	3568.6	3467.3	3346.8	3223.7	3099.8	2955.8	2748.2	2516.4	2328.8
10°	5165.0	5117.3	5009.3	4944.9	4677.8	4497.0	4304.4	4009.8	3629.7	3209.5	2859.6
12.5°	6571.3	6515.2	6352.0	6214.8	5858.9	5697.3	5447.1	5075.4	4593.3	3994.7	3441.3
15°	7390.0	7402.6	7217.6	7210.8	6904.5	6694.3	6477.6	6038.0	5426.2	4738.9	4008.0
17.5°	7869.7	7900.7	7717.4	7769.2	7463.7	7246.0	7084.5	6763.0	6112.6	5288.0	4446.0
20°	8140.9	8190.3	7995.3	8035.4	7774.2	7626.9	7462.9	7144.8	6570.5	5660.5	4694.5
22.5°	8347.6	8367.0	8150.1	8203.7	7918.3	7770.9	7654.5	7356.5	6789.8	5857.3	4772.3
25°	8511.7	8560.3	8312.5	8316.7	8033.0	7885.5	7756.7	7485.5	6883.6	5909.1	4712.9
27.5°	8747.8	8787.2	8423.0	8391.2	8116.6	7954.3	7814.5	7547.4	6879.4	5793.6	4488.6
30°	9075.1	8855.8	8483.3	8401.2	8092.3	7927.4	7777.6	7431.1	6725.4	5482.2	4080.9
32.5°	8981.4	8803.9	8436.4	8305.9	7999.4	7822.8	7651.2	7229.2	6367.9	5000.1	3525.1
35°	8712.7	8655.7	8269.9	8228.8	7858.0	7672.9	7500.5	6923.7	5819.6	4369.7	2909.0
37.5°	8485.8	8388.7	8140.0	8075.6	7686.4	7482.1	7207.5	6467.5	5094.6	3566.1	2323.0
40°	8207.8	8142.6	7902.3	7833.7	7383.3	7072.0	6736.2	5640.5	4219.0	2775.9	1793.9
42.5°	7912.4	7853.8	7626.9	7482.9	6882.7	6470.9	5949.4	4639.2	3248.0	2091.9	1344.4
45°	7529.0	7446.1	7162.3	6894.4	6033.9	5444.6	4857.7	3540.1	2377.4	1489.2	822.8
47.5°	6870.1	6738.8	6394.7	5856.5	4799.2	4233.3	3622.2	2400.8	1468.3	766.8	414.4
50°	5479.8	5250.4	4792.5	4152.1	3073.9	2531.5	2052.6	1220.5	630.4	395.1	243.6
52.5°	3376.9	3166.8	2776.7	2158.9	1417.2	1091.6	859.7	568.4	347.4	223.5	90.4
55°	1458.3	1326.8	1140.2	869.7	617.8	508.2	408.5	283.8	179.1	68.6	31.0
57.5°	550.9	511.5	463.7	380.9	284.6	237.7	200.1	125.6	43.5	25.9	17.6
60°	259.5	235.3	207.6	164.9	108.8	78.7	49.4	31.8	20.9	14.2	10.1
62.5°	71.2	53.6	44.3	36.0	27.7	24.3	20.9	15.9	11.7	7.5	5.9
65°	20.9	18.4	17.6	15.0	12.5	10.9	9.3	7.5	5.9	4.2	4.2
67.5°	7.5	7.5	6.7	5.9	5.0	4.2	4.2	3.4	3.4	3.4	3.4
70°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	2.5	2.5	3.4	3.4
72.5°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	2.5	3.4	3.4
75°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	2.5	3.4	3.4
77.5°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	4.2
80°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	4.2
82.5°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	4.2
85°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	4.2
87.5°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192197

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3
2.5°	1322.7	1274.1	1205.4	1170.3	1139.3	1130.9	1067.4	1026.3	977.8	927.6	874.8
5°	1732.8	1609.0	1477.5	1367.0	1310.9	1278.2	1154.4	1061.5	971.9	876.4	795.3
7.5°	2139.7	1917.9	1726.1	1547.9	1449.9	1376.2	1198.7	1058.9	923.3	799.5	689.7
10°	2533.1	2213.3	1907.8	1666.7	1531.9	1422.3	1192.9	1011.2	841.3	699.0	584.3
12.5°	2931.5	2465.3	2059.3	1730.3	1569.6	1428.9	1152.7	931.7	751.8	601.1	482.1
15°	3287.3	2661.2	2153.8	1745.4	1551.1	1385.4	1074.0	830.5	651.3	501.5	397.6
17.5°	3534.3	2766.6	2159.7	1690.1	1474.2	1295.8	964.4	724.1	549.9	417.7	326.5
20°	3646.5	2763.3	2080.2	1575.4	1349.4	1163.5	834.6	615.3	458.7	350.8	272.9
22.5°	3612.9	2657.8	1939.6	1413.0	1197.1	1011.2	714.0	519.0	394.3	301.4	239.4
25°	3445.6	2473.7	1774.7	1250.7	1033.0	859.7	605.3	443.7	342.3	272.1	217.7
27.5°	3171.8	2222.6	1552.8	1060.7	861.4	726.7	509.8	383.4	301.4	240.3	226.8
30°	2771.7	1917.9	1292.5	855.6	695.6	575.1	413.5	308.9	241.1	213.5	214.3
32.5°	2330.5	1582.1	1016.2	653.8	524.0	443.7	305.5	216.0	176.6	175.0	175.8
35°	1891.0	1232.3	755.9	478.0	384.2	319.8	196.7	135.6	131.5	130.5	132.3
37.5°	1500.9	916.7	545.0	334.0	254.5	195.0	106.3	92.1	88.8	90.4	91.2
40°	1120.8	642.9	368.4	197.6	123.9	89.6	64.5	59.5	57.8	58.6	58.6
42.5°	771.0	401.8	219.3	82.0	59.5	49.4	41.0	38.5	36.8	36.0	36.8
45°	415.2	250.3	85.4	41.9	35.2	31.8	25.9	24.3	23.5	22.6	22.6
47.5°	265.4	92.9	38.5	25.9	22.6	20.9	17.6	15.9	15.0	14.2	14.2
50°	99.6	36.0	23.5	16.8	14.2	13.4	10.9	10.1	9.3	9.3	9.3
52.5°	34.4	21.8	15.0	10.9	9.3	8.3	7.5	6.7	6.7	6.7	6.7
55°	19.2	13.4	9.3	6.7	6.7	5.9	5.9	5.9	5.9	5.9	5.9
57.5°	11.7	7.5	5.9	5.0	5.0	5.0	5.0	5.9	5.9	5.9	5.9
60°	6.7	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.9	5.9	5.9
62.5°	4.2	4.2	4.2	4.2	4.2	5.0	5.0	5.9	5.9	5.9	5.9
65°	4.2	4.2	4.2	4.2	4.2	5.0	5.0	5.9	5.9	5.9	5.9
67.5°	3.4	4.2	4.2	5.0	5.0	5.0	5.0	5.9	5.9	6.7	5.9
70°	4.2	4.2	4.2	5.0	5.0	5.0	5.9	5.9	6.7	6.7	6.7
72.5°	4.2	4.2	4.2	5.0	5.0	5.0	5.9	5.9	6.7	6.7	6.7
75°	4.2	4.2	5.0	5.0	5.0	5.9	5.9	6.7	6.7	6.7	6.7
77.5°	4.2	4.2	5.0	5.0	5.0	5.9	5.9	6.7	6.7	7.5	6.7
80°	4.2	4.2	5.0	5.9	5.9	5.9	5.9	6.7	6.7	7.5	7.5
82.5°	4.2	5.0	5.0	5.9	5.9	5.9	6.7	6.7	7.5	7.5	7.5
85°	4.2	5.0	5.0	5.9	5.9	5.9	6.7	6.7	7.5	7.5	7.5
87.5°	4.2	5.0	5.0	5.9	5.9	5.9	6.7	6.7	7.5	7.5	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192197

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3
2.5°	846.3	797.7	758.4	759.3	726.7	701.5	669.7	652.1	637.9	614.4	592.7
5°	735.8	661.3	605.3	594.4	556.7	518.1	478.9	449.5	428.7	406.0	385.0
7.5°	616.1	530.7	466.3	451.2	419.4	383.4	347.4	318.1	293.0	268.7	243.6
10°	499.7	421.9	363.3	348.2	316.4	278.8	244.4	218.5	199.3	180.0	160.7
12.5°	404.4	335.7	280.4	261.2	235.3	205.9	178.3	153.2	132.3	123.9	121.4
15°	327.3	262.0	218.5	202.5	180.8	150.7	134.8	130.5	129.7	129.7	129.7
17.5°	264.6	213.5	174.2	157.4	146.5	144.8	144.8	144.8	145.7	147.3	150.7
20°	221.8	176.6	161.6	163.3	163.3	164.9	168.3	170.8	174.2	178.3	183.3
22.5°	196.7	187.5	185.9	190.8	191.7	196.7	203.4	208.4	214.3	221.0	225.2
25°	215.1	218.5	221.0	228.6	231.0	239.4	249.5	257.0	263.7	271.3	276.2
27.5°	234.4	240.3	245.2	252.8	254.5	265.4	273.7	278.8	283.8	287.1	290.5
30°	221.0	226.8	231.9	238.6	238.6	250.3	254.5	258.7	262.8	264.6	267.9
32.5°	181.7	187.5	192.6	197.6	198.4	206.8	211.8	213.5	216.8	217.7	220.1
35°	136.4	139.0	144.0	148.1	149.1	154.8	159.0	160.7	163.3	163.3	164.9
37.5°	93.7	95.5	99.6	102.1	103.8	108.0	110.5	112.1	113.9	114.7	115.5
40°	61.1	61.9	64.5	67.0	68.6	71.2	72.8	74.5	75.3	77.0	77.0
42.5°	37.6	38.5	40.2	41.9	41.9	44.3	45.2	46.9	47.7	48.6	48.6
45°	23.5	24.3	24.3	25.1	25.9	26.7	28.5	28.5	29.3	29.3	29.3
47.5°	14.2	15.0	14.2	15.0	15.0	15.9	16.8	16.8	16.8	16.8	16.8
50°	9.3	9.3	9.3	9.3	9.3	9.3	10.1	10.1	10.1	10.1	9.3
52.5°	6.7	6.7	5.9	6.7	5.9	5.9	5.9	5.9	5.9	5.9	5.0
55°	5.9	5.9	5.9	5.9	5.0	5.0	5.0	4.2	4.2	3.4	3.4
57.5°	5.9	5.9	5.0	5.0	5.0	4.2	4.2	4.2	3.4	3.4	2.5
60°	5.9	5.9	5.0	5.0	5.0	4.2	4.2	3.4	3.4	2.5	2.5
62.5°	5.9	5.9	5.0	5.0	5.0	5.0	4.2	4.2	3.4	3.4	2.5
65°	5.9	5.9	5.9	5.0	5.0	5.0	4.2	4.2	3.4	3.4	2.5
67.5°	5.9	5.9	5.9	5.9	5.0	5.0	5.0	4.2	3.4	3.4	2.5
70°	5.9	5.9	5.9	5.9	5.9	5.0	5.0	4.2	4.2	3.4	2.5
72.5°	6.7	6.7	5.9	5.9	5.9	5.0	5.0	4.2	4.2	3.4	3.4
75°	6.7	6.7	5.9	5.9	5.9	5.0	5.0	4.2	4.2	3.4	3.4
77.5°	6.7	6.7	6.7	6.7	5.9	5.9	5.0	5.0	4.2	4.2	3.4
80°	6.7	6.7	6.7	6.7	5.9	5.9	5.9	5.0	4.2	4.2	3.4
82.5°	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.0	4.2	4.2	3.4
85°	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.0	4.2	4.2	3.4
87.5°	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.0	4.2	4.2	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192197

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3
2.5°	572.6	561.7	560.8	551.7	533.3	542.4	530.7	522.4
5°	366.6	354.9	343.2	344.9	331.5	334.0	324.8	319.8
7.5°	232.7	220.1	216.8	216.8	201.7	201.7	195.9	192.6
10°	146.5	136.4	133.1	127.2	120.6	119.7	117.2	116.3
12.5°	118.9	118.9	116.3	117.2	117.2	117.2	116.3	116.3
15°	129.7	130.5	128.1	128.9	130.5	129.7	130.5	130.5
17.5°	149.9	154.0	150.7	152.3	155.7	154.8	155.7	156.6
20°	183.3	190.0	185.9	189.2	193.4	192.6	195.0	195.9
22.5°	228.6	236.9	232.7	236.1	242.8	241.1	244.4	246.1
25°	278.8	287.1	282.1	286.3	290.5	292.1	292.1	293.0
27.5°	290.5	295.5	292.1	296.4	298.0	299.7	298.0	298.8
30°	266.2	270.3	267.0	271.3	271.3	272.9	271.3	269.5
32.5°	219.3	222.7	218.5	223.5	222.7	223.5	224.4	225.2
35°	165.7	167.5	164.9	165.7	166.5	167.5	169.9	169.9
37.5°	115.5	118.0	115.5	116.3	116.3	118.0	119.7	119.7
40°	77.0	79.5	77.0	78.7	77.9	78.7	80.3	80.3
42.5°	48.6	50.2	48.6	49.4	49.4	49.4	50.2	51.0
45°	29.3	30.1	29.3	30.1	30.1	30.1	31.0	31.0
47.5°	16.8	17.6	16.8	16.8	17.6	16.8	17.6	17.6
50°	9.3	9.3	9.3	9.3	9.3	8.3	8.3	9.3
52.5°	5.0	5.0	4.2	4.2	4.2	4.2	4.2	4.2
55°	2.5	2.5	1.6	1.6	1.6	0.8	1.6	0.8
57.5°	1.6	1.6	0.8	0.8	0.8	0.8	0.0	0.0
60°	1.6	1.6	0.8	0.8	0.8	0.0	0.0	0.0
62.5°	1.6	1.6	0.8	0.8	0.8	0.0	0.0	0.0
65°	1.6	1.6	0.8	0.8	0.8	0.0	0.0	0.0
67.5°	2.5	1.6	0.8	0.8	0.8	0.0	0.0	0.0
70°	2.5	1.6	1.6	0.8	0.8	0.0	0.0	0.0
72.5°	2.5	1.6	1.6	1.6	0.8	0.8	0.0	0.0
75°	2.5	1.6	1.6	1.6	0.8	0.8	0.0	0.0
77.5°	2.5	2.5	1.6	1.6	0.8	0.8	0.8	0.0
80°	2.5	2.5	1.6	1.6	1.6	0.8	0.8	0.8
82.5°	2.5	2.5	1.6	1.6	1.6	0.8	0.8	0.8
85°	2.5	2.5	1.6	1.6	1.6	0.8	0.8	0.8
87.5°	2.5	2.5	1.6	1.6	1.6	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)