

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192735

Luminaire Tested: **LDA6A70940D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70940D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6915.0 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192735

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192735

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	68377	68377	68377
5°	175401	62205	19370
10°	341916	47806	9307
15°	613772	32475	12486
20°	911263	24648	20611
25°	1035792	20312	32318
30°	1122812	22212	30403
35°	1182691	14388	18852
40°	1208264	6391	9181
45°	1091307	2442	3411
50°	718373	972	972
55°	196724	841	0
60°	39284	965	0
65°	2776	1310	0
70°	385	1619	0
75°	0	2415	0
80°	0	3599	410
85°	0	7170	818

TEST NUMBER: P1192735

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.8	2.2
10°-20°	811.7	11.7
20°-30°	1839.8	26.6
30°-40°	2208.4	31.9
40°-50°	1556.4	22.5
50°-60°	321.1	4.6
60°-70°	11.4	0.2
70°-80°	6.8	0.1
80°-90°	6.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2804.3	40.6
0°-40°	5012.7	72.5
0°-60°	6890.2	99.6
0°-90°	6915.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6915.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1247	1247	1247	1247	1247	
5°	3187	2322	1130	470	352	392
15°	10815	4758	572	204	220	3209
25°	17124	5755	336	470	534	7903
35°	17672	4030	215	282	282	10986
45°	14076	1382	32	43	44	10353
55°	2058	28	9	6	0	2712
65°	21	6	10	6	0	63
75°	0	6	11	8	0	0
85°	0	8	11	8	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192735

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3
2.5°	2126.2	2062.0	2087.2	2013.0	1996.8	1982.8	1996.8	1916.2	1870.9	1813.1	1766.7
5°	3187.4	3110.7	3128.3	2998.9	2939.8	2899.5	2891.9	2725.9	2601.6	2464.4	2322.3
7.5°	4437.3	4364.4	4354.3	4153.1	4031.2	3962.0	3933.1	3695.4	3480.4	3236.4	2970.0
10°	6142.3	5976.3	5924.7	5633.1	5400.4	5253.3	5072.3	4692.5	4315.3	3946.9	3607.4
12.5°	8126.4	8035.9	7907.6	7393.3	6985.9	6777.3	6506.9	5913.5	5342.6	4734.1	4165.6
15°	10814.6	10492.8	10274.0	9530.8	8874.5	8552.7	8157.8	7250.1	6387.4	5616.7	4757.9
17.5°	13441.4	13272.8	12930.9	11966.4	10955.5	10447.5	9859.1	8625.6	7407.2	6310.8	5262.1
20°	15620.3	15462.0	15072.1	14163.1	13041.5	12292.1	11551.4	9859.1	8267.3	6864.0	5599.1
22.5°	16664.0	16563.3	16245.2	15467.0	14511.3	13798.4	13002.5	10909.0	8903.4	7226.2	5752.4
25°	17124.1	17077.7	16872.6	16259.0	15358.9	14754.1	14002.2	11652.1	9299.6	7394.6	5755.0
27.5°	17590.6	17599.5	17146.8	16661.4	15807.7	15226.7	14502.6	11981.5	9371.2	7300.2	5566.4
30°	17737.7	17644.7	17444.8	16748.2	15937.2	15319.8	14542.8	11829.4	9077.0	6913.0	5190.5
32.5°	17677.4	17640.9	17420.9	16684.1	15717.2	15036.9	14154.3	11225.9	8496.1	6359.8	4657.3
35°	17672.4	17604.5	17100.2	16467.8	15277.1	14437.1	13274.1	10250.1	7673.7	5630.5	4029.9
37.5°	17353.0	17184.5	16806.0	15953.6	14384.4	13319.4	12015.5	9058.2	6667.8	4812.0	3407.5
40°	16884.0	16657.6	16159.8	14869.7	12837.8	11610.5	10338.1	7703.9	5602.9	4004.7	2746.1
42.5°	15904.4	15562.5	14858.3	13084.2	10777.0	9670.4	8611.8	6332.1	4569.3	3262.9	2096.0
45°	14076.4	13608.6	12656.7	10709.1	8706.0	7803.2	6952.0	5094.8	3657.7	2420.4	1381.9
47.5°	11313.9	10880.1	10013.7	8525.0	6827.6	6064.3	5385.3	3789.7	2479.5	1402.0	660.2
50°	8423.2	8051.0	7374.4	5924.7	4583.1	3983.3	3402.5	2152.6	1161.9	666.4	274.1
52.5°	5025.7	4840.9	4241.1	3285.5	2263.2	1950.2	1565.4	911.5	586.0	241.4	74.2
55°	2058.3	1899.8	1674.8	1344.1	984.6	834.9	714.2	450.1	182.3	50.3	27.6
57.5°	930.5	895.3	793.5	623.6	452.7	379.8	256.5	85.6	40.3	25.2	16.4
60°	358.3	323.1	276.7	149.7	64.1	54.1	44.0	28.9	20.1	13.8	10.1
62.5°	51.6	49.0	44.0	35.2	27.6	25.2	21.4	15.1	11.4	8.8	7.5
65°	21.4	21.4	18.8	15.1	12.5	11.4	10.1	7.5	6.3	6.3	6.3
67.5°	8.8	8.8	7.5	6.3	5.0	5.0	5.0	3.7	5.0	5.0	6.3
70°	2.4	2.4	2.4	2.4	2.4	2.4	3.7	3.7	5.0	5.0	6.3
72.5°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	5.0	6.3	6.3
75°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	5.0	6.3	6.3
77.5°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	5.0	6.3	6.3
80°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	5.0	6.3	7.5
82.5°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	5.0	6.3	7.5
85°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	5.0	6.3	7.5
87.5°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	5.0	6.3	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192735

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3
2.5°	1726.4	1645.9	1623.3	1552.9	1493.8	1464.9	1428.3	1346.7	1285.0	1203.3	1154.3
5°	2223.1	2071.0	1950.2	1803.1	1706.3	1643.4	1545.4	1395.7	1275.0	1130.4	1027.3
7.5°	2759.9	2482.1	2264.5	2021.9	1882.3	1772.9	1605.6	1390.7	1213.4	1021.0	861.3
10°	3278.0	2863.0	2521.0	2172.8	1989.1	1837.0	1606.9	1336.6	1101.5	858.8	690.4
12.5°	3734.4	3198.7	2717.2	2269.5	2041.9	1852.1	1564.2	1239.8	955.7	706.6	558.2
15°	4115.4	3459.0	2855.5	2306.1	2045.8	1819.5	1474.9	1101.5	793.5	572.2	467.8
17.5°	4404.6	3596.1	2898.2	2262.1	1972.9	1726.4	1337.9	926.6	643.8	485.3	393.6
20°	4554.2	3622.5	2836.7	2142.6	1838.3	1585.5	1158.0	751.9	545.7	422.5	329.4
22.5°	4573.0	3548.3	2689.6	1971.6	1668.5	1414.5	959.4	627.4	486.6	373.4	290.5
25°	4461.1	3387.4	2479.5	1777.9	1482.4	1218.4	780.8	562.1	442.6	335.8	334.5
27.5°	4222.3	3110.7	2228.1	1552.9	1257.4	990.8	662.6	508.0	394.9	355.9	378.5
30°	3885.2	2756.1	1918.8	1268.7	982.0	762.0	558.2	418.7	347.0	350.9	369.7
32.5°	3428.8	2316.1	1555.3	929.2	702.9	573.3	418.7	285.4	287.9	289.2	305.6
35°	2855.5	1857.1	1161.9	624.9	494.1	403.6	236.4	209.9	213.8	215.0	226.3
37.5°	2288.4	1427.2	772.0	416.1	310.6	212.5	147.1	140.8	143.4	142.1	154.7
40°	1752.7	994.6	462.7	206.2	119.5	99.4	90.6	86.7	88.0	89.3	96.8
42.5°	1241.0	539.4	228.8	77.9	62.8	57.8	54.1	51.6	52.8	52.8	57.8
45°	630.0	255.2	77.9	42.7	39.0	35.2	32.6	31.5	31.5	31.5	33.9
47.5°	272.8	84.3	36.5	26.5	23.9	22.6	20.1	18.8	18.8	18.8	20.1
50°	85.6	33.9	22.6	17.5	15.1	13.8	12.5	12.5	12.5	11.4	12.5
52.5°	31.5	21.4	15.1	11.4	10.1	10.1	10.1	8.8	10.1	8.8	10.1
55°	18.8	13.8	10.1	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8
57.5°	12.5	10.1	8.8	8.8	7.5	7.5	8.8	8.8	8.8	8.8	8.8
60°	8.8	8.8	7.5	7.5	7.5	7.5	8.8	8.8	8.8	8.8	8.8
62.5°	7.5	7.5	7.5	7.5	7.5	7.5	8.8	8.8	8.8	8.8	10.1
65°	6.3	7.5	7.5	7.5	7.5	7.5	8.8	8.8	10.1	10.1	10.1
67.5°	6.3	7.5	7.5	8.8	8.8	8.8	8.8	10.1	10.1	10.1	10.1
70°	7.5	7.5	8.8	8.8	8.8	8.8	10.1	10.1	10.1	10.1	11.4
72.5°	7.5	7.5	8.8	8.8	8.8	8.8	10.1	10.1	11.4	11.4	11.4
75°	7.5	8.8	8.8	8.8	8.8	10.1	10.1	10.1	11.4	11.4	11.4
77.5°	7.5	8.8	8.8	10.1	10.1	10.1	10.1	11.4	11.4	11.4	11.4
80°	7.5	8.8	8.8	10.1	10.1	10.1	11.4	11.4	11.4	11.4	12.5
82.5°	7.5	8.8	8.8	10.1	10.1	10.1	11.4	11.4	11.4	11.4	12.5
85°	8.8	8.8	10.1	10.1	10.1	10.1	11.4	11.4	11.4	11.4	12.5
87.5°	8.8	8.8	10.1	10.1	10.1	10.1	11.4	11.4	12.5	11.4	12.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192735

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3
2.5°	1088.8	1015.9	965.6	946.8	910.4	852.6	818.5	787.1	728.0	715.4	682.7
5°	909.1	792.2	709.2	677.7	636.3	587.3	539.4	508.0	470.2	455.1	432.5
7.5°	716.7	599.8	528.2	503.0	474.1	433.8	391.0	359.6	320.7	300.5	281.7
10°	563.2	476.5	416.1	391.0	360.9	318.1	274.1	232.7	198.7	177.3	173.6
12.5°	457.7	385.9	321.8	295.5	260.3	217.6	186.1	184.8	182.3	181.0	183.6
15°	374.7	305.6	237.7	208.8	198.7	197.4	201.2	204.9	203.8	207.5	209.9
17.5°	308.0	233.8	218.7	220.0	221.3	225.0	231.4	241.4	242.7	248.9	253.9
20°	251.5	247.8	253.9	259.0	262.9	270.3	284.1	296.8	300.5	309.3	319.4
22.5°	285.4	296.8	310.6	316.9	321.8	335.8	350.9	371.0	378.5	389.8	403.6
25°	344.5	363.4	384.8	392.3	399.9	422.5	440.0	464.0	470.2	484.0	498.0
27.5°	393.6	413.7	436.3	446.3	452.7	475.2	490.3	505.4	505.4	513.1	523.1
30°	385.9	402.3	421.2	428.8	431.2	447.6	462.7	467.8	465.2	469.1	476.5
32.5°	320.7	333.2	348.3	354.6	357.0	368.4	380.9	380.9	379.8	379.8	384.8
35°	237.7	246.5	253.9	260.3	264.0	271.6	282.8	281.7	281.7	279.1	282.8
37.5°	159.8	164.6	173.6	176.0	177.3	182.3	191.1	191.1	188.7	189.8	192.4
40°	96.8	103.1	108.1	109.4	111.9	115.6	121.9	121.9	121.9	121.9	123.2
42.5°	57.8	61.5	65.4	65.4	66.6	71.6	74.2	74.2	74.2	74.2	75.5
45°	33.9	35.2	37.7	39.0	39.0	41.6	42.7	42.7	42.7	42.7	44.0
47.5°	20.1	21.4	21.4	22.6	22.6	23.9	25.2	25.2	23.9	23.9	23.9
50°	12.5	12.5	12.5	12.5	13.8	13.8	13.8	13.8	13.8	13.8	12.5
52.5°	10.1	10.1	10.1	10.1	8.8	8.8	8.8	8.8	7.5	7.5	6.3
55°	8.8	8.8	8.8	8.8	8.8	7.5	7.5	7.5	6.3	5.0	3.7
57.5°	8.8	8.8	8.8	8.8	8.8	7.5	7.5	6.3	5.0	5.0	3.7
60°	8.8	8.8	8.8	8.8	8.8	7.5	7.5	6.3	5.0	5.0	3.7
62.5°	10.1	10.1	8.8	8.8	8.8	7.5	7.5	6.3	6.3	5.0	3.7
65°	10.1	10.1	8.8	8.8	8.8	8.8	7.5	7.5	6.3	5.0	3.7
67.5°	10.1	10.1	10.1	10.1	8.8	8.8	8.8	7.5	6.3	5.0	3.7
70°	11.4	11.4	10.1	10.1	10.1	8.8	8.8	7.5	6.3	6.3	5.0
72.5°	11.4	11.4	10.1	10.1	10.1	10.1	8.8	7.5	7.5	6.3	5.0
75°	11.4	11.4	11.4	11.4	10.1	10.1	8.8	8.8	7.5	6.3	5.0
77.5°	11.4	11.4	11.4	11.4	10.1	10.1	10.1	8.8	7.5	6.3	5.0
80°	11.4	11.4	11.4	11.4	11.4	10.1	10.1	8.8	7.5	6.3	5.0
82.5°	12.5	12.5	11.4	11.4	11.4	10.1	10.1	8.8	7.5	6.3	6.3
85°	12.5	12.5	11.4	11.4	11.4	10.1	10.1	8.8	7.5	7.5	6.3
87.5°	12.5	12.5	11.4	11.4	11.4	10.1	10.1	8.8	7.5	7.5	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192735

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3	1247.3
2.5°	662.6	624.9	612.3	621.2	611.1	603.5	593.4	588.4
5°	415.0	387.2	378.5	380.9	372.1	364.7	354.6	352.0
7.5°	255.2	228.8	218.7	218.7	208.8	199.9	193.7	189.8
10°	171.0	165.9	167.2	168.5	167.2	168.5	164.6	167.2
12.5°	183.6	181.0	183.6	184.8	184.8	187.4	182.3	186.1
15°	213.8	211.2	215.0	217.6	217.6	221.3	216.3	220.0
17.5°	261.6	260.3	266.6	269.0	270.3	276.7	270.3	275.4
20°	330.7	329.4	338.2	341.9	340.8	353.3	344.5	353.3
22.5°	420.0	417.4	430.0	433.8	435.0	451.4	443.9	450.1
25°	509.2	511.8	518.1	524.3	525.6	539.4	528.2	534.3
27.5°	528.2	524.3	528.2	535.6	536.9	543.1	533.2	538.1
30°	477.8	471.5	472.8	481.6	484.0	486.6	477.8	480.3
32.5°	388.5	378.5	378.5	387.2	389.8	393.6	378.5	384.8
35°	286.7	277.8	277.8	284.1	285.4	287.9	276.7	281.7
37.5°	196.1	188.7	191.1	193.7	194.8	197.4	196.1	194.8
40°	125.7	120.6	124.5	124.5	125.7	127.0	127.0	128.3
42.5°	76.6	72.9	75.5	75.5	76.6	76.6	76.6	77.9
45°	44.0	42.7	42.7	44.0	44.0	44.0	42.7	44.0
47.5°	23.9	22.6	23.9	23.9	23.9	23.9	23.9	23.9
50°	12.5	11.4	11.4	11.4	11.4	11.4	11.4	11.4
52.5°	6.3	5.0	5.0	5.0	3.7	5.0	3.7	3.7
55°	3.7	2.4	2.4	2.4	1.3	1.3	0.0	0.0
57.5°	2.4	1.3	1.3	1.3	0.0	0.0	0.0	0.0
60°	2.4	1.3	1.3	1.3	0.0	0.0	0.0	0.0
62.5°	2.4	1.3	1.3	1.3	0.0	0.0	0.0	0.0
65°	2.4	1.3	1.3	1.3	0.0	0.0	0.0	0.0
67.5°	3.7	2.4	1.3	1.3	1.3	0.0	0.0	0.0
70°	3.7	2.4	2.4	1.3	1.3	0.0	0.0	0.0
72.5°	3.7	2.4	2.4	2.4	1.3	1.3	0.0	0.0
75°	3.7	2.4	2.4	2.4	1.3	1.3	0.0	0.0
77.5°	3.7	3.7	2.4	2.4	1.3	1.3	1.3	0.0
80°	5.0	3.7	2.4	2.4	2.4	1.3	1.3	1.3
82.5°	5.0	3.7	2.4	2.4	2.4	1.3	1.3	1.3
85°	5.0	3.7	3.7	2.4	2.4	1.3	1.3	1.3
87.5°	5.0	3.7	3.7	2.4	2.4	1.3	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)