

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192205

Luminaire Tested: **LDA6A40935D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192205
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26673)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40935D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3586.9 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.56 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192205

CATALOG NUMBER: LDA6A40935D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192205

CATALOG NUMBER: LDA6A40935D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82		
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	55	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	55664	55664	55664
5°	111473	52949	14198
10°	186943	45273	3880
15°	285478	33939	5641
20°	409028	24817	66407
25°	608098	41180	34060
30°	710755	18205	5292
35°	714678	3795	2804
40°	591752	2118	1617
45°	442953	1349	1287
50°	310429	964	742
55°	49900	745	583
60°	3059	767	471
65°	908	1012	454
70°	561	1122	689
75°	360	1292	911
80°	253	1926	1357
85°	503	3837	1635



TEST NUMBER: P1192205

CATALOG NUMBER: LDA6A40935D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.2	2.9
10°-20°	444.3	12.4
20°-30°	1068.9	29.8
30°-40°	1138.9	31.8
40°-50°	710.2	19.8
50°-60°	103.8	2.9
60°-70°	6.6	0.2
70°-80°	5.1	0.1
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1618.4	45.1
0°-40°	2757.3	76.9
0°-60°	3571.3	99.6
0°-90°	3586.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3586.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1015	1015	1015	1015	1015	
5°	2026	1625	962	479	258	234
15°	5030	2795	598	92	99	1492
25°	10053	3324	681	705	563	4530
35°	10679	2467	57	52	42	6443
45°	5714	722	17	20	17	4497
55°	522	12	8	9	6	923
65°	7	5	8	7	4	10
75°	2	4	6	6	4	2
85°	1	4	6	5	3	1
90°	0	0	0	0	0	

TEST NUMBER: P1192205

CATALOG NUMBER: LDA6A40935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4
2.5°	1510.5	1459.1	1476.6	1438.2	1424.2	1427.7	1399.8	1377.2	1365.0	1335.3	1304.8
5°	2025.7	1966.4	1983.8	1926.3	1890.5	1882.7	1839.1	1790.3	1746.7	1680.4	1624.7
7.5°	2650.6	2577.4	2589.6	2503.3	2431.0	2406.6	2340.3	2245.3	2157.2	2044.8	1937.6
10°	3358.3	3289.5	3286.0	3154.4	3030.6	2982.7	2886.0	2729.1	2579.1	2410.0	2234.0
12.5°	4192.5	4088.8	4071.3	3902.3	3717.4	3639.1	3503.9	3264.2	3027.1	2780.5	2526.8
15°	5030.1	4918.5	4890.6	4678.0	4420.0	4314.5	4134.1	3815.1	3488.3	3139.5	2795.3
17.5°	5922.6	5743.9	5593.2	5347.4	5049.3	4941.3	4707.6	4298.8	3887.4	3456.9	2996.6
20°	7011.3	6811.7	6599.9	6179.8	5633.3	5420.6	5164.4	4703.2	4189.9	3692.1	3145.7
22.5°	8503.6	8175.8	7726.0	7050.6	6299.2	5995.9	5600.1	5003.1	4422.6	3863.9	3245.1
25°	10053.3	9600.9	9106.7	8068.5	6908.5	6538.1	6017.7	5232.4	4607.3	3990.2	3324.4
27.5°	10945.9	10582.3	10021.9	8934.1	7402.7	6916.3	6316.6	5404.9	4725.0	4051.2	3347.0
30°	11228.2	10933.6	10424.6	9308.9	7568.3	6988.6	6344.5	5406.6	4668.4	3945.0	3216.3
32.5°	11110.6	10830.8	10267.7	9074.5	7264.9	6731.6	6106.5	5187.0	4389.5	3618.1	2880.7
35°	10679.1	10309.5	9625.3	8296.1	6749.0	6219.0	5635.0	4794.0	3960.6	3174.4	2466.7
37.5°	9710.7	9327.2	8548.8	7298.1	6083.9	5622.9	5153.1	4353.8	3529.2	2770.8	2105.8
40°	8269.0	7863.7	7224.0	6346.2	5366.6	5051.9	4655.3	3866.5	3072.5	2375.1	1772.0
42.5°	6814.4	6554.6	6175.5	5479.9	4797.4	4487.1	4101.9	3335.7	2633.2	1967.2	1345.8
45°	5713.5	5507.8	5255.8	4816.6	4172.4	3880.5	3522.2	2801.4	2052.6	1314.4	721.7
47.5°	4978.7	4727.7	4508.0	4018.1	3327.0	2972.3	2592.2	1846.1	1183.7	570.0	199.6
50°	3639.9	3337.4	3132.6	2583.5	1955.9	1660.4	1382.4	856.8	383.5	127.2	33.1
52.5°	1845.2	1616.9	1496.5	1130.5	747.0	558.7	410.5	176.9	75.8	25.3	19.1
55°	522.1	420.1	376.5	248.4	135.1	95.0	61.9	31.4	22.6	17.4	12.2
57.5°	54.0	46.2	43.6	35.7	28.8	27.1	24.4	19.1	14.8	12.2	7.8
60°	27.9	25.3	24.4	21.8	18.3	16.6	15.7	13.1	9.6	7.0	6.1
62.5°	14.8	14.0	12.2	11.3	9.6	9.6	8.7	7.0	6.1	6.1	5.2
65°	7.0	7.0	7.0	7.0	6.1	6.1	5.2	5.2	5.2	5.2	5.2
67.5°	5.2	5.2	5.2	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
70°	3.5	3.5	3.5	3.5	2.6	2.6	2.6	2.6	2.6	3.5	3.5
72.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.6	2.6	3.5	3.5
75°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.6	2.6	3.5	3.5
77.5°	0.8	0.8	1.7	1.7	1.7	1.7	1.7	2.6	2.6	3.5	3.5
80°	0.8	0.8	0.8	0.8	1.7	1.7	1.7	2.6	2.6	3.5	3.5
82.5°	0.8	0.8	0.8	0.8	1.7	1.7	1.7	2.6	2.6	3.5	3.5
85°	0.8	0.8	0.8	0.8	1.7	1.7	1.7	1.7	2.6	3.5	3.5
87.5°	0.0	0.0	0.8	0.8	0.8	1.7	1.7	1.7	2.6	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192205

CATALOG NUMBER: LDA6A40935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4
2.5°	1268.3	1246.5	1211.6	1176.7	1166.2	1137.5	1103.5	1063.3	1025.9	996.3	967.5
5°	1534.9	1476.6	1411.1	1323.1	1291.7	1243.0	1169.7	1091.2	1023.3	962.2	905.6
7.5°	1800.8	1690.9	1571.5	1444.3	1390.3	1317.8	1202.8	1092.1	991.0	901.2	816.7
10°	2036.1	1867.1	1698.8	1523.6	1447.8	1354.5	1201.1	1059.8	930.9	813.3	706.9
12.5°	2253.1	2019.5	1796.4	1571.5	1476.6	1364.1	1175.0	1004.1	850.7	713.0	588.3
15°	2443.1	2142.4	1866.1	1594.1	1473.9	1344.9	1123.5	927.4	756.6	598.0	462.8
17.5°	2575.6	2212.2	1886.2	1570.7	1438.2	1290.0	1045.0	835.9	648.5	482.0	327.7
20°	2654.9	2230.5	1867.1	1519.3	1372.8	1219.4	971.9	760.1	577.9	425.4	296.4
22.5°	2698.5	2239.2	1853.1	1500.9	1351.9	1205.4	975.4	773.2	617.1	514.2	503.8
25°	2742.1	2267.1	1877.4	1521.8	1382.4	1246.5	1026.7	820.2	713.9	680.8	692.1
27.5°	2739.5	2249.6	1854.8	1502.7	1368.5	1227.2	982.3	765.2	692.1	640.7	598.0
30°	2584.3	2084.0	1680.4	1306.5	1153.1	964.9	654.5	449.7	344.3	287.6	258.9
32.5°	2225.2	1699.7	1283.9	908.2	758.3	548.3	281.5	148.1	127.2	113.4	101.1
35°	1849.6	1353.6	966.6	572.7	380.9	208.3	96.8	62.7	58.4	56.7	55.8
37.5°	1525.3	1070.3	635.4	229.2	136.8	77.6	44.4	40.1	39.2	40.1	39.2
40°	1203.7	706.0	251.9	76.7	41.9	33.9	31.4	28.8	28.8	29.6	28.8
42.5°	720.8	263.2	76.7	28.8	27.1	24.4	23.6	22.6	21.8	22.6	22.6
45°	237.9	67.1	25.3	20.1	19.1	18.3	17.4	17.4	17.4	17.4	18.3
47.5°	54.0	23.6	17.4	14.8	14.8	14.0	14.0	13.1	14.0	14.0	14.8
50°	20.9	14.8	12.2	11.3	11.3	10.5	10.5	10.5	10.5	11.3	11.3
52.5°	13.1	10.5	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	9.6
55°	8.7	7.8	7.0	7.0	7.0	7.0	7.0	7.8	7.8	7.8	7.8
57.5°	6.1	6.1	6.1	6.1	7.0	6.1	7.0	6.1	6.1	7.0	7.8
60°	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	7.0	7.0	7.8
62.5°	5.2	6.1	6.1	6.1	6.1	6.1	6.1	7.0	7.0	7.0	7.8
65°	5.2	5.2	6.1	6.1	6.1	6.1	7.0	7.0	7.0	7.8	7.8
67.5°	4.3	5.2	5.2	6.1	6.1	6.1	6.1	7.0	7.0	7.0	7.8
70°	4.3	4.3	5.2	5.2	5.2	5.2	6.1	6.1	6.1	7.0	7.0
72.5°	4.3	4.3	5.2	5.2	5.2	5.2	5.2	6.1	6.1	6.1	7.0
75°	4.3	4.3	5.2	5.2	5.2	5.2	5.2	6.1	6.1	6.1	7.0
77.5°	4.3	4.3	5.2	5.2	5.2	5.2	5.2	6.1	6.1	6.1	7.0
80°	4.3	4.3	5.2	5.2	5.2	5.2	6.1	6.1	6.1	6.1	7.0
82.5°	4.3	4.3	5.2	5.2	5.2	5.2	5.2	6.1	6.1	6.1	6.1
85°	4.3	4.3	5.2	5.2	5.2	5.2	5.2	5.2	6.1	6.1	6.1
87.5°	4.3	4.3	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	6.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192205

CATALOG NUMBER: LDA6A40935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4
2.5°	929.1	893.4	876.0	849.8	851.5	808.0	791.5	760.1	742.6	724.3	703.4
5°	836.7	774.0	729.5	694.7	675.5	618.9	580.5	530.8	479.4	429.7	388.7
7.5°	720.8	638.0	570.0	525.6	498.6	384.4	311.2	252.7	230.1	212.6	195.2
10°	591.8	488.9	368.7	307.7	270.2	216.1	194.4	161.3	137.7	115.9	102.9
12.5°	462.0	305.1	220.5	202.2	189.2	140.3	110.7	102.9	83.6	79.3	77.6
15°	290.3	200.5	156.1	134.2	116.8	97.6	89.8	88.9	92.4	93.3	92.4
17.5°	205.7	160.4	117.7	115.0	115.0	125.5	127.2	135.1	142.1	148.1	149.1
20°	264.1	237.1	276.3	293.7	324.2	361.7	416.6	493.4	560.4	628.4	680.8
22.5°	505.5	564.8	652.0	682.5	733.9	814.1	889.9	960.5	1032.0	1085.2	1096.5
25°	743.5	784.5	835.9	824.6	840.2	835.9	793.2	735.6	705.2	649.4	630.2
27.5°	569.2	526.5	490.7	449.7	429.7	391.3	336.5	301.6	270.2	238.9	225.8
30°	231.9	203.1	182.2	167.4	158.6	137.7	127.2	115.9	110.7	102.9	98.4
32.5°	90.6	85.4	82.8	80.2	79.3	76.7	74.1	70.6	69.7	69.7	66.2
35°	54.0	54.0	54.0	53.2	54.0	53.2	52.3	51.4	52.3	52.3	49.7
37.5°	38.4	39.2	39.2	39.2	39.2	39.2	39.2	39.2	38.4	38.4	35.7
40°	28.8	29.6	30.6	29.6	30.6	30.6	29.6	28.8	28.8	28.8	27.1
42.5°	23.6	23.6	23.6	23.6	24.4	23.6	23.6	23.6	23.6	23.6	22.6
45°	19.1	19.1	19.1	19.1	20.1	20.1	19.1	19.1	20.1	20.1	19.1
47.5°	14.8	14.8	14.8	14.8	14.8	14.8	14.8	14.0	14.0	14.0	13.1
50°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	12.2	11.3	11.3
52.5°	9.6	9.6	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	9.6
55°	8.7	8.7	9.6	9.6	9.6	9.6	9.6	8.7	8.7	8.7	7.8
57.5°	7.8	8.7	8.7	8.7	8.7	8.7	8.7	8.7	7.8	7.8	7.0
60°	7.8	7.8	8.7	8.7	8.7	8.7	7.8	7.8	7.0	7.0	6.1
62.5°	7.8	7.8	8.7	8.7	8.7	7.8	7.8	7.0	7.0	6.1	6.1
65°	7.8	8.7	8.7	8.7	8.7	7.8	7.8	7.0	7.0	6.1	6.1
67.5°	7.8	8.7	8.7	8.7	8.7	7.8	7.8	7.0	7.0	6.1	6.1
70°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.0	7.0	6.1	6.1
72.5°	7.0	7.8	7.8	7.8	7.8	7.8	7.0	7.0	7.0	6.1	6.1
75°	7.0	7.0	7.0	7.0	7.8	7.0	7.0	7.0	6.1	6.1	5.2
77.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	6.1	6.1	6.1	5.2
80°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	6.1	6.1	5.2	5.2
82.5°	7.0	7.0	7.0	7.0	7.0	7.0	6.1	6.1	5.2	5.2	5.2
85°	6.1	6.1	6.1	6.1	6.1	6.1	6.1	5.2	5.2	4.3	4.3
87.5°	6.1	6.1	6.1	6.1	6.1	5.2	5.2	4.3	3.5	3.5	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192205

CATALOG NUMBER: LDA6A40935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4	1015.4
2.5°	680.8	666.0	662.5	662.5	654.5	638.9	636.2	631.1
5°	344.3	307.7	300.7	292.9	279.8	264.1	259.7	258.0
7.5°	177.9	162.1	159.5	154.3	146.4	138.6	136.8	136.0
10°	104.6	95.0	90.6	82.8	75.0	70.6	70.6	69.7
12.5°	77.6	77.6	77.6	77.6	77.6	77.6	77.6	77.6
15°	94.1	96.8	96.8	97.6	98.4	99.4	101.1	99.4
17.5°	158.6	171.7	170.9	172.6	178.7	186.5	183.0	187.4
20°	770.5	870.8	899.5	928.3	1015.4	1097.4	1080.8	1138.3
22.5°	1107.0	1137.5	1125.3	1117.5	1135.8	1126.1	1167.1	1140.1
25°	593.5	587.5	587.5	561.4	566.6	553.4	570.9	563.1
27.5°	218.8	199.6	197.8	185.7	193.5	175.2	180.4	176.9
30°	94.1	95.0	91.6	88.9	86.3	84.6	84.6	83.6
32.5°	64.5	64.5	62.7	61.0	59.3	57.5	56.7	55.8
35°	47.9	47.9	46.2	45.4	44.4	42.7	41.9	41.9
37.5°	34.9	34.9	33.9	33.1	31.4	30.6	29.6	29.6
40°	27.1	26.1	25.3	25.3	23.6	23.6	22.6	22.6
42.5°	21.8	21.8	21.8	20.9	20.1	19.1	19.1	19.1
45°	19.1	19.1	18.3	17.4	17.4	17.4	16.6	16.6
47.5°	13.1	13.1	12.2	12.2	11.3	11.3	10.5	10.5
50°	10.5	10.5	10.5	10.5	9.6	8.7	8.7	8.7
52.5°	9.6	8.7	8.7	8.7	7.8	7.8	7.0	7.0
55°	7.8	7.8	7.0	7.0	6.1	6.1	6.1	6.1
57.5°	7.0	6.1	6.1	6.1	5.2	5.2	5.2	5.2
60°	6.1	5.2	5.2	5.2	4.3	4.3	4.3	4.3
62.5°	5.2	5.2	5.2	5.2	4.3	4.3	4.3	4.3
65°	5.2	5.2	5.2	4.3	4.3	4.3	4.3	3.5
67.5°	5.2	5.2	5.2	5.2	4.3	4.3	4.3	4.3
70°	5.2	5.2	5.2	5.2	4.3	4.3	4.3	4.3
72.5°	5.2	5.2	5.2	5.2	4.3	4.3	4.3	4.3
75°	5.2	5.2	5.2	5.2	4.3	4.3	4.3	4.3
77.5°	5.2	4.3	4.3	4.3	4.3	4.3	4.3	4.3
80°	5.2	4.3	4.3	4.3	4.3	3.5	3.5	4.3
82.5°	4.3	4.3	4.3	4.3	3.5	3.5	3.5	3.5
85°	3.5	3.5	3.5	3.5	2.6	2.6	2.6	2.6
87.5°	2.6	1.7	1.7	1.7	1.7	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)