

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192208

Luminaire Tested: **LDA6A40935D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192208
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26671)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40935D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4243.3 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 2.69 / 0.5 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192208

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192208

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91		
2	105	99	94	89	102	97	92	88	94	90	86	91	87	85	88	85	83	81		
3	98	89	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72		
4	91	81	74	69	89	80	73	68	78	72	68	75	71	67	73	69	66	64		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	78	67	60	54	77	66	59	54	65	58	53	63	57	53	62	57	53	51		
7	73	61	54	48	71	60	53	48	59	53	48	58	52	48	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	35650	35650	35650
5°	93974	32478	11177
10°	189882	25283	6791
15°	349627	18950	9796
20°	542063	15150	16323
25°	636430	13446	20723
30°	690094	13521	16059
35°	727655	8051	8633
40°	746355	3428	3743
45°	699212	1349	1287
50°	488897	597	298
55°	171540	583	0
60°	34602	669	0
65°	2153	791	0
70°	417	1122	0
75°	0	1483	0
80°	0	2210	253
85°	0	4906	503



TEST NUMBER: P1192208

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.4	2.0
10°-20°	465.3	11.0
20°-30°	1099.7	25.9
30°-40°	1339.7	31.6
40°-50°	996.5	23.5
50°-60°	241.3	5.7
60°-70°	8.9	0.2
70°-80°	4.3	0.1
80°-90°	4.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1648.3	38.8
0°-40°	2988.1	70.4
0°-60°	4225.9	99.6
0°-90°	4243.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4243.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	650	650	650	650	650	
5°	1708	1277	590	276	203	214
15°	6160	2670	334	153	173	1856
25°	10522	3348	222	322	343	4832
35°	10873	2445	120	131	129	6772
45°	9019	932	17	19	17	6625
55°	1795	20	6	4	0	2031
65°	17	4	6	4	0	55
75°	0	4	7	5	0	0
85°	0	4	8	5	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192208

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3
2.5°	1134.1	1115.0	1113.2	1094.0	1087.0	1084.4	1057.4	1047.8	1012.1	1005.1	954.5
5°	1707.7	1678.1	1672.0	1628.4	1596.1	1551.7	1528.1	1488.1	1403.5	1359.0	1277.1
7.5°	2429.5	2390.2	2381.6	2313.6	2246.4	2188.0	2139.2	2045.9	1890.8	1784.4	1617.1
10°	3411.1	3301.2	3261.1	3117.3	2978.6	2869.7	2813.0	2608.2	2374.6	2231.6	1998.0
12.5°	4657.7	4474.5	4399.6	4177.4	3933.3	3754.6	3644.7	3323.0	2942.9	2669.2	2335.3
15°	6160.4	5947.8	5813.6	5533.7	5090.0	4835.5	4641.1	4125.9	3571.5	3157.4	2670.1
17.5°	7796.8	7630.2	7429.7	6991.2	6276.5	5970.5	5617.4	4941.8	4181.7	3605.4	2969.1
20°	9291.7	9012.8	8862.0	8373.9	7545.7	7142.0	6707.1	5695.0	4721.2	3970.7	3198.4
22.5°	10101.6	9831.3	9740.7	9317.1	8557.8	8108.8	7555.2	6358.4	5135.4	4220.9	3320.4
25°	10521.7	10275.1	10281.1	9898.5	9213.3	8791.4	8228.2	6859.6	5417.7	4352.5	3348.3
27.5°	10850.4	10547.0	10493.9	10207.9	9598.6	9167.1	8624.0	7132.4	5521.5	4338.6	3272.4
30°	10901.8	10653.4	10691.8	10294.2	9738.1	9289.2	8724.2	7117.6	5415.2	4163.4	3075.4
32.5°	10867.0	10620.3	10708.3	10276.8	9677.9	9185.4	8556.9	6828.3	5103.1	3839.1	2786.1
35°	10873.0	10589.7	10524.4	10159.1	9446.0	8868.0	8109.7	6299.9	4641.9	3417.2	2445.2
37.5°	10743.2	10361.4	10372.7	9891.5	8998.0	8231.7	7373.1	5595.6	4096.2	2966.5	2102.6
40°	10429.4	10143.4	10052.8	9337.9	8145.4	7247.6	6419.4	4830.3	3465.1	2495.8	1700.7
42.5°	9982.2	9637.8	9372.0	8381.7	6937.2	6113.4	5397.8	4032.6	2868.9	2045.9	1320.6
45°	9018.9	8646.7	8131.5	6943.3	5720.3	5005.4	4408.3	3273.4	2320.5	1581.3	931.9
47.5°	7399.2	7049.6	6519.7	5521.5	4567.0	3971.6	3506.0	2563.8	1696.4	997.3	462.0
50°	5732.5	5466.6	5062.1	4195.7	3398.0	2841.0	2426.0	1610.1	865.6	455.1	193.5
52.5°	3736.3	3547.9	3187.9	2528.9	1920.4	1505.5	1223.9	685.2	408.0	191.7	56.7
55°	1794.8	1697.2	1436.7	1041.7	754.0	619.0	523.1	332.2	154.3	46.2	20.1
57.5°	715.7	694.8	619.0	466.4	357.4	303.4	235.4	91.6	30.6	19.1	12.2
60°	315.6	305.9	256.2	169.9	91.6	52.3	38.4	22.6	14.8	11.3	7.8
62.5°	45.4	41.9	35.7	27.9	22.6	19.1	16.6	12.2	7.8	6.1	5.2
65°	16.6	16.6	14.8	12.2	10.5	9.6	8.7	6.1	4.3	4.3	4.3
67.5°	7.0	7.0	7.0	5.2	5.2	4.3	3.5	3.5	3.5	3.5	4.3
70°	2.6	2.6	2.6	1.7	1.7	1.7	2.6	2.6	2.6	3.5	4.3
72.5°	0.0	0.8	0.8	0.8	1.7	1.7	1.7	2.6	2.6	3.5	4.3
75°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	2.6	3.5	4.3
77.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	3.5	3.5	4.3
80°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	3.5	3.5	4.3
82.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	3.5	4.3	4.3
85°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	3.5	3.5	4.3
87.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	3.5	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192208

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3
2.5°	911.8	899.6	858.6	817.7	811.6	794.1	758.4	716.6	662.5	628.5	594.5
5°	1170.7	1109.7	1040.8	961.5	937.1	902.3	827.3	747.0	657.3	590.2	527.4
7.5°	1473.2	1337.2	1207.4	1080.1	1032.2	978.1	863.9	748.8	626.0	528.2	449.8
10°	1756.6	1547.3	1345.9	1165.5	1094.0	1020.8	867.4	719.1	566.6	454.2	373.9
12.5°	2038.9	1739.1	1463.6	1227.4	1130.6	1036.5	848.1	666.0	493.4	386.2	321.7
15°	2261.2	1912.5	1549.1	1258.8	1138.4	1023.4	801.1	592.7	422.0	333.9	276.3
17.5°	2415.5	2012.0	1581.3	1245.7	1108.0	978.1	727.1	507.3	364.4	292.9	237.1
20°	2521.9	2043.4	1558.7	1191.6	1042.6	899.6	633.8	430.6	323.4	259.7	204.0
22.5°	2551.5	2012.8	1494.2	1110.6	957.2	809.9	537.0	380.1	293.8	233.6	197.9
25°	2522.7	1935.3	1397.4	1013.9	852.6	698.3	455.9	349.5	271.1	222.3	230.1
27.5°	2418.2	1798.3	1263.1	889.2	723.6	577.9	401.0	312.9	238.9	234.5	244.1
30°	2245.6	1602.3	1103.6	729.6	571.8	461.2	336.5	246.7	209.2	213.6	219.7
32.5°	1997.1	1361.7	898.8	540.5	419.3	347.0	240.6	170.9	165.6	169.1	173.4
35°	1683.3	1108.0	673.0	373.1	297.3	238.9	141.2	121.2	118.5	120.3	122.0
37.5°	1366.0	856.1	457.7	251.1	180.4	121.2	84.6	79.3	77.6	78.5	79.3
40°	1060.1	595.4	287.6	120.3	70.6	60.2	52.3	49.7	47.9	47.9	48.9
42.5°	774.1	353.0	143.0	47.1	38.4	35.7	31.4	29.6	27.9	28.8	29.6
45°	433.3	156.9	48.9	26.1	23.6	21.8	19.1	18.3	17.4	17.4	17.4
47.5°	184.9	54.9	23.6	16.6	14.8	14.0	12.2	11.3	10.5	10.5	10.5
50°	61.0	21.8	14.8	11.3	9.6	8.7	7.8	7.0	7.0	7.0	7.8
52.5°	21.8	14.0	9.6	7.8	7.0	7.0	6.1	6.1	6.1	6.1	6.1
55°	13.1	9.6	7.0	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1
57.5°	8.7	6.1	6.1	5.2	5.2	5.2	5.2	5.2	5.2	6.1	6.1
60°	6.1	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	6.1	6.1
62.5°	5.2	4.3	4.3	5.2	5.2	5.2	5.2	6.1	6.1	6.1	6.1
65°	4.3	4.3	4.3	5.2	5.2	5.2	5.2	6.1	6.1	6.1	6.1
67.5°	4.3	4.3	5.2	5.2	5.2	5.2	6.1	6.1	6.1	6.1	7.0
70°	4.3	4.3	5.2	5.2	5.2	6.1	6.1	6.1	6.1	7.0	7.0
72.5°	4.3	5.2	5.2	5.2	6.1	6.1	6.1	7.0	7.0	7.0	7.0
75°	4.3	5.2	5.2	6.1	6.1	6.1	6.1	7.0	7.0	7.0	7.0
77.5°	4.3	5.2	5.2	6.1	6.1	6.1	7.0	7.0	7.0	7.0	7.0
80°	5.2	5.2	6.1	6.1	6.1	7.0	7.0	7.0	7.0	7.0	7.8
82.5°	5.2	5.2	6.1	6.1	6.1	7.0	7.0	7.0	7.0	7.0	7.8
85°	5.2	5.2	6.1	6.1	6.1	7.0	7.0	7.0	7.0	7.8	7.8
87.5°	5.2	5.2	6.1	6.1	6.1	7.0	7.0	7.0	7.0	7.8	7.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192208

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3
2.5°	559.6	533.5	496.9	484.7	459.4	441.1	421.0	398.4	394.0	371.4	368.8
5°	466.4	424.5	382.7	367.0	345.2	326.9	306.9	285.0	275.5	253.7	240.6
7.5°	384.4	344.3	306.9	291.1	270.2	246.7	223.1	200.5	187.4	166.5	156.1
10°	322.5	282.5	242.4	226.6	207.5	181.4	156.1	132.5	123.8	118.5	119.4
12.5°	269.4	229.3	189.2	171.7	151.7	130.7	129.9	128.2	131.7	130.7	131.7
15°	225.8	183.1	144.7	139.5	139.5	143.0	146.5	147.3	153.4	153.4	155.1
17.5°	185.7	156.1	157.8	157.8	161.3	167.4	174.4	177.9	187.4	188.2	191.7
20°	172.6	179.6	187.4	189.2	195.2	204.8	214.5	221.4	233.6	237.1	244.1
22.5°	204.8	217.1	229.3	232.8	240.6	254.5	272.0	278.1	292.9	292.9	302.5
25°	241.4	259.7	272.0	276.3	285.0	297.3	308.6	312.1	322.5	319.1	322.5
27.5°	256.2	269.4	277.2	281.5	283.3	293.8	299.0	297.3	304.3	299.0	299.0
30°	227.5	237.1	241.4	244.1	244.1	251.9	251.9	249.4	253.7	249.4	246.7
32.5°	178.7	185.7	189.2	189.2	188.2	193.5	191.7	188.2	190.0	187.4	181.4
35°	124.7	129.9	132.5	131.7	130.7	135.2	132.5	129.9	130.7	129.0	124.7
37.5°	82.0	82.8	84.6	86.3	85.4	88.9	87.1	85.4	86.3	84.6	82.0
40°	49.7	51.4	53.2	53.2	53.2	54.0	54.0	53.2	54.9	53.2	51.4
42.5°	29.6	31.4	31.4	31.4	32.3	32.3	33.1	31.4	33.1	31.4	30.6
45°	18.3	18.3	18.3	19.1	18.3	19.1	19.1	18.3	19.1	18.3	17.4
47.5°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	10.5	11.3	10.5	9.6
50°	7.0	7.8	7.0	7.0	7.0	7.0	7.0	6.1	6.1	5.2	5.2
52.5°	6.1	6.1	6.1	6.1	6.1	6.1	5.2	5.2	4.3	3.5	3.5
55°	6.1	6.1	6.1	5.2	5.2	5.2	5.2	4.3	4.3	3.5	2.6
57.5°	6.1	6.1	5.2	5.2	5.2	5.2	4.3	4.3	3.5	2.6	2.6
60°	6.1	6.1	6.1	5.2	5.2	5.2	4.3	4.3	3.5	2.6	2.6
62.5°	6.1	6.1	6.1	5.2	5.2	5.2	5.2	4.3	3.5	2.6	2.6
65°	6.1	6.1	6.1	6.1	6.1	5.2	5.2	4.3	4.3	3.5	2.6
67.5°	7.0	6.1	6.1	6.1	6.1	6.1	5.2	4.3	4.3	3.5	2.6
70°	7.0	7.0	6.1	6.1	6.1	6.1	5.2	5.2	4.3	3.5	2.6
72.5°	7.0	7.0	7.0	7.0	6.1	6.1	6.1	5.2	4.3	3.5	3.5
75°	7.0	7.0	7.0	7.0	7.0	6.1	6.1	5.2	5.2	4.3	3.5
77.5°	7.8	7.0	7.0	7.0	7.0	7.0	6.1	5.2	5.2	4.3	3.5
80°	7.8	7.8	7.0	7.0	7.0	7.0	6.1	5.2	5.2	4.3	3.5
82.5°	7.8	7.8	7.0	7.0	7.0	7.0	6.1	6.1	5.2	4.3	3.5
85°	7.8	7.8	7.0	7.0	7.0	7.0	6.1	5.2	5.2	4.3	3.5
87.5°	7.8	7.8	7.0	7.0	7.0	7.0	6.1	5.2	5.2	4.3	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192208

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	650.3	650.3	650.3	650.3	650.3	650.3	650.3	650.3
2.5°	353.0	351.3	345.2	347.0	342.6	333.0	333.9	330.4
5°	231.9	226.6	220.5	220.5	214.5	205.7	205.7	203.1
7.5°	141.2	133.4	127.2	126.4	120.3	115.9	115.9	115.1
10°	119.4	120.3	120.3	121.2	120.3	120.3	121.2	122.0
12.5°	134.2	136.8	136.8	137.7	136.8	138.6	138.6	140.3
15°	160.4	164.8	165.6	167.4	166.5	169.1	170.9	172.6
17.5°	201.4	206.6	208.3	213.6	212.7	215.3	217.1	220.5
20°	253.7	261.5	264.2	271.1	270.2	272.8	277.2	279.8
22.5°	312.1	321.7	322.5	328.7	327.7	330.4	332.2	333.0
25°	327.7	333.9	333.0	336.5	336.5	337.4	337.4	342.6
27.5°	299.9	304.3	304.3	304.3	305.1	305.9	305.9	310.4
30°	246.7	248.4	249.4	246.7	248.4	249.4	249.4	253.7
32.5°	183.1	183.9	184.9	181.4	183.9	183.9	183.9	187.4
35°	126.4	126.4	127.2	124.7	126.4	127.2	126.4	129.0
37.5°	82.8	82.8	82.8	82.8	82.8	82.8	82.0	84.6
40°	51.4	52.3	51.4	51.4	50.6	50.6	50.6	52.3
42.5°	30.6	30.6	29.6	29.6	29.6	29.6	30.6	30.6
45°	17.4	17.4	16.6	16.6	15.7	16.6	16.6	16.6
47.5°	9.6	8.7	8.7	8.7	7.8	7.8	7.8	8.7
50°	4.3	4.3	4.3	3.5	3.5	3.5	2.6	3.5
52.5°	2.6	1.7	1.7	1.7	0.8	0.8	0.0	0.8
55°	1.7	1.7	0.8	0.8	0.0	0.0	0.0	0.0
57.5°	1.7	0.8	0.8	0.8	0.0	0.0	0.0	0.0
60°	1.7	0.8	0.8	0.8	0.0	0.0	0.0	0.0
62.5°	1.7	0.8	0.8	0.8	0.0	0.0	0.0	0.0
65°	1.7	0.8	0.8	0.8	0.0	0.0	0.0	0.0
67.5°	1.7	1.7	0.8	0.8	0.8	0.0	0.0	0.0
70°	2.6	1.7	1.7	0.8	0.8	0.0	0.0	0.0
72.5°	2.6	1.7	1.7	1.7	0.8	0.8	0.0	0.0
75°	2.6	1.7	1.7	1.7	0.8	0.8	0.0	0.0
77.5°	2.6	2.6	1.7	1.7	0.8	0.8	0.8	0.8
80°	2.6	2.6	1.7	1.7	1.7	0.8	0.8	0.8
82.5°	2.6	2.6	1.7	1.7	1.7	0.8	0.8	0.8
85°	2.6	2.6	1.7	1.7	1.7	0.8	0.8	0.8
87.5°	2.6	2.6	1.7	1.7	1.7	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)