

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192737

Luminaire Tested: **LDA6A70940D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26690)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70940D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6423.4 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 2.55 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192737

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192737

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	102		103	100	98		99	97	95		95	94	93
2	105	99	94	90	103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	79	96	89	83	78		86	81	77		83	79	76		81	77	75
4	91	82	75	70	89	81	74	69		78	73	68		76	71	68		74	70	67
5	85	74	67	62	83	73	67	62		72	66	61		70	64	60		68	63	60
6	79	68	60	55	77	67	60	55		65	59	55		64	58	54		62	58	54
7	74	62	55	49	72	61	54	49		60	54	49		59	53	49		57	52	48
8	69	57	49	44	67	56	49	44		55	49	44		54	48	44		53	48	44
9	64	52	45	40	63	52	45	40		51	44	40		50	44	40		49	43	39
10	60	48	41	36	59	48	41	36		47	40	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	64721	64721	64721
5°	167092	59988	18754
10°	316978	45768	6301
15°	566791	29756	6277
20°	844548	20243	11440
25°	963642	25247	71871
30°	1042135	21092	21491
35°	1094707	10266	6726
40°	1112019	3685	3414
45°	990746	2442	2054
50°	636303	1714	1399
55°	167516	1195	717
60°	37365	1250	548
65°	3580	1479	649
70°	1202	1827	801
75°	275	2415	1334
80°	0	3946	1989
85°	0	7170	3145



TEST NUMBER: P1192737

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.4	2.2
10°-20°	748.3	11.6
20°-30°	1755.7	27.3
30°-40°	2019.4	31.4
40°-50°	1434.5	22.3
50°-60°	291.7	4.5
60°-70°	14.6	0.2
70°-80°	8.7	0.1
80°-90°	7.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2647.3	41.2
0°-40°	4666.7	72.7
0°-60°	6392.9	99.5
0°-90°	6423.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6423.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1181	1181	1181	1181	1181	
5°	3036	2196	1090	436	341	370
15°	9987	4490	524	118	111	2996
25°	15931	5408	417	912	1188	7342
35°	16358	3797	153	113	100	10162
45°	12779	1350	32	34	26	9418
55°	1753	35	12	12	8	2364
65°	28	10	11	10	5	67
75°	1	6	11	10	6	3
85°	0	6	11	9	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192737

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6
2.5°	2034.3	1972.7	1942.5	1941.2	1853.2	1882.1	1853.2	1830.7	1748.8	1714.9	1658.4
5°	3036.4	2960.9	2900.7	2874.2	2723.4	2690.7	2675.6	2598.8	2427.9	2328.5	2196.5
7.5°	4218.3	4139.0	4039.7	3960.6	3741.7	3680.2	3639.9	3507.9	3255.1	3055.2	2808.8
10°	5694.3	5647.9	5486.8	5341.0	5009.1	4880.9	4760.2	4452.1	4121.5	3720.4	3402.2
12.5°	7682.2	7572.7	7286.2	6994.4	6473.8	6282.7	6082.9	5589.9	5084.6	4456.0	3930.4
15°	9986.8	9893.8	9452.4	8977.2	8236.6	7922.3	7609.3	6833.5	6056.4	5246.7	4489.9
17.5°	12639.7	12463.7	12025.0	11221.4	10185.5	9691.3	9107.9	8119.7	6998.1	5898.1	4957.5
20°	14476.7	14372.3	14001.4	13230.7	12051.3	11398.7	10674.6	9318.0	7784.0	6419.8	5264.4
22.5°	15481.2	15376.8	15099.0	14418.9	13452.0	12796.9	11955.8	10287.3	8377.4	6770.6	5408.9
25°	15931.3	15863.5	15711.3	15156.8	14261.7	13672.0	12876.1	10957.4	8748.4	6930.3	5407.7
27.5°	16347.6	16365.2	15989.3	15532.9	14708.1	14115.8	13361.4	11259.2	8821.3	6849.9	5234.2
30°	16463.2	16419.2	16254.6	15612.0	14843.8	14198.9	13390.3	11099.5	8537.2	6494.0	4889.6
32.5°	16391.6	16392.8	16238.2	15555.4	14652.7	13931.0	13021.9	10527.5	7983.9	5935.8	4354.0
35°	16357.7	16346.3	15945.3	15345.5	14198.9	13350.2	12204.7	9609.6	7217.0	5222.8	3797.1
37.5°	16020.6	15952.8	15663.6	14850.1	13350.2	12265.1	11031.6	8486.9	6272.7	4481.1	3226.2
40°	15539.1	15453.6	14983.4	13816.5	11899.1	10688.4	9462.5	7215.7	5284.5	3743.0	2590.1
42.5°	14552.2	14411.3	13698.5	12150.6	10030.8	8904.3	7888.4	5943.2	4320.1	3039.0	1989.1
45°	12779.3	12549.2	11562.2	9945.4	8097.0	7213.2	6354.5	4764.0	3458.9	2263.2	1350.4
47.5°	10260.9	10009.5	9114.2	7815.5	6339.4	5622.7	4893.4	3507.9	2339.9	1318.9	677.7
50°	7460.9	7287.3	6496.6	5401.4	4191.8	3590.9	3031.4	1956.3	1122.8	637.4	277.8
52.5°	4298.8	4174.3	3623.5	2842.7	2062.0	1726.3	1388.1	853.7	572.0	252.6	89.3
55°	1752.7	1681.0	1439.7	1219.5	915.3	790.9	660.0	426.2	192.4	60.4	35.2
57.5°	857.5	848.7	707.9	567.0	417.4	336.9	253.9	85.6	46.6	30.2	22.6
60°	340.8	328.1	225.0	130.7	72.9	59.1	50.3	35.2	26.5	20.1	16.4
62.5°	59.1	57.8	49.0	41.6	33.9	30.2	27.6	21.4	17.5	13.8	12.5
65°	27.6	27.6	25.2	22.6	18.8	17.5	16.4	13.8	11.4	10.1	10.1
67.5°	13.8	13.8	12.5	11.4	10.1	10.1	8.8	8.8	7.5	7.5	7.5
70°	7.5	7.5	7.5	6.3	6.3	6.3	6.3	6.3	5.0	6.3	6.3
72.5°	5.0	5.0	5.0	3.7	2.4	3.7	3.7	3.7	5.0	6.3	6.3
75°	1.3	1.3	1.3	2.4	2.4	2.4	3.7	3.7	5.0	6.3	6.3
77.5°	1.3	1.3	1.3	1.3	2.4	2.4	2.4	3.7	5.0	6.3	6.3
80°	0.0	1.3	1.3	1.3	2.4	2.4	2.4	3.7	5.0	6.3	6.3
82.5°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	5.0	6.3	6.3
85°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	5.0	6.3	6.3
87.5°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	5.0	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192737

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6
2.5°	1633.2	1567.8	1525.1	1449.6	1418.3	1404.5	1335.3	1268.6	1204.4	1158.0	1086.4
5°	2096.0	1991.6	1832.0	1682.3	1616.8	1575.4	1439.7	1313.9	1194.5	1090.1	965.6
7.5°	2593.8	2378.8	2128.6	1888.5	1775.3	1699.8	1489.9	1306.4	1135.4	977.0	807.1
10°	3071.6	2733.4	2368.8	2025.5	1872.1	1758.9	1484.8	1249.7	1027.3	822.2	640.0
12.5°	3479.0	3041.4	2557.4	2112.2	1912.3	1767.8	1438.4	1151.7	881.3	661.3	502.9
15°	3822.2	3277.8	2681.8	2141.3	1901.0	1730.0	1347.8	1017.2	721.7	524.3	406.1
17.5°	4063.7	3392.2	2710.7	2092.2	1821.9	1624.5	1210.8	844.9	567.0	423.8	320.7
20°	4204.5	3407.3	2640.4	1972.7	1683.6	1474.8	1038.5	663.9	460.1	347.0	248.9
22.5°	4225.9	3333.2	2502.1	1811.8	1523.8	1322.6	865.1	555.8	418.7	324.4	243.9
25°	4122.8	3186.1	2322.3	1654.7	1379.3	1173.1	748.0	562.0	470.2	417.4	433.8
27.5°	3922.8	2943.4	2116.1	1493.8	1228.5	1019.7	706.6	588.4	512.9	521.8	551.9
30°	3616.0	2601.4	1819.3	1220.8	940.4	777.1	562.0	423.8	352.0	333.2	334.5
32.5°	3164.7	2172.6	1428.3	847.4	632.4	524.3	355.8	236.4	237.7	220.0	218.7
35°	2649.2	1748.8	1068.7	568.3	437.6	364.7	209.9	165.9	159.6	153.4	144.7
37.5°	2138.7	1351.5	711.6	388.5	279.1	202.5	105.5	86.7	80.5	75.5	75.5
40°	1628.2	945.5	440.0	203.6	113.2	83.0	62.8	52.8	51.5	51.5	50.3
42.5°	1181.9	558.2	238.8	80.5	62.8	55.4	44.0	39.0	39.0	39.0	39.0
45°	628.7	284.1	91.7	50.3	41.6	39.0	32.6	30.2	30.2	31.5	31.5
47.5°	290.5	106.8	46.6	33.9	28.9	28.9	25.2	23.9	23.9	25.2	25.2
50°	104.4	44.0	30.2	23.9	21.4	22.6	20.1	18.8	20.1	20.1	20.1
52.5°	40.3	27.6	21.4	18.8	16.4	17.5	15.1	15.1	16.4	16.4	16.4
55°	25.2	20.1	16.4	13.8	12.5	13.8	12.5	12.5	12.5	12.5	12.5
57.5°	17.5	15.1	12.5	11.4	10.1	11.4	11.4	11.4	11.4	11.4	11.4
60°	13.8	11.4	10.1	10.1	10.1	10.1	10.1	10.1	10.1	11.4	11.4
62.5°	11.4	10.1	10.1	10.1	10.1	10.1	10.1	10.1	11.4	11.4	11.4
65°	10.1	8.8	10.1	10.1	8.8	10.1	10.1	10.1	11.4	11.4	12.5
67.5°	7.5	7.5	7.5	8.8	8.8	8.8	10.1	10.1	11.4	11.4	11.4
70°	7.5	7.5	8.8	8.8	8.8	8.8	10.1	10.1	11.4	11.4	11.4
72.5°	7.5	7.5	8.8	8.8	8.8	10.1	10.1	10.1	11.4	11.4	11.4
75°	7.5	7.5	8.8	8.8	8.8	10.1	10.1	10.1	11.4	11.4	11.4
77.5°	7.5	7.5	8.8	8.8	8.8	10.1	10.1	11.4	11.4	11.4	11.4
80°	7.5	8.8	8.8	10.1	10.1	10.1	10.1	11.4	11.4	12.5	12.5
82.5°	7.5	8.8	8.8	10.1	10.1	10.1	10.1	11.4	11.4	12.5	12.5
85°	7.5	8.8	8.8	10.1	10.1	10.1	10.1	11.4	11.4	11.4	11.4
87.5°	7.5	8.8	8.8	10.1	10.1	10.1	10.1	10.1	11.4	11.4	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192737

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6
2.5°	1038.5	977.0	915.3	885.2	858.8	821.1	773.2	734.2	692.8	671.4	622.4
5°	867.5	762.0	672.7	630.0	597.2	551.9	502.9	467.8	436.3	418.7	387.2
7.5°	671.4	570.9	492.9	460.1	436.3	391.0	354.6	318.1	285.4	261.6	230.1
10°	519.2	441.3	377.2	345.8	319.4	271.6	227.6	193.7	158.5	134.6	124.5
12.5°	412.4	339.5	274.1	242.7	215.0	165.9	133.3	127.0	120.6	118.2	114.5
15°	316.8	250.2	181.0	149.5	138.3	132.0	124.5	123.2	118.2	118.2	114.5
17.5°	237.7	163.5	138.3	135.7	134.6	132.0	128.3	127.0	125.7	125.7	124.5
20°	171.0	158.5	154.6	157.2	158.5	160.9	159.6	159.6	164.6	176.0	173.6
22.5°	240.1	260.3	281.7	289.2	316.8	344.5	369.7	401.0	475.2	560.8	580.9
25°	475.2	535.6	591.0	621.1	666.4	728.0	787.1	860.0	911.5	954.2	1003.3
27.5°	591.0	613.6	604.8	608.5	603.5	594.7	597.2	612.3	604.8	582.1	591.0
30°	349.6	367.1	357.0	362.1	348.3	348.3	344.5	352.0	347.0	338.2	335.8
32.5°	227.6	237.7	236.4	236.4	231.4	228.8	220.0	217.6	208.6	192.4	188.7
35°	137.0	130.7	124.5	120.6	118.2	118.2	116.9	116.9	113.2	109.4	108.1
37.5°	74.2	75.5	75.5	75.5	75.5	77.9	76.6	76.6	76.6	74.2	74.2
40°	51.5	54.1	54.1	54.1	55.4	55.4	55.4	56.5	55.4	55.4	55.4
42.5°	40.3	41.6	40.3	40.3	41.6	41.6	41.6	42.7	42.7	42.7	41.6
45°	32.6	32.6	31.5	32.6	32.6	33.9	33.9	33.9	33.9	32.6	32.6
47.5°	26.5	26.5	26.5	26.5	27.6	27.6	27.6	27.6	27.6	27.6	27.6
50°	21.4	21.4	21.4	22.6	22.6	22.6	21.4	22.6	22.6	22.6	21.4
52.5°	16.4	16.4	16.4	16.4	16.4	15.1	15.1	15.1	15.1	15.1	13.8
55°	12.5	12.5	12.5	12.5	12.5	13.8	12.5	13.8	12.5	12.5	11.4
57.5°	11.4	11.4	11.4	11.4	12.5	12.5	11.4	11.4	11.4	10.1	10.1
60°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	10.1	8.8	8.8
62.5°	12.5	12.5	11.4	11.4	11.4	11.4	10.1	10.1	10.1	8.8	8.8
65°	12.5	12.5	11.4	12.5	12.5	11.4	11.4	10.1	10.1	8.8	8.8
67.5°	12.5	12.5	12.5	12.5	12.5	12.5	11.4	11.4	10.1	10.1	8.8
70°	12.5	12.5	12.5	12.5	12.5	12.5	11.4	11.4	10.1	10.1	8.8
72.5°	12.5	12.5	12.5	12.5	12.5	12.5	11.4	11.4	11.4	10.1	8.8
75°	12.5	12.5	12.5	12.5	12.5	11.4	11.4	11.4	10.1	10.1	8.8
77.5°	12.5	12.5	12.5	12.5	12.5	11.4	11.4	11.4	10.1	10.1	8.8
80°	12.5	12.5	12.5	12.5	12.5	12.5	11.4	11.4	10.1	10.1	8.8
82.5°	12.5	12.5	12.5	12.5	12.5	11.4	11.4	11.4	10.1	10.1	8.8
85°	12.5	11.4	11.4	11.4	11.4	11.4	10.1	10.1	8.8	8.8	7.5
87.5°	11.4	11.4	11.4	11.4	11.4	10.1	10.1	8.8	7.5	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192737

CATALOG NUMBER: LDA6A70940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6	1180.6
2.5°	622.4	611.0	606.0	597.2	589.7	586.0	572.0	588.4
5°	380.9	367.1	363.4	355.8	347.0	341.9	331.9	340.8
7.5°	217.6	201.2	193.7	187.4	178.6	171.0	162.2	167.2
10°	121.9	116.9	118.2	114.5	113.2	111.9	110.6	113.2
12.5°	113.2	109.4	110.6	108.1	106.8	106.8	105.5	106.8
15°	114.5	110.6	113.2	110.6	109.4	109.4	108.1	110.6
17.5°	124.5	121.9	124.5	121.9	123.2	121.9	123.2	124.5
20°	174.7	178.6	186.1	181.0	184.8	189.8	196.1	196.1
22.5°	614.9	695.3	705.3	745.6	848.7	844.9	914.1	916.6
25°	1073.7	1078.8	1124.1	1109.0	1110.3	1163.0	1158.0	1188.2
27.5°	617.3	616.0	624.9	608.5	613.6	617.3	603.5	619.9
30°	344.5	338.2	341.9	333.2	333.2	335.8	331.9	339.5
32.5°	191.1	186.1	186.1	179.7	178.6	177.3	173.6	177.3
35°	109.4	105.5	106.8	104.4	101.8	100.5	99.4	100.5
37.5°	75.5	72.9	74.2	71.6	69.2	67.9	66.6	67.9
40°	55.4	54.1	54.1	51.5	50.3	49.0	47.7	47.7
42.5°	41.6	40.3	40.3	37.7	36.5	35.2	33.9	35.2
45°	31.5	30.2	30.2	28.9	27.6	26.5	26.5	26.5
47.5°	27.6	26.5	27.6	26.5	25.2	25.2	25.2	25.2
50°	21.4	21.4	21.4	20.1	18.8	18.8	17.5	16.4
52.5°	13.8	12.5	12.5	11.4	11.4	10.1	10.1	10.1
55°	11.4	10.1	10.1	8.8	8.8	7.5	7.5	7.5
57.5°	8.8	8.8	7.5	7.5	6.3	6.3	6.3	6.3
60°	7.5	7.5	7.5	6.3	6.3	5.0	5.0	5.0
62.5°	7.5	6.3	6.3	6.3	5.0	5.0	5.0	5.0
65°	7.5	6.3	6.3	6.3	5.0	5.0	5.0	5.0
67.5°	7.5	6.3	6.3	6.3	5.0	5.0	5.0	5.0
70°	8.8	7.5	7.5	6.3	6.3	6.3	5.0	5.0
72.5°	8.8	7.5	7.5	7.5	6.3	6.3	6.3	6.3
75°	8.8	7.5	7.5	7.5	6.3	6.3	6.3	6.3
77.5°	8.8	7.5	7.5	7.5	6.3	6.3	6.3	6.3
80°	8.8	7.5	7.5	7.5	6.3	6.3	6.3	6.3
82.5°	7.5	7.5	7.5	6.3	6.3	6.3	6.3	6.3
85°	7.5	6.3	6.3	6.3	5.0	5.0	5.0	5.0
87.5°	5.0	5.0	3.7	3.7	3.7	2.4	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)