

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192743

Luminaire Tested: **LDA6A70940D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192743
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70940D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6757.8 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192743

CATALOG NUMBER: LDA6A70940D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192743

CATALOG NUMBER: LDA6A70940D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	102		103	100	98		99	97	95		95	94	93
2	105	99	94	90	103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	79	96	88	83	78		86	81	77		83	79	76		81	77	74
4	91	82	75	70	89	80	74	69		78	73	68		76	71	67		74	70	67
5	85	74	67	62	83	73	67	61		71	65	61		70	64	60		68	63	60
6	79	68	60	55	77	67	60	55		65	59	54		64	58	54		62	57	54
7	74	62	55	49	72	61	54	49		60	54	49		59	53	49		57	52	48
8	69	57	50	44	67	56	49	44		55	49	44		54	48	44		53	48	44
9	64	52	45	40	63	52	45	40		51	44	40		50	44	40		49	44	40
10	60	48	41	37	59	48	41	36		47	41	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	72171	72171	72171
5°	191519	66905	25600
10°	418062	54102	7626
15°	631037	39529	6635
20°	734031	27139	10419
25°	809521	29276	69367
30°	895644	22048	21573
35°	908949	11277	8071
40°	929856	4587	3872
45°	937663	2830	2341
50°	789876	1927	1492
55°	260894	1319	841
60°	51290	1250	548
65°	6045	1621	649
70°	1619	1827	801
75°	275	2415	1334
80°	0	3946	1989
85°	0	7862	3145



TEST NUMBER: P1192743

CATALOG NUMBER: LDA6A70940D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.2	2.6
10°-20°	884.7	13.1
20°-30°	1746.1	25.8
30°-40°	1969.6	29.1
40°-50°	1563.6	23.1
50°-60°	382.3	5.7
60°-70°	20.4	0.3
70°-80°	8.7	0.1
80°-90°	7.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2806.0	41.5
0°-40°	4775.6	70.7
0°-60°	6721.5	99.5
0°-90°	6757.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6757.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1316	1316	1316	1316	1316	
5°	3480	2608	1216	611	465	460
15°	11119	5910	696	137	117	3119
25°	13383	7163	484	876	1147	6199
35°	13582	4559	168	133	121	8542
45°	12095	1421	36	38	30	9065
55°	2730	62	14	14	9	3202
65°	47	11	12	10	5	114
75°	1	6	11	10	6	3
85°	0	6	12	9	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192743

CATALOG NUMBER: LDA6A70940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5
2.5°	2284.6	2240.6	2260.8	2229.3	2140.0	2112.4	2134.9	2101.0	1999.2	1960.2	1920.0
5°	3480.3	3441.3	3454.0	3382.2	3215.0	3157.2	3153.5	3050.3	2844.1	2728.5	2607.7
7.5°	5277.2	5223.1	5208.0	5035.7	4713.8	4593.1	4534.0	4280.1	3891.6	3616.2	3345.9
10°	7510.2	7563.0	7508.9	7229.8	6724.3	6498.0	6354.6	5874.4	5174.1	4649.7	4144.2
12.5°	9749.5	9782.2	9680.4	9333.4	8690.9	8419.3	8208.0	7593.2	6670.3	5780.0	5025.7
15°	11118.8	11273.5	11177.9	10935.3	10437.3	10107.9	9918.1	9158.5	7996.8	7018.5	5909.6
17.5°	12094.6	12237.8	12158.7	11960.0	11397.9	11132.6	11009.5	10384.5	9119.6	7876.0	6570.9
20°	12582.3	12757.2	12685.4	12460.4	12048.0	11826.7	11677.1	11067.3	9926.8	8513.6	7012.2
22.5°	12913.0	13106.7	13028.7	12823.7	12403.9	12146.0	12075.7	11498.5	10349.3	8895.8	7199.6
25°	13383.3	13545.5	13325.5	13072.8	12657.8	12386.2	12343.5	11753.8	10551.8	9040.3	7163.2
27.5°	13720.3	13912.7	13539.3	13282.7	12808.6	12523.2	12468.0	11913.5	10570.6	8926.0	6867.7
30°	14149.0	14024.6	13696.4	13324.2	12818.7	12514.4	12444.0	11820.3	10381.9	8504.8	6289.4
32.5°	13979.3	13949.1	13621.0	13183.4	12711.9	12405.0	12310.8	11533.8	9864.0	7777.9	5470.7
35°	13582.0	13677.5	13403.4	13131.8	12545.9	12226.6	12095.7	11111.3	9083.2	6842.5	4559.2
37.5°	13349.3	13409.7	13236.2	12904.3	12323.3	11903.5	11655.7	10400.8	8060.9	5663.1	3680.3
40°	12993.6	13146.9	12979.6	12598.7	11928.5	11352.7	10921.3	9117.1	6714.3	4464.9	2878.1
42.5°	12603.7	12740.8	12581.2	12124.8	11177.9	10405.8	9689.1	7608.3	5257.0	3411.3	2158.8
45°	12094.6	12217.8	11931.1	11220.7	9880.2	8815.3	8099.9	5975.0	3964.5	2505.9	1420.9
47.5°	11176.7	11143.9	10737.8	9633.9	7983.0	7028.6	6196.2	4280.1	2635.4	1419.6	706.6
50°	9261.6	8956.2	8358.9	7077.6	5357.6	4326.5	3758.3	2209.1	1195.8	687.8	443.9
52.5°	5998.9	5658.1	5111.1	3927.9	2572.5	2064.6	1656.0	998.4	623.6	388.5	174.7
55°	2729.7	2488.2	2138.8	1586.8	1103.9	917.9	777.1	505.4	334.5	144.7	61.5
57.5°	1039.8	959.4	852.4	680.3	510.5	441.3	366.0	242.7	104.4	54.1	36.5
60°	467.8	433.8	398.6	311.9	218.7	157.2	119.5	65.4	44.0	31.5	23.9
62.5°	159.6	133.3	110.6	79.2	59.1	51.6	45.3	36.5	26.5	21.4	16.4
65°	46.6	45.3	42.7	37.7	30.2	27.6	26.5	21.4	16.4	13.8	11.4
67.5°	22.6	21.4	20.1	18.8	15.1	13.8	13.8	12.5	10.1	8.8	7.5
70°	10.1	10.1	8.8	8.8	7.5	7.5	7.5	6.3	6.3	6.3	6.3
72.5°	5.0	5.0	5.0	3.7	3.7	3.7	3.7	5.0	5.0	6.3	6.3
75°	1.3	2.4	2.4	2.4	2.4	3.7	3.7	5.0	5.0	6.3	6.3
77.5°	1.3	1.3	1.3	2.4	2.4	2.4	3.7	5.0	5.0	6.3	6.3
80°	0.0	1.3	1.3	2.4	2.4	2.4	3.7	3.7	5.0	6.3	6.3
82.5°	0.0	1.3	1.3	2.4	2.4	2.4	3.7	3.7	5.0	6.3	6.3
85°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	5.0	6.3	6.3
87.5°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	5.0	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192743

CATALOG NUMBER: LDA6A70940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5
2.5°	1821.9	1795.4	1691.2	1610.7	1573.0	1570.4	1486.1	1434.7	1344.1	1273.7	1207.0
5°	2395.2	2278.3	2067.1	1899.8	1819.5	1777.9	1612.0	1492.5	1336.6	1215.8	1096.4
7.5°	2978.7	2756.1	2459.3	2141.3	2010.6	1930.0	1673.5	1482.4	1274.9	1106.5	958.1
10°	3575.9	3183.6	2741.0	2321.0	2132.5	1996.6	1667.3	1408.2	1169.4	971.9	809.7
12.5°	4198.3	3579.7	2963.6	2438.1	2189.0	2010.6	1610.7	1300.1	1039.8	829.8	675.3
15°	4722.7	3886.5	3104.4	2465.7	2171.5	1955.2	1490.0	1163.0	901.5	696.5	555.8
17.5°	5127.5	4058.8	3130.9	2397.8	2073.4	1832.0	1334.0	1012.2	755.6	574.6	435.0
20°	5331.2	4085.1	3047.8	2236.9	1896.1	1647.2	1156.7	858.8	633.7	465.2	345.8
22.5°	5346.3	3961.9	2866.7	2029.4	1701.3	1448.5	1010.9	740.6	555.8	417.4	328.1
25°	5150.1	3724.3	2624.1	1816.9	1501.2	1273.7	906.5	710.4	559.5	484.0	445.0
27.5°	4777.9	3394.9	2357.5	1604.3	1329.0	1153.0	863.8	710.4	606.1	547.0	560.8
30°	4262.4	2974.9	1986.7	1315.2	1081.3	927.9	679.0	531.9	417.4	348.3	335.8
32.5°	3593.5	2434.2	1540.2	971.9	788.3	668.9	459.0	333.2	269.0	262.7	255.2
35°	2957.3	1922.6	1169.4	718.0	580.9	472.8	292.9	196.1	178.6	168.5	160.9
37.5°	2336.1	1438.4	839.9	521.8	398.6	300.5	150.8	127.0	110.6	100.7	91.7
40°	1756.5	1033.6	592.2	315.6	208.8	129.6	90.6	77.9	69.2	64.1	61.5
42.5°	1242.3	687.8	367.1	133.3	99.4	81.7	62.8	55.4	50.3	47.7	45.3
45°	721.7	427.5	148.4	77.9	62.8	56.5	46.6	41.6	39.0	36.5	35.2
47.5°	451.4	172.3	76.6	50.3	44.0	40.3	33.9	32.6	30.2	28.9	28.9
50°	182.3	76.6	47.7	35.2	31.5	30.2	26.5	25.2	22.6	22.6	22.6
52.5°	69.2	45.3	32.6	25.2	22.6	21.4	18.8	18.8	17.5	17.5	17.5
55°	40.3	30.2	22.6	17.5	16.4	16.4	15.1	15.1	13.8	13.8	13.8
57.5°	26.5	20.1	16.4	12.5	12.5	12.5	11.4	11.4	11.4	11.4	11.4
60°	17.5	13.8	11.4	10.1	10.1	10.1	10.1	11.4	11.4	11.4	11.4
62.5°	12.5	11.4	10.1	10.1	10.1	10.1	10.1	11.4	11.4	11.4	12.5
65°	10.1	8.8	8.8	8.8	8.8	10.1	10.1	11.4	11.4	12.5	12.5
67.5°	7.5	7.5	7.5	7.5	8.8	8.8	10.1	11.4	11.4	11.4	12.5
70°	6.3	7.5	7.5	8.8	8.8	8.8	10.1	10.1	11.4	11.4	12.5
72.5°	6.3	7.5	7.5	8.8	8.8	8.8	10.1	11.4	11.4	11.4	12.5
75°	6.3	7.5	7.5	8.8	8.8	8.8	10.1	11.4	11.4	11.4	12.5
77.5°	7.5	7.5	8.8	8.8	8.8	10.1	10.1	11.4	11.4	12.5	12.5
80°	7.5	7.5	8.8	8.8	8.8	10.1	10.1	11.4	11.4	12.5	12.5
82.5°	7.5	7.5	8.8	8.8	8.8	10.1	10.1	11.4	11.4	12.5	12.5
85°	7.5	7.5	8.8	8.8	8.8	10.1	10.1	11.4	11.4	12.5	12.5
87.5°	7.5	7.5	8.8	8.8	8.8	10.1	10.1	11.4	11.4	11.4	12.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192743

CATALOG NUMBER: LDA6A70940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5
2.5°	1174.4	1116.6	1053.6	1033.6	1013.5	974.5	950.5	907.8	876.4	844.9	819.8
5°	1017.2	925.5	848.7	816.0	784.6	730.5	692.8	647.5	611.1	579.6	550.7
7.5°	853.7	748.2	671.4	638.7	607.3	548.2	500.4	443.9	401.0	366.0	336.9
10°	702.9	602.2	519.2	480.3	443.9	382.2	336.9	291.8	255.2	225.0	198.7
12.5°	572.2	464.0	379.8	350.9	315.6	265.3	222.6	173.6	152.1	143.4	137.0
15°	443.9	347.0	276.7	250.2	218.7	171.0	152.1	143.4	137.0	133.3	128.3
17.5°	338.2	257.8	188.7	171.0	160.9	150.8	145.8	139.6	135.7	134.6	130.7
20°	265.3	194.8	177.3	172.3	172.3	169.7	165.9	165.9	164.6	168.5	168.5
22.5°	272.8	272.8	287.9	286.7	306.9	326.8	341.9	391.0	418.7	477.8	518.1
25°	476.5	521.8	574.6	591.0	630.0	687.8	748.2	823.5	876.4	932.9	955.5
27.5°	594.7	602.2	594.7	613.6	588.4	573.3	578.3	587.1	587.1	591.0	606.1
30°	352.0	369.7	385.9	398.6	392.3	385.9	383.5	364.7	364.7	357.0	350.9
32.5°	238.8	236.4	233.8	238.8	233.8	233.8	230.1	231.4	223.7	218.7	216.3
35°	163.5	155.9	147.1	148.4	143.4	142.1	138.3	138.3	133.3	130.7	129.6
37.5°	90.6	90.6	86.7	88.0	86.7	86.7	86.7	88.0	86.7	86.7	88.0
40°	61.5	61.5	60.4	61.5	60.4	61.5	62.8	62.8	62.8	62.8	61.5
42.5°	46.6	46.6	45.3	46.6	45.3	46.6	47.7	47.7	47.7	47.7	47.7
45°	36.5	36.5	36.5	36.5	36.5	36.5	36.5	37.7	37.7	36.5	36.5
47.5°	28.9	30.2	28.9	28.9	28.9	28.9	30.2	30.2	28.9	28.9	28.9
50°	23.9	23.9	22.6	22.6	22.6	22.6	22.6	22.6	22.6	22.6	22.6
52.5°	18.8	17.5	17.5	16.4	16.4	16.4	16.4	16.4	16.4	16.4	15.1
55°	13.8	13.8	12.5	12.5	12.5	13.8	13.8	13.8	13.8	12.5	12.5
57.5°	12.5	12.5	12.5	11.4	11.4	12.5	12.5	11.4	11.4	11.4	10.1
60°	11.4	12.5	11.4	11.4	11.4	11.4	11.4	10.1	10.1	10.1	8.8
62.5°	12.5	12.5	11.4	11.4	11.4	11.4	10.1	10.1	10.1	8.8	8.8
65°	12.5	12.5	12.5	11.4	11.4	11.4	11.4	10.1	10.1	8.8	8.8
67.5°	12.5	12.5	12.5	12.5	11.4	11.4	11.4	10.1	10.1	10.1	8.8
70°	12.5	12.5	12.5	12.5	12.5	11.4	11.4	11.4	10.1	10.1	8.8
72.5°	12.5	12.5	12.5	11.4	11.4	11.4	11.4	11.4	10.1	10.1	8.8
75°	12.5	12.5	12.5	11.4	11.4	11.4	11.4	10.1	10.1	10.1	8.8
77.5°	12.5	12.5	12.5	11.4	11.4	11.4	11.4	10.1	10.1	10.1	8.8
80°	12.5	12.5	12.5	11.4	11.4	11.4	11.4	10.1	10.1	10.1	8.8
82.5°	12.5	12.5	12.5	11.4	11.4	11.4	11.4	10.1	10.1	8.8	8.8
85°	12.5	12.5	11.4	11.4	11.4	11.4	10.1	10.1	8.8	8.8	7.5
87.5°	11.4	11.4	11.4	11.4	10.1	10.1	10.1	8.8	7.5	7.5	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192743

CATALOG NUMBER: LDA6A70940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5	1316.5
2.5°	789.6	784.6	780.8	788.3	785.8	754.4	758.2	756.9
5°	518.1	506.7	498.0	501.7	491.6	477.8	467.8	465.2
7.5°	308.0	295.5	287.9	280.4	277.8	260.3	252.8	257.8
10°	169.7	152.1	150.8	147.1	142.1	138.3	135.7	137.0
12.5°	130.7	129.6	127.0	125.7	123.2	121.9	120.6	119.5
15°	124.5	123.2	121.9	120.6	119.5	118.2	116.9	116.9
17.5°	128.3	128.3	127.0	125.7	125.7	127.0	125.7	124.5
20°	167.2	167.2	169.7	173.6	173.6	177.3	182.3	178.6
22.5°	543.1	570.9	604.8	614.9	674.0	721.7	809.7	770.7
25°	993.3	1056.2	1071.3	1092.7	1125.3	1141.7	1125.3	1146.8
27.5°	603.5	624.9	627.4	628.7	636.2	635.0	618.6	628.7
30°	350.9	358.3	355.9	354.6	352.0	338.2	335.8	340.8
32.5°	220.0	217.6	216.3	215.0	215.0	207.5	211.2	208.8
35°	125.7	129.6	128.3	127.0	123.2	121.9	121.9	120.6
37.5°	84.3	85.6	84.3	83.0	80.5	79.2	77.9	76.6
40°	60.4	61.5	60.4	59.1	57.8	56.5	55.4	54.1
42.5°	45.3	46.6	45.3	45.3	42.7	41.6	40.3	39.0
45°	35.2	33.9	33.9	33.9	32.6	31.5	30.2	30.2
47.5°	28.9	28.9	28.9	27.6	26.5	26.5	26.5	25.2
50°	21.4	22.6	21.4	21.4	20.1	18.8	18.8	17.5
52.5°	15.1	15.1	13.8	13.8	12.5	11.4	11.4	11.4
55°	11.4	11.4	11.4	10.1	10.1	8.8	8.8	8.8
57.5°	10.1	8.8	8.8	8.8	7.5	7.5	6.3	6.3
60°	8.8	7.5	7.5	6.3	6.3	5.0	5.0	5.0
62.5°	7.5	6.3	6.3	6.3	5.0	5.0	5.0	5.0
65°	7.5	6.3	6.3	6.3	5.0	5.0	5.0	5.0
67.5°	7.5	7.5	6.3	6.3	6.3	5.0	5.0	5.0
70°	7.5	7.5	7.5	6.3	6.3	6.3	5.0	5.0
72.5°	8.8	7.5	7.5	7.5	6.3	6.3	6.3	6.3
75°	8.8	7.5	7.5	7.5	6.3	6.3	6.3	6.3
77.5°	8.8	7.5	7.5	7.5	6.3	6.3	6.3	6.3
80°	7.5	7.5	7.5	6.3	6.3	6.3	6.3	6.3
82.5°	7.5	7.5	7.5	7.5	6.3	6.3	6.3	6.3
85°	7.5	6.3	6.3	6.3	5.0	5.0	5.0	5.0
87.5°	6.3	5.0	5.0	3.7	3.7	3.7	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)