

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192213

Luminaire Tested: **LDA6A40935D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26668)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40935D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3184.2 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 2.16 / 1.11 / 1.51
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192213

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192213

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80		
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70		
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62		
5	83	72	65	59	81	71	64	59	69	63	58	67	62	57	66	61	57	55		
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49		
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44		
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39		
9	63	50	43	38	61	50	43	38	49	42	37	48	42	37	47	41	37	35		
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	52567	52567	52567
5°	83568	51810	33485
10°	124380	49788	22611
15°	176732	47401	17021
20°	231358	45265	17391
25°	275478	45771	30062
30°	305509	44146	28314
35°	311667	37631	20833
40°	297908	29011	15407
45°	259810	20886	11629
50°	198066	15172	7727
55°	110572	10915	4502
60°	50851	7554	1820
65°	23984	4073	791
70°	11733	1955	833
75°	5528	1292	911
80°	2747	1357	1105
85°	1635	2201	1069



TEST NUMBER: P1192213

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	3.1
10°-20°	361.7	11.4
20°-30°	723.6	22.7
30°-40°	888.6	27.9
40°-50°	711.8	22.4
50°-60°	313.1	9.8
60°-70°	70.6	2.2
70°-80°	12.8	0.4
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1184.2	37.2
0°-40°	2072.7	65.1
0°-60°	3097.6	97.3
0°-90°	3184.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3184.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	959	959	959	959	959	
5°	1519	1307	942	697	608	167
15°	3114	2100	835	389	300	908
25°	4554	2594	757	471	497	2096
35°	4657	2338	562	339	311	2883
45°	3351	1544	269	165	150	2548
55°	1157	572	114	65	47	1099
65°	185	117	31	10	6	212
75°	26	15	6	5	4	33
85°	3	3	4	4	2	3
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192213

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9
2.5°	1223.1	1191.7	1217.0	1195.2	1188.2	1185.7	1175.2	1168.2	1165.6	1141.2	1122.0
5°	1518.6	1482.0	1508.2	1475.9	1459.4	1450.6	1432.3	1409.7	1391.4	1345.2	1306.8
7.5°	1864.8	1825.5	1850.0	1803.8	1772.3	1756.7	1727.0	1683.4	1642.5	1568.3	1503.8
10°	2234.4	2202.2	2223.1	2158.6	2109.7	2084.5	2040.9	1985.0	1901.4	1793.3	1698.2
12.5°	2665.1	2618.9	2635.5	2549.2	2479.4	2443.6	2381.7	2294.6	2176.0	2028.7	1898.7
15°	3114.0	3070.5	3080.9	2971.0	2874.3	2824.6	2744.4	2620.7	2463.7	2271.0	2100.2
17.5°	3574.4	3515.1	3513.3	3382.6	3253.5	3190.8	3090.6	2927.5	2743.6	2490.7	2279.8
20°	3965.8	3914.3	3900.4	3764.5	3588.3	3515.1	3393.9	3191.7	2965.9	2672.9	2425.3
22.5°	4301.4	4242.2	4216.9	4057.3	3857.6	3772.3	3633.6	3388.7	3137.6	2806.3	2527.4
25°	4554.3	4505.4	4468.8	4289.3	4066.1	3970.2	3818.5	3553.5	3262.2	2899.6	2594.4
27.5°	4754.8	4689.4	4643.1	4447.1	4196.0	4094.9	3931.8	3644.1	3325.9	2937.1	2614.5
30°	4826.3	4760.8	4707.7	4498.5	4232.6	4121.8	3950.9	3645.8	3308.4	2909.2	2571.0
32.5°	4792.3	4724.3	4664.1	4445.3	4169.7	4053.8	3879.5	3570.0	3216.9	2815.9	2474.2
35°	4657.1	4603.1	4535.0	4314.5	4042.5	3916.1	3742.6	3425.3	3074.8	2670.3	2338.2
37.5°	4466.2	4382.5	4319.7	4103.5	3840.3	3711.3	3544.7	3239.6	2884.7	2496.0	2174.2
40°	4162.9	4078.3	4015.4	3807.1	3568.3	3438.4	3284.9	2993.8	2651.1	2289.3	1982.5
42.5°	3784.5	3706.0	3645.0	3451.4	3240.4	3114.0	2979.0	2709.5	2391.4	2060.0	1772.3
45°	3351.2	3275.3	3223.1	3054.8	2867.3	2755.7	2633.7	2395.7	2104.5	1803.8	1543.9
47.5°	2881.3	2803.7	2759.2	2608.4	2449.7	2348.6	2244.0	2038.2	1777.6	1519.6	1293.8
50°	2322.4	2247.5	2207.3	2081.0	1968.5	1875.3	1799.4	1634.6	1421.0	1217.9	1033.9
52.5°	1700.9	1642.5	1612.9	1525.6	1458.6	1388.8	1340.0	1224.8	1068.8	925.0	786.3
55°	1156.9	1108.9	1094.9	1040.9	1004.3	966.9	932.0	864.8	759.4	664.3	571.9
57.5°	723.6	718.3	728.0	680.0	663.4	647.8	620.7	583.3	517.0	457.7	401.9
60°	463.8	458.6	454.2	436.8	429.0	417.5	404.5	382.7	341.7	306.9	270.2
62.5°	293.8	290.3	294.7	284.2	273.7	273.7	259.8	247.6	222.3	201.4	175.2
65°	184.9	183.9	186.6	179.6	174.4	171.8	164.8	157.8	142.1	129.0	116.9
67.5°	116.9	115.9	117.7	115.9	109.9	108.1	103.8	99.4	88.9	81.1	72.3
70°	73.2	72.3	73.2	71.5	68.0	66.2	63.7	60.2	56.7	47.9	43.6
72.5°	44.4	43.6	44.4	43.6	40.9	40.9	37.4	35.7	33.1	27.9	24.4
75°	26.1	26.1	26.1	25.3	23.6	23.6	21.8	20.9	19.1	16.6	14.8
77.5°	14.8	14.8	14.8	14.8	14.0	14.0	13.1	12.2	11.3	9.6	9.6
80°	8.7	8.7	8.7	8.7	7.8	8.7	7.8	7.8	7.0	6.1	6.1
82.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	4.3	4.3	4.3	4.3
85°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
87.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192213

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9
2.5°	1106.3	1078.4	1073.2	1043.5	1038.3	1021.8	1013.0	997.3	965.9	949.4	929.3
5°	1260.6	1217.0	1191.7	1138.5	1122.0	1094.1	1065.3	1026.9	977.2	941.5	904.0
7.5°	1429.8	1358.3	1305.1	1226.6	1197.9	1156.9	1106.3	1046.2	976.4	923.2	870.1
10°	1599.7	1488.2	1406.2	1300.8	1258.9	1204.8	1131.5	1050.5	963.4	894.4	828.2
12.5°	1755.7	1616.3	1503.8	1369.6	1313.8	1247.6	1151.6	1050.5	946.8	864.8	787.2
15°	1925.8	1741.9	1595.4	1431.5	1362.6	1284.2	1166.4	1047.0	928.5	835.2	749.7
17.5°	2064.5	1845.6	1666.0	1475.1	1393.1	1303.3	1168.2	1033.1	904.9	802.9	714.0
20°	2166.4	1924.0	1714.0	1500.3	1408.0	1310.3	1161.3	1014.8	880.5	775.9	685.2
22.5°	2240.6	1971.2	1738.4	1509.1	1408.8	1306.8	1149.0	999.1	864.0	761.9	675.6
25°	2285.0	1994.7	1746.2	1505.6	1401.9	1295.5	1135.0	985.2	853.5	756.7	677.4
27.5°	2289.3	1985.0	1725.3	1479.4	1373.1	1266.7	1106.3	958.1	830.9	741.9	666.1
30°	2239.6	1931.0	1670.4	1421.9	1314.7	1210.0	1052.2	906.7	785.5	697.4	628.5
32.5°	2143.8	1836.0	1578.0	1334.7	1229.3	1127.2	973.7	836.9	718.3	637.3	569.3
35°	2016.4	1715.7	1458.6	1230.1	1127.2	1030.4	881.4	747.1	639.0	562.3	500.5
37.5°	1865.6	1575.3	1334.7	1114.2	1014.8	925.0	781.2	659.1	555.4	484.7	428.0
40°	1693.9	1416.7	1190.9	981.7	892.7	805.6	674.8	563.2	466.4	405.4	357.5
42.5°	1508.2	1248.4	1040.1	845.7	764.5	685.2	566.7	465.6	381.8	332.2	294.7
45°	1304.2	1070.5	883.1	713.1	635.5	570.2	458.6	374.9	311.3	269.4	243.2
47.5°	1086.3	883.1	720.1	573.6	505.6	449.8	358.3	295.5	250.2	221.5	199.7
50°	867.5	698.3	562.3	435.9	384.4	337.4	277.2	234.5	199.7	177.9	163.9
52.5°	662.6	525.7	418.5	319.9	285.0	252.8	213.6	184.9	158.6	143.0	132.5
55°	480.4	379.3	298.1	234.5	211.0	192.7	163.9	143.0	126.4	114.2	105.4
57.5°	334.7	262.4	208.4	170.9	156.9	143.8	123.8	109.9	98.5	89.8	82.8
60°	226.6	177.9	145.6	123.8	115.1	106.4	93.3	83.7	75.0	68.9	61.9
62.5°	149.1	122.0	103.8	90.6	82.8	76.7	68.9	61.0	54.0	48.9	42.7
65°	96.8	80.2	71.5	61.0	57.5	53.2	46.2	41.9	35.7	31.4	27.1
67.5°	61.0	52.3	46.2	40.1	37.4	34.0	30.6	26.1	22.6	19.1	16.6
70°	36.6	32.3	27.9	24.4	22.6	20.9	18.3	15.7	13.1	12.2	10.5
72.5°	21.8	19.1	16.6	14.8	14.0	13.1	11.3	9.6	8.7	7.8	7.0
75°	13.1	12.2	10.5	8.7	8.7	7.8	7.8	7.0	6.1	6.1	5.2
77.5°	8.7	7.8	7.0	6.1	6.1	6.1	5.2	5.2	5.2	5.2	5.2
80°	5.2	5.2	5.2	5.2	4.3	4.3	4.3	4.3	4.3	4.3	4.3
82.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	4.3	4.3
85°	2.6	2.6	2.6	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
87.5°	2.6	2.6	2.6	2.6	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192213

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9
2.5°	920.7	894.4	884.0	868.3	852.6	851.7	833.4	823.9	816.9	804.6	792.5
5°	878.8	838.7	814.3	793.3	773.3	759.4	732.3	714.0	697.4	680.0	657.3
7.5°	829.9	778.5	743.6	717.5	693.9	672.1	639.0	614.6	593.7	577.1	549.2
10°	777.7	718.3	674.8	646.0	621.6	590.3	558.0	530.9	508.3	490.0	462.9
12.5°	728.8	663.4	614.6	585.0	559.7	525.7	492.5	464.7	440.3	422.8	398.4
15°	683.5	614.6	562.3	532.6	506.5	472.5	439.3	411.5	388.8	370.5	348.7
17.5°	643.3	571.0	519.6	492.5	465.6	434.2	401.0	374.9	352.2	335.7	318.2
20°	616.4	547.5	497.8	472.5	449.0	419.3	393.2	372.3	350.5	337.4	326.9
22.5°	612.0	551.0	508.3	487.3	469.1	447.3	431.5	421.0	406.2	400.2	400.2
25°	620.7	568.4	534.4	517.8	503.0	490.8	483.0	476.0	470.7	471.6	471.6
27.5°	615.5	568.4	540.5	524.8	511.8	503.8	496.0	491.7	486.5	489.0	489.0
30°	581.5	536.1	512.6	496.0	483.9	476.9	465.6	460.3	454.2	455.1	452.4
32.5°	524.8	482.1	459.4	443.8	430.7	423.7	411.5	405.4	397.6	397.6	392.3
35°	458.6	418.5	397.6	383.6	371.4	364.5	353.0	347.0	339.2	334.7	332.2
37.5°	388.8	354.0	334.7	324.3	314.7	307.8	297.3	293.0	285.0	281.5	278.1
40°	324.3	299.0	280.7	272.0	264.2	258.1	248.4	244.9	238.0	235.4	231.9
42.5°	268.5	249.4	234.5	227.5	218.8	215.3	208.4	204.9	198.7	196.2	192.7
45°	224.0	208.4	196.2	190.1	184.9	180.4	173.5	170.9	164.8	162.1	160.4
47.5°	184.9	172.6	163.0	157.8	155.2	150.0	143.8	141.2	136.9	134.2	131.7
50°	151.7	142.1	134.2	129.9	128.2	122.9	117.7	115.9	111.6	109.9	107.2
52.5°	123.8	115.9	108.9	105.4	102.0	98.5	94.1	92.4	88.1	85.5	82.0
55°	99.4	91.6	85.5	82.8	81.1	75.8	71.5	68.9	65.4	61.0	58.4
57.5°	76.7	69.7	64.5	61.0	60.2	54.9	51.4	47.1	42.7	40.1	37.4
60°	56.7	50.6	45.4	41.9	40.9	35.7	31.4	28.8	25.3	23.6	22.6
62.5°	37.4	33.1	28.8	27.1	25.3	21.8	19.1	17.4	15.7	14.8	14.0
65°	23.6	20.1	17.4	16.6	14.8	13.1	12.2	11.3	10.5	9.6	8.7
67.5°	14.0	12.2	10.5	10.5	9.6	8.7	8.7	7.8	7.0	7.0	7.0
70°	8.7	7.8	7.0	7.0	7.0	7.0	7.0	6.1	6.1	6.1	6.1
72.5°	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	5.2	5.2
75°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
77.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	4.3	4.3	4.3	4.3
80°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
82.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	3.5	3.5	3.5
85°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	2.6
87.5°	3.5	3.5	3.5	3.5	3.5	2.6	2.6	2.6	2.6	2.6	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192213

CATALOG NUMBER: LDA6A40935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9
2.5°	782.8	768.0	766.3	762.9	759.4	763.7	761.1	754.1
5°	649.5	631.2	627.7	622.5	617.2	619.0	614.6	608.5
7.5°	537.9	518.8	515.3	509.1	503.8	503.0	498.7	492.5
10°	447.3	432.5	429.0	422.8	416.7	415.9	410.6	406.2
12.5°	382.7	368.8	365.3	359.2	354.0	352.2	347.8	344.4
15°	334.7	321.7	318.2	312.9	306.9	306.9	303.4	299.9
17.5°	305.1	293.8	289.5	285.0	279.8	279.0	277.2	274.7
20°	317.3	306.9	305.1	299.9	300.8	300.8	299.0	298.1
22.5°	395.8	392.3	399.3	394.1	403.7	407.2	408.9	408.9
25°	475.1	476.0	483.0	480.4	489.0	496.0	499.5	497.0
27.5°	489.0	490.0	492.5	491.7	498.7	503.0	505.6	499.5
30°	449.0	448.1	447.3	446.3	450.8	452.4	453.3	447.3
32.5°	387.1	384.4	385.3	381.0	382.7	382.7	386.2	377.5
35°	325.2	321.7	321.7	317.3	317.3	317.3	319.9	311.3
37.5°	272.9	269.4	268.5	264.2	263.2	261.5	264.2	256.3
40°	227.5	224.0	225.0	219.7	220.5	219.7	219.7	215.3
42.5°	188.4	185.7	184.9	183.1	183.9	183.9	186.6	183.1
45°	156.1	153.5	152.6	151.7	152.6	152.6	153.5	150.0
47.5°	129.9	126.4	125.5	123.8	123.8	121.2	121.2	117.7
50°	104.6	99.4	98.5	95.9	95.0	93.3	93.3	90.6
52.5°	79.3	75.0	73.2	71.5	70.6	68.9	68.9	67.2
55°	55.8	51.4	50.6	49.7	48.9	47.9	48.9	47.1
57.5°	34.9	33.1	32.3	31.4	30.6	29.6	29.6	28.8
60°	20.9	19.1	19.1	18.3	17.4	16.6	16.6	16.6
62.5°	13.1	12.2	12.2	11.3	11.3	10.5	10.5	10.5
65°	8.7	7.8	7.8	7.0	7.0	6.1	6.1	6.1
67.5°	6.1	6.1	6.1	6.1	5.2	5.2	5.2	5.2
70°	6.1	5.2	5.2	5.2	5.2	5.2	5.2	5.2
72.5°	5.2	5.2	5.2	5.2	4.3	4.3	4.3	4.3
75°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
77.5°	4.3	4.3	4.3	4.3	3.5	3.5	3.5	3.5
80°	4.3	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	3.5	3.5	3.5	3.5	2.6	2.6	2.6
85°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	1.7
87.5°	1.7	1.7	1.7	1.7	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)