

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192214

Luminaire Tested: **LDA6A40935D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192214
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26672)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40935D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4426.3 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 2.54 / 0.51 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192214

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192214

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	85	75	68	62	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	40	39		
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	54469	54469	54469
5°	139291	50214	18325
10°	299360	40514	6747
15°	436699	29631	7719
20°	494500	21305	11901
25°	536075	17136	18455
30°	598136	14072	17762
35°	607106	9102	11839
40°	611589	4365	5983
45°	607761	1830	2504
50°	486602	819	819
55°	145113	583	76
60°	29625	669	0
65°	2828	791	0
70°	272	1122	0
75°	0	1483	0
80°	0	2462	253
85°	0	4906	503

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192214

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.3	2.9
10°-20°	620.8	14.0
20°-30°	1141.0	25.8
30°-40°	1309.0	29.6
40°-50°	990.4	22.4
50°-60°	219.4	5.0
60°-70°	9.3	0.2
70°-80°	4.1	0.1
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1890.1	42.7
0°-40°	3199.1	72.3
0°-60°	4409.0	99.6
0°-90°	4426.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4426.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	994	994	994	994	994	
5°	2531	1890	912	446	333	335
15°	7695	4173	522	135	136	2144
25°	8863	4907	283	275	305	4135
35°	9072	3029	136	170	177	5682
45°	7839	857	24	31	32	5850
55°	1518	32	6	4	1	1880
65°	22	4	6	4	0	58
75°	0	4	7	4	0	0
85°	0	4	8	4	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192214

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	993.6	993.6	993.6	993.6	993.6	993.6	993.6	993.6	993.6	993.6	993.6
2.5°	1683.1	1666.6	1670.9	1691.8	1605.6	1602.9	1562.8	1557.5	1517.5	1444.3	1407.6
5°	2531.2	2520.7	2502.4	2509.4	2410.9	2344.7	2274.9	2224.3	2121.5	1982.9	1890.5
7.5°	3883.9	3770.6	3715.7	3610.3	3484.8	3356.6	3227.6	3077.7	2861.5	2620.0	2424.8
10°	5377.8	5328.1	5215.7	5148.6	4870.6	4682.3	4481.9	4175.0	3779.4	3341.8	2977.4
12.5°	6842.2	6783.7	6613.8	6470.9	6100.4	5932.2	5671.6	5284.6	4782.5	4159.4	3583.2
15°	7694.6	7707.7	7515.0	7508.1	7189.0	6970.3	6744.5	6287.0	5649.8	4934.2	4173.2
17.5°	8194.0	8226.2	8035.4	8089.4	7771.3	7544.6	7376.5	7041.7	6364.5	5506.0	4629.2
20°	8476.4	8527.9	8324.8	8366.7	8094.7	7941.3	7770.4	7439.2	6841.3	5893.8	4888.0
22.5°	8691.7	8711.8	8486.0	8541.8	8244.6	8091.2	7970.0	7659.7	7069.7	6098.7	4969.0
25°	8862.6	8913.1	8655.1	8659.5	8364.0	8210.6	8076.4	7794.0	7167.3	6152.7	4907.2
27.5°	9108.3	9149.4	8770.2	8737.1	8451.2	8282.1	8136.5	7858.5	7162.9	6032.5	4673.6
30°	9449.1	9220.8	8833.0	8747.5	8425.9	8254.2	8098.2	7737.3	7002.5	5708.2	4249.2
32.5°	9351.5	9166.8	8784.1	8648.1	8329.1	8145.2	7966.5	7527.3	6630.3	5206.1	3670.3
35°	9071.7	9012.5	8610.7	8568.0	8181.8	7989.2	7809.6	7209.1	6059.4	4549.8	3028.8
37.5°	8835.5	8734.4	8475.6	8408.4	8003.1	7790.5	7504.6	6734.0	5304.7	3713.1	2418.7
40°	8546.2	8478.2	8228.0	8156.6	7687.6	7363.4	7013.8	5872.9	4393.0	2890.3	1867.9
42.5°	8238.5	8177.5	7941.3	7791.3	7166.4	6737.5	6194.6	4830.5	3381.9	2178.1	1399.8
45°	7839.3	7753.0	7457.5	7178.6	6282.6	5668.9	5058.0	3686.1	2475.4	1550.6	856.8
47.5°	7153.3	7016.5	6658.2	6097.8	4997.0	4407.8	3771.4	2499.8	1528.8	798.4	431.4
50°	5705.6	5466.8	4990.0	4323.2	3200.5	2635.8	2137.2	1270.8	656.3	411.4	253.7
52.5°	3516.1	3297.3	2891.1	2247.9	1475.6	1136.6	895.2	591.8	361.7	232.7	94.1
55°	1518.3	1381.5	1187.1	905.6	643.2	529.0	425.4	295.4	186.5	71.5	32.3
57.5°	573.5	532.5	482.9	396.6	296.4	247.5	208.3	130.7	45.4	27.1	18.3
60°	270.2	244.9	216.1	171.7	113.4	81.9	51.4	33.1	21.8	14.8	10.5
62.5°	74.1	55.8	46.2	37.4	28.8	25.3	21.8	16.6	12.2	7.8	6.1
65°	21.8	19.1	18.3	15.7	13.1	11.3	9.6	7.8	6.1	4.3	4.3
67.5°	7.8	7.8	7.0	6.1	5.2	4.3	4.3	3.5	3.5	3.5	3.5
70°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.6	2.6	3.5	3.5
72.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	2.6	3.5	3.5
75°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	2.6	3.5	3.5
77.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	3.5	3.5	4.3
80°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	3.5	3.5	4.3
82.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	3.5	3.5	4.3
85°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	3.5	3.5	4.3
87.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	3.5	3.5	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192214

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	993.6	993.6	993.6	993.6	993.6	993.6	993.6	993.6	993.6	993.6	993.6
2.5°	1377.2	1326.6	1255.1	1218.5	1186.3	1177.5	1111.3	1068.6	1018.1	965.7	910.8
5°	1804.2	1675.2	1538.4	1423.4	1365.0	1330.9	1201.9	1105.2	1011.9	912.5	828.0
7.5°	2227.8	1996.9	1797.3	1611.6	1509.6	1432.9	1248.2	1102.6	961.4	832.4	718.2
10°	2637.5	2304.5	1986.4	1735.4	1595.1	1480.9	1242.0	1053.0	876.0	727.8	608.4
12.5°	3052.4	2566.9	2144.2	1801.6	1634.3	1487.9	1200.3	970.1	782.7	625.8	502.1
15°	3422.8	2770.8	2242.6	1817.3	1615.1	1442.5	1118.3	864.6	678.1	522.1	414.0
17.5°	3680.0	2880.7	2248.8	1759.8	1534.9	1349.2	1004.1	753.9	572.7	434.9	340.0
20°	3796.8	2877.2	2166.0	1640.3	1405.1	1211.6	869.0	640.7	477.6	365.2	284.1
22.5°	3761.9	2767.4	2019.5	1471.3	1246.5	1053.0	743.5	540.4	410.5	313.7	249.2
25°	3587.5	2575.6	1847.8	1302.2	1075.6	895.2	630.2	462.0	356.5	283.3	226.6
27.5°	3302.6	2314.1	1616.9	1104.3	896.9	756.6	530.8	399.2	313.7	250.2	236.2
30°	2886.0	1996.9	1345.8	890.8	724.3	598.8	430.6	321.7	251.0	222.3	223.1
32.5°	2426.6	1647.3	1058.1	680.8	545.6	462.0	318.2	224.9	183.9	182.2	183.0
35°	1969.0	1283.0	787.0	497.7	400.1	333.0	204.8	141.2	136.8	136.0	137.7
37.5°	1562.8	954.4	567.4	347.8	265.0	203.1	110.7	95.9	92.4	94.1	95.0
40°	1167.1	669.4	383.5	205.7	129.0	93.3	67.1	61.9	60.2	61.0	61.0
42.5°	802.8	418.4	228.4	85.4	61.9	51.4	42.7	40.1	38.4	37.4	38.4
45°	432.4	260.6	88.9	43.6	36.6	33.1	27.1	25.3	24.4	23.6	23.6
47.5°	276.3	96.8	40.1	27.1	23.6	21.8	18.3	16.6	15.7	14.8	14.8
50°	103.7	37.4	24.4	17.4	14.8	14.0	11.3	10.5	9.6	9.6	9.6
52.5°	35.7	22.6	15.7	11.3	9.6	8.7	7.8	7.0	7.0	7.0	7.0
55°	20.1	14.0	9.6	7.0	7.0	6.1	6.1	6.1	6.1	6.1	6.1
57.5°	12.2	7.8	6.1	5.2	5.2	5.2	5.2	6.1	6.1	6.1	6.1
60°	7.0	5.2	5.2	5.2	5.2	5.2	5.2	5.2	6.1	6.1	6.1
62.5°	4.3	4.3	4.3	4.3	4.3	5.2	5.2	6.1	6.1	6.1	6.1
65°	4.3	4.3	4.3	4.3	4.3	5.2	5.2	6.1	6.1	6.1	6.1
67.5°	3.5	4.3	4.3	5.2	5.2	5.2	5.2	6.1	6.1	7.0	6.1
70°	4.3	4.3	4.3	5.2	5.2	5.2	6.1	6.1	7.0	7.0	7.0
72.5°	4.3	4.3	4.3	5.2	5.2	5.2	6.1	6.1	7.0	7.0	7.0
75°	4.3	4.3	5.2	5.2	5.2	6.1	6.1	7.0	7.0	7.0	7.0
77.5°	4.3	4.3	5.2	5.2	5.2	6.1	6.1	7.0	7.0	7.8	7.0
80°	4.3	4.3	5.2	6.1	6.1	6.1	6.1	7.0	7.0	7.8	7.8
82.5°	4.3	5.2	5.2	6.1	6.1	6.1	7.0	7.0	7.8	7.8	7.8
85°	4.3	5.2	5.2	6.1	6.1	6.1	7.0	7.0	7.8	7.8	7.8
87.5°	4.3	5.2	5.2	6.1	6.1	6.1	7.0	7.0	7.8	7.8	7.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192214

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	993.6	993.6	993.6	993.6	993.6	993.6	993.6	993.6	993.6	993.6	993.6
2.5°	881.2	830.7	789.7	790.5	756.6	730.4	697.3	679.0	664.2	639.7	617.1
5°	766.2	688.6	630.2	618.9	579.7	539.5	498.6	468.0	446.2	422.7	401.0
7.5°	641.5	552.6	485.5	469.8	436.7	399.2	361.7	331.2	305.1	279.8	253.7
10°	520.3	439.2	378.2	362.6	329.5	290.3	254.5	227.4	207.5	187.4	167.4
12.5°	421.0	349.5	292.0	272.0	244.9	214.4	185.7	159.5	137.7	129.0	126.4
15°	340.8	272.8	227.4	210.9	188.2	156.9	140.3	136.0	135.1	135.1	135.1
17.5°	275.5	222.3	181.3	163.9	152.6	150.8	150.8	150.8	151.6	153.4	156.9
20°	230.9	183.9	168.2	169.9	169.9	171.7	175.2	177.9	181.3	185.7	190.9
22.5°	204.8	195.2	193.5	198.7	199.6	204.8	211.8	217.1	223.1	230.1	234.4
25°	224.0	227.4	230.1	237.9	240.6	249.2	259.7	267.6	274.6	282.4	287.6
27.5°	244.0	250.2	255.4	263.2	265.0	276.3	285.0	290.3	295.4	298.9	302.4
30°	230.1	236.2	241.4	248.4	248.4	260.6	265.0	269.3	273.7	275.5	278.9
32.5°	189.2	195.2	200.5	205.7	206.6	215.3	220.5	222.3	225.8	226.6	229.2
35°	142.1	144.7	149.9	154.3	155.1	161.3	165.6	167.4	169.9	169.9	171.7
37.5°	97.6	99.4	103.7	106.4	108.1	112.4	115.0	116.8	118.5	119.4	120.3
40°	63.7	64.5	67.1	69.7	71.5	74.1	75.8	77.6	78.5	80.2	80.2
42.5°	39.2	40.1	41.9	43.6	43.6	46.2	47.1	48.8	49.7	50.5	50.5
45°	24.4	25.3	25.3	26.1	27.1	27.9	29.6	29.6	30.6	30.6	30.6
47.5°	14.8	15.7	14.8	15.7	15.7	16.6	17.4	17.4	17.4	17.4	17.4
50°	9.6	9.6	9.6	9.6	9.6	9.6	10.5	10.5	10.5	10.5	9.6
52.5°	7.0	7.0	6.1	7.0	6.1	6.1	6.1	6.1	6.1	6.1	5.2
55°	6.1	6.1	6.1	6.1	5.2	5.2	5.2	4.3	4.3	3.5	3.5
57.5°	6.1	6.1	5.2	5.2	5.2	4.3	4.3	4.3	3.5	3.5	2.6
60°	6.1	6.1	5.2	5.2	5.2	4.3	4.3	3.5	3.5	2.6	2.6
62.5°	6.1	6.1	5.2	5.2	5.2	5.2	4.3	4.3	3.5	3.5	2.6
65°	6.1	6.1	6.1	5.2	5.2	5.2	4.3	4.3	3.5	3.5	2.6
67.5°	6.1	6.1	6.1	6.1	5.2	5.2	5.2	4.3	3.5	3.5	2.6
70°	6.1	6.1	6.1	6.1	6.1	5.2	5.2	4.3	4.3	3.5	2.6
72.5°	7.0	7.0	6.1	6.1	6.1	5.2	5.2	4.3	4.3	3.5	3.5
75°	7.0	7.0	6.1	6.1	6.1	5.2	5.2	4.3	4.3	3.5	3.5
77.5°	7.0	7.0	7.0	7.0	6.1	6.1	5.2	5.2	4.3	4.3	3.5
80°	7.0	7.0	7.0	7.0	6.1	6.1	6.1	5.2	4.3	4.3	3.5
82.5°	7.0	7.0	7.0	7.0	7.0	6.1	6.1	5.2	4.3	4.3	3.5
85°	7.0	7.0	7.0	7.0	7.0	6.1	6.1	5.2	4.3	4.3	3.5
87.5°	7.0	7.0	7.0	7.0	7.0	6.1	6.1	5.2	4.3	4.3	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192214

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	993.6	993.6	993.6	993.6	993.6	993.6	993.6	993.6
2.5°	596.2	584.8	584.0	574.4	555.2	564.8	552.6	543.9
5°	381.7	369.6	357.4	359.1	345.1	347.8	338.2	333.0
7.5°	242.4	229.2	225.8	225.8	210.1	210.1	204.0	200.5
10°	152.6	142.1	138.6	132.5	125.5	124.7	122.0	121.2
12.5°	123.8	123.8	121.2	122.0	122.0	122.0	121.2	121.2
15°	135.1	136.0	133.3	134.2	136.0	135.1	136.0	136.0
17.5°	156.1	160.4	156.9	158.6	162.1	161.3	162.1	162.9
20°	190.9	197.8	193.5	197.0	201.3	200.5	203.1	204.0
22.5°	237.9	246.7	242.4	245.8	252.7	251.0	254.5	256.2
25°	290.3	298.9	293.7	298.1	302.4	304.2	304.2	305.1
27.5°	302.4	307.7	304.2	308.5	310.2	312.0	310.2	311.2
30°	277.1	281.5	278.1	282.4	282.4	284.1	282.4	280.6
32.5°	228.4	231.9	227.4	232.7	231.9	232.7	233.6	234.4
35°	172.6	174.4	171.7	172.6	173.4	174.4	176.9	176.9
37.5°	120.3	122.9	120.3	121.2	121.2	122.9	124.7	124.7
40°	80.2	82.8	80.2	81.9	81.1	81.9	83.6	83.6
42.5°	50.5	52.3	50.5	51.4	51.4	51.4	52.3	53.2
45°	30.6	31.4	30.6	31.4	31.4	31.4	32.3	32.3
47.5°	17.4	18.3	17.4	17.4	18.3	17.4	18.3	18.3
50°	9.6	9.6	9.6	9.6	9.6	8.7	8.7	9.6
52.5°	5.2	5.2	4.3	4.3	4.3	4.3	4.3	4.3
55°	2.6	2.6	1.7	1.7	1.7	0.8	1.7	0.8
57.5°	1.7	1.7	0.8	0.8	0.8	0.8	0.0	0.0
60°	1.7	1.7	0.8	0.8	0.8	0.0	0.0	0.0
62.5°	1.7	1.7	0.8	0.8	0.8	0.0	0.0	0.0
65°	1.7	1.7	0.8	0.8	0.8	0.0	0.0	0.0
67.5°	2.6	1.7	0.8	0.8	0.8	0.0	0.0	0.0
70°	2.6	1.7	1.7	0.8	0.8	0.0	0.0	0.0
72.5°	2.6	1.7	1.7	1.7	0.8	0.8	0.0	0.0
75°	2.6	1.7	1.7	1.7	0.8	0.8	0.0	0.0
77.5°	2.6	2.6	1.7	1.7	0.8	0.8	0.8	0.0
80°	2.6	2.6	1.7	1.7	1.7	0.8	0.8	0.8
82.5°	2.6	2.6	1.7	1.7	1.7	0.8	0.8	0.8
85°	2.6	2.6	1.7	1.7	1.7	0.8	0.8	0.8
87.5°	2.6	2.6	1.7	1.7	1.7	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)