

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192747

Luminaire Tested: **LDA6A70950D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192747
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70950D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6582.3 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192747

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192747

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	101872	101872	101872
5°	197391	97072	32748
10°	335359	84952	14701
15°	516768	67753	23371
20°	748085	44092	40662
25°	1097567	42553	52279
30°	1276184	40310	40057
35°	1291716	21362	21181
40°	1069447	8044	8895
45°	807704	2737	3248
50°	552613	1015	1015
55°	76862	879	134
60°	1995	855	0
65°	493	1193	0
70°	224	1475	0
75°	0	1949	0
80°	0	3315	442
85°	0	6604	0

TEST NUMBER: P1192747

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.9	3.0
10°-20°	824.1	12.5
20°-30°	1879.8	28.6
30°-40°	2175.4	33.0
40°-50°	1312.0	19.9
50°-60°	178.2	2.7
60°-70°	5.7	0.1
70°-80°	6.2	0.1
80°-90°	5.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2898.8	44.0
0°-40°	5074.3	77.1
0°-60°	6564.5	99.7
0°-90°	6582.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6582.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1858	1858	1858	1858	1858	
5°	3587	2937	1764	965	595	417
15°	9105	5118	1194	367	412	2696
25°	18145	6065	704	846	864	8212
35°	19302	4624	319	326	316	11632
45°	10418	1259	35	43	42	8146
55°	804	9	9	7	1	1577
65°	4	5	9	5	0	6
75°	0	7	9	7	0	0
85°	0	7	10	7	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1192747

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3
2.5°	2687.3	2662.4	2672.9	2645.6	2576.1	2561.7	2560.4	2542.2	2483.2	2437.4	2382.6
5°	3587.0	3585.7	3592.2	3533.4	3411.8	3373.8	3355.6	3310.9	3168.5	3058.7	2937.2
7.5°	4710.3	4702.4	4694.7	4587.3	4396.4	4323.2	4276.2	4115.3	3919.2	3724.3	3507.2
10°	6024.5	6020.7	5990.4	5802.2	5496.2	5361.4	5269.9	5015.0	4699.9	4422.6	4053.8
12.5°	7550.5	7515.2	7461.7	7185.8	6766.0	6619.5	6418.2	6014.1	5530.1	5105.3	4589.9
15°	9105.4	9054.3	8959.0	8604.5	8084.1	7834.4	7584.6	7052.3	6395.9	5778.7	5118.3
17.5°	10626.3	10570.0	10346.3	9744.8	9236.2	8931.4	8654.2	7923.2	7151.7	6358.0	5521.0
20°	12823.2	12619.2	12229.5	11281.5	10336.0	9786.7	9462.3	8689.6	7734.9	6810.4	5807.4
22.5°	15757.6	15305.2	14474.7	12934.3	11583.5	10791.0	10260.0	9232.2	8154.7	7105.9	5984.1
25°	18145.4	17940.1	16996.0	14804.4	12696.3	11762.5	11023.8	9663.8	8460.7	7303.5	6065.1
27.5°	19684.6	19633.5	18554.7	16352.6	13605.2	12379.8	11554.7	9948.8	8608.4	7345.2	6025.8
30°	20160.6	20240.3	19204.6	16878.3	13868.1	12504.0	11601.8	9952.7	8494.8	7155.7	5774.8
32.5°	20125.2	20129.2	18859.5	16424.6	13440.3	12143.1	11209.5	9621.9	8075.0	6681.0	5297.4
35°	19301.5	19098.8	17662.9	15030.5	12445.3	11301.1	10432.8	8981.1	7383.2	5967.0	4624.0
37.5°	17492.9	17227.5	15553.6	13245.4	11266.9	10209.1	9508.1	8140.4	6559.3	5204.6	3928.3
40°	14944.2	14567.6	13186.7	11586.1	9977.7	9182.6	8594.0	7200.1	5678.1	4456.5	3275.7
42.5°	12392.8	12208.5	11295.9	9994.6	8893.7	8145.6	7531.0	6215.4	4830.6	3719.1	2450.7
45°	10418.3	10260.0	9646.7	8788.9	7708.8	7026.2	6433.9	5188.9	3753.0	2495.1	1259.3
47.5°	8979.9	8851.8	8264.7	7363.6	6178.8	5432.2	4821.4	3402.7	2126.3	1077.5	315.1
50°	6479.6	6348.8	5773.5	4729.9	3660.2	3035.0	2595.7	1519.5	602.8	218.3	32.8
52.5°	3176.4	3069.1	2678.1	2004.7	1345.7	967.7	707.5	285.1	69.3	23.5	15.7
55°	804.2	738.8	616.0	387.0	189.6	113.8	73.3	26.2	17.1	13.0	9.2
57.5°	45.8	44.4	40.6	30.1	22.3	19.6	17.1	13.0	9.2	7.8	6.6
60°	18.2	17.1	15.7	13.0	10.5	9.2	9.2	6.6	5.2	5.2	5.2
62.5°	7.8	7.8	7.8	6.6	5.2	5.2	5.2	3.8	5.2	5.2	5.2
65°	3.8	3.8	3.8	2.5	2.5	2.5	3.8	3.8	3.8	5.2	5.2
67.5°	2.5	1.4	1.4	1.4	2.5	2.5	2.5	3.8	3.8	5.2	5.2
70°	1.4	1.4	1.4	1.4	2.5	2.5	2.5	3.8	3.8	5.2	6.6
72.5°	0.0	1.4	1.4	1.4	2.5	2.5	2.5	3.8	3.8	5.2	6.6
75°	0.0	1.4	1.4	1.4	2.5	2.5	2.5	3.8	5.2	5.2	6.6
77.5°	0.0	1.4	1.4	1.4	2.5	2.5	2.5	3.8	5.2	5.2	6.6
80°	0.0	1.4	1.4	1.4	2.5	2.5	2.5	3.8	5.2	5.2	6.6
82.5°	0.0	0.0	1.4	1.4	2.5	2.5	2.5	3.8	5.2	5.2	6.6
85°	0.0	0.0	1.4	1.4	2.5	2.5	2.5	3.8	5.2	5.2	6.6
87.5°	0.0	0.0	1.4	1.4	2.5	2.5	2.5	3.8	3.8	5.2	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192747

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3
2.5°	2312.0	2264.9	2195.6	2149.9	2105.4	2063.5	1994.2	1955.0	1884.3	1819.0	1762.7
5°	2790.5	2672.9	2530.3	2408.7	2330.2	2253.1	2113.3	2009.9	1880.4	1764.0	1656.8
7.5°	3274.5	3066.4	2832.4	2632.3	2510.8	2391.7	2182.5	2015.2	1832.1	1666.0	1507.8
10°	3713.8	3401.3	3070.4	2784.2	2619.3	2465.0	2189.1	1966.7	1731.3	1526.1	1327.2
12.5°	4121.8	3694.2	3262.7	2888.7	2684.7	2498.9	2161.5	1889.6	1609.7	1366.6	1135.1
15°	4485.4	3936.1	3402.7	2948.8	2709.5	2489.9	2097.6	1781.1	1465.9	1193.8	901.1
17.5°	4761.3	4086.6	3464.1	2939.7	2665.1	2420.6	1987.6	1645.1	1312.9	983.4	652.5
20°	4928.7	4150.5	3450.9	2869.0	2569.5	2310.7	1856.9	1497.3	1128.5	755.8	575.3
22.5°	4999.3	4145.3	3389.5	2763.2	2451.8	2190.4	1731.3	1353.5	935.0	683.9	600.3
25°	5011.0	4091.8	3303.2	2646.7	2335.5	2075.3	1604.5	1190.0	812.0	703.5	672.3
27.5°	4920.9	3966.1	3141.1	2479.4	2172.0	1902.7	1414.9	945.5	762.4	701.0	721.9
30°	4654.1	3679.7	2854.7	2185.2	1888.3	1618.9	1010.8	741.4	632.8	636.8	642.0
32.5°	4184.6	3203.7	2394.4	1754.9	1430.6	1067.0	629.0	495.6	481.2	481.2	478.5
35°	3558.2	2621.8	1879.1	1110.2	711.4	512.6	325.5	326.9	320.3	319.2	317.8
37.5°	2911.0	2068.7	1190.0	459.0	308.7	214.4	192.2	194.9	192.2	196.2	193.5
40°	2295.0	1277.6	434.1	146.4	108.6	104.7	107.2	109.9	109.9	112.4	112.4
42.5°	1333.8	423.7	113.8	58.8	58.8	56.3	57.6	60.1	61.5	62.8	61.5
45°	396.3	87.7	36.6	32.8	32.8	31.4	31.4	32.8	33.9	35.3	35.3
47.5°	62.8	24.9	20.9	18.2	18.2	18.2	18.2	18.2	19.6	19.6	20.9
50°	19.6	15.7	13.0	11.9	11.9	10.5	10.5	11.9	11.9	11.9	13.0
52.5°	11.9	9.2	9.2	7.8	9.2	9.2	7.8	9.2	9.2	9.2	10.5
55°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	9.2	9.2	9.2
57.5°	6.6	6.6	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8
60°	6.6	6.6	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	9.2
62.5°	6.6	6.6	7.8	7.8	7.8	7.8	7.8	7.8	9.2	9.2	9.2
65°	6.6	6.6	7.8	7.8	7.8	7.8	7.8	9.2	9.2	9.2	9.2
67.5°	6.6	7.8	7.8	7.8	7.8	9.2	9.2	9.2	9.2	9.2	9.2
70°	6.6	7.8	7.8	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2
72.5°	6.6	7.8	7.8	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2
75°	7.8	7.8	7.8	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.5
77.5°	7.8	7.8	9.2	9.2	9.2	9.2	9.2	9.2	10.5	10.5	10.5
80°	7.8	7.8	9.2	9.2	9.2	9.2	9.2	10.5	10.5	10.5	10.5
82.5°	7.8	7.8	9.2	9.2	9.2	9.2	9.2	10.5	10.5	10.5	10.5
85°	7.8	7.8	9.2	9.2	9.2	9.2	9.2	10.5	10.5	10.5	10.5
87.5°	7.8	7.8	9.2	9.2	9.2	9.2	9.2	10.5	10.5	10.5	10.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192747

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3
2.5°	1714.4	1654.1	1625.4	1585.0	1556.2	1492.1	1465.9	1421.5	1384.9	1324.6	1328.6
5°	1565.3	1451.5	1374.4	1314.2	1272.3	1170.3	1102.3	1030.4	965.0	884.0	853.9
7.5°	1358.7	1218.8	1101.2	1029.2	975.5	839.6	689.1	571.4	482.6	418.4	393.6
10°	1152.1	970.2	783.3	672.3	595.1	464.2	397.5	366.1	337.4	302.1	278.6
12.5°	911.5	652.5	482.6	438.0	406.6	363.6	320.3	286.4	293.0	294.1	303.5
15°	622.4	469.5	415.9	385.8	351.7	326.9	341.2	350.4	367.4	368.8	380.6
17.5°	506.1	440.8	397.5	396.3	398.8	413.2	435.4	447.3	469.5	474.7	491.7
20°	506.1	468.1	504.7	504.7	511.3	530.9	559.7	576.7	601.4	610.8	631.6
22.5°	576.7	602.8	648.5	653.8	656.6	677.5	714.0	731.0	759.7	764.9	787.2
25°	703.5	727.1	769.0	772.8	774.2	789.9	817.2	826.4	846.1	835.6	848.6
27.5°	744.0	754.5	780.6	783.3	776.8	783.3	793.8	793.8	800.3	779.5	783.3
30°	653.8	656.6	669.6	670.9	656.6	659.0	660.4	659.0	657.7	635.5	635.5
32.5°	485.2	485.2	502.2	498.3	482.6	486.5	486.5	486.5	485.2	466.9	464.2
35°	321.7	323.0	337.4	334.9	323.0	325.5	325.5	329.6	325.5	315.1	312.5
37.5°	196.2	197.4	203.9	205.3	201.4	202.6	203.9	202.6	205.3	200.1	197.4
40°	113.8	116.4	121.6	122.9	121.6	121.6	122.9	124.3	129.5	122.9	120.2
42.5°	66.7	68.0	70.6	70.6	70.6	70.6	72.0	73.3	74.5	73.3	72.0
45°	38.0	39.2	40.6	40.6	41.9	40.6	41.9	41.9	43.3	41.9	41.9
47.5°	22.3	22.3	23.5	23.5	24.9	23.5	24.9	24.9	24.9	23.5	23.5
50°	13.0	14.4	14.4	14.4	14.4	14.4	14.4	14.4	14.4	13.0	13.0
52.5°	10.5	10.5	10.5	10.5	10.5	9.2	9.2	9.2	9.2	7.8	7.8
55°	9.2	9.2	9.2	9.2	9.2	9.2	7.8	6.6	6.6	5.2	5.2
57.5°	7.8	9.2	9.2	9.2	9.2	7.8	7.8	6.6	5.2	3.8	3.8
60°	9.2	9.2	9.2	9.2	7.8	7.8	7.8	6.6	5.2	3.8	3.8
62.5°	9.2	9.2	9.2	9.2	9.2	7.8	7.8	6.6	5.2	3.8	3.8
65°	9.2	9.2	9.2	9.2	9.2	7.8	7.8	6.6	5.2	3.8	3.8
67.5°	9.2	9.2	9.2	9.2	9.2	7.8	7.8	6.6	5.2	5.2	3.8
70°	9.2	10.5	10.5	9.2	9.2	9.2	7.8	6.6	6.6	5.2	3.8
72.5°	9.2	10.5	10.5	9.2	9.2	9.2	7.8	6.6	6.6	5.2	3.8
75°	10.5	10.5	10.5	10.5	9.2	9.2	7.8	7.8	6.6	5.2	3.8
77.5°	10.5	10.5	10.5	10.5	9.2	9.2	7.8	7.8	6.6	5.2	3.8
80°	10.5	10.5	10.5	10.5	10.5	9.2	9.2	7.8	6.6	5.2	5.2
82.5°	10.5	10.5	10.5	10.5	10.5	9.2	9.2	7.8	6.6	5.2	5.2
85°	10.5	10.5	10.5	10.5	10.5	9.2	9.2	7.8	6.6	5.2	3.8
87.5°	10.5	10.5	10.5	10.5	9.2	9.2	7.8	7.8	6.6	5.2	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192747

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3	1858.3
2.5°	1280.2	1250.1	1237.1	1258.0	1247.5	1216.2	1222.7	1203.1
5°	763.8	718.0	689.1	702.3	660.4	622.4	622.4	595.1
7.5°	368.8	354.4	346.5	349.2	340.1	328.2	321.7	321.7
10°	258.9	253.7	255.0	255.0	262.9	261.6	265.4	264.1
12.5°	307.3	309.8	311.2	316.5	323.0	323.0	326.9	324.4
15°	393.6	391.0	398.8	400.2	410.7	411.8	417.0	411.8
17.5°	500.9	506.1	513.9	512.6	533.6	534.8	534.8	533.6
20°	644.7	648.5	656.6	659.0	683.9	686.6	695.7	697.0
22.5°	801.5	801.5	805.5	810.7	834.3	835.6	839.6	839.6
25°	855.3	847.3	848.6	855.3	868.3	863.0	866.9	864.3
27.5°	785.8	774.2	771.5	780.6	789.9	775.4	780.6	780.6
30°	638.1	627.6	625.1	634.2	640.8	625.1	630.3	632.8
32.5°	466.9	460.3	459.0	465.5	470.8	457.6	462.8	466.9
35°	315.1	312.5	309.8	311.2	319.2	308.7	313.9	316.5
37.5°	200.1	194.9	196.2	198.7	203.9	197.4	202.6	202.6
40°	122.9	120.2	120.2	122.9	125.4	120.2	122.9	124.3
42.5°	72.0	72.0	72.0	73.3	74.5	72.0	72.0	73.3
45°	41.9	40.6	40.6	41.9	43.3	40.6	41.9	41.9
47.5°	23.5	22.3	22.3	23.5	23.5	22.3	23.5	23.5
50°	13.0	11.9	11.9	13.0	13.0	11.9	11.9	11.9
52.5°	6.6	6.6	6.6	6.6	6.6	6.6	5.2	5.2
55°	3.8	3.8	2.5	2.5	2.5	2.5	2.5	1.4
57.5°	2.5	2.5	1.4	1.4	1.4	1.4	0.0	0.0
60°	2.5	2.5	1.4	1.4	1.4	0.0	0.0	0.0
62.5°	2.5	2.5	1.4	1.4	1.4	0.0	0.0	0.0
65°	2.5	2.5	1.4	1.4	1.4	0.0	0.0	0.0
67.5°	2.5	2.5	1.4	1.4	1.4	0.0	0.0	0.0
70°	3.8	2.5	2.5	1.4	1.4	1.4	0.0	0.0
72.5°	3.8	2.5	2.5	2.5	1.4	1.4	0.0	0.0
75°	3.8	2.5	2.5	2.5	1.4	1.4	0.0	0.0
77.5°	3.8	2.5	2.5	2.5	1.4	1.4	1.4	0.0
80°	3.8	2.5	2.5	2.5	1.4	1.4	1.4	1.4
82.5°	3.8	2.5	2.5	2.5	1.4	1.4	1.4	1.4
85°	3.8	2.5	2.5	2.5	1.4	1.4	1.4	0.0
87.5°	3.8	2.5	2.5	2.5	1.4	1.4	1.4	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)