

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192752

Luminaire Tested: **LDA6A70950D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192752
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70950D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7191.6 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192752

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192752

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	71113	71113	71113
5°	182418	64693	20146
10°	355594	49721	9680
15°	638324	33774	12985
20°	947713	25634	21434
25°	1077226	21122	33613
30°	1167724	23098	31619
35°	1229999	14964	19608
40°	1256597	6648	9546
45°	1134963	2543	3551
50°	747106	1015	1015
55°	204590	879	0
60°	40852	1009	0
65°	2893	1362	0
70°	401	1683	0
75°	0	2521	0
80°	0	3757	442
85°	0	7485	881

TEST NUMBER: P1192752

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.9	2.2
10°-20°	844.2	11.7
20°-30°	1913.4	26.6
30°-40°	2296.7	31.9
40°-50°	1618.7	22.5
50°-60°	334.0	4.6
60°-70°	11.8	0.2
70°-80°	7.1	0.1
80°-90°	6.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2916.5	40.6
0°-40°	5213.2	72.5
0°-60°	7165.8	99.6
0°-90°	7191.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7191.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1297	1297	1297	1297	1297	
5°	3315	2415	1176	489	366	408
15°	11247	4948	595	212	229	3338
25°	17809	5985	349	489	556	8219
35°	18379	4191	224	293	293	11426
45°	14640	1437	33	44	46	10767
55°	2141	29	9	7	0	2821
65°	22	7	10	7	0	66
75°	0	7	12	8	0	0
85°	0	8	12	8	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192752

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2
2.5°	2211.2	2144.5	2170.7	2093.5	2076.7	2062.1	2076.7	1992.8	1945.7	1885.6	1837.4
5°	3314.9	3235.1	3253.4	3118.9	3057.4	3015.5	3007.6	2834.9	2705.7	2563.0	2415.2
7.5°	4614.8	4539.0	4528.5	4319.2	4192.4	4120.5	4090.4	3843.2	3619.6	3365.9	3088.8
10°	6388.0	6215.4	6161.7	5858.4	5616.4	5463.4	5275.2	4880.2	4487.9	4104.8	3751.7
12.5°	8451.5	8357.3	8223.9	7689.0	7265.3	7048.4	6767.2	6150.0	5556.3	4923.5	4332.2
15°	11247.2	10912.5	10685.0	9912.0	9229.5	8894.8	8484.1	7540.1	6642.9	5841.4	4948.2
17.5°	13979.1	13803.7	13448.1	12445.1	11393.7	10865.4	10253.5	8970.6	7703.5	6563.2	5472.6
20°	16245.1	16080.5	15675.0	14729.6	13563.2	12783.8	12013.5	10253.5	8598.0	7138.6	5823.1
22.5°	17330.6	17225.8	16895.0	16085.7	15091.8	14350.3	13522.6	11345.4	9259.5	7515.2	5982.5
25°	17809.1	17760.8	17547.5	16909.4	15973.3	15344.3	14562.3	12118.2	9671.6	7690.4	5985.2
27.5°	18294.2	18303.5	17832.7	17327.9	16440.0	15835.8	15082.7	12460.8	9746.0	7592.2	5789.1
30°	18447.2	18350.5	18142.6	17418.1	16574.7	15932.6	15124.5	12302.6	9440.1	7189.5	5398.1
32.5°	18384.5	18346.5	18117.7	17351.5	16345.9	15638.4	14720.5	11674.9	8835.9	6614.2	4843.6
35°	18379.3	18308.7	17784.2	17126.5	15888.2	15014.6	13805.1	10660.1	7980.6	5855.7	4191.1
37.5°	18047.1	17871.9	17478.2	16591.7	14959.8	13852.2	12496.1	9420.5	6934.5	5004.5	3543.8
40°	17559.4	17323.9	16806.2	15464.5	13351.3	12074.9	10751.6	8012.1	5827.0	4164.9	2855.9
42.5°	16540.6	16185.0	15452.6	13607.6	11208.1	10057.2	8956.3	6585.4	4752.1	3393.4	2179.8
45°	14639.5	14152.9	13163.0	11137.5	9054.2	8115.3	7230.1	5298.6	3804.0	2517.2	1437.2
47.5°	11766.5	11315.3	10414.2	8866.0	7100.7	6306.9	5600.7	3941.3	2578.7	1458.1	686.6
50°	8760.1	8373.0	7669.4	6161.7	4766.4	4142.6	3538.6	2238.7	1208.4	693.1	285.1
52.5°	5226.7	5034.5	4410.7	3416.9	2353.7	2028.2	1628.0	948.0	609.4	251.1	77.2
55°	2140.6	1975.8	1741.8	1397.9	1024.0	868.3	742.8	468.1	189.6	52.3	28.7
57.5°	967.7	931.1	825.2	648.5	470.8	395.0	266.8	89.0	41.9	26.2	17.1
60°	372.6	336.0	287.8	155.7	66.7	56.3	45.8	30.1	20.9	14.4	10.5
62.5°	53.7	51.0	45.8	36.6	28.7	26.2	22.3	15.7	11.9	9.2	7.8
65°	22.3	22.3	19.6	15.7	13.0	11.9	10.5	7.8	6.6	6.6	6.6
67.5°	9.2	9.2	7.8	6.6	5.2	5.2	5.2	3.8	5.2	5.2	6.6
70°	2.5	2.5	2.5	2.5	2.5	2.5	3.8	3.8	5.2	5.2	6.6
72.5°	0.0	0.0	1.4	1.4	2.5	2.5	2.5	3.8	5.2	6.6	6.6
75°	0.0	0.0	1.4	1.4	2.5	2.5	2.5	3.8	5.2	6.6	6.6
77.5°	0.0	0.0	1.4	1.4	2.5	2.5	3.8	3.8	5.2	6.6	6.6
80°	0.0	0.0	1.4	1.4	2.5	2.5	3.8	3.8	5.2	6.6	7.8
82.5°	0.0	0.0	1.4	1.4	2.5	2.5	3.8	3.8	5.2	6.6	7.8
85°	0.0	0.0	1.4	1.4	2.5	2.5	3.8	3.8	5.2	6.6	7.8
87.5°	0.0	0.0	1.4	1.4	2.5	2.5	3.8	3.8	5.2	6.6	7.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192752

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2
2.5°	1795.5	1711.7	1688.2	1615.0	1553.6	1523.5	1485.4	1400.6	1336.4	1251.4	1200.5
5°	2312.0	2153.8	2028.2	1875.2	1774.6	1709.1	1607.2	1451.5	1326.0	1175.6	1068.4
7.5°	2870.3	2581.4	2355.1	2102.8	1957.6	1843.8	1669.8	1446.3	1261.9	1061.8	895.8
10°	3409.1	2977.5	2621.8	2259.7	2068.7	1910.5	1671.2	1390.1	1145.6	893.2	718.0
12.5°	3883.8	3326.6	2825.9	2360.3	2123.6	1926.2	1626.8	1289.4	993.9	734.9	580.5
15°	4280.0	3597.4	2969.7	2398.3	2127.6	1892.3	1533.9	1145.6	825.2	595.1	486.5
17.5°	4580.8	3739.9	3014.1	2352.6	2051.8	1795.5	1391.4	963.7	669.6	504.7	409.3
20°	4736.4	3767.4	2950.2	2228.3	1911.8	1648.9	1204.3	782.0	567.5	439.4	342.6
22.5°	4755.9	3690.2	2797.2	2050.5	1735.2	1471.1	997.8	652.5	506.1	388.3	302.1
25°	4639.5	3522.9	2578.7	1849.0	1541.7	1267.1	812.0	584.6	460.3	349.2	347.9
27.5°	4391.2	3235.1	2317.2	1615.0	1307.7	1030.4	689.1	528.3	410.7	370.1	393.6
30°	4040.6	2866.3	1995.6	1319.4	1021.3	792.5	580.5	435.4	360.9	364.9	384.5
32.5°	3566.0	2408.7	1617.5	966.4	731.0	596.2	435.4	296.8	299.4	300.8	317.8
35°	2969.7	1931.4	1208.4	649.9	513.9	419.7	245.9	218.3	222.4	223.6	235.4
37.5°	2379.9	1484.3	802.9	432.7	323.0	221.0	153.0	146.4	149.1	147.8	160.9
40°	1822.8	1034.4	481.2	214.4	124.3	103.4	94.2	90.2	91.5	92.9	100.7
42.5°	1290.6	561.0	238.0	81.0	65.3	60.1	56.3	53.7	54.9	54.9	60.1
45°	655.2	265.4	81.0	44.4	40.6	36.6	33.9	32.8	32.8	32.8	35.3
47.5°	283.7	87.7	38.0	27.6	24.9	23.5	20.9	19.6	19.6	19.6	20.9
50°	89.0	35.3	23.5	18.2	15.7	14.4	13.0	13.0	13.0	11.9	13.0
52.5°	32.8	22.3	15.7	11.9	10.5	10.5	10.5	9.2	10.5	9.2	10.5
55°	19.6	14.4	10.5	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2
57.5°	13.0	10.5	9.2	9.2	7.8	7.8	9.2	9.2	9.2	9.2	9.2
60°	9.2	9.2	7.8	7.8	7.8	7.8	9.2	9.2	9.2	9.2	9.2
62.5°	7.8	7.8	7.8	7.8	7.8	7.8	9.2	9.2	9.2	9.2	10.5
65°	6.6	7.8	7.8	7.8	7.8	7.8	9.2	9.2	10.5	10.5	10.5
67.5°	6.6	7.8	7.8	9.2	9.2	9.2	9.2	10.5	10.5	10.5	10.5
70°	7.8	7.8	9.2	9.2	9.2	9.2	10.5	10.5	10.5	10.5	11.9
72.5°	7.8	7.8	9.2	9.2	9.2	9.2	10.5	10.5	11.9	11.9	11.9
75°	7.8	9.2	9.2	9.2	9.2	10.5	10.5	10.5	11.9	11.9	11.9
77.5°	7.8	9.2	9.2	10.5	10.5	10.5	10.5	11.9	11.9	11.9	11.9
80°	7.8	9.2	9.2	10.5	10.5	10.5	11.9	11.9	11.9	11.9	13.0
82.5°	7.8	9.2	9.2	10.5	10.5	10.5	11.9	11.9	11.9	11.9	13.0
85°	9.2	9.2	10.5	10.5	10.5	10.5	11.9	11.9	11.9	11.9	13.0
87.5°	9.2	9.2	10.5	10.5	10.5	10.5	11.9	11.9	13.0	11.9	13.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192752

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2
2.5°	1132.4	1056.5	1004.2	984.7	946.8	886.7	851.2	818.6	757.1	744.0	710.0
5°	945.5	823.9	737.6	704.8	661.8	610.8	561.0	528.3	489.0	473.3	449.8
7.5°	745.4	623.8	549.3	523.1	493.1	451.2	406.6	374.0	333.5	312.5	293.0
10°	585.7	495.6	432.7	406.6	375.3	330.8	285.1	242.0	206.6	184.4	180.5
12.5°	476.0	401.3	334.7	307.3	270.7	226.3	193.5	192.2	189.6	188.2	190.9
15°	389.7	317.8	247.2	217.2	206.6	205.3	209.2	213.1	212.0	215.8	218.3
17.5°	320.3	243.2	227.4	228.8	230.2	234.0	240.7	251.1	252.4	258.9	264.1
20°	261.6	257.7	264.1	269.4	273.4	281.1	295.5	308.7	312.5	321.7	332.2
22.5°	296.8	308.7	323.0	329.6	334.7	349.2	364.9	385.8	393.6	405.4	419.7
25°	358.3	377.9	400.2	408.0	415.9	439.4	457.6	482.6	489.0	503.4	517.9
27.5°	409.3	430.2	453.8	464.2	470.8	494.2	509.9	525.6	525.6	533.6	544.0
30°	401.3	418.4	438.0	446.0	448.4	465.5	481.2	486.5	483.8	487.9	495.6
32.5°	333.5	346.5	362.2	368.8	371.3	383.1	396.1	396.1	395.0	395.0	400.2
35°	247.2	256.4	264.1	270.7	274.6	282.5	294.1	293.0	293.0	290.3	294.1
37.5°	166.2	171.2	180.5	183.0	184.4	189.6	198.7	198.7	196.2	197.4	200.1
40°	100.7	107.2	112.4	113.8	116.4	120.2	126.8	126.8	126.8	126.8	128.1
42.5°	60.1	64.0	68.0	68.0	69.3	74.5	77.2	77.2	77.2	77.2	78.5
45°	35.3	36.6	39.2	40.6	40.6	43.3	44.4	44.4	44.4	44.4	45.8
47.5°	20.9	22.3	22.3	23.5	23.5	24.9	26.2	26.2	24.9	24.9	24.9
50°	13.0	13.0	13.0	13.0	14.4	14.4	14.4	14.4	14.4	14.4	13.0
52.5°	10.5	10.5	10.5	10.5	9.2	9.2	9.2	9.2	7.8	7.8	6.6
55°	9.2	9.2	9.2	9.2	9.2	7.8	7.8	7.8	6.6	5.2	3.8
57.5°	9.2	9.2	9.2	9.2	9.2	7.8	7.8	6.6	5.2	5.2	3.8
60°	9.2	9.2	9.2	9.2	9.2	7.8	7.8	6.6	5.2	5.2	3.8
62.5°	10.5	10.5	9.2	9.2	9.2	7.8	7.8	6.6	6.6	5.2	3.8
65°	10.5	10.5	9.2	9.2	9.2	9.2	7.8	7.8	6.6	5.2	3.8
67.5°	10.5	10.5	10.5	10.5	9.2	9.2	9.2	7.8	6.6	5.2	3.8
70°	11.9	11.9	10.5	10.5	10.5	9.2	9.2	7.8	6.6	6.6	5.2
72.5°	11.9	11.9	10.5	10.5	10.5	10.5	9.2	7.8	7.8	6.6	5.2
75°	11.9	11.9	11.9	11.9	10.5	10.5	9.2	9.2	7.8	6.6	5.2
77.5°	11.9	11.9	11.9	11.9	10.5	10.5	10.5	9.2	7.8	6.6	5.2
80°	11.9	11.9	11.9	11.9	11.9	10.5	10.5	9.2	7.8	6.6	5.2
82.5°	13.0	13.0	11.9	11.9	11.9	10.5	10.5	9.2	7.8	6.6	6.6
85°	13.0	13.0	11.9	11.9	11.9	10.5	10.5	9.2	7.8	7.8	6.6
87.5°	13.0	13.0	11.9	11.9	11.9	10.5	10.5	9.2	7.8	7.8	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192752

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2	1297.2
2.5°	689.1	649.9	636.8	646.0	635.5	627.6	617.1	611.9
5°	431.6	402.7	393.6	396.1	387.0	379.3	368.8	366.1
7.5°	265.4	238.0	227.4	227.4	217.2	207.9	201.4	197.4
10°	177.8	172.5	173.9	175.2	173.9	175.2	171.2	173.9
12.5°	190.9	188.2	190.9	192.2	192.2	194.9	189.6	193.5
15°	222.4	219.6	223.6	226.3	226.3	230.2	225.0	228.8
17.5°	272.1	270.7	277.3	279.8	281.1	287.8	281.1	286.4
20°	343.9	342.6	351.7	355.6	354.4	367.4	358.3	367.4
22.5°	436.8	434.1	447.2	451.2	452.4	469.5	461.7	468.1
25°	529.6	532.3	538.8	545.3	546.6	561.0	549.3	555.7
27.5°	549.3	545.3	549.3	557.0	558.4	564.8	554.5	559.6
30°	496.9	490.4	491.7	500.9	503.4	506.1	496.9	499.5
32.5°	404.0	393.6	393.6	402.7	405.4	409.3	393.6	400.2
35°	298.2	288.9	288.9	295.5	296.8	299.4	287.8	293.0
37.5°	203.9	196.2	198.7	201.4	202.6	205.3	203.9	202.6
40°	130.7	125.4	129.5	129.5	130.7	132.1	132.1	133.4
42.5°	79.7	75.8	78.5	78.5	79.7	79.7	79.7	81.0
45°	45.8	44.4	44.4	45.8	45.8	45.8	44.4	45.8
47.5°	24.9	23.5	24.9	24.9	24.9	24.9	24.9	24.9
50°	13.0	11.9	11.9	11.9	11.9	11.9	11.9	11.9
52.5°	6.6	5.2	5.2	5.2	3.8	5.2	3.8	3.8
55°	3.8	2.5	2.5	2.5	1.4	1.4	0.0	0.0
57.5°	2.5	1.4	1.4	1.4	0.0	0.0	0.0	0.0
60°	2.5	1.4	1.4	1.4	0.0	0.0	0.0	0.0
62.5°	2.5	1.4	1.4	1.4	0.0	0.0	0.0	0.0
65°	2.5	1.4	1.4	1.4	0.0	0.0	0.0	0.0
67.5°	3.8	2.5	1.4	1.4	1.4	0.0	0.0	0.0
70°	3.8	2.5	2.5	1.4	1.4	0.0	0.0	0.0
72.5°	3.8	2.5	2.5	2.5	1.4	1.4	0.0	0.0
75°	3.8	2.5	2.5	2.5	1.4	1.4	0.0	0.0
77.5°	3.8	3.8	2.5	2.5	1.4	1.4	1.4	0.0
80°	5.2	3.8	2.5	2.5	2.5	1.4	1.4	1.4
82.5°	5.2	3.8	2.5	2.5	2.5	1.4	1.4	1.4
85°	5.2	3.8	3.8	2.5	2.5	1.4	1.4	1.4
87.5°	5.2	3.8	3.8	2.5	2.5	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)