

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192227

Luminaire Tested: **LDA6A40940D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192227
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26674)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40940D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4096.6 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 2.68 / 0.47 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192227

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192227

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91		
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81		
3	98	89	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72		
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	78	67	59	54	77	66	59	54	65	58	53	63	57	53	61	57	53	51		
7	73	61	54	48	71	60	53	48	59	53	48	58	52	47	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	35386	35386	35386
5°	93253	32286	10412
10°	186208	24743	4136
15°	338997	17367	4518
20°	521265	12467	28516
25°	611322	18618	23602
30°	665602	11685	6874
35°	700537	4845	2851
40°	718332	2133	1617
45°	666821	1403	1194
50°	467720	1083	546
55°	171062	774	344
60°	36126	789	208
65°	3061	934	246
70°	1026	1154	433
75°	191	1525	763
80°	284	2273	1137
85°	0	4529	1195

TEST NUMBER: P1192227

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	2.0
10°-20°	446.6	10.9
20°-30°	1079.3	26.3
30°-40°	1268.8	31.0
40°-50°	958.5	23.4
50°-60°	240.5	5.9
60°-70°	11.6	0.3
70°-80°	5.6	0.1
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1607.1	39.2
0°-40°	2875.9	70.2
0°-60°	4074.9	99.5
0°-90°	4096.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4096.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	646	646	646	646	646	
5°	1695	1230	587	249	189	211
15°	5973	2591	306	82	80	1808
25°	10107	3224	308	427	390	4649
35°	10468	2375	72	52	43	6518
45°	8601	933	18	19	15	6338
55°	1790	26	8	7	4	1980
65°	24	6	7	6	2	64
75°	1	4	7	6	4	2
85°	0	4	7	6	2	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192227

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	645.5	645.5	645.5	645.5	645.5	645.5	645.5	645.5	645.5	645.5	645.5
2.5°	1126.2	1108.1	1095.4	1073.6	1062.8	1067.4	1044.7	1014.0	1004.9	977.8	930.6
5°	1694.6	1675.7	1645.8	1599.6	1565.2	1559.8	1515.4	1441.2	1394.2	1324.4	1230.3
7.5°	2392.7	2376.4	2326.6	2257.7	2199.8	2178.1	2112.9	1982.6	1878.5	1739.1	1577.0
10°	3345.1	3281.7	3188.4	3049.0	2915.9	2854.4	2739.4	2524.0	2354.6	2163.6	1943.7
12.5°	4539.1	4426.8	4275.7	4066.6	3837.5	3722.6	3539.7	3210.1	2914.1	2586.4	2266.0
15°	5973.1	5859.9	5640.9	5316.7	4948.3	4763.6	4493.9	3974.2	3533.3	3052.6	2590.9
17.5°	7665.1	7480.3	7188.9	6719.0	6148.7	5859.0	5477.0	4757.2	4100.0	3472.7	2875.2
20°	8935.2	8800.2	8524.1	8032.6	7352.7	6979.8	6466.5	5475.1	4626.9	3808.6	3090.7
22.5°	9714.6	9593.4	9339.8	8928.8	8304.2	7890.5	7312.0	6105.2	5036.1	4041.2	3198.4
25°	10106.6	10019.7	9843.2	9484.7	8938.8	8523.2	7938.4	6571.5	5313.1	4167.1	3223.7
27.5°	10451.5	10305.8	10018.8	9774.4	9290.9	8868.1	8314.2	6803.3	5410.0	4152.6	3159.5
30°	10514.9	10431.6	10205.3	9855.9	9405.9	8978.6	8394.7	6769.7	5300.5	3984.2	2984.7
32.5°	10460.5	10388.1	10217.0	9835.9	9332.6	8860.9	8220.0	6494.6	4979.1	3671.9	2689.6
35°	10467.8	10352.8	10053.2	9727.3	9099.1	8545.0	7792.7	5991.2	4529.2	3266.3	2375.4
37.5°	10329.3	10140.1	9893.0	9472.9	8624.6	7937.6	7077.5	5342.1	3987.8	2852.5	2008.8
40°	10037.8	9893.8	9565.3	8919.8	7816.2	6952.6	6157.8	4597.1	3396.6	2400.8	1637.7
42.5°	9561.7	9389.7	8930.7	7957.4	6645.7	5892.5	5177.3	3834.8	2815.4	1963.5	1285.5
45°	8601.1	8338.6	7738.3	6577.8	5458.9	4819.8	4236.7	3126.9	2282.2	1536.2	933.3
47.5°	7066.7	6843.1	6208.5	5239.8	4358.9	3864.6	3367.7	2465.9	1698.3	987.6	479.8
50°	5484.2	5307.7	4823.4	3973.3	3238.2	2758.4	2367.3	1574.3	905.2	454.5	215.5
52.5°	3608.5	3497.1	3081.6	2480.5	1859.4	1517.3	1232.0	683.5	421.9	201.9	74.3
55°	1789.8	1646.7	1448.5	1073.6	776.8	628.3	533.2	336.8	174.7	57.9	26.2
57.5°	729.6	698.0	628.3	485.2	373.0	315.1	251.7	105.0	38.9	23.6	16.3
60°	329.5	315.1	273.4	192.0	104.1	64.3	45.3	29.0	20.0	14.5	10.9
62.5°	57.9	53.4	47.1	36.2	29.0	25.3	21.7	16.3	12.7	10.0	8.1
65°	23.6	23.6	21.7	19.0	15.4	14.5	12.7	10.0	8.1	7.2	6.4
67.5°	12.7	11.7	11.7	10.0	9.1	8.1	7.2	6.4	6.4	5.5	5.5
70°	6.4	6.4	6.4	5.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
72.5°	3.6	3.6	3.6	3.6	3.6	3.6	2.7	2.7	2.7	3.6	3.6
75°	0.9	0.9	0.9	0.9	1.9	1.9	1.9	2.7	3.6	3.6	4.5
77.5°	0.9	0.9	0.9	0.9	1.9	1.9	1.9	2.7	3.6	3.6	4.5
80°	0.9	0.9	0.9	0.9	1.9	1.9	1.9	2.7	3.6	3.6	4.5
82.5°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.7	2.7	3.6	4.5
85°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.7	2.7	3.6	4.5
87.5°	0.0	0.0	0.9	0.9	0.9	1.9	1.9	2.7	2.7	3.6	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192227

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	645.5	645.5	645.5	645.5	645.5	645.5	645.5	645.5	645.5	645.5	645.5
2.5°	928.8	881.8	845.6	811.1	803.0	774.9	748.7	703.4	662.7	624.6	581.2
5°	1194.1	1101.7	1024.8	949.7	925.2	878.1	814.7	733.2	657.2	586.7	512.4
7.5°	1482.8	1326.3	1189.6	1062.8	1018.5	951.4	849.2	733.2	623.8	522.4	431.8
10°	1766.2	1532.6	1326.3	1143.4	1076.4	989.5	849.2	701.6	562.2	444.5	354.9
12.5°	2039.6	1719.1	1440.4	1198.6	1110.8	1002.1	826.5	646.4	484.3	368.5	293.3
15°	2253.2	1876.6	1520.9	1220.3	1110.8	985.0	774.0	569.4	405.6	306.0	239.0
17.5°	2413.5	1969.9	1548.1	1199.5	1072.8	931.6	694.4	478.9	334.0	253.5	189.2
20°	2506.8	1993.5	1520.0	1138.9	1000.4	850.9	595.7	394.7	283.4	213.7	153.0
22.5°	2528.5	1960.9	1454.8	1061.0	918.0	766.8	508.8	353.0	273.4	218.2	191.0
25°	2504.0	1894.7	1368.8	982.3	840.1	690.8	477.1	380.2	327.7	307.8	329.5
27.5°	2407.1	1771.7	1262.9	894.4	751.3	612.0	452.6	383.0	329.5	320.4	310.6
30°	2234.3	1586.0	1100.0	731.5	580.3	464.4	321.4	228.2	182.0	184.6	182.9
32.5°	1963.5	1316.3	860.9	511.5	399.2	314.2	212.7	134.9	126.7	126.7	124.9
35°	1665.7	1069.1	647.2	359.4	277.9	220.9	126.7	98.7	83.3	72.4	65.2
37.5°	1362.5	832.0	446.3	242.7	176.5	113.2	60.7	49.8	44.3	41.7	40.7
40°	1054.7	585.7	285.1	133.1	77.9	49.8	38.9	33.5	30.8	29.8	29.8
42.5°	780.4	377.5	153.9	52.5	41.7	34.4	28.1	24.5	23.6	23.6	22.6
45°	469.8	189.2	57.9	32.6	27.2	24.5	20.8	19.0	18.1	18.1	19.0
47.5°	217.3	70.6	31.7	21.7	20.0	18.1	16.3	15.4	15.4	15.4	16.3
50°	78.8	30.8	20.0	15.4	14.5	13.6	12.7	11.7	11.7	12.7	12.7
52.5°	29.8	19.0	14.5	11.7	10.9	10.9	10.0	10.0	10.0	10.0	10.0
55°	18.1	13.6	10.9	9.1	9.1	8.1	8.1	8.1	8.1	8.1	8.1
57.5°	11.7	10.0	8.1	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2
60°	9.1	7.2	6.4	6.4	6.4	6.4	6.4	7.2	7.2	7.2	7.2
62.5°	7.2	6.4	6.4	6.4	6.4	6.4	6.4	6.4	7.2	7.2	7.2
65°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	7.2	7.2	7.2	8.1
67.5°	5.5	5.5	5.5	5.5	5.5	6.4	6.4	6.4	7.2	7.2	7.2
70°	4.5	4.5	5.5	5.5	5.5	6.4	6.4	6.4	7.2	7.2	7.2
72.5°	4.5	5.5	5.5	5.5	5.5	6.4	6.4	6.4	7.2	7.2	7.2
75°	4.5	5.5	5.5	5.5	6.4	6.4	6.4	6.4	7.2	7.2	7.2
77.5°	4.5	5.5	5.5	5.5	6.4	6.4	6.4	7.2	7.2	7.2	8.1
80°	4.5	5.5	5.5	6.4	6.4	6.4	6.4	7.2	7.2	7.2	8.1
82.5°	4.5	5.5	5.5	6.4	6.4	6.4	7.2	7.2	7.2	8.1	8.1
85°	4.5	5.5	5.5	6.4	6.4	6.4	7.2	7.2	7.2	7.2	8.1
87.5°	4.5	5.5	5.5	6.4	6.4	6.4	6.4	7.2	7.2	7.2	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192227

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	645.5	645.5	645.5	645.5	645.5	645.5	645.5	645.5	645.5	645.5	645.5
2.5°	557.6	520.5	494.3	470.7	461.7	440.9	418.3	392.0	370.2	368.5	350.4
5°	462.6	411.0	373.9	350.4	338.5	316.8	290.6	273.4	248.9	241.7	223.6
7.5°	373.9	325.9	291.5	269.8	256.2	229.9	200.1	181.0	161.1	145.8	125.8
10°	304.2	258.0	220.9	199.2	185.6	157.5	126.7	105.0	86.9	83.3	81.5
12.5°	244.4	197.4	160.3	136.7	122.2	96.0	87.8	84.1	81.5	78.8	78.8
15°	190.1	142.2	102.3	93.2	90.5	87.8	86.0	84.1	82.4	81.5	82.4
17.5°	138.5	100.5	96.0	95.0	93.2	93.2	95.0	96.0	97.7	99.6	102.3
20°	122.2	123.1	133.1	140.3	137.6	151.2	170.1	185.6	222.7	245.3	276.1
22.5°	219.1	251.7	297.8	325.9	341.3	386.6	436.4	511.5	549.5	603.8	652.7
25°	374.7	412.8	452.6	463.5	471.6	476.2	469.8	435.4	427.3	411.9	407.4
27.5°	280.6	262.5	268.9	271.6	268.9	265.3	254.4	235.4	230.8	223.6	225.4
30°	165.6	160.3	167.5	166.5	166.5	166.5	162.9	147.5	140.3	132.2	126.7
32.5°	122.2	112.2	104.1	96.9	94.1	89.6	86.9	80.5	77.9	74.3	74.3
35°	60.7	57.9	57.9	56.2	55.2	56.2	56.2	53.4	51.6	50.7	50.7
37.5°	39.8	39.8	40.7	39.8	39.8	39.8	39.8	38.9	38.1	37.1	37.1
40°	29.8	29.8	30.8	30.8	29.8	29.8	29.8	29.0	29.0	29.0	29.0
42.5°	23.6	23.6	23.6	23.6	22.6	23.6	23.6	23.6	22.6	22.6	21.7
45°	20.0	19.0	19.0	19.0	19.0	19.0	20.0	19.0	19.0	18.1	18.1
47.5°	16.3	16.3	16.3	16.3	16.3	16.3	16.3	16.3	16.3	15.4	15.4
50°	12.7	12.7	12.7	12.7	12.7	11.7	11.7	10.9	10.9	10.0	10.0
52.5°	10.0	10.0	9.1	9.1	9.1	9.1	9.1	9.1	8.1	8.1	8.1
55°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	7.2	6.4	6.4
57.5°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.4	6.4	5.5
60°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.4	5.5	5.5	5.5
62.5°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.4	5.5	5.5	4.5
65°	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.4	6.4	5.5	5.5
67.5°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.4	6.4	5.5
70°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.4	6.4	5.5
72.5°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.4	6.4	5.5
75°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.4	6.4	5.5
77.5°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.4	6.4	5.5
80°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.4	6.4	5.5
82.5°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.4	6.4	5.5
85°	8.1	8.1	7.2	7.2	7.2	7.2	7.2	6.4	5.5	5.5	4.5
87.5°	7.2	7.2	7.2	7.2	7.2	6.4	6.4	5.5	4.5	4.5	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192227

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	645.5	645.5	645.5	645.5	645.5	645.5	645.5	645.5
2.5°	346.8	334.0	331.3	334.9	320.4	320.4	320.4	326.8
5°	216.3	203.7	200.1	201.0	189.2	181.0	185.6	189.2
7.5°	117.7	104.1	99.6	99.6	87.8	83.3	84.1	86.0
10°	78.8	76.9	76.9	76.0	74.3	73.3	74.3	74.3
12.5°	76.0	75.1	75.1	74.3	74.3	73.3	73.3	74.3
15°	79.6	79.6	79.6	78.8	78.8	77.9	79.6	79.6
17.5°	101.4	103.2	106.8	108.6	112.2	108.6	115.0	114.1
20°	297.8	327.7	383.0	403.8	463.5	434.5	497.0	488.8
22.5°	674.4	696.2	705.3	709.8	710.6	739.6	744.1	754.1
25°	398.3	392.9	388.3	388.3	372.1	391.1	387.5	390.2
27.5°	212.7	211.0	206.5	208.2	200.1	206.5	208.2	208.2
30°	120.4	116.8	113.2	113.2	106.0	109.6	108.6	108.6
32.5°	69.7	67.9	66.0	65.2	63.4	63.4	62.4	62.4
35°	47.9	47.1	46.2	45.3	43.4	42.6	42.6	42.6
37.5°	35.3	34.4	33.5	33.5	32.6	30.8	30.8	30.8
40°	27.2	26.2	25.3	25.3	24.5	22.6	22.6	22.6
42.5°	20.8	20.0	19.0	18.1	18.1	17.2	16.3	16.3
45°	17.2	17.2	16.3	16.3	15.4	15.4	15.4	15.4
47.5°	14.5	14.5	13.6	13.6	13.6	12.7	12.7	11.7
50°	9.1	8.1	8.1	7.2	7.2	6.4	6.4	6.4
52.5°	7.2	6.4	6.4	5.5	5.5	4.5	4.5	4.5
55°	5.5	5.5	4.5	4.5	4.5	3.6	3.6	3.6
57.5°	4.5	4.5	3.6	3.6	3.6	2.7	2.7	2.7
60°	4.5	3.6	3.6	2.7	2.7	2.7	1.9	1.9
62.5°	4.5	3.6	3.6	2.7	2.7	1.9	1.9	1.9
65°	4.5	3.6	3.6	2.7	2.7	2.7	2.7	1.9
67.5°	4.5	4.5	3.6	3.6	3.6	2.7	2.7	2.7
70°	5.5	4.5	4.5	3.6	3.6	3.6	3.6	2.7
72.5°	5.5	4.5	4.5	4.5	3.6	3.6	3.6	3.6
75°	5.5	4.5	4.5	4.5	3.6	3.6	3.6	3.6
77.5°	5.5	4.5	4.5	4.5	3.6	3.6	3.6	3.6
80°	5.5	4.5	4.5	4.5	3.6	3.6	3.6	3.6
82.5°	4.5	4.5	4.5	3.6	3.6	3.6	3.6	3.6
85°	3.6	3.6	3.6	2.7	2.7	2.7	2.7	1.9
87.5°	2.7	2.7	1.9	1.9	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)