

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192242

Luminaire Tested: **LDA6A40950D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192242
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26671)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40950D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4583.5 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 2.69 / 0.5 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192242

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



TEST NUMBER: P1192242

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	89	102	97	92	88	94	90	86		91	87	85		88
3	98	89	83	78	95	88	82	78	85	80	76		83	79	75		80
4	91	81	74	69	89	80	73	68	78	72	68		75	71	67		73
5	84	74	66	61	82	73	66	61	71	65	60		69	64	59		67
6	78	67	60	54	77	66	59	54	65	58	53		63	57	53		62
7	73	61	54	48	71	60	53	48	59	53	48		58	52	48		56
8	68	56	48	43	66	55	48	43	54	48	43		53	47	43		52
9	63	51	44	39	62	51	44	39	50	43	39		49	43	39		48
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	38506	38506	38506
5°	101502	35076	12073
10°	205095	27304	7337
15°	377653	20471	10585
20°	585502	16370	17630
25°	687439	14517	22380
30°	745399	14604	17338
35°	785971	8700	9329
40°	806168	3707	4043
45°	755241	1458	1388
50°	528068	640	316
55°	185303	640	0
60°	37365	735	0
65°	2322	869	0
70°	449	1202	0
75°	0	1589	0
80°	0	2368	284
85°	0	5284	566

TEST NUMBER: P1192242

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	2.0
10°-20°	502.5	11.0
20°-30°	1187.9	25.9
30°-40°	1447.1	31.6
40°-50°	1076.4	23.5
50°-60°	260.6	5.7
60°-70°	9.7	0.2
70°-80°	4.7	0.1
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1780.4	38.8
0°-40°	3227.5	70.4
0°-60°	4564.6	99.6
0°-90°	4583.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4583.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	702	702	702	702	702	
5°	1844	1380	637	298	219	231
15°	6654	2884	361	166	186	2005
25°	11365	3617	240	348	370	5219
35°	11744	2641	130	141	139	7315
45°	9742	1007	19	21	18	7155
55°	1939	22	7	5	0	2193
65°	18	5	7	5	0	60
75°	0	5	8	6	0	0
85°	0	5	8	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192242

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4
2.5°	1224.9	1204.3	1202.3	1181.8	1174.2	1171.4	1142.1	1131.7	1093.1	1085.7	1031.0
5°	1844.5	1812.6	1806.0	1759.0	1724.0	1676.0	1650.6	1607.3	1515.9	1468.0	1379.5
7.5°	2624.1	2581.8	2572.4	2499.0	2426.4	2363.4	2310.6	2209.9	2042.2	1927.4	1746.6
10°	3684.4	3565.8	3522.5	3367.1	3217.3	3099.7	3038.6	2817.2	2565.0	2410.4	2158.2
12.5°	5030.9	4833.2	4752.2	4512.1	4248.4	4055.4	3936.7	3589.4	3178.8	2883.2	2522.5
15°	6654.2	6424.4	6279.4	5977.2	5498.0	5223.0	5013.0	4456.6	3857.7	3410.4	2884.0
17.5°	8421.6	8241.7	8025.2	7551.4	6779.3	6448.9	6067.7	5337.9	4516.8	3894.4	3207.0
20°	10036.3	9735.1	9572.2	9044.9	8150.4	7714.4	7244.5	6151.4	5099.6	4289.0	3454.7
22.5°	10911.2	10619.2	10521.3	10063.7	9243.5	8758.7	8160.8	6868.0	5546.8	4559.2	3586.4
25°	11365.0	11098.5	11105.1	10691.7	9951.7	9495.9	8887.5	7409.3	5852.0	4701.3	3616.7
27.5°	11720.0	11392.3	11334.9	11026.0	10367.8	9901.7	9315.1	7704.0	5964.0	4686.2	3534.8
30°	11775.5	11507.2	11548.6	11119.3	10518.5	10033.6	9423.3	7688.1	5849.2	4497.1	3322.0
32.5°	11737.9	11471.3	11566.5	11100.4	10453.5	9921.5	9242.7	7375.5	5512.1	4146.8	3009.3
35°	11744.4	11438.3	11367.7	10973.2	10203.0	9578.8	8759.6	6804.8	5013.9	3691.0	2641.2
37.5°	11604.1	11191.6	11203.9	10684.1	9719.0	8891.5	7963.9	6044.1	4424.5	3204.2	2271.2
40°	11265.2	10956.3	10858.4	10086.3	8798.2	7828.4	6933.9	5217.4	3742.8	2695.8	1837.0
42.5°	10782.1	10410.2	10123.0	9053.4	7493.2	6603.4	5830.3	4355.8	3098.8	2209.9	1426.5
45°	9741.6	9339.6	8783.2	7499.6	6178.6	5406.5	4761.5	3535.7	2506.5	1708.1	1006.6
47.5°	7992.1	7614.6	7042.2	5964.0	4932.9	4289.9	3787.1	2769.2	1832.3	1077.2	499.1
50°	6191.8	5904.7	5467.8	4531.9	3670.3	3068.6	2620.4	1739.1	935.1	491.5	209.0
52.5°	4035.6	3832.2	3443.3	2731.6	2074.3	1626.1	1321.9	740.1	440.6	207.2	61.2
55°	1938.8	1833.2	1551.8	1125.3	814.4	668.5	564.9	358.7	166.7	49.8	21.6
57.5°	773.0	750.5	668.5	503.8	386.2	327.7	254.2	98.8	33.0	20.8	13.2
60°	340.8	330.5	276.8	183.6	98.8	56.5	41.4	24.5	16.0	12.2	8.4
62.5°	49.0	45.1	38.6	30.2	24.5	20.8	17.9	13.2	8.4	6.7	5.7
65°	17.9	17.9	16.0	13.2	11.3	10.4	9.5	6.7	4.7	4.7	4.7
67.5°	7.5	7.5	7.5	5.7	5.7	4.7	3.7	3.7	3.7	3.7	4.7
70°	2.8	2.8	2.8	2.0	2.0	2.0	2.8	2.8	2.8	3.7	4.7
72.5°	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.8	2.8	3.7	4.7
75°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	2.8	3.7	4.7
77.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	4.7
80°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	4.7
82.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	3.7	4.7	4.7
85°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	4.7
87.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	3.7	4.7	4.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192242

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4
2.5°	984.9	971.7	927.5	883.3	876.6	857.8	819.2	774.0	715.6	678.9	642.1
5°	1264.5	1198.6	1124.2	1038.5	1012.1	974.5	893.6	806.9	709.9	637.4	569.7
7.5°	1591.3	1444.4	1304.2	1166.7	1114.9	1056.4	933.1	808.8	676.0	570.6	485.8
10°	1897.4	1671.3	1453.8	1258.8	1181.8	1102.6	936.8	776.8	612.0	490.5	403.9
12.5°	2202.3	1878.6	1580.9	1325.7	1221.2	1119.6	916.2	719.4	533.0	417.1	347.5
15°	2442.5	2065.9	1673.3	1359.6	1229.8	1105.4	865.3	640.3	455.7	360.7	298.5
17.5°	2609.0	2173.2	1708.1	1345.6	1196.7	1056.4	785.3	548.0	393.6	316.4	256.2
20°	2724.0	2207.1	1683.6	1287.1	1126.1	971.7	684.6	465.2	349.3	280.6	220.4
22.5°	2756.0	2174.1	1613.9	1199.6	1033.9	874.6	580.0	410.5	317.3	252.4	213.7
25°	2724.9	2090.3	1509.4	1095.1	920.9	754.2	492.4	377.5	292.8	240.0	248.7
27.5°	2612.0	1942.5	1364.4	960.3	781.5	624.2	433.2	338.1	258.0	253.3	263.6
30°	2425.5	1730.7	1192.0	788.1	617.8	498.2	363.4	266.4	226.0	230.7	237.3
32.5°	2157.2	1470.8	970.7	583.9	452.8	374.7	259.9	184.5	178.9	182.6	187.3
35°	1818.1	1196.7	727.0	403.0	321.0	258.0	152.6	130.8	128.0	130.0	131.8
37.5°	1475.6	924.7	494.4	271.2	194.9	130.8	91.3	85.7	83.7	84.8	85.7
40°	1144.9	643.0	310.6	130.0	76.2	64.9	56.5	53.7	51.8	51.8	52.7
42.5°	836.2	381.4	154.3	50.9	41.4	38.6	33.9	32.0	30.2	31.0	32.0
45°	467.9	169.4	52.7	28.3	25.5	23.5	20.8	19.8	18.8	18.8	18.8
47.5°	199.7	59.3	25.5	17.9	16.0	15.1	13.2	12.2	11.3	11.3	11.3
50°	65.9	23.5	16.0	12.2	10.4	9.5	8.4	7.5	7.5	7.5	8.4
52.5°	23.5	15.1	10.4	8.4	7.5	7.5	6.7	6.7	6.7	6.7	6.7
55°	14.1	10.4	7.5	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
57.5°	9.5	6.7	6.7	5.7	5.7	5.7	5.7	5.7	5.7	6.7	6.7
60°	6.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	6.7	6.7
62.5°	5.7	4.7	4.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7	6.7
65°	4.7	4.7	4.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7	6.7
67.5°	4.7	4.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7	6.7	7.5
70°	4.7	4.7	5.7	5.7	5.7	6.7	6.7	6.7	6.7	7.5	7.5
72.5°	4.7	5.7	5.7	5.7	6.7	6.7	6.7	7.5	7.5	7.5	7.5
75°	4.7	5.7	5.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5	7.5
77.5°	4.7	5.7	5.7	6.7	6.7	6.7	7.5	7.5	7.5	7.5	7.5
80°	5.7	5.7	6.7	6.7	6.7	7.5	7.5	7.5	7.5	7.5	8.4
82.5°	5.7	5.7	6.7	6.7	6.7	7.5	7.5	7.5	7.5	7.5	8.4
85°	5.7	5.7	6.7	6.7	6.7	7.5	7.5	7.5	7.5	8.4	8.4
87.5°	5.7	5.7	6.7	6.7	6.7	7.5	7.5	7.5	7.5	8.4	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192242

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4
2.5°	604.4	576.2	536.7	523.5	496.2	476.4	454.8	430.2	425.6	401.1	398.3
5°	503.8	458.5	413.4	396.3	372.8	353.1	331.4	307.9	297.5	273.9	259.9
7.5°	415.2	372.0	331.4	314.5	291.8	266.4	241.1	216.5	202.4	179.8	168.5
10°	348.3	305.1	261.8	244.8	224.1	195.9	168.5	143.1	133.7	128.0	129.1
12.5°	291.0	247.6	204.4	185.5	163.8	141.2	140.3	138.4	142.2	141.2	142.2
15°	243.9	197.7	156.3	150.6	150.6	154.3	158.2	159.1	165.7	165.7	167.6
17.5°	200.6	168.5	170.5	170.5	174.2	180.8	188.2	192.0	202.4	203.4	207.2
20°	186.5	194.0	202.4	204.4	210.9	221.2	231.6	239.2	252.4	256.2	263.6
22.5°	221.2	234.5	247.6	251.4	259.9	275.0	293.8	300.5	316.4	316.4	326.8
25°	260.8	280.6	293.8	298.5	307.9	321.0	333.3	337.1	348.3	344.6	348.3
27.5°	276.8	291.0	299.4	304.2	306.0	317.3	323.0	321.0	328.6	323.0	323.0
30°	245.8	256.2	260.8	263.6	263.6	272.2	272.2	269.3	273.9	269.3	266.4
32.5°	193.0	200.6	204.4	204.4	203.4	209.0	207.2	203.4	205.3	202.4	195.9
35°	134.7	140.3	143.1	142.2	141.2	145.9	143.1	140.3	141.2	139.4	134.7
37.5°	88.5	89.4	91.3	93.2	92.4	96.1	94.1	92.4	93.2	91.3	88.5
40°	53.7	55.5	57.4	57.4	57.4	58.4	58.4	57.4	59.3	57.4	55.5
42.5°	32.0	33.9	33.9	33.9	34.8	34.8	35.8	33.9	35.8	33.9	33.0
45°	19.8	19.8	19.8	20.8	19.8	20.8	20.8	19.8	20.8	19.8	18.8
47.5°	12.2	12.2	12.2	12.2	12.2	12.2	12.2	11.3	12.2	11.3	10.4
50°	7.5	8.4	7.5	7.5	7.5	7.5	7.5	6.7	6.7	5.7	5.7
52.5°	6.7	6.7	6.7	6.7	6.7	6.7	5.7	5.7	4.7	3.7	3.7
55°	6.7	6.7	6.7	5.7	5.7	5.7	5.7	4.7	4.7	3.7	2.8
57.5°	6.7	6.7	5.7	5.7	5.7	5.7	4.7	4.7	3.7	2.8	2.8
60°	6.7	6.7	6.7	5.7	5.7	5.7	4.7	4.7	3.7	2.8	2.8
62.5°	6.7	6.7	6.7	5.7	5.7	5.7	5.7	4.7	3.7	2.8	2.8
65°	6.7	6.7	6.7	6.7	6.7	5.7	5.7	4.7	4.7	3.7	2.8
67.5°	7.5	6.7	6.7	6.7	6.7	6.7	5.7	4.7	4.7	3.7	2.8
70°	7.5	7.5	6.7	6.7	6.7	6.7	5.7	5.7	4.7	3.7	2.8
72.5°	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.7	4.7	3.7	3.7
75°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	5.7	5.7	4.7	3.7
77.5°	8.4	7.5	7.5	7.5	7.5	7.5	6.7	5.7	5.7	4.7	3.7
80°	8.4	8.4	7.5	7.5	7.5	7.5	6.7	5.7	5.7	4.7	3.7
82.5°	8.4	8.4	7.5	7.5	7.5	7.5	6.7	6.7	5.7	4.7	3.7
85°	8.4	8.4	7.5	7.5	7.5	7.5	6.7	5.7	5.7	4.7	3.7
87.5°	8.4	8.4	7.5	7.5	7.5	7.5	6.7	5.7	5.7	4.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192242

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4
2.5°	381.4	379.5	372.8	374.7	370.0	359.6	360.7	356.9
5°	250.4	244.8	238.3	238.3	231.6	222.2	222.2	219.4
7.5°	152.6	144.1	137.5	136.6	130.0	125.3	125.3	124.3
10°	129.1	130.0	130.0	130.8	130.0	130.0	130.8	131.8
12.5°	145.0	147.9	147.9	148.8	147.9	149.7	149.7	151.6
15°	173.2	177.9	178.9	180.8	179.8	182.6	184.5	186.5
17.5°	217.5	223.2	225.1	230.7	229.8	232.5	234.5	238.3
20°	273.9	282.5	285.3	292.8	291.8	294.7	299.4	302.2
22.5°	337.1	347.5	348.3	355.0	354.0	356.9	358.7	359.6
25°	354.0	360.7	359.6	363.4	363.4	364.4	364.4	370.0
27.5°	324.0	328.6	328.6	328.6	329.5	330.5	330.5	335.2
30°	266.4	268.3	269.3	266.4	268.3	269.3	269.3	273.9
32.5°	197.7	198.6	199.7	195.9	198.6	198.6	198.6	202.4
35°	136.6	136.6	137.5	134.7	136.6	137.5	136.6	139.4
37.5°	89.4	89.4	89.4	89.4	89.4	89.4	88.5	91.3
40°	55.5	56.5	55.5	55.5	54.6	54.6	54.6	56.5
42.5°	33.0	33.0	32.0	32.0	32.0	32.0	33.0	33.0
45°	18.8	18.8	17.9	17.9	17.0	17.9	17.9	17.9
47.5°	10.4	9.5	9.5	9.5	8.4	8.4	8.4	9.5
50°	4.7	4.7	4.7	3.7	3.7	3.7	2.8	3.7
52.5°	2.8	2.0	2.0	2.0	0.9	0.9	0.0	0.9
55°	2.0	2.0	0.9	0.9	0.0	0.0	0.0	0.0
57.5°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
60°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
62.5°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
65°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
67.5°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
70°	2.8	2.0	2.0	0.9	0.9	0.0	0.0	0.0
72.5°	2.8	2.0	2.0	2.0	0.9	0.9	0.0	0.0
75°	2.8	2.0	2.0	2.0	0.9	0.9	0.0	0.0
77.5°	2.8	2.8	2.0	2.0	0.9	0.9	0.9	0.9
80°	2.8	2.8	2.0	2.0	2.0	0.9	0.9	0.9
82.5°	2.8	2.8	2.0	2.0	2.0	0.9	0.9	0.9
85°	2.8	2.8	2.0	2.0	2.0	0.9	0.9	0.9
87.5°	2.8	2.8	2.0	2.0	2.0	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)