

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192763

Luminaire Tested: **LDA6A70950D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192763
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26685)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70950D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5703.6 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 2.12 / 1.05 / 1.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192763

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192763

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	76	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55		
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44		
8	67	55	47	42	65	54	47	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	43	38	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	100935	100935	100935
5°	162205	98949	63113
10°	239853	94777	42367
15°	326852	89654	31470
20°	404250	84602	29828
25°	468342	83297	48965
30°	510984	79797	49008
35°	525172	68958	38327
40°	511422	54280	29842
45°	463723	40151	23530
50°	365361	29671	15940
55°	217846	21122	9118
60°	111406	14045	3443
65°	53274	7472	1544
70°	25132	3350	1475
75°	10273	2224	1652
80°	4956	2462	1642
85°	2390	4151	2390



TEST NUMBER: P1192763

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	3.3
10°-20°	667.8	11.7
20°-30°	1256.9	22.0
30°-40°	1530.6	26.8
40°-50°	1274.1	22.3
50°-60°	610.2	10.7
60°-70°	146.6	2.6
70°-80°	23.1	0.4
80°-90°	5.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2113.7	37.1
0°-40°	3644.3	63.9
0°-60°	5528.5	96.9
0°-90°	5703.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5703.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1841	1841	1841	1841	1841	
5°	2948	2500	1798	1308	1147	323
15°	5759	3913	1580	717	554	1651
25°	7743	4573	1377	781	810	3556
35°	7847	4016	1030	600	573	4862
45°	5981	2685	518	319	304	4529
55°	2279	1108	221	124	95	2147
65°	411	239	58	18	12	470
75°	48	25	10	9	8	66
85°	4	4	7	5	4	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192763

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2
2.5°	2381.3	2297.7	2323.8	2318.6	2313.4	2285.8	2266.3	2249.2	2206.2	2206.2	2151.1
5°	2947.6	2849.5	2874.4	2855.9	2832.4	2790.5	2752.8	2709.5	2629.8	2595.7	2500.3
7.5°	3594.9	3483.7	3505.8	3469.3	3419.5	3363.4	3301.9	3220.8	3094.0	3016.8	2869.0
10°	4308.8	4150.5	4163.7	4108.8	4026.5	3950.4	3891.7	3737.3	3556.8	3428.7	3222.1
12.5°	4984.9	4846.3	4850.2	4773.1	4654.1	4561.2	4472.2	4268.3	4027.6	3844.6	3572.5
15°	5759.1	5589.1	5548.5	5443.9	5288.3	5174.5	5052.9	4795.2	4493.2	4251.3	3912.6
17.5°	6382.9	6207.6	6181.4	6083.3	5861.1	5723.8	5570.9	5280.4	4897.3	4596.5	4180.6
20°	6929.4	6755.5	6711.1	6584.1	6329.1	6172.3	5987.9	5645.3	5226.8	4856.7	4387.2
22.5°	7376.6	7185.8	7123.0	6966.1	6682.2	6505.8	6280.9	5906.9	5439.9	5026.7	4510.3
25°	7742.8	7525.8	7446.0	7268.1	6949.1	6754.2	6507.0	6088.6	5579.9	5123.6	4573.0
27.5°	7976.9	7759.9	7672.3	7468.2	7110.0	6900.7	6631.2	6178.8	5629.6	5136.7	4559.9
30°	8072.3	7847.4	7748.1	7516.6	7130.9	6909.9	6628.8	6139.5	5565.6	5042.4	4450.1
32.5°	8013.5	7792.5	7681.3	7430.3	7028.7	6790.8	6509.7	5987.9	5396.9	4855.3	4259.1
35°	7847.4	7629.0	7514.0	7245.9	6827.5	6578.9	6299.1	5759.1	5161.5	4608.3	4016.0
37.5°	7561.0	7354.5	7222.4	6957.0	6535.9	6282.0	6005.0	5459.6	4848.9	4328.5	3734.8
40°	7146.5	6950.4	6819.6	6535.9	6138.4	5882.0	5620.5	5067.3	4492.0	3984.6	3411.8
42.5°	6618.2	6437.7	6312.3	6036.4	5657.1	5404.7	5165.4	4634.4	4086.6	3603.9	3062.6
45°	5981.4	5824.4	5701.5	5472.7	5098.7	4859.4	4643.6	4162.4	3630.1	3186.9	2684.7
47.5°	5232.1	5102.6	4983.6	4775.7	4438.3	4212.0	4034.2	3593.5	3142.3	2725.2	2297.7
50°	4284.0	4191.1	4098.3	3882.5	3644.5	3447.1	3317.6	2925.3	2560.4	2233.5	1879.2
52.5°	3229.9	3173.7	3108.4	2954.0	2794.6	2679.5	2564.4	2266.3	1992.8	1749.7	1473.8
55°	2279.3	2250.6	2199.6	2136.8	2015.2	1936.7	1837.4	1685.5	1473.8	1310.3	1107.6
57.5°	1540.4	1532.5	1497.3	1459.4	1392.8	1366.6	1282.8	1184.8	1065.8	944.1	800.3
60°	1016.1	999.1	991.2	970.2	919.3	898.4	868.3	805.5	732.4	647.3	558.4
62.5°	653.8	644.7	638.1	629.0	597.6	597.6	567.5	538.8	483.8	431.6	374.0
65°	410.7	402.7	401.3	395.0	383.1	377.9	355.6	334.9	308.7	279.8	239.3
67.5°	264.1	252.4	245.9	242.0	234.0	225.0	217.2	207.9	186.9	170.0	143.8
70°	156.8	146.4	145.2	146.4	137.3	135.9	128.1	121.6	107.2	96.7	81.0
72.5°	89.0	83.7	82.4	82.4	77.2	75.8	70.6	66.7	58.8	51.0	44.4
75°	48.5	44.4	44.4	44.4	41.9	40.6	38.0	36.6	31.4	28.7	24.9
77.5°	27.6	26.2	26.2	24.9	23.5	22.3	20.9	20.9	18.2	17.1	15.7
80°	15.7	15.7	15.7	15.7	14.4	14.4	13.0	13.0	11.9	11.9	10.5
82.5°	9.2	9.2	9.2	9.2	9.2	9.2	7.8	7.8	7.8	7.8	6.6
85°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
87.5°	0.0	0.0	1.4	1.4	1.4	1.4	1.4	2.5	2.5	2.5	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192763

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2
2.5°	2126.3	2087.1	2084.4	2027.0	1990.4	1960.3	1938.0	1910.5	1849.0	1815.1	1790.3
5°	2433.6	2352.6	2310.7	2206.2	2148.5	2097.6	2034.8	1969.4	1868.8	1798.1	1740.5
7.5°	2752.8	2618.0	2529.0	2373.5	2295.0	2215.3	2109.3	2003.4	1866.1	1760.2	1672.5
10°	3049.6	2858.6	2717.4	2508.3	2406.0	2301.5	2152.5	2009.9	1838.5	1702.6	1587.6
12.5°	3341.2	3090.2	2895.3	2629.8	2505.6	2376.0	2185.2	2006.1	1804.6	1641.1	1506.4
15°	3619.6	3304.6	3056.0	2735.7	2590.4	2435.0	2206.2	1994.2	1765.4	1579.7	1426.7
17.5°	3842.1	3468.0	3169.8	2801.0	2637.5	2461.2	2198.2	1960.3	1711.7	1514.3	1347.0
20°	3995.1	3572.5	3232.6	2827.2	2648.0	2458.5	2168.2	1913.2	1655.5	1450.2	1280.2
22.5°	4077.4	3619.6	3249.7	2819.4	2632.3	2433.6	2131.5	1869.9	1611.1	1405.8	1243.6
25°	4107.5	3623.6	3231.3	2785.3	2597.1	2394.4	2088.4	1829.5	1575.8	1377.1	1225.2
27.5°	4072.2	3568.7	3164.6	2714.7	2523.8	2323.8	2019.1	1771.8	1523.5	1335.2	1192.7
30°	3951.8	3440.5	3033.9	2589.3	2402.2	2210.0	1909.2	1666.0	1438.5	1260.6	1124.6
32.5°	3761.0	3252.2	2849.5	2416.5	2236.2	2051.8	1764.0	1532.5	1320.8	1153.4	1031.8
35°	3524.2	3027.3	2635.0	2215.3	2045.3	1871.3	1598.1	1379.6	1180.8	1030.4	911.5
37.5°	3256.1	2777.5	2398.3	2012.5	1839.9	1676.5	1411.0	1224.1	1033.0	895.8	787.2
40°	2955.4	2491.2	2145.8	1770.6	1618.9	1469.9	1224.1	1054.0	880.0	758.5	664.2
42.5°	2633.7	2200.8	1881.8	1544.4	1392.8	1256.6	1035.6	882.6	728.4	627.6	553.2
45°	2292.5	1910.5	1604.5	1302.4	1165.1	1047.4	846.1	707.5	595.1	517.9	461.7
47.5°	1935.4	1598.1	1326.0	1063.1	941.5	839.6	677.5	571.4	482.6	426.4	383.1
50°	1575.8	1275.0	1059.2	835.6	731.0	649.9	529.6	456.5	391.0	347.9	315.1
52.5°	1231.8	985.9	810.7	630.3	550.5	494.2	413.2	362.2	312.5	279.8	255.0
55°	910.1	742.8	592.4	457.6	410.7	375.3	317.8	281.1	245.9	221.0	202.6
57.5°	657.7	532.3	422.3	336.0	304.6	281.1	239.3	214.4	189.6	171.2	156.8
60°	461.7	367.4	298.2	245.9	223.6	207.9	177.8	162.1	143.8	128.1	113.8
62.5°	303.5	247.2	207.9	173.9	160.9	149.1	128.1	116.4	100.7	90.2	77.2
65°	197.4	162.1	138.6	116.4	105.9	100.7	86.3	77.2	66.7	57.6	49.6
67.5°	120.2	100.7	87.7	73.3	68.0	62.8	53.7	47.1	40.6	33.9	30.1
70°	66.7	58.8	51.0	43.3	39.2	36.6	31.4	28.7	23.5	20.9	17.1
72.5°	39.2	33.9	30.1	24.9	23.5	22.3	18.2	17.1	14.4	13.0	11.9
75°	23.5	19.6	18.2	15.7	14.4	14.4	13.0	11.9	10.5	10.5	9.2
77.5°	14.4	13.0	11.9	10.5	10.5	10.5	9.2	9.2	9.2	7.8	7.8
80°	9.2	9.2	9.2	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8
82.5°	6.6	6.6	6.6	5.2	6.6	5.2	6.6	6.6	6.6	6.6	6.6
85°	3.8	3.8	5.2	5.2	5.2	5.2	5.2	6.6	6.6	6.6	6.6
87.5°	3.8	3.8	5.2	5.2	5.2	5.2	5.2	6.6	6.6	6.6	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192763

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2
2.5°	1761.6	1713.1	1677.7	1651.6	1660.8	1615.0	1600.7	1551.0	1532.5	1532.5	1506.4
5°	1681.7	1604.5	1544.4	1506.4	1503.8	1438.5	1404.4	1341.7	1307.7	1282.8	1258.0
7.5°	1586.2	1486.8	1407.1	1361.4	1348.2	1271.0	1225.2	1162.6	1111.6	1078.8	1048.7
10°	1484.3	1365.2	1275.0	1222.7	1203.1	1119.4	1059.2	1001.6	946.8	912.8	881.4
12.5°	1386.1	1256.6	1157.3	1103.6	1078.8	992.6	931.1	871.0	818.6	783.3	751.9
15°	1295.9	1158.6	1054.0	1000.4	972.9	887.8	826.4	767.6	716.7	683.9	655.2
17.5°	1210.9	1071.1	966.4	914.1	884.0	805.5	746.7	689.1	643.3	613.3	587.1
20°	1146.9	1008.3	911.5	865.7	835.6	762.4	711.4	661.8	623.8	601.4	576.7
22.5°	1119.4	991.2	908.8	866.9	846.1	787.2	751.9	716.7	691.8	687.8	672.3
25°	1115.5	1003.0	935.0	899.7	886.7	842.1	821.2	799.0	780.6	785.8	788.5
27.5°	1098.4	993.9	937.7	907.6	897.1	860.5	844.8	823.9	810.7	817.2	819.9
30°	1039.7	942.9	890.6	865.7	855.3	818.6	805.5	782.0	771.5	772.8	771.5
32.5°	948.2	856.4	808.2	785.8	774.2	741.4	727.1	706.2	690.5	689.1	686.6
35°	836.9	754.5	710.0	690.5	678.6	651.2	638.1	618.5	600.3	598.9	596.2
37.5°	723.2	649.9	611.9	595.1	584.6	562.3	546.6	533.6	521.8	516.6	515.2
40°	613.3	548.0	520.4	507.4	499.5	476.0	468.1	455.1	446.0	440.8	439.4
42.5°	509.9	464.2	442.1	430.2	423.7	406.6	397.5	387.0	377.9	372.6	371.3
45°	432.7	395.0	374.0	364.9	359.6	343.9	337.4	326.9	319.2	315.1	313.9
47.5°	360.9	330.8	316.5	306.0	304.6	291.6	282.5	274.6	266.8	262.9	261.6
50°	295.5	270.7	258.9	252.4	251.1	238.0	231.5	225.0	218.3	214.4	212.0
52.5°	243.2	219.6	212.0	202.6	201.4	189.6	184.4	177.8	171.2	166.2	162.1
55°	192.2	173.9	166.2	158.2	156.8	143.8	138.6	130.7	124.3	119.1	113.8
57.5°	146.4	132.1	124.3	116.4	115.0	105.9	96.7	90.2	83.7	77.2	73.3
60°	107.2	92.9	83.7	79.7	75.8	66.7	60.1	54.9	49.6	45.8	41.9
62.5°	70.6	60.1	53.7	48.5	45.8	39.2	35.3	31.4	28.7	27.6	26.2
65°	43.3	36.6	31.4	28.7	28.7	24.9	22.3	19.6	18.2	18.2	17.1
67.5°	26.2	22.3	19.6	18.2	17.1	15.7	14.4	14.4	13.0	13.0	11.9
70°	15.7	14.4	13.0	11.9	11.9	11.9	11.9	11.9	10.5	10.5	10.5
72.5°	11.9	10.5	10.5	10.5	10.5	10.5	10.5	10.5	9.2	9.2	9.2
75°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	7.8
77.5°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8
80°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	6.6	6.6	6.6
82.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
85°	6.6	6.6	6.6	6.6	6.6	6.6	5.2	5.2	5.2	5.2	5.2
87.5°	6.6	5.2	5.2	5.2	5.2	5.2	3.8	3.8	3.8	3.8	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192763

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2	1841.2
2.5°	1493.3	1503.8	1488.1	1477.7	1467.2	1475.1	1438.5	1422.8
5°	1234.5	1222.7	1214.8	1205.7	1190.0	1192.7	1161.3	1146.9
7.5°	1021.3	1013.5	993.9	983.4	967.7	967.7	938.9	927.2
10°	852.6	840.9	822.5	813.4	799.0	787.2	772.8	761.1
12.5°	724.4	711.4	695.7	687.8	673.4	664.2	649.9	652.5
15°	629.0	616.0	601.4	593.7	581.9	572.7	561.0	554.5
17.5°	562.3	550.5	538.8	530.9	521.8	513.9	503.6	502.2
20°	557.0	548.0	541.3	536.1	528.3	523.1	517.9	511.3
22.5°	667.0	668.2	669.6	669.6	670.9	670.9	672.3	659.0
25°	787.2	801.5	801.5	805.5	817.2	817.2	814.7	809.5
27.5°	818.6	832.9	829.1	831.7	843.4	846.1	836.9	838.2
30°	766.3	779.5	771.5	772.8	780.6	780.6	769.0	774.2
32.5°	678.6	686.6	676.1	676.1	682.7	681.3	673.4	673.4
35°	585.7	589.8	580.5	584.6	584.6	580.5	572.7	572.7
37.5°	506.1	507.4	498.3	499.5	499.5	495.6	487.9	487.9
40°	430.2	434.1	426.4	428.9	426.4	422.3	418.4	417.0
42.5°	363.6	366.1	359.6	363.6	362.2	362.2	360.9	362.2
45°	306.0	308.7	303.5	306.0	307.3	306.0	302.1	303.5
47.5°	253.7	256.4	256.4	253.7	252.4	245.9	242.0	242.0
50°	205.3	203.9	202.6	198.7	194.9	190.9	186.9	186.9
52.5°	154.3	151.6	150.5	146.4	145.2	141.1	141.1	137.3
55°	105.9	104.7	104.7	100.7	100.7	96.7	95.4	95.4
57.5°	66.7	64.0	65.3	62.8	61.5	57.6	57.6	56.3
60°	38.0	36.6	36.6	35.3	33.9	31.4	31.4	31.4
62.5°	24.9	23.5	23.5	22.3	22.3	20.9	20.9	19.6
65°	15.7	14.4	14.4	13.0	13.0	11.9	11.9	11.9
67.5°	11.9	10.5	10.5	10.5	10.5	10.5	9.2	9.2
70°	10.5	10.5	9.2	9.2	9.2	9.2	9.2	9.2
72.5°	9.2	9.2	9.2	9.2	7.8	7.8	7.8	7.8
75°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8
77.5°	7.8	6.6	6.6	6.6	6.6	6.6	6.6	6.6
80°	6.6	6.6	6.6	6.6	6.6	6.6	5.2	5.2
82.5°	6.6	5.2	5.2	5.2	5.2	5.2	5.2	5.2
85°	5.2	3.8	3.8	3.8	3.8	3.8	3.8	3.8
87.5°	2.5	2.5	2.5	2.5	1.4	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)