

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192247

Luminaire Tested: **LDA6A40950D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192247
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26668)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40950D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3439.4 lumens
Efficiency: N/A
Efficacy: 69.1 lumens/watt
Spacing Criteria (0/90/45): 2.16 / 1.11 / 1.51
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192247

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192247

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95
2	104	98	92	88	102	96	91	87	93	89	85		89	86	83		87
3	97	88	82	76	94	87	81	76	84	79	75		81	77	73		79
4	90	80	72	67	87	78	72	66	76	70	66		74	69	65		72
5	83	72	65	59	81	71	64	59	69	63	58		67	62	57		66
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60
7	72	60	52	47	70	59	52	46	58	51	46		56	50	46		55
8	67	55	47	42	65	54	47	42	53	46	41		52	46	41		51
9	63	50	43	38	61	50	43	38	49	42	37		48	42	37		47
10	59	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	56783	56783	56783
5°	90271	55965	36171
10°	134350	53784	24432
15°	190903	51198	18388
20°	249898	48893	18785
25°	297555	49436	32464
30°	329987	47691	30574
35°	336643	40649	22493
40°	321774	31330	16638
45°	280626	22560	12552
50°	213946	16392	8349
55°	119432	11785	4865
60°	54930	8157	1963
65°	25904	4397	869
70°	12662	2116	914
75°	5994	1419	996
80°	2999	1484	1168
85°	1761	2327	1258



TEST NUMBER: P1192247

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.8	3.1
10°-20°	390.7	11.4
20°-30°	781.6	22.7
30°-40°	959.8	27.9
40°-50°	768.8	22.4
50°-60°	338.2	9.8
60°-70°	76.3	2.2
70°-80°	13.9	0.4
80°-90°	3.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1279.1	37.2
0°-40°	2238.8	65.1
0°-60°	3345.9	97.3
0°-90°	3439.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3439.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1036	1036	1036	1036	1036	
5°	1640	1412	1017	753	657	180
15°	3364	2268	902	420	324	981
25°	4919	2802	817	508	537	2263
35°	5030	2526	607	366	336	3114
45°	3620	1668	291	178	162	2752
55°	1250	618	123	71	51	1188
65°	200	126	34	11	7	229
75°	28	16	7	6	5	36
85°	3	3	4	4	2	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192247

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8
2.5°	1321.1	1287.2	1314.6	1291.1	1283.5	1280.7	1269.3	1261.8	1258.9	1232.6	1211.9
5°	1640.4	1600.8	1629.1	1594.2	1576.4	1567.0	1547.2	1522.7	1502.9	1452.9	1411.5
7.5°	2014.2	1971.8	1998.3	1948.2	1914.3	1897.5	1865.4	1818.3	1774.1	1694.1	1624.3
10°	2413.5	2378.7	2401.3	2331.6	2278.8	2251.6	2204.4	2144.2	2053.8	1937.0	1834.4
12.5°	2878.7	2828.7	2846.6	2753.4	2678.1	2639.5	2572.6	2478.4	2350.4	2191.2	2051.0
15°	3363.7	3316.6	3327.8	3209.1	3104.6	3050.9	2964.4	2830.7	2661.0	2453.0	2268.4
17.5°	3860.8	3796.8	3794.9	3653.6	3514.3	3446.5	3338.2	3162.1	2963.4	2690.3	2462.4
20°	4283.6	4228.0	4212.9	4066.1	3875.9	3796.8	3665.9	3447.4	3203.5	2887.1	2619.7
22.5°	4646.1	4582.1	4554.8	4382.5	4166.9	4074.5	3924.9	3660.2	3388.9	3031.3	2729.9
25°	4919.3	4866.6	4827.0	4633.0	4391.9	4288.3	4124.5	3838.2	3523.7	3132.0	2802.4
27.5°	5135.8	5065.2	5015.2	4803.4	4532.2	4423.0	4246.8	3936.1	3592.5	3172.4	2824.0
30°	5213.0	5142.5	5085.0	4859.0	4571.8	4452.2	4267.6	3938.1	3573.6	3142.3	2776.9
32.5°	5176.4	5102.9	5038.0	4801.5	4503.9	4378.7	4190.4	3856.1	3474.6	3041.5	2672.4
35°	5030.3	4972.0	4898.5	4660.2	4366.5	4230.0	4042.6	3699.8	3321.2	2884.3	2525.5
37.5°	4824.1	4733.8	4666.0	4432.4	4148.0	4008.7	3828.8	3499.2	3115.9	2696.0	2348.5
40°	4496.4	4405.1	4337.3	4112.2	3854.2	3713.9	3548.2	3233.7	2863.6	2472.8	2141.4
42.5°	4087.7	4003.0	3937.0	3728.0	3500.1	3363.7	3217.7	2926.8	2582.9	2225.1	1914.3
45°	3619.7	3537.8	3481.3	3299.6	3097.1	2976.6	2844.8	2587.7	2273.1	1948.2	1667.6
47.5°	3112.2	3028.4	2980.3	2817.5	2646.1	2536.9	2423.8	2201.6	1920.0	1641.3	1397.4
50°	2508.6	2427.7	2384.3	2247.8	2126.3	2025.5	1943.6	1765.6	1534.8	1315.5	1116.8
52.5°	1837.3	1774.1	1742.1	1647.9	1575.4	1500.1	1447.4	1323.1	1154.4	999.1	849.4
55°	1249.6	1197.8	1182.7	1124.3	1084.8	1044.3	1006.6	934.1	820.2	717.5	617.8
57.5°	781.7	775.9	786.3	734.6	716.6	699.7	670.5	630.0	558.5	494.4	434.1
60°	501.0	495.4	490.7	471.7	463.3	451.0	436.9	413.4	369.1	331.4	291.9
62.5°	317.3	313.6	318.2	306.9	295.7	295.7	280.6	267.5	240.1	217.5	189.3
65°	199.7	198.6	201.6	194.0	188.2	185.5	178.0	170.5	153.5	139.4	126.2
67.5°	126.2	125.3	127.1	125.3	118.7	116.7	112.0	107.3	96.1	87.6	78.2
70°	79.0	78.2	79.0	77.3	73.5	71.6	68.7	64.9	61.2	51.8	47.1
72.5°	48.0	47.1	48.0	47.1	44.3	44.3	40.5	38.6	35.8	30.2	26.3
75°	28.3	28.3	28.3	27.2	25.5	25.5	23.5	22.6	20.8	17.9	16.0
77.5°	16.0	16.0	16.0	16.0	15.1	15.1	14.1	13.2	12.2	10.4	10.4
80°	9.5	9.5	9.5	9.5	8.4	9.5	8.4	8.4	7.5	6.7	6.7
82.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7
85°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
87.5°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192247

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8
2.5°	1195.0	1164.8	1159.2	1127.2	1121.5	1103.6	1094.2	1077.2	1043.4	1025.4	1003.8
5°	1361.7	1314.6	1287.2	1229.8	1211.9	1181.9	1150.7	1109.3	1055.6	1017.0	976.6
7.5°	1544.3	1467.1	1409.7	1324.9	1293.9	1249.6	1195.0	1130.0	1054.7	997.2	939.7
10°	1728.0	1607.4	1518.9	1405.0	1359.8	1301.4	1222.3	1134.6	1040.5	966.2	894.6
12.5°	1896.4	1745.8	1624.3	1479.4	1419.1	1347.5	1243.8	1134.6	1022.6	934.1	850.3
15°	2080.2	1881.4	1723.3	1546.2	1471.9	1387.0	1260.0	1130.9	1002.9	902.1	809.8
17.5°	2229.9	1993.5	1799.5	1593.3	1504.8	1407.7	1261.8	1115.8	977.4	867.3	771.3
20°	2340.0	2078.2	1851.3	1620.5	1520.8	1415.2	1254.2	1096.2	951.1	838.1	740.1
22.5°	2420.1	2129.1	1877.6	1630.0	1521.7	1411.5	1241.1	1079.1	933.2	823.1	729.9
25°	2468.1	2154.6	1886.1	1626.2	1514.2	1399.3	1226.1	1064.0	921.9	817.3	731.6
27.5°	2472.8	2144.2	1863.6	1598.0	1483.1	1368.2	1195.0	1034.8	897.4	801.3	719.5
30°	2419.0	2085.7	1804.3	1535.9	1420.0	1307.0	1136.6	979.4	848.4	753.4	678.9
32.5°	2315.6	1983.2	1704.5	1441.6	1327.8	1217.5	1051.9	904.0	775.9	688.4	615.0
35°	2178.1	1853.2	1575.4	1328.7	1217.5	1113.0	952.0	806.9	690.2	607.4	540.5
37.5°	2015.1	1701.5	1441.6	1203.5	1096.2	999.1	843.8	711.9	599.9	523.5	462.4
40°	1829.6	1530.2	1286.4	1060.3	964.2	870.1	728.8	608.3	503.8	437.8	386.2
42.5°	1629.1	1348.4	1123.4	913.4	825.8	740.1	612.0	502.8	412.5	358.8	318.2
45°	1408.8	1156.4	953.9	770.2	686.5	615.9	495.4	405.0	336.1	291.0	262.7
47.5°	1173.3	953.9	777.7	619.6	546.1	485.9	387.1	319.3	270.2	239.2	215.7
50°	936.9	754.2	607.4	470.8	415.3	364.4	299.4	253.3	215.7	192.2	177.0
52.5°	715.7	567.8	452.0	345.6	307.9	273.1	230.7	199.7	171.4	154.4	143.1
55°	518.9	409.7	322.0	253.3	227.9	208.1	177.0	154.4	136.6	123.3	114.0
57.5°	361.6	283.4	225.1	184.5	169.4	155.4	133.7	118.7	106.5	97.0	89.4
60°	244.9	192.2	157.2	133.7	124.3	114.9	100.8	90.4	81.0	74.4	66.9
62.5°	161.0	131.8	112.0	97.9	89.4	82.9	74.4	65.9	58.4	52.7	46.1
65°	104.5	86.6	77.3	65.9	62.2	57.4	49.9	45.1	38.6	33.9	29.2
67.5°	65.9	56.5	49.9	43.4	40.5	36.7	33.0	28.3	24.5	20.8	17.9
70°	39.6	34.8	30.2	26.3	24.5	22.6	19.8	17.0	14.1	13.2	11.3
72.5°	23.5	20.8	17.9	16.0	15.1	14.1	12.2	10.4	9.5	8.4	7.5
75°	14.1	13.2	11.3	9.5	9.5	8.4	8.4	7.5	6.7	6.7	5.7
77.5°	9.5	8.4	7.5	6.7	6.7	6.7	5.7	5.7	5.7	5.7	5.7
80°	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
82.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	4.7	4.7
85°	2.8	2.8	2.8	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
87.5°	2.8	2.8	2.8	2.8	3.7	3.7	3.7	3.7	3.7	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192247

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8
2.5°	994.4	966.2	954.8	937.9	920.9	920.1	900.2	889.9	882.3	869.1	855.9
5°	949.1	905.9	879.5	857.0	835.2	820.2	791.0	771.3	753.4	734.6	710.0
7.5°	896.4	840.8	803.2	775.0	749.5	726.0	690.2	663.8	641.3	623.4	593.2
10°	839.9	775.9	728.8	697.7	671.4	637.5	602.7	573.5	549.0	529.3	500.0
12.5°	787.2	716.6	663.8	631.8	604.6	567.8	532.1	501.9	475.5	456.7	430.4
15°	738.3	663.8	607.4	575.3	547.1	510.4	474.6	444.5	420.1	400.2	376.7
17.5°	694.9	616.7	561.2	532.1	502.8	468.9	433.2	405.0	380.4	362.5	343.7
20°	665.7	591.4	537.7	510.4	485.0	452.9	424.7	402.1	378.5	364.4	353.2
22.5°	661.0	595.2	549.0	526.3	506.6	483.0	466.1	454.8	438.9	432.2	432.2
25°	670.5	614.0	577.3	559.3	543.4	530.2	521.7	514.2	508.5	509.5	509.5
27.5°	664.8	614.0	583.9	566.9	552.8	544.3	535.8	531.0	525.5	528.3	528.3
30°	628.1	579.1	553.7	535.8	522.6	515.1	502.8	497.1	490.7	491.6	488.7
32.5°	566.9	520.8	496.3	479.2	465.2	457.7	444.5	437.8	429.4	429.4	423.8
35°	495.4	452.0	429.4	414.3	401.2	393.6	381.4	374.7	366.3	361.6	358.8
37.5°	420.1	382.3	361.6	350.3	340.0	332.4	321.0	316.4	307.9	304.2	300.5
40°	350.3	323.0	303.2	293.8	285.3	278.7	268.4	264.6	257.1	254.3	250.4
42.5°	290.1	269.3	253.3	245.8	236.3	232.5	225.1	221.2	214.8	211.8	208.1
45°	242.0	225.1	211.8	205.3	199.7	194.9	187.4	184.5	178.0	175.1	173.3
47.5°	199.7	186.5	176.1	170.5	167.6	161.9	155.4	152.6	147.9	145.1	142.2
50°	163.9	153.5	145.1	140.3	138.4	132.8	127.1	125.3	120.5	118.7	115.9
52.5°	133.7	125.3	117.7	114.0	110.2	106.5	101.7	99.8	95.1	92.4	88.5
55°	107.3	98.8	92.4	89.4	87.6	82.0	77.3	74.4	70.6	65.9	63.1
57.5°	82.9	75.3	69.7	65.9	64.9	59.4	55.5	50.9	46.1	43.4	40.5
60°	61.2	54.7	49.0	45.1	44.3	38.6	33.9	31.0	27.2	25.5	24.5
62.5°	40.5	35.8	31.0	29.2	27.2	23.5	20.8	18.8	17.0	16.0	15.1
65°	25.5	21.6	18.8	17.9	16.0	14.1	13.2	12.2	11.3	10.4	9.5
67.5°	15.1	13.2	11.3	11.3	10.4	9.5	9.5	8.4	7.5	7.5	7.5
70°	9.5	8.4	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	6.7
72.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.7	5.7
75°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
77.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7
80°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
82.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	3.7	3.7	3.7
85°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	2.8
87.5°	3.7	3.7	3.7	3.7	3.7	2.8	2.8	2.8	2.8	2.8	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192247

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8
2.5°	845.6	829.6	827.7	824.0	820.2	824.9	822.0	814.5
5°	701.5	681.8	678.0	672.4	666.7	668.5	663.8	657.3
7.5°	581.0	560.2	556.5	549.8	544.3	543.4	538.6	532.1
10°	483.0	467.1	463.3	456.7	450.1	449.2	443.6	438.9
12.5°	413.4	398.3	394.6	387.9	382.3	380.4	375.8	372.0
15°	361.6	347.5	343.7	338.1	331.4	331.4	327.7	324.0
17.5°	329.6	317.3	312.6	307.9	302.2	301.4	299.4	296.7
20°	342.8	331.4	329.6	324.0	324.9	324.9	323.0	322.0
22.5°	427.5	423.8	431.3	425.7	436.0	439.8	441.6	441.6
25°	513.2	514.2	521.7	518.9	528.3	535.8	539.7	536.7
27.5°	528.3	529.3	532.1	531.0	538.6	543.4	546.1	539.7
30°	485.0	484.0	483.0	482.1	486.9	488.7	489.6	483.0
32.5°	418.1	415.3	416.2	411.4	413.4	413.4	417.1	407.7
35°	351.2	347.5	347.5	342.8	342.8	342.8	345.6	336.1
37.5°	294.7	291.0	290.1	285.3	284.3	282.6	285.3	276.8
40°	245.8	242.0	242.9	237.3	238.3	237.3	237.3	232.5
42.5°	203.4	200.6	199.7	197.7	198.6	198.6	201.6	197.7
45°	168.6	165.7	164.7	163.9	164.7	164.7	165.7	161.9
47.5°	140.3	136.6	135.5	133.7	133.7	130.8	130.8	127.1
50°	112.9	107.3	106.5	103.6	102.6	100.8	100.8	97.9
52.5°	85.7	81.0	79.0	77.3	76.2	74.4	74.4	72.5
55°	60.2	55.5	54.7	53.7	52.7	51.8	52.7	50.9
57.5°	37.6	35.8	34.8	33.9	33.0	32.0	32.0	31.0
60°	22.6	20.8	20.8	19.8	18.8	17.9	17.9	17.9
62.5°	14.1	13.2	13.2	12.2	12.2	11.3	11.3	11.3
65°	9.5	8.4	8.4	7.5	7.5	6.7	6.7	6.7
67.5°	6.7	6.7	6.7	6.7	5.7	5.7	5.7	5.7
70°	6.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
72.5°	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7
75°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
77.5°	4.7	4.7	4.7	4.7	3.7	3.7	3.7	3.7
80°	4.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
82.5°	3.7	3.7	3.7	3.7	3.7	2.8	2.8	2.8
85°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.0
87.5°	2.0	2.0	2.0	2.0	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)